



GreenSpace Accent Projector mini – A flexible, affordable and compact all-rounder for Retail applications

GreenSpace Accent Projector mini

The GreenSpace Accent Projector mini is the smallest size projector in the GreenSpace Accent range. With a diameter of only 80mm and integrated onboard driver, it offers a clean and small design to be discretely integrated in the store environment. The high performance and Philips Food LED recipes will deliver a strong fit to food retail and small city center store formats. The full range of beam angles and Philips Fashion LED flavors on the other hand, is creating a high quality of light to enhance the fashion collection, making this projector suitable for many different retail applications.

Benefits

- Clean, robust and neutral design
- High light output in a compact size
- Integrated onboard driver and small track adaptor allowing installation of numerous spots even in limited track space
- High energy efficiency, maintained over the full lifetime of the product

GreenSpace Accent Projector mini

Features

- Toolless installation and repositioning on Track
- Available with a high flux up to 3900lm, a wide range of optics, optional barndoor accessories
- Retail LED flavors for fashion application and Fresh food LED recipes for food application are included
- Available for normal mains (PSU), Digital Dimming (DALI)

Application

- Food Retail
- Fashion Retail
- Hospitality

Warnings and Safety

- During manipulation and/or maintenance, the product has to be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulating glove
- Luminaire should be installed and removed in accordance to the instructions in the Mounting Instruction

Specifications

Type	ST315T
Initial input power	22 W, 23.5 W, 24 W, 25 W, 26 W, 28 W, 28.5 W, 31.5 W
Beam spread luminaire	-, 24°
Initial luminous flux	1900 lm, 2000 lm, 2700 lm, 3900 lm
Initial correlated color temperature	2700 K, 3000 K, 3500 K, 4000 K
Light source color	-, 827 warm white, 830 warm white, 840 neutral white, fresh meat
Driver failure rate at 5000 h in %	1, 10 % 0.15% per 5000 hours
Ambient Temperature	+10 to +35 °C +10 to +40 °C
Driver	Power supply unit (Power supply unit)

Input voltage	220 to 240 V
Dimming	No, yes
Material	Housing: aluminum, metal-Plastic
Material	Bracket: Polymide
Material	Reflector: polycarbonate aluminum coated
Main color of the Luminaire	Black, black RAL 9004, silver, white
Connection	- (-) Track (Track)
Installation	On 3-circuit track
Warranty period	5 years
Accessories	Barndoor (BD) accessory, to be ordered separately

Versions



ST315T PSU BK Greenspace
Accent Projector mini product
photo



ST315T PSU WH Greenspace
Accent Projector mini product
photo

GreenSpace Accent Projector mini

Versions



GREENSPACE ACCENT
PROJECTOR MINI - - - 830 warm
white - Power supply unit -
Medium beam - Silver

Product details



ST315T PSU BK Greenspace
Accent Projector mini lens detail



ST315T PSU BK Greenspace
Accent Projector mini front view



ST315T BK Greenspace accent
Projector mini + ST710Z BD BK
Barndoor



ST315T PSU BK Greenspace
Accent Projector mini side view



ST315T PSU BK Greenspace
Accent Projector mini back view
hinge detail



ST315T PSU WH Greenspace
Accent Projector mini side view

GreenSpace Accent Projector mini

Product details



ST315T PSU WH Greenspace
Accent Projector mini front view



ST315T PSU WH Greenspace
Accent Projector mini back view
hinge detail



ST315T PSU WH Greenspace
Accent Projector mini lens detail



ST315T PSU SI Greenspace Accent
Projector mini lens detail



ST315T PSU SI Greenspace Accent
Projector mini side view



ST315T PSU SI Greenspace Accent
Projector mini back view hinge
detail



ST315T PSU SI Greenspace Accent
Projector mini front view

GreenSpace Accent Projector mini

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

Beam angle of light source	120 °
Cap-Base	-
CE mark	CE mark
Protection class IEC	Safety class I
Optical cover/lens type	Polymethyl methacrylate bowl/cover
Driver included	Yes
ENEC mark	ENEC mark
Lamp family code	-
Light source replaceable	No
Number of gear units	1 unit
Product Family Code	ST315T
Service tag	Yes
UL mark	-

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

-

Order Code	Full Product Name	Driver failure rate at 5000 h
910500465626	ST315T LED27S/CH PSU FR24 BK	1 %
910500465627	ST315T LED27S/830 PSU FR24 BK	10 %
910500465629	ST315T LED27S/830 PSU FR36 BK	10 %
910500465631	ST315T LED17S/FMT PSU FR24 BK	10 %
910500465633	ST315T LED20S/PW930 PSU FR12 BK	10 %
910500465634	ST315T LED27S/PW930 PSU FR18 BK	10 %
910500465636	ST315T LED27S/PW930 PSU FR24 BK	10 %
910500465637	ST315T LED27S/PW930 PSD FR24 BK	10 %
910500465638	ST315T LED27S/PW930 PSU FR30 BK	10 %
910500465639	ST315T LED27S/PW930 PSU FR36 BK	10 %
910500465640	ST315T LED27S/PW930 PSU FR60 BK	10 %
910500465641	ST315T LED27S/PW935 PSU FR24 BK	10 %
910500465643	ST315T LED20S/PC930 PSU FR12 BK	10 %
910500465645	ST315T LED27S/DNM PSU FR24 BK	10 %
910505100335	ST315T LED39S/830 PSU FR24 BK	1 %
910505100336	ST315T LED39S/830 PSU FR36 BK	1 %
910505100337	ST315T LED39S/830 PSU FR60 BK	1 %
910505100338	ST315T LED39S/827 PSU FR24 BK	1 %
910505100339	ST315T LED39S/827 PSU FR36 BK	1 %
910505100340	ST315T LED39S/840 PSU FR24 BK	1 %
910505100341	ST315T LED39S/840 PSU FR36 BK	1 %
910500465628	ST315T LED27S/830 PSU FR24 WH	10 %
910500465632	ST315T LED20S/PW930 PSU FR12 WH	10 %
910500465635	ST315T LED27S/PW930 PSU FR24 WH	10 %
910500465642	ST315T LED27S/PW940 PSU FR24 WH	10 %
910500465644	ST315T LED27S/PC930 PSU FR24 WH	10 %
910505100326	ST315T LED39S/830 PSU FR24 WH	1 %
910505100327	ST315T LED39S/830 PSU FR30 WH	1 %
910505100328	ST315T LED39S/830 PSU FR36 WH	1 %
910505100329	ST315T LED39S/830 PSU FR60 WH	1 %
910505100330	ST315T LED39S/827 PSU FR24 WH	1 %
910505100331	ST315T LED39S/827 PSU FR36 WH	1 %
910505100332	ST315T LED39S/840 PSU FR24 WH	1 %
910505100333	ST315T LED39S/840 PSU FR36 WH	1 %
910505100342	ST315T LED39S/830 PSU FR24 SI	1 %
910505100343	ST315T LED39S/830 PSU FR36 SI	1 %

Application Conditions

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500465626	ST315T LED27S/CH PSU FR24 BK	+10 to +40 °C	-	Not applicable
910500465627	ST315T LED27S/830 PSU FR24 BK	+10 to +40 °C	-	Not applicable
910500465629	ST315T LED27S/830 PSU FR36 BK	+10 to +40 °C	-	Not applicable

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500465631	ST315T LED17S/FMT PSU FR24 BK	+10 to +35 °C	-	Not applicable
910500465633	ST315T LED20S/PW930 PSU FR12 BK	+10 to +40 °C	-	Not applicable

GreenSpace Accent Projector mini

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500465634	ST315T LED27S/ PW930 PSU FR18 BK	+10 to +40 °C	-	Not applicable
910500465636	ST315T LED27S/ PW930 PSU FR24 BK	+10 to +40 °C	-	Not applicable
910500465637	ST315T LED27S/ PW930 PSD FR24 BK	+10 to +40 °C	-	Not applicable
910500465638	ST315T LED27S/ PW930 PSU FR30 BK	+10 to +40 °C	-	Not applicable
910500465639	ST315T LED27S/ PW930 PSU FR36 BK	+10 to +40 °C	-	Not applicable
910500465640	ST315T LED27S/ PW930 PSU FR60 BK	+10 to +40 °C	-	Not applicable
910500465641	ST315T LED27S/ PW935 PSU FR24 BK	+10 to +40 °C	-	Not applicable
910500465643	ST315T LED20S/ PC930 PSU FR12 BK	+10 to +40 °C	-	Not applicable
910500465645	ST315T LED27S/DNM PSU FR24 BK	+10 to +40 °C	-	Not applicable
910505100335	ST315T LED39S/830 PSU FR24 BK	+10 to +35 °C	-	Not applicable
910505100336	ST315T LED39S/830 PSU FR36 BK	+10 to +35 °C	-	Not applicable
910505100337	ST315T LED39S/830 PSU FR60 BK	+10 to +35 °C	-	Not applicable
910505100338	ST315T LED39S/827 PSU FR24 BK	+10 to +35 °C	-	Not applicable
910505100339	ST315T LED39S/827 PSU FR36 BK	+10 to +35 °C	-	Not applicable
910505100340	ST315T LED39S/840 PSU FR24 BK	+10 to +35 °C	-	Not applicable
910505100341	ST315T LED39S/840 PSU FR36 BK	+10 to +35 °C	-	Not applicable

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500465628	ST315T LED27S/830 PSU FR24 WH	+10 to +40 °C	-	Not applicable
910500465632	ST315T LED20S/ PW930 PSU FR12 WH	+10 to +40 °C	-	Not applicable
910500465635	ST315T LED27S/ PW930 PSU FR24 WH	+10 to +40 °C	-	Not applicable
910500465642	ST315T LED27S/ PW940 PSU FR24 WH	+10 to +40 °C	Not applicable	Not applicable
910500465644	ST315T LED27S/ PC930 PSU FR24 WH	+10 to +40 °C	-	Not applicable
910505100326	ST315T LED39S/830 PSU FR24 WH	+10 to +35 °C	-	Not applicable
910505100327	ST315T LED39S/830 PSU FR30 WH	+10 to +35 °C	-	Not applicable
910505100328	ST315T LED39S/830 PSU FR36 WH	+10 to +35 °C	-	Not applicable
910505100329	ST315T LED39S/830 PSU FR60 WH	+10 to +35 °C	-	Not applicable
910505100330	ST315T LED39S/827 PSU FR24 WH	+10 to +35 °C	-	Not applicable
910505100331	ST315T LED39S/827 PSU FR36 WH	+10 to +35 °C	-	Not applicable
910505100332	ST315T LED39S/840 PSU FR24 WH	+10 to +35 °C	-	Not applicable
910505100333	ST315T LED39S/840 PSU FR36 WH	+10 to +35 °C	-	Not applicable
910505100342	ST315T LED39S/830 PSU FR24 SI	+10 to +35 °C	-	Not applicable
910505100343	ST315T LED39S/830 PSU FR36 SI	+10 to +35 °C	-	Not applicable

Controls and Dimming

GreenSpace Accent Projector mini

Order Code	Full Product Name	Dimmable
910500465626	ST315T LED27S/CH PSU FR24 BK	No
910500465627	ST315T LED27S/830 PSU FR24 BK	No
910500465629	ST315T LED27S/830 PSU FR36 BK	No
910500465631	ST315T LED17S/FMT PSU FR24 BK	No
910500465633	ST315T LED20S/PW930 PSU FR12 BK	No
910500465634	ST315T LED27S/PW930 PSU FR18 BK	No
910500465636	ST315T LED27S/PW930 PSU FR24 BK	No
910500465637	ST315T LED27S/PW930 PSD FR24 BK	Yes
910500465638	ST315T LED27S/PW930 PSU FR30 BK	No
910500465639	ST315T LED27S/PW930 PSU FR36 BK	No
910500465640	ST315T LED27S/PW930 PSU FR60 BK	No
910500465641	ST315T LED27S/PW935 PSU FR24 BK	No
910500465643	ST315T LED20S/PC930 PSU FR12 BK	No
910500465645	ST315T LED27S/DNM PSU FR24 BK	No
910505100335	ST315T LED39S/830 PSU FR24 BK	No
910505100336	ST315T LED39S/830 PSU FR36 BK	No
910505100337	ST315T LED39S/830 PSU FR60 BK	No
910505100338	ST315T LED39S/827 PSU FR24 BK	No

Order Code	Full Product Name	Dimmable
910505100339	ST315T LED39S/827 PSU FR36 BK	No
910505100340	ST315T LED39S/840 PSU FR24 BK	No
910505100341	ST315T LED39S/840 PSU FR36 BK	No
910500465628	ST315T LED27S/830 PSU FR24 WH	No
910500465632	ST315T LED20S/PW930 PSU FR12 WH	No
910500465635	ST315T LED27S/PW930 PSU FR24 WH	No
910500465642	ST315T LED27S/PW940 PSU FR24 WH	No
910500465644	ST315T LED27S/PC930 PSU FR24 WH	No
910505100326	ST315T LED39S/830 PSU FR24 WH	No
910505100327	ST315T LED39S/830 PSU FR30 WH	No
910505100328	ST315T LED39S/830 PSU FR36 WH	No
910505100329	ST315T LED39S/830 PSU FR60 WH	No
910505100330	ST315T LED39S/827 PSU FR24 WH	No
910505100331	ST315T LED39S/827 PSU FR36 WH	No
910505100332	ST315T LED39S/840 PSU FR24 WH	No
910505100333	ST315T LED39S/840 PSU FR36 WH	No
910505100342	ST315T LED39S/830 PSU FR24 SI	No
910505100343	ST315T LED39S/830 PSU FR36 SI	No

General Information (1/2)

Order Code	Full Product Name	Flammability mark	Glare shielding		Glow-wire test
			Gear	accessories	
910500465626	ST315T LED27S/CH PSU FR24 BK	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910500465627	ST315T LED27S/830 PSU FR24 BK	-	-	-	Temperature 650 °C, duration 5 s
910500465629	ST315T LED27S/830 PSU FR36 BK	-	-	-	Temperature 650 °C, duration 5 s
910500465631	ST315T LED17S/FMT PSU FR24 BK	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 30 s
910500465633	ST315T LED20S/PW930 PSU FR12 BK	-	-	-	Temperature 650 °C, duration 5 s
910500465634	ST315T LED27S/PW930 PSU FR18 BK	-	-	-	Temperature 650 °C, duration 5 s
910500465636	ST315T LED27S/PW930 PSU FR24 BK	-	-	-	Temperature 650 °C, duration 5 s
910500465637	ST315T LED27S/	-	-	-	Temperature 650 °C, duration 5 s

Order Code	Full Product Name	Flammability mark	Glare shielding		Glow-wire test
			Gear	accessories	
910500465638	ST315T LED27S/PW930 PSD FR24 BK	-	-	-	Temperature 650 °C, duration 5 s
910500465639	ST315T LED27S/PW930 PSU FR36 BK	-	-	-	Temperature 650 °C, duration 5 s
910500465640	ST315T LED27S/PW930 PSU FR60 BK	-	-	-	Temperature 650 °C, duration 5 s
910500465641	ST315T LED27S/PW935 PSU FR24 BK	-	-	-	Temperature 650 °C, duration 5 s
910500465643	ST315T LED20S/PC930 PSU FR12 BK	-	-	-	Temperature 650 °C, duration 5 s
910500465645	ST315T LED27S/DNM PSU FR24 BK	-	-	-	Temperature 650 °C, duration 5 s
910505100335	ST315T LED39S/830 PSU FR24 BK	For mounting on normally	-	-	Temperature 650 °C, duration 5 s

GreenSpace Accent Projector mini

Order Code	Full Product Name	Flammability mark	Glare shielding		Glow-wire test
			Gear	accessories	
		flammable surfaces			
910505100336	ST315T LED39S/830 PSU FR36 BK	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100337	ST315T LED39S/830 PSU FR60 BK	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100338	ST315T LED39S/827 PSU FR24 BK	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100339	ST315T LED39S/827 PSU FR36 BK	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100340	ST315T LED39S/840 PSU FR24 BK	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100341	ST315T LED39S/840 PSU FR36 BK	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910500465628	ST315T LED27S/830 PSU FR24 WH	-	-	-	Temperature 650 °C, duration 5 s
910500465632	ST315T LED20S/ PW930 PSU FR12 WH	-	-	-	Temperature 650 °C, duration 5 s
910500465635	ST315T LED27S/ PW930 PSU FR24 WH	-	-	-	Temperature 650 °C, duration 5 s
910500465642	ST315T LED27S/ PW940 PSU FR24 WH	-	-	-	Temperature 650 °C, duration 5 s
910500465644	ST315T LED27S/ PC930 PSU FR24 WH	-	-	-	Temperature 650 °C, duration 5 s

Order Code	Full Product Name	Flammability mark	Glare shielding		Glow-wire test
			Gear	accessories	
910505100326	ST315T LED39S/830 PSU FR24 WH	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100327	ST315T LED39S/830 PSU FR30 WH	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100328	ST315T LED39S/830 PSU FR36 WH	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100329	ST315T LED39S/830 PSU FR60 WH	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100330	ST315T LED39S/827 PSU FR24 WH	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100331	ST315T LED39S/827 PSU FR36 WH	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100332	ST315T LED39S/840 PSU FR24 WH	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100333	ST315T LED39S/840 PSU FR36 WH	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100342	ST315T LED39S/830 PSU FR24 SI	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s
910505100343	ST315T LED39S/830 PSU FR36 SI	For mounting on normally flammable surfaces	-	-	Temperature 650 °C, duration 5 s

General Information (2/2)

GreenSpace Accent Projector mini

Order Code	Full Product Name	Number of light sources	Optic type
910500465626	ST315T LED27S/CH PSU FR24 BK	-	Medium beam
910500465627	ST315T LED27S/830 PSU FR24 BK	-	Medium beam
910500465629	ST315T LED27S/830 PSU FR36 BK	-	Medium beam
910500465631	ST315T LED17S/FMT PSU FR24 BK	-	Medium beam
910500465633	ST315T LED20S/PW930 PSU FR12 BK	-	Narrow beam
910500465634	ST315T LED27S/PW930 PSU FR18 BK	-	Narrow beam
910500465636	ST315T LED27S/PW930 PSU FR24 BK	-	Medium beam
910500465637	ST315T LED27S/PW930 PSD FR24 BK	-	Medium beam
910500465638	ST315T LED27S/PW930 PSU FR30 BK	-	Medium beam
910500465639	ST315T LED27S/PW930 PSU FR36 BK	-	Medium beam
910500465640	ST315T LED27S/PW930 PSU FR60 BK	-	Wide beam
910500465641	ST315T LED27S/PW935 PSU FR24 BK	-	Medium beam
910500465643	ST315T LED20S/PC930 PSU FR12 BK	-	Narrow beam
910500465645	ST315T LED27S/DNM PSU FR24 BK	-	Medium beam
910505100335	ST315T LED39S/830 PSU FR24 BK	1 pc	Medium beam
910505100336	ST315T LED39S/830 PSU FR36 BK	1 pc	Wide beam

Order Code	Full Product Name	Number of light sources	Optic type
910505100337	ST315T LED39S/830 PSU FR60 BK	1 pc	Very wide beam
910505100338	ST315T LED39S/827 PSU FR24 BK	1 pc	Medium beam
910505100339	ST315T LED39S/827 PSU FR36 BK	1 pc	Wide beam
910505100340	ST315T LED39S/840 PSU FR24 BK	1 pc	Medium beam
910505100341	ST315T LED39S/840 PSU FR36 BK	1 pc	Wide beam
910500465628	ST315T LED27S/830 PSU FR24 WH	-	Medium beam
910500465632	ST315T LED20S/PW930 PSU FR12 WH	-	Narrow beam
910500465635	ST315T LED27S/PW930 PSU FR24 WH	-	Medium beam
910500465642	ST315T LED27S/PW940 PSU FR24 WH	-	Medium beam
910500465644	ST315T LED27S/PC930 PSU FR24 WH	-	Medium beam
910505100326	ST315T LED39S/830 PSU FR24 WH	1 pc	Medium beam
910505100327	ST315T LED39S/830 PSU FR30 WH	1 pc	Medium beam
910505100328	ST315T LED39S/830 PSU FR36 WH	1 pc	Wide beam
910505100329	ST315T LED39S/830 PSU FR60 WH	1 pc	Very wide beam
910505100330	ST315T LED39S/827 PSU FR24 WH	1 pc	Medium beam
910505100331	ST315T LED39S/827 PSU FR36 WH	1 pc	Wide beam
910505100332	ST315T LED39S/840 PSU FR24 WH	1 pc	Medium beam
910505100333	ST315T LED39S/840 PSU FR36 WH	1 pc	Wide beam
910505100342	ST315T LED39S/830 PSU FR24 SI	1 pc	Medium beam
910505100343	ST315T LED39S/830 PSU FR36 SI	1 pc	Wide beam

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910500465626	ST315T LED27S/CH PSU FR24 BK	(0.46, 0.41)	2700 K	≥80	115 lm/W
910500465627	ST315T LED27S/830 PSU FR24 BK	(0.43, 0.40)	3000 K	≥80	113 lm/W
910500465629	ST315T LED27S/830 PSU FR36 BK	(0.43, 0.40)	3000 K	≥80	113 lm/W
910500465631	ST315T LED17S/FMT PSU FR24 BK	(0.406, 0.350)	3000 K	≥85	86 lm/W
910500465633	ST315T LED20S/PW930 PSU FR12 BK	(0.42, 0.38)	3000 K	≥90	85 lm/W
910500465634	ST315T LED27S/PW930 PSU FR18 BK	(0.42, 0.38)	3000 K	≥90	96 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910500465636	ST315T LED27S/PW930 PSU FR24 BK	(0.42, 0.38)	3000 K	≥90	96 lm/W
910500465637	ST315T LED27S/PW930 PSD FR24 BK	(0.42, 0.38)	3000 K	≥90	96 lm/W
910500465638	ST315T LED27S/PW930 PSU FR30 BK	(0.42, 0.38)	3000 K	≥90	96 lm/W
910500465639	ST315T LED27S/PW930 PSU FR36 BK	(0.42, 0.38)	3000 K	≥90	96 lm/W
910500465640	ST315T LED27S/PW930 PSU FR60 BK	(0.42, 0.38)	3000 K	≥90	96 lm/W

GreenSpace Accent Projector mini

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
	PW930 PSU FR60 BK				
910500465641	ST315T LED27S/ PW935 PSU FR24 BK	(0.40, 0.38) SDCM<3	3500 K	≥90	104 lm/W
910500465643	ST315T LED20S/ PC930 PSU FR12 BK	(0.42, 0.38) SDCM<3	3000 K	≥90	85 lm/W
910500465645	ST315T LED27S/DN M PSU FR24 BK	(0.42, 0.38) SDCM<3	3000 K	≥90	95 lm/W
910505100335	ST315T LED39S/830 PSU FR24 BK	(0.434, 0.403) SDCM <3	3000 K	≥80	122 lm/W
910505100336	ST315T LED39S/830 PSU FR36 BK	(0.434, 0.403) SDCM <3	3000 K	≥80	122 lm/W
910505100337	ST315T LED39S/830 PSU FR60 BK	(0.434, 0.403) SDCM <3	3000 K	≥80	122 lm/W
910505100338	ST315T LED39S/827 PSU FR24 BK	(0.458, 0.410) SDCM <3	2700 K	≥80	119 lm/W
910505100339	ST315T LED39S/827 PSU FR36 BK	(0.458, 0.410) SDCM <3	2700 K	≥80	119 lm/W
910505100340	ST315T LED39S/840 PSU FR24 BK	(0.382, 0.380) SDCM <3	4000 K	≥80	129 lm/W
910505100341	ST315T LED39S/840 PSU FR36 BK	(0.382, 0.380) SDCM <3	4000 K	≥80	129 lm/W
910500465628	ST315T LED27S/830 PSU FR24 WH	(0.43, 0.40) SDCM<3	3000 K	≥80	112 lm/W
910500465632	ST315T LED20S/ PW930 PSU FR12 WH	(0.42, 0.38) SDCM<3	3000 K	≥90	85 lm/W
910500465635	ST315T LED27S/ SDCM<3	(0.42, 0.38) SDCM<3	3000 K	≥90	96 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
	PW930 PSU FR24 WH				
910500465642	ST315T LED27S/ PW940 PSU FR24 WH	(0.37, 0.36) SDCM<3	4000 K	≥90	108 lm/W
910500465644	ST315T LED27S/ PC930 PSU FR24 WH	(0.42, 0.38) SDCM<3	3000 K	≥90	95 lm/W
910505100326	ST315T LED39S/830 PSU FR24 WH	(0.434, 0.403) SDCM <3	3000 K	≥80	122 lm/W
910505100327	ST315T LED39S/830 PSU FR30 WH	(0.434, 0.403) SDCM <3	3000 K	≥80	122 lm/W
910505100328	ST315T LED39S/830 PSU FR36 WH	(0.434, 0.403) SDCM <3	3000 K	≥80	122 lm/W
910505100329	ST315T LED39S/830 PSU FR60 WH	(0.434, 0.403) SDCM <3	3000 K	≥80	122 lm/W
910505100330	ST315T LED39S/827 PSU FR24 WH	(0.458, 0.410) SDCM <3	2700 K	≥80	119 lm/W
910505100331	ST315T LED39S/827 PSU FR36 WH	(0.458, 0.410) SDCM <3	2700 K	≥80	119 lm/W
910505100332	ST315T LED39S/840 PSU FR24 WH	(0.382, 0.380) SDCM <3	4000 K	≥80	129 lm/W
910505100333	ST315T LED39S/840 PSU FR36 WH	(0.382, 0.380) SDCM <3	4000 K	≥80	129 lm/W
910505100342	ST315T LED39S/830 PSU FR24 SI	(0.434, 0.403) SDCM <3	3000 K	≥80	122 lm/W
910505100343	ST315T LED39S/830 PSU FR36 SI	(0.434, 0.403) SDCM <3	3000 K	≥80	122 lm/W

Initial Performance (IEC Compliant) (2/2)

GreenSpace Accent Projector mini

Order Code	Full Product Name	Initial luminous flux	Initial input power
910500465626	ST315T LED27S/CH PSU FR24 BK	3900 lm	23.5 W
910500465627	ST315T LED27S/830 PSU FR24 BK	2700 lm	24 W
910500465629	ST315T LED27S/830 PSU FR36 BK	2700 lm	24 W
910500465631	ST315T LED17S/FMT PSU FR24 BK	1900 lm	22 W
910500465633	ST315T LED20S/PW930 PSU FR12 BK	2000 lm	23.5 W
910500465634	ST315T LED27S/PW930 PSU FR18 BK	2700 lm	28 W
910500465636	ST315T LED27S/PW930 PSU FR24 BK	2700 lm	28 W
910500465637	ST315T LED27S/PW930 PSD FR24 BK	2700 lm	28 W
910500465638	ST315T LED27S/PW930 PSU FR30 BK	2700 lm	28 W
910500465639	ST315T LED27S/PW930 PSU FR36 BK	2700 lm	28 W
910500465640	ST315T LED27S/PW930 PSU FR60 BK	2700 lm	28 W
910500465641	ST315T LED27S/PW935 PSU FR24 BK	2700 lm	26 W
910500465643	ST315T LED20S/PC930 PSU FR12 BK	2000 lm	23.5 W
910500465645	ST315T LED27S/DNM PSU FR24 BK	2700 lm	28.5 W
910505100335	ST315T LED39S/830 PSU FR24 BK	3900 lm	31.5 W
910505100336	ST315T LED39S/830 PSU FR36 BK	3900 lm	31.5 W
910505100337	ST315T LED39S/830 PSU FR60 BK	3900 lm	31.5 W
910505100338	ST315T LED39S/827 PSU FR24 BK	3900 lm	31.5 W
910505100339	ST315T LED39S/827 PSU FR36 BK	3900 lm	31.5 W

Mechanical and Housing

Order Code	Full Product Name	Color	Diameter	Width
910500465626	ST315T LED27S/CH PSU FR24 BK	Black	-	-
910500465627	ST315T LED27S/830 PSU FR24 BK	Black	-	-
910500465629	ST315T LED27S/830 PSU FR36 BK	Black	-	-
910500465631	ST315T LED17S/FMT PSU FR24 BK	Black RAL 9004	-	-
910500465633	ST315T LED20S/PW930 PSU FR12 BK	Black	-	-
910500465634	ST315T LED27S/PW930 PSU FR18 BK	Black	-	-
910500465636	ST315T LED27S/PW930 PSU FR24 BK	Black	-	-
910500465637	ST315T LED27S/PW930 PSD FR24 BK	Black	-	-
910500465638	ST315T LED27S/PW930 PSU FR30 BK	Black	-	-
910500465639	ST315T LED27S/PW930 PSU FR36 BK	Black	-	-
910500465640	ST315T LED27S/PW930 PSU FR60 BK	Black	-	-
910500465641	ST315T LED27S/PW935 PSU FR24 BK	Black	-	-
910500465643	ST315T LED20S/PC930 PSU FR12 BK	Black	-	-
910500465645	ST315T LED27S/DNM PSU FR24 BK	Black	-	-
910505100335	ST315T LED39S/830 PSU FR24 BK	Black	-	-

Order Code	Full Product Name	Initial luminous flux	Initial input power
910505100340	ST315T LED39S/840 PSU FR24 BK	3900 lm	31.5 W
910505100341	ST315T LED39S/840 PSU FR36 BK	3900 lm	31.5 W
910500465628	ST315T LED27S/830 PSU FR24 WH	2700 lm	24 W
910500465632	ST315T LED20S/PW930 PSU FR12 WH	2000 lm	23.5 W
910500465635	ST315T LED27S/PW930 PSU FR24 WH	2700 lm	28 W
910500465642	ST315T LED27S/PW940 PSU FR24 WH	2700 lm	25 W
910500465644	ST315T LED27S/PC930 PSU FR24 WH	2700 lm	28.5 W
910505100326	ST315T LED39S/830 PSU FR24 WH	3900 lm	31.5 W
910505100327	ST315T LED39S/830 PSU FR30 WH	3900 lm	31.5 W
910505100328	ST315T LED39S/830 PSU FR36 WH	3900 lm	31.5 W
910505100329	ST315T LED39S/830 PSU FR60 WH	3900 lm	31.5 W
910505100330	ST315T LED39S/827 PSU FR24 WH	3900 lm	31.5 W
910505100331	ST315T LED39S/827 PSU FR36 WH	3900 lm	31.5 W
910505100332	ST315T LED39S/840 PSU FR24 WH	3900 lm	31.5 W
910505100333	ST315T LED39S/840 PSU FR36 WH	3900 lm	31.5 W
910505100342	ST315T LED39S/830 PSU FR24 SI	3900 lm	31.5 W
910505100343	ST315T LED39S/830 PSU FR36 SI	3900 lm	31.5 W

GreenSpace Accent Projector mini

Order Code	Full Product Name	Color	Diameter	Width
910505100331	ST315T LED39S/827 PSU FR36 WH	White	-	-
910505100332	ST315T LED39S/840 PSU FR24 WH	White	-	-
910505100333	ST315T LED39S/840 PSU FR36 WH	White	-	-

Order Code	Full Product Name	Color	Diameter	Width
910505100342	ST315T LED39S/830 PSU FR24 SI	Silver	-	-
910505100343	ST315T LED39S/830 PSU FR36 SI	Silver	-	-

