



Robust, connectable luminaire with outstanding performance.

Pacific LED Gen5

Pacific LED gen5 is an innovative and best-in-class LED waterproof luminaire that is praised for its optimal performance. It meets the demanding requirements of contemporary and harsh industries. It is a very robust, compact and reliable luminaire with excellent quality of light. With a high degree of mechanical (IK08), water and dust protection (IP66), combined with proven chemical resistance, the Pacific LED gen5 can perfectly withstand the harsh conditions of the automotive, food and heavy industries. But it also performs well in parking garages and warehouses. Pacific LED gen5 luminaires provide superior, artefact-free light quality and homogeneous light, offered with multiple optics and broad range of light outputs (up to 15,000 lm). This ensures more flexibility in optimized light scheme planning. They are also designed with a circular approach, which means these fully-serviceable luminaires can be upgraded to extend their overall lifecycle. The luminaires stand out because of their quick and easy installation that facilitates through wiring and various connection and mounting options. But also, because of their attractive TCO, energy efficiency, and ease of maintenance – with minimum of disruption to operations in demanding applications. To make the Pacific LED gen5 even more complete, system integration with Interact Industry opens up additional opportunities for optimized efficiency, energy savings, improved light management, productivity, and safety. Making it future proof in every aspect. Discover Pacific LED gen5. Optimal performance for demanding environments.

Pacific LED Gen5

Benefits

- Long service life offering peace of mind on your lighting installation.
- Suitable for your industrial application due to wide coverage including food production, heavy and chemical industries, automotive, parking garages and warehousing.
- Lowers your maintenance investments due to easy servicing and parts replacements with a modular approach.
- Can be integrated into an Interact connected lighting installation to optimize your operations and maximize energy saving and insights.

Features

- Highly energy efficient and long lifetime: up to 160 lm/W and lifetime up to 100,000 hrs L80.
- Wide application coverage with extensive lumen output (up to 15000 lumen) and optics choice, combined with high quality chemical-resistant materials.
- Robust and compact product architecture, with high water and dust protection (IP66), combined with a high degree of mechanical protection (IK08).
- High uniformity, glare control and artefact-free light distributions.
- Hassle-free installation and maintenance.

Application

- Food Processing
- Parking Garages
- Manufacturing
- Warehouses/distribution centers

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Versions










Pacific LED gen5, L700



Pacific LED gen5, Wieland connector




Pacific LED Gen5

Dimensional drawing



Pacific LED Gen5

Dimensional drawing



Product details

Pacific LED gen5, looping connection, 2 entry on one side



Pacific LED gen5 with push in 7-pole (PI7) connector



Pacific LED gen5, Wieland connector




Pacific LED gen5 with WAGO connector



Pacific LED Gen5

Product details



Pacific LED gen5 connection through WAGO connector side view



Pacific LED gen5 with push in 5-pole (PI5) connecto



Pacific LED gen5 with Wieland connector



Pacific LED gen5 connection through WAGO connector

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC plus mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Light source replaceable	Yes
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Housing Color	White
Approval and Application	
Mech. impact protection code	IK08
Ingress protection code	IP66
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Application Conditions	
Suitable for random switching	No

General Information

Order Code	Full Product Name	Product family code	Service tag
910925867731	WT490C 80S/840 PSU NB-HRO PI5 L1800	WT490C	Yes
910925867732	WT490C 80S/840 PSD NB-HRO PI5 L1800	WT490C	Yes
910925867733	WT490C 80S/840 PSU WB TW3 PI5 L1800	WT490C	Yes
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	WT490C	Yes
910925867735	WT490C 80S/840 PSD WB PI5 L1800	WT490C	Yes
910925867736	WT490C 80S/840 PSD WB TW3 PI7 L1800	WT490C	Yes
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	WT490C	Yes
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	WT490C	Yes
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	WT490C	Yes
910925867740	WT490C 100S/840 PSD WB PI5 L1800	WT490C	Yes
910925867741	WT490C 120S/840 PSD WB PI5 L1800	WT490C	Yes
910925868292	WT490C 80S/840 PSU WB PI5 L1800	WT490C	Yes
910925868293	WT490C 100S/840 PSU WB PI5 L1800	WT490C	Yes
910925868294	WT490C 120S/840 PSU WB PI5 L1800	WT490C	Yes
910925868516	WT490C 80S/840 SIA WB IA9 PI5 L1800	WT490C	Yes
910925868697	WT490C 80S/840 PSU O L1800	WT490C	-
910925868698	WT490C 80S/840 PSU PCO L1800	WT490C	-
910925868701	WT495C 80S/840 PSU WB PI5 L1800	WT495C	-
910925868703	WT495C 80S/840 PSD WB PI5 L1800	WT495C	-
910925868709	WT490C 80S/840 PSU CLII WB WA7 L1800	WT490C	-
910925869405	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1800	WT490C	-
910925869406	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1800	WT490C	-
910925869607	WT490C 150S/840 PSD WB PI5 L1800	WT490C	-
910925869611	WT490C 150S/840 PSU WB PI5 L1800	WT490C	-
910925868704	WT492C 64S/840 PSU WB W5 L1200	WT492C	-
910925868705	WT492C 80S/840 PSU WB W5 L1800	WT492C	-
910925868706	WT492C 64S/840 PSD WB W5 L1200	WT492C	-
910925868707	WT492C 80S/840 PSD WB W5 L1800	WT492C	-
910770229590	WT490C 42S/830 PSU WB PI5 L1200	WT490C	-
910925867704	WT490C 42S/840 PSD WB PI5 L1200	WT490C	Yes

Order Code	Full Product Name	Product family code	Service tag
910925867705	WT490C 64S/840 PSU NB-HRO PI5 L1200	WT490C	Yes
910925867706	WT490C 64S/840 PSD NB-HRO PI5 L1200	WT490C	Yes
910925867707	WT490C 64S/840 PSU WB TW1 PI5 L1200	WT490C	Yes
910925867708	WT490C 64S/840 PSU WB TW3 PI5 L1200	WT490C	Yes
910925867709	WT490C 64S/840 PSU WB TCW5 PI5 L1200	WT490C	Yes
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	WT490C	Yes
910925867711	WT490C 64S/840 PSU WB ELP3TW1 PI5 L12	WT490C	Yes
910925867712	WT490C 64S/840 PSD WB PI5 L1200	WT490C	Yes
910925867713	WT490C 64S/840 PSD WB TW1 PI5 L1200	WT490C	Yes
910925867714	WT490C 64S/840 PSD WB TW3 PI7 L1200	WT490C	Yes
910925867715	WT490C 64S/840 PSD WB ELD3PI7 L1200	WT490C	Yes
910925867716	WT490C 64S/840 PSD WB ELD3TW1 PI7 L12	WT490C	Yes
910925867717	WT490C 64S/840 PSU VWB PI5L1200	WT490C	Yes
910925867718	WT490C 64S/840 PSD VWB PI5L1200	WT490C	Yes
910925867719	WT490C 80S/840 PSU NB-HRO PI5 L1200	WT490C	Yes
910925867720	WT490C 80S/840 PSD NB-HRO PI5 L1200	WT490C	Yes
910925867721	WT490C 80S/840 PSU WB TW1 PI5 L1200	WT490C	Yes
910925867722	WT490C 80S/840 PSU WB TW3 PI5 L1200	WT490C	Yes
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	WT490C	Yes
910925867724	WT490C 80S/840 PSD WB PI5 L1200	WT490C	Yes
910925867725	WT490C 80S/840 PSD WB TW1 PI5 L1200	WT490C	Yes
910925867726	WT490C 80S/840 PSD WB TW3 PI7 L1200	WT490C	Yes
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	WT490C	Yes
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	WT490C	Yes
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	WT490C	Yes
910925867743	WT490C 64S/840 PSU NB-HRO WA7 L1200	WT490C	Yes
910925867744	WT490C 64S/840 PSD NB-HRO WA7 L1200	WT490C	Yes
910925868247	WT490C 64S/840 PSU WB WA7 L1200	WT490C	Yes
910925868249	WT490C 64S/840 PSU WB TW3 WA7 L1200	WT490C	Yes
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	WT490C	Yes
910925868252	WT490C 64S/840 PSD WB WA7 L1200	WT490C	Yes
910925868253	WT490C 64S/840 PSD WB TW3 WA7 L1200	WT490C	Yes
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	WT490C	Yes
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	WT490C	Yes
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	WT490C	Yes
910925868257	WT490C 80S/840 PSU NB-HRO WA7 L1200	WT490C	Yes
910925868258	WT490C 80S/840 PSD NB-HRO WA7 L1200	WT490C	Yes
910925868259	WT490C 80S/840 PSU WB WA7 L1200	WT490C	Yes
910925868260	WT490C 80S/840 PSU WB TW3 WA7 L1200	WT490C	Yes
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	WT490C	Yes
910925868262	WT490C 80S/840 PSD WB WA7 L1200	WT490C	Yes
910925868263	WT490C 80S/840 PSD WB TW3 WA7 L1200	WT490C	Yes
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	WT490C	Yes
910925868265	WT490C 80S/840 PSU VWB WA7L1200	WT490C	Yes
910925868266	WT490C 80S/840 PSD VWB WA7L1200	WT490C	Yes
910925868288	WT490C 42S/840 PSU WB PI5 L1200	WT490C	Yes
910925868289	WT490C 64S/840 PSU WB PI5 L1200	WT490C	Yes
910925868290	WT490C 80S/840 PSU WB PI5 L1200	WT490C	Yes
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	WT490C	Yes
910925868611	WT490C 42S/840 PSU WB WA7 L1200	WT490C	Yes
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	WT490C	Yes
910925868613	WT490C 42S/840 PSU WB TW3 WA7 L1200	WT490C	Yes

Order Code	Full Product Name	Product family code	Service tag
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	WT490C	Yes
910925868615	WT490C 42S/840 PSD WB WA7 L1200	WT490C	Yes
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	WT490C	Yes
910925868617	WT490C 42S/840 PSD WB TW3 WA7 L1200	WT490C	Yes
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	WT490C	Yes
910925868619	WT490C 64S/840 PSU NB-HRO TW3 WA7 L12	WT490C	Yes
910925868620	WT490C 64S/840 PSD NB-HRO TW3 WA7 L12	WT490C	Yes
910925868621	WT490C 80S/840 PSU NB-HRO TW3 WA7 L12	WT490C	Yes
910925868622	WT490C 80S/840 PSD NB-HRO TW3 WA7 L12	WT490C	Yes
910925868691	WT490C 35S/840 PSU WB PI5 L1200	WT490C	-
910925868693	WT490C 35S/840 PSU WB WA7 L1200	WT490C	-
910925868695	WT490C 64S/840 PSU O L1200	WT490C	-
910925868696	WT490C 64S/840 PSU PCO L1200	WT490C	-
910925868699	WT495C 64S/840 PSU WB PI5 L1200	WT495C	-
910925868702	WT495C 64S/840 PSD WB PI5 L1200	WT495C	-
910925868708	WT490C 64S/840 PSU CLII WB WA7 L1200	WT490C	-
910925869401	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1200	WT490C	-
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	WT490C	-
910925869403	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1200	WT490C	-
910925869404	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1200	WT490C	-
910925869410	WT490C 42S/840 PSU WB TW3x2.5 PI5 L1200	WT490C	-
910925869606	WT490C 100S/840 PSD WB PI5 L1200	WT490C	-
910925869608	WT490C 100S/840 PSU WB WA7 L1200	WT490C	-
910925869609	WT490C 100S/840 PSD WB WA7 L1200	WT490C	-
910925869610	WT490C 100S/840 PSU WB PI5 L1200	WT490C	-
910925868412	WT490C 64S/840 PSD WB PI5 L1600	WT490C	Yes
910925868413	WT490C 64S/840 PSU WB TW3 PI5 L1600	WT490C	Yes
910925868414	WT490C 64S/840 PSU WB PI5 L1600	WT490C	Yes
910925868415	WT490C 80S/840 PSU WB PI5 L1600	WT490C	Yes
910925868416	WT490C 80S/840 PSD WB PI5 L1600	WT490C	Yes
910925868417	WT490C 80S/840 PSU WB TW3 PI5 L1600	WT490C	Yes
910925868418	WT490C 64S/840 PSD WB WA7 L1600	WT490C	Yes
910925868419	WT490C 64S/840 PSU WB TW3 WA7 L1600	WT490C	Yes
910925868420	WT490C 64S/840 PSU WB WA7 L1600	WT490C	Yes
910925868421	WT490C 80S/840 PSU WB WA7 L1600	WT490C	Yes
910925868422	WT490C 80S/840 PSD WB WA7 L1600	WT490C	Yes
910925868423	WT490C 80S/840 PSU WB TW3 WA7 L1600	WT490C	Yes
910925868692	WT490C 35S/840 PSU WB PI5 L1600	WT490C	-
910925868694	WT490C 35S/840 PSU WB WA7 L1600	WT490C	-
910925869407	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1600	WT490C	-
910925869408	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1600	WT490C	-
910925867703	WT490C 23S/840 PSD WB PI5 L700	WT490C	Yes
910925868287	WT490C 23S/840 PSU WB PI5 L700	WT490C	Yes
910925868250	WT490C 64S/840 PSU WB TCW5W5 L1200	WT490C	Yes
910925868510	WT490C 64S/840 PSU WB W5 L1200	WT490C	Yes
910925868511	WT490C 80S/840 PSU WB W5 L1200	WT490C	Yes
910925868512	WT490C 64S/840 PSD WB W5 L1200	WT490C	Yes
910925868513	WT490C 80S/840 PSD WB W5 L1200	WT490C	Yes

Light Technical (1/2)

Pacific LED Gen5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
		(K)	(lm/W)	(lm)	
910925867731	WT490C 80S/840 PSU NB-HRO PI5 L1800	4000 K	165 lm/W	8,000 lm	Narrow beam - High-rack optic
910925867732	WT490C 80S/840 PSD NB-HRO PI5 L1800	4000 K	165 lm/W	8,000 lm	Narrow beam - High-rack optic
910925867733	WT490C 80S/840 PSU WB TW3 PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	4000 K	154 lm/W	8,000 lm	Wide beam
910925867735	WT490C 80S/840 PSD WB PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925867736	WT490C 80S/840 PSD WB TW3 PI7 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	4000 K	154 lm/W	8,000 lm	Wide beam
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	4000 K	165 lm/W	8,000 lm	Very wide beam
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	4000 K	165 lm/W	8,000 lm	Very wide beam
910925867740	WT490C 100S/840 PSD WB PI5 L1800	4000 K	161 lm/W	10,000 lm	Wide beam
910925867741	WT490C 120S/840 PSD WB PI5 L1800	4000 K	158 lm/W	12,000 lm	Wide beam
910925868292	WT490C 80S/840 PSU WB PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925868293	WT490C 100S/840 PSU WB PI5 L1800	4000 K	161 lm/W	10,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
		(K)	(lm/W)	(lm)	
910925868294	WT490C 120S/840 PSU WB PI5 L1800	4000 K	158 lm/W	12,000 lm	Wide beam
910925868516	WT490C 80S/840 SIA WB IA9 PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925868697	WT490C 80S/840 PSU O L1800	4000 K	157 lm/W	7,600 lm	Opal
910925868698	WT490C 80S/840 PSU PCO L1800	4000 K	136 lm/W	6,600 lm	Opal
910925868701	WT495C 80S/840 PSU WB PI5 L1800	4000 K	157 lm/W	8,000 lm	Wide beam
910925868703	WT495C 80S/840 PSD WB PI5 L1800	4000 K	157 lm/W	8,000 lm	Wide beam
910925868709	WT490C 80S/840 PSU CLII WB WA7 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925869405	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925869406	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925869607	WT490C 150S/840 PSD WB PI5 L1800	4000 K	155 lm/W	15,000 lm	Very wide beam
910925869611	WT490C 150S/840 PSU WB PI5 L1800	4000 K	155 lm/W	15,000 lm	Very wide beam
910925868704	WT492C 64S/840 PSU WB W5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868705	WT492C 80S/840 PSU WB W5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925868706	WT492C 64S/840 PSD WB W5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925868707	WT492C 80S/840 PSD WB W5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam

Pacific LED Gen5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910770229590	WT490C 42S/830 PSU WB PI5 L1200	3000 K	157 lm/W	4,200 lm	Wide beam
910925867704	WT490C 42S/840 PSD WB PI5 L1200	4000 K	162 lm/W	4,200 lm	Wide beam
910925867705	WT490C 64S/840 PSU NB-HRO PI5 L1200	4000 K	160 lm/W	6,400 lm	Narrow beam - High-rack optic
910925867706	WT490C 64S/840 PSD NB-HRO PI5 L1200	4000 K	162 lm/W	6,400 lm	Narrow beam - High-rack optic
910925867707	WT490C 64S/840 PSU WB TW1 PI5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925867708	WT490C 64S/840 PSU WB TW3 PI5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925867709	WT490C 64S/840 PSU WB TCW5 PI5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	4000 K	146 lm/W	6,400 lm	Wide beam
910925867711	WT490C 64S/840 PSU WB ELP3TW1 PI5 L12	4000 K	146 lm/W	6,400 lm	Wide beam
910925867712	WT490C 64S/840 PSD WB PI5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925867713	WT490C 64S/840 PSD WB TW1 PI5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925867714	WT490C 64S/840 PSD WB TW3 PI7 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925867715	WT490C 64S/840 PSD	4000 K	147 lm/W	6,400 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
	WB ELD3PI7 L1200				
910925867716	WT490C 64S/840 PSD WB ELD3TW1 PI7 L12	4000 K	147 lm/W	6,400 lm	Wide beam
910925867717	WT490C 64S/840 PSU VWB PI5L1200	4000 K	160 lm/W	6,400 lm	Very wide beam
910925867718	WT490C 64S/840 PSD VWB PI5L1200	4000 K	162 lm/W	6,400 lm	Very wide beam
910925867719	WT490C 80S/840 PSU NB-HRO PI5 L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925867720	WT490C 80S/840 PSD NB-HRO PI5 L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925867721	WT490C 80S/840 PSU WB TW1 PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925867722	WT490C 80S/840 PSU WB TW3 PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
910925867724	WT490C 80S/840 PSD WB PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925867725	WT490C 80S/840 PSD WB TW1 PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925867726	WT490C 80S/840 PSD WB TW3 PI7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam

Pacific LED Gen5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925867728	WT490C 80S/840 PSU VWB P15 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
910925867729	WT490C 80S/840 PSD VWB P15 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
910925867743	WT490C 64S/840 PSU NB-HRO WA7 L1200	4000 K	160 lm/W	6,400 lm	Narrow beam - High-rack optic
910925867744	WT490C 64S/840 PSD NB-HRO WA7 L1200	4000 K	162 lm/W	6,400 lm	Narrow beam - High-rack optic
910925868247	WT490C 64S/840 PSU WB WA7 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868249	WT490C 64S/840 PSU WB TW3 WA7 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	4000 K	146 lm/W	6,400 lm	Wide beam
910925868252	WT490C 64S/840 PSD WB WA7 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925868253	WT490C 64S/840 PSD WB TW3 WA7 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	4000 K	147 lm/W	6,400 lm	Wide beam
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	4000 K	160 lm/W	6,400 lm	Very wide beam
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	4000 K	162 lm/W	6,400 lm	Very wide beam
910925868257	WT490C 80S/840 PSU NB-HRO WA7 L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925868258	WT490C 80S/840 PSD NB-HRO WA7 L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925868259	WT490C 80S/840 PSU WB WA7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868260	WT490C 80S/840 PSU WB TW3 WA7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
910925868262	WT490C 80S/840 PSD WB WA7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868263	WT490C 80S/840 PSD WB TW3 WA7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
910925868265	WT490C 80S/840 PSU VWB WA7L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
910925868266	WT490C 80S/840 PSD VWB WA7L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
910925868288	WT490C 42S/840 PSU WB P15 L1200	4000 K	165 lm/W	4,200 lm	Wide beam
910925868289	WT490C 64S/840 PSU WB P15 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868290	WT490C 80S/840 PSU WB P15 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868509	WT490C 42S/840 PSD VWB P15 L1200	4000 K	162 lm/W	4,200 lm	Very wide beam
910925868611	WT490C 42S/840 PSU WB WA7 L1200	4000 K	165 lm/W	4,200 lm	Wide beam

Pacific LED Gen5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	4000 K	165 lm/W	4,200 lm	Very wide beam
910925868613	WT490C 42S/840 PSU WB TW3 WA7 L1200	4000 K	165 lm/W	4,200 lm	Wide beam
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	4000 K	162 lm/W	4,200 lm	Wide beam
910925868615	WT490C 42S/840 PSD WB WA7 L1200	4000 K	162 lm/W	4,200 lm	Wide beam
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	4000 K	162 lm/W	4,200 lm	Very wide beam
910925868617	WT490C 42S/840 PSD WB TW3 WA7 L1200	4000 K	162 lm/W	4,200 lm	Wide beam
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	4000 K	162 lm/W	4,200 lm	Very wide beam
910925868619	WT490C 64S/840 PSU NB-HRO TW3 WA7 L12	4000 K	160 lm/W	6,400 lm	Narrow beam - High-rack optic
910925868620	WT490C 64S/840 PSD NB-HRO TW3 WA7 L12	4000 K	162 lm/W	6,400 lm	Narrow beam - High-rack optic
910925868621	WT490C 80S/840 PSU NB-HRO TW3 WA7 L12	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925868622	WT490C 80S/840 PSD NB-HRO TW3 WA7 L12	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925868691	WT490C 35S/840 PSU WB PI5 L1200	4000 K	159 lm/W	3,500 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925868693	WT490C 35S/840 PSU WB WA7 L1200	4000 K	159 lm/W	3,500 lm	Wide beam
910925868695	WT490C 64S/840 PSU O L1200	4000 K	155 lm/W	6,200 lm	Opal
910925868696	WT490C 64S/840 PSU PCO L1200	4000 K	133 lm/W	5,300 lm	Opal
910925868699	WT495C 64S/840 PSU WB PI5 L1200	4000 K	158 lm/W	6,400 lm	Wide beam
910925868702	WT495C 64S/840 PSD WB PI5 L1200	4000 K	158 lm/W	6,400 lm	Wide beam
910925868708	WT490C 64S/840 PSU CLII WB WA7 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925869401	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	4000 K	146 lm/W	6,400 lm	Wide beam
910925869403	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925869404	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925869410	WT490C 42S/840 PSU WB TW3x2.5 PI5 L1200	4000 K	165 lm/W	4,200 lm	Wide beam
6	100S/840 PSD WB PI5 L1200	4000 K	152 lm/W	10,000 lm	Very wide beam
8	100S/840 PSU WB WA7 L1200	4000 K	154 lm/W	10,000 lm	Very wide beam
91092586960	WT490C 100S/840 PSD WB WA7 L1200	4000 K	152 lm/W	10,000 lm	Very wide beam
9	100S/840 PSD WB WA7 L1200	4000 K	152 lm/W	10,000 lm	Very wide beam

Pacific LED Gen5

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
910925869610	WT490C 100S/840 PSU WB PI5 L1200	4000 K	154 lm/W	10,000 lm	Very wide beam
910925868412	WT490C 64S/840 PSD WB PI5 L1600	4000 K	162 lm/W	6,400 lm	Wide beam
910925868413	WT490C 64S/840 PSU WB TW3 PI5 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
910925868414	WT490C 64S/840 PSU WB PI5 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
910925868415	WT490C 80S/840 PSU WB PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868416	WT490C 80S/840 PSD WB PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868417	WT490C 80S/840 PSU WB TW3 PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868418	WT490C 64S/840 PSD WB WA7 L1600	4000 K	162 lm/W	6,400 lm	Wide beam
910925868419	WT490C 64S/840 PSU WB TW3 WA7 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
910925868420	WT490C 64S/840 PSU WB WA7 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
910925868421	WT490C 80S/840 PSU WB WA7 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868422	WT490C 80S/840 PSD WB WA7 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868423	WT490C 80S/840 PSU WB TW3 WA7 L1600	4000 K	157 lm/W	8,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
910925868692	WT490C 35S/840 PSU WB PI5 L1600	4000 K	159 lm/W	3,500 lm	Wide beam
910925868694	WT490C 35S/840 PSU WB WA7 L1600	4000 K	159 lm/W	3,500 lm	Wide beam
910925869407	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
910925869408	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925867703	WT490C 23S/840 PSD WB PI5 L700	4000 K	160 lm/W	2,300 lm	Wide beam
910925868287	WT490C 23S/840 PSU WB PI5 L700	4000 K	151 lm/W	2,300 lm	Wide beam
910925868250	WT490C 64S/840 PSU WB TCW5W5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868510	WT490C 64S/840 PSU WB W5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868511	WT490C 80S/840 PSU WB W5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868512	WT490C 64S/840 PSD WB W5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925868513	WT490C 80S/840 PSD WB W5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam

Light Technical (2/2)

Pacific LED Gen5

Order Code	Full Product Name	Flickering value (PstLM)	
		- Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925867731	WT490C 80S/840 PSU NB-HRO PI5 L1800	1	0.4
910925867732	WT490C 80S/840 PSD NB-HRO PI5 L1800	1	0.4
910925867733	WT490C 80S/840 PSU WB TW3 PI5 L1800	1	0.4
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	1	0.4
910925867735	WT490C 80S/840 PSD WB PI5 L1800	1	0.4
910925867736	WT490C 80S/840 PSD WB TW3 PI7 L1800	1	0.4
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	1	0.4
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	1	0.4
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	1	0.4
910925867740	WT490C 100S/840 PSD WB PI5 L1800	1	0.4
910925867741	WT490C 120S/840 PSD WB PI5 L1800	1	0.4
910925868292	WT490C 80S/840 PSU WB PI5 L1800	1	0.4
910925868293	WT490C 100S/840 PSU WB PI5 L1800	1	0.4
910925868294	WT490C 120S/840 PSU WB PI5 L1800	1	0.4
910925868516	WT490C 80S/840 SIA WB IA9 PI5 L1800	1	0.4
910925868697	WT490C 80S/840 PSU O L1800	1	0.4
910925868698	WT490C 80S/840 PSU PCO L1800	1	0.4
910925868701	WT495C 80S/840 PSU WB PI5 L1800	1	0.4
910925868703	WT495C 80S/840 PSD WB PI5 L1800	1	0.4
910925868709	WT490C 80S/840 PSU CLII WB WA7 L1800	1	0.4
910925869405	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1800	1	0.4
910925869406	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1800	1	0.4
910925869607	WT490C 150S/840 PSD WB PI5 L1800	-	-
910925869611	WT490C 150S/840 PSU WB PI5 L1800	-	-
910925868704	WT492C 64S/840 PSU WB W5 L1200	1	0.4

Order Code	Full Product Name	Flickering value (PstLM)	
		- Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925868705	WT492C 80S/840 PSU WB W5 L1800	1	0.4
910925868706	WT492C 64S/840 PSD WB W5 L1200	1	0.4
910925868707	WT492C 80S/840 PSD WB W5 L1800	1	0.4
910770229590	WT490C 42S/830 PSU WB PI5 L1200	1	0.4
910925867704	WT490C 42S/840 PSD WB PI5 L1200	1	0.4
910925867705	WT490C 64S/840 PSU NB-HRO PI5 L1200	1	0.4
910925867706	WT490C 64S/840 PSD NB-HRO PI5 L1200	1	0.4
910925867707	WT490C 64S/840 PSU WB TW1 PI5 L1200	1	0.4
910925867708	WT490C 64S/840 PSU WB TW3 PI5 L1200	1	0.4
910925867709	WT490C 64S/840 PSU WB TCW5 PI5 L1200	1	0.4
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	1	0.4
910925867711	WT490C 64S/840 PSU WB ELP3TW1 PI5 L12	1	0.4
910925867712	WT490C 64S/840 PSD WB PI5 L1200	1	0.4
910925867713	WT490C 64S/840 PSD WB TW1 PI5 L1200	1	0.4
910925867714	WT490C 64S/840 PSD WB TW3 PI7 L1200	1	0.4
910925867715	WT490C 64S/840 PSD WB ELD3PI7 L1200	1	0.4
910925867716	WT490C 64S/840 PSD WB ELD3TW1 PI7 L12	1	0.4
910925867717	WT490C 64S/840 PSU VWB PI5L1200	1	0.4
910925867718	WT490C 64S/840 PSD VWB PI5L1200	1	0.4
910925867719	WT490C 80S/840 PSU NB-HRO PI5 L1200	1	0.4
910925867720	WT490C 80S/840 PSD NB-HRO PI5 L1200	1	0.4
910925867721	WT490C 80S/840 PSU WB TW1 PI5 L1200	1	0.4
910925867722	WT490C 80S/840 PSU WB TW3 PI5 L1200	1	0.4
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	1	0.4

Pacific LED Gen5

Order Code	Full Product Name	Flickering value (PstLM)	
		- Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925867724	WT490C 80S/840 PSD WB PI5 L1200	1	0.4
910925867725	WT490C 80S/840 PSD WB TW1 PI5 L1200	1	0.4
910925867726	WT490C 80S/840 PSD WB TW3 PI7 L1200	1	0.4
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	1	0.4
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	1	0.4
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	1	0.4
910925867743	WT490C 64S/840 PSU NB-HRO WA7 L1200	1	0.4
910925867744	WT490C 64S/840 PSD NB-HRO WA7 L1200	1	0.4
910925868247	WT490C 64S/840 PSU WB WA7 L1200	1	0.4
910925868249	WT490C 64S/840 PSU WB TW3 WA7 L1200	1	0.4
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	1	0.4
910925868252	WT490C 64S/840 PSD WB WA7 L1200	1	0.4
910925868253	WT490C 64S/840 PSD WB TW3 WA7 L1200	1	0.4
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	1	0.4
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	1	0.4
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	1	0.4
910925868257	WT490C 80S/840 PSU NB-HRO WA7 L1200	1	0.4
910925868258	WT490C 80S/840 PSD NB-HRO WA7 L1200	1	0.4
910925868259	WT490C 80S/840 PSU WB WA7 L1200	1	0.4
910925868260	WT490C 80S/840 PSU WB TW3 WA7 L1200	1	0.4
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	1	0.4
910925868262	WT490C 80S/840 PSD WB WA7 L1200	1	0.4
910925868263	WT490C 80S/840 PSD WB TW3 WA7 L1200	1	0.4
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	1	0.4

Order Code	Full Product Name	Flickering value (PstLM)	
		- Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925868265	WT490C 80S/840 PSU VWB WA7L1200	1	0.4
910925868266	WT490C 80S/840 PSD VWB WA7L1200	1	0.4
910925868288	WT490C 42S/840 PSU WB PI5 L1200	1	0.4
910925868289	WT490C 64S/840 PSU WB PI5 L1200	1	0.4
910925868290	WT490C 80S/840 PSU WB PI5 L1200	1	0.4
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	1	0.4
910925868611	WT490C 42S/840 PSU WB WA7 L1200	1	0.4
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	1	0.4
910925868613	WT490C 42S/840 PSU WB TW3 WA7 L1200	1	0.4
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	1	0.4
910925868615	WT490C 42S/840 PSD WB WA7 L1200	1	0.4
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	1	0.4
910925868617	WT490C 42S/840 PSD WB TW3 WA7 L1200	1	0.4
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	1	0.4
910925868619	WT490C 64S/840 PSU NB-HRO TW3 WA7 L12	1	0.4
910925868620	WT490C 64S/840 PSD NB-HRO TW3 WA7 L12	1	0.4
910925868621	WT490C 80S/840 PSU NB-HRO TW3 WA7 L12	1	0.4
910925868622	WT490C 80S/840 PSD NB-HRO TW3 WA7 L12	1	0.4
910925868691	WT490C 35S/840 PSU WB PI5 L1200	1	0.4
910925868693	WT490C 35S/840 PSU WB WA7 L1200	1	0.4
910925868695	WT490C 64S/840 PSU O L1200	1	0.4
910925868696	WT490C 64S/840 PSU PCO L1200	1	0.4
910925868699	WT495C 64S/840 PSU WB PI5 L1200	1	0.4
910925868702	WT495C 64S/840 PSD WB PI5 L1200	1	0.4
910925868708	WT490C 64S/840 PSU CLII WB WA7 L1200	1	0.4

Pacific LED Gen5

Order Code	Full Product Name	Flickering value (PstLM)	
		- Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925869401	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1200	1	0.4
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	1	0.4
910925869403	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1200	1	0.4
910925869404	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1200	1	0.4
910925869410	WT490C 42S/840 PSU WB TW3x2.5 PI5 L1200	1	0.4
910925869606	WT490C 100S/840 PSD WB PI5 L1200	-	-
910925869608	WT490C 100S/840 PSU WB WA7 L1200	-	-
910925869609	WT490C 100S/840 PSD WB WA7 L1200	-	-
910925869610	WT490C 100S/840 PSU WB PI5 L1200	-	-
910925868412	WT490C 64S/840 PSD WB PI5 L1600	1	0.4
910925868413	WT490C 64S/840 PSU WB TW3 PI5 L1600	1	0.4
910925868414	WT490C 64S/840 PSU WB PI5 L1600	1	0.4
910925868415	WT490C 80S/840 PSU WB PI5 L1600	1	0.4
910925868416	WT490C 80S/840 PSD WB PI5 L1600	1	0.4
910925868417	WT490C 80S/840 PSU WB TW3 PI5 L1600	1	0.4
910925868418	WT490C 64S/840 PSD WB WA7 L1600	1	0.4

Order Code	Full Product Name	Flickering value (PstLM)	
		- Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925868419	WT490C 64S/840 PSU WB TW3 WA7 L1600	1	0.4
910925868420	WT490C 64S/840 PSU WB WA7 L1600	1	0.4
910925868421	WT490C 80S/840 PSU WB WA7 L1600	1	0.4
910925868422	WT490C 80S/840 PSD WB WA7 L1600	1	0.4
910925868423	WT490C 80S/840 PSU WB TW3 WA7 L1600	1	0.4
910925868692	WT490C 35S/840 PSU WB PI5 L1600	1	0.4
910925868694	WT490C 35S/840 PSU WB WA7 L1600	1	0.4
910925869407	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1600	1	0.4
910925869408	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1600	1	0.4
910925867703	WT490C 23S/840 PSD WB PI5 L700	1	0.4
910925868287	WT490C 23S/840 PSU WB PI5 L700	1	0.4
910925868250	WT490C 64S/840 PSU WB TCW5W5 L1200	1	0.4
910925868510	WT490C 64S/840 PSU WB W5 L1200	1	0.4
910925868511	WT490C 80S/840 PSU WB W5 L1200	1	0.4
910925868512	WT490C 64S/840 PSD WB W5 L1200	1	0.4
910925868513	WT490C 80S/840 PSD WB W5 L1200	1	0.4

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925867731	WT490C 80S/840 PSU NB-HRO PI5 L1800	48.5 W
910925867732	WT490C 80S/840 PSD NB-HRO PI5 L1800	48.5 W
910925867733	WT490C 80S/840 PSU WB TW3 PI5 L1800	48.5 W
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	52 W
910925867735	WT490C 80S/840 PSD WB PI5 L1800	48.5 W
910925867736	WT490C 80S/840 PSD WB TW3 PI7 L1800	48.5 W
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	52 W
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	48.5 W
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	48.5 W
910925867740	WT490C 100S/840 PSD WB PI5 L1800	62 W
910925867741	WT490C 120S/840 PSD WB PI5 L1800	76 W
910925868292	WT490C 80S/840 PSU WB PI5 L1800	48.5 W

Order Code	Full Product Name	Power Consumption
910925868293	WT490C 100S/840 PSU WB PI5 L1800	62 W
910925868294	WT490C 120S/840 PSU WB PI5 L1800	76 W
910925868516	WT490C 80S/840 SIA WB IA9 PI5 L1800	48.5 W
910925868697	WT490C 80S/840 PSU O L1800	51 W
910925868698	WT490C 80S/840 PSU PCO L1800	48.5 W
910925868701	WT495C 80S/840 PSU WB PI5 L1800	49 W
910925868703	WT495C 80S/840 PSD WB PI5 L1800	48.5 W
910925868709	WT490C 80S/840 PSU CLII WB WA7 L1800	51 W
910925869405	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1800	48.5 W
910925869406	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1800	48.5 W
910925869607	WT490C 150S/840 PSD WB PI5 L1800	97 W
910925869611	WT490C 150S/840 PSU WB PI5 L1800	97 W

Pacific LED Gen5

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910925868704	WT492C 64S/840 PSU WB W5 L1200	40 W	910925868289	WT490C 64S/840 PSU WB PI5 L1200	40 W
910925868705	WT492C 80S/840 PSU WB W5 L1800	49 W	910925868290	WT490C 80S/840 PSU WB PI5 L1200	51 W
910925868706	WT492C 64S/840 PSD WB W5 L1200	39.5 W	910925868509	WT490C 42S/840 PSD VWB PI5 L1200	26 W
910925868707	WT492C 80S/840 PSD WB W5 L1800	48.5 W	910925868611	WT490C 42S/840 PSU WB WA7 L1200	25.5 W
910770229590	WT490C 42S/830 PSU WB PI5 L1200	25.5 W	910925868612	WT490C 42S/840 PSU VWB WA7 L1200	25.5 W
910925867704	WT490C 42S/840 PSD WB PI5 L1200	26 W	910925868613	WT490C 42S/840 PSU WB TW3 WA7 L1200	25.5 W
910925867705	WT490C 64S/840 PSU NB-HRO PI5 L1200	40 W	910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	26 W
910925867706	WT490C 64S/840 PSD NB-HRO PI5 L1200	39.5 W	910925868615	WT490C 42S/840 PSD WB WA7 L1200	26 W
910925867707	WT490C 64S/840 PSU WB TW1 PI5 L1200	40 W	910925868616	WT490C 42S/840 PSD VWB WA7 L1200	26 W
910925867708	WT490C 64S/840 PSU WB TW3 PI5 L1200	40 W	910925868617	WT490C 42S/840 PSD WB TW3 WA7 L1200	26 W
910925867709	WT490C 64S/840 PSU WB TCW5 PI5 L1200	40 W	910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	26 W
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	44 W	910925868619	WT490C 64S/840 PSU NB-HRO TW3 WA7 L12	40 W
910925867711	WT490C 64S/840 PSU WB ELP3TW1 PI5 L12	44 W	910925868620	WT490C 64S/840 PSD NB-HRO TW3 WA7 L12	39.5 W
910925867712	WT490C 64S/840 PSD WB PI5 L1200	39.5 W	910925868621	WT490C 80S/840 PSU NB-HRO TW3 WA7 L12	51 W
910925867713	WT490C 64S/840 PSD WB TW1 PI5 L1200	39.5 W	910925868622	WT490C 80S/840 PSD NB-HRO TW3 WA7 L12	51 W
910925867714	WT490C 64S/840 PSD WB TW3 PI7 L1200	39.5 W	910925868691	WT490C 35S/840 PSU WB PI5 L1200	22 W
910925867715	WT490C 64S/840 PSD WB ELD3PI7 L1200	43.5 W	910925868693	WT490C 35S/840 PSU WB WA7 L1200	22 W
910925867716	WT490C 64S/840 PSD WB ELD3TW1 PI7 L12	43.5 W	910925868695	WT490C 64S/840 PSU O L1200	40 W
910925867717	WT490C 64S/840 PSU VWB PI5L1200	40 W	910925868696	WT490C 64S/840 PSU PCO L1200	40 W
910925867718	WT490C 64S/840 PSD VWB PI5L1200	39.5 W	910925868699	WT495C 64S/840 PSU WB PI5 L1200	40.5 W
910925867719	WT490C 80S/840 PSU NB-HRO PI5 L1200	51 W	910925868702	WT495C 64S/840 PSD WB PI5 L1200	40.5 W
910925867720	WT490C 80S/840 PSD NB-HRO PI5 L1200	51 W	910925868708	WT490C 64S/840 PSU CLII WB WA7 L1200	40 W
910925867721	WT490C 80S/840 PSU WB TW1 PI5 L1200	51 W	910925869401	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1200	40 W
910925867722	WT490C 80S/840 PSU WB TW3 PI5 L1200	51 W	910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	44 W
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	55 W	910925869403	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1200	51 W
910925867724	WT490C 80S/840 PSD WB PI5 L1200	51 W	910925869404	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1200	51 W
910925867725	WT490C 80S/840 PSD WB TW1 PI5 L1200	51 W	910925869410	WT490C 42S/840 PSU WB TW3x2.5 PI5 L1200	25.5 W
910925867726	WT490C 80S/840 PSD WB TW3 PI7 L1200	51 W	910925869606	WT490C 100S/840 PSD WB PI5 L1200	66 W
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	55 W	910925869608	WT490C 100S/840 PSU WB WA7 L1200	65 W
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	51 W	910925869609	WT490C 100S/840 PSD WB WA7 L1200	66 W
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	51 W	910925869610	WT490C 100S/840 PSU WB PI5 L1200	65 W
910925867743	WT490C 64S/840 PSU NB-HRO WA7 L1200	40 W	910925868412	WT490C 64S/840 PSD WB PI5 L1600	39.5 W
910925867744	WT490C 64S/840 PSD NB-HRO WA7 L1200	39.5 W	910925868413	WT490C 64S/840 PSU WB TW3 PI5 L1600	40 W
910925868247	WT490C 64S/840 PSU WB WA7 L1200	40 W	910925868414	WT490C 64S/840 PSU WB PI5 L1600	40 W
910925868249	WT490C 64S/840 PSU WB TW3 WA7 L1200	40 W	910925868415	WT490C 80S/840 PSU WB PI5 L1600	51 W
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	44 W	910925868416	WT490C 80S/840 PSD WB PI5 L1600	51 W
910925868252	WT490C 64S/840 PSD WB WA7 L1200	39.5 W	910925868417	WT490C 80S/840 PSU WB TW3 PI5 L1600	51 W
910925868253	WT490C 64S/840 PSD WB TW3 WA7 L1200	39.5 W	910925868418	WT490C 64S/840 PSD WB WA7 L1600	39.5 W
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	43.5 W	910925868419	WT490C 64S/840 PSU WB TW3 WA7 L1600	40 W
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	40 W	910925868420	WT490C 64S/840 PSU WB WA7 L1600	40 W
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	39.5 W	910925868421	WT490C 80S/840 PSU WB WA7 L1600	51 W
910925868257	WT490C 80S/840 PSU NB-HRO WA7 L1200	51 W	910925868422	WT490C 80S/840 PSD WB WA7 L1600	51 W
910925868258	WT490C 80S/840 PSD NB-HRO WA7 L1200	51 W	910925868423	WT490C 80S/840 PSU WB TW3 WA7 L1600	51 W
910925868259	WT490C 80S/840 PSU WB WA7 L1200	51 W	910925868692	WT490C 35S/840 PSU WB PI5 L1600	22 W
910925868260	WT490C 80S/840 PSU WB TW3 WA7 L1200	51 W	910925868694	WT490C 35S/840 PSU WB WA7 L1600	22 W
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	55 W	910925869407	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1600	40 W
910925868262	WT490C 80S/840 PSD WB WA7 L1200	51 W	910925869408	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1600	51 W
910925868263	WT490C 80S/840 PSD WB TW3 WA7 L1200	51 W	910925867703	WT490C 23S/840 PSD WB PI5 L700	14.4 W
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	55 W	910925868287	WT490C 23S/840 PSU WB PI5 L700	15.2 W
910925868265	WT490C 80S/840 PSU VWB WA7L1200	51 W	910925868250	WT490C 64S/840 PSU WB TCW5W5 L1200	40 W
910925868266	WT490C 80S/840 PSD VWB WA7L1200	51 W	910925868510	WT490C 64S/840 PSU WB W5 L1200	40 W
910925868288	WT490C 42S/840 PSU WB PI5 L1200	25.5 W	910925868511	WT490C 80S/840 PSU WB W5 L1200	51 W

Pacific LED Gen5

Order Code	Full Product Name	Power Consumption
910925868512	WT490C 64S/840 PSD WB W5 L1200	39.5 W

Order Code	Full Product Name	Power Consumption
910925868513	WT490C 80S/840 PSD WB W5 L1200	51 W

Temperature

Order Code	Full Product Name	Ambient temperature range
910925867731	WT490C 80S/840 PSU NB-HRO PI5 L1800	-25 to +45 °C
910925867732	WT490C 80S/840 PSD NB-HRO PI5 L1800	-25 to +45 °C
910925867733	WT490C 80S/840 PSU WB TW3 PI5 L1800	-25 to +45 °C
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	0 to +30 °C
910925867735	WT490C 80S/840 PSD WB PI5 L1800	-25 to +45 °C
910925867736	WT490C 80S/840 PSD WB TW3 PI7 L1800	-25 to +45 °C
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	0 to +30 °C
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	-25 to +45 °C
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	-25 to +45 °C
910925867740	WT490C 100S/840 PSD WB PI5 L1800	-25 to +45 °C
910925867741	WT490C 120S/840 PSD WB PI5 L1800	-25 to +45 °C
910925868292	WT490C 80S/840 PSU WB PI5 L1800	-25 to +45 °C
910925868293	WT490C 100S/840 PSU WB PI5 L1800	-25 to +45 °C
910925868294	WT490C 120S/840 PSU WB PI5 L1800	-25 to +45 °C
910925868516	WT490C 80S/840 SIA WB IA9 PI5 L1800	-25 to +45 °C
910925868697	WT490C 80S/840 PSU O L1800	-25 to +45 °C
910925868698	WT490C 80S/840 PSU PCO L1800	-25 to +45 °C
910925868701	WT495C 80S/840 PSU WB PI5 L1800	-35 to +60 °C
910925868703	WT495C 80S/840 PSD WB PI5 L1800	-35 to +60 °C
910925868709	WT490C 80S/840 PSU CLII WB WA7 L1800	-25 to +45 °C
910925869405	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1800	-25 to +45 °C
910925869406	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1800	-25 to +45 °C
910925869607	WT490C 150S/840 PSD WB PI5 L1800	-25 to +25 °C
910925869611	WT490C 150S/840 PSU WB PI5 L1800	-25 to +25 °C
910925868704	WT492C 64S/840 PSU WB W5 L1200	-25 to +45 °C
910925868705	WT492C 80S/840 PSU WB W5 L1800	-25 to +45 °C
910925868706	WT492C 64S/840 PSD WB W5 L1200	-25 to +45 °C
910925868707	WT492C 80S/840 PSD WB W5 L1800	-25 to +45 °C
910770229590	WT490C 42S/830 PSU WB PI5 L1200	-25 to +45 °C
910925867704	WT490C 42S/840 PSD WB PI5 L1200	-25 to +45 °C
910925867705	WT490C 64S/840 PSU NB-HRO PI5 L1200	-25 to +45 °C
910925867706	WT490C 64S/840 PSD NB-HRO PI5 L1200	-25 to +45 °C
910925867707	WT490C 64S/840 PSU WB TW1 PI5 L1200	-25 to +45 °C
910925867708	WT490C 64S/840 PSU WB TW3 PI5 L1200	-25 to +45 °C

Order Code	Full Product Name	Ambient temperature range
910925867709	WT490C 64S/840 PSU WB TCW5 PI5 L1200	-25 to +45 °C
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	0 to +40 °C
910925867711	WT490C 64S/840 PSU WB ELP3TW1 PI5 L12	0 to +40 °C
910925867712	WT490C 64S/840 PSD WB PI5 L1200	-25 to +45 °C
910925867713	WT490C 64S/840 PSD WB TW1 PI5 L1200	-25 to +45 °C
910925867714	WT490C 64S/840 PSD WB TW3 PI7 L1200	-25 to +45 °C
910925867715	WT490C 64S/840 PSD WB ELD3PI7 L1200	0 to +40 °C
910925867716	WT490C 64S/840 PSD WB ELD3TW1 PI7 L12	0 to +40 °C
910925867717	WT490C 64S/840 PSU VWB PI5L1200	-25 to +45 °C
910925867718	WT490C 64S/840 PSD VWB PI5L1200	-25 to +45 °C
910925867719	WT490C 80S/840 PSU NB-HRO PI5 L1200	-25 to +45 °C
910925867720	WT490C 80S/840 PSD NB-HRO PI5 L1200	-25 to +45 °C
910925867721	WT490C 80S/840 PSU WB TW1 PI5 L1200	-25 to +45 °C
910925867722	WT490C 80S/840 PSU WB TW3 PI5 L1200	-25 to +45 °C
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	0 to +30 °C
910925867724	WT490C 80S/840 PSD WB PI5 L1200	-25 to +45 °C
910925867725	WT490C 80S/840 PSD WB TW1 PI5 L1200	-25 to +45 °C
910925867726	WT490C 80S/840 PSD WB TW3 PI7 L1200	-25 to +45 °C
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	0 to +30 °C
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	-25 to +45 °C
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	-25 to +45 °C
910925867743	WT490C 64S/840 PSU NB-HRO WA7 L1200	-25 to +45 °C
910925867744	WT490C 64S/840 PSD NB-HRO WA7 L1200	-25 to +45 °C
910925868247	WT490C 64S/840 PSU WB WA7 L1200	-25 to +45 °C
910925868249	WT490C 64S/840 PSU WB TW3 WA7 L1200	-25 to +45 °C
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	0 to +40 °C
910925868252	WT490C 64S/840 PSD WB WA7 L1200	-25 to +45 °C

Pacific LED Gen5

Order Code	Full Product Name	Ambient temperature range
910925868253	WT490C 64S/840 PSD WB TW3 WA7 L1200	-25 to +45 °C
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	0 to +40 °C
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	-25 to +45 °C
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	-25 to +45 °C
910925868257	WT490C 80S/840 PSU NB-HRO WA7 L1200	-25 to +45 °C
910925868258	WT490C 80S/840 PSD NB-HRO WA7 L1200	-25 to +45 °C
910925868259	WT490C 80S/840 PSU WB WA7 L1200	-25 to +45 °C
910925868260	WT490C 80S/840 PSU WB TW3 WA7 L1200	-25 to +45 °C
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	0 to +30 °C
910925868262	WT490C 80S/840 PSD WB WA7 L1200	-25 to +45 °C
910925868263	WT490C 80S/840 PSD WB TW3 WA7 L1200	-25 to +45 °C
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	0 to +30 °C
910925868265	WT490C 80S/840 PSU VWB WA7L1200	-25 to +45 °C
910925868266	WT490C 80S/840 PSD VWB WA7L1200	-25 to +45 °C
910925868288	WT490C 42S/840 PSU WB PI5 L1200	-25 to +45 °C
910925868289	WT490C 64S/840 PSU WB PI5 L1200	-25 to +45 °C
910925868290	WT490C 80S/840 PSU WB PI5 L1200	-25 to +45 °C
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	-25 to +45 °C
910925868611	WT490C 42S/840 PSU WB WA7 L1200	-25 to +45 °C
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	-25 to +45 °C
910925868613	WT490C 42S/840 PSU WB TW3 WA7 L1200	-25 to +45 °C
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	-25 to +45 °C
910925868615	WT490C 42S/840 PSD WB WA7 L1200	-25 to +45 °C
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	-25 to +45 °C
910925868617	WT490C 42S/840 PSD WB TW3 WA7 L1200	-25 to +45 °C
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	-25 to +45 °C
910925868619	WT490C 64S/840 PSU NB-HRO TW3 WA7 L12	-25 to +45 °C
910925868620	WT490C 64S/840 PSD NB-HRO TW3 WA7 L12	-25 to +45 °C
910925868621	WT490C 80S/840 PSU NB-HRO TW3 WA7 L12	-25 to +45 °C
910925868622	WT490C 80S/840 PSD NB-HRO TW3 WA7 L12	-25 to +45 °C
910925868691	WT490C 35S/840 PSU WB PI5 L1200	-25 to +45 °C
910925868693	WT490C 35S/840 PSU WB WA7 L1200	-25 to +45 °C
910925868695	WT490C 64S/840 PSU O L1200	-25 to +45 °C
910925868696	WT490C 64S/840 PSU PCO L1200	-25 to +45 °C
910925868699	WT495C 64S/840 PSU WB PI5 L1200	-35 to +60 °C

Order Code	Full Product Name	Ambient temperature range
910925868702	WT495C 64S/840 PSD WB PI5 L1200	-35 to +60 °C
910925868708	WT490C 64S/840 PSU CLII WB WA7 L1200	-25 to +45 °C
910925869401	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1200	-25 to +45 °C
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	0 to +40 °C
910925869403	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1200	-25 to +45 °C
910925869404	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1200	-25 to +45 °C
910925869410	WT490C 42S/840 PSU WB TW3x2.5 PI5 L1200	-25 to +45 °C
91092586960	WT490C 100S/840 PSD WB PI5 L1200 6	-25 to +25 °C
91092586960	WT490C 100S/840 PSU WB WA7 L1200 8	-25 to +25 °C
91092586960	WT490C 100S/840 PSD WB WA7 L1200 9	-25 to +25 °C
910925869610	WT490C 100S/840 PSU WB PI5 L1200	-25 to +25 °C
910925868412	WT490C 64S/840 PSD WB PI5 L1600	-25 to +45 °C
910925868413	WT490C 64S/840 PSU WB TW3 PI5 L1600	-25 to +45 °C
910925868414	WT490C 64S/840 PSU WB PI5 L1600	-25 to +45 °C
910925868415	WT490C 80S/840 PSU WB PI5 L1600	-25 to +45 °C
910925868416	WT490C 80S/840 PSD WB PI5 L1600	-25 to +45 °C
910925868417	WT490C 80S/840 PSU WB TW3 PI5 L1600	-25 to +45 °C
910925868418	WT490C 64S/840 PSD WB WA7 L1600	-25 to +45 °C
910925868419	WT490C 64S/840 PSU WB TW3 WA7 L1600	-25 to +45 °C
910925868420	WT490C 64S/840 PSU WB WA7 L1600	-25 to +45 °C
910925868421	WT490C 80S/840 PSU WB WA7 L1600	-25 to +45 °C
910925868422	WT490C 80S/840 PSD WB WA7 L1600	-25 to +45 °C
910925868423	WT490C 80S/840 PSU WB TW3 WA7 L1600	-25 to +45 °C
910925868692	WT490C 35S/840 PSU WB PI5 L1600	-25 to +45 °C
910925868694	WT490C 35S/840 PSU WB WA7 L1600	-25 to +45 °C
910925869407	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1600	-25 to +45 °C
910925869408	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1600	-25 to +45 °C
910925867703	WT490C 23S/840 PSD WB PI5 L700	-25 to +45 °C
910925868287	WT490C 23S/840 PSU WB PI5 L700	-25 to +45 °C
910925868250	WT490C 64S/840 PSU WB TCW5W5 L1200	-25 to +45 °C
910925868510	WT490C 64S/840 PSU WB W5 L1200	-25 to +45 °C
910925868511	WT490C 80S/840 PSU WB W5 L1200	-25 to +45 °C
910925868512	WT490C 64S/840 PSD WB W5 L1200	-25 to +45 °C
910925868513	WT490C 80S/840 PSD WB W5 L1200	-25 to +45 °C

Controls and Dimming

Pacific LED Gen5

Order Code	Full Product Name	Dimmable
910925867731	WT490C 80S/840 PSU NB-HRO PI5 L1800	No
910925867732	WT490C 80S/840 PSD NB-HRO PI5 L1800	Yes
910925867733	WT490C 80S/840 PSU WB TW3 PI5 L1800	No
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	No
910925867735	WT490C 80S/840 PSD WB PI5 L1800	Yes
910925867736	WT490C 80S/840 PSD WB TW3 PI7 L1800	Yes
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	Yes
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	No
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	Yes
910925867740	WT490C 100S/840 PSD WB PI5 L1800	Yes
910925867741	WT490C 120S/840 PSD WB PI5 L1800	Yes
910925868292	WT490C 80S/840 PSU WB PI5 L1800	No
910925868293	WT490C 100S/840 PSU WB PI5 L1800	No
910925868294	WT490C 120S/840 PSU WB PI5 L1800	No
910925868516	WT490C 80S/840 SIA WB IA9 PI5 L1800	Yes
910925868697	WT490C 80S/840 PSU O L1800	No
910925868698	WT490C 80S/840 PSU PCO L1800	No
910925868701	WT495C 80S/840 PSU WB PI5 L1800	No
910925868703	WT495C 80S/840 PSD WB PI5 L1800	Yes
910925868709	WT490C 80S/840 PSU CLII WB WA7 L1800	No
910925869405	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1800	No
910925869406	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1800	Yes
910925869607	WT490C 150S/840 PSD WB PI5 L1800	Yes
910925869611	WT490C 150S/840 PSU WB PI5 L1800	No
910925868704	WT492C 64S/840 PSU WB W5 L1200	No
910925868705	WT492C 80S/840 PSU WB W5 L1800	No
910925868706	WT492C 64S/840 PSD WB W5 L1200	Yes
910925868707	WT492C 80S/840 PSD WB W5 L1800	Yes
910770229590	WT490C 42S/830 PSU WB PI5 L1200	No
910925867704	WT490C 42S/840 PSD WB PI5 L1200	Yes
910925867705	WT490C 64S/840 PSU NB-HRO PI5 L1200	No
910925867706	WT490C 64S/840 PSD NB-HRO PI5 L1200	Yes
910925867707	WT490C 64S/840 PSU WB TW1 PI5 L1200	No
910925867708	WT490C 64S/840 PSU WB TW3 PI5 L1200	No
910925867709	WT490C 64S/840 PSU WB TCW5 PI5 L1200	No
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	No
910925867711	WT490C 64S/840 PSU WB ELP3TW1 PI5 L12	No
910925867712	WT490C 64S/840 PSD WB PI5 L1200	Yes
910925867713	WT490C 64S/840 PSD WB TW1 PI5 L1200	Yes
910925867714	WT490C 64S/840 PSD WB TW3 PI7 L1200	Yes
910925867715	WT490C 64S/840 PSD WB ELD3PI7 L1200	Yes
910925867716	WT490C 64S/840 PSD WB ELD3TW1 PI7 L12	Yes
910925867717	WT490C 64S/840 PSU VWB PI5L1200	No
910925867718	WT490C 64S/840 PSD VWB PI5L1200	Yes
910925867719	WT490C 80S/840 PSU NB-HRO PI5 L1200	No
910925867720	WT490C 80S/840 PSD NB-HRO PI5 L1200	Yes
910925867721	WT490C 80S/840 PSU WB TW1 PI5 L1200	No
910925867722	WT490C 80S/840 PSU WB TW3 PI5 L1200	No
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	No
910925867724	WT490C 80S/840 PSD WB PI5 L1200	Yes
910925867725	WT490C 80S/840 PSD WB TW1 PI5 L1200	Yes
910925867726	WT490C 80S/840 PSD WB TW3 PI7 L1200	Yes

Order Code	Full Product Name	Dimmable
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	Yes
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	No
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	Yes
910925867743	WT490C 64S/840 PSU NB-HRO WA7 L1200	No
910925867744	WT490C 64S/840 PSD NB-HRO WA7 L1200	Yes
910925868247	WT490C 64S/840 PSU WB WA7 L1200	No
910925868249	WT490C 64S/840 PSU WB TW3 WA7 L1200	No
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	No
910925868252	WT490C 64S/840 PSD WB WA7 L1200	Yes
910925868253	WT490C 64S/840 PSD WB TW3 WA7 L1200	Yes
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	Yes
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	No
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	Yes
910925868257	WT490C 80S/840 PSU NB-HRO WA7 L1200	No
910925868258	WT490C 80S/840 PSD NB-HRO WA7 L1200	Yes
910925868259	WT490C 80S/840 PSU WB WA7 L1200	No
910925868260	WT490C 80S/840 PSU WB TW3 WA7 L1200	No
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	No
910925868262	WT490C 80S/840 PSD WB WA7 L1200	Yes
910925868263	WT490C 80S/840 PSD WB TW3 WA7 L1200	Yes
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	Yes
910925868265	WT490C 80S/840 PSU VWB WA7L1200	No
910925868266	WT490C 80S/840 PSD VWB WA7L1200	Yes
910925868288	WT490C 42S/840 PSU WB PI5 L1200	No
910925868289	WT490C 64S/840 PSU WB PI5 L1200	No
910925868290	WT490C 80S/840 PSU WB PI5 L1200	No
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	Yes
910925868611	WT490C 42S/840 PSU WB WA7 L1200	No
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	No
910925868613	WT490C 42S/840 PSU WB TW3 WA7 L1200	No
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	No
910925868615	WT490C 42S/840 PSD WB WA7 L1200	Yes
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	Yes
910925868617	WT490C 42S/840 PSD WB TW3 WA7 L1200	Yes
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	Yes
910925868619	WT490C 64S/840 PSU NB-HRO TW3 WA7 L12	No
910925868620	WT490C 64S/840 PSD NB-HRO TW3 WA7 L12	Yes
910925868621	WT490C 80S/840 PSU NB-HRO TW3 WA7 L12	No
910925868622	WT490C 80S/840 PSD NB-HRO TW3 WA7 L12	Yes
910925868691	WT490C 35S/840 PSU WB PI5 L1200	No
910925868693	WT490C 35S/840 PSU WB WA7 L1200	No
910925868695	WT490C 64S/840 PSU O L1200	No
910925868696	WT490C 64S/840 PSU PCO L1200	No
910925868699	WT495C 64S/840 PSU WB PI5 L1200	No
910925868702	WT495C 64S/840 PSD WB PI5 L1200	Yes
910925868708	WT490C 64S/840 PSU CLII WB WA7 L1200	No
910925869401	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1200	No
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	No
910925869403	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1200	No
910925869404	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1200	Yes
910925869410	WT490C 42S/840 PSU WB TW3x2.5 PI5 L1200	No
910925869606	WT490C 100S/840 PSD WB PI5 L1200	Yes

Pacific LED Gen5

Order Code	Full Product Name	Dimmable
910925869608	WT490C 100S/840 PSU WB WA7 L1200	No
910925869609	WT490C 100S/840 PSD WB WA7 L1200	Yes
910925869610	WT490C 100S/840 PSU WB PI5 L1200	No
910925868412	WT490C 64S/840 PSD WB PI5 L1600	Yes
910925868413	WT490C 64S/840 PSU WB TW3 PI5 L1600	No
910925868414	WT490C 64S/840 PSU WB PI5 L1600	No
910925868415	WT490C 80S/840 PSU WB PI5 L1600	No
910925868416	WT490C 80S/840 PSD WB PI5 L1600	Yes
910925868417	WT490C 80S/840 PSU WB TW3 PI5 L1600	No
910925868418	WT490C 64S/840 PSD WB WA7 L1600	Yes
910925868419	WT490C 64S/840 PSU WB TW3 WA7 L1600	No
910925868420	WT490C 64S/840 PSU WB WA7 L1600	No
910925868421	WT490C 80S/840 PSU WB WA7 L1600	No

Order Code	Full Product Name	Dimmable
910925868422	WT490C 80S/840 PSD WB WA7 L1600	Yes
910925868423	WT490C 80S/840 PSU WB TW3 WA7 L1600	No
910925868692	WT490C 35S/840 PSU WB PI5 L1600	No
910925868694	WT490C 35S/840 PSU WB WA7 L1600	No
910925869407	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1600	No
910925869408	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1600	No
910925867703	WT490C 23S/840 PSD WB PI5 L700	Yes
910925868287	WT490C 23S/840 PSU WB PI5 L700	No
910925868250	WT490C 64S/840 PSU WB TCW5W5 L1200	No
910925868510	WT490C 64S/840 PSU WB W5 L1200	No
910925868511	WT490C 80S/840 PSU WB W5 L1200	No
910925868512	WT490C 64S/840 PSD WB W5 L1200	Yes
910925868513	WT490C 80S/840 PSD WB W5 L1200	Yes

Approval and Application

Order Code	Full Product Name	Protection class IEC
910925867731	WT490C 80S/840 PSU NB-HRO PI5 L1800	Safety class I
910925867732	WT490C 80S/840 PSD NB-HRO PI5 L1800	Safety class I
910925867733	WT490C 80S/840 PSU WB TW3 PI5 L1800	Safety class I
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	Safety class I
910925867735	WT490C 80S/840 PSD WB PI5 L1800	Safety class I
910925867736	WT490C 80S/840 PSD WB TW3 PI7 L1800	Safety class I
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	Safety class I
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	Safety class I
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	Safety class I
910925867740	WT490C 100S/840 PSD WB PI5 L1800	Safety class I
910925867741	WT490C 120S/840 PSD WB PI5 L1800	Safety class I
910925868292	WT490C 80S/840 PSU WB PI5 L1800	Safety class I
910925868293	WT490C 100S/840 PSU WB PI5 L1800	Safety class I
910925868294	WT490C 120S/840 PSU WB PI5 L1800	Safety class I
910925868516	WT490C 80S/840 SIA WB IA9 PI5 L1800	Safety class I
910925868697	WT490C 80S/840 PSU O L1800	Safety class I
910925868698	WT490C 80S/840 PSU PCO L1800	Safety class I
910925868701	WT495C 80S/840 PSU WB PI5 L1800	Safety class I
910925868703	WT495C 80S/840 PSD WB PI5 L1800	Safety class I
910925868709	WT490C 80S/840 PSU CLII WB WA7 L1800	Safety class II
910925869405	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1800	Safety class I
910925869406	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1800	Safety class I
910925869607	WT490C 150S/840 PSD WB PI5 L1800	Safety class I
910925869611	WT490C 150S/840 PSU WB PI5 L1800	Safety class I
910925868704	WT492C 64S/840 PSU WB W5 L1200	Safety class I
910925868705	WT492C 80S/840 PSU WB W5 L1800	Safety class I
910925868706	WT492C 64S/840 PSD WB W5 L1200	Safety class I
910925868707	WT492C 80S/840 PSD WB W5 L1800	Safety class I
910770229590	WT490C 42S/830 PSU WB PI5 L1200	Safety class I
910925867704	WT490C 42S/840 PSD WB PI5 L1200	Safety class I
910925867705	WT490C 64S/840 PSU NB-HRO PI5 L1200	Safety class I
910925867706	WT490C 64S/840 PSD NB-HRO PI5 L1200	Safety class I
910925867707	WT490C 64S/840 PSU WB TW1 PI5 L1200	Safety class I
910925867708	WT490C 64S/840 PSU WB TW3 PI5 L1200	Safety class I
910925867709	WT490C 64S/840 PSU WB TCW5 PI5 L1200	Safety class I

Order Code	Full Product Name	Protection class IEC
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	Safety class I
910925867711	WT490C 64S/840 PSU WB ELP3TW1 PI5 L12	Safety class I
910925867712	WT490C 64S/840 PSD WB PI5 L1200	Safety class I
910925867713	WT490C 64S/840 PSD WB TW1 PI5 L1200	Safety class I
910925867714	WT490C 64S/840 PSD WB TW3 PI7 L1200	Safety class I
910925867715	WT490C 64S/840 PSD WB ELD3PI7 L1200	Safety class I
910925867716	WT490C 64S/840 PSD WB ELD3TW1 PI7 L12	Safety class I
910925867717	WT490C 64S/840 PSU VWB PI5L1200	Safety class I
910925867718	WT490C 64S/840 PSD VWB PI5L1200	Safety class I
910925867719	WT490C 80S/840 PSU NB-HRO PI5 L1200	Safety class I
910925867720	WT490C 80S/840 PSD NB-HRO PI5 L1200	Safety class I
910925867721	WT490C 80S/840 PSU WB TW1 PI5 L1200	Safety class I
910925867722	WT490C 80S/840 PSU WB TW3 PI5 L1200	Safety class I
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	Safety class I
910925867724	WT490C 80S/840 PSD WB PI5 L1200	Safety class I
910925867725	WT490C 80S/840 PSD WB TW1 PI5 L1200	Safety class I
910925867726	WT490C 80S/840 PSD WB TW3 PI7 L1200	Safety class I
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	Safety class I
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	Safety class I
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	Safety class I
910925867743	WT490C 64S/840 PSU NB-HRO WA7 L1200	Safety class I
910925867744	WT490C 64S/840 PSD NB-HRO WA7 L1200	Safety class I
910925868247	WT490C 64S/840 PSU WB WA7 L1200	Safety class I
910925868249	WT490C 64S/840 PSU WB TW3 WA7 L1200	Safety class I
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	Safety class I
910925868252	WT490C 64S/840 PSD WB WA7 L1200	Safety class I
910925868253	WT490C 64S/840 PSD WB TW3 WA7 L1200	Safety class I
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	Safety class I
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	Safety class I
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	Safety class I
910925868257	WT490C 80S/840 PSU NB-HRO WA7 L1200	Safety class I
910925868258	WT490C 80S/840 PSD NB-HRO WA7 L1200	Safety class I
910925868259	WT490C 80S/840 PSU WB WA7 L1200	Safety class I
910925868260	WT490C 80S/840 PSU WB TW3 WA7 L1200	Safety class I
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	Safety class I

Pacific LED Gen5

Order Code	Full Product Name	Protection class IEC
910925868262	WT490C 80S/840 PSD WB WA7 L1200	Safety class I
910925868263	WT490C 80S/840 PSD WB TW3 WA7 L1200	Safety class I
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	Safety class I
910925868265	WT490C 80S/840 PSU VWB WA7L1200	Safety class I
910925868266	WT490C 80S/840 PSD VWB WA7L1200	Safety class I
910925868288	WT490C 42S/840 PSU WB PI5 L1200	Safety class I
910925868289	WT490C 64S/840 PSU WB PI5 L1200	Safety class I
910925868290	WT490C 80S/840 PSU WB PI5 L1200	Safety class I
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	Safety class I
910925868611	WT490C 42S/840 PSU WB WA7 L1200	Safety class I
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	Safety class I
910925868613	WT490C 42S/840 PSU WB TW3 WA7 L1200	Safety class I
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	Safety class I
910925868615	WT490C 42S/840 PSD WB WA7 L1200	Safety class I
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	Safety class I
910925868617	WT490C 42S/840 PSD WB TW3 WA7 L1200	Safety class I
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	Safety class I
910925868619	WT490C 64S/840 PSU NB-HRO TW3 WA7 L12	Safety class I
910925868620	WT490C 64S/840 PSD NB-HRO TW3 WA7 L12	Safety class I
910925868621	WT490C 80S/840 PSU NB-HRO TW3 WA7 L12	Safety class I
910925868622	WT490C 80S/840 PSD NB-HRO TW3 WA7 L12	Safety class I
910925868691	WT490C 35S/840 PSU WB PI5 L1200	Safety class I
910925868693	WT490C 35S/840 PSU WB WA7 L1200	Safety class I
910925868695	WT490C 64S/840 PSU O L1200	Safety class I
910925868696	WT490C 64S/840 PSU PCO L1200	Safety class I
910925868699	WT495C 64S/840 PSU WB PI5 L1200	Safety class I
910925868702	WT495C 64S/840 PSD WB PI5 L1200	Safety class I
910925868708	WT490C 64S/840 PSU CLII WB WA7 L1200	Safety class II
910925869401	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1200	Safety class I
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	Safety class I

Order Code	Full Product Name	Protection class IEC
910925869403	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1200	Safety class I
910925869404	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1200	Safety class I
910925869410	WT490C 42S/840 PSU WB TW3x2.5 PI5 L1200	Safety class I
910925869606	WT490C 100S/840 PSD WB PI5 L1200	Safety class I
910925869608	WT490C 100S/840 PSU WB WA7 L1200	Safety class I
910925869609	WT490C 100S/840 PSD WB WA7 L1200	Safety class I
910925869610	WT490C 100S/840 PSU WB PI5 L1200	Safety class I
910925868412	WT490C 64S/840 PSD WB PI5 L1600	Safety class I
910925868413	WT490C 64S/840 PSU WB TW3 PI5 L1600	Safety class I
910925868414	WT490C 64S/840 PSU WB PI5 L1600	Safety class I
910925868415	WT490C 80S/840 PSU WB PI5 L1600	Safety class I
910925868416	WT490C 80S/840 PSD WB PI5 L1600	Safety class I
910925868417	WT490C 80S/840 PSU WB TW3 PI5 L1600	Safety class I
910925868418	WT490C 64S/840 PSD WB WA7 L1600	Safety class I
910925868419	WT490C 64S/840 PSU WB TW3 WA7 L1600	Safety class I
910925868420	WT490C 64S/840 PSU WB WA7 L1600	Safety class I
910925868421	WT490C 80S/840 PSU WB WA7 L1600	Safety class I
910925868422	WT490C 80S/840 PSD WB WA7 L1600	Safety class I
910925868423	WT490C 80S/840 PSU WB TW3 WA7 L1600	Safety class I
910925868692	WT490C 35S/840 PSU WB PI5 L1600	Safety class I
910925868694	WT490C 35S/840 PSU WB WA7 L1600	Safety class I
910925869407	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1600	Safety class I
910925869408	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1600	Safety class I
910925867703	WT490C 23S/840 PSD WB PI5 L700	Safety class I
910925868287	WT490C 23S/840 PSU WB PI5 L700	Safety class I
910925868250	WT490C 64S/840 PSU WB TCW5W5 L1200	Safety class I
910925868510	WT490C 64S/840 PSU WB W5 L1200	Safety class I
910925868511	WT490C 80S/840 PSU WB W5 L1200	Safety class I
910925868512	WT490C 64S/840 PSD WB W5 L1200	Safety class I
910925868513	WT490C 80S/840 PSD WB W5 L1200	Safety class I

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910925867731	WT490C 80S/840 PSU NB-HRO PI5 L1800	(0.38, 0.38) SDCM <3
910925867732	WT490C 80S/840 PSD NB-HRO PI5 L1800	(0.38, 0.38) SDCM <3
910925867733	WT490C 80S/840 PSU WB TW3 PI5 L1800	(0.38, 0.38) SDCM <3
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	(0.38, 0.38) SDCM <3
910925867735	WT490C 80S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
910925867736	WT490C 80S/840 PSD WB TW3 PI7 L1800	(0.38, 0.38) SDCM <3
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	(0.38, 0.38) SDCM <3
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	(0.38, 0.38) SDCM <3
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	(0.38, 0.38) SDCM <3
910925867740	WT490C 100S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
910925867741	WT490C 120S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868292	WT490C 80S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868293	WT490C 100S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868294	WT490C 120S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868516	WT490C 80S/840 SIA WB IA9 PI5 L1800	(0.38, 0.38) SDCM <3
910925868697	WT490C 80S/840 PSU O L1800	(0.38, 0.38) SDCM <3
910925868698	WT490C 80S/840 PSU PCO L1800	(0.38, 0.38) SDCM <3
910925868701	WT495C 80S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925868703	WT495C 80S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868709	WT490C 80S/840 PSU CLII WB WA7 L1800	(0.38, 0.38) SDCM <3
910925869405	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1800	(0.38, 0.38) SDCM <3
910925869406	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1800	(0.38, 0.38) SDCM <3
910925869607	WT490C 150S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
910925869611	WT490C 150S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868704	WT492C 64S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
910925868705	WT492C 80S/840 PSU WB W5 L1800	(0.38, 0.38) SDCM <3
910925868706	WT492C 64S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3
910925868707	WT492C 80S/840 PSD WB W5 L1800	(0.38, 0.38) SDCM <3
910770229590	WT490C 42S/830 PSU WB PI5 L1200	(0.43, 0.40) SDCM <3
910925867704	WT490C 42S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
910925867705	WT490C 64S/840 PSU NB-HRO PI5 L1200	(0.38, 0.38) SDCM <3
910925867706	WT490C 64S/840 PSD NB-HRO PI5 L1200	(0.38, 0.38) SDCM <3
910925867707	WT490C 64S/840 PSU WB TW1 PI5 L1200	(0.38, 0.38) SDCM <3
910925867708	WT490C 64S/840 PSU WB TW3 PI5 L1200	(0.38, 0.38) SDCM <3
910925867709	WT490C 64S/840 PSU WB TCW5 PI5 L1200	(0.38, 0.38) SDCM <3
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	(0.38, 0.38) SDCM <3

Pacific LED Gen5

Order Code	Full Product Name	Initial chromaticity
910925867711	WT490C 64S/840 PSU WB ELP3TW1 PI5 L12	(0.38, 0.38) SDCM <3
910925867712	WT490C 64S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
910925867713	WT490C 64S/840 PSD WB TW1 PI5 L1200	(0.38, 0.38) SDCM <3
910925867714	WT490C 64S/840 PSD WB TW3 PI7 L1200	(0.38, 0.38) SDCM <3
910925867715	WT490C 64S/840 PSD WB ELD3PI7 L1200	(0.38, 0.38) SDCM <3
910925867716	WT490C 64S/840 PSD WB ELD3TW1 PI7 L12	(0.38, 0.38) SDCM <3
910925867717	WT490C 64S/840 PSU VVB PI5L1200	(0.38, 0.38) SDCM <3
910925867718	WT490C 64S/840 PSD VVB PI5L1200	(0.38, 0.38) SDCM <3
910925867719	WT490C 80S/840 PSU NB-HRO PI5 L1200	(0.38, 0.38) SDCM <3
910925867720	WT490C 80S/840 PSD NB-HRO PI5 L1200	(0.38, 0.38) SDCM <3
910925867721	WT490C 80S/840 PSU WB TW1 PI5 L1200	(0.38, 0.38) SDCM <3
910925867722	WT490C 80S/840 PSU WB TW3 PI5 L1200	(0.38, 0.38) SDCM <3
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	(0.38, 0.38) SDCM <3
910925867724	WT490C 80S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
910925867725	WT490C 80S/840 PSD WB TW1 PI5 L1200	(0.38, 0.38) SDCM <3
910925867726	WT490C 80S/840 PSD WB TW3 PI7 L1200	(0.38, 0.38) SDCM <3
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	(0.38, 0.38) SDCM <3
910925867728	WT490C 80S/840 PSU VVB PI5 L1200	(0.38, 0.38) SDCM <3
910925867729	WT490C 80S/840 PSD VVB PI5 L1200	(0.38, 0.38) SDCM <3
910925867743	WT490C 64S/840 PSU NB-HRO WA7 L1200	(0.38, 0.38) SDCM <3
910925867744	WT490C 64S/840 PSD NB-HRO WA7 L1200	(0.38, 0.38) SDCM <3
910925868247	WT490C 64S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868249	WT490C 64S/840 PSU WB TW3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868252	WT490C 64S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868253	WT490C 64S/840 PSD WB TW3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868255	WT490C 64S/840 PSU VVB WA7 L1200	(0.38, 0.38) SDCM <3
910925868256	WT490C 64S/840 PSD VVB WA7 L1200	(0.38, 0.38) SDCM <3
910925868257	WT490C 80S/840 PSU NB-HRO WA7 L1200	(0.38, 0.38) SDCM <3
910925868258	WT490C 80S/840 PSD NB-HRO WA7 L1200	(0.38, 0.38) SDCM <3
910925868259	WT490C 80S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868260	WT490C 80S/840 PSU WB TW3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868262	WT490C 80S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868263	WT490C 80S/840 PSD WB TW3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868265	WT490C 80S/840 PSU VVB WA7L1200	(0.38, 0.38) SDCM <3
910925868266	WT490C 80S/840 PSD VVB WA7L1200	(0.38, 0.38) SDCM <3
910925868288	WT490C 42S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868289	WT490C 64S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868290	WT490C 80S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868509	WT490C 42S/840 PSD VVB PI5 L1200	(0.38, 0.38) SDCM <3
910925868611	WT490C 42S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868612	WT490C 42S/840 PSU VVB WA7 L1200	(0.38, 0.38) SDCM <3
910925868613	WT490C 42S/840 PSU WB TW3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868614	WT490C 42S/840 PSU VVB TW3 WA7 L1200	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925868615	WT490C 42S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868616	WT490C 42S/840 PSD VVB WA7 L1200	(0.38, 0.38) SDCM <3
910925868617	WT490C 42S/840 PSD WB TW3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868618	WT490C 42S/840 PSD VVB TW3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868619	WT490C 64S/840 PSU NB-HRO TW3 WA7 L12	(0.38, 0.38) SDCM <3
910925868620	WT490C 64S/840 PSD NB-HRO TW3 WA7 L12	(0.38, 0.38) SDCM <3
910925868621	WT490C 80S/840 PSU NB-HRO TW3 WA7 L12	(0.38, 0.38) SDCM <3
910925868622	WT490C 80S/840 PSD NB-HRO TW3 WA7 L12	(0.38, 0.38) SDCM <3
910925868691	WT490C 35S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868693	WT490C 35S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868695	WT490C 64S/840 PSU O L1200	(0.38, 0.38) SDCM <3
910925868696	WT490C 64S/840 PSU PCO L1200	(0.38, 0.38) SDCM <3
910925868699	WT495C 64S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868702	WT495C 64S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868708	WT490C 64S/840 PSU CLII WB WA7 L1200	(0.38, 0.38) SDCM <3
910925869401	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1200	(0.38, 0.38) SDCM <3
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	(0.38, 0.38) SDCM <3
910925869403	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1200	(0.38, 0.38) SDCM <3
910925869404	WT490C 80S/840 PSD WB TW3x2.5 PI7 L1200	(0.38, 0.38) SDCM <3
910925869410	WT490C 42S/840 PSU WB TW3x2.5 PI5 L1200	(0.38, 0.38) SDCM <3
910925869606	WT490C 100S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
910925869608	WT490C 100S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
910925869609	WT490C 100S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
910925869610	WT490C 100S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868412	WT490C 64S/840 PSD WB PI5 L1600	(0.38, 0.38) SDCM <3
910925868413	WT490C 64S/840 PSU WB TW3 PI5 L1600	(0.38, 0.38) SDCM <3
910925868414	WT490C 64S/840 PSU WB PI5 L1600	(0.38, 0.38) SDCM <3
910925868415	WT490C 80S/840 PSU WB PI5 L1600	(0.38, 0.38) SDCM <3
910925868416	WT490C 80S/840 PSD WB PI5 L1600	(0.38, 0.38) SDCM <3
910925868417	WT490C 80S/840 PSU WB TW3 PI5 L1600	(0.38, 0.38) SDCM <3
910925868418	WT490C 64S/840 PSD WB WA7 L1600	(0.38, 0.38) SDCM <3
910925868419	WT490C 64S/840 PSU WB TW3 WA7 L1600	(0.38, 0.38) SDCM <3
910925868420	WT490C 64S/840 PSU WB WA7 L1600	(0.38, 0.38) SDCM <3
910925868421	WT490C 80S/840 PSU WB WA7 L1600	(0.38, 0.38) SDCM <3
910925868422	WT490C 80S/840 PSD WB WA7 L1600	(0.38, 0.38) SDCM <3
910925868423	WT490C 80S/840 PSU WB TW3 WA7 L1600	(0.38, 0.38) SDCM <3
910925868692	WT490C 35S/840 PSU WB PI5 L1600	(0.38, 0.38) SDCM <3
910925868694	WT490C 35S/840 PSU WB WA7 L1600	(0.38, 0.38) SDCM <3
910925869407	WT490C 64S/840 PSU WB TW3x2.5 PI5 L1600	(0.38, 0.38) SDCM <3
910925869408	WT490C 80S/840 PSU WB TW3x2.5 PI5 L1600	(0.38, 0.38) SDCM <3
910925867703	WT490C 23S/840 PSD WB PI5 L700	(0.38, 0.38) SDCM <3
910925868287	WT490C 23S/840 PSU WB PI5 L700	(0.38, 0.38) SDCM <3
910925868250	WT490C 64S/840 PSU WB TCW5W5 L1200	(0.38, 0.38) SDCM <3
910925868510	WT490C 64S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
910925868511	WT490C 80S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
910925868512	WT490C 64S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3
910925868513	WT490C 80S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3

Pacific LED Gen5

