



Safe & Reliable

Essential Smartbright Projector Gen 2

Essential SmartBright Projector ST033T is a value for money product designed for Mass market trade. It is designed to replace halogen and CDM-standard-based projectors for retail and hospitality applications. This track based luminaire supports retailers to let their products stand out, or highlight certain objects. The clean and contemporary design with integrated driver, and choice in 24 or 36 degree beam angle makes the Essential SmartBright Projector relevant to many applications. The choice of 2 colors in White and Black helps the Retailer to choose products best suited to blend into the Store Environment. Compared to its predecessor, it is not only cost effective, but also a more sleek and lighter product design. The product family includes 1M and 2M Track in Black and white color with I and L connector to support various applications.

Benefits

- Reduced operating costs thanks to energy savings and longer lifetime, compared to conventional CDM-standard-based projectors
- Value for Money product for Mass market retail applications
- Clean, simple finish ensures Essential SmartBright Projector blends into many interior designs.

Features

- Unobtrusive design in white or black finish
- 24 and 36 degree beam angle with Lumen output ranging from 800-2500 Lm.
- Energy-efficient: 80 lm/W
- Integrated driver and uniform track adaptor
- color temperature 3000 or 4000 K

Application

- Fashion
- Retail
- Hospitality

Essential Smartbright Projector Gen 2

Versions




ST033T GM 10W

ST033T GM 20W


ST033T GM 7W

Essential SmartBright Projector 30W


Dimensional drawing




ST033T 30W




ST033T 30W




ST033T 10W



ST033T 7W



ST033T 30W



ST033T 30W

Essential Smartbright Projector Gen 2

General Information

CE mark	-
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +45 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Mech. impact protection code	IK03
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Flammability mark
911401888682	ST033T LED8/830 10W 220-240V I MB WH GM	-
911401888782	ST033T LED8/830 10W 220-240V I WB WH GM	-
911401888882	ST033T LED8/840 10W 220-240V I MB WH GM	-
911401888982	ST033T LED8/840 10W 220-240V I WB WH GM	-
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	For mounting on normally flammable surfaces
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	For mounting on normally flammable surfaces
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	For mounting on normally flammable surfaces
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	For mounting on normally flammable surfaces
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	For mounting on normally flammable surfaces
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	For mounting on normally flammable surfaces
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	For mounting on normally flammable surfaces
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	For mounting on normally flammable surfaces
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	For mounting on normally flammable surfaces
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	-
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	-
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	-
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	-
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	For mounting on normally flammable surfaces
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	For mounting on normally flammable surfaces
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	For mounting on normally flammable surfaces
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	-
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	-
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	-
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	-
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	For mounting on normally flammable surfaces
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	For mounting on normally flammable surfaces
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	For mounting on normally flammable surfaces
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	For mounting on normally flammable surfaces
911401888282	ST033T LED5/830 7W 220-240V I WB WH GM	-
911401888382	ST033T LED5/840 7W 220-240V I WB WH GM	-
911401889482	ST033T LED17/830 20W 220-240V I MB WH GM	-
911401889582	ST033T LED17/830 20W 220-240V I WB WH GM	-
911401889682	ST033T LED17/840 20W 220-240V I MB WH GM	-
911401889782	ST033T LED17/840 20W 220-240V I WB WH GM	-

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Flammability mark
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	For mounting on normally flammable surfaces
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	For mounting on normally flammable surfaces
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	For mounting on normally flammable surfaces
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	-
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	-
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	-
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	-
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	For mounting on normally flammable surfaces
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	-
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	-
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	-
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	-
911401889082	ST033T LED8/830 10W 220-240V I MB BK GM	-
911401889182	ST033T LED8/830 10W 220-240V I WB BK GM	-
911401889282	ST033T LED8/840 10W 220-240V I MB BK GM	-
911401889382	ST033T LED8/840 10W 220-240V I WB BK GM	-
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	-
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	-
911401889882	ST033T LED17/830 20W 220-240V I MB BK GM	-
911401889982	ST033T LED17/830 20W 220-240V I WB BK GM	-
911401890082	ST033T LED17/840 20W 220-240V I MB BK GM	-
911401890182	ST033T LED17/840 20W 220-240V I WB BK GM	-
911401857182	ST033T LED8/830 10W 220-240V I MB WH CN	-
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	-
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	-
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	-
911401890282	ST033T LED25/830 30W 220-240V I MB WH GM	-
911401890382	ST033T LED25/830 30W 220-240V I WB WH GM	-
911401890482	ST033T LED25/840 30W 220-240V I MB WH GM	-
911401890582	ST033T LED25/840 30W 220-240V I WB WH GM	-
911401890682	ST033T LED25/830 30W 220-240V I MB BK GM	-
911401890782	ST033T LED25/830 30W 220-240V I WB BK GM	-
911401890882	ST033T LED25/840 30W 220-240V I MB BK GM	-
911401890982	ST033T LED25/840 30W 220-240V I WB BK GM	-
911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	-
911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	-
911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	-
911401857882	ST033T LED8/840 10W 220-240V I WB BK CN	-
911401888482	ST033T LED5/830 7W 220-240V I WB BK GM	-
911401888582	ST033T LED5/840 7W 220-240V I WB BK GM	-
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	-
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	-

Light Technical

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Correlated Color		Luminous Efficacy	
		Temperature (Nom)	Optical cover type	(rated) (Nom)	Luminous Flux
911401888682	ST033T LED8/830 10W 220-240V I MB WH GM	3000 K	Fashion proof optic beam angle 24°	80 lm/W	800 lm
911401888782	ST033T LED8/830 10W 220-240V I WB WH GM	3000 K	Fashion proof optic beam angle 36°	80 lm/W	800 lm
911401888882	ST033T LED8/840 10W 220-240V I MB WH GM	4000 K	Fashion proof optic beam angle 24°	85 lm/W	850 lm
911401888982	ST033T LED8/840 10W 220-240V I WB WH GM	4000 K	Fashion proof optic beam angle 36°	85 lm/W	850 lm
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	3000 K	Collimator with focus angle 24°	85 lm/W	850 lm
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	4000 K	Collimator with focus angle 24°	90 lm/W	900 lm
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	3000 K	Collimator with focus angle 24°	80 lm/W	1,600 lm
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	4000 K	Collimator with focus angle 24°	85 lm/W	1,700 lm
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	3000 K	Collimator with focus angle 24°	80 lm/W	2,400 lm
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	4000 K	Collimator with focus angle 24°	85 lm/W	2,500 lm

Order Code	Full Product Name	Correlated Color		Luminous Efficacy	
		Temperature (Nom)	Optical cover type	(rated) (Nom)	Luminous Flux
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	3000 K	Collimator with focus angle 24°	80 lm/W	2,400 lm
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	4000 K	Collimator with focus angle 24°	85 lm/W	2,500 lm
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	6000 K	Fashion proof optic beam angle 24°	85 lm/W	1,700 lm
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	3000 K	Fashion proof optic beam angle 24°	80 lm/W	1,600 lm
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	4000 K	Fashion proof optic beam angle 24°	85 lm/W	1,700 lm
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	3000 K	Fashion proof optic beam angle 36°	80 lm/W	1,600 lm
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	4000 K	Fashion proof optic beam angle 36°	85 lm/W	1,700 lm
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	3000 K	Collimator with focus angle 30°	85 lm/W	600 lm
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	4000 K	Collimator with focus angle 30°	85 lm/W	600 lm
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	6000 K	Fashion proof optic beam angle 24°	85 lm/W	2,500 lm

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Correlated Color		Luminous Efficacy	
		Temperature (Nom)	Optical cover type	(rated) (Nom)	Luminous Flux
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	3000 K	Fashion proof optic beam angle 24°	80 lm/W	2,400 lm
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	4000 K	Fashion proof optic beam angle 24°	83 lm/W	2,500 lm
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	3000 K	Fashion proof optic beam angle 36°	80 lm/W	2,400 lm
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	4000 K	Fashion proof optic beam angle 36°	83 lm/W	2,500 lm
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	3000 K	Collimator with focus angle 24°	85 lm/W	850 lm
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	4000 K	Collimator with focus angle 24°	90 lm/W	900 lm
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	3000 K	Collimator with focus angle 24°	80 lm/W	1,600 lm
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	4000 K	Collimator with focus angle 24°	85 lm/W	1,700 lm
911401888282	ST033T LED5/830 7W 220-240V I WB WH GM	3000 K	Fashion proof optic beam angle 30°	80 lm/W	560 lm
911401888382	ST033T LED5/840 7W 220-240V I WB WH GM	4000 K	Fashion proof optic beam angle 30°	85 lm/W	595 lm
911401889482	ST033T LED17/830 20W	3000 K	Fashion proof optic beam angle 24°	80 lm/W	1,600 lm

Order Code	Full Product Name	Correlated Color		Luminous Efficacy	
		Temperature (Nom)	Optical cover type	(rated) (Nom)	Luminous Flux
	220-240V I MB WH GM				
911401889582	ST033T LED17/830 20W 220-240V I WB WH GM	3000 K	Fashion proof optic beam angle 36°	80 lm/W	1,600 lm
911401889682	ST033T LED17/840 20W 220-240V I MB WH GM	4000 K	Fashion proof optic beam angle 24°	85 lm/W	1,700 lm
911401889782	ST033T LED17/840 20W 220-240V I WB WH GM	4000 K	Fashion proof optic beam angle 36°	85 lm/W	1,700 lm
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	3000 K	Collimator with focus angle 30°	80 lm/W	560 lm
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	4000 K	Collimator with focus angle 30°	80 lm/W	560 lm
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	6000 K	Fashion proof optic beam angle 24°	85 lm/W	2,500 lm
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	3000 K	Fashion proof optic beam angle 24°	80 lm/W	2,400 lm
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	4000 K	Fashion proof optic beam angle 24°	83 lm/W	2,500 lm
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	3000 K	Fashion proof optic beam angle 36°	80 lm/W	2,400 lm
911401859382	ST033T LED25/840 30W	4000 K	Fashion proof optic beam angle 36°	83 lm/W	2,500 lm

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Correlated Color		Luminous Efficacy	
		Temperature (Nom)	Optical cover type	(rated) (Nom)	Luminous Flux
	220-240V I WB WH CN				
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	6000 K	Fashion proof optic beam angle 24°	85 lm/W	1,700 lm
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	3000 K	Fashion proof optic beam angle 24°	80 lm/W	1,600 lm
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	4000 K	Fashion proof optic beam angle 24°	85 lm/W	1,700 lm
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	3000 K	Fashion proof optic beam angle 36°	80 lm/W	1,600 lm
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	4000 K	Fashion proof optic beam angle 36°	85 lm/W	1,700 lm
911401889082	ST033T LED8/830 10W 220-240V I MB BK GM	3000 K	Fashion proof optic beam angle 24°	80 lm/W	800 lm
911401889182	ST033T LED8/830 10W 220-240V I WB BK GM	3000 K	Fashion proof optic beam angle 36°	80 lm/W	800 lm
911401889282	ST033T LED8/840 10W 220-240V I MB BK GM	4000 K	Fashion proof optic beam angle 24°	85 lm/W	850 lm
911401889382	ST033T LED8/840 10W 220-240V I WB BK GM	4000 K	Fashion proof optic beam angle 36°	85 lm/W	850 lm
911401826784	ST033T LED25/830	3000 K	Polycarbonate micro lens optic	80 lm/W	2,400 lm

Order Code	Full Product Name	Correlated Color		Luminous Efficacy	
		Temperature (Nom)	Optical cover type	(rated) (Nom)	Luminous Flux
	30W 110-240V I WB WH KC				
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	4000 K	Polycarbonate micro lens optic	85 lm/W	2,500 lm
911401889882	ST033T LED17/830 20W 220-240V I MB BK GM	3000 K	Fashion proof optic beam angle 24°	80 lm/W	1,600 lm
911401889982	ST033T LED17/830 20W 220-240V I WB BK GM	3000 K	Fashion proof optic beam angle 36°	80 lm/W	1,600 lm
911401890082	ST033T LED17/840 20W 220-240V I MB BK GM	4000 K	Fashion proof optic beam angle 24°	85 lm/W	1,700 lm
911401890182	ST033T LED17/840 20W 220-240V I WB BK GM	4000 K	Fashion proof optic beam angle 36°	85 lm/W	1,700 lm
911401857182	ST033T LED8/830 10W 220-240V I MB WH CN	3000 K	Fashion proof optic beam angle 24°	80 lm/W	800 lm
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	4000 K	Fashion proof optic beam angle 24°	85 lm/W	850 lm
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	3000 K	Fashion proof optic beam angle 36°	80 lm/W	800 lm
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	4000 K	Fashion proof optic beam angle 36°	85 lm/W	850 lm

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Correlated Color		Luminous Efficacy	
		Temperature (Nom)	Optical cover type	(rated) (Nom)	Luminous Flux
911401890282	ST033T LED25/830 30W 220-240V I MB WH GM	3000 K	Fashion proof optic beam angle 24°	80 lm/W	2,400 lm
911401890382	ST033T LED25/830 30W 220-240V I WB WH GM	3000 K	Fashion proof optic beam angle 36°	80 lm/W	2,400 lm
911401890482	ST033T LED25/840 30W 220-240V I MB WH GM	4000 K	Fashion proof optic beam angle 24°	85 lm/W	2,500 lm
911401890582	ST033T LED25/840 30W 220-240V I WB WH GM	4000 K	Fashion proof optic beam angle 36°	85 lm/W	2,500 lm
911401890682	ST033T LED25/830 30W 220-240V I MB BK GM	3000 K	Fashion proof optic beam angle 24°	80 lm/W	2,400 lm
911401890782	ST033T LED25/830 30W 220-240V I WB BK GM	3000 K	Fashion proof optic beam angle 36°	80 lm/W	2,400 lm
911401890882	ST033T LED25/840 30W 220-240V I MB BK GM	4000 K	Fashion proof optic beam angle 24°	85 lm/W	2,500 lm
911401890982	ST033T LED25/840 30W	4000 K	Fashion proof optic beam angle 36°	85 lm/W	2,500 lm

Order Code	Full Product Name	Correlated Color		Luminous Efficacy	
		Temperature (Nom)	Optical cover type	(rated) (Nom)	Luminous Flux
	220-240V I WB BK GM				
911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	3000 K	Fashion proof optic beam angle 24°	80 lm/W	800 lm
911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	4000 K	Fashion proof optic beam angle 24°	85 lm/W	850 lm
911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	3000 K	Fashion proof optic beam angle 36°	80 lm/W	800 lm
911401857882	ST033T LED8/840 10W 220-240V I WB BK CN	4000 K	Fashion proof optic beam angle 36°	85 lm/W	850 lm
911401888482	ST033T LED5/830 7W 220-240V I WB BK GM	3000 K	Fashion proof optic beam angle 30°	80 lm/W	560 lm
911401888582	ST033T LED5/840 7W 220-240V I WB BK GM	4000 K	Fashion proof optic beam angle 30°	85 lm/W	595 lm
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	3000 K	Polycarbonate micro lens optic	80 lm/W	2,400 lm
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	4000 K	Polycarbonate micro lens optic	85 lm/W	2,500 lm

Operating and Electrical

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
911401888682	ST033T LED8/830 10W 220-240V I MB WH GM	220 to 240 V	10 W
911401888782	ST033T LED8/830 10W 220-240V I WB WH GM	220 to 240 V	10 W

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
911401888882	ST033T LED8/840 10W 220-240V I MB WH GM	220 to 240 V	10 W
911401888982	ST033T LED8/840 10W 220-240V I WB WH GM	220 to 240 V	10 W

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Input Voltage	Power	
			Consumption	
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	110 to 240 V	10 W	
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	110 to 240 V	10 W	
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	110 to 240 V	20 W	
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	110 to 240 V	20 W	
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	110 to 240 V	30 W	
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	110 to 240 V	30 W	
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	110 to 240 V	30 W	
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	110 to 240 V	30 W	
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	220 to 240 V	20 W	
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	220 to 240 V	20 W	
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	220 to 240 V	20 W	
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	220 to 240 V	20 W	
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	220 to 240 V	20 W	
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	110 to 240 V	7 W	
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	110 to 240 V	7 W	
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	220 to 240 V	30 W	
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	220 to 240 V	30 W	
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	220 to 240 V	30 W	
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	220 to 240 V	30 W	
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	220 to 240 V	30 W	
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	110 to 240 V	10 W	
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	110 to 240 V	10 W	
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	110 to 240 V	20 W	
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	110 to 240 V	20 W	
911401888282	ST033T LED5/830 7W 220-240V I WB WH GM	220 to 240 V	7 W	

Order Code	Full Product Name	Input Voltage	Power	
			Consumption	
911401888382	ST033T LED5/840 7W 220-240V I WB WH GM	220 to 240 V	7 W	
911401889482	ST033T LED17/830 20W 220-240V I MB WH GM	220 to 240 V	20 W	
911401889582	ST033T LED17/830 20W 220-240V I WB WH GM	220 to 240 V	20 W	
911401889682	ST033T LED17/840 20W 220-240V I MB WH GM	220 to 240 V	20 W	
911401889782	ST033T LED17/840 20W 220-240V I WB WH GM	220 to 240 V	20 W	
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	110 to 240 V	7 W	
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	110 to 240 V	7 W	
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	220 to 240 V	30 W	
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	220 to 240 V	30 W	
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	220 to 240 V	30 W	
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	220 to 240 V	30 W	
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	220 to 240 V	30 W	
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	220 to 240 V	20 W	
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	220 to 240 V	20 W	
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	220 to 240 V	20 W	
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	220 to 240 V	20 W	
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	220 to 240 V	20 W	
911401889082	ST033T LED8/830 10W 220-240V I MB BK GM	220 to 240 V	10 W	
911401889182	ST033T LED8/830 10W 220-240V I WB BK GM	220 to 240 V	10 W	
911401889282	ST033T LED8/840 10W 220-240V I MB BK GM	220 to 240 V	10 W	
911401889382	ST033T LED8/840 10W 220-240V I WB BK GM	220 to 240 V	10 W	
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	110 to 240 V	30 W	
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	110 to 240 V	30 W	
911401889882	ST033T LED17/830 20W 220-240V I MB BK GM	220 to 240 V	20 W	
911401889982	ST033T LED17/830 20W 220-240V I WB BK GM	220 to 240 V	20 W	

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
911401890082	ST033T LED17/840 20W 220-240V I MB BK GM	220 to 240 V	20 W
911401890182	ST033T LED17/840 20W 220-240V I WB BK GM	220 to 240 V	20 W
911401857182	ST033T LED8/830 10W 220-240V I MB WH CN	220 to 240 V	10 W
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	220 to 240 V	10 W
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	220 to 240 V	10 W
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	220 to 240 V	10 W
911401890282	ST033T LED25/830 30W 220-240V I MB WH GM	220 to 240 V	30 W
911401890382	ST033T LED25/830 30W 220-240V I WB WH GM	220 to 240 V	30 W
911401890482	ST033T LED25/840 30W 220-240V I MB WH GM	220 to 240 V	30 W
911401890582	ST033T LED25/840 30W 220-240V I WB WH GM	220 to 240 V	30 W
911401890682	ST033T LED25/830 30W 220-240V I MB BK GM	220 to 240 V	30 W

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
911401890782	ST033T LED25/830 30W 220-240V I WB BK GM	220 to 240 V	30 W
911401890882	ST033T LED25/840 30W 220-240V I MB BK GM	220 to 240 V	30 W
911401890982	ST033T LED25/840 30W 220-240V I WB BK GM	220 to 240 V	30 W
911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	220 to 240 V	10 W
911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	220 to 240 V	10 W
911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	220 to 240 V	10 W
911401857882	ST033T LED8/840 10W 220-240V I WB BK CN	220 to 240 V	10 W
911401888482	ST033T LED5/830 7W 220-240V I WB BK GM	220 to 240 V	7 W
911401888582	ST033T LED5/840 7W 220-240V I WB BK GM	220 to 240 V	7 W
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	110 to 240 V	30 W
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	110 to 240 V	30 W

Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401888682	ST033T LED8/830 10W 220-240V I MB WH GM	White
911401888782	ST033T LED8/830 10W 220-240V I WB WH GM	White
911401888882	ST033T LED8/840 10W 220-240V I MB WH GM	White
911401888982	ST033T LED8/840 10W 220-240V I WB WH GM	White
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	Black
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	Black
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	Black
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	Black
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	White
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	White
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	Black
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	Black
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	Aluminum and black
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	Aluminum and black
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	Aluminum and black
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	Aluminum and black
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	Aluminum and black
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	White
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	White
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	Aluminum and black
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	Aluminum and black
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	Aluminum and black
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	Aluminum and black
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	Aluminum and black
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	White

Order Code	Full Product Name	Housing Color
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	White
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	White
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	White
911401888282	ST033T LED5/830 7W 220-240V I WB WH GM	White
911401888382	ST033T LED5/840 7W 220-240V I WB WH GM	White
911401889482	ST033T LED17/830 20W 220-240V I MB WH GM	White
911401889582	ST033T LED17/830 20W 220-240V I WB WH GM	White
911401889682	ST033T LED17/840 20W 220-240V I MB WH GM	White
911401889782	ST033T LED17/840 20W 220-240V I WB WH GM	White
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	Black
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	Black
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	Aluminum and white
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	Aluminum and white
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	Aluminum and white
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	Aluminum and white
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	Aluminum and white
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	Aluminum and white
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	Aluminum and white
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	Aluminum and white
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	Aluminum and white
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	Aluminum and white
911401889082	ST033T LED8/830 10W 220-240V I MB BK GM	Black
911401889182	ST033T LED8/830 10W 220-240V I WB BK GM	Black
911401889282	ST033T LED8/840 10W 220-240V I MB BK GM	Black
911401889382	ST033T LED8/840 10W 220-240V I WB BK GM	Black

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Housing Color
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	White
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	White
911401889882	ST033T LED17/830 20W 220-240V I MB BK GM	Black
911401889982	ST033T LED17/830 20W 220-240V I WB BK GM	Black
911401890082	ST033T LED17/840 20W 220-240V I MB BK GM	Black
911401890182	ST033T LED17/840 20W 220-240V I WB BK GM	Black
911401857182	ST033T LED8/830 10W 220-240V I MB WH CN	Aluminum and white
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	Aluminum and white
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	Aluminum and white
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	Aluminum and white
911401890282	ST033T LED25/830 30W 220-240V I MB WH GM	White
911401890382	ST033T LED25/830 30W 220-240V I WB WH GM	White
911401890482	ST033T LED25/840 30W 220-240V I MB WH GM	White

Order Code	Full Product Name	Housing Color
911401890582	ST033T LED25/840 30W 220-240V I WB WH GM	White
911401890682	ST033T LED25/830 30W 220-240V I MB BK GM	Black
911401890782	ST033T LED25/830 30W 220-240V I WB BK GM	Black
911401890882	ST033T LED25/840 30W 220-240V I MB BK GM	Black
911401890982	ST033T LED25/840 30W 220-240V I WB BK GM	Black
911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	Aluminum and black
911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	Aluminum and black
911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	Aluminum and black
911401857882	ST033T LED8/840 10W 220-240V I WB BK CN	Aluminum and black
911401888482	ST033T LED5/830 7W 220-240V I WB BK GM	Black
911401888582	ST033T LED5/840 7W 220-240V I WB BK GM	Black
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	Black
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	Black

Approval and Application

Order Code	Full Product Name	Protection class IEC
911401888682	ST033T LED8/830 10W 220-240V I MB WH GM	Safety class I
911401888782	ST033T LED8/830 10W 220-240V I WB WH GM	Safety class I
911401888882	ST033T LED8/840 10W 220-240V I MB WH GM	Safety class I
911401888982	ST033T LED8/840 10W 220-240V I WB WH GM	Safety class I
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	Safety class II
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	Safety class II
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	Safety class II
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	Safety class II
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	Safety class II
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	Safety class II
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	Safety class II
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	Safety class II
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	Safety class I
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	Safety class I
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	Safety class I
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	Safety class I
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	Safety class I
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	Safety class II
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	Safety class II
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	Safety class I
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	Safety class I
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	Safety class I
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	Safety class I
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	Safety class I
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	Safety class II
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	Safety class II
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	Safety class II
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	Safety class II
911401888282	ST033T LED5/830 7W 220-240V I WB WH GM	Safety class I
911401888382	ST033T LED5/840 7W 220-240V I WB WH GM	Safety class I
911401889482	ST033T LED17/830 20W 220-240V I MB WH GM	Safety class I
911401889582	ST033T LED17/830 20W 220-240V I WB WH GM	Safety class I
911401889682	ST033T LED17/840 20W 220-240V I MB WH GM	Safety class I
911401889782	ST033T LED17/840 20W 220-240V I WB WH GM	Safety class I
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	Safety class II

Order Code	Full Product Name	Protection class IEC
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	Safety class II
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	Safety class I
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	Safety class I
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	Safety class I
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	Safety class I
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	Safety class I
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	Safety class I
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	Safety class I
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	Safety class I
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	Safety class I
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	Safety class I
911401889082	ST033T LED8/830 10W 220-240V I MB BK GM	Safety class I
911401889182	ST033T LED8/830 10W 220-240V I WB BK GM	Safety class I
911401889282	ST033T LED8/840 10W 220-240V I MB BK GM	Safety class I
911401889382	ST033T LED8/840 10W 220-240V I WB BK GM	Safety class I
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	Safety class II
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	Safety class II
911401889882	ST033T LED17/830 20W 220-240V I MB BK GM	Safety class I
911401889982	ST033T LED17/830 20W 220-240V I WB BK GM	Safety class I
911401890082	ST033T LED17/840 20W 220-240V I MB BK GM	Safety class I
911401890182	ST033T LED17/840 20W 220-240V I WB BK GM	Safety class I
911401857182	ST033T LED8/830 10W 220-240V I MB WH CN	Safety class I
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	Safety class I
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	Safety class I
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	Safety class I
911401890282	ST033T LED25/830 30W 220-240V I MB WH GM	Safety class I
911401890382	ST033T LED25/830 30W 220-240V I WB WH GM	Safety class I
911401890482	ST033T LED25/840 30W 220-240V I MB WH GM	Safety class I
911401890582	ST033T LED25/840 30W 220-240V I WB WH GM	Safety class I
911401890682	ST033T LED25/830 30W 220-240V I MB BK GM	Safety class I
911401890782	ST033T LED25/830 30W 220-240V I WB BK GM	Safety class I
911401890882	ST033T LED25/840 30W 220-240V I MB BK GM	Safety class I
911401890982	ST033T LED25/840 30W 220-240V I WB BK GM	Safety class I
911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	Safety class I
911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	Safety class I

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Protection class IEC
911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	Safety class I
911401857882	ST033T LED8/840 10W 220-240V I WB BK CN	Safety class I
911401888482	ST033T LED5/830 7W 220-240V I WB BK GM	Safety class I

Order Code	Full Product Name	Protection class IEC
911401888582	ST033T LED5/840 7W 220-240V I WB BK GM	Safety class I
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	Safety class II
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	Safety class II

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401888682	ST033T LED8/830 10W 220-240V I MB WH GM	(0.4316, 0.3984) SDCM <5
911401888782	ST033T LED8/830 10W 220-240V I MB WH GM	(0.4316, 0.3984) SDCM <5
911401888882	ST033T LED8/840 10W 220-240V I MB WH GM	(0.3811, 0.3772) SDCM <5
911401888982	ST033T LED8/840 10W 220-240V I MB WH GM	(0.3811, 0.3772) SDCM <5
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	(0.4338, 0.4030) SDCM <5
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	(0.3818, 0.3797) SDCM <5
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	(0.4338, 0.4030) SDCM <5
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	(0.3818, 0.3797) SDCM <5
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	(0.4338, 0.4030) SDCM <5
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	(0.3818, 0.3797) SDCM <5
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	(0.4338, 0.4030) SDCM <5
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	(0.3818, 0.3797) SDCM <5
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	(0.318, 0.333) SDCM≤5
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	(0.4338, 0.4030) SDCM <5
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	(0.3818, 0.3797) SDCM <5
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	(0.318, 0.333) SDCM≤5
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5

Order Code	Full Product Name	Initial chromaticity
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	(0.4338, 0.4030) SDCM <5
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	(0.3818, 0.3797) SDCM <5
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	(0.4338, 0.4030) SDCM <5
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	(0.3818, 0.3797) SDCM <5
911401888282	ST033T LED5/830 7W 220-240V I WB WH GM	(0.4338, 0.4030) SDCM <5
911401888382	ST033T LED5/840 7W 220-240V I WB WH GM	(0.3818, 0.3797) SDCM <5
911401889482	ST033T LED17/830 20W 220-240V I MB WH GM	(0.4316, 0.3984) SDCM <5
911401889582	ST033T LED17/830 20W 220-240V I WB WH GM	(0.4316, 0.3984) SDCM <5
911401889682	ST033T LED17/840 20W 220-240V I MB WH GM	(0.3811, 0.3772) SDCM <5
911401889782	ST033T LED17/840 20W 220-240V I WB WH GM	(0.3811, 0.3772) SDCM <5
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	(0.4338, 0.4030) SDCM <5
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	(0.3818, 0.3797) SDCM <5
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	(0.318, 0.333) SDCM≤5
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	(0.318, 0.333) SDCM≤5
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Initial chromaticity	Order Code	Full Product Name	Initial chromaticity
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5	911401890382	ST033T LED25/830 30W 220-240V I WB WH GM	(0.4316, 0.3984) SDCM <5
911401889082	ST033T LED8/830 10W 220-240V I MB BK GM	(0.4316, 0.3984) SDCM <5	911401890482	ST033T LED25/840 30W 220-240V I MB WH GM	(0.3811, 0.3772) SDCM <5
911401889182	ST033T LED8/830 10W 220-240V I WB BK GM	(0.4316, 0.3984) SDCM <5	911401890582	ST033T LED25/840 30W 220-240V I WB WH GM	(0.3811, 0.3772) SDCM <5
911401889282	ST033T LED8/840 10W 220-240V I MB BK GM	(0.3811, 0.3772) SDCM <5	911401890682	ST033T LED25/830 30W 220-240V I MB BK GM	(0.4316, 0.3984) SDCM <5
911401889382	ST033T LED8/840 10W 220-240V I WB BK GM	(0.3811, 0.3772) SDCM <5	911401890782	ST033T LED25/830 30W 220-240V I WB BK GM	(0.4316, 0.3984) SDCM <5
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	(0.43, 0.40) SDCM <5	911401890882	ST033T LED25/840 30W 220-240V I MB BK GM	(0.3811, 0.3772) SDCM <5
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	(0.38, 0.38) SDCM <5	911401890982	ST033T LED25/840 30W 220-240V I WB BK GM	(0.3811, 0.3772) SDCM <5
911401889882	ST033T LED17/830 20W 220-240V I MB BK GM	(0.4316, 0.3984) SDCM <5	911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5
911401889982	ST033T LED17/830 20W 220-240V I WB BK GM	(0.4316, 0.3984) SDCM <5	911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5
911401890082	ST033T LED17/840 20W 220-240V I MB BK GM	(0.3811, 0.3772) SDCM <5	911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5
911401890182	ST033T LED17/840 20W 220-240V I WB BK GM	(0.3811, 0.3772) SDCM <5	911401857882	ST033T LED8/840 10W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5
911401857182	ST033T LED8/830 10W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5	911401888482	ST033T LED5/830 7W 220-240V I WB BK GM	(0.4338, 0.4030) SDCM <5
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5	911401888582	ST033T LED5/840 7W 220-240V I WB BK GM	(0.3818, 0.3797) SDCM <5
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5	911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	(0.43, 0.40) SDCM <5
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5	911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	(0.38, 0.38) SDCM <5
911401890282	ST033T LED25/830 30W 220-240V I MB WH GM	(0.4316, 0.3984) SDCM <5			

