



# The most reliable and complete lighting solution for retail and industry of today and tomorrow

## SlimPerform Batten

Lighting plays a different role in every application. Some require latest-generation solutions with high light quality and connectivity; others just simple functionality. But whether for retail or industrial applications, you always need a combination of quality, performance, and flexibility. Get to know SlimPerform. The Batten LED luminaire where all these benefits come together. Putting the new lighting trend in your company.

### Benefits

- High efficiency and longer service life to reduce operating costs
- Superior optical performance
- Easy installation
- Ready for the future

### Features

- Efficacy up to 169lm/W
- Quality and reliability with a lifetime > 50k hours
- Four optics options - DA (double asymmetric), WB (open), MB (medium) and HRO (corridor)
- Version with integrated emergency module with 3-hour autonomy
- Ready for Interact Indoor Navigation system

# SlimPerform Batten

## Application

- Hypermarkets
- Supermarkets
- Wholesalers
- Department Stores
- Pet Centers
- Home Centers
- Industries
- Logistic Warehouses

## Warnings and Safety

- 5-year warranty

## Versions



Application Conditions	
Ambient temperature range	-20 to +35 °C
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
Protection class IEC	Safety class I
Driver included	Yes
Light source replaceable	No
Initial Performance (IEC Compliant)	
Init. Color Rendering Index	>80
Luminous flux tolerance	+/-10%

## Application Conditions

Order Code	Full Product Name	Maximum dim level
919406020741	BN310P LED70/840 PSU WB L1150 WH	Not applicable
919406020751	BN310P LED70/840 PSD- VLC WB L1150 WH	1%
919406020761	BN310P LED92/840 PSU WB L1150 WH	Not applicable
919406020771	BN310P LED92/840 PSD- VLC WB L1150 WH	1%
919406020781	BN310P LED92/840 PSD- VLC WB EL L1150 WH	1%
919406020791	BN310P LED160/840 PSU WB L1700 WH	Not applicable

Order Code	Full Product Name	Maximum dim level
919406020801	BN310P LED160/840 PSD- VLC WB L1700 WH	1%
919406020811	BN310P LED160/840PSD- VLC WB EL L1700 WH	1%
919406020821	BN310P LED70/865 PSU MB L1150 WH	Not applicable
919406020831	BN310P LED70 /865 PSD- VLC MB L1150 WH	1%
919406020841	BN310P LED92/830 PSU DA L1150 WH	Not applicable
919406020851	BN310P LED92/830 PSD- VLC DA L1150 WH	1%

## SlimPerform Batten

Order Code	Full Product Name	Maximum dim level
919406020881	BN310P LED160/865 PSU HRO L1700 WH	Not applicable
919406020891	BN310P LED160/865 PSD- VLC HRO L1700 WH	1%
919406020901	BN310P LED92/865 PSU DA L1150 WH	Not applicable
919406020911	BN310P LED92/865 PSD- VLC DA L1150 WH	1%
919406020951	BN310P LED70/865 PSU WB L1150 WH	Not applicable
919406020961	BN310P LED70/865 PSD-VLC WB L1150 WH	1%
919406020971	BN310P LED70/840 PSD-VLC MB L1150 WH	1%
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	Not applicable
919406020991	BN310P LED70/840 PSD-VLC WB EL L1150 WH	1%
919406021001	BN310P LED70/830 PSU MB L1150 WH	Not applicable
919406021011	BN310P LED70/830 PSD-VLC MB L1150 WH	1%
919406021021	BN310P LED70/830 PSU WB L1150 WH	Not applicable
919406021031	BN310P LED70/830 PSD-VLC WB L1150 WH	1%
919406021041	BN310P LED92/865 PSU MB L1150 WH	Not applicable
919406021051	BN310P LED92/865 PSD-VLC MB L1150 WH	1%
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	Not applicable
919406021071	BN310P LED92/865 PSD-VLC MB EL L1150 WH	1%
919406021081	BN310P LED92/865 PSU WB L1150 WH	Not applicable
919406021091	BN310P LED92/865 PSD-VLC WB L1150 WH	1%
919406021101	BN310P LED92/865 PSU WB EL L1150 WH	Not applicable
919406021111	BN310P LED92/865 PSD WB EL L1150 WH	1%
919406021121	BN310P LED92/865 PSU DA EL L1150 WH	Not applicable
919406021131	BN310P LED92/865 PSD-VLC DA EL L1150 WH	1%
919406021141	BN310P LED92/840 PSU MB L1150 WH	Not applicable
919406021151	BN310P LED92/840 PSD-VLC MB L1150 WH	1%
919406021161	BN310P LED92/840 PSU MB EL L1150 WH	Not applicable
919406021171	BN310P LED92/840 PSD-VLC MB EL L1150 WH	1%
919406021181	BN310P LED92/840 PSU WB EL L1150 WH	Not applicable
919406021191	BN310P LED92/840 PSU DA EL L1150 WH	Not applicable
919406021201	BN310P LED92/840 PSD-VLC DA EL L1150 WH	1%
919406021211	BN310P LED92/830 PSU MB L1150 WH	Not applicable
919406021221	BN310P LED92/830 PSD-VLC MB L1150 WH	1%
919406021231	BN310P LED92/830 PSU MB EL L1150 WH	Not applicable

Order Code	Full Product Name	Maximum dim level
919406021241	BN310P LED92/830 PSD-VLC MB EL L1150 WH	1%
919406021251	BN310P LED92/830 PSU WB L1150 WH	Not applicable
919406021261	BN310P LED92/830 PSD-VLC WB L1150 WH	1%
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	Not applicable
919406021281	BN310P LED92/830 PSD-VLC WB EL L1150 WH	1%
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	Not applicable
919406021301	BN310P LED92/830 PSD-VLC DA EL L1150 WH	1%
919406021341	BN310P LED160/865 PSU MB L1700 WH	Not applicable
919406021351	BN310P LED160/865 PSD-VLC MB L1700 WH	1%
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	Not applicable
919406021371	BN310P LED160/865 PSD-VLC MB EL L1700 WH	1%
919406021381	BN310P LED160/865 PSU WB L1700 WH	Not applicable
919406021391	BN310P LED160/865 PSD-VLC WB L1700 WH	1%
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	Not applicable
919406021411	BN310P LED160/865 PSD-VLC WB EL L1700 WH	1%
919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	Not applicable
919406021431	BN310P LED160/865 PSD-VLC HRO EL L1700 WH	1%
919406021441	BN310P LED160/840 PSU MB L1700 WH	Not applicable
919406021451	BN310P LED160/840 PSD-VLC MB L1700 WH	1%
919406021461	BN310P LED160/840 PSU MB EL L1700 WH	Not applicable
919406021471	BN310P LED160/840 PSD-VLC MB EL L1700 WH	1%
919406021481	BN310P LED160/840 PSU WB EL L1700 WH	Not applicable
919406021491	BN310P LED160/840 PSD-VLC HRO L1700 WH	1%
919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	Not applicable
919406021511	BN310P LED160/840 PSD-VLC HRO EL L1700 WH	1%
919406021521	BN310P LED92/840 PSU DA L1150 WH	Not applicable
919406021531	BN310P LED92/840 PSD- VLC DA L1150 WH	1%
919406020861	BN310P LED92/840 PSU DA L1150 BK	Not applicable
919406020871	BN310P LED92/840 PSD- VLC DA L1150 BK	1%
919406021311	BN310P LED92/840 PSD-VLC WB L1150 BK	1%
919406021321	BN310P LED92/840 PSU WB EL L1150 BK	Not applicable
919406021331	BN310P LED92/840 PSD-VLC WB EL L1150 BK	1%

## Approval and Application

Order Code	Full Product Name	Ingress protection code
919406020741	BN310P LED70/840 PSU WB L1150 WH	IP20
919406020751	BN310P LED70/840 PSD- VLC WB L1150 WH	IP20
919406020761	BN310P LED92/840 PSU WB L1150 WH	IP20
919406020771	BN310P LED92/840 PSD- VLC WB L1150 WH	IP20
919406020781	BN310P LED92/840 PSD- VLC WB EL L1150 WH	IP23
919406020791	BN310P LED160/840 PSU WB L1700 WH	IP20
919406020801	BN310P LED160/840 PSD- VLC WB L1700 WH	IP20
919406020811	BN310P LED160/840 PSD- VLC WB EL L1700 WH	IP20
919406020821	BN310P LED70/865 PSU MB L1150 WH	IP20
919406020831	BN310P LED70 /865 PSD- VLC MB L1150 WH	IP20
919406020841	BN310P LED92/830 PSU DA L1150 WH	IP20
919406020851	BN310P LED92/830 PSD- VLC DA L1150 WH	IP20
919406020881	BN310P LED160/865 PSU HRO L1700 WH	IP20
919406020891	BN310P LED160/865 PSD- VLC HRO L1700 WH	IP20

Order Code	Full Product Name	Ingress protection code
919406020901	BN310P LED92/865 PSU DA L1150 WH	IP20
919406020911	BN310P LED92/865 PSD- VLC DA L1150 WH	IP20
919406020951	BN310P LED70/865 PSU WB L1150 WH	IP20
919406020961	BN310P LED70/865 PSD-VLC WB L1150 WH	IP20
919406020971	BN310P LED70/840 PSD-VLC MB L1150 WH	IP20
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	IP23
919406020991	BN310P LED70/840 PSD-VLC WB EL L1150 WH	IP23
919406021001	BN310P LED70/830 PSU MB L1150 WH	IP20
919406021011	BN310P LED70/830 PSD-VLC MB L1150 WH	IP20
919406021021	BN310P LED70/830 PSU WB L1150 WH	IP20
919406021031	BN310P LED70/830 PSD-VLC WB L1150 WH	IP20
919406021041	BN310P LED92/865 PSU MB L1150 WH	IP20
919406021051	BN310P LED92/865 PSD-VLC MB L1150 WH	IP20
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	IP23

## SlimPerform Batten

Order Code	Full Product Name	Ingress protection code
919406021071	BN310P LED92/865 PSD-VLC MB EL L1150 WH	IP23
919406021081	BN310P LED92/865 PSU WB L1150 WH	IP20
919406021091	BN310P LED92/865 PSD-VLC WB L1150 WH	IP20
919406021101	BN310P LED92/865 PSU WB EL L1150 WH	IP23
919406021111	BN310P LED92/865 PSD WB EL L1150 WH	IP23
919406021121	BN310P LED92/865 PSU DA EL L1150 WH	IP23
919406021131	BN310P LED92/865 PSD-VLC DA EL L1150 WH	IP23
919406021141	BN310P LED92/840 PSU MB L1150 WH	IP20
919406021151	BN310P LED92/840 PSD-VLC MB L1150 WH	IP20
919406021161	BN310P LED92/840 PSU MB EL L1150 WH	IP23
919406021171	BN310P LED92/840 PSD-VLC MB EL L1150 WH	IP23
919406021181	BN310P LED92/840 PSU WB EL L1150 WH	IP23
919406021191	BN310P LED92/840 PSU DA EL L1150 WH	IP23
919406021201	BN310P LED92/840 PSD-VLC DA EL L1150 WH	IP23
919406021211	BN310P LED92/830 PSU MB L1150 WH	IP20
919406021221	BN310P LED92/830 PSD-VLC MB L1150 WH	IP20
919406021231	BN310P LED92/830 PSU MB EL L1150 WH	IP23
919406021241	BN310P LED92/830 PSD-VLC MB EL L1150 WH	IP23
919406021251	BN310P LED92/830 PSU WB L1150 WH	IP20
919406021261	BN310P LED92/830 PSD-VLC WB L1150 WH	IP20
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	IP23
919406021281	BN310P LED92/830 PSD-VLC WB EL L1150 WH	IP23
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	IP23
919406021301	BN310P LED92/830 PSD-VLC DA EL L1150 WH	IP23
919406021341	BN310P LED160/865 PSU MB L1700 WH	IP20

Order Code	Full Product Name	Ingress protection code
919406021351	BN310P LED160/865 PSD-VLC MB L1700 WH	IP20
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	IP23
919406021371	BN310P LED160/865 PSD-VLC MB EL L1700 WH	IP23
919406021381	BN310P LED160/865 PSU WB L1700 WH	IP20
919406021391	BN310P LED160/865 PSD-VLC WB L1700 WH	IP20
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	IP23
919406021411	BN310P LED160/865 PSD-VLC WB EL L1700 WH	IP23
919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	IP23
919406021431	BN310P LED160/865PSD-VLC HRO EL L1700 WH	IP23
919406021441	BN310P LED160/840 PSU MB L1700 WH	IP20
919406021451	BN310P LED160/840 PSD-VLC MB L1700 WH	IP20
919406021461	BN310P LED160/840 PSU MB EL L1700 WH	IP23
919406021471	BN310P LED160/840 PSD-VLC MB EL L1700 WH	IP23
919406021481	BN310P LED160/840 PSU WB EL L1700 WH	IP23
919406021491	BN310P LED160/840 PSD-VLC HRO L1700 WH	IP20
919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	IP23
919406021511	BN310P LED160/840PSD-VLC HRO EL L1700 WH	IP23
919406021521	BN310P LED92/840 PSU DA L1150 WH	IP20
919406021531	BN310P LED92/840 PSD- VLC DA L1150 WH	IP20
919406020861	BN310P LED92/840 PSU DA L1150 BK	IP20
919406020871	BN310P LED92/840 PSD- VLC DA L1150 BK	IP20
919406021311	BN310P LED92/840 PSD-VLC WB L1150 BK	IP20
919406021321	BN310P LED92/840 PSU WB EL L1150 BK	IP23
919406021331	BN310P LED92/840 PSD-VLC WB EL L1150 BK	IP23

### Controls and Dimming

Order Code	Full Product Name	Dimmable
919406020741	BN310P LED70/840 PSU WB L1150 WH	No
919406020751	BN310P LED70/840 PSD- VLC WB L1150 WH	Yes
919406020761	BN310P LED92/840 PSU WB L1150 WH	No
919406020771	BN310P LED92/840 PSD- VLC WB L1150 WH	Yes
919406020781	BN310P LED92/840 PSD- VLC WB EL L1150 WH	Yes
919406020791	BN310P LED160/840 PSU WB L1700 WH	No
919406020801	BN310P LED160/840 PSD- VLC WB L1700 WH	Yes
919406020811	BN310P LED160/840PSD- VLC WB EL L1700 WH	Yes
919406020821	BN310P LED70/865 PSU MB L1150 WH	No
919406020831	BN310P LED70 /865 PSD- VLC MB L1150 WH	Yes
919406020841	BN310P LED92/830 PSU DA L1150 WH	No
919406020851	BN310P LED92/830 PSD- VLC DA L1150 WH	Yes
919406020881	BN310P LED160/865 PSU HRO L1700 WH	No
919406020891	BN310P LED160/865 PSD- VLC HRO L1700 WH	Yes
919406020901	BN310P LED92/865 PSU DA L1150 WH	No
919406020911	BN310P LED92/865 PSD- VLC DA L1150 WH	Yes
919406020951	BN310P LED70/865 PSU WB L1150 WH	No
919406020961	BN310P LED70/865 PSD-VLC WB L1150 WH	Yes
919406020971	BN310P LED70/840 PSD-VLC MB L1150 WH	Yes
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	No
919406020991	BN310P LED70/840 PSD-VLC WB EL L1150 WH	Yes
919406021001	BN310P LED70/830 PSU MB L1150 WH	No

Order Code	Full Product Name	Dimmable
919406021011	BN310P LED70/830 PSD-VLC MB L1150 WH	Yes
919406021021	BN310P LED70/830 PSU WB L1150 WH	No
919406021031	BN310P LED70/830 PSD-VLC WB L1150 WH	Yes
919406021041	BN310P LED92/865 PSU MB L1150 WH	No
919406021051	BN310P LED92/865 PSD-VLC MB L1150 WH	Yes
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	No
919406021071	BN310P LED92/865 PSD-VLC MB EL L1150 WH	Yes
919406021081	BN310P LED92/865 PSU WB L1150 WH	No
919406021091	BN310P LED92/865 PSD-VLC WB L1150 WH	Yes
919406021101	BN310P LED92/865 PSU WB EL L1150 WH	No
919406021111	BN310P LED92/865 PSD WB EL L1150 WH	Yes
919406021121	BN310P LED92/865 PSU DA EL L1150 WH	No
919406021131	BN310P LED92/865 PSD-VLC DA EL L1150 WH	Yes
919406021141	BN310P LED92/840 PSU MB L1150 WH	No
919406021151	BN310P LED92/840 PSD-VLC MB L1150 WH	Yes
919406021161	BN310P LED92/840 PSU MB EL L1150 WH	No
919406021171	BN310P LED92/840 PSD-VLC MB EL L1150 WH	Yes
919406021181	BN310P LED92/840 PSU WB EL L1150 WH	No
919406021191	BN310P LED92/840 PSU DA EL L1150 WH	No
919406021201	BN310P LED92/840 PSD-VLC DA EL L1150 WH	Yes
919406021211	BN310P LED92/830 PSU MB L1150 WH	No
919406021221	BN310P LED92/830 PSD-VLC MB L1150 WH	Yes

## SlimPerform Batten

Order Code	Full Product Name	Dimmable
919406021231	BN310P LED92/830 PSU MB EL L1150 WH	No
919406021241	BN310P LED92/830 PSD-VLC MB EL L1150 WH	Yes
919406021251	BN310P LED92/830 PSU WB L1150 WH	No
919406021261	BN310P LED92/830 PSD-VLC WB L1150 WH	Yes
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	No
919406021281	BN310P LED92/830 PSD-VLC WB EL L1150 WH	Yes
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	No
919406021301	BN310P LED92/830 PSD-VLC DA EL L1150 WH	Yes
919406021341	BN310P LED160/865 PSU MB L1700 WH	No
919406021351	BN310P LED160/865 PSD-VLC MB L1700 WH	Yes
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	No
919406021371	BN310P LED160/865 PSD-VLC MB EL L1700 WH	Yes
919406021381	BN310P LED160/865 PSU WB L1700 WH	No
919406021391	BN310P LED160/865 PSD-VLC WB L1700 WH	Yes
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	No
919406021411	BN310P LED160/865 PSD-VLC WB EL L1700 WH	Yes
919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	No

Order Code	Full Product Name	Dimmable
919406021431	BN310P LED160/865PSD-VLC HRO EL L1700 WH	Yes
919406021441	BN310P LED160/840 PSU MB L1700 WH	No
919406021451	BN310P LED160/840 PSD-VLC MB L1700 WH	Yes
919406021461	BN310P LED160/840 PSU MB EL L1700 WH	No
919406021471	BN310P LED160/840 PSD-VLC MB EL L1700 WH	Yes
919406021481	BN310P LED160/840 PSU WB EL L1700 WH	No
919406021491	BN310P LED160/840 PSD-VLC HRO L1700 WH	Yes
919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	No
919406021511	BN310P LED160/840PSD-VLC HRO EL L1700 WH	Yes
919406021521	BN310P LED92/840 PSU DA L1150 WH	No
919406021531	BN310P LED92/840 PSD-VLC DA L1150 WH	Yes
919406020861	BN310P LED92/840 PSU DA L1150 BK	No
919406020871	BN310P LED92/840 PSD-VLC DA L1150 BK	Yes
919406021311	BN310P LED92/840 PSD-VLC WB L1150 BK	Yes
919406021321	BN310P LED92/840 PSU WB EL L1150 BK	No
919406021331	BN310P LED92/840 PSD-VLC WB EL L1150 BK	Yes

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
919406020741	BN310P LED70/840 PSU WB L1150 WH	4000 K	165.11627906976744 lm/W	7100 lm	43 W
919406020751	BN310P LED70/840 PSD-VLC WB L1150 WH	4000 K	161.36363636363637 lm/W	7100 lm	44 W
919406020761	BN310P LED92/840 PSU WB L1150 WH	4000 K	169.64285714285714 lm/W	9500 lm	56 W
919406020771	BN310P LED92/840 PSD-VLC WB L1150 WH	4000 K	163.79310344827587 lm/W	9500 lm	58 W
919406020781	BN310P LED92/840 PSD-VLC WB EL L1150 WH	4000 K	163.79310344827587 lm/W	9500 lm	58 W
919406020791	BN310P LED160/840 PSU WB L1700 WH	4000 K	163.36633663366337 lm/W	16500 lm	101 W
919406020801	BN310P LED160/840 PSD-VLC WB L1700 WH	4000 K	161.76470588235293 lm/W	16500 lm	102 W
919406020811	BN310P LED160/840PSD-VLC WB EL L1700 WH	4000 K	161.76470588235293 lm/W	16500 lm	102 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
919406020821	BN310P LED70/865 PSU MB L1150 WH	6500 K	165.11627906976744 lm/W	7100 lm	43 W
919406020831	BN310P LED70 /865 PSD-VLC MB L1150 WH	6500 K	161.36363636363637 lm/W	7100 lm	44 W
919406020841	BN310P LED92/830 PSU DA L1150 WH	3000 K	164.28571428571428 lm/W	9200 lm	56 W
919406020851	BN310P LED92/830 PSD-VLC DA L1150 WH	3000 K	158.6206896551724 lm/W	9200 lm	58 W
919406020881	BN310P LED160/865 PSU HRO L1700 WH	6500 K	163.36633663366337 lm/W	16500 lm	101 W
919406020891	BN310P LED160/865 PSD-VLC HRO L1700 WH	6500 K	161.76470588235293 lm/W	16500 lm	102 W
919406020901	BN310P LED92/865 PSU DA L1150 WH	6500 K	169.64285714285714 lm/W	9500 lm	56 W
919406020911	BN310P LED92/865 PSD-VLC DA L1150 WH	6500 K	163.79310344827587 lm/W	9500 lm	58 W
919406020951	BN310P LED70/865 PSU WB L1150 WH	6500 K	165.11627906976744 lm/W	7100 lm	43 W

## SlimPerform Batten

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power	Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
919406020961	BN310P LED70/865 PSD- VLC WB L1150 WH	6500 K	161.36363636363637 lm/W	7100 lm	44 W	919406021101	BN310P LED92/865 PSU WB EL L1150 WH	6500 K	169.64285714285714 lm/W	9500 lm	56 W
919406020971	BN310P LED70/840 PSD- VLC MB L1150 WH	4000 K	161.36363636363637 lm/W	7100 lm	44 W	919406021111	BN310P LED92/865 PSD WB EL L1150 WH	6500 K	163.79310344827587 lm/W	9500 lm	58 W
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	4000 K	161.36363636363637 lm/W	7100 lm	44 W	919406021121	BN310P LED92/865 PSU DA EL L1150 WH	6500 K	169.64285714285714 lm/W	9500 lm	56 W
919406020991	BN310P LED70/840 PSD- VLC WB EL L1150 WH	4000 K	161.36363636363637 lm/W	7100 lm	44 W	919406021131	BN310P LED92/865 PSD- VLC DA EL L1150 WH	6500 K	163.79310344827587 lm/W	9500 lm	58 W
919406021001	BN310P LED70/830 PSU MB L1150 WH	3000 K	162.7906976744186 lm/W	7000 lm	43 W	919406021141	BN310P LED92/840 PSU MB L1150 WH	4000 K	169.64285714285714 lm/W	9500 lm	56 W
919406021011	BN310P LED70/830 PSD- VLC MB L1150 WH	3000 K	159.0909090909091 lm/W	7000 lm	44 W	919406021151	BN310P LED92/840 PSD- VLC MB L1150 WH	4000 K	163.79310344827587 lm/W	9500 lm	58 W
919406021021	BN310P LED70/830 PSU WB L1150 WH	3000 K	162.7906976744186 lm/W	7000 lm	43 W	919406021161	BN310P LED92/840 PSU MB EL L1150 WH	4000 K	169.64285714285714 lm/W	9500 lm	56 W
919406021031	BN310P LED70/830 PSD- VLC WB L1150 WH	3000 K	159.0909090909091 lm/W	7000 lm	44 W	919406021171	BN310P LED92/840 PSD- VLC MB EL L1150 WH	4000 K	163.79310344827587 lm/W	9500 lm	58 W
919406021041	BN310P LED92/865 PSU MB L1150 WH	6500 K	169.64285714285714 lm/W	9500 lm	56 W	919406021181	BN310P LED92/840 PSU WB EL L1150 WH	4000 K	169.64285714285714 lm/W	9500 lm	56 W
919406021051	BN310P LED92/865 PSD- VLC MB L1150 WH	6500 K	163.79310344827587 lm/W	9500 lm	58 W	919406021191	BN310P LED92/840 PSU DA EL L1150 WH	4000 K	169.64285714285714 lm/W	9500 lm	56 W
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	6500 K	169.64285714285714 lm/W	9500 lm	56 W	919406021201	BN310P LED92/840 PSD- VLC DA EL L1150 WH	4000 K	163.79310344827587 lm/W	9500 lm	58 W
919406021071	BN310P LED92/865 PSD- VLC MB EL L1150 WH	6500 K	163.79310344827587 lm/W	9500 lm	58 W	919406021211	BN310P LED92/830 PSU MB L1150 WH	3000 K	164.28571428571428 lm/W	9200 lm	56 W
919406021081	BN310P LED92/865 PSU WB L1150 WH	6500 K	169.64285714285714 lm/W	9500 lm	56 W	919406021221	BN310P LED92/830 PSD- VLC MB L1150 WH	3000 K	158.6206896551724 lm/W	9200 lm	58 W
919406021091	BN310P LED92/865 PSD- VLC WB L1150 WH	6500 K	163.79310344827587 lm/W	9500 lm	58 W	919406021231	BN310P LED92/830 PSU MB EL L1150 WH	3000 K	164.28571428571428 lm/W	9200 lm	56 W
						919406021241	BN310P LED92/830 PSD-	3000 K	158.6206896551724 lm/W	9200 lm	58 W

## SlimPerform Batten

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power	Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
	VLC MB EL L1150 WH						PSD-VLC WB EL L1700 WH				
919406021251	BN310P LED92/830 PSU WB L1150 WH	3000 K	164.28571428571428 lm/W	9200 lm	56 W	919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	6500 K	163.36633663366337 lm/W	16500 lm	101 W
919406021261	BN310P LED92/830 PSD-VLC WB L1150 WH	3000 K	158.6206896551724 lm/W	9200 lm	58 W	919406021431	BN310P LED160/865PSD-VLC HRO EL L1700 WH	6500 K	161.76470588235293 lm/W	16500 lm	102 W
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	3000 K	164.28571428571428 lm/W	9200 lm	56 W	919406021441	BN310P LED160/840 PSU MB L1700 WH	4000 K	163.36633663366337 lm/W	16500 lm	101 W
919406021281	BN310P LED92/830 PSD-VLC WB EL L1150 WH	3000 K	158.6206896551724 lm/W	9200 lm	58 W	919406021451	BN310P LED160/840 PSD-VLC MB L1700 WH	4000 K	161.76470588235293 lm/W	16500 lm	102 W
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	3000 K	164.28571428571428 lm/W	9200 lm	56 W	919406021461	BN310P LED160/840 PSU MB EL L1700 WH	4000 K	163.36633663366337 lm/W	16500 lm	101 W
919406021301	BN310P LED92/830 PSD-VLC DA EL L1150 WH	3000 K	158.6206896551724 lm/W	9200 lm	58 W	919406021471	BN310P LED160/840 PSD-VLC MB EL L1700 WH	4000 K	161.76470588235293 lm/W	16500 lm	102 W
919406021341	BN310P LED160/865 PSU MB L1700 WH	6500 K	163.36633663366337 lm/W	16500 lm	101 W	919406021481	BN310P LED160/840 PSU WB EL L1700 WH	4000 K	163.36633663366337 lm/W	16500 lm	101 W
919406021351	BN310P LED160/865 PSD-VLC MB L1700 WH	6500 K	161.76470588235293 lm/W	16500 lm	102 W	919406021491	BN310P LED160/840 PSD-VLC HRO L1700 WH	4000 K	161.76470588235293 lm/W	16500 lm	102 W
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	6500 K	163.36633663366337 lm/W	16500 lm	101 W	919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	4000 K	163.36633663366337 lm/W	16500 lm	101 W
919406021371	BN310P LED160/865 PSD-VLC MB EL L1700 WH	6500 K	161.76470588235293 lm/W	16500 lm	102 W	919406021511	BN310P LED160/840PSD-VLC HRO EL L1700 WH	4000 K	161.76470588235293 lm/W	16500 lm	102 W
919406021381	BN310P LED160/865 PSU WB L1700 WH	6500 K	163.36633663366337 lm/W	16500 lm	101 W	919406021521	BN310P LED92/840 PSU DA L1150 WH	4000 K	169.64285714285714 lm/W	9500 lm	56 W
919406021391	BN310P LED160/865 PSD-VLC WB L1700 WH	6500 K	161.76470588235293 lm/W	16500 lm	102 W	919406021531	BN310P LED92/840 PSD-VLC DA L1150 WH	4000 K	163.79310344827587 lm/W	9500 lm	58 W
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	6500 K	163.36633663366337 lm/W	16500 lm	101 W	919406020861	BN310P LED92/840 PSU DA L1150 BK	4000 K	169.64285714285714 lm/W	9500 lm	56 W
919406021411	BN310P LED160/865	6500 K	161.76470588235293 lm/W	16500 lm	102 W						

## SlimPerform Batten

Order Code	Full Product Name	Init. Corr.	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
		Color Temperature			
919406020871	BN310P LED92/840 PSD-VLC DA L1150 BK	4000 K	163.79310344827587 lm/W	9500 lm	58 W
919406021311	BN310P LED92/840 PSD-VLC WB L1150 BK	4000 K	163.79310344827587 lm/W	9500 lm	58 W
919406021321	BN310P LED92/840 PSU WB EL L1150 BK	4000 K	169.64285714285714 lm/W	9500 lm	56 W

Order Code	Full Product Name	Init. Corr.	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
		Color Temperature			
919406021331	BN310P LED92/840 PSD-VLC WB EL L1150 BK	4000 K	163.79310344827587 lm/W	9500 lm	58 W

### Mechanical and Housing

Order Code	Full Product Name	Color
919406020741	BN310P LED70/840 PSU WB L1150 WH	White
919406020751	BN310P LED70/840 PSD- VLC WB L1150 WH	White
919406020761	BN310P LED92/840 PSU WB L1150 WH	White
919406020771	BN310P LED92/840 PSD- VLC WB L1150 WH	White
919406020781	BN310P LED92/840 PSD- VLC WB EL L1150 WH	White
919406020791	BN310P LED160/840 PSU WB L1700 WH	White
919406020801	BN310P LED160/840 PSD- VLC WB L1700 WH	White
919406020811	BN310P LED160/840PSD- VLC WB EL L1700 WH	White
919406020821	BN310P LED70/865 PSU MB L1150 WH	White
919406020831	BN310P LED70 /865 PSD- VLC MB L1150 WH	White
919406020841	BN310P LED92/830 PSU DA L1150 WH	White
919406020851	BN310P LED92/830 PSD- VLC DA L1150 WH	White
919406020881	BN310P LED160/865 PSU HRO L1700 WH	White
919406020891	BN310P LED160/865 PSD- VLC HRO L1700 WH	White
919406020901	BN310P LED92/865 PSU DA L1150 WH	White
919406020911	BN310P LED92/865 PSD- VLC DA L1150 WH	White
919406020951	BN310P LED70/865 PSU WB L1150 WH	White
919406020961	BN310P LED70/865 PSD-VLC WB L1150 WH	White
919406020971	BN310P LED70/840 PSD-VLC MB L1150 WH	White
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	White
919406020991	BN310P LED70/840 PSD-VLC WB EL L1150 WH	White
919406021001	BN310P LED70/830 PSU MB L1150 WH	White
919406021011	BN310P LED70/830 PSD-VLC MB L1150 WH	White
919406021021	BN310P LED70/830 PSU WB L1150 WH	White
919406021031	BN310P LED70/830 PSD-VLC WB L1150 WH	White
919406021041	BN310P LED92/865 PSU MB L1150 WH	White
919406021051	BN310P LED92/865 PSD-VLC MB L1150 WH	White
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	White
919406021071	BN310P LED92/865 PSD-VLC MB EL L1150 WH	White
919406021081	BN310P LED92/865 PSU WB L1150 WH	White
919406021091	BN310P LED92/865 PSD-VLC WB L1150 WH	White
919406021101	BN310P LED92/865 PSU WB EL L1150 WH	White
919406021111	BN310P LED92/865 PSD WB EL L1150 WH	White
919406021121	BN310P LED92/865 PSU DA EL L1150 WH	White
919406021131	BN310P LED92/865 PSD-VLC DA EL L1150 WH	White
919406021141	BN310P LED92/840 PSU MB L1150 WH	White
919406021151	BN310P LED92/840 PSD-VLC MB L1150 WH	White

Order Code	Full Product Name	Color
919406021161	BN310P LED92/840 PSU MB EL L1150 WH	White
919406021171	BN310P LED92/840 PSD-VLC MB EL L1150 WH	White
919406021181	BN310P LED92/840 PSU WB EL L1150 WH	White
919406021191	BN310P LED92/840 PSU DA EL L1150 WH	White
919406021201	BN310P LED92/840 PSD-VLC DA EL L1150 WH	White
919406021211	BN310P LED92/830 PSU MB L1150 WH	White
919406021221	BN310P LED92/830 PSD-VLC MB L1150 WH	White
919406021231	BN310P LED92/830 PSU MB EL L1150 WH	White
919406021241	BN310P LED92/830 PSD-VLC MB EL L1150 WH	White
919406021251	BN310P LED92/830 PSU WB L1150 WH	White
919406021261	BN310P LED92/830 PSD-VLC WB L1150 WH	White
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	White
919406021281	BN310P LED92/830 PSD-VLC WB EL L1150 WH	White
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	White
919406021301	BN310P LED92/830 PSD-VLC DA EL L1150 WH	White
919406021341	BN310P LED160/865 PSU MB L1700 WH	White
919406021351	BN310P LED160/865 PSD-VLC MB L1700 WH	White
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	White
919406021371	BN310P LED160/865 PSD-VLC MB EL L1700 WH	White
919406021381	BN310P LED160/865 PSU WB L1700 WH	White
919406021391	BN310P LED160/865 PSD-VLC WB L1700 WH	White
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	White
919406021411	BN310P LED160/865 PSD-VLC WB EL L1700 WH	White
919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	White
919406021431	BN310P LED160/865PSD-VLC HRO EL L1700 WH	White
919406021441	BN310P LED160/840 PSU MB L1700 WH	White
919406021451	BN310P LED160/840 PSD-VLC MB L1700 WH	White
919406021461	BN310P LED160/840 PSU MB EL L1700 WH	White
919406021471	BN310P LED160/840 PSD-VLC MB EL L1700 WH	White
919406021481	BN310P LED160/840 PSU WB EL L1700 WH	White
919406021491	BN310P LED160/840 PSD-VLC HRO L1700 WH	White
919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	White
919406021511	BN310P LED160/840PSD-VLC HRO EL L1700 WH	White
919406021521	BN310P LED92/840 PSU DA L1150 WH	White
919406021531	BN310P LED92/840 PSD- VLC DA L1150 WH	White
919406020861	BN310P LED92/840 PSU DA L1150 BK	Black
919406020871	BN310P LED92/840 PSD- VLC DA L1150 BK	Black



## SlimPerform Batten

Order Code	Full Product Name	Color
919406021311	BN310P LED92/840 PSD-VLC WB L1150 BK	Black
919406021321	BN310P LED92/840 PSU WB EL L1150 BK	Black

Order Code	Full Product Name	Color
919406021331	BN310P LED92/840 PSD-VLC WB EL L1150 BK	Black

