



Philips UniFlood M gen2: A high power floodlight with true modularity

UniFlood M G2

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

UniFlood M G2

Application

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape

Warnings and Safety





- For outdoor use only.

Versions





UniFlood M Gen2

Dimensional drawing



UniFlood M G2

Dimensional drawing



General Information

| | |
|-------------------|---|
| CE mark | CE mark |
| Driver included | Yes |
| Flammability mark | For mounting on normally flammable surfaces |

Light Technical

| | |
|-----------------------------|-------------|
| Optical cover type | Clear glass |
| Color rendering index (CRI) | >80 |

Mechanical and Housing

| | |
|---------------|-----------|
| Housing Color | Dark gray |
|---------------|-----------|

Approval and Application

| | |
|------------------------------|------|
| Mech. impact protection code | IK06 |
| Ingress protection code | IP66 |

Light Technical

| Order Code | Full Product Name | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|------------------------------------|--------------------|------------------------------------|---------------|
| 911401746863 | BVP353 30LED 27K 220V L30 10 | 827 warm white | 2700 K | 4,515 lm |
| 911401746873 | BVP353 30LED 30K 220V L30 10 | 830 warm white | 3000 K | 4,710 lm |
| 911401746883 | BVP353 30LED 40K 220V L30 10 | 840 neutral white | 4000 K | 5,255 lm |
| 911401746893 | BVP353 30LED 27K 220V L30 10 DMX | 827 warm white | 2700 K | 4,220 lm |
| 911401746903 | BVP353 30LED 30K 220V L30 10 DMX | 830 warm white | 3000 K | 4,400 lm |
| 911401746913 | BVP353 30LED 40K 220V L30 10 DMX | 840 neutral white | 4000 K | 4,910 lm |
| 911401746923 | BVP353 30LED RGB 220V L30 10 DMX | RGB | - | 2,495 lm |
| 911401746933 | BVP353 32LED RGBWW 220V L30 10 DMX | RGBW | - | 2,855 lm |
| 911401746943 | BVP353 32LED RGBNW 220V L30 10 DMX | RGBW | - | 2,985 lm |
| 911401746953 | BVP353 30LED 27K 220V L30 15 | 827 warm white | 2700 K | 4,740 lm |
| 911401746963 | BVP353 30LED 30K 220V L30 15 | 830 warm white | 3000 K | 4,945 lm |
| 911401746973 | BVP353 30LED 40K 220V L30 15 | 840 neutral white | 4000 K | 5,520 lm |
| 911401746983 | BVP353 30LED 27K 220V L30 15 DMX | 827 warm white | 2700 K | 4,430 lm |
| 911401746993 | BVP353 30LED 30K 220V L30 15 DMX | 830 warm white | 3000 K | 4,620 lm |
| 911401747003 | BVP353 30LED 40K 220V L30 15 DMX | 840 neutral white | 4000 K | 5,155 lm |
| 911401747013 | BVP353 30LED RGB 220V L30 15 DMX | RGB | - | 2,620 lm |
| 911401747023 | BVP353 32LED RGBWW 220V L30 15 DMX | RGBW | - | 3,000 lm |
| 911401747033 | BVP353 32LED RGBNW 220V L30 15 DMX | RGBW | - | 3,130 lm |
| 911401747043 | BVP353 30LED 27K 220V L30 30 | 827 warm white | 2700 K | 4,910 lm |
| 911401747053 | BVP353 30LED 30K 220V L30 30 | 830 warm white | 3000 K | 5,125 lm |
| 911401747063 | BVP353 30LED 40K 220V L30 30 | 840 neutral white | 4000 K | 5,715 lm |
| 911401747073 | BVP353 30LED 27K 220V L30 30 DMX | 827 warm white | 2700 K | 4,585 lm |
| 911401747083 | BVP353 30LED 30K 220V L30 30 DMX | 830 warm white | 3000 K | 4,785 lm |
| 911401747093 | BVP353 30LED 40K 220V L30 30 DMX | 840 neutral white | 4000 K | 5,340 lm |
| 911401747103 | BVP353 30LED RGB 220V L30 30 DMX | RGB | - | 2,715 lm |
| 911401747113 | BVP353 32LED RGBWW 220V L30 30 DMX | RGBW | - | 3,105 lm |

| Order Code | Full Product Name | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|------------------------------------|--------------------|------------------------------------|---------------|
| 911401747123 | BVP353 32LED RGBNW 220V L30 30 DMX | RGBW | - | 3,245 lm |
| 911401747133 | BVP353 30LED 27K 220V L30 45 | 827 warm white | 2700 K | 4,740 lm |
| 911401747143 | BVP353 30LED 30K 220V L30 45 | 830 warm white | 3000 K | 4,945 lm |
| 911401747153 | BVP353 30LED 40K 220V L30 45 | 840 neutral white | 4000 K | 5,520 lm |
| 911401747163 | BVP353 30LED 27K 220V L30 45 DMX | 827 warm white | 2700 K | 4,430 lm |
| 911401747173 | BVP353 30LED 30K 220V L30 45 DMX | 830 warm white | 3000 K | 4,620 lm |
| 911401747183 | BVP353 30LED 40K 220V L30 45 DMX | 840 neutral white | 4000 K | 5,155 lm |
| 911401747193 | BVP353 30LED RGB 220V L30 45 DMX | RGB | - | 2,620 lm |
| 911401747203 | BVP353 32LED RGBWW 220V L30 45 DMX | RGBW | - | 3,000 lm |
| 911401747213 | BVP353 32LED RGBNW 220V L30 45 DMX | RGBW | - | 3,130 lm |
| 911401748663 | BVP354 96LED 27K 220V L40 10 | 827 warm white | 2700 K | 15,870 lm |
| 911401748673 | BVP354 96LED 30K 220V L40 10 | 830 warm white | 3000 K | 16,555 lm |
| 911401748683 | BVP354 96LED 40K 220V L40 10 | 840 neutral white | 4000 K | 18,470 lm |
| 911401748693 | BVP354 96LED 27K 220V L40 10 DMX | 827 warm white | 2700 K | 14,640 lm |
| 911401748703 | BVP354 96LED 30K 220V L40 10 DMX | 830 warm white | 3000 K | 15,270 lm |
| 911401748713 | BVP354 96LED 40K 220V L40 10 DMX | 840 neutral white | 4000 K | 17,035 lm |
| 911401748723 | BVP354 96LED RGB 220V L40 10 DMX | RGB | - | 8,170 lm |
| 911401748733 | BVP354 96LED RGBWW 220V L40 10 DMX | RGBW | - | 10,505 lm |
| 911401748743 | BVP354 96LED RGBNW 220V L40 10 DMX | RGBW | - | 10,975 lm |
| 911401748753 | BVP354 96LED 27K 220V L40 15 | 827 warm white | 2700 K | 16,665 lm |
| 911401748763 | BVP354 96LED 30K 220V L40 15 | 830 warm white | 3000 K | 17,385 lm |
| 911401748773 | BVP354 96LED 40K 220V L40 15 | 840 neutral white | 4000 K | 19,395 lm |
| 911401748783 | BVP354 96LED 27K 220V L40 15 DMX | 827 warm white | 2700 K | 15,370 lm |
| 911401748793 | BVP354 96LED 30K 220V L40 15 DMX | 830 warm white | 3000 K | 16,035 lm |
| 911401748803 | BVP354 96LED 40K 220V L40 15 DMX | 840 neutral white | 4000 K | 17,890 lm |
| 911401748813 | BVP354 96LED RGB 220V L40 15 DMX | RGB | - | 8,580 lm |
| 911401748823 | BVP354 96LED RGBWW 220V L40 15 DMX | RGBW | - | 11,030 lm |
| 911401748833 | BVP354 96LED RGBNW 220V L40 15 DMX | RGBW | - | 11,520 lm |
| 911401748843 | BVP354 96LED 27K 220V L40 30 | 827 warm white | 2700 K | 17,260 lm |
| 911401748853 | BVP354 96LED 30K 220V L40 30 | 830 warm white | 3000 K | 18,005 lm |
| 911401748863 | BVP354 96LED 40K 220V L40 30 | 840 neutral white | 4000 K | 20,085 lm |
| 911401748873 | BVP354 96LED 27K 220V L40 30 DMX | 827 warm white | 2700 K | 15,920 lm |
| 911401748883 | BVP354 96LED 30K 220V L40 30 DMX | 830 warm white | 3000 K | 16,605 lm |
| 911401748893 | BVP354 96LED 40K 220V L40 30 DMX | 840 neutral white | 4000 K | 18,525 lm |
| 911401748903 | BVP354 96LED RGB 220V L40 30 DMX | RGB | - | 8,885 lm |
| 911401748913 | BVP354 96LED RGBWW 220V L40 30 DMX | RGBW | - | 11,425 lm |
| 911401748923 | BVP354 96LED RGBNW 220V L40 30 DMX | RGBW | - | 11,935 lm |

| Order Code | Full Product Name | Light source | Correlated Color | Luminous Flux |
|--------------|-------------------------------------|-------------------|-------------------|---------------|
| | | color | Temperature (Nom) | |
| 911401748933 | EVP354 96LED 27K 220V L40 45 | 827 warm white | 2700 K | 16,665 lm |
| 911401748943 | EVP354 96LED 30K 220V L40 45 | 830 warm white | 3000 K | 17,385 lm |
| 911401748953 | EVP354 96LED 40K 220V L40 45 | 840 neutral white | 4000 K | 19,395 lm |
| 911401748963 | EVP354 96LED 27K 220V L40 45 DMX | 827 warm white | 2700 K | 15,370 lm |
| 911401748973 | EVP354 96LED 30K 220V L40 45 DMX | 830 warm white | 3000 K | 16,035 lm |
| 911401748983 | EVP354 96LED 40K 220V L40 45 DMX | 840 neutral white | 4000 K | 17,890 lm |
| 911401748993 | EVP354 96LED RGB 220V L40 45 DMX | RGB | - | 8,580 lm |
| 911401749003 | EVP354 96LED RGBWW 220V L40 45 DMX | RGBW | - | 11,030 lm |
| 911401749013 | EVP354 96LED RGBNW 220V L40 45 DMX | RGBW | - | 11,520 lm |
| 911401749023 | EVP354 120LED 27K 220V L50 10 | 827 warm white | 2700 K | 18,075 lm |
| 911401749033 | EVP354 120LED 30K 220V L50 10 | 830 warm white | 3000 K | 18,850 lm |
| 911401749043 | EVP354 120LED 40K 220V L50 10 | 840 neutral white | 4000 K | 21,035 lm |
| 911401749053 | EVP354 120LED 27K 220V L50 10 DMX | 827 warm white | 2700 K | 16,880 lm |
| 911401749063 | EVP354 120LED 30K 220V L50 10 DMX | 830 warm white | 3000 K | 17,605 lm |
| 911401749073 | EVP354 120LED 40K 220V L50 10 DMX | 840 neutral white | 4000 K | 19,645 lm |
| 911401749083 | EVP354 120LED RGB 220V L50 10 DMX | RGB | - | 9,985 lm |
| 911401749093 | EVP354 120LED RGBWW 220V L50 10 DMX | RGBW | - | 10,720 lm |
| 911401749103 | EVP354 120LED RGBNW 220V L50 10 DMX | RGBW | - | 11,190 lm |
| 911401749113 | EVP354 120LED 27K 220V L50 15 | 827 warm white | 2700 K | 18,975 lm |
| 911401749123 | EVP354 120LED 30K 220V L50 15 | 830 warm white | 3000 K | 19,795 lm |
| 911401749133 | EVP354 120LED 40K 220V L50 15 | 840 neutral white | 4000 K | 22,085 lm |
| 911401749143 | EVP354 120LED 27K 220V L50 15 DMX | 827 warm white | 2700 K | 17,720 lm |
| 911401749153 | EVP354 120LED 30K 220V L50 15 DMX | 830 warm white | 3000 K | 18,485 lm |
| 911401749163 | EVP354 120LED 40K 220V L50 15 DMX | 840 neutral white | 4000 K | 20,625 lm |
| 911401749173 | EVP354 120LED RGB 220V L50 15 DMX | RGB | - | 10,485 lm |
| 911401749183 | EVP354 120LED RGBWW 220V L50 15 DMX | RGBW | - | 11,255 lm |
| 911401749193 | EVP354 120LED RGBNW 220V L50 15 DMX | RGBW | - | 11,750 lm |
| 911401749203 | EVP354 120LED 27K 220V L50 30 | 827 warm white | 2700 K | 19,655 lm |
| 911401749213 | EVP354 120LED 30K 220V L50 30 | 830 warm white | 3000 K | 20,500 lm |
| 911401749223 | EVP354 120LED 40K 220V L50 30 | 840 neutral white | 4000 K | 22,875 lm |
| 911401749233 | EVP354 120LED 27K 220V L50 30 DMX | 827 warm white | 2700 K | 18,355 lm |
| 911401749243 | EVP354 120LED 30K 220V L50 30 DMX | 830 warm white | 3000 K | 19,145 lm |

| Order Code | Full Product Name | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|-------------------------------------|--------------------|------------------------------------|---------------|
| 911401749253 | EVP354 120LED 40K 220V L50 30 DMX | 840 neutral white | 4000 K | 21,360 lm |
| 911401749263 | EVP354 120LED RGB 220V L50 30 DMX | RGB | - | 10,860 lm |
| 911401749273 | EVP354 120LED RGBWW 220V L50 30 DMX | RGBW | - | 11,655 lm |
| 911401749283 | EVP354 120LED RGBNW 220V L50 30 DMX | RGBW | - | 12,170 lm |
| 911401749293 | EVP354 120LED 27K 220V L50 45 | 827 warm white | 2700 K | 18,975 lm |
| 911401749303 | EVP354 120LED 30K 220V L50 45 | 830 warm white | 3000 K | 19,795 lm |
| 911401749313 | EVP354 120LED 40K 220V L50 45 | 840 neutral white | 4000 K | 22,085 lm |
| 911401749323 | EVP354 120LED 27K 220V L50 45 DMX | 827 warm white | 2700 K | 17,720 lm |
| 911401749333 | EVP354 120LED 30K 220V L50 45 DMX | 830 warm white | 3000 K | 18,485 lm |
| 911401749343 | EVP354 120LED 40K 220V L50 45 DMX | 840 neutral white | 4000 K | 20,625 lm |
| 911401749353 | EVP354 120LED RGB 220V L50 45 DMX | RGB | - | 10,485 lm |
| 911401749363 | EVP354 120LED RGBWW 220V L50 45 DMX | RGBW | - | 11,255 lm |
| 911401749373 | EVP354 120LED RGBNW 220V L50 45 DMX | RGBW | - | 11,750 lm |
| 911401749383 | EVP354 144LED 27K 220V L57 10 | 827 warm white | 2700 K | 22,765 lm |
| 911401749393 | EVP354 144LED 30K 220V L57 10 | 830 warm white | 3000 K | 23,745 lm |
| 911401749403 | EVP354 144LED 40K 220V L57 10 | 840 neutral white | 4000 K | 26,490 lm |
| 911401749413 | EVP354 144LED 27K 220V L57 10 DMX | 827 warm white | 2700 K | 21,690 lm |
| 911401749423 | EVP354 144LED 30K 220V L57 10 DMX | 830 warm white | 3000 K | 22,625 lm |
| 911401749433 | EVP354 144LED 40K 220V L57 10 DMX | 840 neutral white | 4000 K | 25,240 lm |
| 911401749443 | EVP354 144LED RGB 220V L57 10 DMX | RGB | - | 13,410 lm |
| 911401749453 | EVP354 144LED RGBWW 220V L57 10 DMX | RGBW | - | 14,395 lm |
| 911401749463 | EVP354 144LED RGBNW 220V L57 10 DMX | RGBW | - | 15,030 lm |
| 911401749473 | EVP354 144LED 27K 220V L57 15 | 827 warm white | 2700 K | 23,900 lm |
| 911401749483 | EVP354 144LED 30K 220V L57 15 | 830 warm white | 3000 K | 24,930 lm |
| 911401749493 | EVP354 144LED 40K 220V L57 15 | 840 neutral white | 4000 K | 27,815 lm |
| 911401749503 | EVP354 144LED 27K 220V L57 15 DMX | 827 warm white | 2700 K | 22,775 lm |
| 911401749513 | EVP354 144LED 30K 220V L57 15 DMX | 830 warm white | 3000 K | 23,755 lm |
| 911401749523 | EVP354 144LED 40K 220V L57 15 DMX | 840 neutral white | 4000 K | 26,505 lm |
| 911401749533 | EVP354 144LED RGB 220V L57 15 DMX | RGB | - | 14,080 lm |
| 911401749543 | EVP354 144LED RGBWW 220V L57 15 DMX | RGBW | - | 15,115 lm |
| 911401749553 | EVP354 144LED RGBNW 220V L57 15 DMX | RGBW | - | 15,785 lm |
| 911401749563 | EVP354 144LED 27K 220V L57 30 | 827 warm white | 2700 K | 24,755 lm |
| 911401749573 | EVP354 144LED 30K 220V L57 30 | 830 warm white | 3000 K | 25,820 lm |
| 911401749583 | EVP354 144LED 40K 220V L57 30 | 840 neutral white | 4000 K | 28,810 lm |

| Order Code | Full Product Name | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|-------------------------------------|--------------------|------------------------------------|---------------|
| 911401749593 | EVP354 144LED 27K 220V L57 30 DMX | 827 warm white | 2700 K | 23,585 lm |
| 911401749603 | EVP354 144LED 30K 220V L57 30 DMX | 830 warm white | 3000 K | 24,605 lm |
| 911401749613 | EVP354 144LED 40K 220V L57 30 DMX | 840 neutral white | 4000 K | 27,450 lm |
| 911401749623 | EVP354 144LED RGB 220V L57 30 DMX | RGB | - | 14,585 lm |
| 911401749633 | EVP354 144LED RGBWW 220V L57 30 DMX | RGBW | - | 15,655 lm |
| 911401749643 | EVP354 144LED RGBNW 220V L57 30 DMX | RGBW | - | 16,345 lm |
| 911401749653 | EVP354 144LED 27K 220V L57 45 | 827 warm white | 2700 K | 23,900 lm |
| 911401749663 | EVP354 144LED 30K 220V L57 45 | 830 warm white | 3000 K | 24,930 lm |
| 911401749673 | EVP354 144LED 40K 220V L57 45 | 840 neutral white | 4000 K | 27,815 lm |
| 911401749683 | EVP354 144LED 27K 220V L57 45 DMX | 827 warm white | 2700 K | 22,775 lm |
| 911401749693 | EVP354 144LED 30K 220V L57 45 DMX | 830 warm white | 3000 K | 23,755 lm |
| 911401749703 | EVP354 144LED 40K 220V L57 45 DMX | 840 neutral white | 4000 K | 26,505 lm |
| 911401749713 | EVP354 144LED RGB 220V L57 45 DMX | RGB | - | 14,080 lm |
| 911401749723 | EVP354 144LED RGBWW 220V L57 45 DMX | RGBW | - | 15,115 lm |
| 911401749733 | EVP354 144LED RGBNW 220V L57 45 DMX | RGBW | - | 15,785 lm |
| 911401748303 | EVP353 72LED 27K 220V L57 10 | 827 warm white | 2700 K | 11,380 lm |
| 911401748313 | EVP353 72LED 30K 220V L57 10 | 830 warm white | 3000 K | 11,870 lm |
| 911401748323 | EVP353 72LED 40K 220V L57 10 | 840 neutral white | 4000 K | 13,245 lm |
| 911401748333 | EVP353 72LED 27K 220V L57 10 DMX | 827 warm white | 2700 K | 10,845 lm |
| 911401748343 | EVP353 72LED 30K 220V L57 10 DMX | 830 warm white | 3000 K | 11,310 lm |
| 911401748353 | EVP353 72LED 40K 220V L57 10 DMX | 840 neutral white | 4000 K | 12,620 lm |
| 911401748363 | EVP353 72LED RGB 220V L57 10 DMX | RGB | - | 6,705 lm |
| 911401748373 | EVP353 72LED RGBWW 220V L57 10 DMX | RGBW | - | 7,195 lm |
| 911401748383 | EVP353 72LED RGBNW 220V L57 10 DMX | RGBW | - | 7,515 lm |
| 911401748393 | EVP353 72LED 27K 220V L57 15 | 827 warm white | 2700 K | 11,950 lm |
| 911401748403 | EVP353 72LED 30K 220V L57 15 | 830 warm white | 3000 K | 12,465 lm |
| 911401748413 | EVP353 72LED 40K 220V L57 15 | 840 neutral white | 4000 K | 13,905 lm |
| 911401748423 | EVP353 72LED 27K 220V L57 15 DMX | 827 warm white | 2700 K | 11,385 lm |
| 911401748433 | EVP353 72LED 30K 220V L57 15 DMX | 830 warm white | 3000 K | 11,875 lm |
| 911401748443 | EVP353 72LED 40K 220V L57 15 DMX | 840 neutral white | 4000 K | 13,250 lm |
| 911401748453 | EVP353 72LED RGB 220V L57 15 DMX | RGB | - | 7,040 lm |
| 911401748463 | EVP353 72LED RGBWW 220V L57 15 DMX | RGBW | - | 7,555 lm |
| 911401748473 | EVP353 72LED RGBNW 220V L57 15 DMX | RGBW | - | 7,890 lm |
| 911401748483 | EVP353 72LED 27K 220V L57 30 | 827 warm white | 2700 K | 12,375 lm |
| 911401748493 | EVP353 72LED 30K 220V L57 30 | 830 warm white | 3000 K | 12,910 lm |
| 911401748503 | EVP353 72LED 40K 220V L57 30 | 840 neutral white | 4000 K | 14,405 lm |
| 911401748513 | EVP353 72LED 27K 220V L57 30 DMX | 827 warm white | 2700 K | 11,790 lm |

| Order Code | Full Product Name | Light source | Correlated Color | Luminous Flux |
|--------------|------------------------------------|-------------------|-------------------|---------------|
| | | color | Temperature (Nom) | |
| 911401748523 | EVP353 72LED 30K 220V L57 30 DMX | 830 warm white | 3000 K | 12,300 lm |
| 911401748533 | EVP353 72LED 40K 220V L57 30 DMX | 840 neutral white | 4000 K | 13,725 lm |
| 911401748543 | EVP353 72LED RGB 220V L57 30 DMX | RGB | - | 7,290 lm |
| 911401748553 | EVP353 72LED RGBWW 220V L57 30 DMX | RGBW | - | 7,825 lm |
| 911401748563 | EVP353 72LED RGBNW 220V L57 30 DMX | RGBW | - | 8,170 lm |
| 911401748573 | EVP353 72LED 27K 220V L57 45 | 827 warm white | 2700 K | 11,950 lm |
| 911401748583 | EVP353 72LED 30K 220V L57 45 | 830 warm white | 3000 K | 12,465 lm |
| 911401748593 | EVP353 72LED 40K 220V L57 45 | 840 neutral white | 4000 K | 13,905 lm |
| 911401748603 | EVP353 72LED 27K 220V L57 45 DMX | 827 warm white | 2700 K | 11,385 lm |
| 911401748613 | EVP353 72LED 30K 220V L57 45 DMX | 830 warm white | 3000 K | 11,875 lm |
| 911401748623 | EVP353 72LED 40K 220V L57 45 DMX | 840 neutral white | 4000 K | 13,250 lm |
| 911401748633 | EVP353 72LED RGB 220V L57 45 DMX | RGB | - | 7,040 lm |
| 911401748643 | EVP353 72LED RGBWW 220V L57 45 DMX | RGBW | - | 7,555 lm |
| 911401748653 | EVP353 72LED RGBNW 220V L57 45 DMX | RGBW | - | 7,890 lm |
| 911401746143 | EVP353 18LED 27K 220V L21 10 | 827 warm white | 2700 K | 2,845 lm |
| 911401746153 | EVP353 18LED 30K 220V L21 10 | 830 warm white | 3000 K | 2,965 lm |
| 911401746163 | EVP353 18LED 40K 220V L21 10 | 840 neutral white | 4000 K | 3,310 lm |
| 911401746173 | EVP353 18LED 27K 220V L21 10 DMX | 827 warm white | 2700 K | 2,640 lm |
| 911401746183 | EVP353 18LED 30K 220V L21 10 DMX | 830 warm white | 3000 K | 2,755 lm |
| 911401746193 | EVP353 18LED 40K 220V L21 10 DMX | 840 neutral white | 4000 K | 3,075 lm |
| 911401746203 | EVP353 18LED RGB 220V L21 10 DMX | RGB | - | 1,565 lm |
| 911401746213 | EVP353 20LED RGBWW 220V L21 10 DMX | RGBW | - | 1,860 lm |
| 911401746223 | EVP353 20LED RGBNW 220V L21 10 DMX | RGBW | - | 1,945 lm |
| 911401746233 | EVP353 18LED 27K 220V L21 15 | 827 warm white | 2700 K | 2,985 lm |
| 911401746243 | EVP353 18LED 30K 220V L21 15 | 830 warm white | 3000 K | 3,115 lm |
| 911401746253 | EVP353 18LED 40K 220V L21 15 | 840 neutral white | 4000 K | 3,475 lm |
| 911401746263 | EVP353 18LED 27K 220V L21 15 DMX | 827 warm white | 2700 K | 2,770 lm |
| 911401746273 | EVP353 18LED 30K 220V L21 15 DMX | 830 warm white | 3000 K | 2,890 lm |
| 911401746283 | EVP353 18LED 40K 220V L21 15 DMX | 840 neutral white | 4000 K | 3,225 lm |
| 911401746293 | EVP353 18LED RGB 220V L21 15 DMX | RGB | - | 1,640 lm |
| 911401746303 | EVP353 20LED RGBWW 220V L21 15 DMX | RGBW | - | 1,955 lm |
| 911401746313 | EVP353 20LED RGBNW 220V L21 15 DMX | RGBW | - | 2,040 lm |
| 911401746323 | EVP353 18LED 27K 220V L21 30 | 827 warm white | 2700 K | 3,090 lm |
| 911401746333 | EVP353 18LED 30K 220V L21 30 | 830 warm white | 3000 K | 3,225 lm |
| 911401746343 | EVP353 18LED 40K 220V L21 30 | 840 neutral white | 4000 K | 3,600 lm |
| 911401746353 | EVP353 18LED 27K 220V L21 30 DMX | 827 warm white | 2700 K | 2,870 lm |
| 911401746363 | EVP353 18LED 30K 220V L21 30 DMX | 830 warm white | 3000 K | 2,995 lm |
| 911401746373 | EVP353 18LED 40K 220V L21 30 DMX | 840 neutral white | 4000 K | 3,340 lm |
| 911401746383 | EVP353 18LED RGB 220V L21 30 DMX | RGB | - | 1,700 lm |
| 911401746393 | EVP353 20LED RGBWW 220V L21 30 DMX | RGBW | - | 2,025 lm |
| 911401746403 | EVP353 20LED RGBNW 220V L21 30 DMX | RGBW | - | 2,115 lm |

| Order Code | Full Product Name | Light source | Correlated Color | | Luminous Flux |
|--------------|------------------------------------|-------------------|-------------------|--|---------------|
| | | color | Temperature (Nom) | | |
| 911401746413 | EVP353 18LED 27K 220V L21 45 | 827 warm white | 2700 K | | 2,985 lm |
| 911401746423 | EVP353 18LED 30K 220V L21 45 | 830 warm white | 3000 K | | 3,115 lm |
| 911401746433 | EVP353 18LED 40K 220V L21 45 | 840 neutral white | 4000 K | | 3,475 lm |
| 911401746443 | EVP353 18LED 27K 220V L21 45 DMX | 827 warm white | 2700 K | | 2,770 lm |
| 911401746453 | EVP353 18LED 30K 220V L21 45 DMX | 830 warm white | 3000 K | | 2,890 lm |
| 911401746463 | EVP353 18LED 40K 220V L21 45 DMX | 840 neutral white | 4000 K | | 3,225 lm |
| 911401746473 | EVP353 18LED RGB 220V L21 45 DMX | RGB | - | | 1,640 lm |
| 911401746483 | EVP353 20LED RGBWW 220V L21 45 DMX | RGBW | - | | 1,955 lm |
| 911401746493 | EVP353 20LED RGBNW 220V L21 45 DMX | RGBW | - | | 2,040 lm |
| 911401745423 | EVP353 12LED 27K 220V L15 10 | 827 warm white | 2700 K | | 1,760 lm |
| 911401745433 | EVP353 12LED 30K 220V L15 10 | 830 warm white | 3000 K | | 1,835 lm |
| 911401745443 | EVP353 12LED 40K 220V L15 10 | 840 neutral white | 4000 K | | 2,050 lm |
| 911401745453 | EVP353 12LED 27K 220V L15 10 DMX | 827 warm white | 2700 K | | 1,615 lm |
| 911401745463 | EVP353 12LED 30K 220V L15 10 DMX | 830 warm white | 3000 K | | 1,685 lm |
| 911401745473 | EVP353 12LED 40K 220V L15 10 DMX | 840 neutral white | 4000 K | | 1,880 lm |
| 911401745483 | EVP353 12LED RGB 220V L15 10 DMX | RGB | - | | 960 lm |
| 911401745493 | EVP353 12LED RGBWW 220V L15 10 DMX | RGBW | - | | 1,175 lm |
| 911401745503 | EVP353 12LED RGBNW 220V L15 10 DMX | RGBW | - | | 1,225 lm |
| 911401745513 | EVP353 12LED 27K 220V L15 15 | 827 warm white | 2700 K | | 1,845 lm |
| 911401745523 | EVP353 12LED 30K 220V L15 15 | 830 warm white | 3000 K | | 1,925 lm |
| 911401745533 | EVP353 12LED 40K 220V L15 15 | 840 neutral white | 4000 K | | 2,150 lm |
| 911401745543 | EVP353 12LED 27K 220V L15 15 DMX | 827 warm white | 2700 K | | 1,695 lm |
| 911401745553 | EVP353 12LED 30K 220V L15 15 DMX | 830 warm white | 3000 K | | 1,770 lm |
| 911401745563 | EVP353 12LED 40K 220V L15 15 DMX | 840 neutral white | 4000 K | | 1,975 lm |
| 911401745573 | EVP353 12LED RGB 220V L15 15 DMX | RGB | - | | 1,010 lm |
| 911401745583 | EVP353 12LED RGBWW 220V L15 15 DMX | RGBW | - | | 1,230 lm |
| 911401745593 | EVP353 12LED RGBNW 220V L15 15 DMX | RGBW | - | | 1,285 lm |
| 911401745603 | EVP353 12LED 27K 220V L15 30 | 827 warm white | 2700 K | | 1,915 lm |
| 911401745613 | EVP353 12LED 30K 220V L15 30 | 830 warm white | 3000 K | | 1,995 lm |
| 911401745623 | EVP353 12LED 40K 220V L15 30 | 840 neutral white | 4000 K | | 2,225 lm |
| 911401745633 | EVP353 12LED 27K 220V L15 30 DMX | 827 warm white | 2700 K | | 1,755 lm |
| 911401745643 | EVP353 12LED 30K 220V L15 30 DMX | 830 warm white | 3000 K | | 1,830 lm |
| 911401745653 | EVP353 12LED 40K 220V L15 30 DMX | 840 neutral white | 4000 K | | 2,045 lm |
| 911401745663 | EVP353 12LED RGB 220V L15 30 DMX | RGB | - | | 1,045 lm |
| 911401745673 | EVP353 12LED RGBWW 220V L15 30 DMX | RGBW | - | | 1,275 lm |
| 911401745683 | EVP353 12LED RGBNW 220V L15 30 DMX | RGBW | - | | 1,330 lm |
| 911401745693 | EVP353 12LED 27K 220V L15 45 | 827 warm white | 2700 K | | 1,845 lm |
| 911401745703 | EVP353 12LED 30K 220V L15 45 | 830 warm white | 3000 K | | 1,925 lm |
| 911401745713 | EVP353 12LED 40K 220V L15 45 | 840 neutral white | 4000 K | | 2,150 lm |
| 911401745723 | EVP353 12LED 27K 220V L15 45 DMX | 827 warm white | 2700 K | | 1,695 lm |
| 911401745733 | EVP353 12LED 30K 220V L15 45 DMX | 830 warm white | 3000 K | | 1,770 lm |
| 911401745743 | EVP353 12LED 40K 220V L15 45 DMX | 840 neutral white | 4000 K | | 1,975 lm |
| 911401745753 | EVP353 12LED RGB 220V L15 45 DMX | RGB | - | | 1,010 lm |

| Order Code | Full Product Name | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|------------------------------------|--------------------|------------------------------------|---------------|
| 911401745763 | BVP353 12LED RGBWW 220V L15 45 DMX | RGBW | - | 1,230 lm |
| 911401745773 | BVP353 12LED RGBNW 220V L15 45 DMX | RGBW | - | 1,285 lm |
| 911401747223 | BVP353 36LED 27K 220V L35 10 | 827 warm white | 2700 K | 5,950 lm |
| 911401747233 | BVP353 36LED 30K 220V L35 10 | 830 warm white | 3000 K | 6,205 lm |
| 911401747243 | BVP353 36LED 40K 220V L35 10 | 840 neutral white | 4000 K | 6,925 lm |
| 911401747253 | BVP353 36LED 27K 220V L35 10 DMX | 827 warm white | 2700 K | 5,350 lm |
| 911401747263 | BVP353 36LED 30K 220V L35 10 DMX | 830 warm white | 3000 K | 5,585 lm |
| 911401747273 | BVP353 36LED 40K 220V L35 10 DMX | 840 neutral white | 4000 K | 6,230 lm |
| 911401747283 | BVP353 36LED RGB 220V L35 10 DMX | RGB | - | 3,290 lm |
| 911401747293 | BVP353 36LED RGBWW 220V L35 10 DMX | RGBW | - | 3,640 lm |
| 911401747303 | BVP353 36LED RGBNW 220V L35 10 DMX | RGBW | - | 3,805 lm |
| 911401747313 | BVP353 36LED 27K 220V L35 15 | 827 warm white | 2700 K | 6,245 lm |
| 911401747323 | BVP353 36LED 30K 220V L35 15 | 830 warm white | 3000 K | 6,515 lm |
| 911401747333 | BVP353 36LED 40K 220V L35 15 | 840 neutral white | 4000 K | 7,270 lm |
| 911401747343 | BVP353 36LED 27K 220V L35 15 DMX | 827 warm white | 2700 K | 5,620 lm |
| 911401747353 | BVP353 36LED 30K 220V L35 15 DMX | 830 warm white | 3000 K | 5,860 lm |
| 911401747363 | BVP353 36LED 40K 220V L35 15 DMX | 840 neutral white | 4000 K | 6,540 lm |
| 911401747373 | BVP353 36LED RGB 220V L35 15 DMX | RGB | - | 3,455 lm |
| 911401747383 | BVP353 36LED RGBWW 220V L35 15 DMX | RGBW | - | 3,825 lm |
| 911401747393 | BVP353 36LED RGBNW 220V L35 15 DMX | RGBW | - | 3,995 lm |
| 911401747403 | BVP353 36LED 27K 220V L35 30 | 827 warm white | 2700 K | 6,470 lm |
| 911401747413 | BVP353 36LED 30K 220V L35 30 | 830 warm white | 3000 K | 6,750 lm |
| 911401747423 | BVP353 36LED 40K 220V L35 30 | 840 neutral white | 4000 K | 7,530 lm |
| 911401747433 | BVP353 36LED 27K 220V L35 30 DMX | 827 warm white | 2700 K | 5,820 lm |
| 911401747443 | BVP353 36LED 30K 220V L35 30 DMX | 830 warm white | 3000 K | 6,070 lm |
| 911401747453 | BVP353 36LED 40K 220V L35 30 DMX | 840 neutral white | 4000 K | 6,775 lm |
| 911401747463 | BVP353 36LED RGB 220V L35 30 DMX | RGB | - | 3,580 lm |
| 911401747473 | BVP353 36LED RGBWW 220V L35 30 DMX | RGBW | - | 3,960 lm |
| 911401747483 | BVP353 36LED RGBNW 220V L35 30 DMX | RGBW | - | 4,135 lm |
| 911401747493 | BVP353 36LED 27K 220V L35 45 | 827 warm white | 2700 K | 6,245 lm |
| 911401747503 | BVP353 36LED 30K 220V L35 45 | 830 warm white | 3000 K | 6,515 lm |
| 911401747513 | BVP353 36LED 40K 220V L35 45 | 840 neutral white | 4000 K | 7,270 lm |
| 911401747523 | BVP353 36LED 27K 220V L35 45 DMX | 827 warm white | 2700 K | 5,620 lm |
| 911401747533 | BVP353 36LED 30K 220V L35 45 DMX | 830 warm white | 3000 K | 5,860 lm |
| 911401747543 | BVP353 36LED 40K 220V L35 45 DMX | 840 neutral white | 4000 K | 6,540 lm |
| 911401747553 | BVP353 36LED RGB 220V L35 45 DMX | RGB | - | 3,455 lm |
| 911401747563 | BVP353 36LED RGBWW 220V L35 45 DMX | RGBW | - | 3,825 lm |
| 911401747573 | BVP353 36LED RGBNW 220V L35 45 DMX | RGBW | - | 3,995 lm |
| 911401746503 | BVP353 24LED 27K 220V L24 10 | 827 warm white | 2700 K | 3,615 lm |
| 911401746513 | BVP353 24LED 30K 220V L24 10 | 830 warm white | 3000 K | 3,770 lm |

| Order Code | Full Product Name | Light source | Correlated Color | | Luminous Flux |
|--------------|------------------------------------|-------------------|-------------------|--|---------------|
| | | color | Temperature (Nom) | | |
| 911401746523 | BVP353 24LED 40K 220V L24 10 | 840 neutral white | 4000 K | | 4,205 lm |
| 911401746533 | BVP353 24LED 27K 220V L24 10 DMX | 827 warm white | 2700 K | | 3,465 lm |
| 911401746543 | BVP353 24LED 30K 220V L24 10 DMX | 830 warm white | 3000 K | | 3,615 lm |
| 911401746553 | BVP353 24LED 40K 220V L24 10 DMX | 840 neutral white | 4000 K | | 4,035 lm |
| 911401746563 | BVP353 24LED RGB 220V L24 10 DMX | RGB | - | | 2,085 lm |
| 911401746573 | BVP353 24LED RGBWW 220V L24 10 DMX | RGBW | - | | 2,350 lm |
| 911401746583 | BVP353 24LED RGBNW 220V L24 10 DMX | RGBW | - | | 2,450 lm |
| 911401746593 | BVP353 24LED 27K 220V L24 15 | 827 warm white | 2700 K | | 3,795 lm |
| 911401746603 | BVP353 24LED 30K 220V L24 15 | 830 warm white | 3000 K | | 3,955 lm |
| 911401746613 | BVP353 24LED 40K 220V L24 15 | 840 neutral white | 4000 K | | 4,415 lm |
| 911401746623 | BVP353 24LED 27K 220V L24 15 DMX | 827 warm white | 2700 K | | 3,640 lm |
| 911401746633 | BVP353 24LED 30K 220V L24 15 DMX | 830 warm white | 3000 K | | 3,800 lm |
| 911401746643 | BVP353 24LED 40K 220V L24 15 DMX | 840 neutral white | 4000 K | | 4,235 lm |
| 911401746653 | BVP353 24LED RGB 220V L24 15 DMX | RGB | - | | 2,190 lm |
| 911401746663 | BVP353 24LED RGBWW 220V L24 15 DMX | RGBW | - | | 2,465 lm |
| 911401746673 | BVP353 24LED RGBNW 220V L24 15 DMX | RGBW | - | | 2,575 lm |
| 911401746683 | BVP353 24LED 27K 220V L24 30 | 827 warm white | 2700 K | | 3,930 lm |
| 911401746693 | BVP353 24LED 30K 220V L24 30 | 830 warm white | 3000 K | | 4,100 lm |
| 911401746703 | BVP353 24LED 40K 220V L24 30 | 840 neutral white | 4000 K | | 4,575 lm |
| 911401746713 | BVP353 24LED 27K 220V L24 30 DMX | 827 warm white | 2700 K | | 3,770 lm |
| 911401746723 | BVP353 24LED 30K 220V L24 30 DMX | 830 warm white | 3000 K | | 3,935 lm |
| 911401746733 | BVP353 24LED 40K 220V L24 30 DMX | 840 neutral white | 4000 K | | 4,390 lm |
| 911401746743 | BVP353 24LED RGB 220V L24 30 DMX | RGB | - | | 2,270 lm |
| 911401746753 | BVP353 24LED RGBWW 220V L24 30 DMX | RGBW | - | | 2,555 lm |
| 911401746763 | BVP353 24LED RGBNW 220V L24 30 DMX | RGBW | - | | 2,665 lm |
| 911401746773 | BVP353 24LED 27K 220V L24 45 | 827 warm white | 2700 K | | 3,795 lm |
| 911401746783 | BVP353 24LED 30K 220V L24 45 | 830 warm white | 3000 K | | 3,955 lm |
| 911401746793 | BVP353 24LED 40K 220V L24 45 | 840 neutral white | 4000 K | | 4,415 lm |
| 911401746803 | BVP353 24LED 27K 220V L24 45 DMX | 827 warm white | 2700 K | | 3,640 lm |
| 911401746813 | BVP353 24LED 30K 220V L24 45 DMX | 830 warm white | 3000 K | | 3,800 lm |
| 911401746823 | BVP353 24LED 40K 220V L24 45 DMX | 840 neutral white | 4000 K | | 4,235 lm |
| 911401746833 | BVP353 24LED RGB 220V L24 45 DMX | RGB | - | | 2,190 lm |
| 911401746843 | BVP353 24LED RGBWW 220V L24 45 DMX | RGBW | - | | 2,465 lm |
| 911401746853 | BVP353 24LED RGBNW 220V L24 45 DMX | RGBW | - | | 2,575 lm |
| 911401747943 | BVP353 60LED 27K 220V L50 10 | 827 warm white | 2700 K | | 9,150 lm |
| 911401747953 | BVP353 60LED 30K 220V L50 10 | 830 warm white | 3000 K | | 9,540 lm |
| 911401747963 | BVP353 60LED 40K 220V L50 10 | 840 neutral white | 4000 K | | 10,645 lm |
| 911401747973 | BVP353 60LED 27K 220V L50 10 DMX | 827 warm white | 2700 K | | 8,805 lm |
| 911401747983 | BVP353 60LED 30K 220V L50 10 DMX | 830 warm white | 3000 K | | 9,185 lm |
| 911401747993 | BVP353 60LED 40K 220V L50 10 DMX | 840 neutral white | 4000 K | | 10,250 lm |
| 911401748003 | BVP353 60LED RGB 220V L50 10 DMX | RGB | - | | 5,215 lm |

| Order Code | Full Product Name | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|------------------------------------|--------------------|------------------------------------|---------------|
| 911401748013 | BVP353 60LED RGBWW 220V L50 10 DMX | RGBW | - | 5,995 lm |
| 911401748023 | BVP353 60LED RGBNW 220V L50 10 DMX | RGBW | - | 6,260 lm |
| 911401748033 | BVP353 60LED 27K 220V L50 15 | 827 warm white | 2700 K | 9,605 lm |
| 911401748043 | BVP353 60LED 30K 220V L50 15 | 830 warm white | 3000 K | 10,020 lm |
| 911401748053 | BVP353 60LED 40K 220V L50 15 | 840 neutral white | 4000 K | 11,180 lm |
| 911401748063 | BVP353 60LED 27K 220V L50 15 DMX | 827 warm white | 2700 K | 9,245 lm |
| 911401748073 | BVP353 60LED 30K 220V L50 15 DMX | 830 warm white | 3000 K | 9,645 lm |
| 911401748083 | BVP353 60LED 40K 220V L50 15 DMX | 840 neutral white | 4000 K | 10,760 lm |
| 911401748093 | BVP353 60LED RGB 220V L50 15 DMX | RGB | - | 5,480 lm |
| 911401748103 | BVP353 60LED RGBWW 220V L50 15 DMX | RGBW | - | 6,295 lm |
| 911401748113 | BVP353 60LED RGBNW 220V L50 15 DMX | RGBW | - | 6,575 lm |
| 911401748123 | BVP353 60LED 27K 220V L50 30 | 827 warm white | 2700 K | 9,950 lm |
| 911401748133 | BVP353 60LED 30K 220V L50 30 | 830 warm white | 3000 K | 10,380 lm |
| 911401748143 | BVP353 60LED 40K 220V L50 30 | 840 neutral white | 4000 K | 11,580 lm |
| 911401748153 | BVP353 60LED 27K 220V L50 30 DMX | 827 warm white | 2700 K | 9,575 lm |
| 911401748163 | BVP353 60LED 30K 220V L50 30 DMX | 830 warm white | 3000 K | 9,990 lm |
| 911401748173 | BVP353 60LED 40K 220V L50 30 DMX | 840 neutral white | 4000 K | 11,145 lm |
| 911401748183 | BVP353 60LED RGB 220V L50 30 DMX | RGB | - | 5,675 lm |
| 911401748193 | BVP353 60LED RGBWW 220V L50 30 DMX | RGBW | - | 6,520 lm |
| 911401748203 | BVP353 60LED RGBNW 220V L50 30 DMX | RGBW | - | 6,810 lm |
| 911401748213 | BVP353 60LED 27K 220V L50 45 | 827 warm white | 2700 K | 9,605 lm |
| 911401748223 | BVP353 60LED 30K 220V L50 45 | 830 warm white | 3000 K | 10,020 lm |
| 911401748233 | BVP353 60LED 40K 220V L50 45 | 840 neutral white | 4000 K | 11,180 lm |
| 911401748243 | BVP353 60LED 27K 220V L50 45 DMX | 827 warm white | 2700 K | 9,245 lm |
| 911401748253 | BVP353 60LED 30K 220V L50 45 DMX | 830 warm white | 3000 K | 9,645 lm |
| 911401748263 | BVP353 60LED 40K 220V L50 45 DMX | 840 neutral white | 4000 K | 10,760 lm |
| 911401748273 | BVP353 60LED RGB 220V L50 45 DMX | RGB | - | 5,480 lm |
| 911401748283 | BVP353 60LED RGBWW 220V L50 45 DMX | RGBW | - | 6,295 lm |
| 911401748293 | BVP353 60LED RGBNW 220V L50 45 DMX | RGBW | - | 6,575 lm |
| 911401745783 | BVP353 16LED 27K 220V L18 10 | 827 warm white | 2700 K | 2,755 lm |
| 911401745793 | BVP353 16LED 30K 220V L18 10 | 830 warm white | 3000 K | 2,875 lm |
| 911401745803 | BVP353 16LED 40K 220V L18 10 | 840 neutral white | 4000 K | 3,205 lm |
| 911401745813 | BVP353 16LED 27K 220V L18 10 DMX | 827 warm white | 2700 K | 2,060 lm |
| 911401745823 | BVP353 16LED 30K 220V L18 10 DMX | 830 warm white | 3000 K | 2,145 lm |
| 911401745833 | BVP353 16LED 40K 220V L18 10 DMX | 840 neutral white | 4000 K | 2,395 lm |
| 911401745843 | BVP353 15LED RGB 220V L18 10 DMX | RGB | - | 1,200 lm |
| 911401745853 | BVP353 16LED RGBWW 220V L18 10 DMX | RGBW | - | 1,425 lm |

| Order Code | Full Product Name | Light source | Correlated Color | | Luminous Flux |
|--------------|-------------------------------------|-------------------|-------------------|--|---------------|
| | | color | Temperature (Nom) | | |
| 911401745863 | BVP353 16LED RGBNW 220V L18 10 DMX | RGBW | - | | 1,490 lm |
| 911401745873 | BVP353 16LED 27K 220V L18 15 | 827 warm white | 2700 K | | 2,895 lm |
| 911401745883 | BVP353 16LED 30K 220V L18 15 | 830 warm white | 3000 K | | 3,020 lm |
| 911401745893 | BVP353 16LED 40K 220V L18 15 | 840 neutral white | 4000 K | | 3,365 lm |
| 911401745903 | BVP353 16LED 27K 220V L18 15 DMX | 827 warm white | 2700 K | | 2,160 lm |
| 911401745913 | BVP353 16LED 30K 220V L18 15 DMX | 830 warm white | 3000 K | | 2,255 lm |
| 911401745923 | BVP353 16LED 40K 220V L18 15 DMX | 840 neutral white | 4000 K | | 2,515 lm |
| 911401745933 | BVP353 15LED RGB 220V L18 15 DMX | RGB | - | | 1,260 lm |
| 911401745943 | BVP353 16LED RGBWW 220V L18 15 DMX | RGBW | - | | 1,500 lm |
| 911401745953 | BVP353 16LED RGBNW 220V L18 15 DMX | RGBW | - | | 1,565 lm |
| 911401745963 | BVP353 16LED 27K 220V L18 30 | 827 warm white | 2700 K | | 2,995 lm |
| 911401745973 | BVP353 16LED 30K 220V L18 30 | 830 warm white | 3000 K | | 3,125 lm |
| 911401745983 | BVP353 16LED 40K 220V L18 30 | 840 neutral white | 4000 K | | 3,490 lm |
| 911401745993 | BVP353 16LED 27K 220V L18 30 DMX | 827 warm white | 2700 K | | 2,240 lm |
| 911401746003 | BVP353 16LED 30K 220V L18 30 DMX | 830 warm white | 3000 K | | 2,335 lm |
| 911401746013 | BVP353 16LED 40K 220V L18 30 DMX | 840 neutral white | 4000 K | | 2,605 lm |
| 911401746023 | BVP353 15LED RGB 220V L18 30 DMX | RGB | - | | 1,305 lm |
| 911401746033 | BVP353 16LED RGBWW 220V L18 30 DMX | RGBW | - | | 1,550 lm |
| 911401746043 | BVP353 16LED RGBNW 220V L18 30 DMX | RGBW | - | | 1,620 lm |
| 911401746053 | BVP353 16LED 27K 220V L18 45 | 827 warm white | 2700 K | | 2,895 lm |
| 911401746063 | BVP353 16LED 30K 220V L18 45 | 830 warm white | 3000 K | | 3,020 lm |
| 911401746073 | BVP353 16LED 40K 220V L18 45 | 840 neutral white | 4000 K | | 3,365 lm |
| 911401746083 | BVP353 16LED 27K 220V L18 45 DMX | 827 warm white | 2700 K | | 2,160 lm |
| 911401746093 | BVP353 16LED 30K 220V L18 45 DMX | 830 warm white | 3000 K | | 2,255 lm |
| 911401746103 | BVP353 16LED 40K 220V L18 45 DMX | 840 neutral white | 4000 K | | 2,515 lm |
| 911401746113 | BVP353 15LED RGB 220V L18 45 DMX | RGB | - | | 1,260 lm |
| 911401746123 | BVP353 16LED RGBWW 220V L18 45 DMX | RGBW | - | | 1,500 lm |
| 911401746133 | BVP353 16LED RGBNW 220V L18 45 DMX | RGBW | - | | 1,565 lm |
| 911401749743 | BVP355 216LED 27K 220V L57 10 | 827 warm white | 2700 K | | 34,145 lm |
| 911401749753 | BVP355 216LED 30K 220V L57 10 | 830 warm white | 3000 K | | 35,615 lm |
| 911401749763 | BVP355 216LED 40K 220V L57 10 | 840 neutral white | 4000 K | | 39,740 lm |
| 911401749773 | BVP355 216LED 27K 220V L57 10 DMX | 827 warm white | 2700 K | | 32,535 lm |
| 911401749783 | BVP355 216LED 30K 220V L57 10 DMX | 830 warm white | 3000 K | | 33,935 lm |
| 911401749793 | BVP355 216LED 40K 220V L57 10 DMX | 840 neutral white | 4000 K | | 37,860 lm |
| 911401749803 | BVP355 216LED RGB 220V L57 10 DMX | RGB | - | | 20,115 lm |
| 911401749813 | BVP355 216LED RGBWW 220V L57 10 DMX | RGBW | - | | 21,590 lm |
| 911401749823 | BVP355 216LED RGBNW 220V L57 10 DMX | RGBW | - | | 22,550 lm |
| 911401749833 | BVP355 216LED 27K 220V L57 15 | 827 warm white | 2700 K | | 35,850 lm |
| 911401749843 | BVP355 216LED 30K 220V L57 15 | 830 warm white | 3000 K | | 37,400 lm |
| 911401749853 | BVP355 216LED 40K 220V L57 15 | 840 neutral white | 4000 K | | 41,725 lm |
| 911401749863 | BVP355 216LED 27K 220V L57 15 DMX | 827 warm white | 2700 K | | 34,160 lm |

| Order Code | Full Product Name | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|-------------------------------------|--------------------|------------------------------------|---------------|
| 911401749873 | EVP355 216LED 30K 220V L57 15 DMX | 830 warm white | 3000 K | 35,635 lm |
| 911401749883 | EVP355 216LED 40K 220V L57 15 DMX | 840 neutral white | 4000 K | 39,755 lm |
| 911401749893 | EVP355 216LED RGB 220V L57 15 DMX | RGB | - | 21,120 lm |
| 911401749903 | EVP355 216LED RGBWW 220V L57 15 DMX | RGBW | - | 22,670 lm |
| 911401749913 | EVP355 216LED RGBNW 220V L57 15 DMX | RGBW | - | 23,675 lm |
| 911401749923 | EVP355 216LED 27K 220V L57 30 | 827 warm white | 2700 K | 37,135 lm |
| 911401749933 | EVP355 216LED 30K 220V L57 30 | 830 warm white | 3000 K | 38,735 lm |
| 911401749943 | EVP355 216LED 40K 220V L57 30 | 840 neutral white | 4000 K | 43,215 lm |
| 911401749953 | EVP355 216LED 27K 220V L57 30 DMX | 827 warm white | 2700 K | 35,380 lm |
| 911401749963 | EVP355 216LED 30K 220V L57 30 DMX | 830 warm white | 3000 K | 36,905 lm |
| 911401749973 | EVP355 216LED 40K 220V L57 30 DMX | 840 neutral white | 4000 K | 41,175 lm |
| 911401749983 | EVP355 216LED RGB 220V L57 30 DMX | RGB | - | 21,875 lm |
| 911401749993 | EVP355 216LED RGBWW 220V L57 30 DMX | RGBW | - | 23,480 lm |
| 911401750003 | EVP355 216LED RGBNW 220V L57 30 DMX | RGBW | - | 24,520 lm |
| 911401750013 | EVP355 216LED 27K 220V L57 45 | 827 warm white | 2700 K | 35,850 lm |
| 911401750023 | EVP355 216LED 30K 220V L57 45 | 830 warm white | 3000 K | 37,400 lm |
| 911401750033 | EVP355 216LED 40K 220V L57 45 | 840 neutral white | 4000 K | 41,725 lm |
| 911401750043 | EVP355 216LED 27K 220V L57 45 DMX | 827 warm white | 2700 K | 34,160 lm |
| 911401750053 | EVP355 216LED 30K 220V L57 45 DMX | 830 warm white | 3000 K | 35,635 lm |
| 911401750063 | EVP355 216LED 40K 220V L57 45 DMX | 840 neutral white | 4000 K | 39,755 lm |
| 911401750073 | EVP355 216LED RGB 220V L57 45 DMX | RGB | - | 21,120 lm |
| 911401750083 | EVP355 216LED RGBWW 220V L57 45 DMX | RGBW | - | 22,670 lm |
| 911401750093 | EVP355 216LED RGBNW 220V L57 45 DMX | RGBW | - | 23,675 lm |
| 911401750103 | EVP355 180LED 27K 220V L50 10 | 827 warm white | 2700 K | 27,450 lm |
| 911401750113 | EVP355 180LED 30K 220V L50 10 | 830 warm white | 3000 K | 28,630 lm |
| 911401750123 | EVP355 180LED 40K 220V L50 10 | 840 neutral white | 4000 K | 31,945 lm |
| 911401750133 | EVP355 180LED 27K 220V L50 10 DMX | 827 warm white | 2700 K | 26,425 lm |
| 911401750143 | EVP355 180LED 30K 220V L50 10 DMX | 830 warm white | 3000 K | 27,565 lm |
| 911401750153 | EVP355 180LED 40K 220V L50 10 DMX | 840 neutral white | 4000 K | 30,750 lm |
| 911401750163 | EVP355 180LED RGB 220V L50 10 DMX | RGB | - | 15,655 lm |
| 911401750173 | EVP355 180LED RGBWW 220V L50 10 DMX | RGBW | - | 17,990 lm |
| 911401750183 | EVP355 180LED RGBNW 220V L50 10 DMX | RGBW | - | 18,790 lm |

| Order Code | Full Product Name | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|-------------------------------------|--------------------|------------------------------------|---------------|
| 911401750193 | EVP355 180LED 27K 220V L50 15 | 827 warm white | 2700 K | 28,820 lm |
| 911401750203 | EVP355 180LED 30K 220V L50 15 | 830 warm white | 3000 K | 30,065 lm |
| 911401750213 | EVP355 180LED 40K 220V L50 15 | 840 neutral white | 4000 K | 33,540 lm |
| 911401750223 | EVP355 180LED 27K 220V L50 15 DMX | 827 warm white | 2700 K | 27,745 lm |
| 911401750233 | EVP355 180LED 30K 220V L50 15 DMX | 830 warm white | 3000 K | 28,940 lm |
| 911401750243 | EVP355 180LED 40K 220V L50 15 DMX | 840 neutral white | 4000 K | 32,290 lm |
| 911401750253 | EVP355 180LED RGB 220V L50 15 DMX | RGB | - | 16,440 lm |
| 911401750263 | EVP355 180LED RGBWW 220V L50 15 DMX | RGBW | - | 18,890 lm |
| 911401750273 | EVP355 180LED RGBNW 220V L50 15 DMX | RGBW | - | 19,730 lm |
| 911401750283 | EVP355 180LED 27K 220V L50 30 | 827 warm white | 2700 K | 29,850 lm |
| 911401750293 | EVP355 180LED 30K 220V L50 30 | 830 warm white | 3000 K | 31,140 lm |
| 911401750303 | EVP355 180LED 40K 220V L50 30 | 840 neutral white | 4000 K | 34,740 lm |
| 911401750313 | EVP355 180LED 27K 220V L50 30 DMX | 827 warm white | 2700 K | 28,735 lm |
| 911401750323 | EVP355 180LED 30K 220V L50 30 DMX | 830 warm white | 3000 K | 29,975 lm |
| 911401750333 | EVP355 180LED 40K 220V L50 30 DMX | 840 neutral white | 4000 K | 33,445 lm |
| 911401750343 | EVP355 180LED RGB 220V L50 30 DMX | RGB | - | 17,025 lm |
| 911401750353 | EVP355 180LED RGBWW 220V L50 30 DMX | RGBW | - | 19,565 lm |
| 911401750363 | EVP355 180LED RGBNW 220V L50 30 DMX | RGBW | - | 20,435 lm |
| 911401750373 | EVP355 180LED 27K 220V L50 45 | 827 warm white | 2700 K | 28,820 lm |
| 911401750383 | EVP355 180LED 30K 220V L50 45 | 830 warm white | 3000 K | 30,065 lm |
| 911401750393 | EVP355 180LED 40K 220V L50 45 | 840 neutral white | 4000 K | 33,540 lm |
| 911401750403 | EVP355 180LED 27K 220V L50 45 DMX | 827 warm white | 2700 K | 27,745 lm |
| 911401750413 | EVP355 180LED 30K 220V L50 45 DMX | 830 warm white | 3000 K | 28,940 lm |
| 911401750423 | EVP355 180LED 40K 220V L50 45 DMX | 840 neutral white | 4000 K | 32,290 lm |
| 911401750433 | EVP355 180LED RGB 220V L50 45 DMX | RGB | - | 16,440 lm |
| 911401750443 | EVP355 180LED RGBWW 220V L50 45 DMX | RGBW | - | 18,890 lm |
| 911401750453 | EVP355 180LED RGBNW 220V L50 45 DMX | RGBW | - | 19,730 lm |
| 911401747583 | EVP353 48LED 27K 220V L40 10 | 827 warm white | 2700 K | 7,440 lm |
| 911401747593 | EVP353 48LED 30K 220V L40 10 | 830 warm white | 3000 K | 7,760 lm |
| 911401747603 | EVP353 48LED 40K 220V L40 10 | 840 neutral white | 4000 K | 8,655 lm |
| 911401747613 | EVP353 48LED 27K 220V L40 10 DMX | 827 warm white | 2700 K | 6,860 lm |
| 911401747623 | EVP353 48LED 30K 220V L40 10 DMX | 830 warm white | 3000 K | 7,155 lm |
| 911401747633 | EVP353 48LED 40K 220V L40 10 DMX | 840 neutral white | 4000 K | 7,985 lm |
| 911401747643 | EVP353 48LED RGB 220V L40 10 DMX | RGB | - | 3,830 lm |

| Order Code | Full Product Name | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|------------------------------------|--------------------|------------------------------------|---------------|
| 911401747653 | BVP353 48LED RGBWW 220V L40 10 DMX | RGBW | - | 5,250 lm |
| 911401747663 | BVP353 48LED RGBNW 220V L40 10 DMX | RGBW | - | 5,485 lm |
| 911401747673 | BVP353 48LED 27K 220V L40 15 | 827 warm white | 2700 K | 7,810 lm |
| 911401747683 | BVP353 48LED 30K 220V L40 15 | 830 warm white | 3000 K | 8,145 lm |
| 911401747693 | BVP353 48LED 40K 220V L40 15 | 840 neutral white | 4000 K | 9,090 lm |
| 911401747703 | BVP353 48LED 27K 220V L40 15 DMX | 827 warm white | 2700 K | 7,205 lm |
| 911401747713 | BVP353 48LED 30K 220V L40 15 DMX | 830 warm white | 3000 K | 7,515 lm |
| 911401747723 | BVP353 48LED 40K 220V L40 15 DMX | 840 neutral white | 4000 K | 8,385 lm |
| 911401747733 | BVP353 48LED RGB 220V L40 15 DMX | RGB | - | 4,020 lm |
| 911401747743 | BVP353 48LED RGBWW 220V L40 15 DMX | RGBW | - | 5,515 lm |
| 911401747753 | BVP353 48LED RGBNW 220V L40 15 DMX | RGBW | - | 5,760 lm |
| 911401747763 | BVP353 48LED 27K 220V L40 30 | 827 warm white | 2700 K | 8,090 lm |
| 911401747773 | BVP353 48LED 30K 220V L40 30 | 830 warm white | 3000 K | 8,440 lm |
| 911401747783 | BVP353 48LED 40K 220V L40 30 | 840 neutral white | 4000 K | 9,415 lm |
| 911401747793 | BVP353 48LED 27K 220V L40 30 DMX | 827 warm white | 2700 K | 7,460 lm |
| 911401747803 | BVP353 48LED 30K 220V L40 30 DMX | 830 warm white | 3000 K | 7,785 lm |
| 911401747813 | BVP353 48LED 40K 220V L40 30 DMX | 840 neutral white | 4000 K | 8,685 lm |
| 911401747823 | BVP353 48LED RGB 220V L40 30 DMX | RGB | - | 4,165 lm |
| 911401747833 | BVP353 48LED RGBWW 220V L40 30 DMX | RGBW | - | 5,710 lm |
| 911401747843 | BVP353 48LED RGBNW 220V L40 30 DMX | RGBW | - | 5,965 lm |
| 911401747853 | BVP353 48LED 27K 220V L40 45 | 827 warm white | 2700 K | 7,810 lm |
| 911401747863 | BVP353 48LED 30K 220V L40 45 | 830 warm white | 3000 K | 8,145 lm |
| 911401747873 | BVP353 48LED 40K 220V L40 45 | 840 neutral white | 4000 K | 9,090 lm |
| 911401747883 | BVP353 48LED 27K 220V L40 45 DMX | 827 warm white | 2700 K | 7,205 lm |
| 911401747893 | BVP353 48LED 30K 220V L40 45 DMX | 830 warm white | 3000 K | 7,515 lm |
| 911401747903 | BVP353 48LED 40K 220V L40 45 DMX | 840 neutral white | 4000 K | 8,385 lm |
| 911401747913 | BVP353 48LED RGB 220V L40 45 DMX | RGB | - | 4,020 lm |
| 911401747923 | BVP353 48LED RGBWW 220V L40 45 DMX | RGBW | - | 5,515 lm |
| 911401747933 | BVP353 48LED RGBNW 220V L40 45 DMX | RGBW | - | 5,760 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption | Order Code | Full Product Name | Power Consumption |
|--------------|----------------------------------|-------------------|--------------|------------------------------------|-------------------|
| 911401746863 | BVP353 30LED 27K 220V L30 10 | 60 W | 911401746933 | BVP353 32LED RGBWW 220V L30 10 DMX | 60 W |
| 911401746873 | BVP353 30LED 30K 220V L30 10 | 60 W | 911401746943 | BVP353 32LED RGBNW 220V L30 10 DMX | 60 W |
| 911401746883 | BVP353 30LED 40K 220V L30 10 | 60 W | 911401746953 | BVP353 30LED 27K 220V L30 15 | 60 W |
| 911401746893 | BVP353 30LED 27K 220V L30 10 DMX | 60 W | 911401746963 | BVP353 30LED 30K 220V L30 15 | 60 W |
| 911401746903 | BVP353 30LED 30K 220V L30 10 DMX | 60 W | 911401746973 | BVP353 30LED 40K 220V L30 15 | 60 W |
| 911401746913 | BVP353 30LED 40K 220V L30 10 DMX | 60 W | 911401746983 | BVP353 30LED 27K 220V L30 15 DMX | 60 W |
| 911401746923 | BVP353 30LED RGB 220V L30 10 DMX | 60 W | 911401746993 | BVP353 30LED 30K 220V L30 15 DMX | 60 W |

UniFlood M G2

| Order Code | Full Product Name | Power Consumption |
|--------------|------------------------------------|-------------------|
| 911401747003 | BVP353 30LED 40K 220V L30 15 DMX | 60 W |
| 911401747013 | BVP353 30LED RGB 220V L30 15 DMX | 60 W |
| 911401747023 | BVP353 32LED RGBWW 220V L30 15 DMX | 60 W |
| 911401747033 | BVP353 32LED RGBNW 220V L30 15 DMX | 60 W |
| 911401747043 | BVP353 30LED 27K 220V L30 30 | 60 W |
| 911401747053 | BVP353 30LED 30K 220V L30 30 | 60 W |
| 911401747063 | BVP353 30LED 40K 220V L30 30 | 60 W |
| 911401747073 | BVP353 30LED 27K 220V L30 30 DMX | 60 W |
| 911401747083 | BVP353 30LED 30K 220V L30 30 DMX | 60 W |
| 911401747093 | BVP353 30LED 40K 220V L30 30 DMX | 60 W |
| 911401747103 | BVP353 30LED RGB 220V L30 30 DMX | 60 W |
| 911401747113 | BVP353 32LED RGBWW 220V L30 30 DMX | 60 W |
| 911401747123 | BVP353 32LED RGBNW 220V L30 30 DMX | 60 W |
| 911401747133 | BVP353 30LED 27K 220V L30 45 | 60 W |
| 911401747143 | BVP353 30LED 30K 220V L30 45 | 60 W |
| 911401747153 | BVP353 30LED 40K 220V L30 45 | 60 W |
| 911401747163 | BVP353 30LED 27K 220V L30 45 DMX | 60 W |
| 911401747173 | BVP353 30LED 30K 220V L30 45 DMX | 60 W |
| 911401747183 | BVP353 30LED 40K 220V L30 45 DMX | 60 W |
| 911401747193 | BVP353 30LED RGB 220V L30 45 DMX | 60 W |
| 911401747203 | BVP353 32LED RGBWW 220V L30 45 DMX | 60 W |
| 911401747213 | BVP353 32LED RGBNW 220V L30 45 DMX | 60 W |
| 911401748663 | BVP354 96LED 27K 220V L40 10 | 200 W |
| 911401748673 | BVP354 96LED 30K 220V L40 10 | 200 W |
| 911401748683 | BVP354 96LED 40K 220V L40 10 | 200 W |
| 911401748693 | BVP354 96LED 27K 220V L40 10 DMX | 200 W |
| 911401748703 | BVP354 96LED 30K 220V L40 10 DMX | 200 W |
| 911401748713 | BVP354 96LED 40K 220V L40 10 DMX | 200 W |
| 911401748723 | BVP354 96LED RGB 220V L40 10 DMX | 200 W |
| 911401748733 | BVP354 96LED RGBWW 220V L40 10 DMX | 200 W |
| 911401748743 | BVP354 96LED RGBNW 220V L40 10 DMX | 200 W |
| 911401748753 | BVP354 96LED 27K 220V L40 15 | 200 W |
| 911401748763 | BVP354 96LED 30K 220V L40 15 | 200 W |
| 911401748773 | BVP354 96LED 40K 220V L40 15 | 200 W |
| 911401748783 | BVP354 96LED 27K 220V L40 15 DMX | 200 W |
| 911401748793 | BVP354 96LED 30K 220V L40 15 DMX | 200 W |
| 911401748803 | BVP354 96LED 40K 220V L40 15 DMX | 200 W |
| 911401748813 | BVP354 96LED RGB 220V L40 15 DMX | 200 W |
| 911401748823 | BVP354 96LED RGBWW 220V L40 15 DMX | 200 W |
| 911401748833 | BVP354 96LED RGBNW 220V L40 15 DMX | 200 W |
| 911401748843 | BVP354 96LED 27K 220V L40 30 | 200 W |
| 911401748853 | BVP354 96LED 30K 220V L40 30 | 200 W |
| 911401748863 | BVP354 96LED 40K 220V L40 30 | 200 W |
| 911401748873 | BVP354 96LED 27K 220V L40 30 DMX | 200 W |
| 911401748883 | BVP354 96LED 30K 220V L40 30 DMX | 200 W |
| 911401748893 | BVP354 96LED 40K 220V L40 30 DMX | 200 W |
| 911401748903 | BVP354 96LED RGB 220V L40 30 DMX | 200 W |
| 911401748913 | BVP354 96LED RGBWW 220V L40 30 DMX | 200 W |
| 911401748923 | BVP354 96LED RGBNW 220V L40 30 DMX | 200 W |
| 911401748933 | BVP354 96LED 27K 220V L40 45 | 200 W |
| 911401748943 | BVP354 96LED 30K 220V L40 45 | 200 W |
| 911401748953 | BVP354 96LED 40K 220V L40 45 | 200 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|-------------------------------------|-------------------|
| 911401748963 | BVP354 96LED 27K 220V L40 45 DMX | 200 W |
| 911401748973 | BVP354 96LED 30K 220V L40 45 DMX | 200 W |
| 911401748983 | BVP354 96LED 40K 220V L40 45 DMX | 200 W |
| 911401748993 | BVP354 96LED RGB 220V L40 45 DMX | 200 W |
| 911401749003 | BVP354 96LED RGBWW 220V L40 45 DMX | 200 W |
| 911401749013 | BVP354 96LED RGBNW 220V L40 45 DMX | 200 W |
| 911401749023 | BVP354 120LED 27K 220V L50 10 | 240 W |
| 911401749033 | BVP354 120LED 30K 220V L50 10 | 240 W |
| 911401749043 | BVP354 120LED 40K 220V L50 10 | 240 W |
| 911401749053 | BVP354 120LED 27K 220V L50 10 DMX | 240 W |
| 911401749063 | BVP354 120LED 30K 220V L50 10 DMX | 240 W |
| 911401749073 | BVP354 120LED 40K 220V L50 10 DMX | 240 W |
| 911401749083 | BVP354 120LED RGB 220V L50 10 DMX | 240 W |
| 911401749093 | BVP354 120LED RGBWW 220V L50 10 DMX | 240 W |
| 911401749103 | BVP354 120LED RGBNW 220V L50 10 DMX | 240 W |
| 911401749113 | BVP354 120LED 27K 220V L50 15 | 240 W |
| 911401749123 | BVP354 120LED 30K 220V L50 15 | 240 W |
| 911401749133 | BVP354 120LED 40K 220V L50 15 | 240 W |
| 911401749143 | BVP354 120LED 27K 220V L50 15 DMX | 240 W |
| 911401749153 | BVP354 120LED 30K 220V L50 15 DMX | 240 W |
| 911401749163 | BVP354 120LED 40K 220V L50 15 DMX | 240 W |
| 911401749173 | BVP354 120LED RGB 220V L50 15 DMX | 240 W |
| 911401749183 | BVP354 120LED RGBWW 220V L50 15 DMX | 240 W |
| 911401749193 | BVP354 120LED RGBNW 220V L50 15 DMX | 240 W |
| 911401749203 | BVP354 120LED 27K 220V L50 30 | 240 W |
| 911401749213 | BVP354 120LED 30K 220V L50 30 | 240 W |
| 911401749223 | BVP354 120LED 40K 220V L50 30 | 240 W |
| 911401749233 | BVP354 120LED 27K 220V L50 30 DMX | 240 W |
| 911401749243 | BVP354 120LED 30K 220V L50 30 DMX | 240 W |
| 911401749253 | BVP354 120LED 40K 220V L50 30 DMX | 240 W |
| 911401749263 | BVP354 120LED RGB 220V L50 30 DMX | 240 W |
| 911401749273 | BVP354 120LED RGBWW 220V L50 30 DMX | 240 W |
| 911401749283 | BVP354 120LED RGBNW 220V L50 30 DMX | 240 W |
| 911401749293 | BVP354 120LED 27K 220V L50 45 | 240 W |
| 911401749303 | BVP354 120LED 30K 220V L50 45 | 240 W |
| 911401749313 | BVP354 120LED 40K 220V L50 45 | 240 W |
| 911401749323 | BVP354 120LED 27K 220V L50 45 DMX | 240 W |
| 911401749333 | BVP354 120LED 30K 220V L50 45 DMX | 240 W |
| 911401749343 | BVP354 120LED 40K 220V L50 45 DMX | 240 W |
| 911401749353 | BVP354 120LED RGB 220V L50 45 DMX | 240 W |
| 911401749363 | BVP354 120LED RGBWW 220V L50 45 DMX | 240 W |
| 911401749373 | BVP354 120LED RGBNW 220V L50 45 DMX | 240 W |
| 911401749383 | BVP354 144LED 27K 220V L57 10 | 300 W |
| 911401749393 | BVP354 144LED 30K 220V L57 10 | 300 W |
| 911401749403 | BVP354 144LED 40K 220V L57 10 | 300 W |
| 911401749413 | BVP354 144LED 27K 220V L57 10 DMX | 300 W |
| 911401749423 | BVP354 144LED 30K 220V L57 10 DMX | 300 W |
| 911401749433 | BVP354 144LED 40K 220V L57 10 DMX | 300 W |
| 911401749443 | BVP354 144LED RGB 220V L57 10 DMX | 300 W |
| 911401749453 | BVP354 144LED RGBWW 220V L57 10 DMX | 300 W |
| 911401749463 | BVP354 144LED RGBNW 220V L57 10 DMX | 300 W |
| 911401749473 | BVP354 144LED 27K 220V L57 15 | 300 W |

UniFlood M G2

| Order Code | Full Product Name | Power Consumption |
|--------------|-------------------------------------|-------------------|
| 911401749483 | BVP354 144LED 30K 220V L57 15 | 300 W |
| 911401749493 | BVP354 144LED 40K 220V L57 15 | 300 W |
| 911401749503 | BVP354 144LED 27K 220V L57 15 DMX | 300 W |
| 911401749513 | BVP354 144LED 30K 220V L57 15 DMX | 300 W |
| 911401749523 | BVP354 144LED 40K 220V L57 15 DMX | 300 W |
| 911401749533 | BVP354 144LED RGB 220V L57 15 DMX | 300 W |
| 911401749543 | BVP354 144LED RGBWW 220V L57 15 DMX | 300 W |
| 911401749553 | BVP354 144LED RGBNW 220V L57 15 DMX | 300 W |
| 911401749563 | BVP354 144LED 27K 220V L57 30 | 300 W |
| 911401749573 | BVP354 144LED 30K 220V L57 30 | 300 W |
| 911401749583 | BVP354 144LED 40K 220V L57 30 | 300 W |
| 911401749593 | BVP354 144LED 27K 220V L57 30 DMX | 300 W |
| 911401749603 | BVP354 144LED 30K 220V L57 30 DMX | 300 W |
| 911401749613 | BVP354 144LED 40K 220V L57 30 DMX | 300 W |
| 911401749623 | BVP354 144LED RGB 220V L57 30 DMX | 300 W |
| 911401749633 | BVP354 144LED RGBWW 220V L57 30 DMX | 300 W |
| 911401749643 | BVP354 144LED RGBNW 220V L57 30 DMX | 300 W |
| 911401749653 | BVP354 144LED 27K 220V L57 45 | 300 W |
| 911401749663 | BVP354 144LED 30K 220V L57 45 | 300 W |
| 911401749673 | BVP354 144LED 40K 220V L57 45 | 300 W |
| 911401749683 | BVP354 144LED 27K 220V L57 45 DMX | 300 W |
| 911401749693 | BVP354 144LED 30K 220V L57 45 DMX | 300 W |
| 911401749703 | BVP354 144LED 40K 220V L57 45 DMX | 300 W |
| 911401749713 | BVP354 144LED RGB 220V L57 45 DMX | 300 W |
| 911401749723 | BVP354 144LED RGBWW 220V L57 45 DMX | 300 W |
| 911401749733 | BVP354 144LED RGBNW 220V L57 45 DMX | 300 W |
| 911401748303 | BVP353 72LED 27K 220V L57 10 | 150 W |
| 911401748313 | BVP353 72LED 30K 220V L57 10 | 150 W |
| 911401748323 | BVP353 72LED 40K 220V L57 10 | 150 W |
| 911401748333 | BVP353 72LED 27K 220V L57 10 DMX | 150 W |
| 911401748343 | BVP353 72LED 30K 220V L57 10 DMX | 150 W |
| 911401748353 | BVP353 72LED 40K 220V L57 10 DMX | 150 W |
| 911401748363 | BVP353 72LED RGB 220V L57 10 DMX | 150 W |
| 911401748373 | BVP353 72LED RGBWW 220V L57 10 DMX | 150 W |
| 911401748383 | BVP353 72LED RGBNW 220V L57 10 DMX | 150 W |
| 911401748393 | BVP353 72LED 27K 220V L57 15 | 150 W |
| 911401748403 | BVP353 72LED 30K 220V L57 15 | 150 W |
| 911401748413 | BVP353 72LED 40K 220V L57 15 | 150 W |
| 911401748423 | BVP353 72LED 27K 220V L57 15 DMX | 150 W |
| 911401748433 | BVP353 72LED 30K 220V L57 15 DMX | 150 W |
| 911401748443 | BVP353 72LED 40K 220V L57 15 DMX | 150 W |
| 911401748453 | BVP353 72LED RGB 220V L57 15 DMX | 150 W |
| 911401748463 | BVP353 72LED RGBWW 220V L57 15 DMX | 150 W |
| 911401748473 | BVP353 72LED RGBNW 220V L57 15 DMX | 150 W |
| 911401748483 | BVP353 72LED 27K 220V L57 30 | 150 W |
| 911401748493 | BVP353 72LED 30K 220V L57 30 | 150 W |
| 911401748503 | BVP353 72LED 40K 220V L57 30 | 150 W |
| 911401748513 | BVP353 72LED 27K 220V L57 30 DMX | 150 W |
| 911401748523 | BVP353 72LED 30K 220V L57 30 DMX | 150 W |
| 911401748533 | BVP353 72LED 40K 220V L57 30 DMX | 150 W |
| 911401748543 | BVP353 72LED RGB 220V L57 30 DMX | 150 W |
| 911401748553 | BVP353 72LED RGBWW 220V L57 30 DMX | 150 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|------------------------------------|-------------------|
| 911401748563 | BVP353 72LED RGBNW 220V L57 30 DMX | 150 W |
| 911401748573 | BVP353 72LED 27K 220V L57 45 | 150 W |
| 911401748583 | BVP353 72LED 30K 220V L57 45 | 150 W |
| 911401748593 | BVP353 72LED 40K 220V L57 45 | 150 W |
| 911401748603 | BVP353 72LED 27K 220V L57 45 DMX | 150 W |
| 911401748613 | BVP353 72LED 30K 220V L57 45 DMX | 150 W |
| 911401748623 | BVP353 72LED 40K 220V L57 45 DMX | 150 W |
| 911401748633 | BVP353 72LED RGB 220V L57 45 DMX | 150 W |
| 911401748643 | BVP353 72LED RGBWW 220V L57 45 DMX | 150 W |
| 911401748653 | BVP353 72LED RGBNW 220V L57 45 DMX | 150 W |
| 911401746143 | BVP353 18LED 27K 220V L21 10 | 40 W |
| 911401746153 | BVP353 18LED 30K 220V L21 10 | 40 W |
| 911401746163 | BVP353 18LED 40K 220V L21 10 | 40 W |
| 911401746173 | BVP353 18LED 27K 220V L21 10 DMX | 40 W |
| 911401746183 | BVP353 18LED 30K 220V L21 10 DMX | 40 W |
| 911401746193 | BVP353 18LED 40K 220V L21 10 DMX | 40 W |
| 911401746203 | BVP353 18LED RGB 220V L21 10 DMX | 40 W |
| 911401746213 | BVP353 20LED RGBWW 220V L21 10 DMX | 40 W |
| 911401746223 | BVP353 20LED RGBNW 220V L21 10 DMX | 40 W |
| 911401746233 | BVP353 18LED 27K 220V L21 15 | 40 W |
| 911401746243 | BVP353 18LED 30K 220V L21 15 | 40 W |
| 911401746253 | BVP353 18LED 40K 220V L21 15 | 40 W |
| 911401746263 | BVP353 18LED 27K 220V L21 15 DMX | 40 W |
| 911401746273 | BVP353 18LED 30K 220V L21 15 DMX | 40 W |
| 911401746283 | BVP353 18LED 40K 220V L21 15 DMX | 40 W |
| 911401746293 | BVP353 18LED RGB 220V L21 15 DMX | 40 W |
| 911401746303 | BVP353 20LED RGBWW 220V L21 15 DMX | 40 W |
| 911401746313 | BVP353 20LED RGBNW 220V L21 15 DMX | 40 W |
| 911401746323 | BVP353 18LED 27K 220V L21 30 | 40 W |
| 911401746333 | BVP353 18LED 30K 220V L21 30 | 40 W |
| 911401746343 | BVP353 18LED 40K 220V L21 30 | 40 W |
| 911401746353 | BVP353 18LED 27K 220V L21 30 DMX | 40 W |
| 911401746363 | BVP353 18LED 30K 220V L21 30 DMX | 40 W |
| 911401746373 | BVP353 18LED 40K 220V L21 30 DMX | 40 W |
| 911401746383 | BVP353 18LED RGB 220V L21 30 DMX | 40 W |
| 911401746393 | BVP353 20LED RGBWW 220V L21 30 DMX | 40 W |
| 911401746403 | BVP353 20LED RGBNW 220V L21 30 DMX | 40 W |
| 911401746413 | BVP353 18LED 27K 220V L21 45 | 40 W |
| 911401746423 | BVP353 18LED 30K 220V L21 45 | 40 W |
| 911401746433 | BVP353 18LED 40K 220V L21 45 | 40 W |
| 911401746443 | BVP353 18LED 27K 220V L21 45 DMX | 40 W |
| 911401746453 | BVP353 18LED 30K 220V L21 45 DMX | 40 W |
| 911401746463 | BVP353 18LED 40K 220V L21 45 DMX | 40 W |
| 911401746473 | BVP353 18LED RGB 220V L21 45 DMX | 40 W |
| 911401746483 | BVP353 20LED RGBWW 220V L21 45 DMX | 40 W |
| 911401746493 | BVP353 20LED RGBNW 220V L21 45 DMX | 40 W |
| 911401745423 | BVP353 12LED 27K 220V L15 10 | 24 W |
| 911401745433 | BVP353 12LED 30K 220V L15 10 | 24 W |
| 911401745443 | BVP353 12LED 40K 220V L15 10 | 24 W |
| 911401745453 | BVP353 12LED 27K 220V L15 10 DMX | 24 W |
| 911401745463 | BVP353 12LED 30K 220V L15 10 DMX | 24 W |
| 911401745473 | BVP353 12LED 40K 220V L15 10 DMX | 24 W |

UniFlood M G2

| Order Code | Full Product Name | Power Consumption |
|--------------|------------------------------------|-------------------|
| 911401745483 | BVP353 12LED RGB 220V L15 10 DMX | 24 W |
| 911401745493 | BVP353 12LED RGBWW 220V L15 10 DMX | 24 W |
| 911401745503 | BVP353 12LED RGBNW 220V L15 10 DMX | 24 W |
| 911401745513 | BVP353 12LED 27K 220V L15 15 | 24 W |
| 911401745523 | BVP353 12LED 30K 220V L15 15 | 24 W |
| 911401745533 | BVP353 12LED 40K 220V L15 15 | 24 W |
| 911401745543 | BVP353 12LED 27K 220V L15 15 DMX | 24 W |
| 911401745553 | BVP353 12LED 30K 220V L15 15 DMX | 24 W |
| 911401745563 | BVP353 12LED 40K 220V L15 15 DMX | 24 W |
| 911401745573 | BVP353 12LED RGB 220V L15 15 DMX | 24 W |
| 911401745583 | BVP353 12LED RGBWW 220V L15 15 DMX | 24 W |
| 911401745593 | BVP353 12LED RGBNW 220V L15 15 DMX | 24 W |
| 911401745603 | BVP353 12LED 27K 220V L15 30 | 24 W |
| 911401745613 | BVP353 12LED 30K 220V L15 30 | 24 W |
| 911401745623 | BVP353 12LED 40K 220V L15 30 | 24 W |
| 911401745633 | BVP353 12LED 27K 220V L15 30 DMX | 24 W |
| 911401745643 | BVP353 12LED 30K 220V L15 30 DMX | 24 W |
| 911401745653 | BVP353 12LED 40K 220V L15 30 DMX | 24 W |
| 911401745663 | BVP353 12LED RGB 220V L15 30 DMX | 24 W |
| 911401745673 | BVP353 12LED RGBWW 220V L15 30 DMX | 24 W |
| 911401745683 | BVP353 12LED RGBNW 220V L15 30 DMX | 24 W |
| 911401745693 | BVP353 12LED 27K 220V L15 45 | 24 W |
| 911401745703 | BVP353 12LED 30K 220V L15 45 | 24 W |
| 911401745713 | BVP353 12LED 40K 220V L15 45 | 24 W |
| 911401745723 | BVP353 12LED 27K 220V L15 45 DMX | 24 W |
| 911401745733 | BVP353 12LED 30K 220V L15 45 DMX | 24 W |
| 911401745743 | BVP353 12LED 40K 220V L15 45 DMX | 24 W |
| 911401745753 | BVP353 12LED RGB 220V L15 45 DMX | 24 W |
| 911401745763 | BVP353 12LED RGBWW 220V L15 45 DMX | 24 W |
| 911401745773 | BVP353 12LED RGBNW 220V L15 45 DMX | 24 W |
| 911401747223 | BVP353 36LED 27K 220V L35 10 | 80 W |
| 911401747233 | BVP353 36LED 30K 220V L35 10 | 80 W |
| 911401747243 | BVP353 36LED 40K 220V L35 10 | 80 W |
| 911401747253 | BVP353 36LED 27K 220V L35 10 DMX | 80 W |
| 911401747263 | BVP353 36LED 30K 220V L35 10 DMX | 80 W |
| 911401747273 | BVP353 36LED 40K 220V L35 10 DMX | 80 W |
| 911401747283 | BVP353 36LED RGB 220V L35 10 DMX | 80 W |
| 911401747293 | BVP353 36LED RGBWW 220V L35 10 DMX | 80 W |
| 911401747303 | BVP353 36LED RGBNW 220V L35 10 DMX | 80 W |
| 911401747313 | BVP353 36LED 27K 220V L35 15 | 80 W |
| 911401747323 | BVP353 36LED 30K 220V L35 15 | 80 W |
| 911401747333 | BVP353 36LED 40K 220V L35 15 | 80 W |
| 911401747343 | BVP353 36LED 27K 220V L35 15 DMX | 80 W |
| 911401747353 | BVP353 36LED 30K 220V L35 15 DMX | 80 W |
| 911401747363 | BVP353 36LED 40K 220V L35 15 DMX | 80 W |
| 911401747373 | BVP353 36LED RGB 220V L35 15 DMX | 80 W |
| 911401747383 | BVP353 36LED RGBWW 220V L35 15 DMX | 80 W |
| 911401747393 | BVP353 36LED RGBNW 220V L35 15 DMX | 80 W |
| 911401747403 | BVP353 36LED 27K 220V L35 30 | 80 W |
| 911401747413 | BVP353 36LED 30K 220V L35 30 | 80 W |
| 911401747423 | BVP353 36LED 40K 220V L35 30 | 80 W |
| 911401747433 | BVP353 36LED 27K 220V L35 30 DMX | 80 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|------------------------------------|-------------------|
| 911401747443 | BVP353 36LED 30K 220V L35 30 DMX | 80 W |
| 911401747453 | BVP353 36LED 40K 220V L35 30 DMX | 80 W |
| 911401747463 | BVP353 36LED RGB 220V L35 30 DMX | 80 W |
| 911401747473 | BVP353 36LED RGBWW 220V L35 30 DMX | 80 W |
| 911401747483 | BVP353 36LED RGBNW 220V L35 30 DMX | 80 W |
| 911401747493 | BVP353 36LED 27K 220V L35 45 | 80 W |
| 911401747503 | BVP353 36LED 30K 220V L35 45 | 80 W |
| 911401747513 | BVP353 36LED 40K 220V L35 45 | 80 W |
| 911401747523 | BVP353 36LED 27K 220V L35 45 DMX | 80 W |
| 911401747533 | BVP353 36LED 30K 220V L35 45 DMX | 80 W |
| 911401747543 | BVP353 36LED 40K 220V L35 45 DMX | 80 W |
| 911401747553 | BVP353 36LED RGB 220V L35 45 DMX | 80 W |
| 911401747563 | BVP353 36LED RGBWW 220V L35 45 DMX | 80 W |
| 911401747573 | BVP353 36LED RGBNW 220V L35 45 DMX | 80 W |
| 911401746503 | BVP353 24LED 27K 220V L24 10 | 50 W |
| 911401746513 | BVP353 24LED 30K 220V L24 10 | 50 W |
| 911401746523 | BVP353 24LED 40K 220V L24 10 | 50 W |
| 911401746533 | BVP353 24LED 27K 220V L24 10 DMX | 50 W |
| 911401746543 | BVP353 24LED 30K 220V L24 10 DMX | 50 W |
| 911401746553 | BVP353 24LED 40K 220V L24 10 DMX | 50 W |
| 911401746563 | BVP353 24LED RGB 220V L24 10 DMX | 50 W |
| 911401746573 | BVP353 24LED RGBWW 220V L24 10 DMX | 50 W |
| 911401746583 | BVP353 24LED RGBNW 220V L24 10 DMX | 50 W |
| 911401746593 | BVP353 24LED 27K 220V L24 15 | 50 W |
| 911401746603 | BVP353 24LED 30K 220V L24 15 | 50 W |
| 911401746613 | BVP353 24LED 40K 220V L24 15 | 50 W |
| 911401746623 | BVP353 24LED 27K 220V L24 15 DMX | 50 W |
| 911401746633 | BVP353 24LED 30K 220V L24 15 DMX | 50 W |
| 911401746643 | BVP353 24LED 40K 220V L24 15 DMX | 50 W |
| 911401746653 | BVP353 24LED RGB 220V L24 15 DMX | 50 W |
| 911401746663 | BVP353 24LED RGBWW 220V L24 15 DMX | 50 W |
| 911401746673 | BVP353 24LED RGBNW 220V L24 15 DMX | 50 W |
| 911401746683 | BVP353 24LED 27K 220V L24 30 | 50 W |
| 911401746693 | BVP353 24LED 30K 220V L24 30 | 50 W |
| 911401746703 | BVP353 24LED 40K 220V L24 30 | 50 W |
| 911401746713 | BVP353 24LED 27K 220V L24 30 DMX | 50 W |
| 911401746723 | BVP353 24LED 30K 220V L24 30 DMX | 50 W |
| 911401746733 | BVP353 24LED 40K 220V L24 30 DMX | 50 W |
| 911401746743 | BVP353 24LED RGB 220V L24 30 DMX | 50 W |
| 911401746753 | BVP353 24LED RGBWW 220V L24 30 DMX | 50 W |
| 911401746763 | BVP353 24LED RGBNW 220V L24 30 DMX | 50 W |
| 911401746773 | BVP353 24LED 27K 220V L24 45 | 50 W |
| 911401746783 | BVP353 24LED 30K 220V L24 45 | 50 W |
| 911401746793 | BVP353 24LED 40K 220V L24 45 | 50 W |
| 911401746803 | BVP353 24LED 27K 220V L24 45 DMX | 50 W |
| 911401746813 | BVP353 24LED 30K 220V L24 45 DMX | 50 W |
| 911401746823 | BVP353 24LED 40K 220V L24 45 DMX | 50 W |
| 911401746833 | BVP353 24LED RGB 220V L24 45 DMX | 50 W |
| 911401746843 | BVP353 24LED RGBWW 220V L24 45 DMX | 50 W |
| 911401746853 | BVP353 24LED RGBNW 220V L24 45 DMX | 50 W |
| 911401747943 | BVP353 60LED 27K 220V L50 10 | 120 W |
| 911401747953 | BVP353 60LED 30K 220V L50 10 | 120 W |

UniFlood M G2

| Order Code | Full Product Name | Power Consumption |
|--------------|------------------------------------|-------------------|
| 911401747963 | BVP353 60LED 40K 220V L50 10 | 120 W |
| 911401747973 | BVP353 60LED 27K 220V L50 10 DMX | 120 W |
| 911401747983 | BVP353 60LED 30K 220V L50 10 DMX | 120 W |
| 911401747993 | BVP353 60LED 40K 220V L50 10 DMX | 120 W |
| 911401748003 | BVP353 60LED RGB 220V L50 10 DMX | 120 W |
| 911401748013 | BVP353 60LED RGBWW 220V L50 10 DMX | 120 W |
| 911401748023 | BVP353 60LED RGBNW 220V L50 10 DMX | 120 W |
| 911401748033 | BVP353 60LED 27K 220V L50 15 | 120 W |
| 911401748043 | BVP353 60LED 30K 220V L50 15 | 120 W |
| 911401748053 | BVP353 60LED 40K 220V L50 15 | 120 W |
| 911401748063 | BVP353 60LED 27K 220V L50 15 DMX | 120 W |
| 911401748073 | BVP353 60LED 30K 220V L50 15 DMX | 120 W |
| 911401748083 | BVP353 60LED 40K 220V L50 15 DMX | 120 W |
| 911401748093 | BVP353 60LED RGB 220V L50 15 DMX | 120 W |
| 911401748103 | BVP353 60LED RGBWW 220V L50 15 DMX | 120 W |
| 911401748113 | BVP353 60LED RGBNW 220V L50 15 DMX | 120 W |
| 911401748123 | BVP353 60LED 27K 220V L50 30 | 120 W |
| 911401748133 | BVP353 60LED 30K 220V L50 30 | 120 W |
| 911401748143 | BVP353 60LED 40K 220V L50 30 | 120 W |
| 911401748153 | BVP353 60LED 27K 220V L50 30 DMX | 120 W |
| 911401748163 | BVP353 60LED 30K 220V L50 30 DMX | 120 W |
| 911401748173 | BVP353 60LED 40K 220V L50 30 DMX | 120 W |
| 911401748183 | BVP353 60LED RGB 220V L50 30 DMX | 120 W |
| 911401748193 | BVP353 60LED RGBWW 220V L50 30 DMX | 120 W |
| 911401748203 | BVP353 60LED RGBNW 220V L50 30 DMX | 120 W |
| 911401748213 | BVP353 60LED 27K 220V L50 45 | 120 W |
| 911401748223 | BVP353 60LED 30K 220V L50 45 | 120 W |
| 911401748233 | BVP353 60LED 40K 220V L50 45 | 120 W |
| 911401748243 | BVP353 60LED 27K 220V L50 45 DMX | 120 W |
| 911401748253 | BVP353 60LED 30K 220V L50 45 DMX | 120 W |
| 911401748263 | BVP353 60LED 40K 220V L50 45 DMX | 120 W |
| 911401748273 | BVP353 60LED RGB 220V L50 45 DMX | 120 W |
| 911401748283 | BVP353 60LED RGBWW 220V L50 45 DMX | 120 W |
| 911401748293 | BVP353 60LED RGBNW 220V L50 45 DMX | 120 W |
| 911401745783 | BVP353 16LED 27K 220V L18 10 | 30 W |
| 911401745793 | BVP353 16LED 30K 220V L18 10 | 30 W |
| 911401745803 | BVP353 16LED 40K 220V L18 10 | 30 W |
| 911401745813 | BVP353 16LED 27K 220V L18 10 DMX | 30 W |
| 911401745823 | BVP353 16LED 30K 220V L18 10 DMX | 30 W |
| 911401745833 | BVP353 16LED 40K 220V L18 10 DMX | 30 W |
| 911401745843 | BVP353 15LED RGB 220V L18 10 DMX | 30 W |
| 911401745853 | BVP353 16LED RGBWW 220V L18 10 DMX | 30 W |
| 911401745863 | BVP353 16LED RGBNW 220V L18 10 DMX | 30 W |
| 911401745873 | BVP353 16LED 27K 220V L18 15 | 30 W |
| 911401745883 | BVP353 16LED 30K 220V L18 15 | 30 W |
| 911401745893 | BVP353 16LED 40K 220V L18 15 | 30 W |
| 911401745903 | BVP353 16LED 27K 220V L18 15 DMX | 30 W |
| 911401745913 | BVP353 16LED 30K 220V L18 15 DMX | 30 W |
| 911401745923 | BVP353 16LED 40K 220V L18 15 DMX | 30 W |
| 911401745933 | BVP353 15LED RGB 220V L18 15 DMX | 30 W |
| 911401745943 | BVP353 16LED RGBWW 220V L18 15 DMX | 30 W |
| 911401745953 | BVP353 16LED RGBNW 220V L18 15 DMX | 30 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|-------------------------------------|-------------------|
| 911401745963 | BVP353 16LED 27K 220V L18 30 | 30 W |
| 911401745973 | BVP353 16LED 30K 220V L18 30 | 30 W |
| 911401745983 | BVP353 16LED 40K 220V L18 30 | 30 W |
| 911401745993 | BVP353 16LED 27K 220V L18 30 DMX | 30 W |
| 911401746003 | BVP353 16LED 30K 220V L18 30 DMX | 30 W |
| 911401746013 | BVP353 16LED 40K 220V L18 30 DMX | 30 W |
| 911401746023 | BVP353 15LED RGB 220V L18 30 DMX | 30 W |
| 911401746033 | BVP353 16LED RGBWW 220V L18 30 DMX | 30 W |
| 911401746043 | BVP353 16LED RGBNW 220V L18 30 DMX | 30 W |
| 911401746053 | BVP353 16LED 27K 220V L18 45 | 30 W |
| 911401746063 | BVP353 16LED 30K 220V L18 45 | 30 W |
| 911401746073 | BVP353 16LED 40K 220V L18 45 | 30 W |
| 911401746083 | BVP353 16LED 27K 220V L18 45 DMX | 30 W |
| 911401746093 | BVP353 16LED 30K 220V L18 45 DMX | 30 W |
| 911401746103 | BVP353 16LED 40K 220V L18 45 DMX | 30 W |
| 911401746113 | BVP353 15LED RGB 220V L18 45 DMX | 30 W |
| 911401746123 | BVP353 16LED RGBWW 220V L18 45 DMX | 30 W |
| 911401746133 | BVP353 16LED RGBNW 220V L18 45 DMX | 30 W |
| 911401749743 | BVP355 216LED 27K 220V L57 10 | 450 W |
| 911401749753 | BVP355 216LED 30K 220V L57 10 | 450 W |
| 911401749763 | BVP355 216LED 40K 220V L57 10 | 450 W |
| 911401749773 | BVP355 216LED 27K 220V L57 10 DMX | 450 W |
| 911401749783 | BVP355 216LED 30K 220V L57 10 DMX | 450 W |
| 911401749793 | BVP355 216LED 40K 220V L57 10 DMX | 450 W |
| 911401749803 | BVP355 216LED RGB 220V L57 10 DMX | 450 W |
| 911401749813 | BVP355 216LED RGBWW 220V L57 10 DMX | 450 W |
| 911401749823 | BVP355 216LED RGBNW 220V L57 10 DMX | 450 W |
| 911401749833 | BVP355 216LED 27K 220V L57 15 | 450 W |
| 911401749843 | BVP355 216LED 30K 220V L57 15 | 450 W |
| 911401749853 | BVP355 216LED 40K 220V L57 15 | 450 W |
| 911401749863 | BVP355 216LED 27K 220V L57 15 DMX | 450 W |
| 911401749873 | BVP355 216LED 30K 220V L57 15 DMX | 450 W |
| 911401749883 | BVP355 216LED 40K 220V L57 15 DMX | 450 W |
| 911401749893 | BVP355 216LED RGB 220V L57 15 DMX | 450 W |
| 911401749903 | BVP355 216LED RGBWW 220V L57 15 DMX | 450 W |
| 911401749913 | BVP355 216LED RGBNW 220V L57 15 DMX | 450 W |
| 911401749923 | BVP355 216LED 27K 220V L57 30 | 450 W |
| 911401749933 | BVP355 216LED 30K 220V L57 30 | 450 W |
| 911401749943 | BVP355 216LED 40K 220V L57 30 | 450 W |
| 911401749953 | BVP355 216LED 27K 220V L57 30 DMX | 450 W |
| 911401749963 | BVP355 216LED 30K 220V L57 30 DMX | 450 W |
| 911401749973 | BVP355 216LED 40K 220V L57 30 DMX | 450 W |
| 911401749983 | BVP355 216LED RGB 220V L57 30 DMX | 450 W |
| 911401749993 | BVP355 216LED RGBWW 220V L57 30 DMX | 450 W |
| 911401750003 | BVP355 216LED RGBNW 220V L57 30 DMX | 450 W |
| 911401750013 | BVP355 216LED 27K 220V L57 45 | 450 W |
| 911401750023 | BVP355 216LED 30K 220V L57 45 | 450 W |
| 911401750033 | BVP355 216LED 40K 220V L57 45 | 450 W |
| 911401750043 | BVP355 216LED 27K 220V L57 45 DMX | 450 W |
| 911401750053 | BVP355 216LED 30K 220V L57 45 DMX | 450 W |
| 911401750063 | BVP355 216LED 40K 220V L57 45 DMX | 450 W |
| 911401750073 | BVP355 216LED RGB 220V L57 45 DMX | 450 W |

UniFlood M G2

| Order Code | Full Product Name | Power Consumption |
|--------------|-------------------------------------|-------------------|
| 911401750083 | BVP355 216LED RGBWW 220V L57 45 DMX | 450 W |
| 911401750093 | BVP355 216LED RGBNW 220V L57 45 DMX | 450 W |
| 911401750103 | BVP355 180LED 27K 220V L50 10 | 360 W |
| 911401750113 | BVP355 180LED 30K 220V L50 10 | 360 W |
| 911401750123 | BVP355 180LED 40K 220V L50 10 | 360 W |
| 911401750133 | BVP355 180LED 27K 220V L50 10 DMX | 360 W |
| 911401750143 | BVP355 180LED 30K 220V L50 10 DMX | 360 W |
| 911401750153 | BVP355 180LED 40K 220V L50 10 DMX | 360 W |
| 911401750163 | BVP355 180LED RGB 220V L50 10 DMX | 360 W |
| 911401750173 | BVP355 180LED RGBWW 220V L50 10 DMX | 360 W |
| 911401750183 | BVP355 180LED RGBNW 220V L50 10 DMX | 360 W |
| 911401750193 | BVP355 180LED 27K 220V L50 15 | 360 W |
| 911401750203 | BVP355 180LED 30K 220V L50 15 | 360 W |
| 911401750213 | BVP355 180LED 40K 220V L50 15 | 360 W |
| 911401750223 | BVP355 180LED 27K 220V L50 15 DMX | 360 W |
| 911401750233 | BVP355 180LED 30K 220V L50 15 DMX | 360 W |
| 911401750243 | BVP355 180LED 40K 220V L50 15 DMX | 360 W |
| 911401750253 | BVP355 180LED RGB 220V L50 15 DMX | 360 W |
| 911401750263 | BVP355 180LED RGBWW 220V L50 15 DMX | 360 W |
| 911401750273 | BVP355 180LED RGBNW 220V L50 15 DMX | 360 W |
| 911401750283 | BVP355 180LED 27K 220V L50 30 | 360 W |
| 911401750293 | BVP355 180LED 30K 220V L50 30 | 360 W |
| 911401750303 | BVP355 180LED 40K 220V L50 30 | 360 W |
| 911401750313 | BVP355 180LED 27K 220V L50 30 DMX | 360 W |
| 911401750323 | BVP355 180LED 30K 220V L50 30 DMX | 360 W |
| 911401750333 | BVP355 180LED 40K 220V L50 30 DMX | 360 W |
| 911401750343 | BVP355 180LED RGB 220V L50 30 DMX | 360 W |
| 911401750353 | BVP355 180LED RGBWW 220V L50 30 DMX | 360 W |
| 911401750363 | BVP355 180LED RGBNW 220V L50 30 DMX | 360 W |
| 911401750373 | BVP355 180LED 27K 220V L50 45 | 360 W |
| 911401750383 | BVP355 180LED 30K 220V L50 45 | 360 W |
| 911401750393 | BVP355 180LED 40K 220V L50 45 | 360 W |
| 911401750403 | BVP355 180LED 27K 220V L50 45 DMX | 360 W |
| 911401750413 | BVP355 180LED 30K 220V L50 45 DMX | 360 W |
| 911401750423 | BVP355 180LED 40K 220V L50 45 DMX | 360 W |
| 911401750433 | BVP355 180LED RGB 220V L50 45 DMX | 360 W |
| 911401750443 | BVP355 180LED RGBWW 220V L50 45 DMX | 360 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|-------------------------------------|-------------------|
| 911401750453 | BVP355 180LED RGBNW 220V L50 45 DMX | 360 W |
| 911401747583 | BVP353 48LED 27K 220V L40 10 | 100 W |
| 911401747593 | BVP353 48LED 30K 220V L40 10 | 100 W |
| 911401747603 | BVP353 48LED 40K 220V L40 10 | 100 W |
| 911401747613 | BVP353 48LED 27K 220V L40 10 DMX | 100 W |
| 911401747623 | BVP353 48LED 30K 220V L40 10 DMX | 100 W |
| 911401747633 | BVP353 48LED 40K 220V L40 10 DMX | 100 W |
| 911401747643 | BVP353 48LED RGB 220V L40 10 DMX | 100 W |
| 911401747653 | BVP353 48LED RGBWW 220V L40 10 DMX | 100 W |
| 911401747663 | BVP353 48LED RGBNW 220V L40 10 DMX | 100 W |
| 911401747673 | BVP353 48LED 27K 220V L40 15 | 100 W |
| 911401747683 | BVP353 48LED 30K 220V L40 15 | 100 W |
| 911401747693 | BVP353 48LED 40K 220V L40 15 | 100 W |
| 911401747703 | BVP353 48LED 27K 220V L40 15 DMX | 100 W |
| 911401747713 | BVP353 48LED 30K 220V L40 15 DMX | 100 W |
| 911401747723 | BVP353 48LED 40K 220V L40 15 DMX | 100 W |
| 911401747733 | BVP353 48LED RGB 220V L40 15 DMX | 100 W |
| 911401747743 | BVP353 48LED RGBWW 220V L40 15 DMX | 100 W |
| 911401747753 | BVP353 48LED RGBNW 220V L40 15 DMX | 100 W |
| 911401747763 | BVP353 48LED 27K 220V L40 30 | 100 W |
| 911401747773 | BVP353 48LED 30K 220V L40 30 | 100 W |
| 911401747783 | BVP353 48LED 40K 220V L40 30 | 100 W |
| 911401747793 | BVP353 48LED 27K 220V L40 30 DMX | 100 W |
| 911401747803 | BVP353 48LED 30K 220V L40 30 DMX | 100 W |
| 911401747813 | BVP353 48LED 40K 220V L40 30 DMX | 100 W |
| 911401747823 | BVP353 48LED RGB 220V L40 30 DMX | 100 W |
| 911401747833 | BVP353 48LED RGBWW 220V L40 30 DMX | 100 W |
| 911401747843 | BVP353 48LED RGBNW 220V L40 30 DMX | 100 W |
| 911401747853 | BVP353 48LED 27K 220V L40 45 | 100 W |
| 911401747863 | BVP353 48LED 30K 220V L40 45 | 100 W |
| 911401747873 | BVP353 48LED 40K 220V L40 45 | 100 W |
| 911401747883 | BVP353 48LED 27K 220V L40 45 DMX | 100 W |
| 911401747893 | BVP353 48LED 30K 220V L40 45 DMX | 100 W |
| 911401747903 | BVP353 48LED 40K 220V L40 45 DMX | 100 W |
| 911401747913 | BVP353 48LED RGB 220V L40 45 DMX | 100 W |
| 911401747923 | BVP353 48LED RGBWW 220V L40 45 DMX | 100 W |
| 911401747933 | BVP353 48LED RGBNW 220V L40 45 DMX | 100 W |

Controls and Dimming

| Order Code | Full Product Name | Dimmable |
|--------------|------------------------------------|----------|
| 911401746863 | BVP353 30LED 27K 220V L30 10 | No |
| 911401746873 | BVP353 30LED 30K 220V L30 10 | No |
| 911401746883 | BVP353 30LED 40K 220V L30 10 | No |
| 911401746893 | BVP353 30LED 27K 220V L30 10 DMX | Yes |
| 911401746903 | BVP353 30LED 30K 220V L30 10 DMX | Yes |
| 911401746913 | BVP353 30LED 40K 220V L30 10 DMX | Yes |
| 911401746923 | BVP353 30LED RGB 220V L30 10 DMX | Yes |
| 911401746933 | BVP353 32LED RGBWW 220V L30 10 DMX | Yes |
| 911401746943 | BVP353 32LED RGBNW 220V L30 10 DMX | Yes |
| 911401746953 | BVP353 30LED 27K 220V L30 15 | No |
| 911401746963 | BVP353 30LED 30K 220V L30 15 | No |

| Order Code | Full Product Name | Dimmable |
|--------------|------------------------------------|----------|
| 911401746973 | BVP353 30LED 40K 220V L30 15 | No |
| 911401746983 | BVP353 30LED 27K 220V L30 15 DMX | Yes |
| 911401746993 | BVP353 30LED 30K 220V L30 15 DMX | Yes |
| 911401747003 | BVP353 30LED 40K 220V L30 15 DMX | Yes |
| 911401747013 | BVP353 30LED RGB 220V L30 15 DMX | Yes |
| 911401747023 | BVP353 32LED RGBWW 220V L30 15 DMX | Yes |
| 911401747033 | BVP353 32LED RGBNW 220V L30 15 DMX | Yes |
| 911401747043 | BVP353 30LED 27K 220V L30 30 | No |
| 911401747053 | BVP353 30LED 30K 220V L30 30 | No |
| 911401747063 | BVP353 30LED 40K 220V L30 30 | No |
| 911401747073 | BVP353 30LED 27K 220V L30 30 DMX | Yes |

UniFlood M G2

| Order Code | Full Product Name | Dimmable |
|--------------|------------------------------------|----------|
| 911401747083 | BVP353 30LED 30K 220V L30 30 DMX | Yes |
| 911401747093 | BVP353 30LED 40K 220V L30 30 DMX | Yes |
| 911401747103 | BVP353 30LED RGB 220V L30 30 DMX | Yes |
| 911401747113 | BVP353 32LED RGBWW 220V L30 30 DMX | Yes |
| 911401747123 | BVP353 32LED RGBNW 220V L30 30 DMX | Yes |
| 911401747133 | BVP353 30LED 27K 220V L30 45 | No |
| 911401747143 | BVP353 30LED 30K 220V L30 45 | No |
| 911401747153 | BVP353 30LED 40K 220V L30 45 | No |
| 911401747163 | BVP353 30LED 27K 220V L30 45 DMX | Yes |
| 911401747173 | BVP353 30LED 30K 220V L30 45 DMX | Yes |
| 911401747183 | BVP353 30LED 40K 220V L30 45 DMX | Yes |
| 911401747193 | BVP353 30LED RGB 220V L30 45 DMX | Yes |
| 911401747203 | BVP353 32LED RGBWW 220V L30 45 DMX | Yes |
| 911401747213 | BVP353 32LED RGBNW 220V L30 45 DMX | Yes |
| 911401748663 | BVP354 96LED 27K 220V L40 10 | No |
| 911401748673 | BVP354 96LED 30K 220V L40 10 | No |
| 911401748683 | BVP354 96LED 40K 220V L40 10 | No |
| 911401748693 | BVP354 96LED 27K 220V L40 10 DMX | Yes |
| 911401748703 | BVP354 96LED 30K 220V L40 10 DMX | Yes |
| 911401748713 | BVP354 96LED 40K 220V L40 10 DMX | Yes |
| 911401748723 | BVP354 96LED RGB 220V L40 10 DMX | Yes |
| 911401748733 | BVP354 96LED RGBWW 220V L40 10 DMX | Yes |
| 911401748743 | BVP354 96LED RGBNW 220V L40 10 DMX | Yes |
| 911401748753 | BVP354 96LED 27K 220V L40 15 | No |
| 911401748763 | BVP354 96LED 30K 220V L40 15 | No |
| 911401748773 | BVP354 96LED 40K 220V L40 15 | No |
| 911401748783 | BVP354 96LED 27K 220V L40 15 DMX | Yes |
| 911401748793 | BVP354 96LED 30K 220V L40 15 DMX | Yes |
| 911401748803 | BVP354 96LED 40K 220V L40 15 DMX | Yes |
| 911401748813 | BVP354 96LED RGB 220V L40 15 DMX | Yes |
| 911401748823 | BVP354 96LED RGBWW 220V L40 15 DMX | Yes |
| 911401748833 | BVP354 96LED RGBNW 220V L40 15 DMX | Yes |
| 911401748843 | BVP354 96LED 27K 220V L40 30 | No |
| 911401748853 | BVP354 96LED 30K 220V L40 30 | No |
| 911401748863 | BVP354 96LED 40K 220V L40 30 | No |
| 911401748873 | BVP354 96LED 27K 220V L40 30 DMX | Yes |
| 911401748883 | BVP354 96LED 30K 220V L40 30 DMX | Yes |
| 911401748893 | BVP354 96LED 40K 220V L40 30 DMX | Yes |
| 911401748903 | BVP354 96LED RGB 220V L40 30 DMX | Yes |
| 911401748913 | BVP354 96LED RGBWW 220V L40 30 DMX | Yes |
| 911401748923 | BVP354 96LED RGBNW 220V L40 30 DMX | Yes |
| 911401748933 | BVP354 96LED 27K 220V L40 45 | No |
| 911401748943 | BVP354 96LED 30K 220V L40 45 | No |
| 911401748953 | BVP354 96LED 40K 220V L40 45 | No |
| 911401748963 | BVP354 96LED 27K 220V L40 45 DMX | Yes |
| 911401748973 | BVP354 96LED 30K 220V L40 45 DMX | Yes |
| 911401748983 | BVP354 96LED 40K 220V L40 45 DMX | Yes |
| 911401748993 | BVP354 96LED RGB 220V L40 45 DMX | Yes |
| 911401749003 | BVP354 96LED RGBWW 220V L40 45 DMX | Yes |
| 911401749013 | BVP354 96LED RGBNW 220V L40 45 DMX | Yes |
| 911401749023 | BVP354 120LED 27K 220V L50 10 | No |
| 911401749033 | BVP354 120LED 30K 220V L50 10 | No |

| Order Code | Full Product Name | Dimmable |
|--------------|-------------------------------------|----------|
| 911401749043 | BVP354 120LED 40K 220V L50 10 | No |
| 911401749053 | BVP354 120LED 27K 220V L50 10 DMX | Yes |
| 911401749063 | BVP354 120LED 30K 220V L50 10 DMX | Yes |
| 911401749073 | BVP354 120LED 40K 220V L50 10 DMX | Yes |
| 911401749083 | BVP354 120LED RGB 220V L50 10 DMX | Yes |
| 911401749093 | BVP354 120LED RGBWW 220V L50 10 DMX | Yes |
| 911401749103 | BVP354 120LED RGBNW 220V L50 10 DMX | Yes |
| 911401749113 | BVP354 120LED 27K 220V L50 15 | No |
| 911401749123 | BVP354 120LED 30K 220V L50 15 | No |
| 911401749133 | BVP354 120LED 40K 220V L50 15 | No |
| 911401749143 | BVP354 120LED 27K 220V L50 15 DMX | Yes |
| 911401749153 | BVP354 120LED 30K 220V L50 15 DMX | Yes |
| 911401749163 | BVP354 120LED 40K 220V L50 15 DMX | Yes |
| 911401749173 | BVP354 120LED RGB 220V L50 15 DMX | Yes |
| 911401749183 | BVP354 120LED RGBWW 220V L50 15 DMX | Yes |
| 911401749193 | BVP354 120LED RGBNW 220V L50 15 DMX | Yes |
| 911401749203 | BVP354 120LED 27K 220V L50 30 | No |
| 911401749213 | BVP354 120LED 30K 220V L50 30 | No |
| 911401749223 | BVP354 120LED 40K 220V L50 30 | No |
| 911401749233 | BVP354 120LED 27K 220V L50 30 DMX | Yes |
| 911401749243 | BVP354 120LED 30K 220V L50 30 DMX | Yes |
| 911401749253 | BVP354 120LED 40K 220V L50 30 DMX | Yes |
| 911401749263 | BVP354 120LED RGB 220V L50 30 DMX | Yes |
| 911401749273 | BVP354 120LED RGBWW 220V L50 30 DMX | Yes |
| 911401749283 | BVP354 120LED RGBNW 220V L50 30 DMX | Yes |
| 911401749293 | BVP354 120LED 27K 220V L50 45 | No |
| 911401749303 | BVP354 120LED 30K 220V L50 45 | No |
| 911401749313 | BVP354 120LED 40K 220V L50 45 | No |
| 911401749323 | BVP354 120LED 27K 220V L50 45 DMX | Yes |
| 911401749333 | BVP354 120LED 30K 220V L50 45 DMX | Yes |
| 911401749343 | BVP354 120LED 40K 220V L50 45 DMX | Yes |
| 911401749353 | BVP354 120LED RGB 220V L50 45 DMX | Yes |
| 911401749363 | BVP354 120LED RGBWW 220V L50 45 DMX | Yes |
| 911401749373 | BVP354 120LED RGBNW 220V L50 45 DMX | Yes |
| 911401749383 | BVP354 144LED 27K 220V L57 10 | No |
| 911401749393 | BVP354 144LED 30K 220V L57 10 | No |
| 911401749403 | BVP354 144LED 40K 220V L57 10 | No |
| 911401749413 | BVP354 144LED 27K 220V L57 10 DMX | Yes |
| 911401749423 | BVP354 144LED 30K 220V L57 10 DMX | Yes |
| 911401749433 | BVP354 144LED 40K 220V L57 10 DMX | Yes |
| 911401749443 | BVP354 144LED RGB 220V L57 10 DMX | Yes |
| 911401749453 | BVP354 144LED RGBWW 220V L57 10 DMX | Yes |
| 911401749463 | BVP354 144LED RGBNW 220V L57 10 DMX | Yes |
| 911401749473 | BVP354 144LED 27K 220V L57 15 | No |
| 911401749483 | BVP354 144LED 30K 220V L57 15 | No |
| 911401749493 | BVP354 144LED 40K 220V L57 15 | No |
| 911401749503 | BVP354 144LED 27K 220V L57 15 DMX | Yes |
| 911401749513 | BVP354 144LED 30K 220V L57 15 DMX | Yes |
| 911401749523 | BVP354 144LED 40K 220V L57 15 DMX | Yes |
| 911401749533 | BVP354 144LED RGB 220V L57 15 DMX | Yes |
| 911401749543 | BVP354 144LED RGBWW 220V L57 15 DMX | Yes |
| 911401749553 | BVP354 144LED RGBNW 220V L57 15 DMX | Yes |

UniFlood M G2

| Order Code | Full Product Name | Dimmable | Order Code | Full Product Name | Dimmable |
|--------------|-------------------------------------|----------|--------------|------------------------------------|----------|
| 911401749563 | BVP354 144LED 27K 220V L57 30 | No | 911401748643 | BVP353 72LED RGBWW 220V L57 45 DMX | Yes |
| 911401749573 | BVP354 144LED 30K 220V L57 30 | No | 911401748653 | BVP353 72LED RGBNW 220V L57 45 DMX | Yes |
| 911401749583 | BVP354 144LED 40K 220V L57 30 | No | 911401746143 | BVP353 18LED 27K 220V L21 10 | No |
| 911401749593 | BVP354 144LED 27K 220V L57 30 DMX | Yes | 911401746153 | BVP353 18LED 30K 220V L21 10 | No |
| 911401749603 | BVP354 144LED 30K 220V L57 30 DMX | Yes | 911401746163 | BVP353 18LED 40K 220V L21 10 | No |
| 911401749613 | BVP354 144LED 40K 220V L57 30 DMX | Yes | 911401746173 | BVP353 18LED 27K 220V L21 10 DMX | Yes |
| 911401749623 | BVP354 144LED RGB 220V L57 30 DMX | Yes | 911401746183 | BVP353 18LED 30K 220V L21 10 DMX | Yes |
| 911401749633 | BVP354 144LED RGBWW 220V L57 30 DMX | Yes | 911401746193 | BVP353 18LED 40K 220V L21 10 DMX | Yes |
| 911401749643 | BVP354 144LED RGBNW 220V L57 30 DMX | Yes | 911401746203 | BVP353 18LED RGB 220V L21 10 DMX | Yes |
| 911401749653 | BVP354 144LED 27K 220V L57 45 | No | 911401746213 | BVP353 20LED RGBWW 220V L21 10 DMX | Yes |
| 911401749663 | BVP354 144LED 30K 220V L57 45 | No | 911401746223 | BVP353 20LED RGBNW 220V L21 10 DMX | Yes |
| 911401749673 | BVP354 144LED 40K 220V L57 45 | No | 911401746233 | BVP353 18LED 27K 220V L21 15 | No |
| 911401749683 | BVP354 144LED 27K 220V L57 45 DMX | Yes | 911401746243 | BVP353 18LED 30K 220V L21 15 | No |
| 911401749693 | BVP354 144LED 30K 220V L57 45 DMX | Yes | 911401746253 | BVP353 18LED 40K 220V L21 15 | No |
| 911401749703 | BVP354 144LED 40K 220V L57 45 DMX | Yes | 911401746263 | BVP353 18LED 27K 220V L21 15 DMX | Yes |
| 911401749713 | BVP354 144LED RGB 220V L57 45 DMX | Yes | 911401746273 | BVP353 18LED 30K 220V L21 15 DMX | Yes |
| 911401749723 | BVP354 144LED RGBWW 220V L57 45 DMX | Yes | 911401746283 | BVP353 18LED 40K 220V L21 15 DMX | Yes |
| 911401749733 | BVP354 144LED RGBNW 220V L57 45 DMX | Yes | 911401746293 | BVP353 18LED RGB 220V L21 15 DMX | Yes |
| 911401748303 | BVP353 72LED 27K 220V L57 10 | No | 911401746303 | BVP353 20LED RGBWW 220V L21 15 DMX | Yes |
| 911401748313 | BVP353 72LED 30K 220V L57 10 | No | 911401746313 | BVP353 20LED RGBNW 220V L21 15 DMX | Yes |
| 911401748323 | BVP353 72LED 40K 220V L57 10 | No | 911401746323 | BVP353 18LED 27K 220V L21 30 | No |
| 911401748333 | BVP353 72LED 27K 220V L57 10 DMX | Yes | 911401746333 | BVP353 18LED 30K 220V L21 30 | No |
| 911401748343 | BVP353 72LED 30K 220V L57 10 DMX | Yes | 911401746343 | BVP353 18LED 40K 220V L21 30 | No |
| 911401748353 | BVP353 72LED 40K 220V L57 10 DMX | Yes | 911401746353 | BVP353 18LED 27K 220V L21 30 DMX | Yes |
| 911401748363 | BVP353 72LED RGB 220V L57 10 DMX | Yes | 911401746363 | BVP353 18LED 30K 220V L21 30 DMX | Yes |
| 911401748373 | BVP353 72LED RGBWW 220V L57 10 DMX | Yes | 911401746373 | BVP353 18LED 40K 220V L21 30 DMX | Yes |
| 911401748383 | BVP353 72LED RGBNW 220V L57 10 DMX | Yes | 911401746383 | BVP353 18LED RGB 220V L21 30 DMX | Yes |
| 911401748393 | BVP353 72LED 27K 220V L57 15 | No | 911401746393 | BVP353 20LED RGBWW 220V L21 30 DMX | Yes |
| 911401748403 | BVP353 72LED 30K 220V L57 15 | No | 911401746403 | BVP353 20LED RGBNW 220V L21 30 DMX | Yes |
| 911401748413 | BVP353 72LED 40K 220V L57 15 | No | 911401746413 | BVP353 18LED 27K 220V L21 45 | No |
| 911401748423 | BVP353 72LED 27K 220V L57 15 DMX | Yes | 911401746423 | BVP353 18LED 30K 220V L21 45 | No |
| 911401748433 | BVP353 72LED 30K 220V L57 15 DMX | Yes | 911401746433 | BVP353 18LED 40K 220V L21 45 | No |
| 911401748443 | BVP353 72LED 40K 220V L57 15 DMX | Yes | 911401746443 | BVP353 18LED 27K 220V L21 45 DMX | Yes |
| 911401748453 | BVP353 72LED RGB 220V L57 15 DMX | Yes | 911401746453 | BVP353 18LED 30K 220V L21 45 DMX | Yes |
| 911401748463 | BVP353 72LED RGBWW 220V L57 15 DMX | Yes | 911401746463 | BVP353 18LED 40K 220V L21 45 DMX | Yes |
| 911401748473 | BVP353 72LED RGBNW 220V L57 15 DMX | Yes | 911401746473 | BVP353 18LED RGB 220V L21 45 DMX | Yes |
| 911401748483 | BVP353 72LED 27K 220V L57 30 | No | 911401746483 | BVP353 20LED RGBWW 220V L21 45 DMX | Yes |
| 911401748493 | BVP353 72LED 30K 220V L57 30 | No | 911401746493 | BVP353 20LED RGBNW 220V L21 45 DMX | Yes |
| 911401748503 | BVP353 72LED 40K 220V L57 30 | No | 911401745423 | BVP353 12LED 27K 220V L15 10 | No |
| 911401748513 | BVP353 72LED 27K 220V L57 30 DMX | Yes | 911401745433 | BVP353 12LED 30K 220V L15 10 | No |
| 911401748523 | BVP353 72LED 30K 220V L57 30 DMX | Yes | 911401745443 | BVP353 12LED 40K 220V L15 10 | No |
| 911401748533 | BVP353 72LED 40K 220V L57 30 DMX | Yes | 911401745453 | BVP353 12LED 27K 220V L15 10 DMX | Yes |
| 911401748543 | BVP353 72LED RGB 220V L57 30 DMX | Yes | 911401745463 | BVP353 12LED 30K 220V L15 10 DMX | Yes |
| 911401748553 | BVP353 72LED RGBWW 220V L57 30 DMX | Yes | 911401745473 | BVP353 12LED 40K 220V L15 10 DMX | Yes |
| 911401748563 | BVP353 72LED RGBNW 220V L57 30 DMX | Yes | 911401745483 | BVP353 12LED RGB 220V L15 10 DMX | Yes |
| 911401748573 | BVP353 72LED 27K 220V L57 45 | No | 911401745493 | BVP353 12LED RGBWW 220V L15 10 DMX | Yes |
| 911401748583 | BVP353 72LED 30K 220V L57 45 | No | 911401745503 | BVP353 12LED RGBNW 220V L15 10 DMX | Yes |
| 911401748593 | BVP353 72LED 40K 220V L57 45 | No | 911401745513 | BVP353 12LED 27K 220V L15 15 | No |
| 911401748603 | BVP353 72LED 27K 220V L57 45 DMX | Yes | 911401745523 | BVP353 12LED 30K 220V L15 15 | No |
| 911401748613 | BVP353 72LED 30K 220V L57 45 DMX | Yes | 911401745533 | BVP353 12LED 40K 220V L15 15 | No |
| 911401748623 | BVP353 72LED 40K 220V L57 45 DMX | Yes | 911401745543 | BVP353 12LED 27K 220V L15 15 DMX | Yes |
| 911401748633 | BVP353 72LED RGB 220V L57 45 DMX | Yes | 911401745553 | BVP353 12LED 30K 220V L15 15 DMX | Yes |

UniFlood M G2

| Order Code | Full Product Name | Dimmable | Order Code | Full Product Name | Dimmable |
|--------------|------------------------------------|----------|--------------|------------------------------------|----------|
| 911401745563 | BVP353 12LED 40K 220V L15 15 DMX | Yes | 911401747523 | BVP353 36LED 27K 220V L35 45 DMX | Yes |
| 911401745573 | BVP353 12LED RGB 220V L15 15 DMX | Yes | 911401747533 | BVP353 36LED 30K 220V L35 45 DMX | Yes |
| 911401745583 | BVP353 12LED RGBWW 220V L15 15 DMX | Yes | 911401747543 | BVP353 36LED 40K 220V L35 45 DMX | Yes |
| 911401745593 | BVP353 12LED RGBNW 220V L15 15 DMX | Yes | 911401747553 | BVP353 36LED RGB 220V L35 45 DMX | Yes |
| 911401745603 | BVP353 12LED 27K 220V L15 30 | No | 911401747563 | BVP353 36LED RGBWW 220V L35 45 DMX | Yes |
| 911401745613 | BVP353 12LED 30K 220V L15 30 | No | 911401747573 | BVP353 36LED RGBNW 220V L35 45 DMX | Yes |
| 911401745623 | BVP353 12LED 40K 220V L15 30 | No | 911401746503 | BVP353 24LED 27K 220V L24 10 | No |
| 911401745633 | BVP353 12LED 27K 220V L15 30 DMX | Yes | 911401746513 | BVP353 24LED 30K 220V L24 10 | No |
| 911401745643 | BVP353 12LED 30K 220V L15 30 DMX | Yes | 911401746523 | BVP353 24LED 40K 220V L24 10 | No |
| 911401745653 | BVP353 12LED 40K 220V L15 30 DMX | Yes | 911401746533 | BVP353 24LED 27K 220V L24 10 DMX | Yes |
| 911401745663 | BVP353 12LED RGB 220V L15 30 DMX | Yes | 911401746543 | BVP353 24LED 30K 220V L24 10 DMX | Yes |
| 911401745673 | BVP353 12LED RGBWW 220V L15 30 DMX | Yes | 911401746553 | BVP353 24LED 40K 220V L24 10 DMX | Yes |
| 911401745683 | BVP353 12LED RGBNW 220V L15 30 DMX | Yes | 911401746563 | BVP353 24LED RGB 220V L24 10 DMX | Yes |
| 911401745693 | BVP353 12LED 27K 220V L15 45 | No | 911401746573 | BVP353 24LED RGBWW 220V L24 10 DMX | Yes |
| 911401745703 | BVP353 12LED 30K 220V L15 45 | No | 911401746583 | BVP353 24LED RGBNW 220V L24 10 DMX | Yes |
| 911401745713 | BVP353 12LED 40K 220V L15 45 | No | 911401746593 | BVP353 24LED 27K 220V L24 15 | No |
| 911401745723 | BVP353 12LED 27K 220V L15 45 DMX | Yes | 911401746603 | BVP353 24LED 30K 220V L24 15 | No |
| 911401745733 | BVP353 12LED 30K 220V L15 45 DMX | Yes | 911401746613 | BVP353 24LED 40K 220V L24 15 | No |
| 911401745743 | BVP353 12LED 40K 220V L15 45 DMX | Yes | 911401746623 | BVP353 24LED 27K 220V L24 15 DMX | Yes |
| 911401745753 | BVP353 12LED RGB 220V L15 45 DMX | Yes | 911401746633 | BVP353 24LED 30K 220V L24 15 DMX | Yes |
| 911401745763 | BVP353 12LED RGBWW 220V L15 45 DMX | Yes | 911401746643 | BVP353 24LED 40K 220V L24 15 DMX | Yes |
| 911401745773 | BVP353 12LED RGBNW 220V L15 45 DMX | Yes | 911401746653 | BVP353 24LED RGB 220V L24 15 DMX | Yes |
| 911401747223 | BVP353 36LED 27K 220V L35 10 | No | 911401746663 | BVP353 24LED RGBWW 220V L24 15 DMX | Yes |
| 911401747233 | BVP353 36LED 30K 220V L35 10 | No | 911401746673 | BVP353 24LED RGBNW 220V L24 15 DMX | Yes |
| 911401747243 | BVP353 36LED 40K 220V L35 10 | No | 911401746683 | BVP353 24LED 27K 220V L24 30 | No |
| 911401747253 | BVP353 36LED 27K 220V L35 10 DMX | Yes | 911401746693 | BVP353 24LED 30K 220V L24 30 | No |
| 911401747263 | BVP353 36LED 30K 220V L35 10 DMX | Yes | 911401746703 | BVP353 24LED 40K 220V L24 30 | No |
| 911401747273 | BVP353 36LED 40K 220V L35 10 DMX | Yes | 911401746713 | BVP353 24LED 27K 220V L24 30 DMX | Yes |
| 911401747283 | BVP353 36LED RGB 220V L35 10 DMX | Yes | 911401746723 | BVP353 24LED 30K 220V L24 30 DMX | Yes |
| 911401747293 | BVP353 36LED RGBWW 220V L35 10 DMX | Yes | 911401746733 | BVP353 24LED 40K 220V L24 30 DMX | Yes |
| 911401747303 | BVP353 36LED RGBNW 220V L35 10 DMX | Yes | 911401746743 | BVP353 24LED RGB 220V L24 30 DMX | Yes |
| 911401747313 | BVP353 36LED 27K 220V L35 15 | No | 911401746753 | BVP353 24LED RGBWW 220V L24 30 DMX | Yes |
| 911401747323 | BVP353 36LED 30K 220V L35 15 | No | 911401746763 | BVP353 24LED RGBNW 220V L24 30 DMX | Yes |
| 911401747333 | BVP353 36LED 40K 220V L35 15 | No | 911401746773 | BVP353 24LED 27K 220V L24 45 | No |
| 911401747343 | BVP353 36LED 27K 220V L35 15 DMX | Yes | 911401746783 | BVP353 24LED 30K 220V L24 45 | No |
| 911401747353 | BVP353 36LED 30K 220V L35 15 DMX | Yes | 911401746793 | BVP353 24LED 40K 220V L24 45 | No |
| 911401747363 | BVP353 36LED 40K 220V L35 15 DMX | Yes | 911401746803 | BVP353 24LED 27K 220V L24 45 DMX | Yes |
| 911401747373 | BVP353 36LED RGB 220V L35 15 DMX | Yes | 911401746813 | BVP353 24LED 30K 220V L24 45 DMX | Yes |
| 911401747383 | BVP353 36LED RGBWW 220V L35 15 DMX | Yes | 911401746823 | BVP353 24LED 40K 220V L24 45 DMX | Yes |
| 911401747393 | BVP353 36LED RGBNW 220V L35 15 DMX | Yes | 911401746833 | BVP353 24LED RGB 220V L24 45 DMX | Yes |
| 911401747403 | BVP353 36LED 27K 220V L35 30 | No | 911401746843 | BVP353 24LED RGBWW 220V L24 45 DMX | Yes |
| 911401747413 | BVP353 36LED 30K 220V L35 30 | No | 911401746853 | BVP353 24LED RGBNW 220V L24 45 DMX | Yes |
| 911401747423 | BVP353 36LED 40K 220V L35 30 | No | 911401747943 | BVP353 60LED 27K 220V L50 10 | No |
| 911401747433 | BVP353 36LED 27K 220V L35 30 DMX | Yes | 911401747953 | BVP353 60LED 30K 220V L50 10 | No |
| 911401747443 | BVP353 36LED 30K 220V L35 30 DMX | Yes | 911401747963 | BVP353 60LED 40K 220V L50 10 | No |
| 911401747453 | BVP353 36LED 40K 220V L35 30 DMX | Yes | 911401747973 | BVP353 60LED 27K 220V L50 10 DMX | Yes |
| 911401747463 | BVP353 36LED RGB 220V L35 30 DMX | Yes | 911401747983 | BVP353 60LED 30K 220V L50 10 DMX | Yes |
| 911401747473 | BVP353 36LED RGBWW 220V L35 30 DMX | Yes | 911401747993 | BVP353 60LED 40K 220V L50 10 DMX | Yes |
| 911401747483 | BVP353 36LED RGBNW 220V L35 30 DMX | Yes | 911401748003 | BVP353 60LED RGB 220V L50 10 DMX | Yes |
| 911401747493 | BVP353 36LED 27K 220V L35 45 | No | 911401748013 | BVP353 60LED RGBWW 220V L50 10 DMX | Yes |
| 911401747503 | BVP353 36LED 30K 220V L35 45 | No | 911401748023 | BVP353 60LED RGBNW 220V L50 10 DMX | Yes |
| 911401747513 | BVP353 36LED 40K 220V L35 45 | No | 911401748033 | BVP353 60LED 27K 220V L50 15 | No |

UniFlood M G2

| Order Code | Full Product Name | Dimmable | Order Code | Full Product Name | Dimmable |
|--------------|------------------------------------|----------|--------------|-------------------------------------|----------|
| 911401748043 | BVP353 60LED 30K 220V L50 15 | No | 911401746043 | BVP353 16LED RGBNW 220V L18 30 DMX | Yes |
| 911401748053 | BVP353 60LED 40K 220V L50 15 | No | 911401746053 | BVP353 16LED 27K 220V L18 45 | No |
| 911401748063 | BVP353 60LED 27K 220V L50 15 DMX | Yes | 911401746063 | BVP353 16LED 30K 220V L18 45 | No |
| 911401748073 | BVP353 60LED 30K 220V L50 15 DMX | Yes | 911401746073 | BVP353 16LED 40K 220V L18 45 | No |
| 911401748083 | BVP353 60LED 40K 220V L50 15 DMX | Yes | 911401746083 | BVP353 16LED 27K 220V L18 45 DMX | Yes |
| 911401748093 | BVP353 60LED RGB 220V L50 15 DMX | Yes | 911401746093 | BVP353 16LED 30K 220V L18 45 DMX | Yes |
| 911401748103 | BVP353 60LED RGBWW 220V L50 15 DMX | Yes | 911401746103 | BVP353 16LED 40K 220V L18 45 DMX | Yes |
| 911401748113 | BVP353 60LED RGBNW 220V L50 15 DMX | Yes | 911401746113 | BVP353 15LED RGB 220V L18 45 DMX | Yes |
| 911401748123 | BVP353 60LED 27K 220V L50 30 | No | 911401746123 | BVP353 16LED RGBWW 220V L18 45 DMX | Yes |
| 911401748133 | BVP353 60LED 30K 220V L50 30 | No | 911401746133 | BVP353 16LED RGBNW 220V L18 45 DMX | Yes |
| 911401748143 | BVP353 60LED 40K 220V L50 30 | No | 911401749743 | BVP355 216LED 27K 220V L57 10 | No |
| 911401748153 | BVP353 60LED 27K 220V L50 30 DMX | Yes | 911401749753 | BVP355 216LED 30K 220V L57 10 | No |
| 911401748163 | BVP353 60LED 30K 220V L50 30 DMX | Yes | 911401749763 | BVP355 216LED 40K 220V L57 10 | No |
| 911401748173 | BVP353 60LED 40K 220V L50 30 DMX | Yes | 911401749773 | BVP355 216LED 27K 220V L57 10 DMX | Yes |
| 911401748183 | BVP353 60LED RGB 220V L50 30 DMX | Yes | 911401749783 | BVP355 216LED 30K 220V L57 10 DMX | Yes |
| 911401748193 | BVP353 60LED RGBWW 220V L50 30 DMX | Yes | 911401749793 | BVP355 216LED 40K 220V L57 10 DMX | Yes |
| 911401748203 | BVP353 60LED RGBNW 220V L50 30 DMX | Yes | 911401749803 | BVP355 216LED RGB 220V L57 10 DMX | Yes |
| 911401748213 | BVP353 60LED 27K 220V L50 45 | No | 911401749813 | BVP355 216LED RGBWW 220V L57 10 DMX | Yes |
| 911401748223 | BVP353 60LED 30K 220V L50 45 | No | 911401749823 | BVP355 216LED RGBNW 220V L57 10 DMX | Yes |
| 911401748233 | BVP353 60LED 40K 220V L50 45 | No | 911401749833 | BVP355 216LED 27K 220V L57 15 | No |
| 911401748243 | BVP353 60LED 27K 220V L50 45 DMX | Yes | 911401749843 | BVP355 216LED 30K 220V L57 15 | No |
| 911401748253 | BVP353 60LED 30K 220V L50 45 DMX | Yes | 911401749853 | BVP355 216LED 40K 220V L57 15 | No |
| 911401748263 | BVP353 60LED 40K 220V L50 45 DMX | Yes | 911401749863 | BVP355 216LED 27K 220V L57 15 DMX | Yes |
| 911401748273 | BVP353 60LED RGB 220V L50 45 DMX | Yes | 911401749873 | BVP355 216LED 30K 220V L57 15 DMX | Yes |
| 911401748283 | BVP353 60LED RGBWW 220V L50 45 DMX | Yes | 911401749883 | BVP355 216LED 40K 220V L57 15 DMX | Yes |
| 911401748293 | BVP353 60LED RGBNW 220V L50 45 DMX | Yes | 911401749893 | BVP355 216LED RGB 220V L57 15 DMX | Yes |
| 911401745783 | BVP353 16LED 27K 220V L18 10 | No | 911401749903 | BVP355 216LED RGBWW 220V L57 15 DMX | Yes |
| 911401745793 | BVP353 16LED 30K 220V L18 10 | No | 911401749913 | BVP355 216LED RGBNW 220V L57 15 DMX | Yes |
| 911401745803 | BVP353 16LED 40K 220V L18 10 | No | 911401749923 | BVP355 216LED 27K 220V L57 30 | No |
| 911401745813 | BVP353 16LED 27K 220V L18 10 DMX | Yes | 911401749933 | BVP355 216LED 30K 220V L57 30 | No |
| 911401745823 | BVP353 16LED 30K 220V L18 10 DMX | Yes | 911401749943 | BVP355 216LED 40K 220V L57 30 | No |
| 911401745833 | BVP353 16LED 40K 220V L18 10 DMX | Yes | 911401749953 | BVP355 216LED 27K 220V L57 30 DMX | Yes |
| 911401745843 | BVP353 15LED RGB 220V L18 10 DMX | Yes | 911401749963 | BVP355 216LED 30K 220V L57 30 DMX | Yes |
| 911401745853 | BVP353 16LED RGBWW 220V L18 10 DMX | Yes | 911401749973 | BVP355 216LED 40K 220V L57 30 DMX | Yes |
| 911401745863 | BVP353 16LED RGBNW 220V L18 10 DMX | Yes | 911401749983 | BVP355 216LED RGB 220V L57 30 DMX | Yes |
| 911401745873 | BVP353 16LED 27K 220V L18 15 | No | 911401749993 | BVP355 216LED RGBWW 220V L57 30 DMX | Yes |
| 911401745883 | BVP353 16LED 30K 220V L18 15 | No | 911401750003 | BVP355 216LED RGBNW 220V L57 30 DMX | Yes |
| 911401745893 | BVP353 16LED 40K 220V L18 15 | No | 911401750013 | BVP355 216LED 27K 220V L57 45 | No |
| 911401745903 | BVP353 16LED 27K 220V L18 15 DMX | Yes | 911401750023 | BVP355 216LED 30K 220V L57 45 | No |
| 911401745913 | BVP353 16LED 30K 220V L18 15 DMX | Yes | 911401750033 | BVP355 216LED 40K 220V L57 45 | No |
| 911401745923 | BVP353 16LED 40K 220V L18 15 DMX | Yes | 911401750043 | BVP355 216LED 27K 220V L57 45 DMX | Yes |
| 911401745933 | BVP353 15LED RGB 220V L18 15 DMX | Yes | 911401750053 | BVP355 216LED 30K 220V L57 45 DMX | Yes |
| 911401745943 | BVP353 16LED RGBWW 220V L18 15 DMX | Yes | 911401750063 | BVP355 216LED 40K 220V L57 45 DMX | Yes |
| 911401745953 | BVP353 16LED RGBNW 220V L18 15 DMX | Yes | 911401750073 | BVP355 216LED RGB 220V L57 45 DMX | Yes |
| 911401745963 | BVP353 16LED 27K 220V L18 30 | No | 911401750083 | BVP355 216LED RGBWW 220V L57 45 DMX | Yes |
| 911401745973 | BVP353 16LED 30K 220V L18 30 | No | 911401750093 | BVP355 216LED RGBNW 220V L57 45 DMX | Yes |
| 911401745983 | BVP353 16LED 40K 220V L18 30 | No | 911401750103 | BVP355 180LED 27K 220V L50 10 | No |
| 911401745993 | BVP353 16LED 27K 220V L18 30 DMX | Yes | 911401750113 | BVP355 180LED 30K 220V L50 10 | No |
| 911401746003 | BVP353 16LED 30K 220V L18 30 DMX | Yes | 911401750123 | BVP355 180LED 40K 220V L50 10 | No |
| 911401746013 | BVP353 16LED 40K 220V L18 30 DMX | Yes | 911401750133 | BVP355 180LED 27K 220V L50 10 DMX | Yes |
| 911401746023 | BVP353 15LED RGB 220V L18 30 DMX | Yes | 911401750143 | BVP355 180LED 30K 220V L50 10 DMX | Yes |
| 911401746033 | BVP353 16LED RGBWW 220V L18 30 DMX | Yes | 911401750153 | BVP355 180LED 40K 220V L50 10 DMX | Yes |

UniFlood M G2

| Order Code | Full Product Name | Dimmable | Order Code | Full Product Name | Dimmable |
|--------------|-------------------------------------|----------|--------------|------------------------------------|----------|
| 911401750163 | BVP355 180LED RGB 220V L50 10 DMX | Yes | 911401747613 | BVP353 48LED 27K 220V L40 10 DMX | Yes |
| 911401750173 | BVP355 180LED RGBWW 220V L50 10 DMX | Yes | 911401747623 | BVP353 48LED 30K 220V L40 10 DMX | Yes |
| 911401750183 | BVP355 180LED RGBNW 220V L50 10 DMX | Yes | 911401747633 | BVP353 48LED 40K 220V L40 10 DMX | Yes |
| 911401750193 | BVP355 180LED 27K 220V L50 15 | No | 911401747643 | BVP353 48LED RGB 220V L40 10 DMX | Yes |
| 911401750203 | BVP355 180LED 30K 220V L50 15 | No | 911401747653 | BVP353 48LED RGBWW 220V L40 10 DMX | Yes |
| 911401750213 | BVP355 180LED 40K 220V L50 15 | No | 911401747663 | BVP353 48LED RGBNW 220V L40 10 DMX | Yes |
| 911401750223 | BVP355 180LED 27K 220V L50 15 DMX | Yes | 911401747673 | BVP353 48LED 27K 220V L40 15 | No |
| 911401750233 | BVP355 180LED 30K 220V L50 15 DMX | Yes | 911401747683 | BVP353 48LED 30K 220V L40 15 | No |
| 911401750243 | BVP355 180LED 40K 220V L50 15 DMX | Yes | 911401747693 | BVP353 48LED 40K 220V L40 15 | No |
| 911401750253 | BVP355 180LED RGB 220V L50 15 DMX | Yes | 911401747703 | BVP353 48LED 27K 220V L40 15 DMX | Yes |
| 911401750263 | BVP355 180LED RGBWW 220V L50 15 DMX | Yes | 911401747713 | BVP353 48LED 30K 220V L40 15 DMX | Yes |
| 911401750273 | BVP355 180LED RGBNW 220V L50 15 DMX | Yes | 911401747723 | BVP353 48LED 40K 220V L40 15 DMX | Yes |
| 911401750283 | BVP355 180LED 27K 220V L50 30 | No | 911401747733 | BVP353 48LED RGB 220V L40 15 DMX | Yes |
| 911401750293 | BVP355 180LED 30K 220V L50 30 | No | 911401747743 | BVP353 48LED RGBWW 220V L40 15 DMX | Yes |
| 911401750303 | BVP355 180LED 40K 220V L50 30 | No | 911401747753 | BVP353 48LED RGBNW 220V L40 15 DMX | Yes |
| 911401750313 | BVP355 180LED 27K 220V L50 30 DMX | Yes | 911401747763 | BVP353 48LED 27K 220V L40 30 | No |
| 911401750323 | BVP355 180LED 30K 220V L50 30 DMX | Yes | 911401747773 | BVP353 48LED 30K 220V L40 30 | No |
| 911401750333 | BVP355 180LED 40K 220V L50 30 DMX | Yes | 911401747783 | BVP353 48LED 40K 220V L40 30 | No |
| 911401750343 | BVP355 180LED RGB 220V L50 30 DMX | Yes | 911401747793 | BVP353 48LED 27K 220V L40 30 DMX | Yes |
| 911401750353 | BVP355 180LED RGBWW 220V L50 30 DMX | Yes | 911401747803 | BVP353 48LED 30K 220V L40 30 DMX | Yes |
| 911401750363 | BVP355 180LED RGBNW 220V L50 30 DMX | Yes | 911401747813 | BVP353 48LED 40K 220V L40 30 DMX | Yes |
| 911401750373 | BVP355 180LED 27K 220V L50 45 | No | 911401747823 | BVP353 48LED RGB 220V L40 30 DMX | Yes |
| 911401750383 | BVP355 180LED 30K 220V L50 45 | No | 911401747833 | BVP353 48LED RGBWW 220V L40 30 DMX | Yes |
| 911401750393 | BVP355 180LED 40K 220V L50 45 | No | 911401747843 | BVP353 48LED RGBNW 220V L40 30 DMX | Yes |
| 911401750403 | BVP355 180LED 27K 220V L50 45 DMX | Yes | 911401747853 | BVP353 48LED 27K 220V L40 45 | No |
| 911401750413 | BVP355 180LED 30K 220V L50 45 DMX | Yes | 911401747863 | BVP353 48LED 30K 220V L40 45 | No |
| 911401750423 | BVP355 180LED 40K 220V L50 45 DMX | Yes | 911401747873 | BVP353 48LED 40K 220V L40 45 | No |
| 911401750433 | BVP355 180LED RGB 220V L50 45 DMX | Yes | 911401747883 | BVP353 48LED 27K 220V L40 45 DMX | Yes |
| 911401750443 | BVP355 180LED RGBWW 220V L50 45 DMX | Yes | 911401747893 | BVP353 48LED 30K 220V L40 45 DMX | Yes |
| 911401750453 | BVP355 180LED RGBNW 220V L50 45 DMX | Yes | 911401747903 | BVP353 48LED 40K 220V L40 45 DMX | Yes |
| 911401747583 | BVP353 48LED 27K 220V L40 10 | No | 911401747913 | BVP353 48LED RGB 220V L40 45 DMX | Yes |
| 911401747593 | BVP353 48LED 30K 220V L40 10 | No | 911401747923 | BVP353 48LED RGBWW 220V L40 45 DMX | Yes |
| 911401747603 | BVP353 48LED 40K 220V L40 10 | No | 911401747933 | BVP353 48LED RGBNW 220V L40 45 DMX | Yes |

