



# Philips GreenPerform Highbay G5: a versatile LED highbay with optimized performance and future-proof control system

## GreenPerform Highbay G5

The GreenPerform Highbay G5 continues the GreenPerform family's enviable reputation for reliable performance. Not only does it deliver leading system efficacy and extended long-term quality, it also promises Unified Glare Rating (UGR) control with compact dimensions. GreenPerform Highbay G5 is also fully compatible with IoT software such as Interact, which is a scalable, future-proof control system. The family also has a series that supports cold room applications with 100% humidity and no condensation. All benefits that make this robust, optimized, and versatile family suitable for almost all industrial applications.

### Benefits

- Excellent energy savings
- Long-term quality and reliability
- Visual comfort
- Wide range of applications
- Connected ready for cloud-based IoT software applications

# GreenPerform Highbay G5

## Features

- 160 lm/W system efficacy
- 75,000 hours lifetime @Ta 35°
- Glare control (Narrow Beam), uniform illuminance (Wide Beam)
- Works seamlessly with the Interact IoT software and platform
- Cold room application support

## Application


- Manufacturing
- Warehouses
- Logistic center
- Exhibition hall

## Specifications

<b>Mounting type</b>	Suspended
	Pipe
	Surface
<b>Operating Temperature range</b>	-30 to +50 °C
<b>Light Source</b>	LED
<b>Mains Voltage</b>	220-240V / 50-60Hz
<b>Mains connection</b>	Flying cable
<b>Mechanical Accessories</b>	Hook for suspension
	Mounting bracket for surface
<b>Dimming</b>	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	Connected: Wireless control, compatible with SNH210 sensor
<b>Control system input</b>	DALI/Wireless
<b>Integrated sensors</b>	SNH210
<b>Material</b>	Housing: die-cast aluminium
<b>Main color of the luminaire</b>	RAL7012
<b>Flicker / Pst / SVM</b>	PSU: <30%
	PSD/Connected: <3.2%
<b>Luminous flux</b>	10klm-30klm
<b>Power consumption</b>	67W-205W









<b>Luminaire efficacy</b>	Up to 160lm/W
<b>Correlated color temperature - CCT</b>	4000K 6500K
<b>Color Rendering index - CRI</b>	80
<b>Beam angle</b>	WB: 85°
	NB: 55°
<b>Optical cover/lens material</b>	PC
<b>Optical cover/lens finish</b>	Clear
<b>Protection Class IEC61140</b>	Class I
<b>Mechanical impact protection</b>	IK08
<b>Ingress protection</b>	IP65
<b>Driver replaceable</b>	Yes
<b>UGR</b>	WB: 25
	NB: 22
<b>Installation</b>	Suspended
	Pipe
	Surface

## Dimensional drawing



# GreenPerform Highbay G5

## Dimensional drawing



# GreenPerform Highbay G5

Light Technical	
Optical cover type	Lens
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Approval and Application	
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

## General Information

Order Code	Full Product Name	Flammability	
		CE mark	mark
911401523991	BY698X G5 LED150/NW Connected WB GC	CE mark	-
911401524091	BY698X G5 LED150/NW Connected NB GC	CE mark	-
911401524191	BY698X G5 LED150/CW Connected WB GC	CE mark	-
911401524291	BY698X G5 LED150/CW Connected NB GC	CE mark	-
911401524391	BY698X G5 LED200/NW Connected WB GC	CE mark	-
911401524491	BY698X G5 LED200/NW Connected NB GC	CE mark	-
911401524591	BY698X G5 LED200/CW Connected WB GC	CE mark	-
911401524691	BY698X G5 LED200/CW Connected NB GC	CE mark	-
911401524791	BY698X G5 LED250/NW Connected WB GC	CE mark	-
911401524891	BY698X G5 LED250/NW Connected NB GC	CE mark	-
911401524991	BY698X G5 LED250/CW Connected WB GC	CE mark	-
911401525091	BY698X G5 LED250/CW Connected NB GC	CE mark	-
911401525191	BY698X G5 LED300/NW Connected WB GC	CE mark	-
911401525291	BY698X G5 LED300/NW Connected NB GC	CE mark	-
911401525391	BY698X G5 LED300/CW Connected WB GC	CE mark	-
911401525491	BY698X G5 LED300/CW Connected NB GC	CE mark	-
911401525991	BY698X G5 LED150/NW Connected WB GM	CE mark	-
911401526091	BY698X G5 LED150/NW Connected NB GM	CE mark	-

Order Code	Full Product Name	Flammability	
		CE mark	mark
911401526191	BY698X G5 LED150/CW Connected WB GM	CE mark	-
911401526291	BY698X G5 LED150/CW Connected NB GM	CE mark	-
911401526391	BY698X G5 LED200/NW Connected WB GM	CE mark	-
911401526491	BY698X G5 LED200/NW Connected NB GM	CE mark	-
911401526591	BY698X G5 LED200/CW Connected WB GM	CE mark	-
911401526691	BY698X G5 LED200/CW Connected NB GM	CE mark	-
911401526791	BY698X G5 LED250/NW Connected WB GM	CE mark	-
911401526891	BY698X G5 LED250/NW Connected NB GM	CE mark	-
911401526991	BY698X G5 LED250/CW Connected WB GM	CE mark	-
911401527091	BY698X G5 LED250/CW Connected NB GM	CE mark	-
911401527191	BY698X G5 LED300/NW Connected WB GM	CE mark	-
911401527291	BY698X G5 LED300/NW Connected NB GM	CE mark	-
911401527391	BY698X G5 LED300/CW Connected WB GM	CE mark	-
911401527491	BY698X G5 LED300/CW Connected NB GM	CE mark	-
911401528791	BY698X G5 LED200/840 Connected WB CAU	-	-
911401528991	BY698X G5 LED200/850 Connected WB CAU	-	-
911401529391	BY698X G5 LED250/840 Connected WB CAU	-	-
911401529591	BY698X G5 LED250/850 Connected WB CAU	-	-

# GreenPerform Highbay G5

Order Code	Full Product Name	Flammability	
		CE mark	mark
911401529991	BY698X G5 LED300/840 Connected WB CAU	-	-
911401530191	BY698X G5 LED300/850 Connected WB CAU	-	-
911401558791	BY698X G5 LED150/NW Connected WB LA	-	-
911401558891	BY698X G5 LED150/NW Connected NB LA	-	-
911401558991	BY698X G5 LED150/CW Connected WB LA	-	-
911401559091	BY698X G5 LED150/CW Connected NB LA	-	-
911401559191	BY698X G5 LED200/NW Connected WB LA	-	-
911401559291	BY698X G5 LED200/NW Connected NB LA	-	-
911401559391	BY698X G5 LED200/CW Connected WB LA	-	-
911401559491	BY698X G5 LED200/CW Connected NB LA	-	-
911401559591	BY698X G5 LED250/NW Connected WB LA	-	-
911401559691	BY698X G5 LED250/NW Connected NB LA	-	-
911401559791	BY698X G5 LED250/CW Connected WB LA	-	-
911401559891	BY698X G5 LED250/CW Connected NB LA	-	-
911401559991	BY698X G5 LED300/NW Connected WB LA	-	-
911401560091	BY698X G5 LED300/NW Connected NB LA	-	-
911401560191	BY698X G5 LED300/CW Connected WB LA	-	-
911401560291	BY698X G5 LED300/CW Connected NB LA	-	-
911401507891	BY698P G5 LED200/NW PSU WB GC	CE mark	-
911401507991	BY698P G5 LED200/NW PSU NB GC	CE mark	-
911401508091	BY698P G5 LED200/CW PSU WB GC	CE mark	-
911401508191	BY698P G5 LED200/CW PSU NB GC	CE mark	-
911401509891	BY698P G5 LED200/NW PSU WB GM	CE mark	-
911401509991	BY698P G5 LED200/NW PSU NB GM	CE mark	-
911401510091	BY698P G5 LED200/CW PSU WB GM	CE mark	-
911401510191	BY698P G5 LED200/CW PSU NB GM	CE mark	-
911401515691	BY698P G5 LED200/840 PSU WB CAU CL	-	-
911401515791	BY698P G5 LED200/850 PSU WB CAU CL	-	-
911401516591	BY698P G5 LED105/NW PSD WB GC	CE mark	-
911401516991	BY698P G5 LED150/NW PSD WB GC	CE mark	-
911401517191	BY698P G5 LED150/CW PSD WB GC	CE mark	-
911401517391	BY698P G5 LED200/NW PSD WB GC	CE mark	-
911401517491	BY698P G5 LED200/NW PSD NB GC	CE mark	-

Order Code	Full Product Name	Flammability	
		CE mark	mark
911401518591	BY698P G5 LED105/NW PSD WB GM	CE mark	-
911401518691	BY698P G5 LED105/NW PSD NB GM	CE mark	-
911401518991	BY698P G5 LED150/NW PSD WB GM	CE mark	-
911401519091	BY698P G5 LED150/NW PSD NB GM	CE mark	-
911401519391	BY698P G5 LED200/NW PSD WB GM	CE mark	-
911401519491	BY698P G5 LED200/NW PSD NB GM	CE mark	-
911401519591	BY698P G5 LED200/CW PSD WB GM	CE mark	-
911401533391	BY690P LED200/NW PSU WB GM	CE mark	-
911401533591	BY690P LED200/CW PSU WB GM	CE mark	-
911401534502	BY690P LED200/NW PSU WB KSA	CE mark	-
911401534602	BY690P LED200/NW PSU NB KSA	CE mark	-
911401534702	BY690P LED200/CW PSU WB KSA	CE mark	-
911401534802	BY690P LED200/CW PSU NB KSA	CE mark	-
911401555191	BY698P G5 LED200/NW PSU WB LA	-	-
911401555291	BY698P G5 LED200/NW PSU NB LA	-	-
911401555391	BY698P G5 LED200/CW PSU WB LA	-	-
9114015556591	BY698P G5 LED105/CW PSD WB LA	-	-
9114015557191	BY698P G5 LED200/NW PSD WB LA	-	-
9114015557391	BY698P G5 LED200/CW PSD WB LA	-	-
911401569891	BY698P G5 LED200/NW PSU WB GM L3m	CE mark	-
911401569991	BY698P G5 LED200/NW PSU NB GM L3m	CE mark	-
911401570091	BY698P G5 LED200/CW PSU WB GM L3m	CE mark	-
911401570191	BY698P G5 LED200/CW PSU NB GM L3m	CE mark	-
911401545502	BY698X G5 LED105/NW L1 W WB GC	-	For mounting on normally flammable surfaces
911401545602	BY698X G5 LED105/CW L1 W WB GC	-	For mounting on normally flammable surfaces
911401545702	BY698X G5 LED150/NW L1 W WB GC	-	For mounting on normally flammable surfaces
911401545802	BY698X G5 LED150/CW L1 W WB GC	-	For mounting on normally flammable surfaces
911401545902	BY698X G5 LED200/NW L1 W WB GC	-	For mounting on normally flammable surfaces
911401546002	BY698X G5 LED200/CW L1 W WB GC	-	For mounting on normally flammable surfaces
911401546102	BY698X G5 LED250/NW L1 W WB GC	-	For mounting on normally

## GreenPerform Highbay G5

Order Code	Full Product Name	CE mark	Flammability mark
			flammable surfaces
911401546202	BY698X G5 LED250/CW L1 W WB GC	-	For mounting on normally flammable surfaces
911401546302	BY698X G5 LED300/NW L1 W WB GC	-	For mounting on normally flammable surfaces
911401546402	BY698X G5 LED300/CW L1 W WB GC	-	For mounting on normally flammable surfaces
911401546502	BY698X G5 LED105/NW L1 W WB GM	CE mark	For mounting on normally flammable surfaces
911401546602	BY698X G5 LED105/CW L1 W WB GM	CE mark	For mounting on normally flammable surfaces
911401546702	BY698X G5 LED150/NW L1 W WB GM	CE mark	For mounting on normally flammable surfaces
911401546802	BY698X G5 LED150/CW L1 W WB GM	CE mark	For mounting on normally flammable surfaces
911401546902	BY698X G5 LED200/NW L1 W WB GM	CE mark	For mounting on normally flammable surfaces
911401547002	BY698X G5 LED200/CW L1 W WB GM	CE mark	For mounting on normally flammable surfaces
911401547102	BY698X G5 LED250/NW L1 W WB GM	CE mark	For mounting on normally flammable surfaces
911401547202	BY698X G5 LED250/CW L1 W WB GM	CE mark	For mounting on normally flammable surfaces
911401547302	BY698X G5 LED300/NW L1 W WB GM	CE mark	For mounting on normally flammable surfaces

Order Code	Full Product Name	CE mark	Flammability mark
911401547402	BY698X G5 LED300/CW L1 W WB GM	CE mark	For mounting on normally flammable surfaces
911401547502	BY698X G5 LED105/840 L1 W WB CAU	CE mark	For mounting on normally flammable surfaces
911401547602	BY698X G5 LED150/840 L1 W WB CAU	CE mark	For mounting on normally flammable surfaces
911401547702	BY698X G5 LED200/840 L1 W WB CAU	CE mark	For mounting on normally flammable surfaces
911401547802	BY698X G5 LED250/840 L1 W WB CAU	CE mark	For mounting on normally flammable surfaces
911401547902	BY698X G5 LED300/840 L1 W WB CAU	CE mark	For mounting on normally flammable surfaces
911401548002	BY698X G5 LED105/NW L1 W WB GM L3m	CE mark	For mounting on normally flammable surfaces
911401548102	BY698X G5 LED105/CW L1 W WB GM L3m	CE mark	For mounting on normally flammable surfaces
911401548202	BY698X G5 LED150/NW L1 W WB GM L3m	CE mark	For mounting on normally flammable surfaces
911401548302	BY698X G5 LED150/CW L1 W WB GM L3m	CE mark	For mounting on normally flammable surfaces
911401548402	BY698X G5 LED200/NW L1 W WB GM L3m	CE mark	For mounting on normally flammable surfaces
911401548502	BY698X G5 LED200/CW L1 W WB GM L3m	CE mark	For mounting on normally flammable surfaces
911401548602	BY698X G5 LED250/NW L1 W WB GM L3m	CE mark	For mounting on normally flammable surfaces

# GreenPerform Highbay G5

Order Code	Full Product Name	CE mark	Flammability	
			mark	
			flammable	
			surfaces	
911401548702	BY698X G5 LED250/CW L1 W WB GM L3m	CE mark	For mounting on normally flammable surfaces	
911401548802	BY698X G5 LED300/NW L1 W WB GM L3m	CE mark	For mounting on normally flammable surfaces	
911401548902	BY698X G5 LED300/CW L1 W WB GM L3m	CE mark	For mounting on normally flammable surfaces	
911401507091	BY698P G5 LED105/NW PSU WB GC	CE mark	-	
911401507191	BY698P G5 LED105/NW PSU NB GC	CE mark	-	
911401507291	BY698P G5 LED105/CW PSU WB GC	CE mark	-	
911401507391	BY698P G5 LED105/CW PSU NB GC	CE mark	-	
911401507491	BY698P G5 LED150/NW PSU WB GC	CE mark	-	
911401507591	BY698P G5 LED150/NW PSU NB GC	CE mark	-	
911401507691	BY698P G5 LED150/CW PSU WB GC	CE mark	-	
911401507791	BY698P G5 LED150/CW PSU NB GC	CE mark	-	
911401509091	BY698P G5 LED105/NW PSU WB GM	CE mark	-	
911401509291	BY698P G5 LED105/CW PSU WB GM	CE mark	-	
911401509391	BY698P G5 LED105/CW PSU NB GM	CE mark	-	
911401509491	BY698P G5 LED150/NW PSU WB GM	CE mark	-	
911401509591	BY698P G5 LED150/NW PSU NB GM	CE mark	-	
911401509691	BY698P G5 LED150/CW PSU WB GM	CE mark	-	
911401509791	BY698P G5 LED150/CW PSU NB GM	CE mark	-	
911401530991	BY690P LED150/NW PSU WB GC	CE mark	-	
911401532991	BY690P LED150/NW PSU WB GM	CE mark	-	
911401533702	BY690P LED105/NW PSU WB KSA	CE mark	-	
911401533802	BY690P LED105/NW PSU NB KSA	CE mark	-	
911401533902	BY690P LED105/CW PSU WB KSA	CE mark	-	
911401534002	BY690P LED105/CW PSU NB KSA	CE mark	-	
911401534102	BY690P LED150/NW PSU WB KSA	CE mark	-	
911401534202	BY690P LED150/NW PSU NB KSA	CE mark	-	
911401534302	BY690P LED150/CW PSU WB KSA	CE mark	-	
911401534402	BY690P LED150/CW PSU NB KSA	CE mark	-	
911401554391	BY698P G5 LED105/NW PSU WB LA	-	-	
911401554591	BY698P G5 LED105/CW PSU WB LA	-	-	
911401554791	BY698P G5 LED150/NW PSU WB LA	-	-	
911401554991	BY698P G5 LED150/CW PSU WB LA	-	-	
911401569091	BY698P G5 LED105/NW PSU WB GM L3m	CE mark	-	
911401569291	BY698P G5 LED105/CW PSU WB GM L3m	CE mark	-	
911401569491	BY698P G5 LED150/NW PSU WB GM L3m	CE mark	-	
911401569691	BY698P G5 LED150/CW PSU WB GM L3m	CE mark	-	
911401508291	BY698P G5 LED250/NW PSU WB GC	CE mark	-	
911401508391	BY698P G5 LED250/NW PSU NB GC	CE mark	-	
911401508491	BY698P G5 LED250/CW PSU WB GC	CE mark	-	
911401508591	BY698P G5 LED250/CW PSU NB GC	CE mark	-	

Order Code	Full Product Name	CE mark	Flammability	
			mark	
911401508691	BY698P G5 LED300/NW PSU WB GC	CE mark	-	
911401508791	BY698P G5 LED300/NW PSU NB GC	CE mark	-	
911401508891	BY698P G5 LED300/CW PSU WB GC	CE mark	-	
911401508991	BY698P G5 LED300/CW PSU NB GC	CE mark	-	
911401510291	BY698P G5 LED250/NW PSU WB GM	CE mark	-	
911401510391	BY698P G5 LED250/NW PSU NB GM	CE mark	-	
911401510491	BY698P G5 LED250/CW PSU WB GM	CE mark	-	
911401510591	BY698P G5 LED250/CW PSU NB GM	CE mark	-	
911401510691	BY698P G5 LED300/NW PSU WB GM	CE mark	-	
911401510791	BY698P G5 LED300/NW PSU NB GM	CE mark	-	
911401510891	BY698P G5 LED300/CW PSU WB GM	CE mark	-	
911401510991	BY698P G5 LED300/CW PSU NB GM	CE mark	-	
911401513891	BY698P G5 LED250/840 PSU WB CAU	-	-	
911401514091	BY698P G5 LED250/850 PSU WB CAU	-	-	
911401514491	BY698P G5 LED300/840 PSU WB CAU	-	-	
911401514691	BY698P G5 LED300/850 PSU WB CAU	-	-	
911401515991	BY698P G5 LED250/840 PSU WB CAU CL	-	-	
911401516091	BY698P G5 LED250/850 PSU WB CAU CL	-	-	
911401516291	BY698P G5 LED300/840 PSU WB CAU CL	-	-	
911401516391	BY698P G5 LED300/850 PSU WB CAU CL	-	-	
911401517791	BY698P G5 LED250/NW PSD WB GC	CE mark	-	
911401517891	BY698P G5 LED250/NW PSD NB GC	CE mark	-	
911401517991	BY698P G5 LED250/CW PSD WB GC	CE mark	-	
911401518091	BY698P G5 LED250/CW PSD NB GC	CE mark	-	
911401518191	BY698P G5 LED300/NW PSD WB GC	CE mark	-	
911401518291	BY698P G5 LED300/NW PSD NB GC	CE mark	-	
911401518391	BY698P G5 LED300/CW PSD WB GC	CE mark	-	
911401518491	BY698P G5 LED300/CW PSD NB GC	CE mark	-	
911401519791	BY698P G5 LED250/NW PSD WB GM	CE mark	-	
911401519891	BY698P G5 LED250/NW PSD NB GM	CE mark	-	
911401519991	BY698P G5 LED250/CW PSD WB GM	CE mark	-	
911401520091	BY698P G5 LED250/CW PSD NB GM	CE mark	-	
911401520191	BY698P G5 LED300/NW PSD WB GM	CE mark	-	
911401520291	BY698P G5 LED300/NW PSD NB GM	CE mark	-	
911401520391	BY698P G5 LED300/CW PSD WB GM	CE mark	-	
911401520491	BY698P G5 LED300/CW PSD NB GM	CE mark	-	
911401522391	BY698P G5 LED250/840 PSD WB CAU	-	-	
911401522591	BY698P G5 LED250/850 PSD WB CAU	-	-	
911401522991	BY698P G5 LED300/840 PSD WB CAU	-	-	
911401523191	BY698P G5 LED300/850 PSD WB CAU	-	-	
911401531791	BY690P LED250/NW PSU WB GC	CE mark	-	
911401531891	BY690P LED250/NW PSU NB GC	CE mark	-	
911401531991	BY690P LED250/CW PSU WB GC	CE mark	-	
911401532091	BY690P LED250/CW PSU NB GC	CE mark	-	
911401532191	BY690P LED300/NW PSU WB GC	CE mark	-	
911401532291	BY690P LED300/NW PSU NB GC	CE mark	-	
911401532391	BY690P LED300/CW PSU WB GC	CE mark	-	
911401532491	BY690P LED300/CW PSU NB GC	CE mark	-	
911401533791	BY690P LED250/NW PSU WB GM	CE mark	-	
911401533891	BY690P LED250/NW PSU NB GM	CE mark	-	
911401533991	BY690P LED250/CW PSU WB GM	CE mark	-	

# GreenPerform Highbay G5

Order Code	Full Product Name	Flammability	
		CE mark	mark
911401534091	BY690P LED250/CW PSU NB GM	CE mark	-
911401534191	BY690P LED300/NW PSU WB GM	CE mark	-
911401534291	BY690P LED300/NW PSU NB GM	CE mark	-
911401534391	BY690P LED300/CW PSU WB GM	CE mark	-
911401534491	BY690P LED300/CW PSU NB GM	CE mark	-
911401534902	BY690P LED250/NW PSU WB KSA	CE mark	-
911401535002	BY690P LED250/NW PSU NB KSA	CE mark	-
911401535102	BY690P LED250/CW PSU WB KSA	CE mark	-
911401535202	BY690P LED250/CW PSU NB KSA	CE mark	-
911401535302	BY690P LED300/NW PSU WB KSA	CE mark	-
911401535402	BY690P LED300/NW PSU NB KSA	CE mark	-
911401535502	BY690P LED300/CW PSU WB KSA	CE mark	-
911401535602	BY690P LED300/CW PSU NB KSA	CE mark	-
911401555591	BY698P G5 LED250/NW PSU WB LA	-	-
911401555691	BY698P G5 LED250/NW PSU NB LA	-	-
911401555791	BY698P G5 LED250/CW PSU WB LA	-	-
911401555891	BY698P G5 LED250/CW PSU NB LA	-	-
911401555991	BY698P G5 LED300/NW PSU WB LA	-	-
911401556091	BY698P G5 LED300/NW PSU NB LA	-	-
911401556191	BY698P G5 LED300/CW PSU WB LA	-	-

Order Code	Full Product Name	Flammability	
		CE mark	mark
911401556291	BY698P G5 LED300/CW PSU NB LA	-	-
911401557591	BY698P G5 LED250/NW PSD WB LA	-	-
911401557691	BY698P G5 LED250/NW PSD NB LA	-	-
911401557791	BY698P G5 LED250/CW PSD WB LA	-	-
911401557891	BY698P G5 LED250/CW PSD NB LA	-	-
911401557991	BY698P G5 LED300/NW PSD WB LA	-	-
911401558091	BY698P G5 LED300/NW PSD NB LA	-	-
911401558191	BY698P G5 LED300/CW PSD WB LA	-	-
911401558291	BY698P G5 LED300/CW PSD NB LA	-	-
911401570291	BY698P G5 LED250/NW PSU WB GM L3m	CE mark	-
911401570391	BY698P G5 LED250/NW PSU NB GM L3m	CE mark	-
911401570491	BY698P G5 LED250/CW PSU WB GM L3m	CE mark	-
911401570591	BY698P G5 LED250/CW PSU NB GM L3m	CE mark	-
911401570691	BY698P G5 LED300/NW PSU WB GM L3m	CE mark	-
911401570791	BY698P G5 LED300/NW PSU NB GM L3m	CE mark	-
911401570891	BY698P G5 LED300/CW PSU WB GM L3m	CE mark	-
911401570991	BY698P G5 LED300/CW PSU NB GM L3m	CE mark	-

## Light Technical

Order Code	Full Product Name	Correlated Color	Color rendering index	Luminous Efficacy (rated)	Luminous Flux
		Temperature (Nom)	(CRI)	(Nom)	(Nom)
911401523991	BY698X G5 LED150/NW Connected WB GC	4000 K	80	150 lm/W	15,000 lm
911401524091	BY698X G5 LED150/NW Connected NB GC	4000 K	80	150 lm/W	15,000 lm
911401524191	BY698X G5 LED150/CW Connected WB GC	6500 K	80	150 lm/W	15,000 lm
911401524291	BY698X G5 LED150/CW Connected NB GC	6500 K	80	150 lm/W	15,000 lm
911401524391	BY698X G5 LED200/NW Connected WB GC	4000 K	80	150 lm/W	20,000 lm
911401524491	BY698X G5 LED200/NW Connected NB GC	4000 K	80	150 lm/W	20,000 lm
911401524591	BY698X G5 LED200/CW	6500 K	80	150 lm/W	20,000 lm

Order Code	Full Product Name	Correlated Color	Color rendering index	Luminous Efficacy (rated)	Luminous Flux
		Temperature (Nom)	(CRI)	(Nom)	(Nom)
911401524691	BY698X G5 LED200/CW Connected NB GC	6500 K	80	150 lm/W	20,000 lm
911401524791	BY698X G5 LED250/NW Connected WB GC	4000 K	80	150 lm/W	25,000 lm
911401524891	BY698X G5 LED250/NW Connected NB GC	4000 K	80	150 lm/W	25,000 lm
911401524991	BY698X G5 LED250/CW Connected WB GC	6500 K	80	150 lm/W	25,000 lm
911401525091	BY698X G5 LED250/CW Connected NB GC	6500 K	80	150 lm/W	25,000 lm
911401525191	BY698X G5 LED300/NW Connected WB GC	4000 K	80	150 lm/W	30,000 lm



# GreenPerform Highbay G5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401525291	BY698X G5 LED300/NW Connected NB GC	4000 K	80	150 lm/W	30,000 lm
911401525391	BY698X G5 LED300/CW Connected WB GC	6500 K	80	150 lm/W	30,000 lm
911401525491	BY698X G5 LED300/CW Connected NB GC	6500 K	80	150 lm/W	30,000 lm
911401525991	BY698X G5 LED150/NW Connected WB GM	4000 K	80	150 lm/W	15,000 lm
911401526091	BY698X G5 LED150/NW Connected NB GM	4000 K	80	150 lm/W	15,000 lm
911401526191	BY698X G5 LED150/CW Connected WB GM	6500 K	80	150 lm/W	15,000 lm
911401526291	BY698X G5 LED150/CW Connected NB GM	6500 K	80	150 lm/W	15,000 lm
911401526391	BY698X G5 LED200/NW Connected WB GM	4000 K	80	150 lm/W	20,000 lm
911401526491	BY698X G5 LED200/NW Connected NB GM	4000 K	80	150 lm/W	20,000 lm
911401526591	BY698X G5 LED200/CW Connected WB GM	6500 K	80	150 lm/W	20,000 lm
911401526691	BY698X G5 LED200/CW Connected NB GM	6500 K	80	150 lm/W	20,000 lm
911401526791	BY698X G5 LED250/NW Connected WB GM	4000 K	80	150 lm/W	25,000 lm
911401526891	BY698X G5 LED250/NW	4000 K	80	150 lm/W	25,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	Connected NB GM				
911401526991	BY698X G5 LED250/CW Connected WB GM	6500 K	80	150 lm/W	25,000 lm
911401527091	BY698X G5 LED250/CW Connected NB GM	6500 K	80	150 lm/W	25,000 lm
911401527191	BY698X G5 LED300/NW Connected WB GM	4000 K	80	150 lm/W	30,000 lm
911401527291	BY698X G5 LED300/NW Connected NB GM	4000 K	80	150 lm/W	30,000 lm
911401527391	BY698X G5 LED300/CW Connected WB GM	6500 K	80	150 lm/W	30,000 lm
911401527491	BY698X G5 LED300/CW Connected NB GM	6500 K	80	150 lm/W	30,000 lm
91140152791	BY698X G5 LED200/840 Connected WB CAU	4000 K	80	150 lm/W	20,000 lm
911401528991	BY698X G5 LED200/850 Connected WB CAU	5000 K	80	150 lm/W	20,000 lm
911401529391	BY698X G5 LED250/840 Connected WB CAU	4000 K	80	150 lm/W	25,000 lm
911401529591	BY698X G5 LED250/850 Connected WB CAU	5000 K	80	150 lm/W	25,000 lm
911401529991	BY698X G5 LED300/840 Connected WB CAU	4000 K	80	150 lm/W	30,000 lm
911401530191	BY698X G5 LED300/850	5000 K	80	150 lm/W	30,000 lm

## GreenPerform Highbay G5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	Connected WB CAU				
911401558791	BY698X G5 LED150/NW Connected WB LA	4000 K	80	150 lm/W	15,000 lm
911401558891	BY698X G5 LED150/NW Connected NB LA	4000 K	80	150 lm/W	15,000 lm
911401558991	BY698X G5 LED150/CW Connected WB LA	6500 K	80	150 lm/W	15,000 lm
911401559091	BY698X G5 LED150/CW Connected NB LA	6500 K	80	150 lm/W	15,000 lm
911401559191	BY698X G5 LED200/NW Connected WB LA	4000 K	80	150 lm/W	20,000 lm
911401559291	BY698X G5 LED200/NW Connected NB LA	4000 K	80	150 lm/W	20,000 lm
911401559391	BY698X G5 LED200/CW Connected WB LA	6500 K	80	150 lm/W	20,000 lm
911401559491	BY698X G5 LED200/CW Connected NB LA	6500 K	80	150 lm/W	20,000 lm
911401559591	BY698X G5 LED250/NW Connected WB LA	4000 K	80	150 lm/W	25,000 lm
911401559691	BY698X G5 LED250/NW Connected NB LA	4000 K	80	150 lm/W	25,000 lm
911401559791	BY698X G5 LED250/CW Connected WB LA	6500 K	80	150 lm/W	25,000 lm
911401559891	BY698X G5 LED250/CW Connected NB LA	6500 K	80	150 lm/W	25,000 lm
911401559991	BY698X G5 LED300/NW Connected WB LA	4000 K	80	150 lm/W	30,000 lm
911401560091	BY698X G5 LED300/NW Connected NB LA	4000 K	80	150 lm/W	30,000 lm
911401560191	BY698X G5 LED300/CW Connected WB LA	6500 K	80	150 lm/W	30,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401560291	BY698X G5 LED300/CW Connected NB LA	6500 K	80	150 lm/W	30,000 lm
911401507891	BY698P G5 LED200/NW PSU WB GC	4000 K	80	160 lm/W	20,000 lm
911401507991	BY698P G5 LED200/NW PSU NB GC	4000 K	80	160 lm/W	20,000 lm
911401508091	BY698P G5 LED200/CW PSU WB GC	6500 K	80	160 lm/W	20,000 lm
911401508191	BY698P G5 LED200/CW PSU NB GC	6500 K	80	160 lm/W	20,000 lm
911401509891	BY698P G5 LED200/NW PSU WB GM	4000 K	80	160 lm/W	20,000 lm
911401509991	BY698P G5 LED200/NW PSU NB GM	4000 K	80	160 lm/W	20,000 lm
911401510091	BY698P G5 LED200/CW PSU WB GM	6500 K	80	160 lm/W	20,000 lm
911401510191	BY698P G5 LED200/CW PSU NB GM	6500 K	80	160 lm/W	20,000 lm
911401515691	BY698P G5 LED200/840 PSU WB CAU CL	4000 K	80	160 lm/W	20,000 lm
911401515791	BY698P G5 LED200/850 PSU WB CAU CL	5000 K	80	160 lm/W	20,000 lm
911401516591	BY698P G5 LED105/NW PSD WB GC	4000 K	80	150 lm/W	10,500 lm
911401516991	BY698P G5 LED150/NW PSD WB GC	4000 K	80	150 lm/W	15,000 lm
911401517191	BY698P G5 LED150/CW PSD WB GC	6500 K	80	150 lm/W	15,000 lm
911401517391	BY698P G5 LED200/NW PSD WB GC	4000 K	80	150 lm/W	20,000 lm
911401517491	BY698P G5 LED200/NW PSD NB GC	4000 K	80	150 lm/W	20,000 lm

## GreenPerform Highbay G5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401518591	BY698P G5 LED105/NW PSD WB GM	4000 K	80	150 lm/W	10,500 lm
911401518691	BY698P G5 LED105/NW PSD NB GM	4000 K	80	150 lm/W	10,500 lm
911401518991	BY698P G5 LED150/NW PSD WB GM	4000 K	80	150 lm/W	15,000 lm
911401519091	BY698P G5 LED150/NW PSD NB GM	4000 K	80	150 lm/W	15,000 lm
911401519391	BY698P G5 LED200/NW PSD WB GM	4000 K	80	150 lm/W	20,000 lm
911401519491	BY698P G5 LED200/NW PSD NB GM	4000 K	80	150 lm/W	20,000 lm
911401519591	BY698P G5 LED200/CW PSD WB GM	6500 K	80	150 lm/W	20,000 lm
911401533391	BY690P LED200/NW PSU WB GM	4000 K	>80	160 lm/W	20,000 lm
911401533591	BY690P LED200/CW PSU WB GM	6500 K	>80	160 lm/W	20,000 lm
911401534502	BY690P LED200/NW PSU WB KSA	4000 K	>80	160 lm/W	20,000 lm
911401534602	BY690P LED200/NW PSU NB KSA	4000 K	>80	160 lm/W	20,000 lm
911401534702	BY690P LED200/CW PSU WB KSA	6500 K	>80	160 lm/W	20,000 lm
911401534802	BY690P LED200/CW PSU NB KSA	6500 K	>80	160 lm/W	20,000 lm
911401555191	BY698P G5 LED200/NW PSU WB LA	4000 K	80	160 lm/W	20,000 lm
911401555291	BY698P G5 LED200/NW PSU NB LA	4000 K	80	160 lm/W	20,000 lm
911401555391	BY698P G5 LED200/CW PSU WB LA	6500 K	80	160 lm/W	20,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401556591	BY698P G5 LED105/CW PSD WB LA	6500 K	80	150 lm/W	10,500 lm
911401557191	BY698P G5 LED200/NW PSD WB LA	4000 K	80	150 lm/W	20,000 lm
911401557391	BY698P G5 LED200/CW PSD WB LA	6500 K	80	150 lm/W	20,000 lm
911401569891	BY698P G5 LED200/NW PSU WB GM L3m	4000 K	80	160 lm/W	20,000 lm
911401569991	BY698P G5 LED200/NW PSU NB GM L3m	4000 K	80	160 lm/W	20,000 lm
911401570091	BY698P G5 LED200/CW PSU WB GM L3m	6500 K	80	160 lm/W	20,000 lm
911401570191	BY698P G5 LED200/CW PSU NB GM L3m	6500 K	80	160 lm/W	20,000 lm
911401545502	BY698X G5 LED105/NW L1 W WB GC	4000 K	>80	160 lm/W	10,500 lm
911401545602	BY698X G5 LED105/CW L1 W WB GC	6500 K	>80	160 lm/W	10,500 lm
911401545702	BY698X G5 LED150/NW L1 W WB GC	4000 K	>80	160 lm/W	15,000 lm
911401545802	BY698X G5 LED150/CW L1 W WB GC	6500 K	>80	160 lm/W	15,000 lm
911401545902	BY698X G5 LED200/NW L1 W WB GC	4000 K	>80	160 lm/W	20,000 lm
911401546002	BY698X G5 LED200/CW L1 W WB GC	6500 K	>80	160 lm/W	20,000 lm
911401546102	BY698X G5 LED250/NW L1 W WB GC	4000 K	>80	160 lm/W	25,000 lm
911401546202	BY698X G5 LED250/CW L1 W WB GC	6500 K	>80	160 lm/W	25,000 lm
911401546302	BY698X G5 LED300/NW L1 W WB GC	4000 K	>80	160 lm/W	30,000 lm

## GreenPerform Highbay G5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401546402	BY698X G5 LED300/CW L1 W WB GC	6500 K	>80	160 lm/W	30,000 lm
911401546502	BY698X G5 LED105/NW L1 W WB GM	4000 K	>80	160 lm/W	10,500 lm
911401546602	BY698X G5 LED105/CW L1 W WB GM	6500 K	>80	160 lm/W	10,500 lm
911401546702	BY698X G5 LED150/NW L1 W WB GM	4000 K	>80	160 lm/W	15,000 lm
911401546802	BY698X G5 LED150/CW L1 W WB GM	6500 K	>80	160 lm/W	15,000 lm
911401546902	BY698X G5 LED200/NW L1 W WB GM	4000 K	>80	160 lm/W	20,000 lm
911401547002	BY698X G5 LED200/CW L1 W WB GM	6500 K	>80	160 lm/W	20,000 lm
911401547102	BY698X G5 LED250/NW L1 W WB GM	4000 K	>80	160 lm/W	25,000 lm
911401547202	BY698X G5 LED250/CW L1 W WB GM	6500 K	>80	160 lm/W	25,000 lm
911401547302	BY698X G5 LED300/NW L1 W WB GM	4000 K	>80	160 lm/W	30,000 lm
911401547402	BY698X G5 LED300/CW L1 W WB GM	6500 K	>80	160 lm/W	30,000 lm
911401547502	BY698X G5 LED105/840 L1 W WB CAU	4000 K	>80	160 lm/W	10,500 lm
911401547602	BY698X G5 LED150/840 L1 W WB CAU	4000 K	>80	160 lm/W	15,000 lm
911401547702	BY698X G5 LED200/840 L1 W WB CAU	4000 K	>80	160 lm/W	20,000 lm
911401547802	BY698X G5 LED250/840 L1 W WB CAU	4000 K	>80	160 lm/W	25,000 lm
911401547902	BY698X G5 LED300/840 L1 W WB CAU	4000 K	>80	160 lm/W	30,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401548002	BY698X G5 LED105/NW L1 W WB GM L3m	4000 K	>80	160 lm/W	10,500 lm
911401548102	BY698X G5 LED105/CW L1 W WB GM L3m	6500 K	>80	160 lm/W	10,500 lm
911401548202	BY698X G5 LED150/NW L1 W WB GM L3m	4000 K	>80	160 lm/W	15,000 lm
911401548302	BY698X G5 LED150/CW L1 W WB GM L3m	6500 K	>80	160 lm/W	15,000 lm
911401548402	BY698X G5 LED200/NW L1 W WB GM L3m	4000 K	>80	160 lm/W	20,000 lm
911401548502	BY698X G5 LED200/CW L1 W WB GM L3m	6500 K	>80	160 lm/W	20,000 lm
911401548602	BY698X G5 LED250/NW L1 W WB GM L3m	4000 K	>80	160 lm/W	25,000 lm
911401548702	BY698X G5 LED250/CW L1 W WB GM L3m	6500 K	>80	160 lm/W	25,000 lm
911401548802	BY698X G5 LED300/NW L1 W WB GM L3m	4000 K	>80	160 lm/W	30,000 lm
911401548902	BY698X G5 LED300/CW L1 W WB GM L3m	6500 K	>80	160 lm/W	30,000 lm
911401507091	BY698P G5 LED105/NW PSU WB GC	4000 K	80	160 lm/W	10,500 lm
911401507191	BY698P G5 LED105/NW PSU NB GC	4000 K	80	160 lm/W	10,500 lm
911401507291	BY698P G5 LED105/CW PSU WB GC	6500 K	80	160 lm/W	10,500 lm
911401507391	BY698P G5 LED105/CW PSU NB GC	6500 K	80	160 lm/W	10,500 lm
911401507491	BY698P G5 LED150/NW PSU WB GC	4000 K	80	160 lm/W	15,000 lm
911401507591	BY698P G5 LED150/NW PSU NB GC	4000 K	80	160 lm/W	15,000 lm

## GreenPerform Highbay G5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401507691	BY698P G5 LED150/CW PSU WB GC	6500 K	80	160 lm/W	15,000 lm
911401507791	BY698P G5 LED150/CW PSU NB GC	6500 K	80	160 lm/W	15,000 lm
911401509091	BY698P G5 LED105/NW PSU WB GM	4000 K	80	160 lm/W	10,500 lm
911401509291	BY698P G5 LED105/CW PSU WB GM	6500 K	80	160 lm/W	10,500 lm
911401509391	BY698P G5 LED105/CW PSU NB GM	6500 K	80	160 lm/W	10,500 lm
911401509491	BY698P G5 LED150/NW PSU WB GM	4000 K	80	160 lm/W	15,000 lm
911401509591	BY698P G5 LED150/NW PSU NB GM	4000 K	80	160 lm/W	15,000 lm
911401509691	BY698P G5 LED150/CW PSU WB GM	6500 K	80	160 lm/W	15,000 lm
911401509791	BY698P G5 LED150/CW PSU NB GM	6500 K	80	160 lm/W	15,000 lm
911401530991	BY690P LED150/NW PSU WB GC	4000 K	>80	160 lm/W	15,000 lm
911401532991	BY690P LED150/NW PSU WB GM	4000 K	>80	160 lm/W	15,000 lm
911401533702	BY690P LED105/NW PSU WB KSA	4000 K	>80	160 lm/W	10,500 lm
911401533802	BY690P LED105/NW PSU NB KSA	4000 K	>80	160 lm/W	10,500 lm
911401533902	BY690P LED105/CW PSU WB KSA	6500 K	>80	160 lm/W	10,500 lm
911401534002	BY690P LED105/CW PSU NB KSA	6500 K	>80	160 lm/W	10,500 lm
911401534102	BY690P LED150/NW PSU WB KSA	4000 K	>80	160 lm/W	15,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401534202	BY690P LED150/NW PSU NB KSA	4000 K	>80	160 lm/W	15,000 lm
911401534302	BY690P LED150/CW PSU WB KSA	6500 K	>80	160 lm/W	15,000 lm
911401534402	BY690P LED150/CW PSU NB KSA	6500 K	>80	160 lm/W	15,000 lm
911401554391	BY698P G5 LED105/NW PSU WB LA	4000 K	80	160 lm/W	10,500 lm
911401554591	BY698P G5 LED105/CW PSU WB LA	6500 K	80	160 lm/W	10,500 lm
911401554791	BY698P G5 LED150/NW PSU WB LA	4000 K	80	160 lm/W	15,000 lm
911401554991	BY698P G5 LED150/CW PSU WB LA	6500 K	80	160 lm/W	15,000 lm
911401569091	BY698P G5 LED105/NW PSU WB GM L3m	4000 K	80	160 lm/W	10,500 lm
911401569291	BY698P G5 LED105/CW PSU WB GM L3m	6500 K	80	160 lm/W	10,500 lm
911401569491	BY698P G5 LED150/NW PSU WB GM L3m	4000 K	80	160 lm/W	15,000 lm
911401569691	BY698P G5 LED150/CW PSU WB GM L3m	6500 K	80	160 lm/W	15,000 lm
911401508291	BY698P G5 LED250/NW PSU WB GC	4000 K	80	160 lm/W	25,000 lm
911401508391	BY698P G5 LED250/NW PSU NB GC	4000 K	80	160 lm/W	25,000 lm
911401508491	BY698P G5 LED250/CW PSU WB GC	6500 K	80	160 lm/W	25,000 lm
911401508591	BY698P G5 LED250/CW PSU NB GC	6500 K	80	160 lm/W	25,000 lm
911401508691	BY698P G5 LED300/NW PSU WB GC	4000 K	80	160 lm/W	30,000 lm

## GreenPerform Highbay G5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401508791	BY698P G5 LED300/NW PSU NB GC	4000 K	80	160 lm/W	30,000 lm
911401508891	BY698P G5 LED300/CW PSU WB GC	6500 K	80	160 lm/W	30,000 lm
911401508991	BY698P G5 LED300/CW PSU NB GC	6500 K	80	160 lm/W	30,000 lm
911401510291	BY698P G5 LED250/NW PSU WB GM	4000 K	80	160 lm/W	25,000 lm
911401510391	BY698P G5 LED250/NW PSU NB GM	4000 K	80	160 lm/W	25,000 lm
911401510491	BY698P G5 LED250/CW PSU WB GM	6500 K	80	160 lm/W	25,000 lm
911401510591	BY698P G5 LED250/CW PSU NB GM	6500 K	80	160 lm/W	25,000 lm
911401510691	BY698P G5 LED300/NW PSU WB GM	4000 K	80	160 lm/W	30,000 lm
911401510791	BY698P G5 LED300/NW PSU NB GM	4000 K	80	160 lm/W	30,000 lm
911401510891	BY698P G5 LED300/CW PSU WB GM	6500 K	80	160 lm/W	30,000 lm
911401510991	BY698P G5 LED300/CW PSU NB GM	6500 K	80	160 lm/W	30,000 lm
911401513891	BY698P G5 LED250/840 PSU WB CAU	4000 K	80	160 lm/W	25,000 lm
911401514091	BY698P G5 LED250/850 PSU WB CAU	5000 K	80	160 lm/W	25,000 lm
911401514491	BY698P G5 LED300/840 PSU WB CAU	4000 K	80	160 lm/W	30,000 lm
911401514691	BY698P G5 LED300/850 PSU WB CAU	5000 K	80	160 lm/W	30,000 lm
911401515991	BY698P G5 LED250/840 PSU WB CAU CL	4000 K	80	160 lm/W	25,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401516091	BY698P G5 LED250/850 PSU WB CAU CL	5000 K	80	160 lm/W	25,000 lm
911401516291	BY698P G5 LED300/840 PSU WB CAU CL	4000 K	80	160 lm/W	30,000 lm
911401516391	BY698P G5 LED300/850 PSU WB CAU CL	5000 K	80	160 lm/W	30,000 lm
911401517791	BY698P G5 LED250/NW PSD WB GC	4000 K	80	150 lm/W	25,000 lm
911401517891	BY698P G5 LED250/NW PSD NB GC	4000 K	80	150 lm/W	25,000 lm
911401517991	BY698P G5 LED250/CW PSD WB GC	6500 K	80	150 lm/W	25,000 lm
911401518091	BY698P G5 LED250/CW PSD NB GC	6500 K	80	150 lm/W	25,000 lm
911401518191	BY698P G5 LED300/NW PSD WB GC	4000 K	80	150 lm/W	30,000 lm
911401518291	BY698P G5 LED300/NW PSD NB GC	4000 K	80	150 lm/W	30,000 lm
911401518391	BY698P G5 LED300/CW PSD WB GC	6500 K	80	150 lm/W	30,000 lm
911401518491	BY698P G5 LED300/CW PSD NB GC	6500 K	80	150 lm/W	30,000 lm
911401519791	BY698P G5 LED250/NW PSD WB GM	4000 K	80	150 lm/W	25,000 lm
911401519891	BY698P G5 LED250/NW PSD NB GM	4000 K	80	150 lm/W	25,000 lm
911401519991	BY698P G5 LED250/CW PSD WB GM	6500 K	80	150 lm/W	25,000 lm
911401520091	BY698P G5 LED250/CW PSD NB GM	6500 K	80	150 lm/W	25,000 lm
911401520191	BY698P G5 LED300/NW PSD WB GM	4000 K	80	150 lm/W	30,000 lm

## GreenPerform Highbay G5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401520291	BY698P G5 LED300/NW PSD NB GM	4000 K	80	150 lm/W	30,000 lm
911401520391	BY698P G5 LED300/CW PSD WB GM	6500 K	80	150 lm/W	30,000 lm
911401520491	BY698P G5 LED300/CW PSD NB GM	6500 K	80	150 lm/W	30,000 lm
911401522391	BY698P G5 LED250/840 PSD WB CAU	4000 K	80	150 lm/W	25,000 lm
911401522591	BY698P G5 LED250/850 PSD WB CAU	5000 K	80	150 lm/W	25,000 lm
911401522991	BY698P G5 LED300/840 PSD WB CAU	4000 K	80	150 lm/W	30,000 lm
911401523191	BY698P G5 LED300/850 PSD WB CAU	5000 K	80	150 lm/W	30,000 lm
911401531791	BY690P LED250/NW PSU WB GC	4000 K	>80	160 lm/W	25,000 lm
911401531891	BY690P LED250/NW PSU NB GC	4000 K	>80	160 lm/W	25,000 lm
911401531991	BY690P LED250/CW PSU WB GC	6500 K	>80	160 lm/W	25,000 lm
911401532091	BY690P LED250/CW PSU NB GC	6500 K	>80	160 lm/W	25,000 lm
911401532191	BY690P LED300/NW PSU WB GC	4000 K	>80	160 lm/W	30,000 lm
911401532291	BY690P LED300/NW PSU NB GC	4000 K	>80	160 lm/W	30,000 lm
911401532391	BY690P LED300/CW PSU WB GC	6500 K	>80	160 lm/W	30,000 lm
911401532491	BY690P LED300/CW PSU NB GC	6500 K	>80	160 lm/W	30,000 lm
911401533791	BY690P LED250/NW PSU WB GM	4000 K	>80	160 lm/W	25,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401533891	BY690P LED250/NW PSU NB GM	4000 K	>80	160 lm/W	25,000 lm
911401533991	BY690P LED250/CW PSU WB GM	6500 K	>80	160 lm/W	25,000 lm
911401534091	BY690P LED250/CW PSU NB GM	6500 K	>80	160 lm/W	25,000 lm
911401534191	BY690P LED300/NW PSU WB GM	4000 K	>80	160 lm/W	30,000 lm
911401534291	BY690P LED300/NW PSU NB GM	4000 K	>80	160 lm/W	30,000 lm
911401534391	BY690P LED300/CW PSU WB GM	6500 K	>80	160 lm/W	30,000 lm
911401534491	BY690P LED300/CW PSU NB GM	6500 K	>80	160 lm/W	30,000 lm
911401534902	BY690P LED250/NW PSU WB KSA	4000 K	>80	160 lm/W	25,000 lm
911401535002	BY690P LED250/NW PSU NB KSA	4000 K	>80	160 lm/W	25,000 lm
911401535102	BY690P LED250/CW PSU WB KSA	6500 K	>80	160 lm/W	25,000 lm
911401535202	BY690P LED250/CW PSU NB KSA	6500 K	>80	160 lm/W	25,000 lm
911401535302	BY690P LED300/NW PSU WB KSA	4000 K	>80	160 lm/W	30,000 lm
911401535402	BY690P LED300/NW PSU NB KSA	4000 K	>80	160 lm/W	30,000 lm
911401535502	BY690P LED300/CW PSU WB KSA	6500 K	>80	160 lm/W	30,000 lm
911401535602	BY690P LED300/CW PSU NB KSA	6500 K	>80	160 lm/W	30,000 lm
911401555591	BY698P G5 LED250/NW PSU WB LA	4000 K	80	160 lm/W	25,000 lm

## GreenPerform Highbay G5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401555691	BY698P G5 LED250/NW PSU NB LA	4000 K	80	160 lm/W	25,000 lm
911401555791	BY698P G5 LED250/CW PSU WB LA	6500 K	80	160 lm/W	25,000 lm
911401555891	BY698P G5 LED250/CW PSU NB LA	6500 K	80	160 lm/W	25,000 lm
911401555991	BY698P G5 LED300/NW PSU WB LA	4000 K	80	160 lm/W	30,000 lm
911401556091	BY698P G5 LED300/NW PSU NB LA	4000 K	80	160 lm/W	30,000 lm
911401556191	BY698P G5 LED300/CW PSU WB LA	6500 K	80	160 lm/W	30,000 lm
911401556291	BY698P G5 LED300/CW PSU NB LA	6500 K	80	160 lm/W	30,000 lm
911401557591	BY698P G5 LED250/NW PSD WB LA	4000 K	80	150 lm/W	25,000 lm
911401557691	BY698P G5 LED250/NW PSD NB LA	4000 K	80	150 lm/W	25,000 lm
911401557791	BY698P G5 LED250/CW PSD WB LA	6500 K	80	150 lm/W	25,000 lm
911401557891	BY698P G5 LED250/CW PSD NB LA	6500 K	80	150 lm/W	25,000 lm
911401557991	BY698P G5 LED300/NW PSD WB LA	4000 K	80	150 lm/W	30,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401558091	BY698P G5 LED300/NW PSD NB LA	4000 K	80	150 lm/W	30,000 lm
911401558191	BY698P G5 LED300/CW PSD WB LA	6500 K	80	150 lm/W	30,000 lm
911401558291	BY698P G5 LED300/CW PSD NB LA	6500 K	80	150 lm/W	30,000 lm
911401570291	BY698P G5 LED250/NW PSU WB GM L3m	4000 K	80	160 lm/W	25,000 lm
911401570391	BY698P G5 LED250/NW PSU NB GM L3m	4000 K	80	160 lm/W	25,000 lm
911401570491	BY698P G5 LED250/CW PSU WB GM L3m	6500 K	80	160 lm/W	25,000 lm
911401570591	BY698P G5 LED250/CW PSU NB GM L3m	6500 K	80	160 lm/W	25,000 lm
911401570691	BY698P G5 LED300/NW PSU WB GM L3m	4000 K	80	160 lm/W	30,000 lm
911401570791	BY698P G5 LED300/NW PSU NB GM L3m	4000 K	80	160 lm/W	30,000 lm
911401570891	BY698P G5 LED300/CW PSU WB GM L3m	6500 K	80	160 lm/W	30,000 lm
911401570991	BY698P G5 LED300/CW PSU NB GM L3m	6500 K	80	160 lm/W	30,000 lm

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401523991	BY698X G5 LED150/NW Connected WB GC	98 W
911401524091	BY698X G5 LED150/NW Connected NB GC	98 W
911401524191	BY698X G5 LED150/CW Connected WB GC	98 W
911401524291	BY698X G5 LED150/CW Connected NB GC	98 W
911401524391	BY698X G5 LED200/NW Connected WB GC	133 W
911401524491	BY698X G5 LED200/NW Connected NB GC	133 W
911401524591	BY698X G5 LED200/CW Connected WB GC	133 W
911401524691	BY698X G5 LED200/CW Connected NB GC	133 W
911401524791	BY698X G5 LED250/NW Connected WB GC	166 W

Order Code	Full Product Name	Power Consumption
911401524891	BY698X G5 LED250/NW Connected NB GC	166 W
911401524991	BY698X G5 LED250/CW Connected WB GC	166 W
911401525091	BY698X G5 LED250/CW Connected NB GC	166 W
911401525191	BY698X G5 LED300/NW Connected WB GC	203 W
911401525291	BY698X G5 LED300/NW Connected NB GC	203 W
911401525391	BY698X G5 LED300/CW Connected WB GC	203 W
911401525491	BY698X G5 LED300/CW Connected NB GC	203 W
911401525991	BY698X G5 LED150/NW Connected WB GM	98 W
911401526091	BY698X G5 LED150/NW Connected NB GM	98 W



## GreenPerform Highbay G5

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401526191	BY698X G5 LED150/CW Connected WB GM	98 W	911401518691	BY698P G5 LED105/NW PSD NB GM	72 W
911401526291	BY698X G5 LED150/CW Connected NB GM	98 W	911401518991	BY698P G5 LED150/NW PSD WB GM	102 W
911401526391	BY698X G5 LED200/NW Connected WB GM	133 W	911401519091	BY698P G5 LED150/NW PSD NB GM	102 W
911401526491	BY698X G5 LED200/NW Connected NB GM	133 W	911401519391	BY698P G5 LED200/NW PSD WB GM	134 W
911401526591	BY698X G5 LED200/CW Connected WB GM	133 W	911401519491	BY698P G5 LED200/NW PSD NB GM	134 W
911401526691	BY698X G5 LED200/CW Connected NB GM	133 W	911401519591	BY698P G5 LED200/CW PSD WB GM	134 W
911401526791	BY698X G5 LED250/NW Connected WB GM	166 W	911401533391	BY690P LED200/NW PSU WB GM	126 W
911401526891	BY698X G5 LED250/NW Connected NB GM	166 W	911401533591	BY690P LED200/CW PSU WB GM	126 W
911401526991	BY698X G5 LED250/CW Connected WB GM	166 W	911401534502	BY690P LED200/NW PSU WB KSA	126 W
911401527091	BY698X G5 LED250/CW Connected NB GM	166 W	911401534602	BY690P LED200/NW PSU NB KSA	126 W
911401527191	BY698X G5 LED300/NW Connected WB GM	203 W	911401534702	BY690P LED200/CW PSU WB KSA	126 W
911401527291	BY698X G5 LED300/NW Connected NB GM	203 W	911401534802	BY690P LED200/CW PSU NB KSA	126 W
911401527391	BY698X G5 LED300/CW Connected WB GM	203 W	911401555191	BY698P G5 LED200/NW PSU WB LA	126 W
911401527491	BY698X G5 LED300/CW Connected NB GM	203 W	911401555291	BY698P G5 LED200/NW PSU NB LA	126 W
911401528791	BY698X G5 LED200/840 Connected WB CAU	133 W	911401555391	BY698P G5 LED200/CW PSU WB LA	126 W
911401528991	BY698X G5 LED200/850 Connected WB CAU	133 W	911401555591	BY698P G5 LED105/CW PSD WB LA	72 W
911401529391	BY698X G5 LED250/840 Connected WB CAU	166 W	911401557191	BY698P G5 LED200/NW PSD WB LA	134 W
911401529591	BY698X G5 LED250/850 Connected WB CAU	166 W	911401557391	BY698P G5 LED200/CW PSD WB LA	134 W
911401529991	BY698X G5 LED300/840 Connected WB CAU	203 W	911401569891	BY698P G5 LED200/NW PSU WB GM L3m	126 W
911401530191	BY698X G5 LED300/850 Connected WB CAU	203 W	911401569991	BY698P G5 LED200/NW PSU NB GM L3m	126 W
911401558791	BY698X G5 LED150/NW Connected WB LA	98 W	911401570091	BY698P G5 LED200/CW PSU WB GM L3m	126 W
911401558891	BY698X G5 LED150/NW Connected NB LA	98 W	911401570191	BY698P G5 LED200/CW PSU NB GM L3m	126 W
911401558991	BY698X G5 LED150/CW Connected WB LA	98 W	911401545502	BY698X G5 LED105/NW L1 W WB GC	67 W
911401559091	BY698X G5 LED150/CW Connected NB LA	98 W	911401545602	BY698X G5 LED105/CW L1 W WB GC	67 W
911401559191	BY698X G5 LED200/NW Connected WB LA	133 W	911401545702	BY698X G5 LED150/NW L1 W WB GC	95 W
911401559291	BY698X G5 LED200/NW Connected NB LA	133 W	911401545802	BY698X G5 LED150/CW L1 W WB GC	95 W
911401559391	BY698X G5 LED200/CW Connected WB LA	133 W	911401545902	BY698X G5 LED200/NW L1 W WB GC	126 W
911401559491	BY698X G5 LED200/CW Connected NB LA	133 W	911401546002	BY698X G5 LED200/CW L1 W WB GC	126 W
911401559591	BY698X G5 LED250/NW Connected WB LA	166 W	911401546102	BY698X G5 LED250/NW L1 W WB GC	157 W
911401559691	BY698X G5 LED250/NW Connected NB LA	166 W	911401546202	BY698X G5 LED250/CW L1 W WB GC	157 W
911401559791	BY698X G5 LED250/CW Connected WB LA	166 W	911401546302	BY698X G5 LED300/NW L1 W WB GC	192 W
911401559891	BY698X G5 LED250/CW Connected NB LA	166 W	911401546402	BY698X G5 LED300/CW L1 W WB GC	192 W
911401559991	BY698X G5 LED300/NW Connected WB LA	203 W	911401546502	BY698X G5 LED105/NW L1 W WB GM	67 W
911401560091	BY698X G5 LED300/NW Connected NB LA	203 W	911401546602	BY698X G5 LED105/CW L1 W WB GM	67 W
911401560191	BY698X G5 LED300/CW Connected WB LA	203 W	911401546702	BY698X G5 LED150/NW L1 W WB GM	95 W
911401560291	BY698X G5 LED300/CW Connected NB LA	203 W	911401546802	BY698X G5 LED150/CW L1 W WB GM	95 W
911401507891	BY698P G5 LED200/NW PSU WB GC	126 W	911401546902	BY698X G5 LED200/NW L1 W WB GM	126 W
911401507991	BY698P G5 LED200/NW PSU NB GC	126 W	911401547002	BY698X G5 LED200/CW L1 W WB GM	126 W
911401508091	BY698P G5 LED200/CW PSU WB GC	126 W	911401547102	BY698X G5 LED250/NW L1 W WB GM	157 W
911401508191	BY698P G5 LED200/CW PSU NB GC	126 W	911401547202	BY698X G5 LED250/CW L1 W WB GM	157 W
911401509891	BY698P G5 LED200/NW PSU WB GM	126 W	911401547302	BY698X G5 LED300/NW L1 W WB GM	192 W
911401509991	BY698P G5 LED200/NW PSU NB GM	126 W	911401547402	BY698X G5 LED300/CW L1 W WB GM	192 W
911401510091	BY698P G5 LED200/CW PSU WB GM	126 W	911401547502	BY698X G5 LED105/840 L1 W WB CAU	67 W
911401510191	BY698P G5 LED200/CW PSU NB GM	126 W	911401547602	BY698X G5 LED150/840 L1 W WB CAU	95 W
911401515691	BY698P G5 LED200/840 PSU WB CAU CL	126 W	911401547702	BY698X G5 LED200/840 L1 W WB CAU	126 W
911401515791	BY698P G5 LED200/850 PSU WB CAU CL	126 W	911401547802	BY698X G5 LED250/840 L1 W WB CAU	157 W
911401516591	BY698P G5 LED105/NW PSD WB GC	72 W	911401547902	BY698X G5 LED300/840 L1 W WB CAU	192 W
911401516991	BY698P G5 LED150/NW PSD WB GC	102 W	911401548002	BY698X G5 LED105/NW L1 W WB GM L3m	67 W
911401517191	BY698P G5 LED150/CW PSD WB GC	102 W	911401548102	BY698X G5 LED105/CW L1 W WB GM L3m	67 W
911401517391	BY698P G5 LED200/NW PSD WB GC	134 W	911401548202	BY698X G5 LED150/NW L1 W WB GM L3m	95 W
911401517491	BY698P G5 LED200/NW PSD NB GC	134 W	911401548302	BY698X G5 LED150/CW L1 W WB GM L3m	95 W
911401518591	BY698P G5 LED105/NW PSD WB GM	72 W	911401548402	BY698X G5 LED200/NW L1 W WB GM L3m	126 W

## GreenPerform Highbay G5

Order Code	Full Product Name	Power Consumption
911401548502	BY698X G5 LED200/CW L1 W WB GM L3m	126 W
911401548602	BY698X G5 LED250/NW L1 W WB GM L3m	157 W
911401548702	BY698X G5 LED250/CW L1 W WB GM L3m	157 W
911401548802	BY698X G5 LED300/NW L1 W WB GM L3m	192 W
911401548902	BY698X G5 LED300/CW L1 W WB GM L3m	192 W
911401507091	BY698P G5 LED105/NW PSU WB GC	67 W
911401507191	BY698P G5 LED105/NW PSU NB GC	67 W
911401507291	BY698P G5 LED105/CW PSU WB GC	67 W
911401507391	BY698P G5 LED105/CW PSU NB GC	67 W
911401507491	BY698P G5 LED150/NW PSU WB GC	95 W
911401507591	BY698P G5 LED150/NW PSU NB GC	95 W
911401507691	BY698P G5 LED150/CW PSU WB GC	95 W
911401507791	BY698P G5 LED150/CW PSU NB GC	95 W
911401509091	BY698P G5 LED105/NW PSU WB GM	67 W
911401509291	BY698P G5 LED105/CW PSU WB GM	67 W
911401509391	BY698P G5 LED105/CW PSU NB GM	67 W
911401509491	BY698P G5 LED150/NW PSU WB GM	95 W
911401509591	BY698P G5 LED150/NW PSU NB GM	95 W
911401509691	BY698P G5 LED150/CW PSU WB GM	95 W
911401509791	BY698P G5 LED150/CW PSU NB GM	95 W
911401530991	BY690P LED150/NW PSU WB GC	95 W
911401532991	BY690P LED150/NW PSU WB GM	95 W
911401533702	BY690P LED105/NW PSU WB KSA	67 W
911401533802	BY690P LED105/NW PSU NB KSA	67 W
911401533902	BY690P LED105/CW PSU WB KSA	67 W
911401534002	BY690P LED105/CW PSU NB KSA	67 W
911401534102	BY690P LED150/NW PSU WB KSA	95 W
911401534202	BY690P LED150/NW PSU NB KSA	95 W
911401534302	BY690P LED150/CW PSU WB KSA	95 W
911401534402	BY690P LED150/CW PSU NB KSA	95 W
911401554391	BY698P G5 LED105/NW PSU WB LA	67 W
911401554591	BY698P G5 LED105/CW PSU WB LA	67 W
911401554791	BY698P G5 LED150/NW PSU WB LA	95 W
911401554991	BY698P G5 LED150/CW PSU WB LA	95 W
911401569091	BY698P G5 LED105/NW PSU WB GM L3m	67 W
911401569291	BY698P G5 LED105/CW PSU WB GM L3m	67 W
911401569491	BY698P G5 LED150/NW PSU WB GM L3m	95 W
911401569691	BY698P G5 LED150/CW PSU WB GM L3m	95 W
911401508291	BY698P G5 LED250/NW PSU WB GC	157 W
911401508391	BY698P G5 LED250/NW PSU NB GC	157 W
911401508491	BY698P G5 LED250/CW PSU WB GC	157 W
911401508591	BY698P G5 LED250/CW PSU NB GC	157 W
911401508691	BY698P G5 LED300/NW PSU WB GC	192 W
911401508791	BY698P G5 LED300/NW PSU NB GC	192 W
911401508891	BY698P G5 LED300/CW PSU WB GC	192 W
911401508991	BY698P G5 LED300/CW PSU NB GC	192 W
911401510291	BY698P G5 LED250/NW PSU WB GM	157 W
911401510391	BY698P G5 LED250/NW PSU NB GM	157 W
911401510491	BY698P G5 LED250/CW PSU WB GM	157 W
911401510591	BY698P G5 LED250/CW PSU NB GM	157 W
911401510691	BY698P G5 LED300/NW PSU WB GM	192 W
911401510791	BY698P G5 LED300/NW PSU NB GM	192 W

Order Code	Full Product Name	Power Consumption
911401510891	BY698P G5 LED300/CW PSU WB GM	192 W
911401510991	BY698P G5 LED300/CW PSU NB GM	192 W
911401513891	BY698P G5 LED250/840 PSU WB CAU	157 W
911401514091	BY698P G5 LED250/850 PSU WB CAU	157 W
911401514491	BY698P G5 LED300/840 PSU WB CAU	192 W
911401514691	BY698P G5 LED300/850 PSU WB CAU	192 W
911401515991	BY698P G5 LED250/840 PSU WB CAU CL	157 W
911401516091	BY698P G5 LED250/850 PSU WB CAU CL	157 W
911401516291	BY698P G5 LED300/840 PSU WB CAU CL	192 W
911401516391	BY698P G5 LED300/850 PSU WB CAU CL	192 W
911401517791	BY698P G5 LED250/NW PSD WB GC	168 W
911401517891	BY698P G5 LED250/NW PSD NB GC	168 W
911401517991	BY698P G5 LED250/CW PSD WB GC	168 W
911401518091	BY698P G5 LED250/CW PSD NB GC	168 W
911401518191	BY698P G5 LED300/NW PSD WB GC	205 W
911401518291	BY698P G5 LED300/NW PSD NB GC	205 W
911401518391	BY698P G5 LED300/CW PSD WB GC	205 W
911401518491	BY698P G5 LED300/CW PSD NB GC	205 W
911401519791	BY698P G5 LED250/NW PSD WB GM	168 W
911401519891	BY698P G5 LED250/NW PSD NB GM	168 W
911401519991	BY698P G5 LED250/CW PSD WB GM	168 W
911401520091	BY698P G5 LED250/CW PSD NB GM	168 W
911401520191	BY698P G5 LED300/NW PSD WB GM	205 W
911401520291	BY698P G5 LED300/NW PSD NB GM	205 W
911401520391	BY698P G5 LED300/CW PSD WB GM	205 W
911401520491	BY698P G5 LED300/CW PSD NB GM	205 W
911401522391	BY698P G5 LED250/840 PSD WB CAU	168 W
911401522591	BY698P G5 LED250/850 PSD WB CAU	168 W
911401522991	BY698P G5 LED300/840 PSD WB CAU	205 W
911401523191	BY698P G5 LED300/850 PSD WB CAU	205 W
911401531791	BY690P LED250/NW PSU WB GC	157 W
911401531891	BY690P LED250/NW PSU NB GC	157 W
911401531991	BY690P LED250/CW PSU WB GC	157 W
911401532091	BY690P LED250/CW PSU NB GC	157 W
911401532191	BY690P LED300/NW PSU WB GC	192 W
911401532291	BY690P LED300/NW PSU NB GC	192 W
911401532391	BY690P LED300/CW PSU WB GC	192 W
911401532491	BY690P LED300/CW PSU NB GC	192 W
911401533791	BY690P LED250/NW PSU WB GM	157 W
911401533891	BY690P LED250/NW PSU NB GM	157 W
911401533991	BY690P LED250/CW PSU WB GM	157 W
911401534091	BY690P LED250/CW PSU NB GM	157 W
911401534191	BY690P LED300/NW PSU WB GM	192 W
911401534291	BY690P LED300/NW PSU NB GM	192 W
911401534391	BY690P LED300/CW PSU WB GM	192 W
911401534491	BY690P LED300/CW PSU NB GM	192 W
911401534902	BY690P LED250/NW PSU WB KSA	157 W
911401535002	BY690P LED250/NW PSU NB KSA	157 W
911401535102	BY690P LED250/CW PSU WB KSA	157 W
911401535202	BY690P LED250/CW PSU NB KSA	157 W
911401535302	BY690P LED300/NW PSU WB KSA	192 W
911401535402	BY690P LED300/NW PSU NB KSA	192 W

## GreenPerform Highbay G5

Order Code	Full Product Name	Power Consumption
911401535502	BY690P LED300/CW PSU WB KSA	192 W
911401535602	BY690P LED300/CW PSU NB KSA	192 W
911401555591	BY698P G5 LED250/NW PSU WB LA	157 W
911401555691	BY698P G5 LED250/NW PSU NB LA	157 W
911401555791	BY698P G5 LED250/CW PSU WB LA	157 W
911401555891	BY698P G5 LED250/CW PSU NB LA	157 W
911401555991	BY698P G5 LED300/NW PSU WB LA	192 W
911401556091	BY698P G5 LED300/NW PSU NB LA	192 W
911401556191	BY698P G5 LED300/CW PSU WB LA	192 W
911401556291	BY698P G5 LED300/CW PSU NB LA	192 W
911401557591	BY698P G5 LED250/NW PSD WB LA	168 W
911401557691	BY698P G5 LED250/NW PSD NB LA	168 W
911401557791	BY698P G5 LED250/CW PSD WB LA	168 W

Order Code	Full Product Name	Power Consumption
911401557891	BY698P G5 LED250/CW PSD NB LA	168 W
911401557991	BY698P G5 LED300/NW PSD WB LA	205 W
911401558091	BY698P G5 LED300/NW PSD NB LA	205 W
911401558191	BY698P G5 LED300/CW PSD WB LA	205 W
911401558291	BY698P G5 LED300/CW PSD NB LA	205 W
911401570291	BY698P G5 LED250/NW PSU WB GM L3m	157 W
911401570391	BY698P G5 LED250/NW PSU NB GM L3m	157 W
911401570491	BY698P G5 LED250/CW PSU WB GM L3m	157 W
911401570591	BY698P G5 LED250/CW PSU NB GM L3m	157 W
911401570691	BY698P G5 LED300/NW PSU WB GM L3m	192 W
911401570791	BY698P G5 LED300/NW PSU NB GM L3m	192 W
911401570891	BY698P G5 LED300/CW PSU WB GM L3m	192 W
911401570991	BY698P G5 LED300/CW PSU NB GM L3m	192 W

### Temperature

Order Code	Full Product Name	Ambient temperature range
911401523991	BY698X G5 LED150/NW Connected WB GC	-30 to +50 °C
911401524091	BY698X G5 LED150/NW Connected NB GC	-30 to +50 °C
911401524191	BY698X G5 LED150/CW Connected WB GC	-30 to +50 °C
911401524291	BY698X G5 LED150/CW Connected NB GC	-30 to +50 °C
911401524391	BY698X G5 LED200/NW Connected WB GC	-30 to +50 °C
911401524491	BY698X G5 LED200/NW Connected NB GC	-30 to +50 °C
911401524591	BY698X G5 LED200/CW Connected WB GC	-30 to +50 °C
911401524691	BY698X G5 LED200/CW Connected NB GC	-30 to +50 °C
911401524791	BY698X G5 LED250/NW Connected WB GC	-30 to +50 °C
911401524891	BY698X G5 LED250/NW Connected NB GC	-30 to +50 °C
911401524991	BY698X G5 LED250/CW Connected WB GC	-30 to +50 °C
911401525091	BY698X G5 LED250/CW Connected NB GC	-30 to +50 °C
911401525191	BY698X G5 LED300/NW Connected WB GC	-30 to +50 °C
911401525291	BY698X G5 LED300/NW Connected NB GC	-30 to +50 °C
911401525391	BY698X G5 LED300/CW Connected WB GC	-30 to +50 °C
911401525491	BY698X G5 LED300/CW Connected NB GC	-30 to +50 °C
911401525991	BY698X G5 LED150/NW Connected WB GM	-30 to +50 °C
911401526091	BY698X G5 LED150/NW Connected NB GM	-30 to +50 °C

Order Code	Full Product Name	Ambient temperature range
911401526191	BY698X G5 LED150/CW Connected WB GM	-30 to +50 °C
911401526291	BY698X G5 LED150/CW Connected NB GM	-30 to +50 °C
911401526391	BY698X G5 LED200/NW Connected WB GM	-30 to +50 °C
911401526491	BY698X G5 LED200/NW Connected NB GM	-30 to +50 °C
911401526591	BY698X G5 LED200/CW Connected WB GM	-30 to +50 °C
911401526691	BY698X G5 LED200/CW Connected NB GM	-30 to +50 °C
911401526791	BY698X G5 LED250/NW Connected WB GM	-30 to +50 °C
911401526891	BY698X G5 LED250/NW Connected NB GM	-30 to +50 °C
911401526991	BY698X G5 LED250/CW Connected WB GM	-30 to +50 °C
911401527091	BY698X G5 LED250/CW Connected NB GM	-30 to +50 °C
911401527191	BY698X G5 LED300/NW Connected WB GM	-30 to +50 °C
911401527291	BY698X G5 LED300/NW Connected NB GM	-30 to +50 °C
911401527391	BY698X G5 LED300/CW Connected WB GM	-30 to +50 °C
911401527491	BY698X G5 LED300/CW Connected NB GM	-30 to +50 °C
911401528791	BY698X G5 LED200/840 Connected WB CAU	-30 to +50 °C
911401528991	BY698X G5 LED200/850 Connected WB CAU	-30 to +50 °C
911401529391	BY698X G5 LED250/840 Connected WB CAU	-30 to +50 °C

## GreenPerform Highbay G5

Order Code	Full Product Name	Ambient temperature range
911401529591	BY698X G5 LED250/850 Connected WB CAU	-30 to +50 °C
911401529991	BY698X G5 LED300/840 Connected WB CAU	-30 to +50 °C
911401530191	BY698X G5 LED300/850 Connected WB CAU	-30 to +50 °C
911401558791	BY698X G5 LED150/NW Connected WB LA	-30 to +50 °C
911401558891	BY698X G5 LED150/NW Connected NB LA	-30 to +50 °C
911401558991	BY698X G5 LED150/CW Connected WB LA	-30 to +50 °C
911401559091	BY698X G5 LED150/CW Connected NB LA	-30 to +50 °C
911401559191	BY698X G5 LED200/NW Connected WB LA	-30 to +50 °C
911401559291	BY698X G5 LED200/NW Connected NB LA	-30 to +50 °C
911401559391	BY698X G5 LED200/CW Connected WB LA	-30 to +50 °C
911401559491	BY698X G5 LED200/CW Connected NB LA	-30 to +50 °C
911401559591	BY698X G5 LED250/NW Connected WB LA	-30 to +50 °C
911401559691	BY698X G5 LED250/NW Connected NB LA	-30 to +50 °C
911401559791	BY698X G5 LED250/CW Connected WB LA	-30 to +50 °C
911401559891	BY698X G5 LED250/CW Connected NB LA	-30 to +50 °C
911401559991	BY698X G5 LED300/NW Connected WB LA	-30 to +50 °C
911401560091	BY698X G5 LED300/NW Connected NB LA	-30 to +50 °C
911401560191	BY698X G5 LED300/CW Connected WB LA	-30 to +50 °C
911401560291	BY698X G5 LED300/CW Connected NB LA	-30 to +50 °C
911401507891	BY698P G5 LED200/NW PSU WB GC	-30 to +50 °C
911401507991	BY698P G5 LED200/NW PSU NB GC	-30 to +50 °C
911401508091	BY698P G5 LED200/CW PSU WB GC	-30 to +50 °C
911401508191	BY698P G5 LED200/CW PSU NB GC	-30 to +50 °C
911401509891	BY698P G5 LED200/NW PSU WB GM	-30 to +50 °C
911401509991	BY698P G5 LED200/NW PSU NB GM	-30 to +50 °C
911401510091	BY698P G5 LED200/CW PSU WB GM	-30 to +50 °C
911401510191	BY698P G5 LED200/CW PSU NB GM	-30 to +50 °C
911401515691	BY698P G5 LED200/840 PSU WB CAU CL	-30 to +50 °C
911401515791	BY698P G5 LED200/850 PSU WB CAU CL	-30 to +50 °C
9114015156591	BY698P G5 LED105/NW PSD WB GC	-30 to +50 °C
9114015156991	BY698P G5 LED150/NW PSD WB GC	-30 to +50 °C
911401517191	BY698P G5 LED150/CW PSD WB GC	-30 to +50 °C
911401517391	BY698P G5 LED200/NW PSD WB GC	-30 to +50 °C
911401517491	BY698P G5 LED200/NW PSD NB GC	-30 to +50 °C
911401518591	BY698P G5 LED105/NW PSD WB GM	-30 to +50 °C
911401518691	BY698P G5 LED105/NW PSD NB GM	-30 to +50 °C
911401518991	BY698P G5 LED150/NW PSD WB GM	-30 to +50 °C
911401519091	BY698P G5 LED150/NW PSD NB GM	-30 to +50 °C
911401519391	BY698P G5 LED200/NW PSD WB GM	-30 to +50 °C
911401519491	BY698P G5 LED200/NW PSD NB GM	-30 to +50 °C
911401519591	BY698P G5 LED200/CW PSD WB GM	-30 to +50 °C

Order Code	Full Product Name	Ambient temperature range
911401533391	BY690P LED200/NW PSU WB GM	-40 to +50 °C
911401533591	BY690P LED200/CW PSU WB GM	-40 to +50 °C
911401534502	BY690P LED200/NW PSU WB KSA	-40 to +50 °C
911401534602	BY690P LED200/NW PSU NB KSA	-40 to +50 °C
911401534702	BY690P LED200/CW PSU WB KSA	-40 to +50 °C
911401534802	BY690P LED200/CW PSU NB KSA	-40 to +50 °C
911401555191	BY698P G5 LED200/NW PSU WB LA	-30 to +50 °C
911401555291	BY698P G5 LED200/NW PSU NB LA	-30 to +50 °C
911401555391	BY698P G5 LED200/CW PSU WB LA	-30 to +50 °C
9114015556591	BY698P G5 LED105/CW PSD WB LA	-30 to +50 °C
911401557191	BY698P G5 LED200/NW PSD WB LA	-30 to +50 °C
911401557391	BY698P G5 LED200/CW PSD WB LA	-30 to +50 °C
911401569891	BY698P G5 LED200/NW PSU WB GM L3m	-30 to +50 °C
911401569991	BY698P G5 LED200/NW PSU NB GM L3m	-30 to +50 °C
911401570091	BY698P G5 LED200/CW PSU WB GM L3m	-30 to +50 °C
911401570191	BY698P G5 LED200/CW PSU NB GM L3m	-30 to +50 °C
911401545502	BY698X G5 LED105/NW L1 W WB GC	-30 to +50 °C
911401545602	BY698X G5 LED105/CW L1 W WB GC	-30 to +50 °C
911401545702	BY698X G5 LED150/NW L1 W WB GC	-30 to +50 °C
911401545802	BY698X G5 LED150/CW L1 W WB GC	-30 to +50 °C
911401545902	BY698X G5 LED200/NW L1 W WB GC	-30 to +50 °C
911401546002	BY698X G5 LED200/CW L1 W WB GC	-30 to +50 °C
911401546102	BY698X G5 LED250/NW L1 W WB GC	-30 to +50 °C
911401546202	BY698X G5 LED250/CW L1 W WB GC	-30 to +50 °C
911401546302	BY698X G5 LED300/NW L1 W WB GC	-30 to +50 °C
911401546402	BY698X G5 LED300/CW L1 W WB GC	-30 to +50 °C
911401546502	BY698X G5 LED105/NW L1 W WB GM	-30 to +50 °C
911401546602	BY698X G5 LED105/CW L1 W WB GM	-30 to +50 °C
911401546702	BY698X G5 LED150/NW L1 W WB GM	-30 to +50 °C
911401546802	BY698X G5 LED150/CW L1 W WB GM	-30 to +50 °C
911401546902	BY698X G5 LED200/NW L1 W WB GM	-30 to +50 °C
911401547002	BY698X G5 LED200/CW L1 W WB GM	-30 to +50 °C
911401547102	BY698X G5 LED250/NW L1 W WB GM	-30 to +50 °C
911401547202	BY698X G5 LED250/CW L1 W WB GM	-30 to +50 °C
911401547302	BY698X G5 LED300/NW L1 W WB GM	-30 to +50 °C
911401547402	BY698X G5 LED300/CW L1 W WB GM	-30 to +50 °C
911401547502	BY698X G5 LED105/840 L1 W WB CAU	-30 to +50 °C
911401547602	BY698X G5 LED150/840 L1 W WB CAU	-30 to +50 °C
911401547702	BY698X G5 LED200/840 L1 W WB CAU	-30 to +50 °C
911401547802	BY698X G5 LED250/840 L1 W WB CAU	-30 to +50 °C
911401547902	BY698X G5 LED300/840 L1 W WB CAU	-30 to +50 °C
911401548002	BY698X G5 LED105/NW L1 W WB GM L3m	-30 to +50 °C
911401548102	BY698X G5 LED105/CW L1 W WB GM L3m	-30 to +50 °C
911401548202	BY698X G5 LED150/NW L1 W WB GM L3m	-30 to +50 °C
911401548302	BY698X G5 LED150/CW L1 W WB GM L3m	-30 to +50 °C
911401548402	BY698X G5 LED200/NW L1 W WB GM L3m	-30 to +50 °C
911401548502	BY698X G5 LED200/CW L1 W WB GM L3m	-30 to +50 °C
911401548602	BY698X G5 LED250/NW L1 W WB GM L3m	-30 to +50 °C
911401548702	BY698X G5 LED250/CW L1 W WB GM L3m	-30 to +50 °C
911401548802	BY698X G5 LED300/NW L1 W WB GM L3m	-30 to +50 °C
911401548902	BY698X G5 LED300/CW L1 W WB GM L3m	-30 to +50 °C
911401507091	BY698P G5 LED105/NW PSU WB GC	-30 to +50 °C

## GreenPerform Highbay G5

Order Code	Full Product Name	Ambient temperature range	Order Code	Full Product Name	Ambient temperature range
911401507191	BY698P G5 LED105/NW PSU NB GC	-30 to +50 °C	911401515991	BY698P G5 LED250/840 PSU WB CAU CL	-30 to +50 °C
911401507291	BY698P G5 LED105/CW PSU WB GC	-30 to +50 °C	911401516091	BY698P G5 LED250/850 PSU WB CAU CL	-30 to +50 °C
911401507391	BY698P G5 LED105/CW PSU NB GC	-30 to +50 °C	911401516291	BY698P G5 LED300/840 PSU WB CAU CL	-30 to +50 °C
911401507491	BY698P G5 LED150/NW PSU WB GC	-30 to +50 °C	911401516391	BY698P G5 LED300/850 PSU WB CAU CL	-30 to +50 °C
911401507591	BY698P G5 LED150/NW PSU NB GC	-30 to +50 °C	911401517791	BY698P G5 LED250/NW PSD WB GC	-30 to +50 °C
911401507691	BY698P G5 LED150/CW PSU WB GC	-30 to +50 °C	911401517891	BY698P G5 LED250/NW PSD NB GC	-30 to +50 °C
911401507791	BY698P G5 LED150/CW PSU NB GC	-30 to +50 °C	911401517991	BY698P G5 LED250/CW PSD WB GC	-30 to +50 °C
911401509091	BY698P G5 LED105/NW PSU WB GM	-30 to +50 °C	911401518091	BY698P G5 LED250/CW PSD NB GC	-30 to +50 °C
911401509291	BY698P G5 LED105/CW PSU WB GM	-30 to +50 °C	911401518191	BY698P G5 LED300/NW PSD WB GC	-30 to +50 °C
911401509391	BY698P G5 LED105/CW PSU NB GM	-30 to +50 °C	911401518291	BY698P G5 LED300/NW PSD NB GC	-30 to +50 °C
911401509491	BY698P G5 LED150/NW PSU WB GM	-30 to +50 °C	911401518391	BY698P G5 LED300/CW PSD WB GC	-30 to +50 °C
911401509591	BY698P G5 LED150/NW PSU NB GM	-30 to +50 °C	911401518491	BY698P G5 LED300/CW PSD NB GC	-30 to +50 °C
911401509691	BY698P G5 LED150/CW PSU WB GM	-30 to +50 °C	911401519791	BY698P G5 LED250/NW PSD WB GM	-30 to +50 °C
911401509791	BY698P G5 LED150/CW PSU NB GM	-30 to +50 °C	911401519891	BY698P G5 LED250/NW PSD NB GM	-30 to +50 °C
911401530991	BY690P LED150/NW PSU WB GC	-40 to +50 °C	911401519991	BY698P G5 LED250/CW PSD WB GM	-30 to +50 °C
911401532991	BY690P LED150/NW PSU WB GM	-40 to +50 °C	911401520091	BY698P G5 LED250/CW PSD NB GM	-30 to +50 °C
911401533702	BY690P LED105/NW PSU WB KSA	-40 to +50 °C	911401520191	BY698P G5 LED300/NW PSD WB GM	-30 to +50 °C
911401533802	BY690P LED105/NW PSU NB KSA	-40 to +50 °C	911401520291	BY698P G5 LED300/NW PSD NB GM	-30 to +50 °C
911401533902	BY690P LED105/CW PSU WB KSA	-40 to +50 °C	911401520391	BY698P G5 LED300/CW PSD WB GM	-30 to +50 °C
911401534002	BY690P LED105/CW PSU NB KSA	-40 to +50 °C	911401520491	BY698P G5 LED300/CW PSD NB GM	-30 to +50 °C
911401534102	BY690P LED150/NW PSU WB KSA	-40 to +50 °C	911401522391	BY698P G5 LED250/840 PSD WB CAU	-30 to +50 °C
911401534202	BY690P LED150/NW PSU NB KSA	-40 to +50 °C	911401522591	BY698P G5 LED250/850 PSD WB CAU	-30 to +50 °C
911401534302	BY690P LED150/CW PSU WB KSA	-40 to +50 °C	911401522991	BY698P G5 LED300/840 PSD WB CAU	-30 to +50 °C
911401534402	BY690P LED150/CW PSU NB KSA	-40 to +50 °C	911401523191	BY698P G5 LED300/850 PSD WB CAU	-30 to +50 °C
911401554391	BY698P G5 LED105/NW PSU WB LA	-30 to +50 °C	911401531791	BY690P LED250/NW PSU WB GC	-40 to +50 °C
911401554591	BY698P G5 LED105/CW PSU WB LA	-30 to +50 °C	911401531891	BY690P LED250/NW PSU NB GC	-40 to +50 °C
911401554791	BY698P G5 LED150/NW PSU WB LA	-30 to +50 °C	911401531991	BY690P LED250/CW PSU WB GC	-40 to +50 °C
911401554991	BY698P G5 LED150/CW PSU WB LA	-30 to +50 °C	911401532091	BY690P LED250/CW PSU NB GC	-40 to +50 °C
911401569091	BY698P G5 LED105/NW PSU WB GM L3m	-30 to +50 °C	911401532191	BY690P LED300/NW PSU WB GC	-40 to +50 °C
911401569291	BY698P G5 LED105/CW PSU WB GM L3m	-30 to +50 °C	911401532291	BY690P LED300/NW PSU NB GC	-40 to +50 °C
911401569491	BY698P G5 LED150/NW PSU WB GM L3m	-30 to +50 °C	911401532391	BY690P LED300/CW PSU WB GC	-40 to +50 °C
911401569691	BY698P G5 LED150/CW PSU WB GM L3m	-30 to +50 °C	911401532491	BY690P LED300/CW PSU NB GC	-40 to +50 °C
911401508291	BY698P G5 LED250/NW PSU WB GC	-30 to +50 °C	911401533791	BY690P LED250/NW PSU WB GM	-40 to +50 °C
911401508391	BY698P G5 LED250/NW PSU NB GC	-30 to +50 °C	911401533891	BY690P LED250/NW PSU NB GM	-40 to +50 °C
911401508491	BY698P G5 LED250/CW PSU WB GC	-30 to +50 °C	911401533991	BY690P LED250/CW PSU WB GM	-40 to +50 °C
911401508591	BY698P G5 LED250/CW PSU NB GC	-30 to +50 °C	911401534091	BY690P LED250/CW PSU NB GM	-40 to +50 °C
911401508691	BY698P G5 LED300/NW PSU WB GC	-30 to +50 °C	911401534191	BY690P LED300/NW PSU WB GM	-40 to +50 °C
911401508791	BY698P G5 LED300/NW PSU NB GC	-30 to +50 °C	911401534291	BY690P LED300/NW PSU NB GM	-40 to +50 °C
911401508891	BY698P G5 LED300/CW PSU WB GC	-30 to +50 °C	911401534391	BY690P LED300/CW PSU WB GM	-40 to +50 °C
911401508991	BY698P G5 LED300/CW PSU NB GC	-30 to +50 °C	911401534491	BY690P LED300/CW PSU NB GM	-40 to +50 °C
911401510291	BY698P G5 LED250/NW PSU WB GM	-30 to +50 °C	911401534902	BY690P LED250/NW PSU WB KSA	-40 to +50 °C
911401510391	BY698P G5 LED250/NW PSU NB GM	-30 to +50 °C	911401535002	BY690P LED250/NW PSU NB KSA	-40 to +50 °C
911401510491	BY698P G5 LED250/CW PSU WB GM	-30 to +50 °C	911401535102	BY690P LED250/CW PSU WB KSA	-40 to +50 °C
911401510591	BY698P G5 LED250/CW PSU NB GM	-30 to +50 °C	911401535202	BY690P LED250/CW PSU NB KSA	-40 to +50 °C
911401510691	BY698P G5 LED300/NW PSU WB GM	-30 to +50 °C	911401535302	BY690P LED300/NW PSU WB KSA	-40 to +50 °C
911401510791	BY698P G5 LED300/NW PSU NB GM	-30 to +50 °C	911401535402	BY690P LED300/NW PSU NB KSA	-40 to +50 °C
911401510891	BY698P G5 LED300/CW PSU WB GM	-30 to +50 °C	911401535502	BY690P LED300/CW PSU WB KSA	-40 to +50 °C
911401510991	BY698P G5 LED300/CW PSU NB GM	-30 to +50 °C	911401535602	BY690P LED300/CW PSU NB KSA	-40 to +50 °C
911401513891	BY698P G5 LED250/840 PSU WB CAU	-30 to +50 °C	911401555591	BY698P G5 LED250/NW PSU WB LA	-30 to +50 °C
911401514091	BY698P G5 LED250/850 PSU WB CAU	-30 to +50 °C	911401555691	BY698P G5 LED250/NW PSU NB LA	-30 to +50 °C
911401514491	BY698P G5 LED300/840 PSU WB CAU	-30 to +50 °C	911401555791	BY698P G5 LED250/CW PSU WB LA	-30 to +50 °C
911401514691	BY698P G5 LED300/850 PSU WB CAU	-30 to +50 °C	911401555891	BY698P G5 LED250/CW PSU NB LA	-30 to +50 °C

## GreenPerform Highbay G5

Order Code	Full Product Name	Ambient temperature range
911401555991	BY698P G5 LED300/NW PSU WB LA	-30 to +50 °C
911401556091	BY698P G5 LED300/NW PSU NB LA	-30 to +50 °C
911401556191	BY698P G5 LED300/CW PSU WB LA	-30 to +50 °C
911401556291	BY698P G5 LED300/CW PSU NB LA	-30 to +50 °C
911401557591	BY698P G5 LED250/NW PSD WB LA	-30 to +50 °C
911401557691	BY698P G5 LED250/NW PSD NB LA	-30 to +50 °C
911401557791	BY698P G5 LED250/CW PSD WB LA	-30 to +50 °C
911401557891	BY698P G5 LED250/CW PSD NB LA	-30 to +50 °C
911401557991	BY698P G5 LED300/NW PSD WB LA	-30 to +50 °C
911401558091	BY698P G5 LED300/NW PSD NB LA	-30 to +50 °C

Order Code	Full Product Name	Ambient temperature range
911401558191	BY698P G5 LED300/CW PSD WB LA	-30 to +50 °C
911401558291	BY698P G5 LED300/CW PSD NB LA	-30 to +50 °C
911401570291	BY698P G5 LED250/NW PSU WB GM L3m	-30 to +50 °C
911401570391	BY698P G5 LED250/NW PSU NB GM L3m	-30 to +50 °C
911401570491	BY698P G5 LED250/CW PSU WB GM L3m	-30 to +50 °C
911401570591	BY698P G5 LED250/CW PSU NB GM L3m	-30 to +50 °C
911401570691	BY698P G5 LED300/NW PSU WB GM L3m	-30 to +50 °C
911401570791	BY698P G5 LED300/NW PSU NB GM L3m	-30 to +50 °C
911401570891	BY698P G5 LED300/CW PSU WB GM L3m	-30 to +50 °C
911401570991	BY698P G5 LED300/CW PSU NB GM L3m	-30 to +50 °C

### Controls and Dimming

Order Code	Full Product Name	Dimmable
911401523991	BY698X G5 LED150/NW Connected WB GC	Yes
911401524091	BY698X G5 LED150/NW Connected NB GC	Yes
911401524191	BY698X G5 LED150/CW Connected WB GC	Yes
911401524291	BY698X G5 LED150/CW Connected NB GC	Yes
911401524391	BY698X G5 LED200/NW Connected WB GC	Yes
911401524491	BY698X G5 LED200/NW Connected NB GC	Yes
911401524591	BY698X G5 LED200/CW Connected WB GC	Yes
911401524691	BY698X G5 LED200/CW Connected NB GC	Yes
911401524791	BY698X G5 LED250/NW Connected WB GC	Yes
911401524891	BY698X G5 LED250/NW Connected NB GC	Yes
911401524991	BY698X G5 LED250/CW Connected WB GC	Yes
911401525091	BY698X G5 LED250/CW Connected NB GC	Yes
911401525191	BY698X G5 LED300/NW Connected WB GC	Yes
911401525291	BY698X G5 LED300/NW Connected NB GC	Yes
911401525391	BY698X G5 LED300/CW Connected WB GC	Yes
911401525491	BY698X G5 LED300/CW Connected NB GC	Yes
911401525991	BY698X G5 LED150/NW Connected WB GM	Yes
911401526091	BY698X G5 LED150/NW Connected NB GM	Yes
911401526191	BY698X G5 LED150/CW Connected WB GM	Yes
911401526291	BY698X G5 LED150/CW Connected NB GM	Yes
911401526391	BY698X G5 LED200/NW Connected WB GM	Yes
911401526491	BY698X G5 LED200/NW Connected NB GM	Yes
911401526591	BY698X G5 LED200/CW Connected WB GM	Yes
911401526691	BY698X G5 LED200/CW Connected NB GM	Yes
911401526791	BY698X G5 LED250/NW Connected WB GM	Yes
911401526891	BY698X G5 LED250/NW Connected NB GM	Yes
911401526991	BY698X G5 LED250/CW Connected WB GM	Yes
911401527091	BY698X G5 LED250/CW Connected NB GM	Yes
911401527191	BY698X G5 LED300/NW Connected WB GM	Yes
911401527291	BY698X G5 LED300/NW Connected NB GM	Yes
911401527391	BY698X G5 LED300/CW Connected WB GM	Yes
911401527491	BY698X G5 LED300/CW Connected NB GM	Yes
911401528791	BY698X G5 LED200/840 Connected WB CAU	Yes
911401528991	BY698X G5 LED200/850 Connected WB CAU	Yes
911401529391	BY698X G5 LED250/840 Connected WB CAU	Yes
911401529591	BY698X G5 LED250/850 Connected WB CAU	Yes
911401529991	BY698X G5 LED300/840 Connected WB CAU	Yes
911401530191	BY698X G5 LED300/850 Connected WB CAU	Yes

Order Code	Full Product Name	Dimmable
911401558791	BY698X G5 LED150/NW Connected WB LA	Yes
911401558891	BY698X G5 LED150/NW Connected NB LA	Yes
911401558991	BY698X G5 LED150/CW Connected WB LA	Yes
911401559091	BY698X G5 LED150/CW Connected NB LA	Yes
911401559191	BY698X G5 LED200/NW Connected WB LA	Yes
911401559291	BY698X G5 LED200/NW Connected NB LA	Yes
911401559391	BY698X G5 LED200/CW Connected WB LA	Yes
911401559491	BY698X G5 LED200/CW Connected NB LA	Yes
911401559591	BY698X G5 LED250/NW Connected WB LA	Yes
911401559691	BY698X G5 LED250/NW Connected NB LA	Yes
911401559791	BY698X G5 LED250/CW Connected WB LA	Yes
911401559891	BY698X G5 LED250/CW Connected NB LA	Yes
911401559991	BY698X G5 LED300/NW Connected WB LA	Yes
911401560091	BY698X G5 LED300/NW Connected NB LA	Yes
911401560191	BY698X G5 LED300/CW Connected WB LA	Yes
911401560291	BY698X G5 LED300/CW Connected NB LA	Yes
911401507891	BY698P G5 LED200/NW PSU WB GC	No
911401507991	BY698P G5 LED200/NW PSU NB GC	No
911401508091	BY698P G5 LED200/CW PSU WB GC	No
911401508191	BY698P G5 LED200/CW PSU NB GC	No
911401509891	BY698P G5 LED200/NW PSU WB GM	No
911401509991	BY698P G5 LED200/NW PSU NB GM	No
911401510091	BY698P G5 LED200/CW PSU WB GM	No
911401510191	BY698P G5 LED200/CW PSU NB GM	No
911401515691	BY698P G5 LED200/840 PSU WB CAU CL	No
911401515791	BY698P G5 LED200/850 PSU WB CAU CL	No
911401516591	BY698P G5 LED105/NW PSD WB GC	Yes
911401516991	BY698P G5 LED150/NW PSD WB GC	Yes
911401517191	BY698P G5 LED150/CW PSD WB GC	Yes
911401517391	BY698P G5 LED200/NW PSD WB GC	Yes
911401517491	BY698P G5 LED200/NW PSD NB GC	Yes
911401518591	BY698P G5 LED105/NW PSD WB GM	Yes
911401518691	BY698P G5 LED105/NW PSD NB GM	Yes
911401518991	BY698P G5 LED150/NW PSD WB GM	Yes
911401519091	BY698P G5 LED150/NW PSD NB GM	Yes
911401519391	BY698P G5 LED200/NW PSD WB GM	Yes
911401519491	BY698P G5 LED200/NW PSD NB GM	Yes
911401519591	BY698P G5 LED200/CW PSD WB GM	Yes

## GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401533391	BY690P LED200/NW PSU WB GM	No	911401507191	BY698P G5 LED105/NW PSU NB GC	No
911401533591	BY690P LED200/CW PSU WB GM	No	911401507291	BY698P G5 LED105/CW PSU WB GC	No
911401534502	BY690P LED200/NW PSU WB KSA	No	911401507391	BY698P G5 LED105/CW PSU NB GC	No
911401534602	BY690P LED200/NW PSU NB KSA	No	911401507491	BY698P G5 LED150/NW PSU WB GC	No
911401534702	BY690P LED200/CW PSU WB KSA	No	911401507591	BY698P G5 LED150/NW PSU NB GC	No
911401534802	BY690P LED200/CW PSU NB KSA	No	911401507691	BY698P G5 LED150/CW PSU WB GC	No
911401555191	BY698P G5 LED200/NW PSU WB LA	No	911401507791	BY698P G5 LED150/CW PSU NB GC	No
911401555291	BY698P G5 LED200/NW PSU NB LA	No	911401509091	BY698P G5 LED105/NW PSU WB GM	No
911401555391	BY698P G5 LED200/CW PSU WB LA	No	911401509291	BY698P G5 LED105/CW PSU WB GM	No
911401556591	BY698P G5 LED105/CW PSD WB LA	Yes	911401509391	BY698P G5 LED105/CW PSU NB GM	No
911401557191	BY698P G5 LED200/NW PSD WB LA	Yes	911401509491	BY698P G5 LED150/NW PSU WB GM	No
911401557391	BY698P G5 LED200/CW PSD WB LA	Yes	911401509591	BY698P G5 LED150/NW PSU NB GM	No
911401569891	BY698P G5 LED200/NW PSU WB GM L3m	No	911401509691	BY698P G5 LED150/CW PSU WB GM	No
911401569991	BY698P G5 LED200/NW PSU NB GM L3m	No	911401509791	BY698P G5 LED150/CW PSU NB GM	No
911401570091	BY698P G5 LED200/CW PSU WB GM L3m	No	911401530991	BY690P LED150/NW PSU WB GC	No
911401570191	BY698P G5 LED200/CW PSU NB GM L3m	No	911401532991	BY690P LED150/NW PSU WB GM	No
911401545502	BY698X G5 LED105/NW L1 W WB GC	Wireless Dim	911401533702	BY690P LED105/NW PSU WB KSA	No
911401545602	BY698X G5 LED105/CW L1 W WB GC	Wireless Dim	911401533802	BY690P LED105/NW PSU NB KSA	No
911401545702	BY698X G5 LED150/NW L1 W WB GC	Wireless Dim	911401533902	BY690P LED105/CW PSU WB KSA	No
911401545802	BY698X G5 LED150/CW L1 W WB GC	Wireless Dim	911401534002	BY690P LED105/CW PSU NB KSA	No
911401545902	BY698X G5 LED200/NW L1 W WB GC	Wireless Dim	911401534102	BY690P LED150/NW PSU WB KSA	No
911401546002	BY698X G5 LED200/CW L1 W WB GC	Wireless Dim	911401534202	BY690P LED150/NW PSU NB KSA	No
911401546102	BY698X G5 LED250/NW L1 W WB GC	Wireless Dim	911401534302	BY690P LED150/CW PSU WB KSA	No
911401546202	BY698X G5 LED250/CW L1 W WB GC	Wireless Dim	911401534402	BY690P LED150/CW PSU NB KSA	No
911401546302	BY698X G5 LED300/NW L1 W WB GC	Wireless Dim	911401554391	BY698P G5 LED105/NW PSU WB LA	No
911401546402	BY698X G5 LED300/CW L1 W WB GC	Wireless Dim	911401554591	BY698P G5 LED105/CW PSU WB LA	No
911401546502	BY698X G5 LED105/NW L1 W WB GM	Yes	911401554791	BY698P G5 LED150/NW PSU WB LA	No
911401546602	BY698X G5 LED105/CW L1 W WB GM	Yes	911401554991	BY698P G5 LED150/CW PSU WB LA	No
911401546702	BY698X G5 LED150/NW L1 W WB GM	Yes	911401569091	BY698P G5 LED105/NW PSU WB GM L3m	No
911401546802	BY698X G5 LED150/CW L1 W WB GM	Yes	911401569291	BY698P G5 LED105/CW PSU WB GM L3m	No
911401546902	BY698X G5 LED200/NW L1 W WB GM	Yes	911401569491	BY698P G5 LED150/NW PSU WB GM L3m	No
911401547002	BY698X G5 LED200/CW L1 W WB GM	Yes	911401569691	BY698P G5 LED150/CW PSU WB GM L3m	No
911401547102	BY698X G5 LED250/NW L1 W WB GM	Yes	911401508291	BY698P G5 LED250/NW PSU WB GC	No
911401547202	BY698X G5 LED250/CW L1 W WB GM	Yes	911401508391	BY698P G5 LED250/NW PSU NB GC	No
911401547302	BY698X G5 LED300/NW L1 W WB GM	Yes	911401508491	BY698P G5 LED250/CW PSU WB GC	No
911401547402	BY698X G5 LED300/CW L1 W WB GM	Yes	911401508591	BY698P G5 LED250/CW PSU NB GC	No
911401547502	BY698X G5 LED105/840 L1 W WB CAU	Wireless Dim	911401508691	BY698P G5 LED300/NW PSU WB GC	No
911401547602	BY698X G5 LED150/840 L1 W WB CAU	Wireless Dim	911401508791	BY698P G5 LED300/NW PSU NB GC	No
911401547702	BY698X G5 LED200/840 L1 W WB CAU	Yes	911401508891	BY698P G5 LED300/CW PSU WB GC	No
911401547802	BY698X G5 LED250/840 L1 W WB CAU	Yes	911401508991	BY698P G5 LED300/CW PSU NB GC	No
911401547902	BY698X G5 LED300/840 L1 W WB CAU	Yes	911401510291	BY698P G5 LED250/NW PSU WB GM	No
911401548002	BY698X G5 LED105/NW L1 W WB GM L3m	Wireless Dim	911401510391	BY698P G5 LED250/NW PSU NB GM	No
911401548102	BY698X G5 LED105/CW L1 W WB GM L3m	Wireless Dim	911401510491	BY698P G5 LED250/CW PSU WB GM	No
911401548202	BY698X G5 LED150/NW L1 W WB GM L3m	Wireless Dim	911401510591	BY698P G5 LED250/CW PSU NB GM	No
911401548302	BY698X G5 LED150/CW L1 W WB GM L3m	Wireless Dim	911401510691	BY698P G5 LED300/NW PSU WB GM	No
911401548402	BY698X G5 LED200/NW L1 W WB GM L3m	Wireless Dim	911401510791	BY698P G5 LED300/NW PSU NB GM	No
911401548502	BY698X G5 LED200/CW L1 W WB GM L3m	Wireless Dim	911401510891	BY698P G5 LED300/CW PSU WB GM	No
911401548602	BY698X G5 LED250/NW L1 W WB GM L3m	Wireless Dim	911401510991	BY698P G5 LED300/CW PSU NB GM	No
911401548702	BY698X G5 LED250/CW L1 W WB GM L3m	Wireless Dim	911401513891	BY698P G5 LED250/840 PSU WB CAU	No
911401548802	BY698X G5 LED300/NW L1 W WB GM L3m	Wireless Dim	911401514091	BY698P G5 LED250/850 PSU WB CAU	No
911401548902	BY698X G5 LED300/CW L1 W WB GM L3m	Wireless Dim	911401514491	BY698P G5 LED300/840 PSU WB CAU	No
911401507091	BY698P G5 LED105/NW PSU WB GC	No	911401514691	BY698P G5 LED300/850 PSU WB CAU	No

## GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable
911401515991	BY698P G5 LED250/840 PSU WB CAU CL	No
911401516091	BY698P G5 LED250/850 PSU WB CAU CL	No
911401516291	BY698P G5 LED300/840 PSU WB CAU CL	No
911401516391	BY698P G5 LED300/850 PSU WB CAU CL	No
911401517791	BY698P G5 LED250/NW PSD WB GC	Yes
911401517891	BY698P G5 LED250/NW PSD NB GC	Yes
911401517991	BY698P G5 LED250/CW PSD WB GC	Yes
911401518091	BY698P G5 LED250/CW PSD NB GC	Yes
911401518191	BY698P G5 LED300/NW PSD WB GC	Yes
911401518291	BY698P G5 LED300/NW PSD NB GC	Yes
911401518391	BY698P G5 LED300/CW PSD WB GC	Yes
911401518491	BY698P G5 LED300/CW PSD NB GC	Yes
911401519791	BY698P G5 LED250/NW PSD WB GM	Yes
911401519891	BY698P G5 LED250/NW PSD NB GM	Yes
911401519991	BY698P G5 LED250/CW PSD WB GM	Yes
911401520091	BY698P G5 LED250/CW PSD NB GM	Yes
911401520191	BY698P G5 LED300/NW PSD WB GM	Yes
911401520291	BY698P G5 LED300/NW PSD NB GM	Yes
911401520391	BY698P G5 LED300/CW PSD WB GM	Yes
911401520491	BY698P G5 LED300/CW PSD NB GM	Yes
911401522391	BY698P G5 LED250/840 PSD WB CAU	Yes
911401522591	BY698P G5 LED250/850 PSD WB CAU	Yes
911401522991	BY698P G5 LED300/840 PSD WB CAU	Yes
911401523191	BY698P G5 LED300/850 PSD WB CAU	Yes
911401531791	BY690P LED250/NW PSU WB GC	No
911401531891	BY690P LED250/NW PSU NB GC	No
911401531991	BY690P LED250/CW PSU WB GC	No
911401532091	BY690P LED250/CW PSU NB GC	No
911401532191	BY690P LED300/NW PSU WB GC	No
911401532291	BY690P LED300/NW PSU NB GC	No
911401532391	BY690P LED300/CW PSU WB GC	No
911401532491	BY690P LED300/CW PSU NB GC	No
911401533791	BY690P LED250/NW PSU WB GM	No
911401533891	BY690P LED250/NW PSU NB GM	No
911401533991	BY690P LED250/CW PSU WB GM	No
911401534091	BY690P LED250/CW PSU NB GM	No

Order Code	Full Product Name	Dimmable
911401534191	BY690P LED300/NW PSU WB GM	No
911401534291	BY690P LED300/NW PSU NB GM	No
911401534391	BY690P LED300/CW PSU WB GM	No
911401534491	BY690P LED300/CW PSU NB GM	No
911401534902	BY690P LED250/NW PSU WB KSA	No
911401535002	BY690P LED250/NW PSU NB KSA	No
911401535102	BY690P LED250/CW PSU WB KSA	No
911401535202	BY690P LED250/CW PSU NB KSA	No
911401535302	BY690P LED300/NW PSU WB KSA	No
911401535402	BY690P LED300/NW PSU NB KSA	No
911401535502	BY690P LED300/CW PSU WB KSA	No
911401535602	BY690P LED300/CW PSU NB KSA	No
911401555591	BY698P G5 LED250/NW PSU WB LA	No
911401555691	BY698P G5 LED250/NW PSU NB LA	No
911401555791	BY698P G5 LED250/CW PSU WB LA	No
911401555891	BY698P G5 LED250/CW PSU NB LA	No
911401555991	BY698P G5 LED300/NW PSU WB LA	No
911401556091	BY698P G5 LED300/NW PSU NB LA	No
911401556191	BY698P G5 LED300/CW PSU WB LA	No
911401556291	BY698P G5 LED300/CW PSU NB LA	No
911401557591	BY698P G5 LED250/NW PSD WB LA	Yes
911401557691	BY698P G5 LED250/NW PSD NB LA	Yes
911401557791	BY698P G5 LED250/CW PSD WB LA	Yes
911401557891	BY698P G5 LED250/CW PSD NB LA	Yes
911401557991	BY698P G5 LED300/NW PSD WB LA	Yes
911401558091	BY698P G5 LED300/NW PSD NB LA	Yes
911401558191	BY698P G5 LED300/CW PSD WB LA	Yes
911401558291	BY698P G5 LED300/CW PSD NB LA	Yes
911401570291	BY698P G5 LED250/NW PSU WB GM L3m	No
911401570391	BY698P G5 LED250/NW PSU NB GM L3m	No
911401570491	BY698P G5 LED250/CW PSU WB GM L3m	No
911401570591	BY698P G5 LED250/CW PSU NB GM L3m	No
911401570691	BY698P G5 LED300/NW PSU WB GM L3m	No
911401570791	BY698P G5 LED300/NW PSU NB GM L3m	No
911401570891	BY698P G5 LED300/CW PSU WB GM L3m	No
911401570991	BY698P G5 LED300/CW PSU NB GM L3m	No

### Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401523991	BY698X G5 LED150/NW Connected WB GC	Dark gray
911401524091	BY698X G5 LED150/NW Connected NB GC	Dark gray
911401524191	BY698X G5 LED150/CW Connected WB GC	Dark gray
911401524291	BY698X G5 LED150/CW Connected NB GC	Dark gray
911401524391	BY698X G5 LED200/NW Connected WB GC	Dark gray
911401524491	BY698X G5 LED200/NW Connected NB GC	Dark gray
911401524591	BY698X G5 LED200/CW Connected WB GC	Dark gray
911401524691	BY698X G5 LED200/CW Connected NB GC	Dark gray
911401524791	BY698X G5 LED250/NW Connected WB GC	Dark gray
911401524891	BY698X G5 LED250/NW Connected NB GC	Dark gray
911401524991	BY698X G5 LED250/CW Connected WB GC	Dark gray
911401525091	BY698X G5 LED250/CW Connected NB GC	Dark gray

Order Code	Full Product Name	Housing Color
911401525191	BY698X G5 LED300/NW Connected WB GC	Dark gray
911401525291	BY698X G5 LED300/NW Connected NB GC	Dark gray
911401525391	BY698X G5 LED300/CW Connected WB GC	Dark gray
911401525491	BY698X G5 LED300/CW Connected NB GC	Dark gray
911401525991	BY698X G5 LED150/NW Connected WB GM	Dark gray
911401526091	BY698X G5 LED150/NW Connected NB GM	Dark gray
911401526191	BY698X G5 LED150/CW Connected WB GM	Dark gray
911401526291	BY698X G5 LED150/CW Connected NB GM	Dark gray
911401526391	BY698X G5 LED200/NW Connected WB GM	Dark gray
911401526491	BY698X G5 LED200/NW Connected NB GM	Dark gray
911401526591	BY698X G5 LED200/CW Connected WB GM	Dark gray
911401526691	BY698X G5 LED200/CW Connected NB GM	Dark gray



## GreenPerform Highbay G5

Order Code	Full Product Name	Housing Color	Order Code	Full Product Name	Housing Color
911401526791	BY698X G5 LED250/NW Connected WB GM	Dark gray	911401533391	BY690P LED200/NW PSU WB GM	Dark gray
911401526891	BY698X G5 LED250/NW Connected NB GM	Dark gray	911401533591	BY690P LED200/CW PSU WB GM	Dark gray
911401526991	BY698X G5 LED250/CW Connected WB GM	Dark gray	911401534502	BY690P LED200/NW PSU WB KSA	Dark gray
911401527091	BY698X G5 LED250/CW Connected NB GM	Dark gray	911401534602	BY690P LED200/NW PSU NB KSA	Dark gray
911401527191	BY698X G5 LED300/NW Connected WB GM	Dark gray	911401534702	BY690P LED200/CW PSU WB KSA	Dark gray
911401527291	BY698X G5 LED300/NW Connected NB GM	Dark gray	911401534802	BY690P LED200/CW PSU NB KSA	Dark gray
911401527391	BY698X G5 LED300/CW Connected WB GM	Dark gray	911401555191	BY698P G5 LED200/NW PSU WB LA	Dark gray
911401527491	BY698X G5 LED300/CW Connected NB GM	Dark gray	911401555291	BY698P G5 LED200/NW PSU NB LA	Dark gray
911401528791	BY698X G5 LED200/840 Connected WB CAU	Dark gray	911401555391	BY698P G5 LED200/CW PSU WB LA	Dark gray
911401528991	BY698X G5 LED200/850 Connected WB CAU	Dark gray	911401555591	BY698P G5 LED105/CW PSD WB LA	Dark gray
911401529391	BY698X G5 LED250/840 Connected WB CAU	Dark gray	911401557191	BY698P G5 LED200/NW PSD WB LA	Dark gray
911401529591	BY698X G5 LED250/850 Connected WB CAU	Dark gray	911401557391	BY698P G5 LED200/CW PSD WB LA	Dark gray
911401529991	BY698X G5 LED300/840 Connected WB CAU	Dark gray	911401569891	BY698P G5 LED200/NW PSU WB GM L3m	Dark gray
911401530191	BY698X G5 LED300/850 Connected WB CAU	Dark gray	911401569991	BY698P G5 LED200/NW PSU NB GM L3m	Dark gray
911401558791	BY698X G5 LED150/NW Connected WB LA	Dark gray	911401570091	BY698P G5 LED200/CW PSU WB GM L3m	Dark gray
911401558891	BY698X G5 LED150/NW Connected NB LA	Dark gray	911401570191	BY698P G5 LED200/CW PSU NB GM L3m	Dark gray
911401558991	BY698X G5 LED150/CW Connected WB LA	Dark gray	911401545502	BY698X G5 LED105/NW L1 W WB GC	Gray
911401559091	BY698X G5 LED150/CW Connected NB LA	Dark gray	911401545602	BY698X G5 LED105/CW L1 W WB GC	Gray
911401559191	BY698X G5 LED200/NW Connected WB LA	Dark gray	911401545702	BY698X G5 LED150/NW L1 W WB GC	Gray
911401559291	BY698X G5 LED200/NW Connected NB LA	Dark gray	911401545802	BY698X G5 LED150/CW L1 W WB GC	Gray
911401559391	BY698X G5 LED200/CW Connected WB LA	Dark gray	911401545902	BY698X G5 LED200/NW L1 W WB GC	Gray
911401559491	BY698X G5 LED200/CW Connected NB LA	Dark gray	911401546002	BY698X G5 LED200/CW L1 W WB GC	Gray
911401559591	BY698X G5 LED250/NW Connected WB LA	Dark gray	911401546102	BY698X G5 LED250/NW L1 W WB GC	Gray
911401559691	BY698X G5 LED250/NW Connected NB LA	Dark gray	911401546202	BY698X G5 LED250/CW L1 W WB GC	Gray
911401559791	BY698X G5 LED250/CW Connected WB LA	Dark gray	911401546302	BY698X G5 LED300/NW L1 W WB GC	Gray
911401559891	BY698X G5 LED250/CW Connected NB LA	Dark gray	911401546402	BY698X G5 LED300/CW L1 W WB GC	Gray
911401559991	BY698X G5 LED300/NW Connected WB LA	Dark gray	911401546502	BY698X G5 LED105/NW L1 W WB GM	Gray
911401560091	BY698X G5 LED300/NW Connected NB LA	Dark gray	911401546602	BY698X G5 LED105/CW L1 W WB GM	Gray
911401560191	BY698X G5 LED300/CW Connected WB LA	Dark gray	911401546702	BY698X G5 LED150/NW L1 W WB GM	Gray
911401560291	BY698X G5 LED300/CW Connected NB LA	Dark gray	911401546802	BY698X G5 LED150/CW L1 W WB GM	Gray
911401507891	BY698P G5 LED200/NW PSU WB GC	Dark gray	911401546902	BY698X G5 LED200/NW L1 W WB GM	Gray
911401507991	BY698P G5 LED200/NW PSU NB GC	Dark gray	911401547002	BY698X G5 LED200/CW L1 W WB GM	Gray
911401508091	BY698P G5 LED200/CW PSU WB GC	Dark gray	911401547102	BY698X G5 LED250/NW L1 W WB GM	Gray
911401508191	BY698P G5 LED200/CW PSU NB GC	Dark gray	911401547202	BY698X G5 LED250/CW L1 W WB GM	Gray
911401509891	BY698P G5 LED200/NW PSU WB GM	Dark gray	911401547302	BY698X G5 LED300/NW L1 W WB GM	Gray
911401509991	BY698P G5 LED200/NW PSU NB GM	Dark gray	911401547402	BY698X G5 LED300/CW L1 W WB GM	Gray
911401510091	BY698P G5 LED200/CW PSU WB GM	Dark gray	911401547502	BY698X G5 LED105/840 L1 W WB CAU	Gray
911401510191	BY698P G5 LED200/CW PSU NB GM	Dark gray	911401547602	BY698X G5 LED150/840 L1 W WB CAU	Gray
911401515691	BY698P G5 LED200/840 PSU WB CAU CL	Dark gray	911401547702	BY698X G5 LED200/840 L1 W WB CAU	Gray
911401515791	BY698P G5 LED200/850 PSU WB CAU CL	Dark gray	911401547802	BY698X G5 LED250/840 L1 W WB CAU	Gray
911401516591	BY698P G5 LED105/NW PSD WB GC	Dark gray	911401547902	BY698X G5 LED300/840 L1 W WB CAU	Gray
911401516991	BY698P G5 LED150/NW PSD WB GC	Dark gray	911401548002	BY698X G5 LED105/NW L1 W WB GM L3m	Gray
911401517191	BY698P G5 LED150/CW PSD WB GC	Dark gray	911401548102	BY698X G5 LED105/CW L1 W WB GM L3m	Gray
911401517391	BY698P G5 LED200/NW PSD WB GC	Dark gray	911401548202	BY698X G5 LED150/NW L1 W WB GM L3m	Gray
911401517491	BY698P G5 LED200/NW PSD NB GC	Dark gray	911401548302	BY698X G5 LED150/CW L1 W WB GM L3m	Gray
911401518591	BY698P G5 LED105/NW PSD WB GM	Dark gray	911401548402	BY698X G5 LED200/NW L1 W WB GM L3m	Gray
911401518691	BY698P G5 LED105/NW PSD NB GM	Dark gray	911401548502	BY698X G5 LED200/CW L1 W WB GM L3m	Gray
911401518991	BY698P G5 LED150/NW PSD WB GM	Dark gray	911401548602	BY698X G5 LED250/NW L1 W WB GM L3m	Gray
911401519091	BY698P G5 LED150/NW PSD NB GM	Dark gray	911401548702	BY698X G5 LED250/CW L1 W WB GM L3m	Gray
911401519391	BY698P G5 LED200/NW PSD WB GM	Dark gray	911401548802	BY698X G5 LED300/NW L1 W WB GM L3m	Gray
911401519491	BY698P G5 LED200/NW PSD NB GM	Dark gray	911401548902	BY698X G5 LED300/CW L1 W WB GM L3m	Gray
911401519591	BY698P G5 LED200/CW PSD WB GM	Dark gray	911401507091	BY698P G5 LED105/NW PSU WB GC	Dark gray

## GreenPerform Highbay G5

Order Code	Full Product Name	Housing Color	Order Code	Full Product Name	Housing Color
911401507191	BY698P G5 LED105/NW PSU NB GC	Dark gray	911401515991	BY698P G5 LED250/840 PSU WB CAU CL	Dark gray
911401507291	BY698P G5 LED105/CW PSU WB GC	Dark gray	911401516091	BY698P G5 LED250/850 PSU WB CAU CL	Dark gray
911401507391	BY698P G5 LED105/CW PSU NB GC	Dark gray	911401516291	BY698P G5 LED300/840 PSU WB CAU CL	Dark gray
911401507491	BY698P G5 LED150/NW PSU WB GC	Dark gray	911401516391	BY698P G5 LED300/850 PSU WB CAU CL	Dark gray
911401507591	BY698P G5 LED150/NW PSU NB GC	Dark gray	911401517791	BY698P G5 LED250/NW PSD WB GC	Dark gray
911401507691	BY698P G5 LED150/CW PSU WB GC	Dark gray	911401517891	BY698P G5 LED250/NW PSD NB GC	Dark gray
911401507791	BY698P G5 LED150/CW PSU NB GC	Dark gray	911401517991	BY698P G5 LED250/CW PSD WB GC	Dark gray
911401509091	BY698P G5 LED105/NW PSU WB GM	Dark gray	911401518091	BY698P G5 LED250/CW PSD NB GC	Dark gray
911401509291	BY698P G5 LED105/CW PSU WB GM	Dark gray	911401518191	BY698P G5 LED300/NW PSD WB GC	Dark gray
911401509391	BY698P G5 LED105/CW PSU NB GM	Dark gray	911401518291	BY698P G5 LED300/NW PSD NB GC	Dark gray
911401509491	BY698P G5 LED150/NW PSU WB GM	Dark gray	911401518391	BY698P G5 LED300/CW PSD WB GC	Dark gray
911401509591	BY698P G5 LED150/NW PSU NB GM	Dark gray	911401518491	BY698P G5 LED300/CW PSD NB GC	Dark gray
911401509691	BY698P G5 LED150/CW PSU WB GM	Dark gray	911401519791	BY698P G5 LED250/NW PSD WB GM	Dark gray
911401509791	BY698P G5 LED150/CW PSU NB GM	Dark gray	911401519891	BY698P G5 LED250/NW PSD NB GM	Dark gray
911401530991	BY690P LED150/NW PSU WB GC	Dark gray	911401519991	BY698P G5 LED250/CW PSD WB GM	Dark gray
911401532991	BY690P LED150/NW PSU WB GM	Dark gray	911401520091	BY698P G5 LED250/CW PSD NB GM	Dark gray
911401533702	BY690P LED105/NW PSU WB KSA	Dark gray	911401520191	BY698P G5 LED300/NW PSD WB GM	Dark gray
911401533802	BY690P LED105/NW PSU NB KSA	Dark gray	911401520291	BY698P G5 LED300/NW PSD NB GM	Dark gray
911401533902	BY690P LED105/CW PSU WB KSA	Dark gray	911401520391	BY698P G5 LED300/CW PSD WB GM	Dark gray
911401534002	BY690P LED105/CW PSU NB KSA	Dark gray	911401520491	BY698P G5 LED300/CW PSD NB GM	Dark gray
911401534102	BY690P LED150/NW PSU WB KSA	Dark gray	911401522391	BY698P G5 LED250/840 PSD WB CAU	Dark gray
911401534202	BY690P LED150/NW PSU NB KSA	Dark gray	911401522591	BY698P G5 LED250/850 PSD WB CAU	Dark gray
911401534302	BY690P LED150/CW PSU WB KSA	Dark gray	911401522991	BY698P G5 LED300/840 PSD WB CAU	Dark gray
911401534402	BY690P LED150/CW PSU NB KSA	Dark gray	911401523191	BY698P G5 LED300/850 PSD WB CAU	Dark gray
911401554391	BY698P G5 LED105/NW PSU WB LA	Dark gray	911401531791	BY690P LED250/NW PSU WB GC	Dark gray
911401554591	BY698P G5 LED105/CW PSU WB LA	Dark gray	911401531891	BY690P LED250/NW PSU NB GC	Dark gray
911401554791	BY698P G5 LED150/NW PSU WB LA	Dark gray	911401531991	BY690P LED250/CW PSU WB GC	Dark gray
911401554991	BY698P G5 LED150/CW PSU WB LA	Dark gray	911401532091	BY690P LED250/CW PSU NB GC	Dark gray
911401569091	BY698P G5 LED105/NW PSU WB GM L3m	Dark gray	911401532191	BY690P LED300/NW PSU WB GC	Dark gray
911401569291	BY698P G5 LED105/CW PSU WB GM L3m	Dark gray	911401532291	BY690P LED300/NW PSU NB GC	Dark gray
911401569491	BY698P G5 LED150/NW PSU WB GM L3m	Dark gray	911401532391	BY690P LED300/CW PSU WB GC	Dark gray
911401569691	BY698P G5 LED150/CW PSU WB GM L3m	Dark gray	911401532491	BY690P LED300/CW PSU NB GC	Dark gray
911401508291	BY698P G5 LED250/NW PSU WB GC	Dark gray	911401533791	BY690P LED250/NW PSU WB GM	Dark gray
911401508391	BY698P G5 LED250/NW PSU NB GC	Dark gray	911401533891	BY690P LED250/NW PSU NB GM	Dark gray
911401508491	BY698P G5 LED250/CW PSU WB GC	Dark gray	911401533991	BY690P LED250/CW PSU WB GM	Dark gray
911401508591	BY698P G5 LED250/CW PSU NB GC	Dark gray	911401534091	BY690P LED250/CW PSU NB GM	Dark gray
911401508691	BY698P G5 LED300/NW PSU WB GC	Dark gray	911401534191	BY690P LED300/NW PSU WB GM	Dark gray
911401508791	BY698P G5 LED300/NW PSU NB GC	Dark gray	911401534291	BY690P LED300/NW PSU NB GM	Dark gray
911401508891	BY698P G5 LED300/CW PSU WB GC	Dark gray	911401534391	BY690P LED300/CW PSU WB GM	Dark gray
911401508991	BY698P G5 LED300/CW PSU NB GC	Dark gray	911401534491	BY690P LED300/CW PSU NB GM	Dark gray
911401510291	BY698P G5 LED250/NW PSU WB GM	Dark gray	911401534902	BY690P LED250/NW PSU WB KSA	Dark gray
911401510391	BY698P G5 LED250/NW PSU NB GM	Dark gray	911401535002	BY690P LED250/NW PSU NB KSA	Dark gray
911401510491	BY698P G5 LED250/CW PSU WB GM	Dark gray	911401535102	BY690P LED250/CW PSU WB KSA	Dark gray
911401510591	BY698P G5 LED250/CW PSU NB GM	Dark gray	911401535202	BY690P LED250/CW PSU NB KSA	Dark gray
911401510691	BY698P G5 LED300/NW PSU WB GM	Dark gray	911401535302	BY690P LED300/NW PSU WB KSA	Dark gray
911401510791	BY698P G5 LED300/NW PSU NB GM	Dark gray	911401535402	BY690P LED300/NW PSU NB KSA	Dark gray
911401510891	BY698P G5 LED300/CW PSU WB GM	Dark gray	911401535502	BY690P LED300/CW PSU WB KSA	Dark gray
911401510991	BY698P G5 LED300/CW PSU NB GM	Dark gray	911401535602	BY690P LED300/CW PSU NB KSA	Dark gray
911401513891	BY698P G5 LED250/840 PSU WB CAU	Dark gray	911401555591	BY698P G5 LED250/NW PSU WB LA	Dark gray
911401514091	BY698P G5 LED250/850 PSU WB CAU	Dark gray	911401555691	BY698P G5 LED250/NW PSU NB LA	Dark gray
911401514491	BY698P G5 LED300/840 PSU WB CAU	Dark gray	911401555791	BY698P G5 LED250/CW PSU WB LA	Dark gray
911401514691	BY698P G5 LED300/850 PSU WB CAU	Dark gray	911401555891	BY698P G5 LED250/CW PSU NB LA	Dark gray

## GreenPerform Highbay G5

Order Code	Full Product Name	Housing Color
911401555991	BY698P G5 LED300/NW PSU WB LA	Dark gray
911401556091	BY698P G5 LED300/NW PSU NB LA	Dark gray
911401556191	BY698P G5 LED300/CW PSU WB LA	Dark gray
911401556291	BY698P G5 LED300/CW PSU NB LA	Dark gray
911401557591	BY698P G5 LED250/NW PSD WB LA	Dark gray
911401557691	BY698P G5 LED250/NW PSD NB LA	Dark gray
911401557791	BY698P G5 LED250/CW PSD WB LA	Dark gray
911401557891	BY698P G5 LED250/CW PSD NB LA	Dark gray
911401557991	BY698P G5 LED300/NW PSD WB LA	Dark gray
911401558091	BY698P G5 LED300/NW PSD NB LA	Dark gray

Order Code	Full Product Name	Housing Color
911401558191	BY698P G5 LED300/CW PSD WB LA	Dark gray
911401558291	BY698P G5 LED300/CW PSD NB LA	Dark gray
911401570291	BY698P G5 LED250/NW PSU WB GM L3m	Dark gray
911401570391	BY698P G5 LED250/NW PSU NB GM L3m	Dark gray
911401570491	BY698P G5 LED250/CW PSU WB GM L3m	Dark gray
911401570591	BY698P G5 LED250/CW PSU NB GM L3m	Dark gray
911401570691	BY698P G5 LED300/NW PSU WB GM L3m	Dark gray
911401570791	BY698P G5 LED300/NW PSU NB GM L3m	Dark gray
911401570891	BY698P G5 LED300/CW PSU WB GM L3m	Dark gray
911401570991	BY698P G5 LED300/CW PSU NB GM L3m	Dark gray

### Approval and Application

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401523991	BY698X G5 LED150/NW Connected WB GC	IK05	IP65
911401524091	BY698X G5 LED150/NW Connected NB GC	IK05	IP65
911401524191	BY698X G5 LED150/CW Connected WB GC	IK05	IP65
911401524291	BY698X G5 LED150/CW Connected NB GC	IK05	IP65
911401524391	BY698X G5 LED200/NW Connected WB GC	IK05	IP65
911401524491	BY698X G5 LED200/NW Connected NB GC	IK05	IP65
911401524591	BY698X G5 LED200/CW Connected WB GC	IK05	IP65
911401524691	BY698X G5 LED200/CW Connected NB GC	IK05	IP65
911401524791	BY698X G5 LED250/NW Connected WB GC	IK05	IP65
911401524891	BY698X G5 LED250/NW Connected NB GC	IK05	IP65
911401524991	BY698X G5 LED250/CW Connected WB GC	IK05	IP65
911401525091	BY698X G5 LED250/CW Connected NB GC	IK05	IP65
911401525191	BY698X G5 LED300/NW Connected WB GC	IK05	IP65
911401525291	BY698X G5 LED300/NW Connected NB GC	IK05	IP65
911401525391	BY698X G5 LED300/CW Connected WB GC	IK05	IP65
911401525491	BY698X G5 LED300/CW Connected NB GC	IK05	IP65
911401525991	BY698X G5 LED150/NW Connected WB GM	IK05	IP65
911401526091	BY698X G5 LED150/NW Connected NB GM	IK05	IP65

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401526191	BY698X G5 LED150/CW Connected WB GM	IK05	IP65
911401526291	BY698X G5 LED150/CW Connected NB GM	IK05	IP65
911401526391	BY698X G5 LED200/NW Connected WB GM	IK05	IP65
911401526491	BY698X G5 LED200/NW Connected NB GM	IK05	IP65
911401526591	BY698X G5 LED200/CW Connected WB GM	IK05	IP65
911401526691	BY698X G5 LED200/CW Connected NB GM	IK05	IP65
911401526791	BY698X G5 LED250/NW Connected WB GM	IK05	IP65
911401526891	BY698X G5 LED250/NW Connected NB GM	IK05	IP65
911401526991	BY698X G5 LED250/CW Connected WB GM	IK05	IP65
911401527091	BY698X G5 LED250/CW Connected NB GM	IK05	IP65
911401527191	BY698X G5 LED300/NW Connected WB GM	IK05	IP65
911401527291	BY698X G5 LED300/NW Connected NB GM	IK05	IP65
911401527391	BY698X G5 LED300/CW Connected WB GM	IK05	IP65
911401527491	BY698X G5 LED300/CW Connected NB GM	IK05	IP65
911401528791	BY698X G5 LED200/840 Connected WB CAU	IK05	IP65
911401528991	BY698X G5 LED200/850 Connected WB CAU	IK05	IP65
911401529391	BY698X G5 LED250/840 Connected WB CAU	IK05	IP65
911401529591	BY698X G5 LED250/850 Connected WB CAU	IK05	IP65

# GreenPerform Highbay G5

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401529991	BY698X G5 LED300/840 Connected WB CAU	IK05	IP65
911401530191	BY698X G5 LED300/850 Connected WB CAU	IK05	IP65
911401558791	BY698X G5 LED150/NW Connected WB LA	IK05	IP65
911401558891	BY698X G5 LED150/NW Connected NB LA	IK05	IP65
911401558991	BY698X G5 LED150/CW Connected WB LA	IK05	IP65
911401559091	BY698X G5 LED150/CW Connected NB LA	IK05	IP65
911401559191	BY698X G5 LED200/NW Connected WB LA	IK05	IP65
911401559291	BY698X G5 LED200/NW Connected NB LA	IK05	IP65
911401559391	BY698X G5 LED200/CW Connected WB LA	IK05	IP65
911401559491	BY698X G5 LED200/CW Connected NB LA	IK05	IP65
911401559591	BY698X G5 LED250/NW Connected WB LA	IK05	IP65
911401559691	BY698X G5 LED250/NW Connected NB LA	IK05	IP65
911401559791	BY698X G5 LED250/CW Connected WB LA	IK05	IP65
911401559891	BY698X G5 LED250/CW Connected NB LA	IK05	IP65
911401559991	BY698X G5 LED300/NW Connected WB LA	IK05	IP65
911401560091	BY698X G5 LED300/NW Connected NB LA	IK05	IP65
911401560191	BY698X G5 LED300/CW Connected WB LA	IK05	IP65
911401560291	BY698X G5 LED300/CW Connected NB LA	IK05	IP65
911401507891	BY698P G5 LED200/NW PSU WB GC	IK08	IP65
911401507991	BY698P G5 LED200/NW PSU NB GC	IK08	IP65
911401508091	BY698P G5 LED200/CW PSU WB GC	IK08	IP65
911401508191	BY698P G5 LED200/CW PSU NB GC	IK08	IP65
911401509891	BY698P G5 LED200/NW PSU WB GM	IK08	IP65
911401509991	BY698P G5 LED200/NW PSU NB GM	IK08	IP65
911401510091	BY698P G5 LED200/CW PSU WB GM	IK08	IP65
911401510191	BY698P G5 LED200/CW PSU NB GM	IK08	IP65
911401515691	BY698P G5 LED200/840 PSU WB CAU CL	IK08	IP65
911401515791	BY698P G5 LED200/850 PSU WB CAU CL	IK08	IP65
9114015156591	BY698P G5 LED105/NW PSD WB GC	IK08	IP65
9114015156991	BY698P G5 LED150/NW PSD WB GC	IK08	IP65

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401517191	BY698P G5 LED150/CW PSD WB GC	IK08	IP65
911401517391	BY698P G5 LED200/NW PSD WB GC	IK08	IP65
911401517491	BY698P G5 LED200/NW PSD NB GC	IK08	IP65
911401518591	BY698P G5 LED105/NW PSD WB GM	IK08	IP65
911401518691	BY698P G5 LED105/NW PSD NB GM	IK08	IP65
911401518991	BY698P G5 LED150/NW PSD WB GM	IK08	IP65
911401519091	BY698P G5 LED150/NW PSD NB GM	IK08	IP65
911401519391	BY698P G5 LED200/NW PSD WB GM	IK08	IP65
911401519491	BY698P G5 LED200/NW PSD NB GM	IK08	IP65
911401519591	BY698P G5 LED200/CW PSD WB GM	IK08	IP65
911401533391	BY690P LED200/NW PSU WB GM	IK08	IP66
911401533591	BY690P LED200/CW PSU WB GM	IK08	IP66
911401534502	BY690P LED200/NW PSU WB KSA	IK08	IP66
911401534602	BY690P LED200/NW PSU NB KSA	IK08	IP66
911401534702	BY690P LED200/CW PSU WB KSA	IK08	IP66
911401534802	BY690P LED200/CW PSU NB KSA	IK08	IP66
911401555191	BY698P G5 LED200/NW PSU WB LA	IK08	IP65
911401555291	BY698P G5 LED200/NW PSU NB LA	IK08	IP65
911401555391	BY698P G5 LED200/CW PSU WB LA	IK08	IP65
9114015556591	BY698P G5 LED105/CW PSD WB LA	IK08	IP65
911401557191	BY698P G5 LED200/NW PSD WB LA	IK08	IP65
911401557391	BY698P G5 LED200/CW PSD WB LA	IK08	IP65
911401569891	BY698P G5 LED200/NW PSU WB GM L3m	IK08	IP65
911401569991	BY698P G5 LED200/NW PSU NB GM L3m	IK08	IP65
911401570091	BY698P G5 LED200/CW PSU WB GM L3m	IK08	IP65
911401570191	BY698P G5 LED200/CW PSU NB GM L3m	IK08	IP65
911401545502	BY698X G5 LED105/NW L1 W WB GC	IK08	IP65
911401545602	BY698X G5 LED105/CW L1 W WB GC	IK08	IP65
911401545702	BY698X G5 LED150/NW L1 W WB GC	IK08	IP65
911401545802	BY698X G5 LED150/CW L1 W WB GC	IK08	IP65
911401545902	BY698X G5 LED200/NW L1 W WB GC	IK08	IP65
911401546002	BY698X G5 LED200/CW L1 W WB GC	IK08	IP65
911401546102	BY698X G5 LED250/NW L1 W WB GC	IK08	IP65
911401546202	BY698X G5 LED250/CW L1 W WB GC	IK08	IP65
911401546302	BY698X G5 LED300/NW L1 W WB GC	IK08	IP65
911401546402	BY698X G5 LED300/CW L1 W WB GC	IK08	IP65
911401546502	BY698X G5 LED105/NW L1 W WB GM	IK08	IP65
911401546602	BY698X G5 LED105/CW L1 W WB GM	IK08	IP65
911401546702	BY698X G5 LED150/NW L1 W WB GM	IK08	IP65
911401546802	BY698X G5 LED150/CW L1 W WB GM	IK08	IP65
911401546902	BY698X G5 LED200/NW L1 W WB GM	IK08	IP65
911401547002	BY698X G5 LED200/CW L1 W WB GM	IK08	IP65
911401547102	BY698X G5 LED250/NW L1 W WB GM	IK08	IP65
911401547202	BY698X G5 LED250/CW L1 W WB GM	IK08	IP65
911401547302	BY698X G5 LED300/NW L1 W WB GM	IK08	IP65
911401547402	BY698X G5 LED300/CW L1 W WB GM	IK08	IP65

# GreenPerform Highbay G5

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401547502	BY698X G5 LED105/840 L1 W WB CAU	IK08	IP65
911401547602	BY698X G5 LED150/840 L1 W WB CAU	IK08	IP65
911401547702	BY698X G5 LED200/840 L1 W WB CAU	IK08	IP65
911401547802	BY698X G5 LED250/840 L1 W WB CAU	IK08	IP65
911401547902	BY698X G5 LED300/840 L1 W WB CAU	IK08	IP65
911401548002	BY698X G5 LED105/NW L1 W WB GM L3m	IK08	IP65
911401548102	BY698X G5 LED105/CW L1 W WB GM L3m	IK08	IP65
911401548202	BY698X G5 LED150/NW L1 W WB GM L3m	IK08	IP65
911401548302	BY698X G5 LED150/CW L1 W WB GM L3m	IK08	IP65
911401548402	BY698X G5 LED200/NW L1 W WB GM L3m	IK08	IP65
911401548502	BY698X G5 LED200/CW L1 W WB GM L3m	IK08	IP65
911401548602	BY698X G5 LED250/NW L1 W WB GM L3m	IK08	IP65
911401548702	BY698X G5 LED250/CW L1 W WB GM L3m	IK08	IP65
911401548802	BY698X G5 LED300/NW L1 W WB GM L3m	IK08	IP65
911401548902	BY698X G5 LED300/CW L1 W WB GM L3m	IK08	IP65
911401507091	BY698P G5 LED105/NW PSU WB GC	IK08	IP65
911401507191	BY698P G5 LED105/NW PSU NB GC	IK08	IP65
911401507291	BY698P G5 LED105/CW PSU WB GC	IK08	IP65
911401507391	BY698P G5 LED105/CW PSU NB GC	IK08	IP65
911401507491	BY698P G5 LED150/NW PSU WB GC	IK08	IP65
911401507591	BY698P G5 LED150/NW PSU NB GC	IK08	IP65
911401507691	BY698P G5 LED150/CW PSU WB GC	IK08	IP65
911401507791	BY698P G5 LED150/CW PSU NB GC	IK08	IP65
911401509091	BY698P G5 LED105/NW PSU WB GM	IK08	IP65
911401509291	BY698P G5 LED105/CW PSU WB GM	IK08	IP65
911401509391	BY698P G5 LED105/CW PSU NB GM	IK08	IP65
911401509491	BY698P G5 LED150/NW PSU WB GM	IK08	IP65
911401509591	BY698P G5 LED150/NW PSU NB GM	IK08	IP65
911401509691	BY698P G5 LED150/CW PSU WB GM	IK08	IP65
911401509791	BY698P G5 LED150/CW PSU NB GM	IK08	IP65
911401530991	BY690P LED150/NW PSU WB GC	IK08	IP66
911401532991	BY690P LED150/NW PSU WB GM	IK08	IP66
911401533702	BY690P LED105/NW PSU WB KSA	IK08	IP66
911401533802	BY690P LED105/NW PSU NB KSA	IK08	IP66
911401533902	BY690P LED105/CW PSU WB KSA	IK08	IP66
911401534002	BY690P LED105/CW PSU NB KSA	IK08	IP66
911401534102	BY690P LED150/NW PSU WB KSA	IK08	IP66
911401534202	BY690P LED150/NW PSU NB KSA	IK08	IP66
911401534302	BY690P LED150/CW PSU WB KSA	IK08	IP66
911401534402	BY690P LED150/CW PSU NB KSA	IK08	IP66

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401554391	BY698P G5 LED105/NW PSU WB LA	IK08	IP65
911401554591	BY698P G5 LED105/CW PSU WB LA	IK08	IP65
911401554791	BY698P G5 LED150/NW PSU WB LA	IK08	IP65
911401554991	BY698P G5 LED150/CW PSU WB LA	IK08	IP65
911401569091	BY698P G5 LED105/NW PSU WB GM L3m	IK08	IP65
911401569291	BY698P G5 LED105/CW PSU WB GM L3m	IK08	IP65
911401569491	BY698P G5 LED150/NW PSU WB GM L3m	IK08	IP65
911401569691	BY698P G5 LED150/CW PSU WB GM L3m	IK08	IP65
911401508291	BY698P G5 LED250/NW PSU WB GC	IK08	IP65
911401508391	BY698P G5 LED250/NW PSU NB GC	IK08	IP65
911401508491	BY698P G5 LED250/CW PSU WB GC	IK08	IP65
911401508591	BY698P G5 LED250/CW PSU NB GC	IK08	IP65
911401508691	BY698P G5 LED300/NW PSU WB GC	IK08	IP65
911401508791	BY698P G5 LED300/NW PSU NB GC	IK08	IP65
911401508891	BY698P G5 LED300/CW PSU WB GC	IK08	IP65
911401508991	BY698P G5 LED300/CW PSU NB GC	IK08	IP65
911401510291	BY698P G5 LED250/NW PSU WB GM	IK08	IP65
911401510391	BY698P G5 LED250/NW PSU NB GM	IK08	IP65
911401510491	BY698P G5 LED250/CW PSU WB GM	IK08	IP65
911401510591	BY698P G5 LED250/CW PSU NB GM	IK08	IP65
911401510691	BY698P G5 LED300/NW PSU WB GM	IK08	IP65
911401510791	BY698P G5 LED300/NW PSU NB GM	IK08	IP65
911401510891	BY698P G5 LED300/CW PSU WB GM	IK08	IP65
911401510991	BY698P G5 LED300/CW PSU NB GM	IK08	IP65
911401513891	BY698P G5 LED250/840 PSU WB CAU	IK08	IP65
911401514091	BY698P G5 LED250/850 PSU WB CAU	IK08	IP65
911401514491	BY698P G5 LED300/840 PSU WB CAU	IK08	IP65
911401514691	BY698P G5 LED300/850 PSU WB CAU	IK08	IP65
911401515991	BY698P G5 LED250/840 PSU WB CAU CL	IK08	IP65
911401516091	BY698P G5 LED250/850 PSU WB CAU CL	IK08	IP65
911401516291	BY698P G5 LED300/840 PSU WB CAU CL	IK08	IP65
911401516391	BY698P G5 LED300/850 PSU WB CAU CL	IK08	IP65
911401517791	BY698P G5 LED250/NW PSD WB GC	IK08	IP65
911401517891	BY698P G5 LED250/NW PSD NB GC	IK08	IP65
911401517991	BY698P G5 LED250/CW PSD WB GC	IK08	IP65
911401518091	BY698P G5 LED250/CW PSD NB GC	IK08	IP65
911401518191	BY698P G5 LED300/NW PSD WB GC	IK08	IP65
911401518291	BY698P G5 LED300/NW PSD NB GC	IK08	IP65
911401518391	BY698P G5 LED300/CW PSD WB GC	IK08	IP65
911401518491	BY698P G5 LED300/CW PSD NB GC	IK08	IP65
911401519791	BY698P G5 LED250/NW PSD WB GM	IK08	IP65
911401519891	BY698P G5 LED250/NW PSD NB GM	IK08	IP65

# GreenPerform Highbay G5

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401519991	BY698P G5 LED250/CW PSD WB GM	IK08	IP65
911401520091	BY698P G5 LED250/CW PSD NB GM	IK08	IP65
911401520191	BY698P G5 LED300/NW PSD WB GM	IK08	IP65
911401520291	BY698P G5 LED300/NW PSD NB GM	IK08	IP65
911401520391	BY698P G5 LED300/CW PSD WB GM	IK08	IP65
911401520491	BY698P G5 LED300/CW PSD NB GM	IK08	IP65
911401522391	BY698P G5 LED250/840 PSD WB CAU	IK08	IP65
911401522591	BY698P G5 LED250/850 PSD WB CAU	IK08	IP65
911401522991	BY698P G5 LED300/840 PSD WB CAU	IK08	IP65
911401523191	BY698P G5 LED300/850 PSD WB CAU	IK08	IP65
911401531791	BY690P LED250/NW PSU WB GC	IK08	IP66
911401531891	BY690P LED250/NW PSU NB GC	IK08	IP66
911401531991	BY690P LED250/CW PSU WB GC	IK08	IP66
911401532091	BY690P LED250/CW PSU NB GC	IK08	IP66
911401532191	BY690P LED300/NW PSU WB GC	IK08	IP66
911401532291	BY690P LED300/NW PSU NB GC	IK08	IP66
911401532391	BY690P LED300/CW PSU WB GC	IK08	IP66
911401532491	BY690P LED300/CW PSU NB GC	IK08	IP66
911401533791	BY690P LED250/NW PSU WB GM	IK08	IP66
911401533891	BY690P LED250/NW PSU NB GM	IK08	IP66
911401533991	BY690P LED250/CW PSU WB GM	IK08	IP66
911401534091	BY690P LED250/CW PSU NB GM	IK08	IP66
911401534191	BY690P LED300/NW PSU WB GM	IK08	IP66
911401534291	BY690P LED300/NW PSU NB GM	IK08	IP66
911401534391	BY690P LED300/CW PSU WB GM	IK08	IP66
911401534491	BY690P LED300/CW PSU NB GM	IK08	IP66
911401534902	BY690P LED250/NW PSU WB KSA	IK08	IP66
911401535002	BY690P LED250/NW PSU NB KSA	IK08	IP66
911401535102	BY690P LED250/CW PSU WB KSA	IK08	IP66
911401535202	BY690P LED250/CW PSU NB KSA	IK08	IP66
911401535302	BY690P LED300/NW PSU WB KSA	IK08	IP66
911401535402	BY690P LED300/NW PSU NB KSA	IK08	IP66
911401535502	BY690P LED300/CW PSU WB KSA	IK08	IP66

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401535602	BY690P LED300/CW PSU NB KSA	IK08	IP66
911401555591	BY698P G5 LED250/NW PSU WB LA	IK08	IP65
911401555691	BY698P G5 LED250/NW PSU NB LA	IK08	IP65
911401555791	BY698P G5 LED250/CW PSU WB LA	IK08	IP65
911401555891	BY698P G5 LED250/CW PSU NB LA	IK08	IP65
911401555991	BY698P G5 LED300/NW PSU WB LA	IK08	IP65
911401556091	BY698P G5 LED300/NW PSU NB LA	IK08	IP65
911401556191	BY698P G5 LED300/CW PSU WB LA	IK08	IP65
911401556291	BY698P G5 LED300/CW PSU NB LA	IK08	IP65
911401557591	BY698P G5 LED250/NW PSD WB LA	IK08	IP65
911401557691	BY698P G5 LED250/NW PSD NB LA	IK08	IP65
911401557791	BY698P G5 LED250/CW PSD WB LA	IK08	IP65
911401557891	BY698P G5 LED250/CW PSD NB LA	IK08	IP65
911401557991	BY698P G5 LED300/NW PSD WB LA	IK08	IP65
911401558091	BY698P G5 LED300/NW PSD NB LA	IK08	IP65
911401558191	BY698P G5 LED300/CW PSD WB LA	IK08	IP65
911401558291	BY698P G5 LED300/CW PSD NB LA	IK08	IP65
911401570291	BY698P G5 LED250/NW PSU WB GM L3m	IK08	IP65
911401570391	BY698P G5 LED250/NW PSU NB GM L3m	IK08	IP65
911401570491	BY698P G5 LED250/CW PSU WB GM L3m	IK08	IP65
911401570591	BY698P G5 LED250/CW PSU NB GM L3m	IK08	IP65
911401570691	BY698P G5 LED300/NW PSU WB GM L3m	IK08	IP65
911401570791	BY698P G5 LED300/NW PSU NB GM L3m	IK08	IP65
911401570891	BY698P G5 LED300/CW PSU WB GM L3m	IK08	IP65
911401570991	BY698P G5 LED300/CW PSU NB GM L3m	IK08	IP65

## Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401523991	BY698X G5 LED150/NW Connected WB GC	(0.385, 0.380) SDCM<5
911401524091	BY698X G5 LED150/NW Connected NB GC	(0.385, 0.380) SDCM<5
911401524191	BY698X G5 LED150/CW Connected WB GC	(0.316, 0.332) SDCM<5
911401524291	BY698X G5 LED150/CW Connected NB GC	(0.316, 0.332) SDCM<5
911401524391	BY698X G5 LED200/NW Connected WB GC	(0.385, 0.380) SDCM<5
911401524491	BY698X G5 LED200/NW Connected NB GC	(0.385, 0.380) SDCM<5
911401524591	BY698X G5 LED200/CW Connected WB GC	(0.316, 0.332) SDCM<5
911401524691	BY698X G5 LED200/CW Connected NB GC	(0.316, 0.332) SDCM<5
911401524791	BY698X G5 LED250/NW Connected WB GC	(0.385, 0.380) SDCM<5
911401524891	BY698X G5 LED250/NW Connected NB GC	(0.385, 0.380) SDCM<5
911401524991	BY698X G5 LED250/CW Connected WB GC	(0.316, 0.332) SDCM<5
911401525091	BY698X G5 LED250/CW Connected NB GC	(0.316, 0.332) SDCM<5
911401525191	BY698X G5 LED300/NW Connected WB GC	(0.385, 0.380) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401525291	BY698X G5 LED300/NW Connected NB GC	(0.385, 0.380) SDCM<5
911401525391	BY698X G5 LED300/CW Connected WB GC	(0.316, 0.332) SDCM<5
911401525491	BY698X G5 LED300/CW Connected NB GC	(0.316, 0.332) SDCM<5
911401525991	BY698X G5 LED150/NW Connected WB GM	(0.385, 0.380) SDCM<5
911401526091	BY698X G5 LED150/NW Connected NB GM	(0.385, 0.380) SDCM<5
911401526191	BY698X G5 LED150/CW Connected WB GM	(0.316, 0.332) SDCM<5
911401526291	BY698X G5 LED150/CW Connected NB GM	(0.316, 0.332) SDCM<5
911401526391	BY698X G5 LED200/NW Connected WB GM	(0.385, 0.380) SDCM<5
911401526491	BY698X G5 LED200/NW Connected NB GM	(0.385, 0.380) SDCM<5
911401526591	BY698X G5 LED200/CW Connected WB GM	(0.316, 0.332) SDCM<5
911401526691	BY698X G5 LED200/CW Connected NB GM	(0.316, 0.332) SDCM<5
911401526791	BY698X G5 LED250/NW Connected WB GM	(0.385, 0.380) SDCM<5
911401526891	BY698X G5 LED250/NW Connected NB GM	(0.385, 0.380) SDCM<5

## GreenPerform Highbay G5

Order Code	Full Product Name	Initial chromaticity	Order Code	Full Product Name	Initial chromaticity
911401526991	BY698X G5 LED250/CW Connected WB GM	(0.316, 0.332) SDCM<5	911401534502	BY690P LED200/NW PSU WB KSA	(0.385, 0.380) SDCM<5
911401527091	BY698X G5 LED250/CW Connected NB GM	(0.316, 0.332) SDCM<5	911401534602	BY690P LED200/NW PSU NB KSA	(0.385, 0.380) SDCM<5
911401527191	BY698X G5 LED300/NW Connected WB GM	(0.385, 0.380) SDCM<5	911401534702	BY690P LED200/CW PSU WB KSA	(0.316, 0.332) SDCM<5
911401527291	BY698X G5 LED300/NW Connected NB GM	(0.385, 0.380) SDCM<5	911401534802	BY690P LED200/CW PSU NB KSA	(0.316, 0.332) SDCM<5
911401527391	BY698X G5 LED300/CW Connected WB GM	(0.316, 0.332) SDCM<5	911401555191	BY698P G5 LED200/NW PSU WB LA	(0.385, 0.380) SDCM<5
911401527491	BY698X G5 LED300/CW Connected NB GM	(0.316, 0.332) SDCM<5	911401555291	BY698P G5 LED200/NW PSU NB LA	(0.385, 0.380) SDCM<5
911401528791	BY698X G5 LED200/840 Connected WB CAU	(0.385, 0.380) SDCM<5	911401555391	BY698P G5 LED200/CW PSU WB LA	(0.316, 0.332) SDCM<5
911401528991	BY698X G5 LED200/850 Connected WB CAU	(0.346, 0.356) SDCM<5	911401556591	BY698P G5 LED105/CW PSD WB LA	(0.316, 0.332) SDCM<5
911401529391	BY698X G5 LED250/840 Connected WB CAU	(0.385, 0.380) SDCM<5	911401557191	BY698P G5 LED200/NW PSD WB LA	(0.385, 0.380) SDCM<5
911401529591	BY698X G5 LED250/850 Connected WB CAU	(0.346, 0.356) SDCM<5	911401557391	BY698P G5 LED200/CW PSD WB LA	(0.316, 0.332) SDCM<5
911401529991	BY698X G5 LED300/840 Connected WB CAU	(0.385, 0.380) SDCM<5	911401569891	BY698P G5 LED200/NW PSU WB GM L3m	(0.385, 0.380) SDCM<5
911401530191	BY698X G5 LED300/850 Connected WB CAU	(0.346, 0.356) SDCM<5	911401569991	BY698P G5 LED200/NW PSU NB GM L3m	(0.385, 0.380) SDCM<5
911401558791	BY698X G5 LED150/NW Connected WB LA	(0.385, 0.380) SDCM<5	911401570091	BY698P G5 LED200/CW PSU WB GM L3m	(0.316, 0.332) SDCM<5
911401558891	BY698X G5 LED150/NW Connected NB LA	(0.385, 0.380) SDCM<5	911401570191	BY698P G5 LED200/CW PSU NB GM L3m	(0.316, 0.332) SDCM<5
911401558991	BY698X G5 LED150/CW Connected WB LA	(0.316, 0.332) SDCM<5	911401545502	BY698X G5 LED105/NW L1 W WB GC	(0.385, 0.380) SDCM<5
911401559091	BY698X G5 LED150/CW Connected NB LA	(0.316, 0.332) SDCM<5	911401545602	BY698X G5 LED105/CW L1 W WB GC	(0.316, 0.332) SDCM<5
911401559191	BY698X G5 LED200/NW Connected WB LA	(0.385, 0.380) SDCM<5	911401545702	BY698X G5 LED150/NW L1 W WB GC	(0.385, 0.380) SDCM<5
911401559291	BY698X G5 LED200/NW Connected NB LA	(0.385, 0.380) SDCM<5	911401545802	BY698X G5 LED150/CW L1 W WB GC	(0.316, 0.332) SDCM<5
911401559391	BY698X G5 LED200/CW Connected WB LA	(0.316, 0.332) SDCM<5	911401545902	BY698X G5 LED200/NW L1 W WB GC	(0.385, 0.380) SDCM<5
911401559491	BY698X G5 LED200/CW Connected NB LA	(0.316, 0.332) SDCM<5	911401546002	BY698X G5 LED200/CW L1 W WB GC	(0.316, 0.332) SDCM<5
911401559591	BY698X G5 LED250/NW Connected WB LA	(0.385, 0.380) SDCM<5	911401546102	BY698X G5 LED250/NW L1 W WB GC	(0.385, 0.380) SDCM<5
911401559691	BY698X G5 LED250/NW Connected NB LA	(0.385, 0.380) SDCM<5	911401546202	BY698X G5 LED250/CW L1 W WB GC	(0.316, 0.332) SDCM<5
911401559791	BY698X G5 LED250/CW Connected WB LA	(0.316, 0.332) SDCM<5	911401546302	BY698X G5 LED300/NW L1 W WB GC	(0.385, 0.380) SDCM<5
911401559891	BY698X G5 LED250/CW Connected NB LA	(0.316, 0.332) SDCM<5	911401546402	BY698X G5 LED300/CW L1 W WB GC	(0.316, 0.332) SDCM<5
911401559991	BY698X G5 LED300/NW Connected WB LA	(0.385, 0.380) SDCM<5	911401546502	BY698X G5 LED105/NW L1 W WB GM	(0.385, 0.380) SDCM<5
911401560091	BY698X G5 LED300/NW Connected NB LA	(0.385, 0.380) SDCM<5	911401546602	BY698X G5 LED105/CW L1 W WB GM	(0.316, 0.332) SDCM<5
911401560191	BY698X G5 LED300/CW Connected WB LA	(0.316, 0.332) SDCM<5	911401546702	BY698X G5 LED150/NW L1 W WB GM	(0.385, 0.380) SDCM<5
911401560291	BY698X G5 LED300/CW Connected NB LA	(0.316, 0.332) SDCM<5	911401546802	BY698X G5 LED150/CW L1 W WB GM	(0.316, 0.332) SDCM<5
911401507891	BY698P G5 LED200/NW PSU WB GC	(0.385, 0.380) SDCM<5	911401546902	BY698X G5 LED200/NW L1 W WB GM	(0.385, 0.380) SDCM<5
911401507991	BY698P G5 LED200/NW PSU NB GC	(0.385, 0.380) SDCM<5	911401547002	BY698X G5 LED200/CW L1 W WB GM	(0.316, 0.332) SDCM<5
911401508091	BY698P G5 LED200/CW PSU WB GC	(0.316, 0.332) SDCM<5	911401547102	BY698X G5 LED250/NW L1 W WB GM	(0.385, 0.380) SDCM<5
911401508191	BY698P G5 LED200/CW PSU NB GC	(0.316, 0.332) SDCM<5	911401547202	BY698X G5 LED250/CW L1 W WB GM	(0.316, 0.332) SDCM<5
911401509891	BY698P G5 LED200/NW PSU WB GM	(0.385, 0.380) SDCM<5	911401547302	BY698X G5 LED300/NW L1 W WB GM	(0.385, 0.380) SDCM<5
911401509991	BY698P G5 LED200/NW PSU NB GM	(0.385, 0.380) SDCM<5	911401547402	BY698X G5 LED300/CW L1 W WB GM	(0.316, 0.332) SDCM<5
911401510091	BY698P G5 LED200/CW PSU WB GM	(0.316, 0.332) SDCM<5	911401547502	BY698X G5 LED105/840 L1 W WB CAU	(0.385, 0.380) SDCM<5
911401510191	BY698P G5 LED200/CW PSU NB GM	(0.316, 0.332) SDCM<5	911401547602	BY698X G5 LED150/840 L1 W WB CAU	(0.385, 0.380) SDCM<5
911401515691	BY698P G5 LED200/840 PSU WB CAU CL	(0.385, 0.380) SDCM<5	911401547702	BY698X G5 LED200/840 L1 W WB CAU	(0.385, 0.380) SDCM<5
911401515791	BY698P G5 LED200/850 PSU WB CAU CL	(0.346, 0.356) SDCM<5	911401547802	BY698X G5 LED250/840 L1 W WB CAU	(0.385, 0.380) SDCM<5
911401516591	BY698P G5 LED105/NW PSD WB GC	(0.385, 0.380) SDCM<5	911401547902	BY698X G5 LED300/840 L1 W WB CAU	(0.385, 0.380) SDCM<5
911401516991	BY698P G5 LED150/NW PSD WB GC	(0.385, 0.380) SDCM<5	911401548002	BY698X G5 LED105/NW L1 W WB GM L3m	(0.385, 0.380) SDCM<5
911401517191	BY698P G5 LED150/CW PSD WB GC	(0.316, 0.332) SDCM<5	911401548102	BY698X G5 LED105/CW L1 W WB GM L3m	(0.316, 0.332) SDCM<5
911401517391	BY698P G5 LED200/NW PSD WB GC	(0.385, 0.380) SDCM<5	911401548202	BY698X G5 LED150/NW L1 W WB GM L3m	(0.385, 0.380) SDCM<5
911401517491	BY698P G5 LED200/NW PSD NB GC	(0.385, 0.380) SDCM<5	911401548302	BY698X G5 LED150/CW L1 W WB GM L3m	(0.316, 0.332) SDCM<5
911401518591	BY698P G5 LED105/NW PSD WB GM	(0.385, 0.380) SDCM<5	911401548402	BY698X G5 LED200/NW L1 W WB GM L3m	(0.385, 0.380) SDCM<5
911401518691	BY698P G5 LED105/NW PSD NB GM	(0.385, 0.380) SDCM<5	911401548502	BY698X G5 LED200/CW L1 W WB GM L3m	(0.316, 0.332) SDCM<5
911401518991	BY698P G5 LED150/NW PSD WB GM	(0.385, 0.380) SDCM<5	911401548602	BY698X G5 LED250/NW L1 W WB GM L3m	(0.385, 0.380) SDCM<5
911401519091	BY698P G5 LED150/NW PSD NB GM	(0.385, 0.380) SDCM<5	911401548702	BY698X G5 LED250/CW L1 W WB GM L3m	(0.316, 0.332) SDCM<5
911401519391	BY698P G5 LED200/NW PSD WB GM	(0.385, 0.380) SDCM<5	911401548802	BY698X G5 LED300/NW L1 W WB GM L3m	(0.385, 0.380) SDCM<5
911401519491	BY698P G5 LED200/NW PSD NB GM	(0.385, 0.380) SDCM<5	911401548902	BY698X G5 LED300/CW L1 W WB GM L3m	(0.316, 0.332) SDCM<5
911401519591	BY698P G5 LED200/CW PSD WB GM	(0.316, 0.332) SDCM<5	911401507091	BY698P G5 LED105/NW PSU WB GC	(0.385, 0.380) SDCM<5
911401533391	BY690P LED200/NW PSU WB GM	(0.385, 0.380) SDCM<5	911401507191	BY698P G5 LED105/NW PSU NB GC	(0.385, 0.380) SDCM<5
911401533591	BY690P LED200/CW PSU WB GM	(0.316, 0.332) SDCM<5	911401507291	BY698P G5 LED105/CW PSU WB GC	(0.316, 0.332) SDCM<5

## GreenPerform Highbay G5

Order Code	Full Product Name	Initial chromaticity	Order Code	Full Product Name	Initial chromaticity
911401507391	BY698P G5 LED105/CW PSU NB GC	(0.316, 0.332) SDCM<5	911401516291	BY698P G5 LED300/840 PSU WB CAU CL	(0.385, 0.380) SDCM<5
911401507491	BY698P G5 LED150/NW PSU WB GC	(0.385, 0.380) SDCM<5	911401516391	BY698P G5 LED300/850 PSU WB CAU CL	(0.346, 0.356) SDCM<5
911401507591	BY698P G5 LED150/NW PSU NB GC	(0.385, 0.380) SDCM<5	911401517791	BY698P G5 LED250/NW PSD WB GC	(0.385, 0.380) SDCM<5
911401507691	BY698P G5 LED150/CW PSU WB GC	(0.316, 0.332) SDCM<5	911401517891	BY698P G5 LED250/NW PSD NB GC	(0.385, 0.380) SDCM<5
911401507791	BY698P G5 LED150/CW PSU NB GC	(0.316, 0.332) SDCM<5	911401517991	BY698P G5 LED250/CW PSD WB GC	(0.316, 0.332) SDCM<5
911401509091	BY698P G5 LED105/NW PSU WB GM	(0.385, 0.380) SDCM<5	911401518091	BY698P G5 LED250/CW PSD NB GC	(0.316, 0.332) SDCM<5
911401509291	BY698P G5 LED105/CW PSU WB GM	(0.316, 0.332) SDCM<5	911401518191	BY698P G5 LED300/NW PSD WB GC	(0.385, 0.380) SDCM<5
911401509391	BY698P G5 LED105/CW PSU NB GM	(0.316, 0.332) SDCM<5	911401518291	BY698P G5 LED300/NW PSD NB GC	(0.385, 0.380) SDCM<5
911401509491	BY698P G5 LED150/NW PSU WB GM	(0.385, 0.380) SDCM<5	911401518391	BY698P G5 LED300/CW PSD WB GC	(0.316, 0.332) SDCM<5
911401509591	BY698P G5 LED150/NW PSU NB GM	(0.385, 0.380) SDCM<5	911401518491	BY698P G5 LED300/CW PSD NB GC	(0.316, 0.332) SDCM<5
911401509691	BY698P G5 LED150/CW PSU WB GM	(0.316, 0.332) SDCM<5	911401519791	BY698P G5 LED250/NW PSD WB GM	(0.385, 0.380) SDCM<5
911401509791	BY698P G5 LED150/CW PSU NB GM	(0.316, 0.332) SDCM<5	911401519891	BY698P G5 LED250/NW PSD NB GM	(0.385, 0.380) SDCM<5
911401530991	BY690P LED150/NW PSU WB GC	(0.385, 0.380) SDCM<5	911401519991	BY698P G5 LED250/CW PSD WB GM	(0.316, 0.332) SDCM<5
911401532991	BY690P LED150/NW PSU WB GM	(0.385, 0.380) SDCM<5	911401520091	BY698P G5 LED250/CW PSD NB GM	(0.316, 0.332) SDCM<5
911401533702	BY690P LED105/NW PSU WB KSA	(0.385, 0.380) SDCM<5	911401520191	BY698P G5 LED300/NW PSD WB GM	(0.385, 0.380) SDCM<5
911401533802	BY690P LED105/NW PSU NB KSA	(0.385, 0.380) SDCM<5	911401520291	BY698P G5 LED300/NW PSD NB GM	(0.385, 0.380) SDCM<5
911401533902	BY690P LED105/CW PSU WB KSA	(0.316, 0.332) SDCM<5	911401520391	BY698P G5 LED300/CW PSD WB GM	(0.316, 0.332) SDCM<5
911401534002	BY690P LED105/CW PSU NB KSA	(0.316, 0.332) SDCM<5	911401520491	BY698P G5 LED300/CW PSD NB GM	(0.316, 0.332) SDCM<5
911401534102	BY690P LED150/NW PSU WB KSA	(0.385, 0.380) SDCM<5	911401522391	BY698P G5 LED250/840 PSD WB CAU	(0.385, 0.380) SDCM<5
911401534202	BY690P LED150/NW PSU NB KSA	(0.385, 0.380) SDCM<5	911401522591	BY698P G5 LED250/850 PSD WB CAU	(0.346, 0.356) SDCM<5
911401534302	BY690P LED150/CW PSU WB KSA	(0.316, 0.332) SDCM<5	911401522991	BY698P G5 LED300/840 PSD WB CAU	(0.385, 0.380) SDCM<5
911401534402	BY690P LED150/CW PSU NB KSA	(0.316, 0.332) SDCM<5	911401523191	BY698P G5 LED300/850 PSD WB CAU	(0.346, 0.356) SDCM<5
911401554391	BY698P G5 LED105/NW PSU WB LA	(0.385, 0.380) SDCM<5	911401531791	BY690P LED250/NW PSU WB GC	(0.385, 0.380) SDCM<5
911401554591	BY698P G5 LED105/CW PSU WB LA	(0.316, 0.332) SDCM<5	911401531891	BY690P LED250/NW PSU NB GC	(0.385, 0.380) SDCM<5
911401554791	BY698P G5 LED150/NW PSU WB LA	(0.385, 0.380) SDCM<5	911401531991	BY690P LED250/CW PSU WB GC	(0.316, 0.332) SDCM<5
911401554991	BY698P G5 LED150/CW PSU WB LA	(0.316, 0.332) SDCM<5	911401532091	BY690P LED250/CW PSU NB GC	(0.316, 0.332) SDCM<5
911401569091	BY698P G5 LED105/NW PSU WB GM L3m	(0.385, 0.380) SDCM<5	911401532191	BY690P LED300/NW PSU WB GC	(0.385, 0.380) SDCM<5
911401569291	BY698P G5 LED105/CW PSU WB GM L3m	(0.316, 0.332) SDCM<5	911401532291	BY690P LED300/NW PSU NB GC	(0.385, 0.380) SDCM<5
911401569491	BY698P G5 LED150/NW PSU WB GM L3m	(0.385, 0.380) SDCM<5	911401532391	BY690P LED300/CW PSU WB GC	(0.316, 0.332) SDCM<5
911401569691	BY698P G5 LED150/CW PSU WB GM L3m	(0.316, 0.332) SDCM<5	911401532491	BY690P LED300/CW PSU NB GC	(0.316, 0.332) SDCM<5
911401508291	BY698P G5 LED250/NW PSU WB GC	(0.385, 0.380) SDCM<5	911401533791	BY690P LED250/NW PSU WB GM	(0.385, 0.380) SDCM<5
911401508391	BY698P G5 LED250/NW PSU NB GC	(0.385, 0.380) SDCM<5	911401533891	BY690P LED250/NW PSU NB GM	(0.385, 0.380) SDCM<5
911401508491	BY698P G5 LED250/CW PSU WB GC	(0.316, 0.332) SDCM<5	911401533991	BY690P LED250/CW PSU WB GM	(0.316, 0.332) SDCM<5
911401508591	BY698P G5 LED250/CW PSU NB GC	(0.316, 0.332) SDCM<5	911401534091	BY690P LED250/CW PSU NB GM	(0.316, 0.332) SDCM<5
911401508691	BY698P G5 LED300/NW PSU WB GC	(0.385, 0.380) SDCM<5	911401534191	BY690P LED300/NW PSU WB GM	(0.385, 0.380) SDCM<5
911401508791	BY698P G5 LED300/NW PSU NB GC	(0.385, 0.380) SDCM<5	911401534291	BY690P LED300/NW PSU NB GM	(0.385, 0.380) SDCM<5
911401508891	BY698P G5 LED300/CW PSU WB GC	(0.316, 0.332) SDCM<5	911401534391	BY690P LED300/CW PSU WB GM	(0.316, 0.332) SDCM<5
911401508991	BY698P G5 LED300/CW PSU NB GC	(0.316, 0.332) SDCM<5	911401534491	BY690P LED300/CW PSU NB GM	(0.316, 0.332) SDCM<5
911401510291	BY698P G5 LED250/NW PSU WB GM	(0.385, 0.380) SDCM<5	911401534902	BY690P LED250/NW PSU WB KSA	(0.385, 0.380) SDCM<5
911401510391	BY698P G5 LED250/NW PSU NB GM	(0.385, 0.380) SDCM<5	911401535002	BY690P LED250/NW PSU NB KSA	(0.385, 0.380) SDCM<5
911401510491	BY698P G5 LED250/CW PSU WB GM	(0.316, 0.332) SDCM<5	911401535102	BY690P LED250/CW PSU WB KSA	(0.316, 0.332) SDCM<5
911401510591	BY698P G5 LED250/CW PSU NB GM	(0.316, 0.332) SDCM<5	911401535202	BY690P LED250/CW PSU NB KSA	(0.316, 0.332) SDCM<5
911401510691	BY698P G5 LED300/NW PSU WB GM	(0.385, 0.380) SDCM<5	911401535302	BY690P LED300/NW PSU WB KSA	(0.385, 0.380) SDCM<5
911401510791	BY698P G5 LED300/NW PSU NB GM	(0.385, 0.380) SDCM<5	911401535402	BY690P LED300/NW PSU NB KSA	(0.385, 0.380) SDCM<5
911401510891	BY698P G5 LED300/CW PSU WB GM	(0.316, 0.332) SDCM<5	911401535502	BY690P LED300/CW PSU WB KSA	(0.316, 0.332) SDCM<5
911401510991	BY698P G5 LED300/CW PSU NB GM	(0.316, 0.332) SDCM<5	911401535602	BY690P LED300/CW PSU NB KSA	(0.316, 0.332) SDCM<5
911401513891	BY698P G5 LED250/840 PSU WB CAU	(0.385, 0.380) SDCM<5	911401555591	BY698P G5 LED250/NW PSU WB LA	(0.385, 0.380) SDCM<5
911401514091	BY698P G5 LED250/850 PSU WB CAU	(0.346, 0.356) SDCM<5	911401555691	BY698P G5 LED250/NW PSU NB LA	(0.385, 0.380) SDCM<5
911401514491	BY698P G5 LED300/840 PSU WB CAU	(0.385, 0.380) SDCM<5	911401555791	BY698P G5 LED250/CW PSU WB LA	(0.316, 0.332) SDCM<5
911401514691	BY698P G5 LED300/850 PSU WB CAU	(0.346, 0.356) SDCM<5	911401555891	BY698P G5 LED250/CW PSU NB LA	(0.316, 0.332) SDCM<5
911401515991	BY698P G5 LED250/840 PSU WB CAU CL	(0.385, 0.380) SDCM<5	911401555991	BY698P G5 LED300/NW PSU WB LA	(0.385, 0.380) SDCM<5
911401516091	BY698P G5 LED250/850 PSU WB CAU CL	(0.346, 0.356) SDCM<5	911401556091	BY698P G5 LED300/NW PSU NB LA	(0.385, 0.380) SDCM<5



## GreenPerform Highbay G5

Order Code	Full Product Name	Initial chromaticity
911401556191	BY698P G5 LED300/CW PSU WB LA	(0.316, 0.332) SDCM<5
911401556291	BY698P G5 LED300/CW PSU NB LA	(0.316, 0.332) SDCM<5
911401557591	BY698P G5 LED250/NW PSD WB LA	(0.385, 0.380) SDCM<5
911401557691	BY698P G5 LED250/NW PSD NB LA	(0.385, 0.380) SDCM<5
911401557791	BY698P G5 LED250/CW PSD WB LA	(0.316, 0.332) SDCM<5
911401557891	BY698P G5 LED250/CW PSD NB LA	(0.316, 0.332) SDCM<5
911401557991	BY698P G5 LED300/NW PSD WB LA	(0.385, 0.380) SDCM<5
911401558091	BY698P G5 LED300/NW PSD NB LA	(0.385, 0.380) SDCM<5
911401558191	BY698P G5 LED300/CW PSD WB LA	(0.316, 0.332) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401558291	BY698P G5 LED300/CW PSD NB LA	(0.316, 0.332) SDCM<5
911401570291	BY698P G5 LED250/NW PSU WB GM L3m	(0.385, 0.380) SDCM<5
911401570391	BY698P G5 LED250/NW PSU NB GM L3m	(0.385, 0.380) SDCM<5
911401570491	BY698P G5 LED250/CW PSU WB GM L3m	(0.316, 0.332) SDCM<5
911401570591	BY698P G5 LED250/CW PSU NB GM L3m	(0.316, 0.332) SDCM<5
911401570691	BY698P G5 LED300/NW PSU WB GM L3m	(0.385, 0.380) SDCM<5
911401570791	BY698P G5 LED300/NW PSU NB GM L3m	(0.385, 0.380) SDCM<5
911401570891	BY698P G5 LED300/CW PSU WB GM L3m	(0.316, 0.332) SDCM<5
911401570991	BY698P G5 LED300/CW PSU NB GM L3m	(0.316, 0.332) SDCM<5

