



# UVC Disinfection Batten

## TMS160C 1X36W TUV SLV/6 R

1 pc - 223 to 240 V - 53 or 60 Hz - Safety class I - Finger-protected - 0.2 J standard

The UV-C batten is designed for the disinfection of surfaces and is suitable for a wide range of applications. The UV-C batten provides universal UV-C irradiance with homogenous distribution. Its disinfection capability is based on wattage used and a specific exposure time for a given distance from that surface. No person should be present at the time of usage, due to high risk of harm to eyes and skin. The performance is enhanced by a highly-reflective and durable aluminum body, which improves its efficacy even further and directs the UV-C light to the to-be-irradiated surfaces. The lamp holders and end caps are protected against UV-C thanks to dedicated shielding. There is a 1- and 2-lamp version available, for both the bare batten and reflector batten. This offers even a greater flexibility.

# UVC Disinfection Batten

## Warnings and Safety

- DANGER: Risk Group 3 UV product. Like any disinfection system, UV-C devices must be installed and used in the correct way. Direct exposure to UV-C can be dangerous and result in a sunburn-like reaction to the skin and serious damage to the cornea. As UV-C is invisible to the eye, the UV-C batten must be installed with adequate safeguards to ensure that the UV-C batten can be operated in a safe way. The UV-C battens are only to be used as components in a system that consists of adequate safeguards such as, but not limited to, those indicated in the mounting instruction and/or user manual.
- Philips UV-C products must only be sold through qualified partners and installed by professionals according to our stringent safety and legal requirements. Our UV-C products are not meant to be used in applications or activities which may cause and/or lead to death, personal injury and/or damage to the environment.
- The UV-C battens' effectiveness in the inactivation of certain viruses, bacteria, protozoa, fungi or other harmful micro-organisms is as described under "Benefits". Signify and its group of companies do not promise or warrant that the use of UV-C battens will protect or prevent any user from infection and/or contamination with any harmful micro-organisms, illness or disease. The UV-C battens are not approved for, are not intended and must not be used as medical devices, as such term may be defined under the applicable laws of the countries in which the battens are made available. In addition to and without limitation of any exclusions or limitations of liability of Signify and its group of companies as set forth in any agreement for sale, distribution or otherwise making available of the UV-C battens, Signify and its group of companies shall have no responsibility or liability whatsoever for any claim or damage that may arise from or relate to any use of the UV-C battens outside of their intended use or contrary to their installation and operation instructions, each as described under "Application", the user manual and/or the mounting instruction.

## Product data

General information	
Number of light sources	1 pc
Beam angle of light source	- °
Number of gear units	1 unit
Gear	HFP [ HF Performer]
Optic type	-
Luminaire light beam spread	-
Control interface	-
Connection	Screw connection block 3-pole
Cable	-
Protection class IEC	Safety class I
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	CE mark
ENEC mark	-
Warranty period	1 years
Number of products on MCB of 16 A type B	28
EU RoHS compliant	Yes

## Operating and electrical

Input Voltage	223 to 240 V
Input Frequency	53 or 60 Hz
Inrush current	18 A
Inrush time	0.25 ms
Power Factor (Min)	0.95

## Controls and dimming

Dimmable	No
----------	----

## Mechanical and housing

Housing Material	Steel
------------------	-------

Reflector material	Aluminum
Optic material	Aluminum
Mounting device	Surface & Suspended (Asymmetric/ Symmetric)
Overall length	1230 mm
Overall width	162 mm
Overall height	80 mm
Color	White and black
Dimensions (Height x Width x Depth)	80 x 162 x 1230 mm

## Approval and application

Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]

## UV

UV-C radiation	12.5 W
UV-C irradiance defined at 0.2m	57.6 µW/cm <sup>2</sup>

## Initial performance (IEC compliant)

Initial input power	36 W
Power consumption tolerance	+/-10%

## Application conditions

Ambient temperature range	-10 to +45 °C
Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No


## Product data

Full product code	911401524571
Order product name	TMS160C 1X36W TUV SLV/6 R


# UVC Disinfection Batten

Order code	911401524571
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	911401524571

Net Weight (Piece)	1.366 kg
--------------------	----------



## Dimensional drawing



TMS160C 1X36W TUV SLV/6 R

