



# UniStrip G4

## BCP384 24LED RGB 220V 45 L50 DMX D2

UniStrip G4, 2010 lm, 40 W, Red, green and blue, Dynamic DMX, Safety class I

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### Warnings and Safety

- For outdoor use only

### Product data

General Information		Optical cover type	
Driver included	Yes	Tempered glass	
Lighting Technology		Operating and Electrical	
Lighting Technology	LED	Input Voltage	220 to 240 V
CE mark	CE mark	Line Frequency	50 to 60 Hz
Flammability mark	For mounting on normally flammable surfaces	Inrush current	60 A
Light Technical		Power Consumption	40 W
Luminous Flux	2,010 lm	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	-	Connection	Flying leads/wires and 2 Push-in connector 4-pole
Luminous Efficacy (rated) (Nom)	50 lm/W		
Color rendering index (CRI)	-		
Light source color	Red, green and blue		

# UniStrip G4

<b>Cable</b>	Cable 0.3 m without plug 3-pole + 2 Cables 0.3 m with connector 4-pole
--------------	--

## Temperature

<b>Ambient temperature range</b>	-40 to +50 °C
----------------------------------	---------------

## Controls and Dimming

<b>Dimmable</b>	Yes
<b>Control interface</b>	Dynamic DMX

## Mechanical and Housing

<b>Housing Material</b>	Aluminum extruded
<b>Optical cover material</b>	Polymethyl methacrylate
<b>Housing Color</b>	Dark gray
<b>Effective projected area</b>	0.085 m <sup>2</sup>

## Approval and Application

<b>Ingress protection code</b>	IP66 [Dust penetration-protected, jet-proof]
<b>Mech. impact protection code</b>	IK06 [1 J]

<b>Protection class IEC</b>	Safety class I
-----------------------------	----------------

## Initial Performance (IEC Compliant)

<b>Luminous flux tolerance</b>	+/-10%
<b>Power consumption tolerance</b>	+/-10%

## Product Data

<b>Order product name</b>	BCP384 24LED RGB 220V 45 L50 DMX D2
<b>Full product name</b>	BCP384 24LED RGB 220V 45 L50 DMX D2
<b>Full product code</b>	871951492207599
<b>Order code</b>	911401736583
<b>Material Nr. (12NC)</b>	911401736583
<b>Numerator - Quantity Per Pack</b>	1
<b>EAN/UPC - Product/Case</b>	8719514922075
<b>Numerator - Packs per outer box</b>	4
<b>EAN/UPC - Case</b>	8719514922075

## Dimensional drawing

