



# UniStrip G4

## BCP385 24LED 30K 220V 7 L52 DMX D3

UniStrip G4 - 3048 lm - 50 W - 3000 K

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications.;One family that fits all your needs, wall washing, grazing and also linear flood lighting.;The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution.;Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### Warnings and Safety

- For outdoor use only

### Product data

General Information		Input Frequency	
Light source color	Warm white	Input Frequency	50 to 60 Hz
Driver included	Yes	Inrush current	60 A
Optical cover/lens type	Tempered glass	Power Factor (Min)	0.9
Control interface	Dynamix DMX	<b>Controls and Dimming</b>	
Connection	Flying leads/wires and 2 Push-in connector 4-pole	Dimmable	Yes
Cable	Cable 0.3 m without plug 3-pole + 2 Cables 0.3 m with connector 4-pole	<b>Mechanical and Housing</b>	
Protection class IEC	Safety class I	Housing Material	Aluminum extruded
Flammability mark	For mounting on normally flammable surfaces	Optical cover/lens material	Polymethyl methacrylate
CE mark	CE mark	Effective projected area	0.135 m <sup>2</sup>
<b>Operating and Electrical</b>		Color	Dark gray
Input Voltage	220 to 240 V		

# UniStrip G4

## Approval and Application

Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [ 1 J]

## Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	3048 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	61 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	80
Initial chromaticity	SDCM = 4
Initial input power	50 W
Power consumption tolerance	+/-10%

## Application Conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Product Data

Full product code	871951492223599
Order product name	BCP385 24LED 30K 220V 7 L52 DMX D3
EAN/UPC - Product	8719514922235
Order code	911401736823
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	911401736823
Net Weight (Piece)	2.099 kg



## Dimensional drawing



## Floodlight surface LED

