



CoreLine Recessed Spot gen2

RS150Z CFRM SQR-ADJUST D80 ALU

CoreLine Recessed Spot gen2, Accessory, Aluminum, Aluminum, 0.3 J

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows “configure to fit” option that better responds to your specific needs. The range offers a wide range choice on light color (CCT), light output, color finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing through-wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy makes CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

Product data

General Information		Line Frequency	
Angle	20°		- Hz
Accessory color	Aluminum	Mechanical and Housing	
Value ladder	Performance	Overall length	95 mm
Operating and Electrical		Overall width	95 mm
Input Voltage	- V	Overall height	29 mm
		Dimensions (Height x Width x Depth)	29 x 95 x 95 mm

CoreLine Recessed Spot gen2

Material	Aluminum
Approval and Application	
Ingress protection code	-
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	-
Product Data	
Order product name	RS150Z CFRM SQR-ADJUST D80 ALU
Full product name	RS150Z CFRM SQR-ADJUST D80 ALU

Full product code	871951493851999
Order code	911401812084
Material Nr. (12NC)	911401812084
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514938519
Numerator - Packs per outer box	18
EAN/UPC - Case	8719514938625

