



Ledinaire panel

RC065B G5 41S/840 PSU W60L60 OC CFW

Ledinaire panel, 34 W, 600x600 mm, VPC, 4100 lm, 4000 K, UGR19

The Philips Ledinaire panel Gen5 (RC065B/RC066B) range features a selection of popular off-the-shelf LED luminaires that offer Philips high quality at a competitive price. Reliable, energy-efficient and affordable, this latest generation of 600 x 600 mm, 620 x 620 mm, 300 x 1200 mm, and 600 x 1200 Ledinaire LED panel lights are designed for diffuse, comfortable lighting in a wide range of general lighting applications. Our range of Ledinaire panels lighting is also available with accessories for easy installation on different types of ceilings—just what you need.

Product data

General Information		Color rendering index (CRI)	
Number of gear units	1 unit		80
Driver included	Yes	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Value ladder	Value	Beam angle of light source	90 degree(s)
CE mark	CE mark	Light source color	840 neutral white
Warranty period	3 years	Optic type	Beam angle 90°
Flammability mark	For mounting on normally flammable surfaces	Luminaire light beam spread	90°
ENEC mark	-	Unified glare rating CEN	19
Glow-wire test	Temperature 650 °C, duration 30 s	Operating and Electrical	
EU RoHS compliant	Yes	Input Voltage	220 to 240 V
Light Technical		Line Frequency	50 or 60 Hz
Luminous Flux	4,100 lm	Inrush current	22 A
Correlated Color Temperature (Nom)	4000 K	Inrush time	0.25 ms
Luminous Efficacy (rated) (Nom)	120 lm/W	Power Consumption	34 W
		Power Factor (Fraction)	0.9

Ledinaire panel

Connection	Flying leads/wires
Cable	2x0.75mm ²
Number of products on MCB of 16 A type B	10
Temperature	
Ambient temperature range	-10 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Steel
Reflector material	Acrylate
Optic material	Polystyrene
Optical cover material	Acrylate
Fixation material	-
Housing Color	White
Optical cover finish	Microprismatic lens
Overall length	595 mm
Overall width	595 mm
Overall height	60 mm
Dimensions (Height x Width x Depth)	60 x 595 x 595 mm
Compatible ceiling or ceiling installation accessory type	Visible profile ceiling version
Approval and Application	
Ingress protection code	IP20/40 [Finger-protected, Emitting surface]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Photobiological risk specification	0.2 m
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38, 0.38) SDCM ≤5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life	7.5 %
50000 h	
Lumen maintenance at median useful life*	L80
50000 h	
Lumen maintenance at median useful life*	L70
75000 h	


Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Not applicable

Product Data

Order product name	RC065B G5 41S/840 PSU W60L60 OC CFW
Full product name	RC065B G5 41S/840 PSU W60L60 OC CFW
Full product code	872016951660199
Order code	911401876085
Material Nr. (12NC)	911401876085
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169516601
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169516830

Dimensional drawing



Ledinaire panel

