



# Xitanium LED linear drivers – non-isolated

## Xitanium 35W 0.08-0.35A 220V TD11 230V

Xitanium linear non-isolated drivers are ideal for high voltage (HV) professional general lighting applications. The range includes DALI dimmable and programmable, 1-10V dimmable, non-dimmable and single current versions. They offer high efficiency, good quality of light and full flexibility. The new generation of 16mm DALI drivers offer ultimate performance. They comply with the latest DiiA standards, including implementation of the new DALI parts related to data. Configuring the drivers can be done quickly and wirelessly with SimpleSet. The new 21mm DALI drivers offer the best value for money.

### Product data

General Information	
Lighting Technology	LED

  

Operating and Electrical	
Output Current (Max)	350 mA
Output Power (Max)	35 W
Output Power (Min)	10 W
Output Current (Min)	80 mA
Output Voltage (Max)	220 V
Output Voltage (Min)	50 V

  

Mechanical and Housing	
Housing	Office 280x30x11 7p4p NFC

  

Product Data	
Full product code	871869681963000
Order product name	Xitanium 35W 0.08-0.35A 220V TD11 230V
Order code	929001627706
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	929001627706
Full product name	Xitanium 35W 0.08-0.35A 220V TD11 230V
EAN/UPC - Case	8718696819647