

Ecofit Ledtubes T8

Ledtube DE 600mm 8W 865 T8 G13 KSA

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data


General Information		Temperature	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Lamp Current (Nom)	70 mA
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Nominal Lifetime (Nom)	15000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	50000X	Power Factor (Nom)	0.5
Voltage (Nom)		220-240 V	
Light Technical		Controls and Dimming	
Color Code	865 [CCT of 6500K]	Dimmable	No
Beam Angle (Nom)	240 °	Mechanical and Housing	
Luminous Flux (Nom)	800 lm	Product Length	600 mm
Color Designation	Cool Daylight	Bulb Shape	Tube, double-ended
Correlated Color Temperature (Nom)	6500 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Energy Saving Product	Yes
Color Consistency	<6		
Color Rendering Index (Nom)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power (Nom)	8 W		
Lamp Current (Max)	70 mA		
Lamp Current (Min)	70 mA		

Ecofit Ledtubes T8

Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871951427060200
Order product name	Ledtube DE 600mm 8W 865 T8 G13 KSA
EAN/UPC - Product	8719514270602

Order code	929002454408
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	929002454408
Net Weight (Piece)	0.160 kg



Dimensional drawing



Product	D1	D2	A1	A2	A3
Ledtube DE 600mm 8W 865 T8 G13 KSA	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm


LEDtube 600mm 8W 865 T8 DE KSA

Photometric data



LEDtube ECO 8W G13 800lm



LEDtube ECO 8W G13 800lm 865



LEDtube ECO 8W G13 800lm 865



Ecofit Ledtubes T8

Lifetime




LEDtube 15K FailureRate

LEDtube ECO 8W 15K LumenVsTc



LEDtube 15K

LEDtube 15K LifetimeVsTc



LEDtube 15K

Ecofit Ledtubes T8

