



# Fortimo FastFlex gen 4+



## Fortimo FastFlex LED 2x2/730 DA G5

Fortimo FastFlex DA & DP gen 5 is our 'one-fits-all-solution' for outdoor applications. The new generation comes with an efficiency upgrade and a larger selection.

### Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
Lighting Technology	LED
Light Technical	
Luminous Flux	940 lumen
Color Consistency Initial	5
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	158 lm/W
Color rendering index (CRI)	70
Temperature	
T-Case Lifetime (Max)	85 °C
T-Case Maximum (Max)	95 °C
Mechanical and Housing	
Overall length	70.6 mm
Overall width	49.5 mm
Overall height	6.1 mm

Dimensions (Height x Width x Depth)	6 x 50 x 71 mm
Approval and Application	
Energy Efficiency Class	D
Approval Marks	CE marking ENEC certificate UL certificate REACH compliance RoHS compliance Zhaga compliant
EPREL Registration Number	1008257
Product Data	
Full product code	871951431806900
Order product name	Fortimo FastFlex LED 2x2/730 DA G5
Order code	929002865906
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	929002865906
Full product name	Fortimo FastFlex LED 2x2/730 DA G5
EAN/UPC - Case	8719514318076