


PHILIPS

Lighting



Fortimo FastFlex gen 4+



Fortimo FastFlex LED 2x6/740 DA G5

Fortimo FastFlex DA & DP gen 5 is our 'one-fits-all-solution' for outdoor applications. The new generation comes with an efficiency upgrade and a larger selection.

Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
Lighting Technology	LED
Light Technical	
Luminous Flux	3,065 lumen
Color Consistency Initial	5
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	172 lm/W
Color rendering index (CRI)	70
Temperature	
T-Case Lifetime (Max)	85 °C
T-Case Maximum (Max)	95 °C
Mechanical and Housing	
Overall length	172.2 mm
Overall width	49.5 mm
Overall height	6.1 mm

Dimensions (Height x Width x Depth)	6 x 50 x 172 mm
Approval and Application	
Energy Efficiency Class	D
Approval Marks	CE marking ENEC certificate UL certificate REACH compliance RoHS compliance Zhaga compliant
EPREL Registration Number	1008238
Product Data	
Full product code	871951431828100
Order product name	Fortimo FastFlex LED 2x6/740 DA G5
Order code	929002867006
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	929002867006
Full product name	Fortimo FastFlex LED 2x6/740 DA G5
EAN/UPC - Case	8719514318298