



# Fortimo LED-R



## Fortimo LED-R 1ft MF 830 FC HV5

The Fortimo LED-R modules are designed together with BJB's OptiLine Louvres. Together they make a high efficient and low-glare lighting solution. The system is extremely easy to install due to the one-click-fixation system which enables screwless installation, even for high voltage applications. The Fortimo LED-R modules are available in a full range serving all different needs from different application. There are standard CRI80 modules, CRI90 High Efficiency versions, FlexTune tunable white and BioUp Cyan Enhanced Dynamic versions. Basically covering all the needs for office, retail and hospitality applications.

### Product data

General Information	
Lighting Technology	LED
Light Technical	
Luminous Flux	167 lumen
Life to 70% Lumen Maintenance	70,000 hour(s)
Color Consistency Initial	3
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	167 lm/W
Color rendering index (CRI)	80
Temperature	
T-Case Lifetime (Max)	75 °C
T-Case Maximum (Max)	85 °C
Mechanical and Housing	
Overall length	279.2 mm
Overall width	20 mm
Overall height	4,3 mm

Dimensions (Height x Width x Depth)	4 x 20 x 279 mm
Approval and Application	
Energy Efficiency Class	D
Approval Marks	CE marking ENEC certificate UL certificate BIS Certificate
EPREL Registration Number	1227061
Product Data	
Full product code	871951444745500
Order product name	Fortimo LED-R 1ft MF 830 FC HV5
Order code	929003403806
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	110
Material Nr. (12NC)	929003403806
Full product name	Fortimo LED-R 1ft MF 830 FC HV5
EAN/UPC - Case	8719514447462
EAN/UPC - Product/Case	8719514447455

## Fortimo LED-R

---

