



Fortimo LED-R



Fortimo LED-R 2ft MF 930 FC LV5

The Fortimo LED-R modules are designed together with BJB's OptiLine Louvres. Together they make a high efficient and low-glare lighting solution. The system is extremely easy to install due to the one-click-fixation system which enables screwless installation, even for high voltage applications. The Fortimo LED-R modules are available in a full range serving all different needs from different application. There are standard CRI80 modules, CRI90 High Efficiency versions, FlexTune tunable white and BioUp Cyan Enhanced Dynamic versions. Basically covering all the needs for office, retail and hospitality applications.

Product data

General Information	
Lighting Technology	LED
Light Technical	
Luminous Flux	155 lumen
Life to 70% Lumen Maintenance	70,000 hour(s)
Color Consistency Initial	3
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	155 lm/W
Color rendering index (CRI)	90
Temperature	
T-Case Lifetime (Max)	75 °C
T-Case Maximum (Max)	85 °C
Mechanical and Housing	
Overall length	559.2 mm
Overall width	20 mm
Overall height	4.3 mm

Dimensions (Height x Width x Depth)	4 x 20 x 559 mm
Approval and Application	
Energy Efficiency Class	D
Approval Marks	CE marking ENEC certificate UL certificate BIS Certificate
EPREL Registration Number	1227089
Product Data	
Full product code	871951444787500
Order product name	Fortimo LED-R 2ft MF 930 FC LV5
Order code	929003405906
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	110
Material Nr. (12NC)	929003405906
Full product name	Fortimo LED-R 2ft MF 930 FC LV5
EAN/UPC - Case	8719514447882
EAN/UPC - Product/Case	8719514447875

Fortimo LED-R

