



CorePro LEDtube EM/ Mains T8

CorePro LEDtube 600mm 9W 840 T8 AP I

Philips CorePro LEDtubes are the quick and easy way to replace T8 fluorescent or other LED tubes with a fast pack back time. Not only does the Core range of LEDtubes require a low initial investment, but LED energy efficiency also delivers instant savings that you can bank on over a long and reliable lifetime. Plus, with the same lamp size and light distribution as fluorescent alternatives, you'll never know the difference. There are two ways to install these LED tubes: Rewire your existing fluorescent-based luminaires so the CorePro LEDtubes work directly on the Mains. Or simply change the fluorescent starter to an LED starter that can be used with your Electromagnetic ballasts.

Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.
- Installation must be done according to the installation diagrams provided with the lamp or available online. Installation must be done by a certified professional.

Product data

General Information		Luminous Flux	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Luminous Flux	900 lm
Nominal lifetime	30,000 hour(s)	Color Designation	Cool White (CW)
Switching Cycle	200,000	Correlated Color Temperature (Nom)	4000 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	100.00 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
		Color rendering index (CRI)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	240 degree(s)		

CorePro LEDtube EM/Mains T8

Input Frequency	50 to 60 Hz
Power Consumption	9 W
Lamp Current (Max)	48 mA
Lamp Current (Min)	48 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V

Temperature

Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	45 °C

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass
Product Length	600 mm

Bulb Shape	T8
------------	----


Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate

Product Data


Order product name	CorePro LEDtube 600mm 9W 840 T8 AP I
Full product name	CorePro LEDtube 600mm 9W 840 T8 AP I
Full product code	871951444699100
Order code	929003520108
Material Nr. (12NC)	929003520108
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514446991
Numerator - Packs per outer box	20
EAN/UPC - Case	8719514447004

Dimensional drawing




Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm 9W 840 T8 AP I	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

Photometric data




Spectral Power Distribution Colour - CorePro LEDtube 600mm 9W 840 T8 AP I



Light Distribution Diagram - CorePro LEDtube 600mm 9W 840 T8 AP I



CorePro LEDtube EM/Mains T8

Photometric data





General uniform lighting - CorePro LEDtube 600mm 9W 840 T8 AP I

Lifetime



Life Expectancy Diagram - CorePro LEDtube 600mm 9W 840 T8 AP I

Life Expectancy Diagram - CorePro LEDtube 600mm 9W 840 T8 AP I




Life Expectancy Diagram - CorePro LEDtube 600mm 9W 840 T8 AP I

Lumen Maintenance Diagram - CorePro LEDtube 600mm 9W 840 T8 AP I

CorePro LEDtube EM/Mains T8

Lifetime



Lumen Maintenance Diagram - CorePro LEDtube 600mm 9W 840 T8 AP I

