

Order guide

recessed LED



SERIES		VERSION		LIGHT SOURCE			HOUSING	ELECTRICAL		
FAMILY	SIZE	VERSION	CONFIGURATION	SOURCE	COLOR TEMP	LUMENS	TYPE	WIRING	VOLTAGE	DRIVER
36 ArcForm 94 PureFX 97 Vectra	14 1' x 4' 22 2' x 2'	D1 Standard T-Grid D2 Slot T-Grid	ST Standalone	L LED	A 4000K B 3500K C 3000K	30 3000 lumens (ArcForm only) 36 3600 lumens 44 4400 lumens	S Standard	7 1 cct w/ dimming N 1 cct w/ dimming & battery pack*	D UNV 120-277 3 347V*	E Advance 0-10V (1% dim)
41 VersaForm 42 SilkSpace	14 1' x 4' 22 2' x 2' 24 2' x 4'	D1 Standard T-Grid D2 Slot T-Grid (VersaForm only)			8A 80CRI/4000K 8B 80CRI/3500K 8C 80CRI/3000K 9B 90CRI/3500K (VersaForm Only)	K 1700 lumens (SilkSpace only) E 3000 lumens D 4000 lumens D 4000 lumens C 5200 lumens A 6800 lumens				
42 SilkSpace definiton 33 Shine	14 1' x 4' 22 2' x 2' 24 2' x 4'	D1 Standard T-Grid			850 80CRI/5000K 840 80CRI/4000K 835 80CRI/3500K 830 80CRI/3000K 827 80CRI/2700K 935 90CRI/3500K	25 2500 lm 30 3000 lm 35 3500 lm 40 4000 lm 45 4500 lm 50 5000 lm 40 4000 lm 45 4500 lm 50 5000 lm 55 5500 lm 60 6000 lm 65 6500 lm 70 7000 lm 75 7500 lm 80 8000 lm				

Exclusions:

- All non standard, 3rd party drivers and components
- Connected options (SpaceWise, Interact Pro, Tunable White, PoE)
- No Battery Pack is available for 347V*
- 1 Lumen package not available in CRI90 at 2'x4' or 1'x4'
- Prior Hold for Release or Do Not Ship Before orders

- Surface mount versions
- Chicago housings
- Air Return housings

MAXIMUM 500' PER QUICKSHIP ORDER
Questions? Contact your Ledalite sales rep.



Order guide

linear recessed, cove, & perimeter LED



SERIES		VERSION	LIGHT SOURCE			BODY				ELECTRICAL		
FAMILY	VERSION	DISTRIBUTION	SOURCE	COLOR TEMP	LUMENS	LENS	HOUSING	CEILING/TRIM	RUN LENGTH	WIRING	VOLTAGE	DRIVER
39 TruGroove Recessed	0 Straight Run	1 Symmetric-Performance	L LED	A 4000K	D 4000lm/4ft	Q Flush-Performance	S Standard	1 T-Grid	2'-20' in 2' increments	7 1 cct w/ dimming	D UNV 120-277V	E Advance 0-10V (1% dim)
		8 Asymmetric-Performance (Flush lens only)		B 3500K	E 3000lm/4ft	R Regressed-Performance		3 Drywall Trimless		M 1cct w/ dimming & aux. wiring		
		0 Symmetric-Definition		C 3000K	G 2200lm/4ft	L Flush-Definition		4 Drywall Trim		N 1 cct w/ dimming & battery pack*		
					K 1500lm/4ft	M Regressed-Definition						

FAMILY	VERSION	DISTRIBUTION	SOURCE	COLOR TEMP	LUMENS	LENS	HOUSING	CEILING/TRIM	RUN LENGTH	WIRING	VOLTAGE	DRIVER
23 TruGroove Recessed Micro	0 Straight Run	1 Symmetric	L LED	A 4000K	E 3100lm/4ft	Q Flush MesoOptics Lens	S Standard	1 T-Grid	2'-20' in 2' increments	7 1 cct w/ dimming	D UNV 120-277V	E Advance 0-10V (1% dim)
		8 Asymmetric		B 3500K	G 2200lm/4ft	3 Drywall Trimless		M 1cct w/ dimming & aux. wiring				
				C 3000K	K 1500lm/4ft	4 Drywall Trim		N 1 cct w/ dimming & battery pack*				
					M 1000lm/4ft							

FAMILY	VERSION	DISTRIBUTION	SOURCE	COLOR TEMP	LUMENS	LENS	HOUSING	CEILING/TRIM	RUN LENGTH	WIRING	VOLTAGE	DRIVER
TC TruGroove Cove	0 Straight Run	8 Asymmetric	L LED	840 80CRI/4000K	60 6000lm/4ft	W Focus Optics	N Standard		XX Any length in 6" increments starting at 2'	7 1 cct w/ dimming	D UNV 120-277V	E Advance 0-10V (1% dim)
				835 80CRI/3500K	50 5000lm/4ft	L Fill Optics				M 1cct w/ dimming & aux. wiring		
				830 80CRI/3000K	40 4000lm/4ft					N 1 cct w/ dimming & battery pack (>4' module only)		
				935 90CRI/3500K	30 3000lm/4ft							
					25 2500lm/4ft							
	20 2000lm/4ft											
	15 1500lm/4ft											
	10 1000lm/4ft											

FAMILY	VERSION	DISTRIBUTION	SOURCE	COLOR TEMP	LUMENS	LENS	HOUSING	CEILING/TRIM	RUN LENGTH	WIRING	VOLTAGE	DRIVER
49 TruGroove Perimeter	0 Straight Run	8 Ambient	L LED	A 4000K	D 4100lm/4ft	Q Flush MesoOptics Lens	S Standard	N All Ceilings** (see table below)	2'-20' in 2' increments	7 1 cct w/ dimming	D UNV 120-277V	E Advance 0-10V (1% dim)
				B 3500K	E 3000lm/4ft					M 1cct w/ dimming & aux. wiring		
		9 Graze		C 3000K	G 2100lm/4ft	P Reverse Parabolic Optic w/Flush Lens				N 1 cct w/ dimming & battery pack*		
					K 1400lm/4ft					7 1 cct w/ dimming (Aux. & BP not available in Graze)		

ENDSETS

SLOT & CEILING TRIM

LEFT ENDSET	RIGHT ENDSET	SLOT HEIGHT	SLOT PANEL	CEILING TRIM
C Variable/Wall S Fixed/Pocket	C Variable/Wall S Fixed/Pocket	2 1.75" 4 4"	S Solid A Air Return	1 T-Grid 3 Drywall Trimless 4 Drywall Trim

Exclusions:

- Connected options (SpaceWise, Interact Pro, Tunable White, PoE)
- Prior **Hold for Release** or **Do Not Ship Before** orders
- All non-standard, 3rd party drivers and components
- TruGroove Recessed Micro (23) not available as a 2ft asymmetric
- TruGroove Cove (TC) 6000lm/4ft not available with 90CRI options.
- No Battery Pack is available for 347V

- Thru-wiring for additional circuits
- Chicago housings

MAXIMUM 500' PER QUICKSHIP ORDER
Questions? Contact your Ledalite sales rep.



by @ignify

**Example part number: 4908LBEQSN-16-7-1-E, S/S, 4S3

Order guide

linear suspended/surface LED



SERIES		VERSION		LIGHT SOURCE			OPTICS		BODY	ELECTRICAL			FINISH		MOUNTING	
FAMILY	VERSION	DISTRIBUTION	SOURCE	COLOR TEMP	LUMENS	LOWER OPTICS	UPPER OPTICS	MODULE LENGTH	WIRING TYPE	VOLTAGE	DRIVER	FINISH	ENDS	CEILING KIT	DROP LENGTH	
78 BoldPlay	0 Standard	6 Direct-Indirect	L LED	A 4000K	A 6500lm/4ft	Q MesoOptics Lens	N Lightguide	4' & 8'	7 1 cct w/dimming M 1 cct w/dimming & aux. wiring N 1 cct w/dimming & battery pack*	D UNV 120-277V 3 347V	E Advance 0-10V (1% dim)	W Standard White T Titanium Silver B Black	Sculpted	A1, A2, A3, A5, A6-1, A6-2, A6-3 Surface (where available)	2' 24" 4' 48" 8' 96" 12' 144" All adjustable	
				B 3500K C 3000K	C 4600lm/4ft E 3400lm/4ft											D 55% Down Kit G 80% Down Kit J 100% Down Kit
MF ModiFly	0 Standard	S Suspended		840 4000K	45 4500lm/4ft	Q Vertical Light Guide	N 75% Down / 25% Up	2', 4', 5', 6', & 8'	1N1 cct w/dimming 1E1 cct w/dimming & aux. wiring 1B1 cct w/dimming & battery pack*			W Standard White H Hero Gold S Silver Nova V Venom Black T Titanium Silver B Black	Sculpted	M1, M2, M3, M6-1, M6-2, M6-3		
				835 3500K 830 3000K	40 4000lm/4ft 35 3500lm/4ft 30 3000lm/4ft 25 2500lm/4ft 20 2000lm/4ft 15 1500lm/4ft											
75 Chopstick	0 Standard	5 Semi-Indirect		A 4000K B 3500K C 3000K	C 4800lm/4ft E 3400lm/4ft	Q MesoOptics Lens	N Lightguide	4', 6' & 8'	7 1 cct w/dimming M 1 cct w/dimming & aux. wiring N 1 cct w/dimming & battery pack*			W Standard White T Titanium Silver B Black	Flat Sculpted	A1, A2, A3, A5, A6-1, A6-2, A6-3 Surface (where available)		
24 FloatPlane	G Edge R Curve	5 Direct-Indirect			A 7500lm/4ft B 6000lm/4ft C 4500lm/4ft E 3200lm/4ft	A Acrylic diffusers	A 70% up D 45% down G 75% down H 90% down J 100% down	4', 6' & 8'					Sculpted			
12 Jump	0 Suspended 1 Surface	1 Direct			C 4900lm/4ft E 3600lm/4ft G 2400lm/4ft	Q MesoOptics Lens	E Solid Side / No Perf P Pixel Perf S Splash Perf	4' & 8'					Luminous Sculpted			
22 MicroSquare gen2	0 Suspended	1 Direct			G 2600lm/4ft K 1300lm/4ft	L Flush Silk Lens	N None	4', 6' & 8'					Solid Cube			
					3 Indirect	C 4700lm/4ft E 3400lm/4ft	N Solid Housing	Q Symmetric Wide-Throw Lens	4', 6' & 8'	Solid Cube						
						5 Indirect-Direct	B 5900lm/4ft C 4800lm/4ft E 3100lm/4ft	L Flush Silk Lens	Q Symmetric Wide-Throw Lens	4', 6' & 8'	Solid Cube					
							6 Direct-Indirect	B 6000lm/4ft C 4400lm/4ft E 3900lm/4ft	L Flush Silk Lens	Q Symmetric Wide-Throw Lens	4', 6' & 8'	Solid Cube				
		1 Surface	1 Direct		G 2600lm/4ft K 1300lm/4ft	L Flush Silk Lens		N None	4', 6' & 8'					Solid Cube		

Exclusions:

- ModiFly and TruGroove: no patterns or rows that require drawings
- Connected options (SpaceWise, Interact Pro, Tunable White, PoE)
- Prior **Hold for Release** or **Do Not Ship Before** orders

- All non-standard, 3rd party drivers and components
- No Battery Pack is available for 347V

MAXIMUM 500' PER QUICKSHIP ORDER
Questions? Contact your Ledalite sales rep.



by @ignify

Order guide

linear suspended/surface LED continued



SERIES		VERSION		LIGHT SOURCE			OPTICS		BODY	ELECTRICAL			FINISH		MOUNTING			
FAMILY	VERSION	DISTRIBUTION	SOURCE	COLOR TEMP	LUMENS	LOWER OPTICS	UPPER OPTICS	MODULE LENGTH	WIRING TYPE	VOLTAGE	DRIVER	FINISH	ENDS	CEILING KIT	DROP LENGTH			
74 Sync	0 Standard	6 Direct-Indirect	L LED	A 4000K B 3500K C 3000K	A 6500lm/4ft C 4600lm/4ft E 3400lm/4ft	Q Symmetric MesoOptics	N Lightguide D 55% Down Kit G 80% Down Kit J 100% Down Kit	4' & 8'	7 1 cct w/dimming M 1 cct w/dimming & aux. wiring N 1 cct w/dimming & battery pack*	D UNV 120-277V 3 347V	E Advance 0-10V (1% dim)	W Standard White T Titanium Silver B Black	Flat	A1	2' 24"			
					A2									4' 48"				
29 TruGroove	0 Suspended	1 Direct	L LED	A 4000K B 3500K C 3000K	D 4000lm/4ft E 3200lm/4ft G 2300lm/4ft K 1500lm/4ft	L Silk Lens Q Symmetric MesoOptics W Asymmetric MesoOptics	N None	2', 4', 6' & 8'	7 1 cct w/dimming M 1 cct w/dimming & aux. wiring N 1 cct w/dimming & battery pack*	D UNV 120-277V 3 347V	E Advance 0-10V (1% dim)	W Standard White T Titanium Silver B Black	Flat	A6-1	All adjustable			
					A6-2													
					A6-3													
		Surface (where available)																
		3 Indirect			C 4800lm/4ft E 3200lm/4ft	N Solid Housing	Q Symmetric Performance W Asymmetric Performance							2', 4', 6' & 8'		Sculpted		
	5 Indirect-Direct 6 Direct-Indirect	A 6800lm/4ft B 5200lm/4ft C 4600lm/4ft D 3500lm/4ft			LQ Silk Lens QQ Symmetric MesoOptics WW Asymmetric MesoOptics	2', 4', 6' & 8'	Sculpted											
	1 Surface	1 Direct			D 4000lm/4ft E 3200lm/4ft G 2300lm/4ft K 1500lm/4ft			L Silk Lens Q Symmetric MesoOptics W Asymmetric MesoOptics	N None	2', 4', 6' & 8'	Sculpted							
	76 Verge	0 Standard			6 Direct-Indirect	L LED	A 4000K B 3500K C 3000K	A 6500lm/4ft C 4600lm/4ft E 3400lm/4ft	Q MesoOptics Lens			N Lightguide D 55% Down Kit G 80% Down Kit J 100% Down Kit	4' & 8'	7 1 cct w/dimming M 1 cct w/dimming & aux. wiring N 1 cct w/dimming & battery pack*	D UNV 120-277V 3 347V	E Advance 0-10V (1% dim)	W Standard White T Titanium Silver B Black	Flat
								A2	All adjustable									
								A3										
A5																		
A6-1																		
A6-2																		
77 Sona	0 1 Light Chamber - Upper	3 Indirect	L LED	A 4000K B 3500K C 3000K	C 4900lm/4ft E 3400lm/4ft	N Solid (100% up)	A Acrylic Diffuser	4' & 8'	7 1 cct w/dimming M 1 cct w/dimming & aux. wiring N 1 cct w/dimming & battery pack*	D UNV 120-277V 3 347V	E Advance 0-10V (1% dim)	W Standard White T Titanium Silver B Black	Flat	A1	All adjustable			
					A2													
		5 Indirect/Direct			B 6100lm/4ft C 4500lm/4ft E 3100lm/4ft	A Curved Acrylic Diffuser V White Louver	A Acrylic Diffuser (75% up) D Acrylic Diffuser w/50% Down Kit							4' & 8'		Sculpted		
	1 1 Light Chamber - Lower	1 Direct			C 4700lm/4ft E 3400lm/4ft G 2200lm/4ft	A Curved Acrylic Diffuser V White Louver	N Solid (100% down) G Acrylic Diffuser (75-80% down)	4' & 8'	Sculpted									

Exclusions:

- ModifiFly and TruGroove: no patterns or rows that require drawings
- Connected options (SpaceWise, Interact Pro, Tunable White, PoE)
- Prior Hold for Release or Do Not Ship Before orders

- All non-standard, 3rd party drivers and components
- No Battery Pack is available for 347V

MAXIMUM 500' PER QUICKSHIP ORDER

Questions? Contact your Ledalite sales rep.



by @ignify