



The original!

MASTER PL-S 2 Pin

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base

Benefits

- Optimal light performance for short or long operation per switch-on
- Multiple light color choice
- Good color rendering (CRI >80)

Features

- 2-pin base with a housing incorporating the special instant starter and capacitor
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life

Application

- Application
- Designed for use in hotels, restaurants, theatres and homes
- Suitable for use in signs, corridors, security and orientation lighting

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-S 2 Pin

Versions



G23/GX23, 2P



5W, G23, 2P



G23/GX23, 2P



7W, G23, 2P




9W, G23, 2P



11W, G23, 2P

MASTER PL-S 2 Pin

Dimensional drawing



| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|---------------------------------------|---------|----------|---------|---------|----------|
| MASTER PL-S 5W/827/2P 1CT/ 5X10BOX | 28 mm | 13 mm | 67 mm | 83 mm | 105 mm |
| MASTER PL-S 5W/840/2P 1CT/5X10BOX | 28 mm | 13 mm | 67 mm | 83 mm | 105 mm |
| MASTER PL-S 7W/827/2P 1CT/ 5X10BOX | 28 mm | 13 mm | 97 mm | 113 mm | 135 mm |
| MASTER PL-S 7W/830/2P 1CT/ 5X10BOX | 28 mm | 13 mm | 97 mm | 113 mm | 135 mm |
| MASTER PL-S 7W/840/2P 1CT/5X10BOX | 28 mm | 13 mm | 97 mm | 113 mm | 135 mm |
| MASTER PL-S 9W/827/2P 1CT/ 5X10BOX | 28 mm | 13 mm | 129 mm | 145 mm | 167 mm |
| MASTER PL-S 9W/830/2P 1CT/5X10BOX | 28 mm | 13 mm | 129 mm | 145 mm | 167 mm |
| MASTER PL-S 9W/840/2P 1CT/5X10CC | 28 mm | 13 mm | 129 mm | 145 mm | 167 mm |
| MASTER PL-S 11W/827/2P 1CT/5X10BOX | 28 mm | 13 mm | 198 mm | 214 mm | 235.8 mm |
| MASTER PL-S 11W/830/2P 1CT/5X10BOX | 28 mm | 13 mm | 198 mm | 214 mm | 235.8 mm |
| MASTER PL-S 11W/840/2P 1CT/5X10BOX | 28 mm | 13 mm | 198 mm | 214 mm | 235.8 mm |
| MASTER PL-S 9W/865/2P 1CT/10 | 28 mm | 13 mm | 97 mm | 113 mm | 135 mm |
| MASTER PL-S 11W/865/2P 1CT/10 | 28 mm | 13 mm | 97 mm | 113 mm | 135 mm |
| MASTER PL-S 7W/865/2P 1CT/10 | 28 mm | 13 mm | 97 mm | 113 mm | 135 mm |
| MASTER PL-S 7W/827/2P 1CT/10 | 28 mm | 13 mm | 97 mm | 113 mm | 135 mm |
| MASTER PL-S 9W/840/2P 1CT/10 | 28 mm | 13 mm | 129 mm | 145 mm | 167 mm |
| MASTER PL-S 7W/840/2P 1CT/10 | 28 mm | 13 mm | 97 mm | 113 mm | 135 mm |
| MASTER PL-S 9W/827/2P 1CT/10 | 28 mm | 13 mm | 129 mm | 145 mm | 167 mm |
| MASTER PL-S 11W/827/2P 1CT/10 | 28 mm | 13 mm | 198 mm | 214 mm | 235.8 mm |
| MASTER PL-S 11W/840/2P 1CT/10 | 28 mm | 13 mm | 198 mm | 214 mm | 235.8 mm |

MASTER PL-S 2 Pin

Dimensional drawing

□ □

| Product | D (max) | D1 (max) | C (max) |
|-------------------------------|---------|----------|----------|
| MASTER PL-S 13W/865/2P 1CT/10 | 27.1 mm | 13 mm | 178.2 mm |
| MASTER PL-S 13W/840/2P 1CT/10 | 27.1 mm | 13 mm | 178.2 mm |
| MASTER PL-S 13W/827/2P 1CT/10 | 27.1 mm | 13 mm | 178.2 mm |

Approval and Application

Mercury (Hg) Content (Nom) 1.4 mg

Controls and Dimming

Dimmable No

Approval and Application

| Order Code | Full Product Name | Energy Consumption kWh/1000 h | Energy Efficiency Label (EEL) |
|--------------|-----------------------------------|-------------------------------|-------------------------------|
| 927902882766 | MASTER PL-S 13W/827/2P 1CT/10 | - | B |
| 927902884066 | MASTER PL-S 13W/840/2P 1CT/10 | - | B |
| 927902886566 | MASTER PL-S 13W/865/2P 1CT/10 | - | B |
| 927935282711 | MASTER PL-S 5W/827/2P 1CT/5X10BOX | 7 kWh | B |
| 927935284011 | MASTER PL-S 5W/840/2P 1CT/5X10BOX | 7 kWh | B |
| 927935682711 | MASTER PL-S 7W/827/2P 1CT/5X10BOX | 9 kWh | B |
| 927935682765 | MASTER PL-S 7W/827/2P 1CT/10 | 9 kWh | B |
| 927935684011 | MASTER PL-S 7W/840/2P 1CT/5X10BOX | 9 kWh | B |
| 927935684065 | MASTER PL-S 7W/840/2P 1CT/10 | 9 kWh | B |
| 927935686565 | MASTER PL-S 7W/865/2P 1CT/10 | - | A |
| 927936082711 | MASTER PL-S 9W/827/2P 1CT/5X10BOX | 11 kWh | A |

| Order Code | Full Product Name | Energy Consumption kWh/1000 h | Energy Efficiency Label (EEL) |
|--------------|------------------------------------|-------------------------------|-------------------------------|
| 927936082765 | MASTER PL-S 9W/827/2P 1CT/10 | 11 kWh | A |
| 927936084011 | MASTER PL-S 9W/840/2P 1CT/5X10CC | 11 kWh | A |
| 927936084065 | MASTER PL-S 9W/840/2P 1CT/10 | 11 kWh | A |
| 927936086565 | MASTER PL-S 9W/865/2P 1CT/10 | - | A |
| 927936482711 | MASTER PL-S 11W/827/2P 1CT/5X10BOX | 14 kWh | A |
| 927936482765 | MASTER PL-S 11W/827/2P 1CT/10 | 14 kWh | A |
| 927936484011 | MASTER PL-S 11W/840/2P 1CT/5X10BOX | 14 kWh | A |
| 927936484065 | MASTER PL-S 11W/840/2P 1CT/10 | 14 kWh | A |
| 927936486565 | MASTER PL-S 11W/865/2P 1CT/10 | - | B |
| 927935683011 | MASTER PL-S 7W/830/2P 1CT/5X10BOX | 9 kWh | B |
| 927936083011 | MASTER PL-S 9W/830/2P 1CT/5X10BOX | 11 kWh | A |
| 927936483011 | MASTER PL-S 11W/830/2P 1CT/5X10BOX | 14 kWh | A |

Operating and Electrical

| Order Code | Full Product Name | Lamp Current (Nom) | Voltage (Nom) | Power (Rated) (Nom) |
|--------------|-------------------------------|--------------------|---------------|---------------------|
| 927902882766 | MASTER PL-S 13W/827/2P 1CT/10 | 0.290 A | 56 V | 13.0 W |

| Order Code | Full Product Name | Lamp Current (Nom) | Voltage (Nom) | Power (Rated) (Nom) |
|--------------|-------------------------------|--------------------|---------------|---------------------|
| 927902884066 | MASTER PL-S 13W/840/2P 1CT/10 | 0.290 A | 56 V | 13.0 W |

MASTER PL-S 2 Pin

| Order Code | Full Product Name | Lamp Current (Nom) | Voltage (Nom) | Power (Rated) (Nom) |
|--------------|-----------------------------------|--------------------|---------------|---------------------|
| 927902886566 | MASTER PL-S 13W/865/2P 1CT/10 | 0.290 A | 56 V | 13.0 W |
| 927935282711 | MASTER PL-S 5W/827/2P 1CT/5X10BOX | 0.180 A | - | 5.4 W |
| 927935284011 | MASTER PL-S 5W/840/2P 1CT/5X10BOX | 0.180 A | - | 5.4 W |
| 927935682711 | MASTER PL-S 7W/827/2P 1CT/5X10BOX | 0.175 A | - | 7.1 W |
| 927935682765 | MASTER PL-S 7W/827/2P 1CT/10 | 0.175 A | - | 7.1 W |
| 927935684011 | MASTER PL-S 7W/840/2P 1CT/5X10BOX | 0.175 A | - | 7 W |
| 927935684065 | MASTER PL-S 7W/840/2P 1CT/10 | 0.175 A | - | 7 W |
| 927935686565 | MASTER PL-S 7W/865/2P 1CT/10 | 0.175 A | 46 V | 7.1 W |
| 927936082711 | MASTER PL-S 9W/827/2P 1CT/5X10BOX | 0.170 A | - | 8.7 W |
| 927936082765 | MASTER PL-S 9W/827/2P 1CT/10 | 0.170 A | - | 8.7 W |
| 927936084011 | MASTER PL-S 9W/840/2P 1CT/5X10CC | 0.170 A | - | 8.7 W |

| Order Code | Full Product Name | Lamp Current (Nom) | Voltage (Nom) | Power (Rated) (Nom) |
|--------------|------------------------------------|--------------------|---------------|---------------------|
| 927936084065 | MASTER PL-S 9W/840/2P 1CT/10 | 0.170 A | - | 8.7 W |
| 927936086565 | MASTER PL-S 9W/865/2P 1CT/10 | 0.170 A | 60 V | 8.6 W |
| 927936482711 | MASTER PL-S 11W/827/2P 1CT/5X10BOX | 0.155 A | - | 11.6 W |
| 927936482765 | MASTER PL-S 11W/827/2P 1CT/10 | 0.155 A | - | 11.6 W |
| 927936484011 | MASTER PL-S 11W/840/2P 1CT/5X10BOX | 0.155 A | - | 11.6 W |
| 927936484065 | MASTER PL-S 11W/840/2P 1CT/10 | 0.155 A | - | 11.6 W |
| 927936486565 | MASTER PL-S 11W/865/2P 1CT/10 | 0.160 A | 89 V | 11.6 W |
| 927935683011 | MASTER PL-S 7W/830/2P 1CT/5X10BOX | 0.175 A | - | 7.1 W |
| 927936083011 | MASTER PL-S 9W/830/2P 1CT/5X10BOX | 0.170 A | - | 8.7 W |
| 927936483011 | MASTER PL-S 11W/830/2P 1CT/5X10BOX | 0.155 A | - | 11.6 W |

General Information

| Order Code | Full Product Name | Cap-Base | Life To 10% | | Life To 50% | | LSF 2000 h | LSF 4000 h | LSF 6000 h | LSF 8000 h |
|--------------|------------------------------------|----------|----------------|----------------|-------------|-------|------------|------------|------------|------------|
| | | | Failures (Nom) | Failures (Nom) | Rated | Rated | Rated | Rated | | |
| 927902882766 | MASTER PL-S 13W/827/2P 1CT/10 | GX23 | - | 8000 h | - | - | - | - | - | |
| 927902884066 | MASTER PL-S 13W/840/2P 1CT/10 | GX23 | - | 8000 h | - | - | - | - | - | |
| 927902886566 | MASTER PL-S 13W/865/2P 1CT/10 | GX23 | - | 8000 h | - | - | - | - | - | |
| 927935282711 | MASTER PL-S 5W/827/2P 1CT/5X10BOX | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927935284011 | MASTER PL-S 5W/840/2P 1CT/5X10BOX | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927935682711 | MASTER PL-S 7W/827/2P 1CT/5X10BOX | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927935682765 | MASTER PL-S 7W/827/2P 1CT/10 | G23 | 0 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927935684011 | MASTER PL-S 7W/840/2P 1CT/5X10BOX | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927935684065 | MASTER PL-S 7W/840/2P 1CT/10 | G23 | 0 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927935686565 | MASTER PL-S 7W/865/2P 1CT/10 | G23 | - | 10000 h | - | - | - | - | | |
| 927936082711 | MASTER PL-S 9W/827/2P 1CT/5X10BOX | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927936082765 | MASTER PL-S 9W/827/2P 1CT/10 | G23 | 0 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927936084011 | MASTER PL-S 9W/840/2P 1CT/5X10CC | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927936084065 | MASTER PL-S 9W/840/2P 1CT/10 | G23 | 0 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927936086565 | MASTER PL-S 9W/865/2P 1CT/10 | G23 | - | 10000 h | - | - | - | - | | |
| 927936482711 | MASTER PL-S 11W/827/2P 1CT/5X10BOX | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927936482765 | MASTER PL-S 11W/827/2P 1CT/10 | G23 | 0 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927936484011 | MASTER PL-S 11W/840/2P 1CT/5X10BOX | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927936484065 | MASTER PL-S 11W/840/2P 1CT/10 | G23 | 0 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927936486565 | MASTER PL-S 11W/865/2P 1CT/10 | G23 | - | 10000 h | - | - | - | - | | |
| 927935683011 | MASTER PL-S 7W/830/2P 1CT/5X10BOX | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927936083011 | MASTER PL-S 9W/830/2P 1CT/5X10BOX | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |
| 927936483011 | MASTER PL-S 11W/830/2P 1CT/5X10BOX | G23 | 6500 h | 10000 h | 99 % | 98 % | 95 % | 86 % | | |

MASTER PL-S 2 Pin

Light Technical (1/2)

| Order Code | Full Product Name | Color | | Correlated Color Temperature (Nom) | Color | | | |
|--------------|------------------------------------|-------|--------------------|------------------------------------|-----------------------|-------------------|-------------------|-------------------|
| | | Code | Color Designation | | Rendering Index (Nom) | LLMF 2000 h Rated | LLMF 4000 h Rated | LLMF 6000 h Rated |
| 927902882766 | MASTER PL-S 13W/827/2P 1CT/10 | 827 | Incandescent White | 2700 K | >80 | - | - | - |
| 927902884066 | MASTER PL-S 13W/840/2P 1CT/10 | 840 | Cool White (CW) | 4000 K | 82 | - | - | - |
| 927902886566 | MASTER PL-S 13W/865/2P 1CT/10 | 865 | Cool Daylight | 6500 K | 82 | - | - | - |
| 927935282711 | MASTER PL-S 5W/827/2P 1CT/5X10BOX | 827 | Incandescent White | 2700 K | 82 | 89 % | 83 % | 80 % |
| 927935284011 | MASTER PL-S 5W/840/2P 1CT/5X10BOX | 840 | Cool White (CW) | 4000 K | 82 | 89 % | 83 % | 80 % |
| 927935682711 | MASTER PL-S 7W/827/2P 1CT/5X10BOX | 827 | Incandescent White | 2700 K | 82 | 94 % | 91 % | 89 % |
| 927935682765 | MASTER PL-S 7W/827/2P 1CT/10 | 827 | Incandescent White | 2700 K | 82 | 94 % | 91 % | 89 % |
| 927935684011 | MASTER PL-S 7W/840/2P 1CT/5X10BOX | 840 | Cool White (CW) | 4000 K | 82 | 94 % | 91 % | 89 % |
| 927935684065 | MASTER PL-S 7W/840/2P 1CT/10 | 840 | Cool White (CW) | 4000 K | 82 | 94 % | 91 % | 89 % |
| 927935686565 | MASTER PL-S 7W/865/2P 1CT/10 | 865 | Cool Daylight | 6500 K | 82 | - | - | - |
| 927936082711 | MASTER PL-S 9W/827/2P 1CT/5X10BOX | 827 | Incandescent White | 2700 K | 82 | 94 % | 91 % | 89 % |
| 927936082765 | MASTER PL-S 9W/827/2P 1CT/10 | 827 | Incandescent White | 2700 K | 82 | 94 % | 91 % | 89 % |
| 927936084011 | MASTER PL-S 9W/840/2P 1CT/5X10OCC | 840 | Cool White (CW) | 4000 K | 82 | 94 % | 91 % | 89 % |
| 927936084065 | MASTER PL-S 9W/840/2P 1CT/10 | 840 | Cool White (CW) | 4000 K | 82 | 94 % | 91 % | 89 % |
| 927936086565 | MASTER PL-S 9W/865/2P 1CT/10 | 865 | Cool Daylight | 6500 K | 82 | - | - | - |
| 927936482711 | MASTER PL-S 11W/827/2P 1CT/5X10BOX | 827 | Incandescent White | 2700 K | 82 | 94 % | 91 % | 89 % |
| 927936482765 | MASTER PL-S 11W/827/2P 1CT/10 | 827 | Incandescent White | 2700 K | 82 | 94 % | 91 % | 89 % |
| 927936484011 | MASTER PL-S 11W/840/2P 1CT/5X10BOX | 840 | Cool White (CW) | 4000 K | 82 | 94 % | 91 % | 89 % |
| 927936484065 | MASTER PL-S 11W/840/2P 1CT/10 | 840 | Cool White (CW) | 4000 K | 82 | 94 % | 91 % | 89 % |
| 927936486565 | MASTER PL-S 11W/865/2P 1CT/10 | 865 | Cool Daylight | 6500 K | 82 | - | - | - |
| 927935683011 | MASTER PL-S 7W/830/2P 1CT/5X10BOX | 830 | Warm White (WW) | 3000 K | 82 | 94 % | 91 % | 89 % |
| 927936083011 | MASTER PL-S 9W/830/2P 1CT/5X10BOX | 830 | Warm White (WW) | 3000 K | 82 | 94 % | 91 % | 89 % |
| 927936483011 | MASTER PL-S 11W/830/2P 1CT/5X10BOX | 830 | Warm White (WW) | 3000 K | 82 | 94 % | 91 % | 89 % |

Light Technical (2/2)

| Order Code | Full Product Name | LLMF 8000 h Rated | Lumen Maintenance | | Luminous Efficacy | | | Luminous Flux (Nom) | Luminous Flux (Rated) (Nom) |
|--------------|-----------------------------------|-------------------|-------------------|--------------|------------------------|---------------------------------|--------|---------------------|-----------------------------|
| | | | 2000 h (Nom) | 5000 h (Nom) | Efficacy (rated) (Min) | Luminous Efficacy (rated) (Nom) | | | |
| 927902882766 | MASTER PL-S 13W/827/2P 1CT/10 | - | 85 % | 80 % | - | 62.3 lm/W | 810 lm | - | |
| 927902884066 | MASTER PL-S 13W/840/2P 1CT/10 | - | 85 % | 80 % | - | 66 lm/W | 860 lm | - | |
| 927902886566 | MASTER PL-S 13W/865/2P 1CT/10 | - | 82 % | 77 % | - | 63 lm/W | 820 lm | - | |
| 927935282711 | MASTER PL-S 5W/827/2P 1CT/5X10BOX | 77 % | - | - | 48 lm/W | - | 250 lm | 259 lm | |
| 927935284011 | MASTER PL-S 5W/840/2P 1CT/5X10BOX | 77 % | - | - | - | 48 lm/W | 250 lm | 259 lm | |
| 927935682711 | MASTER PL-S 7W/827/2P 1CT/5X10BOX | 86 % | - | - | - | 57 lm/W | 400 lm | 405 lm | |
| 927935682765 | MASTER PL-S 7W/827/2P 1CT/10 | 86 % | - | - | - | 57 lm/W | 400 lm | 405 lm | |
| 927935684011 | MASTER PL-S 7W/840/2P 1CT/5X10BOX | 86 % | - | - | - | 57 lm/W | 400 lm | 405 lm | |
| 927935684065 | MASTER PL-S 7W/840/2P 1CT/10 | 86 % | - | - | - | 57 lm/W | 400 lm | 405 lm | |
| 927935686565 | MASTER PL-S 7W/865/2P 1CT/10 | - | 91 % | 87 % | - | 56.3 lm/W | 400 lm | - | |
| 927936082711 | MASTER PL-S 9W/827/2P 1CT/5X10BOX | 86 % | - | - | - | 67 lm/W | 600 lm | 583 lm | |
| 927936082765 | MASTER PL-S 9W/827/2P 1CT/10 | 86 % | - | - | - | 67 lm/W | 600 lm | 583 lm | |
| 927936084011 | MASTER PL-S 9W/840/2P 1CT/5X10OCC | 86 % | - | - | - | 67 lm/W | 600 lm | 583 lm | |

MASTER PL-S 2 Pin

| Order Code | Full Product Name | LLMF 8000 h Rated | Lumen | Lumen | Luminous | Luminous Efficacy (rated) (Nom) | Luminous Flux (Nom) | Luminous Flux (Rated) (Nom) |
|--------------|--|----------------------|-----------------------------|-----------------------------|---------------------------|------------------------------------|------------------------|--------------------------------|
| | | | Maintenance 2000 h (Nom) | Maintenance 5000 h (Nom) | Efficacy (rated) (Min) | | | |
| 927936084065 | MASTER PL-S 9W/840/2P 1CT/10 | 86 % | - | - | - | 67 lm/W | 600 lm | 583 lm |
| 927936086565 | MASTER PL-S 9W/865/2P 1CT/10 | - | 91 % | 87 % | - | 62 lm/W | 540 lm | - |
| 927936482711 | MASTER PL-S 11W/827/2P 1CT/ 5X10BOX | 86 % | - | - | - | 77 lm/W | 900 lm | 893 lm |
| 927936482765 | MASTER PL-S 11W/827/2P 1CT/10 | 86 % | - | - | - | 77 lm/W | 900 lm | 893 lm |
| 927936484011 | MASTER PL-S 11W/840/2P 1CT/ 5X10BOX | 86 % | - | - | - | 77 lm/W | 900 lm | 893 lm |
| 927936484065 | MASTER PL-S 11W/840/2P 1CT/10 | 86 % | - | - | - | 77 lm/W | 900 lm | 893 lm |
| 927936486565 | MASTER PL-S 11W/865/2P 1CT/10 | - | 91 % | 87 % | - | 70 lm/W | 835 lm | - |
| 927935683011 | MASTER PL-S 7W/830/2P 1CT/ 5X10BOX | 86 % | - | - | - | 57 lm/W | 400 lm | 405 lm |
| 927936083011 | MASTER PL-S 9W/830/2P 1CT/ 5X10BOX | 86 % | - | - | - | 67 lm/W | 600 lm | 583 lm |
| 927936483011 | MASTER PL-S 11W/830/2P 1CT/ 5X10BOX | 86 % | - | - | - | 77 lm/W | 900 lm | 893 lm |

Temperature

| Order Code | Full Product Name | Design Temperature (Nom) | Order Code | Full Product Name | Design Temperature (Nom) |
|--------------|-----------------------------------|--------------------------|--------------|------------------------------------|--------------------------|
| 927902882766 | MASTER PL-S 13W/827/2P 1CT/10 | - | 927936084011 | MASTER PL-S 9W/840/2P 1CT/5X10CC | 28 °C |
| 927902884066 | MASTER PL-S 13W/840/2P 1CT/10 | - | 927936084065 | MASTER PL-S 9W/840/2P 1CT/10 | 28 °C |
| 927902886566 | MASTER PL-S 13W/865/2P 1CT/10 | - | 927936086565 | MASTER PL-S 9W/865/2P 1CT/10 | - |
| 927935282711 | MASTER PL-S 5W/827/2P 1CT/5X10BOX | 28 °C | 927936482711 | MASTER PL-S 11W/827/2P 1CT/5X10BOX | 28 °C |
| 927935284011 | MASTER PL-S 5W/840/2P 1CT/5X10BOX | 28 °C | 927936482765 | MASTER PL-S 11W/827/2P 1CT/10 | 28 °C |
| 927935682711 | MASTER PL-S 7W/827/2P 1CT/5X10BOX | 28 °C | 927936484011 | MASTER PL-S 11W/840/2P 1CT/5X10BOX | 28 °C |
| 927935682765 | MASTER PL-S 7W/827/2P 1CT/10 | 28 °C | 927936484065 | MASTER PL-S 11W/840/2P 1CT/10 | 28 °C |
| 927935684011 | MASTER PL-S 7W/840/2P 1CT/5X10BOX | 28 °C | 927936486565 | MASTER PL-S 11W/865/2P 1CT/10 | - |
| 927935684065 | MASTER PL-S 7W/840/2P 1CT/10 | 28 °C | 927935683011 | MASTER PL-S 7W/830/2P 1CT/5X10BOX | 28 °C |
| 927935686565 | MASTER PL-S 7W/865/2P 1CT/10 | - | 927936083011 | MASTER PL-S 9W/830/2P 1CT/5X10BOX | 28 °C |
| 927936082711 | MASTER PL-S 9W/827/2P 1CT/5X10BOX | 28 °C | 927936483011 | MASTER PL-S 11W/830/2P 1CT/5X10BOX | 28 °C |
| 927936082765 | MASTER PL-S 9W/827/2P 1CT/10 | 28 °C | | | |

