



10-15% more efficient!

MASTER PL-C 4 Pin

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Benefits

- Optimal light performance for short or long operation per switch-on
- Multiple light color choice
- Good color rendering (CRI >80)
- Dimming possible down to 10%

Features

- 4-pin base
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life

Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-C 4 Pin

Versions



10W, G24q-1, 4P



13W, G24q-1, 4P




18W, G24q-2, 4P



26W, G24q-3, 4P

MASTER PL-C 4 Pin

Dimensional drawing



| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|--|---------|----------|----------|----------|----------|
| MASTER PL-C 10W/ 830/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 75.5 mm | 95.0 mm | 109.9 mm |
| MASTER PL-C 10W/ 840/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 75.5 mm | 95.0 mm | 109.9 mm |
| MASTER PL-C 13W/827/4P 1CT/5X10CC | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 131.9 mm |
| MASTER PL-C 13W/827/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 131.9 mm |
| MASTER PL-C 13W/830/4P 1CT/5X10CC | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 131.9 mm |
| MASTER PL-C 13W/830/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 131.9 mm |
| MASTER PL-C 13W/840/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 131.9 mm |
| MASTER PL-C 13W/840/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 131.9 mm |
| MASTER PL-C 13W/865/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 131.9 mm |
| MASTER PL-C 18W/827/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 142.9 mm |
| MASTER PL-C 18W/827/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 142.9 mm |
| MASTER PL-C 18W/830/4P 1CT/5X10CC | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 142.9 mm |
| MASTER PL-C 18W/830/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 142.9 mm |
| MASTER PL-C 18W/840/4P 1CT/5X10CC | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 142.9 mm |
| MASTER PL-C 18W/840/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 142.9 mm |
| MASTER PL-C 18W/865/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 142.9 mm |
| MASTER PL-C 26W/827/4P 1CT/5X10CC | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |
| MASTER PL-C 26W/827/4P 1CT/5X10CC | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |
| MASTER PL-C 26W/827/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |
| MASTER PL-C 26W/ 830/4P 1CT/5X10CC | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |
| MASTER PL-C 26W/ 830/4P 1CT/5X10CC | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |
| MASTER PL-C 26W/ 830/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |
| MASTER PL-C 26W/ 840/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |
| MASTER PL-C 26W/ 840/4P 1CT/5X10CC | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |
| MASTER PL-C 26W/ 840/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |

MASTER PL-C 4 Pin

Dimensional drawing

| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|--|---------|----------|----------|----------|----------|
| MASTER PL-C 26W/ 865/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |
| MASTER PL-C 26W/ 865/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 163.9 mm |
| MASTER PL-C 18W/840/4P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 142.9 mm |

| Approval and Application | |
|------------------------------------|---------|
| Mercury (Hg) Content (Nom) | 1.4 mg |
| Controls and Dimming | |
| Dimmable | Yes |
| General Information | |
| Life To 50% Failures Preheat (Nom) | 13000 h |
| LSF Preheat 2000 h Rated | 99 % |
| LSF Preheat 4000 h Rated | 98 % |
| LSF Preheat 6000 h Rated | 97 % |
| LSF Preheat 8000 h Rated | 90 % |
| Temperature | |
| Design Temperature (Nom) | 28 °C |

Approval and Application

| Order Code | Full Product Name | Energy Consumption kWh/ 1000 h | Energy Efficiency Label (EEL) |
|--------------|------------------------------------|-----------------------------------|----------------------------------|
| 927907083040 | MASTER PL-C 10W/830/4P 1CT/5X10BOX | 11 kWh | A |
| 927907084040 | MASTER PL-C 10W/840/4P 1CT/5X10BOX | 11 kWh | A |
| 927907182701 | MASTER PL-C 13W/827/4P 1CT/5X10CC | 15 kWh | A |
| 927907182740 | MASTER PL-C 13W/827/4P 1CT/5X10BOX | 15 kWh | A |
| 927907183001 | MASTER PL-C 13W/830/4P 1CT/5X10CC | 15 kWh | A |
| 927907183040 | MASTER PL-C 13W/830/4P 1CT/5X10BOX | 15 kWh | A |
| 927907184002 | MASTER PL-C 13W/840/4P 1CT/5X10BOX | 15 kWh | A |
| 927907184040 | MASTER PL-C 13W/840/4P 1CT/5X10BOX | 15 kWh | A |
| 927907186501 | MASTER PL-C 13W/865/4P 1CT/5X10BOX | 15 kWh | B |
| 927907282701 | MASTER PL-C 18W/827/4P 1CT/5X10BOX | 20 kWh | A |
| 927907282740 | MASTER PL-C 18W/827/4P 1CT/5X10BOX | 20 kWh | A |
| 927907283001 | MASTER PL-C 18W/830/4P 1CT/5X10CC | 20 kWh | A |
| 927907283040 | MASTER PL-C 18W/830/4P 1CT/5X10BOX | 20 kWh | A |
| 927907284003 | MASTER PL-C 18W/840/4P 1CT/5X10CC | 20 kWh | A |
| 927907284040 | MASTER PL-C 18W/840/4P 1CT/5X10BOX | 20 kWh | A |
| 927907284065 | MASTER PL-C 18W/840/4P 1CT/5X10BOX | 20 kWh | A |
| 927907286501 | MASTER PL-C 18W/865/4P 1CT/5X10BOX | 20 kWh | B |
| 927907382701 | MASTER PL-C 26W/827/4P 1CT/5X10CC | 29 kWh | A |
| 927907382703 | MASTER PL-C 26W/827/4P 1CT/5X10CC | 29 kWh | A |
| 927907382740 | MASTER PL-C 26W/827/4P 1CT/5X10BOX | 29 kWh | A |
| 927907383001 | MASTER PL-C 26W/830/4P 1CT/5X10CC | 29 kWh | A |
| 927907383003 | MASTER PL-C 26W/830/4P 1CT/5X10CC | 29 kWh | A |
| 927907383040 | MASTER PL-C 26W/830/4P 1CT/5X10BOX | 29 kWh | A |
| 927907384002 | MASTER PL-C 26W/840/4P 1CT/5X10BOX | 29 kWh | A |
| 927907384004 | MASTER PL-C 26W/840/4P 1CT/5X10BOX | 29 kWh | A |
| 927907384040 | MASTER PL-C 26W/840/4P 1CT/5X10BOX | 29 kWh | A |
| 927907386501 | MASTER PL-C 26W/865/4P 1CT/5X10BOX | 29 kWh | B |
| 927907386565 | MASTER PL-C 26W/865/4P 1CT/5X10BOX | 29 kWh | B |

Operating and Electrical

| Order Code | Full Product Name | Lamp Current (Nom) | Power (Rated) (Nom) | Order Code | Full Product Name | Lamp Current (Nom) | Power (Rated) (Nom) |
|--------------|--|-----------------------|------------------------|--------------|--|-----------------------|------------------------|
| 927907083040 | MASTER PL-C 10W/830/4P 1CT/ 5X10BOX | 0.190 A | 10.0 W | 927907182701 | MASTER PL-C 13W/827/4P 1CT/ 5X10CC | 0.170 A | 13.0 W |
| 927907084040 | MASTER PL-C 10W/840/4P 1CT/ 5X10BOX | 0.190 A | 10.0 W | 927907182740 | MASTER PL-C 13W/827/4P 1CT/ 5X10BOX | 0.170 A | 13.0 W |

MASTER PL-C 4 Pin

| Order Code | Full Product Name | Lamp Current (Nom) | Power (Rated) (Nom) |
|--------------|------------------------------------|--------------------|---------------------|
| 927907183001 | MASTER PL-C 13W/830/4P 1CT/5X10CC | 0.170 A | 13.0 W |
| 927907183040 | MASTER PL-C 13W/830/4P 1CT/5X10BOX | 0.170 A | 13.0 W |
| 927907184002 | MASTER PL-C 13W/840/4P 1CT/5X10BOX | 0.170 A | 13.0 W |
| 927907184040 | MASTER PL-C 13W/840/4P 1CT/5X10BOX | 0.170 A | 13.0 W |
| 927907186501 | MASTER PL-C 13W/865/4P 1CT/5X10BOX | 0.170 A | 13.0 W |
| 927907282701 | MASTER PL-C 18W/827/4P 1CT/5X10BOX | 0.230 A | 16.5 W |
| 927907282740 | MASTER PL-C 18W/827/4P 1CT/5X10BOX | 0.230 A | 16.5 W |
| 927907283001 | MASTER PL-C 18W/830/4P 1CT/5X10CC | 0.230 A | 16.5 W |
| 927907283040 | MASTER PL-C 18W/830/4P 1CT/5X10BOX | 0.230 A | 16.5 W |
| 927907284003 | MASTER PL-C 18W/840/4P 1CT/5X10CC | 0.230 A | 18.0 W |
| 927907284040 | MASTER PL-C 18W/840/4P 1CT/5X10BOX | 0.230 A | 18.0 W |
| 927907284065 | MASTER PL-C 18W/840/4P 1CT/5X10BOX | 0.230 A | 18.0 W |

| Order Code | Full Product Name | Lamp Current (Nom) | Power (Rated) (Nom) |
|--------------|------------------------------------|--------------------|---------------------|
| 927907286501 | MASTER PL-C 18W/865/4P 1CT/5X10BOX | 0.230 A | 18.0 W |
| 927907382701 | MASTER PL-C 26W/827/4P 1CT/5X10CC | 0.335 A | 26.0 W |
| 927907382703 | MASTER PL-C 26W/827/4P 1CT/5X10CC | 0.335 A | 26.0 W |
| 927907382740 | MASTER PL-C 26W/827/4P 1CT/5X10BOX | 0.335 A | 26.0 W |
| 927907383001 | MASTER PL-C 26W/830/4P 1CT/5X10CC | 0.335 A | 26.0 W |
| 927907383003 | MASTER PL-C 26W/830/4P 1CT/5X10CC | 0.335 A | 26.0 W |
| 927907383040 | MASTER PL-C 26W/830/4P 1CT/5X10BOX | 0.335 A | 26.0 W |
| 927907384002 | MASTER PL-C 26W/840/4P 1CT/5X10BOX | 0.335 A | 26.0 W |
| 927907384004 | MASTER PL-C 26W/840/4P 1CT/5X10CC | 0.335 A | 26.0 W |
| 927907384040 | MASTER PL-C 26W/840/4P 1CT/5X10BOX | 0.335 A | 26.0 W |
| 927907386501 | MASTER PL-C 26W/865/4P 1CT/5X10BOX | 0.335 A | 26.0 W |
| 927907386565 | MASTER PL-C 26W/865/4P 1CT/5X10BOX | 0.335 A | 26.0 W |

General Information

| Order Code | Full Product Name | Cap-Base |
|--------------|------------------------------------|----------|
| 927907083040 | MASTER PL-C 10W/830/4P 1CT/5X10BOX | G24Q-1 |
| 927907084040 | MASTER PL-C 10W/840/4P 1CT/5X10BOX | G24Q-1 |
| 927907182701 | MASTER PL-C 13W/827/4P 1CT/5X10CC | G24Q-1 |
| 927907182740 | MASTER PL-C 13W/827/4P 1CT/5X10BOX | G24Q-1 |
| 927907183001 | MASTER PL-C 13W/830/4P 1CT/5X10CC | G24Q-1 |
| 927907183040 | MASTER PL-C 13W/830/4P 1CT/5X10BOX | G24Q-1 |
| 927907184002 | MASTER PL-C 13W/840/4P 1CT/5X10BOX | G24Q-1 |
| 927907184040 | MASTER PL-C 13W/840/4P 1CT/5X10BOX | G24Q-1 |
| 927907186501 | MASTER PL-C 13W/865/4P 1CT/5X10BOX | G24Q-1 |
| 927907282701 | MASTER PL-C 18W/827/4P 1CT/5X10BOX | G24Q-2 |
| 927907282740 | MASTER PL-C 18W/827/4P 1CT/5X10BOX | G24Q-2 |
| 927907283001 | MASTER PL-C 18W/830/4P 1CT/5X10CC | G24Q-2 |
| 927907283040 | MASTER PL-C 18W/830/4P 1CT/5X10BOX | G24Q-2 |
| 927907284003 | MASTER PL-C 18W/840/4P 1CT/5X10CC | G24Q-2 |

| Order Code | Full Product Name | Cap-Base |
|--------------|------------------------------------|----------|
| 927907284040 | MASTER PL-C 18W/840/4P 1CT/5X10BOX | G24Q-2 |
| 927907284065 | MASTER PL-C 18W/840/4P 1CT/5X10BOX | G24Q-2 |
| 927907286501 | MASTER PL-C 18W/865/4P 1CT/5X10BOX | G24Q-2 |
| 927907382701 | MASTER PL-C 26W/827/4P 1CT/5X10CC | G24Q-3 |
| 927907382703 | MASTER PL-C 26W/827/4P 1CT/5X10CC | G24Q-3 |
| 927907382740 | MASTER PL-C 26W/827/4P 1CT/5X10BOX | G24Q-3 |
| 927907383001 | MASTER PL-C 26W/830/4P 1CT/5X10CC | G24Q-3 |
| 927907383003 | MASTER PL-C 26W/830/4P 1CT/5X10CC | G24Q-3 |
| 927907383040 | MASTER PL-C 26W/830/4P 1CT/5X10BOX | G24Q-3 |
| 927907384002 | MASTER PL-C 26W/840/4P 1CT/5X10BOX | G24Q-3 |
| 927907384004 | MASTER PL-C 26W/840/4P 1CT/5X10CC | G24Q-3 |
| 927907384040 | MASTER PL-C 26W/840/4P 1CT/5X10BOX | G24Q-3 |
| 927907386501 | MASTER PL-C 26W/865/4P 1CT/5X10BOX | G24Q-3 |
| 927907386565 | MASTER PL-C 26W/865/4P 1CT/5X10BOX | G24Q-3 |

Light Technical (1/2)

MASTER PL-C 4 Pin

| Order Code | Full Product Name | Color Code | Color Designation | Correlated Color Temperature (Nom) | Color Rendering Index (Nom) |
|--------------|------------------------------------|------------|--------------------|------------------------------------|-----------------------------|
| 927907083040 | MASTER PL-C 10W/830/4P 1CT/5X10BOX | 830 | Warm White (WW) | 3000 K | 82 |
| 927907084040 | MASTER PL-C 10W/840/4P 1CT/5X10BOX | 840 | Cool White (CW) | 4000 K | 82 |
| 927907182701 | MASTER PL-C 13W/827/4P 1CT/5X10CC | 827 | Incandescent White | 2700 K | 82 |
| 927907182740 | MASTER PL-C 13W/827/4P 1CT/5X10BOX | 827 | Incandescent White | 2700 K | 82 |
| 927907183001 | MASTER PL-C 13W/830/4P 1CT/5X10CC | 830 | Warm White (WW) | 3000 K | 82 |
| 927907183040 | MASTER PL-C 13W/830/4P 1CT/5X10BOX | 830 | Warm White (WW) | 3000 K | 82 |
| 927907184002 | MASTER PL-C 13W/840/4P 1CT/5X10BOX | 840 | Cool White (CW) | 4000 K | 82 |
| 927907184040 | MASTER PL-C 13W/840/4P 1CT/5X10BOX | 840 | Cool White (CW) | 4000 K | 82 |
| 927907186501 | MASTER PL-C 13W/865/4P 1CT/5X10BOX | 865 | Cool Daylight | 6500 K | 80 |
| 927907282701 | MASTER PL-C 18W/827/4P 1CT/5X10BOX | 827 | Incandescent White | 2700 K | 82 |
| 927907282740 | MASTER PL-C 18W/827/4P 1CT/5X10BOX | 827 | Incandescent White | 2700 K | 82 |
| 927907283001 | MASTER PL-C 18W/830/4P 1CT/5X10CC | 830 | Warm White (WW) | 3000 K | 82 |
| 927907283040 | MASTER PL-C 18W/830/4P 1CT/5X10BOX | 830 | Warm White (WW) | 3000 K | 82 |
| 927907284003 | MASTER PL-C 18W/840/4P 1CT/5X10CC | 840 | Cool White (CW) | 4000 K | 82 |

| Order Code | Full Product Name | Color Code | Color Designation | Correlated Color Temperature (Nom) | Color Rendering Index (Nom) |
|--------------|------------------------------------|------------|--------------------|------------------------------------|-----------------------------|
| 927907284040 | MASTER PL-C 18W/840/4P 1CT/5X10BOX | 840 | Cool White (CW) | 4000 K | 82 |
| 927907284065 | MASTER PL-C 18W/840/4P 1CT/5X10BOX | 840 | Cool White (CW) | 4000 K | 82 |
| 927907286501 | MASTER PL-C 18W/865/4P 1CT/5X10BOX | 865 | Cool Daylight | 6500 K | 80 |
| 927907382701 | MASTER PL-C 26W/827/4P 1CT/5X10CC | 827 | Incandescent White | 2700 K | 82 |
| 927907382703 | MASTER PL-C 26W/827/4P 1CT/5X10CC | 827 | Incandescent White | 2700 K | 82 |
| 927907382740 | MASTER PL-C 26W/827/4P 1CT/5X10BOX | 827 | Incandescent White | 2700 K | 82 |
| 927907383001 | MASTER PL-C 26W/830/4P 1CT/5X10CC | 830 | Warm White (WW) | 3000 K | 82 |
| 927907383003 | MASTER PL-C 26W/830/4P 1CT/5X10CC | 830 | Warm White (WW) | 3000 K | 82 |
| 927907383040 | MASTER PL-C 26W/830/4P 1CT/5X10BOX | 830 | Warm White (WW) | 3000 K | 82 |
| 927907384002 | MASTER PL-C 26W/840/4P 1CT/5X10BOX | 840 | Cool White (CW) | 4000 K | 82 |
| 927907384004 | MASTER PL-C 26W/840/4P 1CT/5X10CC | 840 | Cool White (CW) | 4100 K | 82 |
| 927907384040 | MASTER PL-C 26W/840/4P 1CT/5X10BOX | 840 | Cool White (CW) | 4000 K | 82 |
| 927907386501 | MASTER PL-C 26W/865/4P 1CT/5X10BOX | 865 | Cool Daylight | 6500 K | 80 |
| 927907386565 | MASTER PL-C 26W/865/4P 1CT/5X10BOX | 865 | Cool Daylight | 6500 K | 80 |

Light Technical (2/2)

MASTER PL-C 4 Pin

| Order Code | Full Product Name | LLMF | | | | | Luminous Efficacy (rated) (Nom) | Luminous Flux (Nom) | Luminous Flux (Rated) (Nom) |
|--------------|--|------------------|----------------------|----------------------|----------------------|----------------------|------------------------------------|------------------------|--------------------------------|
| | | 12000 h Rated | LLMF 2000 h Rated | LLMF 4000 h Rated | LLMF 6000 h Rated | LLMF 8000 h Rated | | | |
| 927907083040 | MASTER PL-C 10W/830/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 60 lm/W | 600 lm | 600 lm |
| 927907084040 | MASTER PL-C 10W/840/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 60 lm/W | 600 lm | 600 lm |
| 927907182701 | MASTER PL-C 13W/827/4P 1CT/ 5X10CC | - | 92 % | 87 % | 83 % | 81 % | 69 lm/W | 925 lm | 925 lm |
| 927907182740 | MASTER PL-C 13W/827/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 69 lm/W | 925 lm | 925 lm |
| 927907183001 | MASTER PL-C 13W/830/4P 1CT/ 5X10CC | - | 92 % | 87 % | 83 % | 81 % | 72 lm/W | 900 lm | 900 lm |
| 927907183040 | MASTER PL-C 13W/830/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 72 lm/W | 900 lm | 900 lm |
| 927907184002 | MASTER PL-C 13W/840/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 69 lm/W | 925 lm | 925 lm |
| 927907184040 | MASTER PL-C 13W/840/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 69 lm/W | 925 lm | 925 lm |
| 927907186501 | MASTER PL-C 13W/865/4P 1CT/ 5X10BOX | - | 90 % | 85 % | 81 % | 77 % | 63 lm/W | 845 lm | 845 lm |
| 927907282701 | MASTER PL-C 18W/827/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927907282740 | MASTER PL-C 18W/827/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927907283001 | MASTER PL-C 18W/830/4P 1CT/ 5X10CC | 81 % | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927907283040 | MASTER PL-C 18W/830/4P 1CT/ 5X10BOX | 81 % | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927907284003 | MASTER PL-C 18W/840/4P 1CT/ 5X10CC | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927907284040 | MASTER PL-C 18W/840/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927907284065 | MASTER PL-C 18W/840/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927907286501 | MASTER PL-C 18W/865/4P 1CT/ 5X10BOX | - | 90 % | 85 % | 81 % | 77 % | 62.3 lm/W | 1120 lm | 1120 lm |
| 927907382701 | MASTER PL-C 26W/827/4P 1CT/ 5X10CC | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1800 lm | 1800 lm |
| 927907382703 | MASTER PL-C 26W/827/4P 1CT/ 5X10CC | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1800 lm | 1800 lm |
| 927907382740 | MASTER PL-C 26W/827/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1800 lm | 1800 lm |
| 927907383001 | MASTER PL-C 26W/830/4P 1CT/ 5X10CC | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1800 lm | 1800 lm |
| 927907383003 | MASTER PL-C 26W/830/4P 1CT/ 5X10CC | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1800 lm | 1800 lm |
| 927907383040 | MASTER PL-C 26W/830/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1800 lm | 1800 lm |
| 927907384002 | MASTER PL-C 26W/840/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1800 lm | 1800 lm |
| 927907384004 | MASTER PL-C 26W/840/4P 1CT/ 5X10CC | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1800 lm | 1800 lm |

MASTER PL-C 4 Pin

| Order Code | Full Product Name | LLMF | | | | | Luminous Efficacy (rated) (Nom) | Luminous Flux (Nom) | Luminous Flux (Rated) (Nom) |
|--------------|--|------------------|----------------------|----------------------|----------------------|----------------------|------------------------------------|------------------------|--------------------------------|
| | | 12000 h Rated | LLMF 2000 h Rated | LLMF 4000 h Rated | LLMF 6000 h Rated | LLMF 8000 h Rated | | | |
| 927907384040 | MASTER PL-C 26W/840/4P 1CT/ 5X10BOX | - | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1800 lm | 1800 lm |
| 927907386501 | MASTER PL-C 26W/865/4P 1CT/ 5X10BOX | - | 90 % | 85 % | 81 % | 77 % | 66 lm/W | 1740 lm | 1740 lm |
| 927907386565 | MASTER PL-C 26W/865/4P 1CT/ 5X10BOX | - | 90 % | 85 % | 81 % | 77 % | 66 lm/W | 1740 lm | 1740 lm |

