



MasterColor CDM ED17 Protected

MasterColor CDM ED17 Protected

Direct retrofit with immediate energy savings! Range of protected, high-efficiency long life ceramic metal halide lamps with a stable color over lifetime and a crisp, sparkling light to be used in open fixtures.

Benefits

- Environmentally Responsible TCLP* Compliant ALTO® Lamp Technology.
- High lamp efficacy (up to 95 LPW)
- Energy-efficient alternative to incandescent/halogen.
- * The TCLP is the US EPA's Toxicity Characteristic Leaching Procedure.

Features

- Excellent Color Rendering.
- Superior Color Stability Over Life.
- Total Cost of Ownership Benefits.
- FadeBlock—Lamps feature integrated UV blocking medium for reduced fading of fabrics and paintings.
- Available in 50, 70, 100, and 150 watt with 3000 & 4000K color temperatures.

Application

- Ideal for general lighting, downlighting, and flood lighting.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA: 21 CFR 1040.30 Canada: SOR/DORS/80-381)

MasterColor CDM ED17 Protected

Versions



E26, ED-17P, CL, Alto & Fadeblock



E26, ED-17P, CL, Elite, 50W /940




E26, ED-17P, CL, Elite, 50W-100W /930



E26 ED17, ED-17P Coated

Dimensional drawing



Product	D	C (max)
MHC150/U/MP/3K ALTO 12PK	2.125 in	5.438 in
MHC150/U/MP/4K ALTO 12PK	2.125 in	5.438 in
MHC50/U/MP/3K ELITE	2.125 in	5.438 in
MHC70/U/MP/3K ELITE	2.125 in	5.438 in
MHC70/C/U/MP/3K ELITE	2.125 in	5.438 in
MHC100/U/MP/3K ELITE	2.125 in	5.438 in
MHC100/C/U/MP/3K ELITE	2.125 in	5.438 in

Product details



E26, ED-17P, CL, Elite,
50W-100W /930

MasterColor CDM ED17 Protected

General Information

Cap-Base	E26
Operating Position	UNIVERSAL

Luminaire Design Requirements

Bulb Temperature (Max)	400 °C
------------------------	--------

Mechanical and Housing

Bulb Material	Hard Glass
Bulb Shape	ED-17P

Approval and Application

Order Code	Full Product Name	Mercury		
		Mercury (Hg) Content (Max)	Mercury (Hg) Content (Nom)	Picogram Per Lumen Hour
928601171501	MHC150/U/MP/3K ALTO 12PK	14.85 mg	-	98.3 pg/lm.h
928601171701	MHC150/U/MP/4K ALTO 12PK	-	12.3 mg	63.3 pg/lm.h
928601173701	MHC50/U/MP/3K ELITE	6.6 mg	-	103.9 pg/lm.h
928601173801	MHC70/U/MP/3K ELITE	8 mg	-	88.6 pg/lm.h

Order Code	Full Product Name	Mercury		
		Mercury (Hg) Content (Max)	Mercury (Hg) Content (Nom)	Picogram Per Lumen Hour
928601174001	MHC100/U/MP/3K ELITE	10.1 mg	-	72.4 pg/lm.h
928601173901	MHC70/C/U/MP/3K ELITE	7.6 mg	-	88.6 pg/lm.h
928601174101	MHC100/C/U/MP/3K ELITE	10.1 mg	-	79 pg/lm.h

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)	Power (Rated) (Nom)	Re-Ignition Time (Min) (Max)
928601171501	MHC150/U/MP/3K ALTO 12PK	1.8 A	105 V	85 V	95 V	-	12 min
928601171701	MHC150/U/MP/4K ALTO 12PK	1.8 A	105 V	85 V	95 V	-	12 min
928601173701	MHC50/U/MP/3K ELITE	0.59 A	110 V	87 V	95 V	50.2 W	8 min
928601173801	MHC70/U/MP/3K ELITE	0.92 A	120 V	92 V	100 V	70.4 W	8 min
928601174001	MHC100/U/MP/3K ELITE	1.1 A	115 V	87 V	101 V	-	10 min
928601173901	MHC70/C/U/MP/3K ELITE	0.92 A	120 V	92 V	100 V	70.4 W	8 min
928601174101	MHC100/C/U/MP/3K ELITE	1.1 A	115 V	87 V	101 V	-	10 min

General Information

Order Code	Full Product Name	Life To 50% Failures (Min)	Life To 50% Failures (Nom)	Main Application
		928601171501	MHC150/U/MP/3K ALTO 12PK	
928601171701	MHC150/U/MP/4K ALTO 12PK	20000 h	-	General Lighting (G)
928601173701	MHC50/U/MP/3K ELITE	-	16000 h	General Lighting (G)
928601173801	MHC70/U/MP/3K ELITE	-	16000 h	General and Street Lighting

Order Code	Full Product Name	Life To 50% Failures (Min)	Life To 50% Failures (Nom)	Main Application
		928601174001	MHC100/U/MP/3K ELITE	
928601173901	MHC70/C/U/MP/3K ELITE	-	16000 h	General and Street Lighting
928601174101	MHC100/C/U/MP/3K ELITE	-	16000 h	General and Street Lighting

Light Technical (1/3)

MasterColor CDM ED17 Protected

Order Code	Full Product Name	Chromaticity	Chromaticity	Chromaticity	Chromaticity	Chromaticity	Chromaticity	Color Code
		Coordinate X (Max)	Coordinate X (Min)	Coordinate X (Nom)	Coordinate Y (Max)	Coordinate Y (Min)	Coordinate Y (Nom)	
928601171501	MHC150/U/MP/3K ALTO 12PK	0.443	0.425	0.434	0.398	0.386	0.392	830
928601171701	MHC150/U/MP/4K ALTO 12PK	0.387	0.369	0.378	0.372	0.360	0.366	940
928601173701	MHC50/U/MP/3K ELITE	0.444	0.426	0.435	0.399	0.387	0.393	930
928601173801	MHC70/U/MP/3K ELITE	0.379	0.361	0.370	0.368	0.356	0.362	930
928601174001	MHC100/U/MP/3K ELITE	0.443	0.425	0.434	0.407	0.395	0.401	930
928601173901	MHC70/C/U/MP/3K ELITE	0.454	0.436	0.445	0.403	0.391	0.397	930
928601174101	MHC100/C/U/MP/3K ELITE	0.447	0.429	0.438	0.409	0.397	0.403	930

Light Technical (2/3)

Order Code	Full Product Name	Color Designation	Correlated Color	Color	Color	Lumen	Lumen	Luminous	Luminous	Design
			Temperature (Nom)	Rendering Index (Min)	Rendering Index (Nom)	Maintenance - 10% Life	Maintenance - 40% Life	Efficacy (rated) (Min)	Efficacy (rated) (Nom)	Mean Lumens
928601171501	MHC150/U/MP/3K ALTO 12PK	Warm White (WW)	3000 K	80	83	85 %	70 %	77.4 lm/W	86 lm/W	9030 lm
928601171701	MHC150/U/MP/4K ALTO 12PK	Deluxe Cool White	4000 K	87	90	87 %	75 %	73 lm/W	80 lm/W	9000 lm
928601173701	MHC50/U/MP/3K ELITE	Warm White (WW)	3000 K	87	90	95 %	90 %	88 lm/W	96 lm/W	4300 lm
928601173801	MHC70/U/MP/3K ELITE	Warm White (WW)	2900 K	87	90	95 %	90 %	87 lm/W	95 lm/W	6400 lm
928601174001	MHC100/U/MP/3K ELITE	Warm White (WW)	3000 K	87	90	95 %	90 %	94 lm/W	100 lm/W	9500 lm
928601173901	MHC70/C/U/MP/3K ELITE	Warm White (WW)	2900 K	87	90	95 %	90 %	78 lm/W	87 lm/W	5800 lm
928601174101	MHC100/C/U/MP/3K ELITE	Warm White (WW)	3000 K	87	90	95 %	90 %	86 lm/W	92 lm/W	8700 lm

Light Technical (3/3)

Order Code	Full Product Name	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)	Order Code	Full Product Name	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)
928601171501	MHC150/U/MP/3K ALTO 12PK	11600 lm	12900 lm	928601174001	MHC100/U/MP/3K ELITE	9000 lm	10000 lm
928601171701	MHC150/U/MP/4K ALTO 12PK	11000 lm	12000 lm	928601173901	MHC70/C/U/MP/3K ELITE	5500 lm	6100 lm
928601173701	MHC50/U/MP/3K ELITE	4400 lm	4800 lm	928601174101	MHC100/C/U/MP/3K ELITE	8300 lm	9200 lm
928601173801	MHC70/U/MP/3K ELITE	6100 lm	6700 lm				

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Order Code	Full Product Name	Bulb Finish
928601171501	MHC150/U/MP/3K ALTO 12PK	Clear	928601174001	MHC100/U/MP/3K ELITE	Clear
928601171701	MHC150/U/MP/4K ALTO 12PK	Clear	928601173901	MHC70/C/U/MP/3K ELITE	Coated glass
928601173701	MHC50/U/MP/3K ELITE	Clear	928601174101	MHC100/C/U/MP/3K ELITE	Coated glass
928601173801	MHC70/U/MP/3K ELITE	Clear			

