



# Highly reliable drivers for medium-wattage lamps

## PrimaVision for CDM Elite MW

Highly reliable electronic drivers for medium-wattage lamps: 80,000 hours lifetime for the Xtreme version and 50,000 hours for the non-Xtreme versions

### Benefits

- Most efficient white-light system in the industry in its power range
- Minimized maintenance costs for outdoor lighting thanks to very long lifetime
- Same energy consumption and smooth driving of the lamp regardless of fluctuations in mains voltage

### Features

- Up to 92% system efficiency
- PrimaVision Xtreme 210W CDM lifetime: 80,000 hours (90% survival  $T_c = 80\text{ }^{\circ}\text{C}$ )
- PrimaVision Xtreme 210W CDM: 5 kA/10 kV lightning strike protection
- PrimaVision 315W CDM: lifetime 50,000 hours

### Application

- High-bay shop lighting
- Flood and area lighting
- Road lighting and petrol stations
- Offices and industry

