



Philips Twistline GU10

Twistline GU10

Bright, white accent light with superior energy savings Philips Twistline GU10 Philips Halogen Twistline MR16 with GU10 base provide bright white accent light. The twist and lock base enables easy installation and a secure fit. Suited for track and recessed lighting applications.

Benefits

- Easy to install and maintain a secure fit.
- Highlight art and featured objects for decorative accent.

Features

- Bright, white light.
- Easy to use twist and lock base.
- Available in a variety of wattages operating on 120 volts.
- Available in 25,35 and 50 Watts.

Application

- Ideal for indoor recessed and track fixtures, floor and desk lamps.

Versions




20W/25W/35W/40W, GU10



50W, GU10, MR16

Twistline GU10

Dimensional drawing



Product	D (max)	C (max)
BC50TWISTLINE GU10/FL 6/6	50.7 mm	47.5 mm
BC35 TWISTLINE GU10/FL25 TP	50.7 mm	53 mm
BC25 TWISTLINE GU10 / FL25	50.7 mm	53 mm
BC50TWISTLINE GU10/FL25 TP	51 mm	53 mm
50TWISTERLINE/FL 120V5/6	51 mm	53 mm
BC50GU10/HAL/TL 120V 6/3	51 mm	53 mm

Approval and Application

Energy Efficiency Label (EEL)	Not applicable
-------------------------------	----------------

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Voltage (Nom)	120 V
Starting Time (Nom)	0.0 s

General Information

Cap-Base	GU10
Nominal Lifetime (Nom)	2000 h
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	2000 h

Light Technical

Correlated Color Temperature (Nom)	2800 K
Color Rendering Index (Nom)	100

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	MR16

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
924712536386	BC50TWISTLINE GU10/FL 6/6	50 W
924887136384	BC35 TWISTLINE GU10/FL25 TP	35 W
924887736301	BC25 TWISTLINE GU10 / FL25	25 W
925691836307	BC50TWISTLINE GU10/FL25 TP	50 W
925691836308	50TWISTERLINE/FL 120V5/6	50 W
925691836309	BC50GU10/HAL/TL 120V 6/3	50 W

General Information

Order Code	Full Product Name	Philips Code
924712536386	BC50TWISTLINE GU10/FL 6/6	NA
924887136384	BC35 TWISTLINE GU10/FL25 TP	-
924887736301	BC25 TWISTLINE GU10 / FL25	-

Order Code	Full Product Name	Philips Code
925691836307	BC50TWISTLINE GU10/FL25 TP	-
925691836308	50TWISTERLINE/FL 120V5/6	-
925691836309	BC50GU10/HAL/TL 120V 6/3	-


Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Luminous Intensity (Max)	Rated Beam Angle
924712536386	BC50TWISTLINE GU10/FL 6/6	40 °	400 cd	-


Order Code	Full Product Name	Beam Angle (Nom)	Luminous Intensity (Max)	Rated Beam Angle
924887136384	BC35 TWISTLINE GU10/FL25 TP	20 °	800 cd	-

Twistline GU10

Order Code	Full Product Name	Beam Angle (Nom)	Luminous Intensity (Max)	Rated Beam Angle
924887736301	BC25 TWISTLINE GU10 / FL25	25 °	400 cd	25 °
925691836307	BC50TWISTLINE GU10/FL25 TP	25 °	700 cd	-
925691836308	50TWISTERLINE/FL 120V5/6	25 °	700 cd	-
925691836309	BC50GU10/HAL/TL 120V 6/3	25 °	700 cd	-




Accent Diagrams



LDAC_HTWIST_Dichr_25D-Accent diagram

Beam Diagrams



LDBE_HTWIST_Dichr_25D-Beam diagram

