



Spot of crisp white light – modern alternative to conventional reflector lamps

HalogenA PAR20

Mains-voltage halogen reflector that is easy to install instead of conventional reflector lamps, putting your objects in a superior-quality spot light. Provides crisp halogen light over a long lifetime.

Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Universal burning position
- Instant start

Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops


HalogenA PAR20

Versions




E27, PAR20, 25°


Dimensional drawing



Product	D (max)	C (max)
PAR20 HAL 50W E27 120V 25D 1CT/15	63.5 mm	105 mm



Accent Diagrams



HalogenA PAR20

Beam Diagrams

$\sqrt{VRA} \quad 2 \times 17 \quad 1/4 \quad 1 \times 2 \times 16 \quad h \quad E \quad d(m)$

LDBE_HPAR20_25D-Beam diagram

