



# Crisp halogen spot light from aluminum-cast reflector

## Aluline 37/56

Low-voltage halogen burner in specialized aluminum reflector prevents heat in the backlight; bayonet cap for secure fitting

### Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement cost due to longer burning hours

### Features

- Superior quality of light with excellent color rendering (Ra=100)
- Low-pressure technology with UV-block glass allows use in luminaires without front glass
- Dichroic coating
- Universal burning position
- Instant start

### Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops


# Aluline 37/56

## Versions




B15 R56 Clear


## Dimensional drawing



Product	D (max)	C (max)
Aluline 50W 12V R56 25D CL 1CT/10X5F	58 mm	58 mm



## Accent Diagrams



## Beam Diagrams

VRΔ	2 × 25	1/4	13	h	E	d(m)
-----	--------	-----	----	---	---	------

LD BE\_HALUPAB\_50W\_25D-Beam diagram

