



CoreLine recessed – for every project, where light really matters

CoreLine Recessed

CoreLine recessed delivers on the CoreLine promise of innovative, easy-to-use, high-quality luminaires. The high-quality CoreLine recessed is designed to replace existing recessed luminaires with T8 or T5 technology. This family features an innovative new choice of multiple lumen outputs in one single luminaire, called MultiLumen. Instant energy savings and a longer lifetime, make this is an environmentally friendly and cost saving solution. With a quick-connector feature, our recessed luminaires are simple and easy to install. Also available within the range are Interact Ready luminaires with integrated wireless communications, fully compatible with Interact gateways, sensors and software.

Benefits

- MultiLumen: the choice of different lumen outputs in one single luminaire
- New connector offers simpler and faster installation
- Energy savings and longer lifetime to reduce operating costs

Features

- MultiLumen: different lumen outputs ranging from 2800 lumen to 4300 lumen in one single luminaire
- Easy connector for faster installation
- Energy efficient and long lifetime: up to 140lm/W and 50khrs L80 lifetime
- Many flicker-free drivers available: On/off (PSU), dimming (Dali) and integrated wireless connectivity (Interact Ready)
- Office compliant versions (OC) & Non-office compliant versions (NOC). Optional versions available: Emergency Lighting (EL) & Wieland/Adels connectors (W)

CoreLine Recessed

Application

- Offices
- Retail
- Education

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Versions



Coreline Recessed



Coreline Recessed

Product details



CoreLine Recessed-
RC134B_plaster ceiling
frame_hook-DPP.TIF



CoreLine_Recessed-
RC134B_plaster_ceiling_W30L120
-DPP.tif



CoreLine_Recessed-
RC134B_plaster_ceiling_frame_W
60L60-DPP.tif



CoreLine_Recessed-
RC134B_plaster_ceiling_W60L60-
DPP.tif

CoreLine Recessed

Product details



CoreLine_Recessed-RC134B_W60L60-DPP.tif



CoreLine_Recessed-RC134B_led_compartment-DPP.tif



CoreLine_Recessed-RC134B_W30L120-DPP.tif



CoreLine_Recessed-RC134B_W30L120_electr-DPP.tif



CoreLine_Recessed-RC134B_W30L120_led_compartment-DPP.tif

Accessories

Coreline Recessed Acc.

Ordercode 910925864621,
910925864622



Coreline Recessed Acc.

Ordercode 910925864623



Application Conditions

| | |
|-------------------------------|---------------|
| Ambient temperature range | +10 to +40 °C |
| Suitable for random switching | Yes |

Approval and Application

| | |
|------------------------------|------|
| Mech. impact protection code | IK02 |
|------------------------------|------|

General Information

| | |
|--------------------------|---|
| CE mark | CE mark |
| Protection class IEC | Safety class I |
| Driver included | Yes |
| ENEC mark | ENEC mark |
| Flammability mark | For mounting on normally flammable surfaces |
| Glow-wire test | Temperature 850 °C, duration 30 s |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Optic type | Wide beam |
| Service tag | Yes |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|-------|
| Init. Color Rendering Index | ≥80 |
| Luminous flux tolerance | +/-8% |

Mechanical and Housing

| | |
|-------|-------|
| Color | White |
|-------|-------|

Application Conditions

| Order Code | Full Product Name | Maximum dim level |
|--------------|--|-----------------------------------|
| 910925864752 | RC134B LED37S/830 PSU W60L60 NOC | Not applicable |
| 910925864753 | RC134B LED27S/830 PSU W60L60 NOC | Not applicable |
| 910925864756 | RC134B LED37S/840 PSD W60L60 NOC | 1% |
| 910925864758 | RC134B LED37S/830 PSD W60L60 NOC | 1% |
| 910925864759 | RC134B LED27S/830 PSD W60L60 NOC | 1% |
| 910925864762 | RC134B LED37S/840 PSD W60L60 OC | 1% |
| 910925864768 | RC134B LED27S/840 PSD W60L60 OC | 1% |
| 910925864771 | RC134B LED37S/830 PSD W60L60 OC | 1% |
| 910925864772 | RC134B LED27S/830 PSD W60L60 OC | 1% |
| 910925864775 | RC134B LED37S/840 PSU W60L60 NOC | Not applicable |
| 910925864777 | RC134B LED37S/840 PSU W60L60 ELB3 NOC | Not applicable |
| 910925864778 | RC134B LED37S/840 PSD W60L60 ELB3 NOC | 1% (no dimming in emergency mode) |
| 910925864779 | RC134B LED37S/840 PSD W60L60 ELB3 OC | 1% (no dimming in emergency mode) |
| 910925864780 | RC134B LED27S/840 PSD W60L60 ELB3 OC | 1% (no dimming in emergency mode) |
| 910925864781 | RC134B LED27S/840 PSU W60L60 NOC | Not applicable |
| 910925864783 | RC134B LED27S/840 PSD W60L60 NOC | 1% |
| 910925864785 | RC134B LED27S/840 PSU W60L60 ELB3 NOC | Not applicable |
| 910925864786 | RC134B LED27S/840 PSD W60L60 ELB3 NOC | 1% (no dimming in emergency mode) |
| 910925864787 | RC134B LED37S/840 PSU W60L60 OC | Not applicable |
| 910925864789 | RC134B LED37S/830 PSU W60L60 OC | Not applicable |
| 910925864803 | RC135B LED37S/840 PSU W62L62 NOC | Not applicable |
| 910925864804 | RC135B LED37S/840 PSD W62L62 OC | 1% |
| 910925864805 | RC135B LED27S/840 PSD W62L62 OC | 1% |
| 910925864806 | RC135B LED37S/840 PSU W62L62 OC | Not applicable |
| 910925864807 | RC135B LED27S/840 PSU W62L62 NOC | Not applicable |
| 910925864808 | RC135B LED27S/840 PSD W62L62 NOC | 1% |
| 910925864809 | RC135B LED37S/840 PSD W62L62 NOC | 1% |
| 910925865169 | RC134B LED37S/840 W60L60 IA1 OC | 1% |
| 910925865170 | RC134B LED37S/840 W60L60 IA1 NOC | 1% |
| 910925865171 | RC134B LED37S/830 W60L60 IA1 NOC | 1% |
| 910925865172 | RC134B LED37S/830 W60L60 IA1 OC | 1% |
| 910925865173 | RC135B LED37S/840 W62L62 IA1 OC | 1% |
| 910925865176 | RC135B LED37S/840 W62L62 IA1 NOC | 1% |
| 910925865179 | RC134B LED37S/840 W60L60 ELB3 IA1 NOC | 1% |
| 910925865180 | RC134B LED37S/840 W60L60 ELB3 IA1 OC | 1% |
| 910925864754 | RC134B LED37S/830 PSU W30L120 NOC | Not applicable |
| 910925864755 | RC134B LED27S/830 PSU W30L120 NOC | Not applicable |
| 910925864757 | RC134B LED37S/840 PSD W30L120 NOC | 1% |
| 910925864760 | RC134B LED37S/830 PSD W30L120 NOC | 1% |
| 910925864761 | RC134B LED27S/830 PSD W30L120 NOC | 1% |
| 910925864769 | RC134B LED37S/840 PSD W30L120 OC | 1% |
| 910925864770 | RC134B LED27S/840 PSD W30L120 OC | 1% |
| 910925864773 | RC134B LED37S/830 PSD W30L120 OC | 1% |
| 910925864774 | RC134B LED27S/830 PSD W30L120 OC | 1% |
| 910925864776 | RC134B LED37S/840 PSU W30L120 NOC | Not applicable |
| 910925864782 | RC134B LED27S/840 PSU W30L120 NOC | Not applicable |
| 910925864784 | RC134B LED27S/840 PSD W30L120 NOC | 1% |
| 910925864788 | RC134B LED37S/840 PSU W30L120 OC | Not applicable |
| 910925864790 | RC134B LED37S/830 PSU W30L120 OC | Not applicable |
| 910925864791 | RC134B LED27S/840 PSU W30L120 ELB3 NOC | Not applicable |
| 910925864792 | RC134B LED37S/840 PSU W30L120 ELB3 NOC | Not applicable |

| Order Code | Full Product Name | Maximum dim level |
|--------------|--|-----------------------------------|
| 910925864793 | RC134B LED27S/840 PSD W30L120 ELB3 NOC | 1% (no dimming in emergency mode) |
| 910925864794 | RC134B LED37S/840 PSD W30L120 ELB3 NOC | 1% (no dimming in emergency mode) |
| 910925864795 | RC134B LED27S/840 PSD W30L120 ELB3 OC | 1% (no dimming in emergency mode) |
| 910925864796 | RC134B LED37S/840 PSD W30L120 ELB3 OC | 1% (no dimming in emergency mode) |
| 910925864797 | RC134B LED27S/830 PSU W30L120 ELB3 NOC | Not applicable |
| 910925864798 | RC134B LED37S/830 PSU W30L120 ELB3 NOC | Not applicable |
| 910925864799 | RC134B LED27S/830 PSD W30L120 ELB3 NOC | 1% (no dimming in emergency mode) |
| 910925864801 | RC134B LED37S/830 PSD W30L120 ELB3 NOC | 1% (no dimming in emergency mode) |
| 910925864802 | RC134B LED37S/830 PSD W30L120 ELB3 OC | 1% (no dimming in emergency mode) |
| 910925865174 | RC134B LED37S/840 W30L120 IA1 NOC | 1% |
| 910925865175 | RC134B LED37S/840 W30L120 IA1 OC | 1% |
| 910925865177 | RC134B LED37S/830 W30L120 IA1 OC | 1% |
| 910925865178 | RC134B LED37S/830 W30L120 IA1 NOC | 1% |
| 910925865181 | RC134B LED37S/840 W30L120 ELB3 IA1 OC | 1% |
| 910925865182 | RC134B LED37S/840 W30L120 ELB3 IA1 NOC | 1% |

Approval and Application

| Order Code | Full Product Name | Ingress protection code |
|--------------|---------------------------------------|-------------------------|
| 910925864752 | RC134B LED37S/830 PSU W60L60 NOC | IP44 |
| 910925864753 | RC134B LED27S/830 PSU W60L60 NOC | IP44 |
| 910925864756 | RC134B LED37S/840 PSD W60L60 NOC | IP44 |
| 910925864758 | RC134B LED37S/830 PSD W60L60 NOC | IP44 |
| 910925864759 | RC134B LED27S/830 PSD W60L60 NOC | IP44 |
| 910925864762 | RC134B LED37S/840 PSD W60L60 OC | IP44 |
| 910925864768 | RC134B LED27S/840 PSD W60L60 OC | IP44 |
| 910925864771 | RC134B LED37S/830 PSD W60L60 OC | IP44 |
| 910925864772 | RC134B LED27S/830 PSD W60L60 OC | IP44 |
| 910925864775 | RC134B LED37S/840 PSU W60L60 NOC | IP44 |
| 910925864777 | RC134B LED37S/840 PSU W60L60 ELB3 NOC | IP44 |
| 910925864778 | RC134B LED37S/840 PSD W60L60 ELB3 NOC | IP44 |
| 910925864779 | RC134B LED37S/840 PSD W60L60 ELB3 OC | IP44 |
| 910925864780 | RC134B LED27S/840 PSD W60L60 ELB3 OC | IP44 |
| 910925864781 | RC134B LED27S/840 PSU W60L60 NOC | IP44 |
| 910925864783 | RC134B LED27S/840 PSD W60L60 NOC | IP44 |
| 910925864785 | RC134B LED27S/840 PSU W60L60 ELB3 NOC | IP44 |
| 910925864786 | RC134B LED27S/840 PSD W60L60 ELB3 NOC | IP44 |
| 910925864787 | RC134B LED37S/840 PSU W60L60 OC | IP44 |
| 910925864789 | RC134B LED37S/830 PSU W60L60 OC | IP44 |
| 910925864803 | RC135B LED37S/840 PSU W62L62 NOC | IP44 |
| 910925864804 | RC135B LED37S/840 PSD W62L62 OC | IP44 |
| 910925864805 | RC135B LED27S/840 PSD W62L62 OC | IP44 |
| 910925864806 | RC135B LED37S/840 PSU W62L62 OC | IP44 |
| 910925864807 | RC135B LED27S/840 PSU W62L62 NOC | IP44 |
| 910925864808 | RC135B LED27S/840 PSD W62L62 NOC | IP44 |
| 910925864809 | RC135B LED37S/840 PSD W62L62 NOC | IP44 |
| 910925865169 | RC134B LED37S/840 W60L60 IA1 OC | IP20/44 |
| 910925865170 | RC134B LED37S/840 W60L60 IA1 NOC | IP20/44 |
| 910925865171 | RC134B LED37S/830 W60L60 IA1 NOC | IP20/44 |
| 910925865172 | RC134B LED37S/830 W60L60 IA1 OC | IP20/44 |
| 910925865173 | RC135B LED37S/840 W62L62 IA1 OC | IP20/44 |

| Order Code | Full Product Name | Ingress protection code |
|--------------|--|-------------------------|
| 910925865176 | RC135B LED37S/840 W62L62 IA1 NOC | IP20/44 |
| 910925865179 | RC134B LED37S/840 W60L60 ELB3 IA1 NOC | IP20/44 |
| 910925865180 | RC134B LED37S/840 W60L60 ELB3 IA1 OC | IP20/44 |
| 910925864754 | RC134B LED37S/830 PSU W30L120 NOC | IP44 |
| 910925864755 | RC134B LED27S/830 PSU W30L120 NOC | IP44 |
| 910925864757 | RC134B LED37S/840 PSD W30L120 NOC | IP44 |
| 910925864760 | RC134B LED37S/830 PSD W30L120 NOC | IP44 |
| 910925864761 | RC134B LED27S/830 PSD W30L120 NOC | IP44 |
| 910925864769 | RC134B LED37S/840 PSD W30L120 OC | IP44 |
| 910925864770 | RC134B LED27S/840 PSD W30L120 OC | IP44 |
| 910925864773 | RC134B LED37S/830 PSD W30L120 OC | IP44 |
| 910925864774 | RC134B LED27S/830 PSD W30L120 OC | IP44 |
| 910925864776 | RC134B LED37S/840 PSU W30L120 NOC | IP44 |
| 910925864782 | RC134B LED27S/840 PSU W30L120 NOC | IP44 |
| 910925864784 | RC134B LED27S/840 PSD W30L120 NOC | IP44 |
| 910925864788 | RC134B LED37S/840 PSU W30L120 OC | IP44 |
| 910925864790 | RC134B LED37S/830 PSU W30L120 OC | IP44 |
| 910925864791 | RC134B LED27S/840 PSU W30L120 ELB3 NOC | IP44 |
| 910925864792 | RC134B LED37S/840 PSU W30L120 ELB3 NOC | IP44 |
| 910925864793 | RC134B LED27S/840 PSD W30L120 ELB3 NOC | IP44 |
| 910925864794 | RC134B LED37S/840 PSD W30L120 ELB3 NOC | IP44 |
| 910925864795 | RC134B LED27S/840 PSD W30L120 ELB3 OC | IP44 |
| 910925864796 | RC134B LED37S/840 PSD W30L120 ELB3 OC | IP44 |
| 910925864797 | RC134B LED27S/830 PSU W30L120 ELB3 NOC | IP44 |
| 910925864798 | RC134B LED37S/830 PSU W30L120 ELB3 NOC | IP44 |
| 910925864799 | RC134B LED27S/830 PSD W30L120 ELB3 NOC | IP44 |
| 910925864801 | RC134B LED37S/830 PSD W30L120 ELB3 NOC | IP44 |
| 910925864802 | RC134B LED37S/830 PSD W30L120 ELB3 OC | IP44 |
| 910925865174 | RC134B LED37S/840 W30L120 IA1 NOC | IP20/44 |
| 910925865175 | RC134B LED37S/840 W30L120 IA1 OC | IP20/44 |
| 910925865177 | RC134B LED37S/830 W30L120 IA1 OC | IP20/44 |
| 910925865178 | RC134B LED37S/830 W30L120 IA1 NOC | IP20/44 |

CoreLine Recessed

| Order Code | Full Product Name | Ingress protection code |
|--------------|---------------------------------------|-------------------------|
| 910925865181 | RC134B LED37S/840 W30L120 ELB3 IA1 OC | IP20/44 |

| Order Code | Full Product Name | Ingress protection code |
|--------------|--|-------------------------|
| 910925865182 | RC134B LED37S/840 W30L120 ELB3 IA1 NOC | IP20/44 |

Controls and Dimming

| Order Code | Full Product Name | Dimmable |
|--------------|---------------------------------------|--------------|
| 910925864752 | RC134B LED37S/830 PSU W60L60 NOC | No |
| 910925864753 | RC134B LED27S/830 PSU W60L60 NOC | No |
| 910925864756 | RC134B LED37S/840 PSD W60L60 NOC | Yes |
| 910925864758 | RC134B LED37S/830 PSD W60L60 NOC | Yes |
| 910925864759 | RC134B LED27S/830 PSD W60L60 NOC | Yes |
| 910925864762 | RC134B LED37S/840 PSD W60L60 OC | Yes |
| 910925864768 | RC134B LED27S/840 PSD W60L60 OC | Yes |
| 910925864771 | RC134B LED37S/830 PSD W60L60 OC | Yes |
| 910925864772 | RC134B LED27S/830 PSD W60L60 OC | Yes |
| 910925864775 | RC134B LED37S/840 PSU W60L60 NOC | No |
| 910925864777 | RC134B LED37S/840 PSU W60L60 ELB3 NOC | No |
| 910925864778 | RC134B LED37S/840 PSD W60L60 ELB3 NOC | Yes |
| 910925864779 | RC134B LED37S/840 PSD W60L60 ELB3 OC | Yes |
| 910925864780 | RC134B LED27S/840 PSD W60L60 ELB3 OC | Yes |
| 910925864781 | RC134B LED27S/840 PSU W60L60 NOC | No |
| 910925864783 | RC134B LED27S/840 PSD W60L60 NOC | Yes |
| 910925864785 | RC134B LED27S/840 PSU W60L60 ELB3 NOC | No |
| 910925864786 | RC134B LED27S/840 PSD W60L60 ELB3 NOC | Yes |
| 910925864787 | RC134B LED37S/840 PSU W60L60 OC | No |
| 910925864789 | RC134B LED37S/830 PSU W60L60 OC | No |
| 910925864803 | RC135B LED37S/840 PSU W62L62 NOC | No |
| 910925864804 | RC135B LED37S/840 PSD W62L62 OC | Yes |
| 910925864805 | RC135B LED27S/840 PSD W62L62 OC | Yes |
| 910925864806 | RC135B LED37S/840 PSU W62L62 OC | No |
| 910925864807 | RC135B LED27S/840 PSU W62L62 NOC | No |
| 910925864808 | RC135B LED27S/840 PSD W62L62 NOC | Yes |
| 910925864809 | RC135B LED37S/840 PSD W62L62 NOC | Yes |
| 910925865169 | RC134B LED37S/840 W60L60 IA1 OC | Wireless Dim |
| 910925865170 | RC134B LED37S/840 W60L60 IA1 NOC | Wireless Dim |
| 910925865171 | RC134B LED37S/830 W60L60 IA1 NOC | Wireless Dim |
| 910925865172 | RC134B LED37S/830 W60L60 IA1 OC | Wireless Dim |
| 910925865173 | RC135B LED37S/840 W62L62 IA1 OC | Wireless Dim |
| 910925865176 | RC135B LED37S/840 W62L62 IA1 NOC | Wireless Dim |

| Order Code | Full Product Name | Dimmable |
|--------------|--|--------------|
| 910925865179 | RC134B LED37S/840 W60L60 ELB3 IA1 NOC | Wireless Dim |
| 910925865180 | RC134B LED37S/840 W60L60 ELB3 IA1 OC | Wireless Dim |
| 910925864754 | RC134B LED37S/830 PSU W30L120 NOC | No |
| 910925864755 | RC134B LED27S/830 PSU W30L120 NOC | No |
| 910925864757 | RC134B LED37S/840 PSD W30L120 NOC | Yes |
| 910925864760 | RC134B LED37S/830 PSD W30L120 NOC | Yes |
| 910925864761 | RC134B LED27S/830 PSD W30L120 NOC | Yes |
| 910925864769 | RC134B LED37S/840 PSD W30L120 OC | Yes |
| 910925864770 | RC134B LED27S/840 PSD W30L120 OC | Yes |
| 910925864773 | RC134B LED37S/830 PSD W30L120 OC | Yes |
| 910925864774 | RC134B LED27S/830 PSD W30L120 OC | Yes |
| 910925864776 | RC134B LED37S/840 PSU W30L120 NOC | No |
| 910925864782 | RC134B LED27S/840 PSU W30L120 NOC | No |
| 910925864784 | RC134B LED27S/840 PSD W30L120 NOC | Yes |
| 910925864788 | RC134B LED37S/840 PSU W30L120 OC | No |
| 910925864790 | RC134B LED37S/830 PSU W30L120 OC | No |
| 910925864791 | RC134B LED27S/840 PSU W30L120 ELB3 NOC | No |
| 910925864792 | RC134B LED37S/840 PSU W30L120 ELB3 NOC | No |
| 910925864793 | RC134B LED27S/840 PSD W30L120 ELB3 NOC | Yes |
| 910925864794 | RC134B LED37S/840 PSD W30L120 ELB3 NOC | Yes |
| 910925864795 | RC134B LED27S/840 PSD W30L120 ELB3 OC | Yes |
| 910925864796 | RC134B LED37S/840 PSD W30L120 ELB3 OC | Yes |
| 910925864797 | RC134B LED27S/830 PSU W30L120 ELB3 NOC | No |
| 910925864798 | RC134B LED37S/830 PSU W30L120 ELB3 NOC | No |
| 910925864799 | RC134B LED27S/830 PSD W30L120 ELB3 NOC | Yes |
| 910925864801 | RC134B LED37S/830 PSD W30L120 ELB3 NOC | Yes |
| 910925864802 | RC134B LED37S/830 PSD W30L120 ELB3 OC | Yes |
| 910925865174 | RC134B LED37S/840 W30L120 IA1 NOC | Wireless Dim |
| 910925865175 | RC134B LED37S/840 W30L120 IA1 OC | Wireless Dim |
| 910925865177 | RC134B LED37S/830 W30L120 IA1 OC | Wireless Dim |
| 910925865178 | RC134B LED37S/830 W30L120 IA1 NOC | Wireless Dim |
| 910925865181 | RC134B LED37S/840 W30L120 ELB3 IA1 OC | Wireless Dim |
| 910925865182 | RC134B LED37S/840 W30L120 ELB3 IA1 NOC | Wireless Dim |

Operating and Electrical

| Order Code | Full Product Name | Input Voltage |
|--------------|----------------------------------|---------------|
| 910925864752 | RC134B LED37S/830 PSU W60L60 NOC | 220 to 240 V |
| 910925864753 | RC134B LED27S/830 PSU W60L60 NOC | 220 to 240 V |
| 910925864756 | RC134B LED37S/840 PSD W60L60 NOC | 220 to 240 V |
| 910925864758 | RC134B LED37S/830 PSD W60L60 NOC | 220 to 240 V |
| 910925864759 | RC134B LED27S/830 PSD W60L60 NOC | 220 to 240 V |
| 910925864762 | RC134B LED37S/840 PSD W60L60 OC | 220 to 240 V |
| 910925864768 | RC134B LED27S/840 PSD W60L60 OC | 220 to 240 V |
| 910925864771 | RC134B LED37S/830 PSD W60L60 OC | 220 to 240 V |

| Order Code | Full Product Name | Input Voltage |
|--------------|---------------------------------------|---------------|
| 910925864772 | RC134B LED27S/830 PSD W60L60 OC | 220 to 240 V |
| 910925864775 | RC134B LED37S/840 PSU W60L60 NOC | 220 to 240 V |
| 910925864777 | RC134B LED37S/840 PSU W60L60 ELB3 NOC | 220 to 240 V |
| 910925864778 | RC134B LED37S/840 PSD W60L60 ELB3 NOC | 220 to 240 V |
| 910925864779 | RC134B LED37S/840 PSD W60L60 ELB3 OC | 220 to 240 V |
| 910925864780 | RC134B LED27S/840 PSD W60L60 ELB3 OC | 220 to 240 V |
| 910925864781 | RC134B LED27S/840 PSU W60L60 NOC | 220 to 240 V |
| 910925864783 | RC134B LED27S/840 PSD W60L60 NOC | 220 to 240 V |

CoreLine Recessed

| Order Code | Full Product Name | Input Voltage |
|--------------|---------------------------------------|---------------|
| 910925864785 | RC134B LED27S/840 PSU W60L60 ELB3 NOC | 220 to 240 V |
| 910925864786 | RC134B LED27S/840 PSD W60L60 ELB3 NOC | 220 to 240 V |
| 910925864787 | RC134B LED37S/840 PSU W60L60 OC | 220 to 240 V |
| 910925864789 | RC134B LED37S/830 PSU W60L60 OC | 220 to 240 V |
| 910925864803 | RC135B LED37S/840 PSU W62L62 NOC | 220 to 240 V |
| 910925864804 | RC135B LED37S/840 PSD W62L62 OC | 220 to 240 V |
| 910925864805 | RC135B LED27S/840 PSD W62L62 OC | 220 to 240 V |
| 910925864806 | RC135B LED37S/840 PSU W62L62 OC | 220 to 240 V |
| 910925864807 | RC135B LED27S/840 PSU W62L62 NOC | 220 to 240 V |
| 910925864808 | RC135B LED27S/840 PSD W62L62 NOC | 220 to 240 V |
| 910925864809 | RC135B LED37S/840 PSD W62L62 NOC | 220 to 240 V |
| 910925865169 | RC134B LED37S/840 W60L60 IA1 OC | 220-240 V |
| 910925865170 | RC134B LED37S/840 W60L60 IA1 NOC | 220-240 V |
| 910925865171 | RC134B LED37S/830 W60L60 IA1 NOC | 220-240 V |
| 910925865172 | RC134B LED37S/830 W60L60 IA1 OC | 220-240 V |
| 910925865173 | RC135B LED37S/840 W62L62 IA1 OC | 220-240 V |
| 910925865176 | RC135B LED37S/840 W62L62 IA1 NOC | 220-240 V |
| 910925865179 | RC134B LED37S/840 W60L60 ELB3 IA1 NOC | 220-240 V |
| 910925865180 | RC134B LED37S/840 W60L60 ELB3 IA1 OC | 220-240 V |
| 910925864754 | RC134B LED37S/830 PSU W30L120 NOC | 220 to 240 V |
| 910925864755 | RC134B LED27S/830 PSU W30L120 NOC | 220 to 240 V |
| 910925864757 | RC134B LED37S/840 PSD W30L120 NOC | 220 to 240 V |
| 910925864760 | RC134B LED37S/830 PSD W30L120 NOC | 220 to 240 V |
| 910925864761 | RC134B LED27S/830 PSD W30L120 NOC | 220 to 240 V |
| 910925864769 | RC134B LED37S/840 PSD W30L120 OC | 220 to 240 V |

| Order Code | Full Product Name | Input Voltage |
|--------------|--|---------------|
| 910925864770 | RC134B LED27S/840 PSD W30L120 OC | 220 to 240 V |
| 910925864773 | RC134B LED37S/830 PSD W30L120 OC | 220 to 240 V |
| 910925864774 | RC134B LED27S/830 PSD W30L120 OC | 220 to 240 V |
| 910925864776 | RC134B LED37S/840 PSU W30L120 NOC | 220 to 240 V |
| 910925864782 | RC134B LED27S/840 PSU W30L120 NOC | 220 to 240 V |
| 910925864784 | RC134B LED27S/840 PSD W30L120 NOC | 220 to 240 V |
| 910925864788 | RC134B LED37S/840 PSU W30L120 OC | 220 to 240 V |
| 910925864790 | RC134B LED37S/830 PSU W30L120 OC | 220 to 240 V |
| 910925864791 | RC134B LED27S/840 PSU W30L120 ELB3 NOC | 220 to 240 V |
| 910925864792 | RC134B LED37S/840 PSU W30L120 ELB3 NOC | 220 to 240 V |
| 910925864793 | RC134B LED27S/840 PSD W30L120 ELB3 NOC | 220 to 240 V |
| 910925864794 | RC134B LED37S/840 PSD W30L120 ELB3 NOC | 220 to 240 V |
| 910925864795 | RC134B LED27S/840 PSD W30L120 ELB3 OC | 220 to 240 V |
| 910925864796 | RC134B LED37S/840 PSD W30L120 ELB3 OC | 220 to 240 V |
| 910925864797 | RC134B LED27S/830 PSU W30L120 ELB3 NOC | 220 to 240 V |
| 910925864798 | RC134B LED37S/830 PSU W30L120 ELB3 NOC | 220 to 240 V |
| 910925864799 | RC134B LED27S/830 PSD W30L120 ELB3 NOC | 220 to 240 V |
| 910925864801 | RC134B LED37S/830 PSD W30L120 ELB3 NOC | 220 to 240 V |
| 910925864802 | RC134B LED37S/830 PSD W30L120 ELB3 OC | 220 to 240 V |
| 910925865174 | RC134B LED37S/840 W30L120 IA1 NOC | 220-240 V |
| 910925865175 | RC134B LED37S/840 W30L120 IA1 OC | 220-240 V |
| 910925865177 | RC134B LED37S/830 W30L120 IA1 OC | 220-240 V |
| 910925865178 | RC134B LED37S/830 W30L120 IA1 NOC | 220-240 V |
| 910925865181 | RC134B LED37S/840 W30L120 ELB3 IA1 OC | 220-240 V |
| 910925865182 | RC134B LED37S/840 W30L120 ELB3 IA1 NOC | 220-240 V |

General Information

| Order Code | Full Product Name | Beam angle | |
|--------------|---------------------------------------|-----------------|---------------------|
| | | of light source | Product Family Code |
| 910925864752 | RC134B LED37S/830 PSU W60L60 NOC | - | RC134B |
| 910925864753 | RC134B LED27S/830 PSU W60L60 NOC | - | RC134B |
| 910925864756 | RC134B LED37S/840 PSD W60L60 NOC | - | RC134B |
| 910925864758 | RC134B LED37S/830 PSD W60L60 NOC | - | RC134B |
| 910925864759 | RC134B LED27S/830 PSD W60L60 NOC | - | RC134B |
| 910925864762 | RC134B LED37S/840 PSD W60L60 OC | - | RC134B |
| 910925864768 | RC134B LED27S/840 PSD W60L60 OC | - | RC134B |
| 910925864771 | RC134B LED37S/830 PSD W60L60 OC | - | RC134B |
| 910925864772 | RC134B LED27S/830 PSD W60L60 OC | - | RC134B |
| 910925864775 | RC134B LED37S/840 PSU W60L60 NOC | - | RC134B |
| 910925864777 | RC134B LED37S/840 PSU W60L60 ELB3 NOC | - | RC134B |
| 910925864778 | RC134B LED37S/840 PSD W60L60 ELB3 NOC | - | RC134B |
| 910925864779 | RC134B LED37S/840 PSD W60L60 ELB3 OC | - | RC134B |
| 910925864780 | RC134B LED27S/840 PSD W60L60 ELB3 OC | - | RC134B |
| 910925864781 | RC134B LED27S/840 PSU W60L60 NOC | - | RC134B |
| 910925864783 | RC134B LED27S/840 PSD W60L60 NOC | - | RC134B |

| Order Code | Full Product Name | Beam angle | |
|--------------|---------------------------------------|-----------------|---------------------|
| | | of light source | Product Family Code |
| 910925864785 | RC134B LED27S/840 PSU W60L60 ELB3 NOC | - | RC134B |
| 910925864786 | RC134B LED27S/840 PSD W60L60 ELB3 NOC | - | RC134B |
| 910925864787 | RC134B LED37S/840 PSU W60L60 OC | - | RC134B |
| 910925864789 | RC134B LED37S/830 PSU W60L60 OC | - | RC134B |
| 910925864803 | RC135B LED37S/840 PSU W62L62 NOC | 120 ° | RC135B |
| 910925864804 | RC135B LED37S/840 PSD W62L62 OC | 120 ° | RC135B |
| 910925864805 | RC135B LED27S/840 PSD W62L62 OC | 120 ° | RC135B |
| 910925864806 | RC135B LED37S/840 PSU W62L62 OC | 120 ° | RC135B |
| 910925864807 | RC135B LED27S/840 PSU W62L62 NOC | 120 ° | RC135B |
| 910925864808 | RC135B LED27S/840 PSD W62L62 NOC | 120 ° | RC135B |
| 910925864809 | RC135B LED37S/840 PSD W62L62 NOC | 120 ° | RC135B |
| 910925865169 | RC134B LED37S/840 W60L60 IA1 OC | - | RC134B |
| 910925865170 | RC134B LED37S/840 W60L60 IA1 NOC | - | RC134B |
| 910925865171 | RC134B LED37S/830 W60L60 IA1 NOC | - | RC134B |
| 910925865172 | RC134B LED37S/830 W60L60 IA1 OC | - | RC134B |
| 910925865173 | RC135B LED37S/840 W62L62 IA1 OC | - | RC135B |
| 910925865176 | RC135B LED37S/840 W62L62 IA1 NOC | - | RC135B |
| 910925865179 | RC134B LED37S/840 W60L60 ELB3 IA1 NOC | - | RC134B |

CoreLine Recessed

| Order Code | Full Product Name | Beam angle | |
|--------------|--|-----------------|---------------------|
| | | of light source | Product Family Code |
| 910925865180 | RC134B LED37S/840 W60L60 ELB3 IA1 OC | - | RC134B |
| 910925864754 | RC134B LED37S/830 PSU W30L120 NOC | - | RC134B |
| 910925864755 | RC134B LED27S/830 PSU W30L120 NOC | - | RC134B |
| 910925864757 | RC134B LED37S/840 PSD W30L120 NOC | - | RC134B |
| 910925864760 | RC134B LED37S/830 PSD W30L120 NOC | - | RC134B |
| 910925864761 | RC134B LED27S/830 PSD W30L120 NOC | - | RC134B |
| 910925864769 | RC134B LED37S/840 PSD W30L120 OC | - | RC134B |
| 910925864770 | RC134B LED27S/840 PSD W30L120 OC | - | RC134B |
| 910925864773 | RC134B LED37S/830 PSD W30L120 OC | - | RC134B |
| 910925864774 | RC134B LED27S/830 PSD W30L120 OC | - | RC134B |
| 910925864776 | RC134B LED37S/840 PSU W30L120 NOC | - | RC134B |
| 910925864782 | RC134B LED27S/840 PSU W30L120 NOC | - | RC134B |
| 910925864784 | RC134B LED27S/840 PSD W30L120 NOC | - | RC134B |
| 910925864788 | RC134B LED37S/840 PSU W30L120 OC | - | RC134B |
| 910925864790 | RC134B LED37S/830 PSU W30L120 OC | - | RC134B |
| 910925864791 | RC134B LED27S/840 PSU W30L120 ELB3 NOC | - | RC134B |
| 910925864792 | RC134B LED37S/840 PSU W30L120 ELB3 NOC | - | RC134B |
| 910925864793 | RC134B LED27S/840 PSD W30L120 ELB3 NOC | - | RC134B |
| 910925864794 | RC134B LED37S/840 PSD W30L120 ELB3 NOC | - | RC134B |

| Order Code | Full Product Name | Beam angle | |
|--------------|--|-----------------|---------------------|
| | | of light source | Product Family Code |
| 910925864795 | RC134B LED27S/840 PSD W30L120 ELB3 OC | - | RC134B |
| 910925864796 | RC134B LED37S/840 PSD W30L120 ELB3 OC | - | RC134B |
| 910925864797 | RC134B LED27S/830 PSU W30L120 ELB3 NOC | - | RC134B |
| 910925864798 | RC134B LED37S/830 PSU W30L120 ELB3 NOC | - | RC134B |
| 910925864799 | RC134B LED27S/830 PSD W30L120 ELB3 NOC | - | RC134B |
| 910925864801 | RC134B LED37S/830 PSD W30L120 ELB3 NOC | - | RC134B |
| 910925864802 | RC134B LED37S/830 PSD W30L120 ELB3 OC | - | RC134B |
| 910925865174 | RC134B LED37S/840 W30L120 IA1 NOC | - | RC134B |
| 910925865175 | RC134B LED37S/840 W30L120 IA1 OC | - | RC134B |
| 910925865177 | RC134B LED37S/830 W30L120 IA1 OC | - | RC134B |
| 910925865178 | RC134B LED37S/830 W30L120 IA1 NOC | - | RC134B |
| 910925865181 | RC134B LED37S/840 W30L120 ELB3 IA1 OC | - | RC134B |
| 910925865182 | RC134B LED37S/840 W30L120 ELB3 IA1 NOC | - | RC134B |

Initial Performance (IEC Compliant) (1/2)

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. | Initial LED | Initial |
|--------------|----------------------------------|----------------------|-------------------|--------------------|---------------|
| | | | Color Temperature | luminaire efficacy | luminous flux |
| 910925864752 | RC134B LED37S/830 PSU W60L60 NOC | (0.43, 0.40) | 3000 K | 109 lm/W | 3700 lm |
| 910925864753 | RC134B LED27S/830 PSU W60L60 NOC | (0.43, 0.40) | 3000 K | 95 lm/W | 2700 lm |
| 910925864756 | RC134B LED37S/840 PSD W60L60 NOC | (0.38, 0.38) | 4000 K | 104 lm/W | 3700 lm |
| 910925864758 | RC134B LED37S/830 PSD W60L60 NOC | (0.43, 0.40) | 3000 K | 104 lm/W | 3700 lm |
| 910925864759 | RC134B LED27S/830 PSD W60L60 NOC | (0.43, 0.40) | 3000 K | 89 lm/W | 2700 lm |

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. | Initial LED | Initial |
|--------------|----------------------------------|----------------------|-------------------|--------------------|---------------|
| | | | Color Temperature | luminaire efficacy | luminous flux |
| 910925864762 | RC134B LED37S/840 PSD W60L60 OC | (0.38, 0.38) | 4000 K | 117 lm/W | 3700 lm |
| 910925864768 | RC134B LED27S/840 PSD W60L60 OC | (0.38, 0.38) | 4000 K | 123 lm/W | 2700 lm |
| 910925864771 | RC134B LED37S/830 PSD W60L60 OC | (0.43, 0.40) | 3000 K | 117 lm/W | 3700 lm |
| 910925864772 | RC134B LED27S/830 PSD W60L60 OC | (0.43, 0.40) | 3000 K | 117 lm/W | 2700 lm |
| 910925864775 | RC134B LED37S/840 PSU W60L60 NOC | (0.38, 0.38) | 4000 K | 109 lm/W | 3700 lm |

CoreLine Recessed

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Initial LED luminaire efficacy | Initial luminous flux |
|--------------|--|-------------------------|-------------------------------|--------------------------------|-----------------------|
| 910925864777 | RC134B LED37S/840 PSU W60L60 ELB3 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 97 lm/W | 3700 lm |
| 910925864778 | RC134B LED37S/840 PSD W60L60 ELB3 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 95 lm/W | 3700 lm |
| 910925864779 | RC134B LED37S/840 PSD W60L60 ELB3 OC | (0.38, 0.38) SDCM <3 | 4000 K | 106 lm/W | 3700 lm |
| 910925864780 | RC134B LED27S/840 PSD W60L60 ELB3 OC | (0.38, 0.38) SDCM <3 | 4000 K | 106 lm/W | 2700 lm |
| 910925864781 | RC134B LED27S/840 PSU W60L60 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 100 lm/W | 2700 lm |
| 910925864783 | RC134B LED27S/840 PSD W60L60 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 102 lm/W | 2700 lm |
| 910925864785 | RC134B LED27S/840 PSU W60L60 ELB3 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 89 lm/W | 2700 lm |
| 910925864786 | RC134B LED27S/840 PSD W60L60 ELB3 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 89 lm/W | 2700 lm |
| 910925864787 | RC134B LED37S/840 PSU W60L60 OC | (0.38, 0.38) SDCM <3 | 4000 K | 121 lm/W | 3700 lm |
| 910925864789 | RC134B LED37S/830 PSU W60L60 OC | (0.43, 0.40) SDCM <3 | 3000 K | 107 lm/W | 3700 lm |
| 910925864803 | RC135B LED37S/840 PSU W62L62 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 109 lm/W | 3700 lm |
| 910925864804 | RC135B LED37S/840 PSD W62L62 OC | (0.38, 0.38) SDCM <3 | 4000 K | 117 lm/W | 3700 lm |
| 910925864805 | RC135B LED27S/840 | (0.38, 0.38) SDCM <3 | 4000 K | 123 lm/W | 2700 lm |

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Initial LED luminaire efficacy | Initial luminous flux |
|--------------|--|-------------------------|-------------------------------|--------------------------------|-----------------------|
| | PSD W62L62 OC | | | | |
| 910925864806 | RC135B LED37S/840 PSU W62L62 OC | (0.38, 0.38) SDCM <3 | 4000 K | 121 lm/W | 3700 lm |
| 910925864807 | RC135B LED27S/840 PSU W62L62 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 100 lm/W | 2700 lm |
| 910925864808 | RC135B LED27S/840 PSD W62L62 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 102 lm/W | 2700 lm |
| 910925864809 | RC135B LED37S/840 PSD W62L62 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 104 lm/W | 3700 lm |
| 910925865169 | RC134B LED37S/840 W60L60 IA1 OC | (0.38, 0.38) SDCM <3 | 4000 K | 104.5 lm/W | 3700 lm |
| 910925865170 | RC134B LED37S/840 W60L60 IA1 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 104.5 lm/W | 3700 lm |
| 910925865171 | RC134B LED37S/830 W60L60 IA1 NOC | (0.43, 0.40) SDCM <3 | 3000 K | 104.5 lm/W | 3700 lm |
| 910925865172 | RC134B LED37S/830 W60L60 IA1 OC | (0.43, 0.40) SDCM <3 | 3000 K | 104.5 lm/W | 3700 lm |
| 910925865173 | RC135B LED37S/840 W62L62 IA1 OC | (0.38, 0.38) SDCM <3 | 4000 K | 104.5 lm/W | 3700 lm |
| 910925865176 | RC135B LED37S/840 W62L62 IA1 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 104.5 lm/W | 3700 lm |
| 910925865179 | RC134B LED37S/840 W60L60 ELB3 IA1 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 94 lm/W | 3700 lm |
| 910925865180 | RC134B LED37S/840 W60L60 ELB3 IA1 OC | (0.38, 0.38) SDCM <3 | 4000 K | 94 lm/W | 3700 lm |

CoreLine Recessed

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Initial LED luminaire efficacy | Initial luminous flux |
|--------------|---|-------------------------|-------------------------------|--------------------------------|-----------------------|
| 910925864754 | RC134B LED37S/830 PSU W30L120 NOC | (0.43, 0.40) SDCM <3 | 3000 K | 109 lm/W | 3700 lm |
| 910925864755 | RC134B LED27S/830 PSU W30L120 NOC | (0.43, 0.40) SDCM <3 | 3000 K | 95 lm/W | 2700 lm |
| 910925864757 | RC134B LED37S/840 PSD W30L120 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 104 lm/W | 3700 lm |
| 910925864760 | RC134B LED37S/830 PSD W30L120 NOC | (0.43, 0.40) SDCM <3 | 3000 K | 104 lm/W | 3700 lm |
| 910925864761 | RC134B LED27S/830 PSD W30L120 NOC | (0.43, 0.40) SDCM <3 | 3000 K | 89 lm/W | 2700 lm |
| 910925864769 | RC134B LED37S/840 PSD W30L120 OC | (0.38, 0.38) SDCM <3 | 4000 K | 117 lm/W | 3700 lm |
| 910925864770 | RC134B LED27S/840 PSD W30L120 OC | (0.38, 0.38) SDCM <3 | 4000 K | 123 lm/W | 2700 lm |
| 910925864773 | RC134B LED37S/830 PSD W30L120 OC | (0.43, 0.40) SDCM <3 | 3000 K | 117 lm/W | 3700 lm |
| 910925864774 | RC134B LED27S/830 PSD W30L120 OC | (0.43, 0.40) SDCM <3 | 3000 K | 117 lm/W | 2700 lm |
| 910925864776 | RC134B LED37S/840 PSU W30L120 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 109 lm/W | 3700 lm |
| 910925864782 | RC134B LED27S/840 PSU | (0.38, 0.38) SDCM <3 | 4000 K | 100 lm/W | 2700 lm |

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Initial LED luminaire efficacy | Initial luminous flux |
|--------------|--|-------------------------|-------------------------------|--------------------------------|-----------------------|
| | W30L120 NOC | | | | |
| 910925864784 | RC134B LED27S/840 PSD W30L120 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 102 lm/W | 2700 lm |
| 910925864788 | RC134B LED37S/840 PSU W30L120 OC | (0.38, 0.38) SDCM <3 | 4000 K | 121 lm/W | 3700 lm |
| 910925864790 | RC134B LED37S/830 PSU W30L120 OC | (0.43, 0.40) SDCM <3 | 3000 K | 107 lm/W | 3700 lm |
| 910925864791 | RC134B LED27S/840 PSU W30L120 ELB3 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 89 lm/W | 2700 lm |
| 910925864792 | RC134B LED37S/840 PSU W30L120 ELB3 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 97 lm/W | 3700 lm |
| 910925864793 | RC134B LED27S/840 PSD W30L120 ELB3 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 89 lm/W | 2700 lm |
| 910925864794 | RC134B LED37S/840 PSD W30L120 ELB3 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 104 lm/W | 3700 lm |
| 910925864795 | RC134B LED27S/840 PSD W30L120 ELB3 OC | (0.38, 0.38) SDCM <3 | 4000 K | 106 lm/W | 2700 lm |
| 910925864796 | RC134B LED37S/840 PSD W30L120 ELB3 OC | (0.38, 0.38) SDCM <3 | 4000 K | 106 lm/W | 3700 lm |
| 910925864797 | RC134B LED27S/830 PSU W30L120 ELB3 NOC | (0.43, 0.40) SDCM <3 | 3000 K | 84 lm/W | 2700 lm |

CoreLine Recessed

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Initial LED luminaire efficacy | Initial luminous flux |
|--------------|--|-------------------------|-------------------------------|--------------------------------|-----------------------|
| 910925864798 | RC134B LED37S/830 PSU W30L120 ELB3 NOC | (0.43, 0.40) SDCM <3 | 3000 K | 97 lm/W | 3700 lm |
| 910925864799 | RC134B LED27S/830 PSD W30L120 ELB3 NOC | (0.43, 0.40) SDCM <3 | 3000 K | 79 lm/W | 2700 lm |
| 910925864801 | RC134B LED37S/830 PSD W30L120 ELB3 NOC | (0.43, 0.40) SDCM <3 | 3000 K | 95 lm/W | 3700 lm |
| 910925864802 | RC134B LED37S/830 PSD W30L120 ELB3 OC | (0.43, 0.40) SDCM <3 | 3000 K | 106 lm/W | 3700 lm |
| 910925865174 | RC134B LED37S/840 | (0.38, 0.38) SDCM <3 | 4000 K | 104.5 lm/W | 3700 lm |

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Initial LED luminaire efficacy | Initial luminous flux |
|--------------|---|-------------------------|-------------------------------|--------------------------------|-----------------------|
| | W30L120 IA1 NOC | | | | |
| 910925865175 | RC134B LED37S/840 W30L120 IA1 OC | (0.38, 0.38) SDCM <3 | 4000 K | 104.5 lm/W | 3700 lm |
| 910925865177 | RC134B LED37S/830 W30L120 IA1 OC | (0.43, 0.40) SDCM <3 | 3000 K | 104.5 lm/W | 3700 lm |
| 910925865178 | RC134B LED37S/830 W30L120 IA1 NOC | (0.43, 0.40) SDCM <3 | 3000 K | 104.5 lm/W | 3700 lm |
| 910925865181 | RC134B LED37S/840 W30L120 ELB3 IA1 OC | (0.38, 0.38) SDCM <3 | 4000 K | 94 lm/W | 3700 lm |
| 910925865182 | RC134B LED37S/840 W30L120 ELB3 IA1 NOC | (0.38, 0.38) SDCM <3 | 4000 K | 94 lm/W | 3700 lm |

Initial Performance (IEC Compliant) (2/2)

| Order Code | Full Product Name | Initial input power |
|--------------|---------------------------------------|---------------------|
| 910925864752 | RC134B LED37S/830 PSU W60L60 NOC | 34 W |
| 910925864753 | RC134B LED27S/830 PSU W60L60 NOC | 28.5 W |
| 910925864756 | RC134B LED37S/840 PSD W60L60 NOC | 35.5 W |
| 910925864758 | RC134B LED37S/830 PSD W60L60 NOC | 35.5 W |
| 910925864759 | RC134B LED27S/830 PSD W60L60 NOC | 30.5 W |
| 910925864762 | RC134B LED37S/840 PSD W60L60 OC | 31.5 W |
| 910925864768 | RC134B LED27S/840 PSD W60L60 OC | 22 W |
| 910925864771 | RC134B LED37S/830 PSD W60L60 OC | 31.5 W |
| 910925864772 | RC134B LED27S/830 PSD W60L60 OC | 23 W |
| 910925864775 | RC134B LED37S/840 PSU W60L60 NOC | 34 W |
| 910925864777 | RC134B LED37S/840 PSU W60L60 ELB3 NOC | 38 W |
| 910925864778 | RC134B LED37S/840 PSD W60L60 ELB3 NOC | 39 W |
| 910925864779 | RC134B LED37S/840 PSD W60L60 ELB3 OC | 35 W |
| 910925864780 | RC134B LED27S/840 PSD W60L60 ELB3 OC | 25.5 W |
| 910925864781 | RC134B LED27S/840 PSU W60L60 NOC | 27 W |
| 910925864783 | RC134B LED27S/840 PSD W60L60 NOC | 26.5 W |
| 910925864785 | RC134B LED27S/840 PSU W60L60 ELB3 NOC | 30.5 W |
| 910925864786 | RC134B LED27S/840 PSD W60L60 ELB3 NOC | 30.5 W |
| 910925864787 | RC134B LED37S/840 PSU W60L60 OC | 30.5 W |
| 910925864789 | RC134B LED37S/830 PSU W60L60 OC | 34.5 W |
| 910925864803 | RC135B LED37S/840 PSU W62L62 NOC | 34 W |
| 910925864804 | RC135B LED37S/840 PSD W62L62 OC | 31.5 W |
| 910925864805 | RC135B LED27S/840 PSD W62L62 OC | 22 W |
| 910925864806 | RC135B LED37S/840 PSU W62L62 OC | 30.5 W |

| Order Code | Full Product Name | Initial input power |
|--------------|---------------------------------------|---------------------|
| 910925864807 | RC135B LED27S/840 PSU W62L62 NOC | 27 W |
| 910925864808 | RC135B LED27S/840 PSD W62L62 NOC | 26.5 W |
| 910925864809 | RC135B LED37S/840 PSD W62L62 NOC | 35.5 W |
| 910925865169 | RC134B LED37S/840 W60L60 IA1 OC | 35.4 W |
| 910925865170 | RC134B LED37S/840 W60L60 IA1 NOC | 35.4 W |
| 910925865171 | RC134B LED37S/830 W60L60 IA1 NOC | 35.4 W |
| 910925865172 | RC134B LED37S/830 W60L60 IA1 OC | 35.4 W |
| 910925865173 | RC135B LED37S/840 W62L62 IA1 OC | 35.4 W |
| 910925865176 | RC135B LED37S/840 W62L62 IA1 NOC | 35.4 W |
| 910925865179 | RC134B LED37S/840 W60L60 ELB3 IA1 NOC | 39.3 W |
| 910925865180 | RC134B LED37S/840 W60L60 ELB3 IA1 OC | 39.3 W |
| 910925864754 | RC134B LED37S/830 PSU W30L120 NOC | 34 W |
| 910925864755 | RC134B LED27S/830 PSU W30L120 NOC | 28.5 W |
| 910925864757 | RC134B LED37S/840 PSD W30L120 NOC | 35.5 W |
| 910925864760 | RC134B LED37S/830 PSD W30L120 NOC | 35.5 W |
| 910925864761 | RC134B LED27S/830 PSD W30L120 NOC | 30.5 W |
| 910925864769 | RC134B LED37S/840 PSD W30L120 OC | 31.5 W |
| 910925864770 | RC134B LED27S/840 PSD W30L120 OC | 22 W |
| 910925864773 | RC134B LED37S/830 PSD W30L120 OC | 31.5 W |
| 910925864774 | RC134B LED27S/830 PSD W30L120 OC | 23 W |
| 910925864776 | RC134B LED37S/840 PSU W30L120 NOC | 34 W |
| 910925864782 | RC134B LED27S/840 PSU W30L120 NOC | 27 W |
| 910925864784 | RC134B LED27S/840 PSD W30L120 NOC | 26.5 W |
| 910925864788 | RC134B LED37S/840 PSU W30L120 OC | 30.5 W |

CoreLine Recessed

| Order Code | Full Product Name | Initial input power |
|--------------|--|---------------------|
| 910925864790 | RC134B LED37S/830 PSU W30L120 OC | 34.5 W |
| 910925864791 | RC134B LED27S/840 PSU W30L120 ELB3 NOC | 30.5 W |
| 910925864792 | RC134B LED37S/840 PSU W30L120 ELB3 NOC | 38 W |
| 910925864793 | RC134B LED27S/840 PSD W30L120 ELB3 NOC | 30.5 W |
| 910925864794 | RC134B LED37S/840 PSD W30L120 ELB3 NOC | 35.5 W |
| 910925864795 | RC134B LED27S/840 PSD W30L120 ELB3 OC | 25.5 W |
| 910925864796 | RC134B LED37S/840 PSD W30L120 ELB3 OC | 35 W |
| 910925864797 | RC134B LED27S/830 PSU W30L120 ELB3 NOC | 32 W |
| 910925864798 | RC134B LED37S/830 PSU W30L120 ELB3 NOC | 38 W |

| Order Code | Full Product Name | Initial input power |
|--------------|--|---------------------|
| 910925864799 | RC134B LED27S/830 PSD W30L120 ELB3 NOC | 34 W |
| 910925864801 | RC134B LED37S/830 PSD W30L120 ELB3 NOC | 39 W |
| 910925864802 | RC134B LED37S/830 PSD W30L120 ELB3 OC | 35 W |
| 910925865174 | RC134B LED37S/840 W30L120 IA1 NOC | 35.4 W |
| 910925865175 | RC134B LED37S/840 W30L120 IA1 OC | 35.4 W |
| 910925865177 | RC134B LED37S/830 W30L120 IA1 OC | 35.4 W |
| 910925865178 | RC134B LED37S/830 W30L120 IA1 NOC | 35.4 W |
| 910925865181 | RC134B LED37S/840 W30L120 ELB3 IA1 OC | 39.3 W |
| 910925865182 | RC134B LED37S/840 W30L120 ELB3 IA1 NOC | 39.3 W |

