



CoreLine waterproof - For every project where light really matters

CoreLine Waterproof

CoreLine waterproof delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. CoreLine waterproof products can directly replace traditional waterproof luminaires with fluorescent lamps ranging from 18W up to 58W. With its slim and stylish design, it continues to keep its well-known and appreciated architecture. Installation is quick and easy, all thanks to its efficient design. CoreLine waterproof provides better wide-beam light distribution for straightforward and effective lighting. Interact Ready luminaires with integrated wireless communications are also available in this range, ready to be used with Interact gateways, sensors and software.

Benefits

- Energy savings and longer lifetime to reduce operating costs
- Robust design enabling smarter, simpler and faster installation
- Uniform, wide-beam light distribution, which supports easy and attractive lighting design

CoreLine Waterproof

Features

- Energy efficient and long lifetime: up to 140lm/W and 50khrs L75 lifetime
- Many options available: L600/1200/1500, up to 8000lm, 4000K
- Smart product architecture with electrical and mechanical design supporting ease and flexibility of installation (longer sliders, faster lock opening, toolless electrical connections)
- Optional controls and versions available: DALI, Integrated wireless connectivity (Interact Ready), Sensors (MDU), Emergency Lighting (EL), waterproof external connector for easier installation (WEC), through wiring (TW)

Application


- Parking Garages
- Manufacturing
- Warehouses
- General lighting

Specifications

Ambient Temperature	-20 to +35 °C
	-20 to +40 °C
	0 to +25 °C
Dimming	No, wireless Dim, yes
Driver	Power supply unit (Power supply unit)
	Power supply unit with DALI interface (Power supply unit with DALI interface)
Initial correlated color temperature	3000 K, 4000 K, 6500 K

Initial input power	15 W, 16 W, 20.5 W, 21 W, 21.5 W, 22 W, 24.3 W, 24.5 W, 25 W,
	25.5 W, 26 W, 27 W, 28.5 W, 28.6 W, 29 W, 29.5 W, 30 W, 30.5
	W, 31 W, 33 W, 34 W, 35 W, 42.9 W, 43 W, 44 W, 45 W, 45.5 W,
	49 W, 50 W, 57.1 W, 60 W, 61 W, 63 W
Initial luminous flux	1800, 1900, 2500, 2700, 3100, 3400, 3700, 4000, 5500, 5700,
	6000, 7500, 8000 lm
Material	Bracket:
Material	Housing: polycarbonate

Versions



Product details



CoreLine Waterproof

Product details




CoreLine Waterproof WT120C G2
PCU-10DPP




CoreLine Waterproof WT120C G2
PCU-9DPP



CoreLine Waterproof WT120C G2
PCU-12DPP



CoreLine Waterproof WT120C G2
PCU-2DPP



CoreLine Waterproof WT120C G2
PCU-13DPP



CoreLine Waterproof WT120C G2
PCU-8DPP



CoreLine Waterproof WT120C G2
PCU-11DPP

Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP65

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Optic type	Beam angle 110°

Initial Performance (IEC Compliant)

Init. Color Rendering Index	>80
Luminous flux tolerance	+/-10%

Mechanical and Housing

Color	Gray
-------	------

Application Conditions

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910505100036	WT120C G2 LED19S/840 PSU MDU L600	-20 to +35 °C	Not applicable	Yes
910505100038	WT120C G2 LED19S/840 PSD L600	-20 to +35 °C	1%	Not applicable
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-20 to +35 °C	Not applicable	Not applicable
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	-20 to +35 °C	Not applicable	Yes
910505100041	WT120C G2 LED27S/840 PSU MDU TW3 L1200	-20 to +35 °C	Not applicable	Yes
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	0 to +25 °C	Not applicable	Not applicable
910505100044	WT120C G2 LED27S/840 PSD L1200	-20 to +35 °C	1%	Not applicable
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	0 to +25 °C	1%	Not applicable
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-20 to +35 °C	Not applicable	Not applicable
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	-20 to +35 °C	Not applicable	Yes
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-20 to +35 °C	Not applicable	Yes
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	-20 to +35 °C	Not applicable	Not applicable
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-20 to +35 °C	Not applicable	Not applicable
910505100052	WT120C G2 LED40S/840 IA1 L1200	-20 to +35 °C	10%	Not applicable
910505100053	WT120C G2 LED40S/840 PSD L1200	-20 to +35 °C	1%	Not applicable
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	0 to +25 °C	Not applicable	Not applicable
910505100055	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	0 to +25 °C	Not applicable	Yes
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	0 to +25 °C	10%	Not applicable
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	0 to +25 °C	1%	Not applicable
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable	Not applicable
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	-20 to +35 °C	Not applicable	Yes
910505100060	WT120C G2 LED34S/840 PSU MDU TW3 L1500	-20 to +35 °C	Not applicable	Yes
910505100061	WT120C G2 LED34S/840 PSD L1500	-20 to +35 °C	1%	Not applicable
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	0 to +25 °C	Not applicable	Not applicable

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910505100063	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	0 to +25 °C	Not applicable	Yes
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	0 to +25 °C	1%	Not applicable
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable	Not applicable
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	-20 to +35 °C	Not applicable	Yes
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-20 to +35 °C	Not applicable	Yes
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-20 to +35 °C	Not applicable	Not applicable
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-20 to +35 °C	Not applicable	Not applicable
910505100071	WT120C G2 LED60S/840 IA1 L1500	-20 to +35 °C	10%	Not applicable
910505100072	WT120C G2 LED60S/840 PSD L1500	-20 to +35 °C	1%	Not applicable
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	0 to +25 °C	Not applicable	Not applicable
910505100074	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	0 to +25 °C	Not applicable	Yes
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	0 to +25 °C	10%	Not applicable
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	0 to +25 °C	1%	Not applicable
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable	Not applicable
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	-20 to +35 °C	Not applicable	Yes
910505100079	WT120C G2 LED80S/840 PSD L1500	-20 to +35 °C	1%	Not applicable
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	0 to +25 °C	Not applicable	Not applicable
911401823480	WT120C G2 LED19S/840 PSU L600	-20 to +40 °C	Not applicable	Not applicable
911401823580	WT120C G2 LED27S/840 PSU L1200	-20 to +40 °C	Not applicable	Not applicable
911401823680	WT120C G2 LED34S/840 PSU L1500	-20 to +40 °C	Not applicable	Not applicable
911401823780	WT120C G2 LED40S/840 PSU L1200	-20 to +40 °C	Not applicable	Not applicable
911401823880	WT120C G2 LED60S/840 PSU L1500	-20 to +40 °C	Not applicable	Not applicable
911401823980	WT120C G2 LED80S/840 PSU L1500	-20 to +40 °C	Not applicable	Not applicable
911401824381	WT120C G2 LED40S/865 PSU L1200	-20 to +40 °C	Not applicable	Not applicable
911401824481	WT120C G2 LED34S/865 PSU L1500	-20 to +40 °C	Not applicable	Not applicable

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
911401824581	WT120C G2 LED60S/865 PSU L1500	-20 to +40 °C	Not applicable	Not applicable
911401824681	WT120C G2 LED37S/830 PSU L1200	-20 to +40 °C	Not applicable	Not applicable
911401824781	WT120C G2 LED55S/830 PSU L1500	-20 to +40 °C	Not applicable	Not applicable
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-20 to +40 °C	Not applicable	Not applicable
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-20 to +40 °C	Not applicable	Not applicable
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-20 to +40 °C	Not applicable	Not applicable
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-20 to +40 °C	Not applicable	Not applicable
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-20 to +40 °C	Not applicable	Not applicable
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-20 to +40 °C	Not applicable	Not applicable

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910505100036	WT120C G2 LED19S/840 PSU MDU L600	No	910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	No
910505100038	WT120C G2 LED19S/840 PSD L600	Yes	910505100069	WT120C G2 LED60S/840 PSU WEC L1500	No
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	No	910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	No
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	No	910505100071	WT120C G2 LED60S/840 IA1 L1500	Wireless Dim
910505100041	WT120C G2 LED27S/840 PSU MDU TW3 L1200	No	910505100072	WT120C G2 LED60S/840 PSD L1500	Yes
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	No	910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	No
910505100044	WT120C G2 LED27S/840 PSD L1200	Yes	910505100074	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	No
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	Yes	910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	Wireless Dim
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	No	910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	Yes
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	No	910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	No
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	No	910505100078	WT120C G2 LED80S/840 PSU MDU L1500	No
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	No	910505100079	WT120C G2 LED80S/840 PSD L1500	Yes
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	No	910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	No
910505100052	WT120C G2 LED40S/840 IA1 L1200	Wireless Dim	911401823480	WT120C G2 LED19S/840 PSU L600	No
910505100053	WT120C G2 LED40S/840 PSD L1200	Yes	911401823580	WT120C G2 LED27S/840 PSU L1200	No
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	No	911401823680	WT120C G2 LED34S/840 PSU L1500	No
910505100055	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	No	911401823780	WT120C G2 LED40S/840 PSU L1200	No
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	Wireless Dim	911401823880	WT120C G2 LED60S/840 PSU L1500	No
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	Yes	911401823980	WT120C G2 LED80S/840 PSU L1500	No
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	No	911401824381	WT120C G2 LED40S/865 PSU L1200	No
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	No	911401824481	WT120C G2 LED34S/865 PSU L1500	No
910505100060	WT120C G2 LED34S/840 PSU MDU TW3 L1500	No	911401824581	WT120C G2 LED60S/865 PSU L1500	No
910505100061	WT120C G2 LED34S/840 PSD L1500	Yes	911401824681	WT120C G2 LED37S/830 PSU L1200	No
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	No	911401824781	WT120C G2 LED55S/830 PSU L1500	No
910505100063	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	No	911401836980	WT120C G2 LED18S/840 PSU PCO L600	No
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	Yes	911401837080	WT120C G2 LED25S/840 PSU PCO L1200	No
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	No	911401837180	WT120C G2 LED31S/840 PSU PCO L1500	No
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	No	911401837280	WT120C G2 LED37S/840 PSU PCO L1200	No

CoreLine Waterproof

Order Code	Full Product Name	Dimmable
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	No

Order Code	Full Product Name	Dimmable
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	No

General Information (1/2)

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Emergency lighting	Lamp family code
910505100036	WT120C G2 LED19S/840 PSU MDU L600	-	Micro-lens optic	-	LED27S
910505100038	WT120C G2 LED19S/840 PSD L600	-	Micro-lens optic	-	LED19S
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-	Micro-lens optic	-	LED27S
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	-	Micro-lens optic	-	LED27S
910505100041	WT120C G2 LED27S/840 PSU MDU TW3 L1200	-	Micro-lens optic	-	LED27S
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	-	Micro-lens optic	Emergency lighting 3 hours duration	LED27S
910505100044	WT120C G2 LED27S/840 PSD L1200	-	Micro-lens optic	-	LED27S
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	-	Micro-lens optic	Emergency lighting 3 hours duration	LED27S
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-	Micro-lens optic	-	LED40S
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	-	Micro-lens optic	-	LED40S
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-	Micro-lens optic	-	LED40S
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	-	Micro-lens optic	-	LED40S
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	Micro-lens optic	-	LED40S
910505100052	WT120C G2 LED40S/840 IA1 L1200	-	Micro-lens optic	-	LED40S

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Emergency lighting	Lamp family code
910505100053	WT120C G2 LED40S/840 PSD L1200	-	Micro-lens optic	-	LED40S
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	-	Micro-lens optic	Emergency lighting 3 hours duration	LED40S
910505100055	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	-	Micro-lens optic	Emergency lighting 3 hours duration	LED40S
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	-	Micro-lens optic	Emergency lighting 3 hours duration	LED40S
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	-	Micro-lens optic	Emergency lighting 3 hours duration	LED40S
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-	Micro-lens optic	-	LED34S
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	-	Micro-lens optic	-	LED34S
910505100060	WT120C G2 LED34S/840 PSU MDU TW3 L1500	-	Micro-lens optic	-	LED34S
910505100061	WT120C G2 LED34S/840 PSD L1500	-	Micro-lens optic	-	LED34S
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	-	Micro-lens optic	Emergency lighting 3 hours duration	LED34S
910505100063	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	-	Micro-lens optic	Emergency lighting 3 hours duration	LED34S
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	-	Micro-lens optic	Emergency lighting 3 hours duration	LED34S
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-	Micro-lens optic	-	LED60S
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	-	Micro-lens optic	-	LED60S

CoreLine Waterproof

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Emergency lighting	Lamp family code
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-	Micro-lens optic	-	LED60S
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-	Micro-lens optic	-	LED60S
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	Micro-lens optic	-	LED60S
910505100071	WT120C G2 LED60S/840 IA1 L1500	-	Micro-lens optic	-	LED60S
910505100072	WT120C G2 LED60S/840 PSD L1500	-	Micro-lens optic	-	LED60S
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	-	Micro-lens optic	Emergency lighting 3 hours duration	LED60S
910505100074	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	-	Micro-lens optic	Emergency lighting 3 hours duration	LED60S
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	-	Micro-lens optic	Emergency lighting 3 hours duration	LED60S
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	-	Micro-lens optic	Emergency lighting 3 hours duration	LED60S
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-	Micro-lens optic	-	LED80S
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	-	Micro-lens optic	-	LED80S
910505100079	WT120C G2 LED80S/840 PSD L1500	-	Micro-lens optic	-	LED80S
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	-	Micro-lens optic	Emergency lighting 3 hours duration	LED80S
911401823480	WT120C G2 LED19S/840 PSU L600	-°	Micro-lens optic	-	-
911401823580	WT120C G2 LED27S/840 PSU L1200	-°	Micro-lens optic	-	-

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Emergency lighting	Lamp family code
911401823680	WT120C G2 LED34S/840 PSU L1500	-°	Micro-lens optic	-	-
911401823780	WT120C G2 LED40S/840 PSU L1200	-°	Micro-lens optic	-	-
911401823880	WT120C G2 LED60S/840 PSU L1500	-°	Micro-lens optic	-	-
911401823980	WT120C G2 LED80S/840 PSU L1500	-°	Micro-lens optic	-	-
911401824381	WT120C G2 LED40S/865 PSU L1200	-°	-	-	-
911401824481	WT120C G2 LED34S/865 PSU L1500	-°	-	-	-
911401824581	WT120C G2 LED60S/865 PSU L1500	-°	-	-	-
911401824681	WT120C G2 LED37S/830 PSU L1200	-°	-	-	-
911401824781	WT120C G2 LED55S/830 PSU L1500	-°	-	-	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-°	Micro-lens optic	-	-
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-°	Micro-lens optic	-	-
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-°	Micro-lens optic	-	-
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-°	Micro-lens optic	-	-
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-°	Micro-lens optic	-	-
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-°	Micro-lens optic	-	-

General Information (2/2)

CoreLine Waterproof

Order Code	Full Product Name	Embedded control	Product Family Code	Service tag
910505100036	WT120C G2 LED19S/840 PSU MDU L600	-	WT130C	Yes
910505100038	WT120C G2 LED19S/840 PSD L600	-	WT130C	Yes
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-	WT130C	Yes
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	-	WT130C	Yes
910505100041	WT120C G2 LED27S/840 PSU MDU TW3 L1200	-	WT130C	Yes
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	-	WT130C	Yes
910505100044	WT120C G2 LED27S/840 PSD L1200	-	WT130C	Yes
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	-	WT130C	Yes
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-	WT130C	Yes
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	-	WT130C	Yes
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-	WT130C	Yes
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	-	WT130C	Yes
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	WT130C	Yes
910505100052	WT120C G2 LED40S/840 IA1 L1200	-	WT130C	Yes
910505100053	WT120C G2 LED40S/840 PSD L1200	-	WT130C	Yes
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	-	WT130C	Yes
910505100055	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	Movement detection unit	WT130C	Yes
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	-	WT130C	Yes
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	-	WT130C	Yes
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-	WT130C	Yes
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	-	WT130C	Yes
910505100060	WT120C G2 LED34S/840 PSU MDU TW3 L1500	-	WT130C	Yes
910505100061	WT120C G2 LED34S/840 PSD L1500	-	WT130C	Yes
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	-	WT130C	Yes
910505100063	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	Movement detection unit	WT130C	Yes

Order Code	Full Product Name	Embedded control	Product Family Code	Service tag
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	-	WT130C	Yes
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-	WT130C	Yes
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	-	WT130C	Yes
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-	WT130C	Yes
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-	WT130C	Yes
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	WT130C	Yes
910505100071	WT120C G2 LED60S/840 IA1 L1500	-	WT130C	Yes
910505100072	WT120C G2 LED60S/840 PSD L1500	-	WT130C	Yes
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	-	WT130C	Yes
910505100074	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	Movement detection unit	WT130C	Yes
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	-	WT130C	Yes
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	-	WT130C	Yes
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-	WT130C	Yes
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	-	WT130C	Yes
910505100079	WT120C G2 LED80S/840 PSD L1500	-	WT130C	Yes
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	-	WT130C	Yes
911401823480	WT120C G2 LED19S/840 PSU L600	-	-	Yes
911401823580	WT120C G2 LED27S/840 PSU L1200	-	-	Yes
911401823680	WT120C G2 LED34S/840 PSU L1500	-	-	Yes
911401823780	WT120C G2 LED40S/840 PSU L1200	-	-	Yes
911401823880	WT120C G2 LED60S/840 PSU L1500	-	-	Yes
911401823980	WT120C G2 LED80S/840 PSU L1500	-	-	Yes
911401824381	WT120C G2 LED40S/865 PSU L1200	-	-	-
911401824481	WT120C G2 LED34S/865 PSU L1500	-	-	-
911401824581	WT120C G2 LED60S/865 PSU L1500	-	-	-

CoreLine Waterproof

Order Code	Full Product Name	Embedded control	Product Family Code	Service tag
911401824681	WT120C G2 LED37S/830 PSU L1200	-	-	-
911401824781	WT120C G2 LED55S/830 PSU L1500	-	-	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-	-	Yes
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-	-	Yes

Order Code	Full Product Name	Embedded control	Product Family Code	Service tag
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-	-	Yes
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-	-	Yes
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-	-	Yes
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-	-	Yes

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticy	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910505100036	WT120C G2 LED19S/8 40 PSU MDU L600	(0.38,0.38)SDCM<=3	4000 K	119 lm/W	1900 lm
910505100038	WT120C G2 LED19S/8 40 PSD L600	(0.38,0.38)SDCM<=3	4000 K	119 lm/W	1900 lm
910505100039	WT120C G2 LED27S/8 40 PSU TW3 L1200	(0.38,0.38)SDCM<=3	4000 K	129 lm/W	2700 lm
910505100040	WT120C G2 LED27S/8 40 PSU MDU L1200	(0.38,0.38)SDCM<=3	4000 K	126 lm/W	2700 lm
910505100041	WT120C G2 LED27S/8 40 PSU MDU TW3 L1200	(0.38,0.38)SDCM<=3	4000 K	125 lm/W	2700 lm
910505100042	WT120C G2 LED27S/8 40 PSU ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	104 lm/W	2700 lm

Order Code	Full Product Name	Initial chromaticy	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910505100044	WT120C G2 LED27S/8 40 PSD L1200	(0.38,0.38)SDCM<=3	4000 K	123 lm/W	2700 lm
910505100045	WT120C G2 LED27S/8 40 PSD ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	100 lm/W	2700 lm
910505100047	WT120C G2 LED40S/8 40 PSU TW3 L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
910505100048	WT120C G2 LED40S/8 40 PSU MDU L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
910505100049	WT120C G2 LED40S/8 40 PSU MDU TW3 L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
910505100050	WT120C G2 LED40S/8 40 PSU WEC L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm

CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	LED luminaire efficacy	Initial luminous flux
910505100051	WT120C G2 LED40S/8 40 PSU TW1 WEC L1200	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	4000 lm
910505100052	WT120C G2 LED40S/8 40 IA1 L1200	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	4000 lm
910505100053	WT120C G2 LED40S/8 40 PSD L1200	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	4000 lm
910505100054	WT120C G2 LED40S/8 40 PSU ELB3 L1200	(0.38,0.38)	SDCM<=3 4000 K	114 lm/W	4000 lm
910505100055	WT120C G2 LED40S/8 40 PSU MDU ELB3 L1200	(0.38,0.38)	SDCM<=3 4000 K	114 lm/W	4000 lm
910505100056	WT120C G2 LED40S/8 40 IA1 ELB3 L1200	(0.38,0.38)	SDCM<=3 4000 K	116 lm/W	4000 lm
910505100057	WT120C G2 LED40S/8 40 PSD ELB3 L1200	(0.38,0.38)	SDCM<=3 4000 K	114 lm/W	4000 lm
910505100058	WT120C G2 LED34S/8 40 PSU TW3 L1500	(0.38,0.38)	SDCM<=3 4000 K	136 lm/W	3400 lm
910505100059	WT120C G2 LED34S/8	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	3400 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	LED luminaire efficacy	Initial luminous flux
	40 PSU MDU L1500				
910505100060	WT120C G2 LED34S/8 40 PSU MDU TW3 L1500	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	3400 lm
910505100061	WT120C G2 LED34S/8 40 PSD L1500	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	3400 lm
910505100062	WT120C G2 LED34S/8 40 PSU ELB3 L1500	(0.38,0.38)	SDCM<=3 4000 K	113 lm/W	3400 lm
910505100063	WT120C G2 LED34S/8 40 PSU MDU ELB3 L1500	(0.38,0.38)	SDCM<=3 4000 K	110 lm/W	3400 lm
910505100064	WT120C G2 LED34S/8 40 PSD ELB3 L1500	(0.38,0.38)	SDCM<=3 4000 K	111 lm/W	3400 lm
910505100066	WT120C G2 LED60S/8 40 PSU TW3 L1500	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	6000 lm
910505100067	WT120C G2 LED60S/8 40 PSU MDU L1500	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	6000 lm
910505100068	WT120C G2 LED60S/8 40 PSU	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	6000 lm

CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticy	Init. Corr. Color Temperature	LED luminaire efficacy	Initial luminous flux
	MDU TW3 L1500				
910505100069	WT120C G2 LED60S/8 40 PSU WEC L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	6000 lm
910505100070	WT120C G2 LED60S/8 40 PSU TW1 WEC L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	6000 lm
910505100071	WT120C G2 LED60S/8 40 IA1 L1500	(0.38,0.38)SDCM<=3	4000 K	132 lm/W	6000 lm
910505100072	WT120C G2 LED60S/8 40 PSD L1500	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	6000 lm
910505100073	WT120C G2 LED60S/8 40 PSU ELB3 L1500	(0.38,0.38)SDCM<=3	4000 K	120 lm/W	6000 lm
910505100074	WT120C G2 LED60S/8 40 PSU MDU ELB3 L1500	(0.38,0.38)SDCM<=3	4000 K	120 lm/W	6000 lm
910505100075	WT120C G2 LED60S/8 40 IA1 ELB3 L1500	(0.38,0.38)SDCM<=3	4000 K	120 lm/W	6000 lm
910505100076	WT120C G2 LED60S/8 40 PSD ELB3 L1500	(0.38,0.38)SDCM<=3	4000 K	118 lm/W	6000 lm

Order Code	Full Product Name	Initial chromaticy	Init. Corr. Color Temperature	LED luminaire efficacy	Initial luminous flux
910505100077	WT120C G2 LED80S/8 40 PSU TW3 L1500	(0.38,0.38)SDCM<=3	4000 K	131 lm/W	8000 lm
910505100078	WT120C G2 LED80S/8 40 PSU MDU L1500	(0.38,0.38)SDCM<=3	4000 K	131 lm/W	8000 lm
910505100079	WT120C G2 LED80S/8 40 PSD L1500	(0.38,0.38)SDCM<=3	4000 K	131 lm/W	8000 lm
910505100080	WT120C G2 LED80S/8 40 PSU L1500 ELB3	(0.38,0.38)SDCM<=3	4000 K	121 lm/W	8000 lm
911401823480	WT120C G2 LED19S/8 40 PSU L600	(0.38,0.38)SDCM<=3	4000 K	127 lm/W	1900 lm
911401823580	WT120C G2 LED27S/8 40 PSU L1200	(0.38,0.38)SDCM<=3	4000 K	135 lm/W	2700 lm
911401823680	WT120C G2 LED34S/8 40 PSU L1500	(0.38,0.38)SDCM<=3	4000 K	142 lm/W	3400 lm
911401823780	WT120C G2 LED40S/8 40 PSU L1200	(0.38,0.38)SDCM<=3	4000 K	143 lm/W	4000 lm
911401823880	WT120C G2 LED60S/8 40 PSU L1500	(0.38,0.38)SDCM<=3	4000 K	143 lm/W	6000 lm

CoreLine Waterproof

Order Code	Full Product		Init. Corr. Color	Init. LED luminaire efficacy	Initial luminous flux
	Name	Initial chromaticity			
911401823980	WT120C G2 LED80S/8 40 PSU L1500	(0.38,0.38)SDCM<=3	4000 K	140 lm/W	8000 lm
911401824381	WT120C G2 LED40S/8 65 PSU L1200	(0.31,0.32)SDCM<=3	6500 K	140 lm/W	4000 lm
911401824481	WT120C G2 LED34S/8 65 PSU L1500	(0.31,0.32)SDCM<=3	6500 K	139 lm/W	3400 lm
911401824581	WT120C G2 LED60S/8 65 PSU L1500	(0.31,0.32)SDCM<=3	6500 K	140 lm/W	6000 lm
911401824681	WT120C G2 LED37S/8 30 PSU L1200	(0.43,0.40)SDCM<=3	3000 K	130 lm/W	3700 lm
911401824781	WT120C G2 LED55S/8 30 PSU L1500	(0.43,0.40)SDCM<=3	3000 K	128 lm/W	5500 lm
911401836980	WT120C G2 LED18S/84	(0.38,0.38)SDCM<=3	4000 K	120 lm/W	1800 lm

Order Code	Full Product		Init. Corr. Color	Init. LED luminaire efficacy	Initial luminous flux
	Name	Initial chromaticity			
	0 PSU PCO L600				
911401837080	WT120C G2 LED25S/8 40 PSU PCO L1200	(0.38,0.38)SDCM<=3	4000 K	125 lm/W	2500 lm
911401837180	WT120C G2 LED31S/84 0 PSU PCO L1500	(0.38,0.38)SDCM<=3	4000 K	129 lm/W	3100 lm
911401837280	WT120C G2 LED37S/8 40 PSU PCO L1200	(0.38,0.38)SDCM<=3	4000 K	132 lm/W	3700 lm
911401837380	WT120C G2 LED57S/8 40 PSU PCO L1500	(0.38,0.38)SDCM<=3	4000 K	136 lm/W	5700 lm
911401837480	WT120C G2 LED75S/8 40 PSU PCO L1500	(0.38,0.38)SDCM<=3	4000 K	132 lm/W	7500 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
910505100036	WT120C G2 LED19S/840 PSU MDU L600	16 W
910505100038	WT120C G2 LED19S/840 PSD L600	16 W
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	21 W
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	21.5 W
910505100041	WT120C G2 LED27S/840 PSU MDU TW3 L1200	21.5 W
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	25.5 W
910505100044	WT120C G2 LED27S/840 PSD L1200	22 W
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	27 W
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	30 W
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	30 W
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	30 W
910505100050	WT120C G2 LED40S/840 PSU WEC L1200	29 W

Order Code	Full Product Name	Initial input power
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	29 W
910505100052	WT120C G2 LED40S/840 IA1 L1200	30 W
910505100053	WT120C G2 LED40S/840 PSD L1200	30 W
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	34 W
910505100055	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	35 W
910505100056	WT120C G2 LED40S/840 IA1 ELB3 L1200	33 W
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	35 W
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	25 W
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	25.5 W
910505100060	WT120C G2 LED34S/840 PSU MDU TW3 L1500	25.5 W
910505100061	WT120C G2 LED34S/840 PSD L1500	26 W
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	29.5 W

CoreLine Waterproof

Order Code	Full Product Name	Initial input power
910505100063	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	31 W
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	30.5 W
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	44 W
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	45 W
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	45 W
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	44 W
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	44 W
910505100071	WT120C G2 LED60S/840 IA1 L1500	45.5 W
910505100072	WT120C G2 LED60S/840 PSD L1500	45 W
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	49 W
910505100074	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	50 W
910505100075	WT120C G2 LED60S/840 IA1 ELB3 L1500	50 W
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	49 W
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	60 W
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	61 W
910505100079	WT120C G2 LED80S/840 PSD L1500	61 W
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	63 W

Order Code	Full Product Name	Initial input power
911401823480	WT120C G2 LED19S/840 PSU L600	15 W
911401823580	WT120C G2 LED27S/840 PSU L1200	20.5 W
911401823680	WT120C G2 LED34S/840 PSU L1500	24.3 W
911401823780	WT120C G2 LED40S/840 PSU L1200	28.6 W
911401823880	WT120C G2 LED60S/840 PSU L1500	42.9 W
911401823980	WT120C G2 LED80S/840 PSU L1500	57.1 W
911401824381	WT120C G2 LED40S/865 PSU L1200	28.5 W
911401824481	WT120C G2 LED34S/865 PSU L1500	24.5 W
911401824581	WT120C G2 LED60S/865 PSU L1500	43 W
911401824681	WT120C G2 LED37S/830 PSU L1200	28.5 W
911401824781	WT120C G2 LED55S/830 PSU L1500	43 W
911401836980	WT120C G2 LED18S/840 PSU PCO L600	15 W
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	20.5 W
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	24.3 W
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	28.6 W
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	42.9 W
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	57.1 W

