



# The affordable LED solution

## CorePro LEDtube InstantFit HF

CorePro LEDtube InstantFit HF is an affordable LED solution suitable for replacing T8 fluorescent lamps. It provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

### Benefits

- Minimizes overall lighting costs
- Offers the cheapest and easiest upgrade to LED lighting technology

### Features

- High energy efficiency
- Long lifetime
- Easy installation; retrofit replacement of existing T8 lamps on electronic (HF) ballast installations
- Conventional form factor to fit into existing luminaires
- No mercury

### Application

- Parking lots and covered car parks
- Industrial facilities and warehouses
- Signage


# CorePro LEDtube InstantFit HF

## Versions



G13

## Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube HF 600mm 9W840 T8 G	27.9 mm	28 mm	589.8 mm	595.7 mm	604 mm
CorePro LEDtube HF 600mm 9W865 T8 G	27.9 mm	28 mm	589.8 mm	595.7 mm	604 mm

# CorePro LEDtube InstantFit HF

## Approval and Application

Energy Consumption kWh/1000 h	12 kWh
Energy Efficiency Label (EEL)	A

## Controls and Dimming

Dimmable	No
----------	----

## Operating and Electrical

Input Frequency	20000-80000 Hz
Voltage (Nom)	30-80 V
Power (Rated) (Nom)	9 W
Starting Time (Nom)	0.5 s

## General Information

Cap-Base	G13
Nominal Lifetime (Nom)	30000 h
Switching Cycle	50000X

## Light Technical

Beam Angle (Nom)	240 °
Color Rendering Index (Nom)	83
Llmf At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux (Nom)	800 lm

## Mechanical and Housing


Bulb Shape	Tube, double-ended
------------	--------------------

## Temperature

T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Case Maximum (Nom)	60 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C

## Light Technical

Order Code	Full Product Name	Color Code	Correlated Color Temperature (Nom)
929001249502	CorePro LEDtube HF 600mm 9W840 T8 G	840	4000 K
929001249602	CorePro LEDtube HF 600mm 9W865 T8 G	865	6500 K



## CorePro LEDtube InstantFit HF

