



LuxSpace recessed – high efficiency, visual comfort and a stylish design

LuxSpace, recessed

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application. For office applications LuxSpace supports the general feeling of health and wellbeing having dedicated Tunable White products

Benefits

- Best-in-class efficacy
- Creates a gentle, natural light, ensuring visual comfort
- Perfect integration with the ceiling thanks to the thin, narrow rim; rimless version ideal for integration into plaster ceilings

LuxSpace, recessed

Features

- Choice of four optics: high-gloss, faceted, matt and white
- Heights: deep (up to UGR 19), low (up to UGR 22)
- Light color: 830, 840, 927, 930 and 940 (CRI90 versions upon request)
- Rim colors: high-gloss metalized, white (RAL9003), grey (RAL9006), black (RAL9004) as standard (any other RAL color possible upon request)
- Rimless version available (not for LED40S versions)
- Surface-mounted version available (not for LED40S versions)
- Compliant for central emergency lighting with DC (upon request)
- Multiple additional options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), suspended deco glasses, through-wiring, Eca and B2ca cable & connector options
- LED boards of 2700 up to 6700 K offering many different color temperatures and light levels
- Predefined dynamic curves vary color temperature and intensity as a function of time

Application

- Halls, offices, conference rooms
- Retail
- Hospitals
- Hotels
- Airports
- Museum

Specifications

Type	DN570B (low height recessed version) DN571B (deep recessed version)
Ceiling type	Plaster (board) ceiling
Light source	Non replaceable LED module
Power	11, 19, 23, 34 W (3000K) 11, 17.4, 21, 32 W (4000K)
Light color:	830, 840, 927, 930 and 940
Luminous flux (for 830 and 840 versions)	DN570B, high-gloss mirror or faceted reflector: 1350, 2200, 2600, 4000 lm DN570B, matt reflector: 1150, 1850, 2200, 4000 lm DN570B, white reflector: 1300, 2100, 2500, 4000 lm DN571B, high-gloss mirror or faceted reflector: 1300, 2100, 2500, 4000 lm DN571B, matt reflector: 1000, 1650, 1950, 4000 lm DN571B, white reflector: 1250, 2000, 2400, 4000 lm
Color Rendering Index	> 80 and > 90
Lumen maintenance at median useful life* 50000 h	L90
Control gear failure rate at median useful life 50000 h	5%
Performance Ambient Temperature Tq	+25 °C

Operating temperature range	+10 to +40 °C
Driver	Separate
Mains voltage	230 or 240 V / 50-60 Hz
Dimming	DALI dimming possible (PSD-E)
Options	Emergency lighting 3 hours (EL3) Protection glass (PG or PGO, IP54 front face) Through-wiring Rimless version for plaster ceiling (not for LED40S) Suspended glasses: opal (SG-O), frosted circle (SG-FRC) and frosted halo ring (SG-HR-FR) Different cable and connector options available to support fast installation
Material	Housing and rim: aluminum Reflector: plastic, aluminum coated (for high-gloss and faceted optics)
Color	Rim: white (RAL 9003), grey (RAL 9006), black (RAL 9004)
Optic	High-gloss mirror (C) Matt mirror (M) Faceted reflector (F) White reflector (WR)
Connection	Push-in connector or with pull relief
Installation	Fixation by means of spring fasteners
Remarks	External driver included

LuxSpace, recessed

Versions



LUXSPACE 2 COMPACT LOW
HEIGHT - LED Module, system flux
1200 lm



LUXSPACE 2 COMPACT DEEP -
LED Module, system flux 1200 lm



LUXSPACE 2 COMPACT LOW
HEIGHT - LED Module, system flux
1200 lm



LUXSPACE 2 COMPACT LOW
HEIGHT - LED Module, system flux
1200 lm



LUXSPACE 2 COMPACT LOW
HEIGHT - LED Module, system flux
1200 lm

Accessories



Ochranné sklo
Ordercode 910503586401



Ochranné sklo opálové
Ordercode 910503586402

Application Conditions

Ambient temperature range	+10 to +25 °C
Suitable for random switching	Yes

Approval and Application

Mech. impact protection code	IK02
------------------------------	------

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

CE mark	CE mark
Protection class IEC	Safety class II
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 5 s
Light source replaceable	No
Number of gear units	1 unit

Initial Performance (IEC Compliant)

Init. Color Rendering Index	>80
Luminous flux tolerance	+/-10%

Mechanical and Housing

Color	White RAL 9003
-------	----------------

Application Conditions

Order Code	Full Product Name	Maximum dim level
910505100834	DN570B LED12S/830 PSU-E C EW WH	-
910505100835	DN570B LED12S/840 PSU-E C WH	-
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	1%
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	1%
910505100842	DN570B LED20S/830 PSU-E C WH	-
910505100843	DN570B LED20S/840 PSU-E C WH	-
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	-
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	-
910505100850	DN570B LED20S/830 PSU-E C PG WH	-
910505100851	DN570B LED20S/840 PSU-E C PG WH	-
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	1%
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	1%
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	1%
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	1%
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	1%
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	1%
910505100868	DN570B LED24S/830 PSU-E C WH	-
910505100869	DN570B LED24S/840 PSU-E C WH	-
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	1%
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	1%
910505100876	DN570B LED24S/830 IA1-E C WH	1%
910505100877	DN570B LED24S/840 IA1-E C WH	1%
910505100878	DN570B LED24S/830 IA1-E C ELP3 WH	1%
910505100879	DN570B LED24S/840 IA1-E C ELP3 WH	1%
910505100884	DN570B LED40S/830 PSU-E C WH	-
910505100885	DN570B LED40S/840 PSU-E C WH	-
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	1%
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	1%
910505100892	DN570B LED40S/830 IA1-E C WH	1%
910505100893	DN570B LED40S/840 IA1-E C WH	1%
910505100894	DN570B LED40S/830 IA1-E C ELP3 WH	1%
910505100895	DN570B LED40S/840 IA1-E C ELP3 WH	1%
910505100903	DN570B LED60S/830 PSU-E C WH	-
910505100904	DN570B LED60S/840 PSU-E C WH	-
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	1%
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	1%
910505101204	DN570B LED12S/830 PSU-E C WH	-
910505100836	DN571B LED12S/830 PSU-E C WH	-
910505100837	DN571B LED12S/840 PSU-E C WH	-
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	1%
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	1%
910505100846	DN571B LED20S/830 PSU-E C WH	-
910505100847	DN571B LED20S/840 PSU-E C WH	-
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	-
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	-
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	1%
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	1%
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	1%
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	1%
910505100870	DN571B LED24S/830 PSU-E C WH	-
910505100871	DN571B LED24S/840 PSU-E C WH	-

Order Code	Full Product Name	Maximum dim level
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	1%
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	1%
910505100880	DN571B LED24S/830 IA1-E C WH	1%
910505100881	DN571B LED24S/840 IA1-E C WH	1%
910505100882	DN571B LED24S/830 IA1-E C ELP3 WH	1%
910505100883	DN571B LED24S/840 IA1-E C ELP3 WH	1%
910505100886	DN571B LED40S/830 PSU-E C WH	-
910505100887	DN571B LED40S/840 PSU-E C WH	-
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	1%
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	1%
910505100896	DN571B LED40S/830 IA1-E C WH	1%
910505100897	DN571B LED40S/840 IA1-E C WH	1%
910505100898	DN571B LED40S/830 IA1-E C ELP3 WH	1%
910505100899	DN571B LED40S/840 IA1-E C ELP3 WH	1%
910505100852	DN570B LED20S/830 PSU-E F WH	-
910505100853	DN570B LED20S/840 PSU-E F WH	-
910505100854	DN570B LED20S/830 PSU-E M WH	-
910505100855	DN570B LED20S/840 PSU-E M WH	-
910505100856	DN570B LED20S/830 PSU-E WR WH	-
910505100857	DN570B LED20S/840 PSU-E WR WH	-

Approval and Application

Order Code	Full Product Name	Ingress protection code	Order Code	Full Product Name	Ingress protection code
910505100834	DN570B LED12S/830 PSU-E C EW WH	IP20	910505100892	DN570B LED40S/830 IA1-E C WH	IP20
910505100835	DN570B LED12S/840 PSU-E C WH	IP20	910505100893	DN570B LED40S/840 IA1-E C WH	IP20
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	IP20	910505100894	DN570B LED40S/830 IA1-E C ELP3 WH	IP20
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	IP20	910505100895	DN570B LED40S/840 IA1-E C ELP3 WH	IP20
910505100842	DN570B LED20S/830 PSU-E C WH	IP20	910505100903	DN570B LED60S/830 PSU-E C WH	IP20
910505100843	DN570B LED20S/840 PSU-E C WH	IP20	910505100904	DN570B LED60S/840 PSU-E C WH	IP20
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	IP20	910505100905	DN570B LED60S/830 DIA-VLC-E C WH	IP20
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	IP20	910505100906	DN570B LED60S/840 DIA-VLC-E C WH	IP20
910505100850	DN570B LED20S/830 PSU-E C PG WH	IP54/20	910505101204	DN570B LED12S/830 PSU-E C WH	IP20
910505100851	DN570B LED20S/840 PSU-E C PG WH	IP54/20	910505100836	DN571B LED12S/830 PSU-E C WH	IP20
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	IP20	910505100837	DN571B LED12S/840 PSU-E C WH	IP20
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	IP20	910505100840	DN571B LED12S/830 DIA-VLC-E C WH	IP20
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	IP20	910505100841	DN571B LED12S/840 DIA-VLC-E C WH	IP20
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	IP20	910505100846	DN571B LED20S/830 PSU-E C WH	IP20
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	IP54/20	910505100847	DN571B LED20S/840 PSU-E C WH	IP20
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	IP54/20	910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	IP20
910505100868	DN570B LED24S/830 PSU-E C WH	IP20	910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	IP20
910505100869	DN570B LED24S/840 PSU-E C WH	IP20	910505100864	DN571B LED20S/830 DIA-VLC-E C WH	IP20
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	IP20	910505100865	DN571B LED20S/840 DIA-VLC-E C WH	IP20
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	IP20	910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	IP20
910505100876	DN570B LED24S/830 IA1-E C WH	IP20	910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	IP20
910505100877	DN570B LED24S/840 IA1-E C WH	IP20	910505100870	DN571B LED24S/830 PSU-E C WH	IP20
910505100878	DN570B LED24S/830 IA1-E C ELP3 WH	IP20	910505100871	DN571B LED24S/840 PSU-E C WH	IP20
910505100879	DN570B LED24S/840 IA1-E C ELP3 WH	IP20	910505100874	DN571B LED24S/830 DIA-VLC-E C WH	IP20
910505100884	DN570B LED40S/830 PSU-E C WH	IP20	910505100875	DN571B LED24S/840 DIA-VLC-E C WH	IP20
910505100885	DN570B LED40S/840 PSU-E C WH	IP20	910505100880	DN571B LED24S/830 IA1-E C WH	IP20
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	IP20	910505100881	DN571B LED24S/840 IA1-E C WH	IP20
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	IP20	910505100882	DN571B LED24S/830 IA1-E C ELP3 WH	IP20

Order Code	Full Product Name	Ingress protection code
910505100883	DN571B LED24S/840 IA1-E C ELP3 WH	IP20
910505100886	DN571B LED40S/830 PSU-E C WH	IP20
910505100887	DN571B LED40S/840 PSU-E C WH	IP20
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	IP20
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	IP20
910505100896	DN571B LED40S/830 IA1-E C WH	IP20
910505100897	DN571B LED40S/840 IA1-E C WH	IP20
910505100898	DN571B LED40S/830 IA1-E C ELP3 WH	IP20

Order Code	Full Product Name	Ingress protection code
910505100899	DN571B LED40S/840 IA1-E C ELP3 WH	IP20
910505100852	DN570B LED20S/830 PSU-E F WH	IP20
910505100853	DN570B LED20S/840 PSU-E F WH	IP20
910505100854	DN570B LED20S/830 PSU-E M WH	IP20
910505100855	DN570B LED20S/840 PSU-E M WH	IP20
910505100856	DN570B LED20S/830 PSU-E WR WH	IP20
910505100857	DN570B LED20S/840 PSU-E WR WH	IP20

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505100834	DN570B LED12S/830 PSU-E C EW WH	No
910505100835	DN570B LED12S/840 PSU-E C WH	No
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	Yes
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	Yes
910505100842	DN570B LED20S/830 PSU-E C WH	No
910505100843	DN570B LED20S/840 PSU-E C WH	No
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	No
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	No
910505100850	DN570B LED20S/830 PSU-E C PG WH	No
910505100851	DN570B LED20S/840 PSU-E C PG WH	No
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	Yes
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	Yes
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	Yes
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	Yes
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	Yes
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	Yes
910505100868	DN570B LED24S/830 PSU-E C WH	No
910505100869	DN570B LED24S/840 PSU-E C WH	No
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	Yes
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	Yes
910505100876	DN570B LED24S/830 IA1-E C WH	Yes
910505100877	DN570B LED24S/840 IA1-E C WH	Yes
910505100878	DN570B LED24S/830 IA1-E C ELP3 WH	Yes
910505100879	DN570B LED24S/840 IA1-E C ELP3 WH	Yes
910505100884	DN570B LED40S/830 PSU-E C WH	No
910505100885	DN570B LED40S/840 PSU-E C WH	No
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	Yes
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	Yes
910505100892	DN570B LED40S/830 IA1-E C WH	Yes
910505100893	DN570B LED40S/840 IA1-E C WH	Yes
910505100894	DN570B LED40S/830 IA1-E C ELP3 WH	Yes
910505100895	DN570B LED40S/840 IA1-E C ELP3 WH	Yes
910505100903	DN570B LED60S/830 PSU-E C WH	No
910505100904	DN570B LED60S/840 PSU-E C WH	No
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	Yes
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	Yes

Order Code	Full Product Name	Dimmable
910505101204	DN570B LED12S/830 PSU-E C WH	No
910505100836	DN571B LED12S/830 PSU-E C WH	No
910505100837	DN571B LED12S/840 PSU-E C WH	No
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	Yes
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	Yes
910505100846	DN571B LED20S/830 PSU-E C WH	No
910505100847	DN571B LED20S/840 PSU-E C WH	No
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	No
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	No
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	Yes
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	Yes
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	Yes
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	Yes
910505100870	DN571B LED24S/830 PSU-E C WH	No
910505100871	DN571B LED24S/840 PSU-E C WH	No
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	Yes
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	Yes
910505100880	DN571B LED24S/830 IA1-E C WH	Yes
910505100881	DN571B LED24S/840 IA1-E C WH	Yes
910505100882	DN571B LED24S/830 IA1-E C ELP3 WH	Yes
910505100883	DN571B LED24S/840 IA1-E C ELP3 WH	Yes
910505100886	DN571B LED40S/830 PSU-E C WH	No
910505100887	DN571B LED40S/840 PSU-E C WH	No
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	Yes
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	Yes
910505100896	DN571B LED40S/830 IA1-E C WH	Yes
910505100897	DN571B LED40S/840 IA1-E C WH	Yes
910505100898	DN571B LED40S/830 IA1-E C ELP3 WH	Yes
910505100899	DN571B LED40S/840 IA1-E C ELP3 WH	Yes
910505100852	DN570B LED20S/830 PSU-E F WH	No
910505100853	DN570B LED20S/840 PSU-E F WH	No
910505100854	DN570B LED20S/830 PSU-E M WH	No
910505100855	DN570B LED20S/840 PSU-E M WH	No
910505100856	DN570B LED20S/830 PSU-E WR WH	No
910505100857	DN570B LED20S/840 PSU-E WR WH	No

General Information

Order Code	Full Product Name	Optic type	Product Family Code	Service tag
910505100834	DN570B LED12S/830 PSU-E C EW WH	High-gloss mirror	DN570B	Yes
910505100835	DN570B LED12S/840 PSU-E C WH	High-gloss mirror	DN570B	Yes
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	High-gloss mirror	DN570B	Yes
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	High-gloss mirror	DN570B	Yes
910505100842	DN570B LED20S/830 PSU-E C WH	High-gloss mirror	DN570B	Yes
910505100843	DN570B LED20S/840 PSU-E C WH	High-gloss mirror	DN570B	Yes
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	High-gloss mirror	DN570B	Yes
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	High-gloss mirror	DN570B	Yes
910505100850	DN570B LED20S/830 PSU-E C PG WH	High-gloss mirror	DN570B	Yes
910505100851	DN570B LED20S/840 PSU-E C PG WH	High-gloss mirror	DN570B	Yes
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	High-gloss mirror	DN570B	Yes
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	High-gloss mirror	DN570B	Yes
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	High-gloss mirror	DN570B	Yes
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	High-gloss mirror	DN570B	Yes
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	High-gloss mirror	DN570B	Yes
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	High-gloss mirror	DN570B	Yes
910505100868	DN570B LED24S/830 PSU-E C WH	High-gloss mirror	DN570B	Yes
910505100869	DN570B LED24S/840 PSU-E C WH	High-gloss mirror	DN570B	Yes
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	High-gloss mirror	DN570B	Yes
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	High-gloss mirror	DN570B	Yes
910505100876	DN570B LED24S/830 IA1-E C WH	High-gloss mirror	DN570B	Yes
910505100877	DN570B LED24S/840 IA1-E C WH	High-gloss mirror	DN570B	Yes
910505100878	DN570B LED24S/830 IA1-E C ELP3 WH	High-gloss mirror	DN570B	Yes
910505100879	DN570B LED24S/840 IA1-E C ELP3 WH	High-gloss mirror	DN570B	Yes
910505100884	DN570B LED40S/830 PSU-E C WH	High-gloss mirror	DN570B	Yes

Order Code	Full Product Name	Optic type	Product Family Code	Service tag
910505100885	DN570B LED40S/840 PSU-E C WH	High-gloss mirror	DN570B	Yes
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	High-gloss mirror	DN570B	Yes
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	High-gloss mirror	DN570B	Yes
910505100892	DN570B LED40S/830 IA1-E C WH	High-gloss mirror	DN570B	Yes
910505100893	DN570B LED40S/840 IA1-E C WH	High-gloss mirror	DN570B	Yes
910505100894	DN570B LED40S/830 IA1-E C ELP3 WH	High-gloss mirror	DN570B	Yes
910505100895	DN570B LED40S/840 IA1-E C ELP3 WH	High-gloss mirror	DN570B	Yes
910505100903	DN570B LED60S/830 PSU-E C WH	High-gloss mirror	DN570B	Yes
910505100904	DN570B LED60S/840 PSU-E C WH	High-gloss mirror	DN570B	Yes
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	High-gloss mirror	DN570B	Yes
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	High-gloss mirror	DN570B	Yes
910505101204	DN570B LED12S/830 PSU-E C WH	High-gloss mirror	DN570B	-
910505100836	DN571B LED12S/830 PSU-E C WH	High-gloss mirror	DN571B	Yes
910505100837	DN571B LED12S/840 PSU-E C WH	High-gloss mirror	DN571B	Yes
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	High-gloss mirror	DN571B	Yes
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	High-gloss mirror	DN571B	Yes
910505100846	DN571B LED20S/830 PSU-E C WH	High-gloss mirror	DN571B	Yes
910505100847	DN571B LED20S/840 PSU-E C WH	High-gloss mirror	DN571B	Yes
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	High-gloss mirror	DN571B	Yes
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	High-gloss mirror	DN571B	Yes
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	High-gloss mirror	DN571B	Yes
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	High-gloss mirror	DN571B	Yes
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	High-gloss mirror	DN571B	Yes
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	High-gloss mirror	DN571B	Yes
910505100870	DN571B LED24S/830 PSU-E C WH	High-gloss mirror	DN571B	Yes

Order Code	Full Product Name	Optic type	Product	
			Family Code	Service tag
910505100871	DN571B LED24S/840 PSU-E C WH	High-gloss mirror	DN571B	Yes
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	High-gloss mirror	DN571B	Yes
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	High-gloss mirror	DN571B	Yes
910505100880	DN571B LED24S/830 IA1-E C WH	High-gloss mirror	DN571B	Yes
910505100881	DN571B LED24S/840 IA1-E C WH	High-gloss mirror	DN571B	Yes
910505100882	DN571B LED24S/830 IA1-E C ELP3 WH	High-gloss mirror	DN571B	Yes
910505100883	DN571B LED24S/840 IA1-E C ELP3 WH	High-gloss mirror	DN571B	Yes
910505100886	DN571B LED40S/830 PSU-E C WH	High-gloss mirror	DN571B	Yes
910505100887	DN571B LED40S/840 PSU-E C WH	High-gloss mirror	DN571B	Yes
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	High-gloss mirror	DN571B	Yes
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	High-gloss mirror	DN571B	Yes

Order Code	Full Product Name	Optic type	Product	
			Family Code	Service tag
910505100896	DN571B LED40S/830 IA1-E C WH	High-gloss mirror	DN571B	Yes
910505100897	DN571B LED40S/840 IA1-E C WH	High-gloss mirror	DN571B	Yes
910505100898	DN571B LED40S/830 IA1-E C ELP3 WH	High-gloss mirror	DN571B	Yes
910505100899	DN571B LED40S/840 IA1-E C ELP3 WH	High-gloss mirror	DN571B	Yes
910505100852	DN570B LED20S/830 PSU-E F WH	Facetted reflector	DN570B	Yes
910505100853	DN570B LED20S/840 PSU-E F WH	Facetted reflector	DN570B	Yes
910505100854	DN570B LED20S/830 PSU-E M WH	Matt optic decorative	DN570B	Yes
910505100855	DN570B LED20S/840 PSU-E M WH	Matt optic decorative	DN570B	Yes
910505100856	DN570B LED20S/830 PSU-E WR WH	High-gloss mirror	DN570B	Yes
910505100857	DN570B LED20S/840 PSU-E WR WH	High-gloss mirror	DN570B	Yes

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr.	Initial LED	Initial
			Color Temperature	luminaire efficacy	luminous flux
910505100834	DN570B LED12S/830 PSU-E C EW WH	(0.43, 0.40) SDCM <2	3000 K	131 lm/W	1300 lm
910505100835	DN570B LED12S/840 PSU-E C WH	(0.38, 0.38) SDCM <2	4000 K	141 lm/W	1300 lm
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM <2	3000 K	131 lm/W	1300 lm
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM <2	4000 K	141 lm/W	1300 lm
910505100842	DN570B LED20S/830 PSU-E C WH	(0.43, 0.40) SDCM <2	3000 K	134 lm/W	2200 lm
910505100843	DN570B LED20S/840 PSU-E C WH	(0.38, 0.38) SDCM <2	4000 K	149 lm/W	2200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr.	Initial LED	Initial
			Color Temperature	luminaire efficacy	luminous flux
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40) SDCM <2	3000 K	113 lm/W	2200 lm
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.38) SDCM <2	4000 K	124 lm/W	2200 lm
910505100850	DN570B LED20S/830 PSU-E C PG WH	(0.43, 0.40) SDCM <2	3000 K	134 lm/W	2200 lm
910505100851	DN570B LED20S/840 PSU-E C PG WH	(0.38, 0.38) SDCM <2	4000 K	149 lm/W	2200 lm
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM <2	3000 K	134 lm/W	2200 lm
910505100859	DN570B LED20S/840	(0.38, 0.38) SDCM <2	4000 K	149 lm/W	2200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	DIA-VLC-E C WH				
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2200 lm
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	(0.38, 0.38)	4000 K	124 lm/W	2200 lm
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm
910505100868	DN570B LED24S/830 PSU-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
910505100869	DN570B LED24S/840 PSU-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
910505100876	DN570B LED24S/830 IA1-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
910505100877	DN570B LED24S/840 IA1-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
910505100878	DN570B LED24S/830 IA1-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2600 lm
910505100879	DN570B LED24S/840 IA1-E C ELP3 WH	(0.38, 0.38)	4000 K	121 lm/W	2600 lm
910505100884	DN570B LED40S/830 PSU-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910505100885	DN570B LED40S/840 PSU-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
910505100892	DN570B LED40S/830 IA1-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm
910505100893	DN570B LED40S/840 IA1-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
910505100894	DN570B LED40S/830 IA1-E C ELP3 WH	(0.43, 0.40)	3000 K	122 lm/W	4400 lm
910505100895	DN570B LED40S/840 IA1-E C ELP3 WH	(0.38, 0.38)	4000 K	133 lm/W	4400 lm
910505100903	DN570B LED60S/830 PSU-E C WH	(0.43, 0.40)	3000 K	129 lm/W	6200 lm
910505100904	DN570B LED60S/840 PSU-E C WH	(0.38, 0.38)	4000 K	141 lm/W	6200 lm
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	129 lm/W	6200 lm
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	141 lm/W	6200 lm
910505101204	DN570B LED12S/830 PSU-E C WH	(0.43, 0.40)	3000 K	131 lm/W	1300 lm
910505100836	DN571B LED12S/830 PSU-E C WH	(0.43, 0.40)	3000 K	131 lm/W	1300 lm
910505100837	DN571B LED12S/840 PSU-E C WH	(0.38, 0.38)	4000 K	141 lm/W	1300 lm
910505100840	DN571B LED12S/830	(0.43, 0.40)	3000 K	131 lm/W	1300 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	DIA-VLC-E C WH				
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	141 lm/W	1300 lm
910505100846	DN571B LED20S/830 PSU-E C WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
910505100847	DN571B LED20S/840 PSU-E C WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2200 lm
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.38)	4000 K	124 lm/W	2200 lm
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2200 lm
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	(0.38, 0.38)	4000 K	124 lm/W	2200 lm
910505100870	DN571B LED24S/830 PSU-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
910505100871	DN571B LED24S/840 PSU-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910505100880	DN571B LED24S/830 IA1-E C WH	(0.43, 0.40)	3000 K	130 lm/W	2600 lm
910505100881	DN571B LED24S/840 IA1-E C WH	(0.38, 0.38)	4000 K	141 lm/W	2600 lm
910505100882	DN571B LED24S/830 IA1-E C ELP3 WH	(0.43, 0.40)	3000 K	113 lm/W	2600 lm
910505100883	DN571B LED24S/840 IA1-E C ELP3 WH	(0.38, 0.38)	4000 K	121 lm/W	2600 lm
910505100886	DN571B LED40S/830 PSU-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm
910505100887	DN571B LED40S/840 PSU-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
910505100896	DN571B LED40S/830 IA1-E C WH	(0.43, 0.40)	3000 K	133 lm/W	4400 lm
910505100897	DN571B LED40S/840 IA1-E C WH	(0.38, 0.38)	4000 K	147 lm/W	4400 lm
910505100898	DN571B LED40S/830 IA1-E C ELP3 WH	(0.43, 0.40)	3000 K	122 lm/W	4400 lm
910505100899	DN571B LED40S/840 IA1-E C ELP3 WH	(0.38, 0.38)	4000 K	133 lm/W	4400 lm
910505100852	DN570B LED20S/830 PSU-E F WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm
910505100853	DN570B LED20S/840 PSU-E F WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910505100854	DN570B LED20S/830 PSU-E M WH	(0.43, 0.40)	3000 K	113 lm/W	1860 lm
910505100855	DN570B LED20S/840 PSU-E M WH	(0.38, 0.38)	4000 K	127 lm/W	1860 lm
910505100856	DN570B LED20S/830 PSU-E WR WH	(0.43, 0.40)	3000 K	134 lm/W	2200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910505100857	DN570B LED20S/840 PSU-E WR WH	(0.38, 0.38)	4000 K	149 lm/W	2200 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
910505100834	DN570B LED12S/830 PSU-E C EW WH	9.9 W
910505100835	DN570B LED12S/840 PSU-E C WH	9.2 W
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	9.9 W
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	9.2 W
910505100842	DN570B LED20S/830 PSU-E C WH	16.4 W
910505100843	DN570B LED20S/840 PSU-E C WH	14.8 W
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	19.4 W
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	17.8 W
910505100850	DN570B LED20S/830 PSU-E C PG WH	16.4 W
910505100851	DN570B LED20S/840 PSU-E C PG WH	14.8 W
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	16.4 W
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	14.8 W
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	19.4 W
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	17.8 W
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	16.4 W
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	14.8 W
910505100868	DN570B LED24S/830 PSU-E C WH	20 W
910505100869	DN570B LED24S/840 PSU-E C WH	18.4 W
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	20 W
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	18.4 W
910505100876	DN570B LED24S/830 IA1-E C WH	20 W
910505100877	DN570B LED24S/840 IA1-E C WH	18.4 W
910505100878	DN570B LED24S/830 IA1-E C ELP3 WH	23 W
910505100879	DN570B LED24S/840 IA1-E C ELP3 WH	21.4 W
910505100884	DN570B LED40S/830 PSU-E C WH	33 W
910505100885	DN570B LED40S/840 PSU-E C WH	30 W
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	33 W
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	30 W
910505100892	DN570B LED40S/830 IA1-E C WH	33 W
910505100893	DN570B LED40S/840 IA1-E C WH	30 W
910505100894	DN570B LED40S/830 IA1-E C ELP3 WH	36 W
910505100895	DN570B LED40S/840 IA1-E C ELP3 WH	33 W
910505100903	DN570B LED60S/830 PSU-E C WH	48 W
910505100904	DN570B LED60S/840 PSU-E C WH	44 W
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	48 W
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	44 W

Order Code	Full Product Name	Initial input power
910505101204	DN570B LED12S/830 PSU-E C WH	9.9 W
910505100836	DN571B LED12S/830 PSU-E C WH	9.9 W
910505100837	DN571B LED12S/840 PSU-E C WH	9.2 W
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	9.9 W
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	9.2 W
910505100846	DN571B LED20S/830 PSU-E C WH	16.4 W
910505100847	DN571B LED20S/840 PSU-E C WH	14.8 W
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	19.4 W
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	17.8 W
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	16.4 W
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	14.8 W
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	19.4 W
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	17.8 W
910505100870	DN571B LED24S/830 PSU-E C WH	20 W
910505100871	DN571B LED24S/840 PSU-E C WH	18.4 W
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	20 W
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	18.4 W
910505100880	DN571B LED24S/830 IA1-E C WH	20 W
910505100881	DN571B LED24S/840 IA1-E C WH	18.4 W
910505100882	DN571B LED24S/830 IA1-E C ELP3 WH	23 W
910505100883	DN571B LED24S/840 IA1-E C ELP3 WH	21.4 W
910505100886	DN571B LED40S/830 PSU-E C WH	33 W
910505100887	DN571B LED40S/840 PSU-E C WH	30 W
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	33 W
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	30 W
910505100896	DN571B LED40S/830 IA1-E C WH	33 W
910505100897	DN571B LED40S/840 IA1-E C WH	30 W
910505100898	DN571B LED40S/830 IA1-E C ELP3 WH	36 W
910505100899	DN571B LED40S/840 IA1-E C ELP3 WH	33 W
910505100852	DN570B LED20S/830 PSU-E F WH	16.4 W
910505100853	DN570B LED20S/840 PSU-E F WH	14.8 W
910505100854	DN570B LED20S/830 PSU-E M WH	16.4 W
910505100855	DN570B LED20S/840 PSU-E M WH	14.8 W
910505100856	DN570B LED20S/830 PSU-E WR WH	16.4 W
910505100857	DN570B LED20S/840 PSU-E WR WH	14.8 W

