



Digital ignitors for silent operation

Electronic parallel ignitor for HID lamp circuits

HID ignitors for parallel systems

Benefits

- Will only work with semi-parallel ballasts
- Silent operation
- Can operate remotely at considerable distance from the lamp

Features

- Parallel ignitor will only work in parallel circuits and must be matched with the relevant ballast
- Ignitors equipped with screw terminal blocks as standard
- Lightweight and compact products
- Current flows through ignitor only at lamp start-up

Application

- Outdoor lighting (most popular applications: road, sports and area lighting)


Electronic parallel ignitor for HID lamp circuits

Versions



SI52 IGNITOR

Dimensional drawing



Product	C1	A1	A2	B1	D1
SI 52	38.5 mm	85.5 mm	65.0 mm	41.5 mm	4.3 mm
SI 51 Plus	38.5 mm	85.5 mm	65.0 mm	41.5 mm	4.3 mm

