



# Digital ignitors for maximum reliability

## Electronic series ignitor for HID lamp circuits

HID ignitors for series systems

### Benefits

- Easy installation and wiring
- Can operate with both semi-parallel and series ballasts
- Digital ignitors ensure maximum reliability

### Features

- Ignitors equipped with screw terminal blocks as standard
- Series ignitor will only work in series circuits

### Application

- Outdoor lighting (most popular application: roads and tunnels)

### Versions



SU 50

# Electronic series ignitor for HID lamp circuits

## Dimensional drawing

Product	C1	A1	A2	B1	D1
SU 50	50 mm	90 mm	69 mm	55 mm	4.3 mm
SU 52	50 mm	90 mm	69 mm	55 mm	4.3 mm

### Operating and Electrical

Input Frequency	50 to 60 Hz
-----------------	-------------

### Mechanical and Housing

Housing	PC UL94V-2
---------	------------

## Operating and Electrical

Order Code	Full Product Name	Input Voltage
913710011213	SU 50	220 to 240 V

Order Code	Full Product Name	Input Voltage
913710011313	SU 52	380-420 V

