



Versatile and cost-efficient LED lighting

ClearWay gen2

ClearWay gen2 enables you to enjoy the benefits of LED technology right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimize your Total Cost of Ownership. ClearWay gen2 significantly improves the most important aspects of the street lighting experience compared to conventional lighting. Ideal for new streets and for renovating existing installations, this affordable range of lighting solutions combines clean, high quality light with significant energy and maintenance savings. In short, ClearWay gen2 means good quality light with all the added benefits of LED – energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design, which makes it easier to install.

Benefits

- All benefits packaged in one single luminaire architecture
- Easy to install
- Low initial cost
- Reasonable Total Cost of Ownership
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

Features

- One flexible design variant offering different options depending on the needs of the application
- Compact and efficient design
- Tilt regulation without needing to open cover
- ClearWay gen2 is also equipped with a dedicated light recipes that preserves a dark night sky.

ClearWay gen2

Application

- Urban and residential roads
- Bicycle and pedestrian paths
- Minor roads

Specifications

Ambient Temperature	-40 to +50 °C
Beam spread luminaire	-, 152° - 25° x 66°, 154° - 31° x 54°, 157° - 33° x 55°, 160° - 42° x 54°, 42° x 44°, 61° x 150°
Main color of the Luminaire	Aluminum, dark gray, gray
Connection	Connection unit 5-pole (Connection unit 5-pole) Push-in connector 5-pole (Push-in connector 5-pole) Screw connection block 3-pole (Screw connection block 3-pole)
Dimming	No, yes
Driver	Power supply unit (Power supply unit) Power supply unit regulating (Power supply unit regulating) Power supply unit with DALI interface and constant light output (Power supply unit with DALI interface and constant light output) Power supply unit with DynaDimmer (Power supply unit with DynaDimmer) Power supply unit with DynaDimmer and constant light output (integrated) (Power supply unit with DynaDimmer and constant light output (integrated))
Initial LED luminaire efficacy	100, 103, 104, 106, 110, 112, 114, 116, 118, 119, 122, 124, 125, 126, 127, 128, 131, 132, 133, 136, 137, 138, 139, 140, 141, 143, 145, 146, 147, 150, 152 lm/W

Initial luminous flux	1000.5, 1522.5, 1566, 1584, 2064, 2088, 2175, 2250, 2371, 2610, 2670, 2958, 3045, 3080, 3115, 3233, 3520, 3560, 3741, 3780, 3828, 3915, 3960, 4005, 4118, 4524, 4698, 4752, 5880, 5916, 6020, 6090, 6160, 6972, 7134, 7308, 8256, 8600, 9030, 9460, 9775, 10200, 10920 lm
Input frequency	50 to 60 Hz
Input voltage	220 to 240, 220-240 V
Light source color	740 neutral white, 830 warm white
Light source replaceable	Yes
Material	Housing: aluminum die cast
Optic	Distribution extra wide 10, distribution medium, distribution medium 10, distribution medium 11, distribution medium 50
Surge protection	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode, luminaire surge protection level until 6 kV differential mode and 8 kV common mode, philips standard surge protection level
Tilt angle housing	Standard tilt angle posttop: 0°Standard tilt angle side entry: 0°
Type	BGP307

Versions



ClearWay gen2 - LED Module
2500 lm - 740 neutral white -
Safety class I - Distribution
medium - Universal for diameter
48 to 60 mm adjustable



ClearWay gen2 - LED module 1800
lm - 740 neutral white - Safety
class I - Distribution medium 50 -
Universal for diameter 48 to 60
mm adjustable

General Information

CE mark	CE mark
Optical cover/lens type	Flat glass
Driver included	Yes
Flammability mark	-
Light source replaceable	Yes
Number of gear units	1 unit
Product Family Code	BGP307

Light Technical

Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Upward light output ratio	0

Application Conditions

Order Code	Full Product Name	Maximum dim level
910925864560	BGP307 LED25/740 I DM 48/60S	Not applicable
910925864561	BGP307 LED30/740 I DM 48/60S	Not applicable
910925864562	BGP307 LED35/740 I DM 48/60S	Not applicable
910925864563	BGP307 LED40/740 I DM 48/60S	Not applicable
910925864564	BGP307 LED45/740 I DM 48/60S	Not applicable
910925864565	BGP307 LED54/740 I DM 48/60S	Not applicable
910925864566	BGP307 LED69/740 I DM 48/60S	Not applicable
910925864567	BGP307 LED84/740 I DM 48/60S	Not applicable
910925864568	BGP307 LED99/740 I DM 48/60S	Not applicable
910925864569	BGP307 LED109/740 I DM 48/60S	Not applicable
910925864572	BGP307 LED25/740 II DM 48/60S	Not applicable
910925864573	BGP307 LED30/740 II DM 48/60S	Not applicable
910925864574	BGP307 LED35/740 II DM 48/60S	Not applicable
910925864575	BGP307 LED40/740 II DM 48/60S	Not applicable
910925864576	BGP307 LED45/740 II DM 48/60S	Not applicable
910925864577	BGP307 LED54/740 II DM 48/60S	Not applicable
910925864578	BGP307 LED69/740 II DM 48/60S	Not applicable
910925864579	BGP307 LED84/740 II DM 48/60S	Not applicable
910925864580	BGP307 LED99/740 II DM 48/60S	Not applicable
910925864581	BGP307 LED109/740 II DM 48/60S	Not applicable
910925865125	BGP307 LED25/740 I DM DDF27 D18 48/60S	0% (digital)
910925865126	BGP307 LED69/740 I DM DDF27 D18 48/60S	0% (digital)
910925865127	BGP307 LED84/740 I DM DDF27 D18 48/60S	0% (digital)
910925865128	BGP307 LED99/740 I DM DDF27 D18 48/60S	0% (digital)
910925865375	BGP307 LED18/830 II DM11 C10	0% (digital)
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05Z1Z1-	0% (digital)
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05Z1Z1-	0% (digital)
910925865378	BGP307 LED54/740 II DM11 C10	0% (digital)
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	0% (digital)
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Not applicable
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Not applicable
910925865746	BGP307 LED12-4S/830 II DM10 MSP CLO-LS-8	Not applicable
910925865748	BGP307 LED25-4S/830 II DM10 MSP CLO-LS-8	Not applicable
910925868754	BGP307 LED25/740 II DM MSP CLO-LS-8 D18	Programmable
910925868755	BGP307 LED35/740 II DM MSP CLO-LS-8 D18	Programmable

Order Code	Full Product Name	Maximum dim level
910925868756	BGP307 LED45/740 II DM MSP CLO-LS-8 D18	Programmable
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	Not applicable
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	Not applicable
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	Not applicable
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	Not applicable
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	Not applicable
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	Not applicable
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	Not applicable
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	Not applicable
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	Not applicable
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	Not applicable
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	Not applicable
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	Not applicable
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	Not applicable
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	Not applicable
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	Not applicable
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	Not applicable
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	Not applicable
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	Not applicable
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	Not applicable
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	Not applicable
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	Not applicable
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	Not applicable
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	Not applicable
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	Not applicable
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	0% (digital)
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	0% (digital)
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	0% (digital)
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	0% (digital)
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	0% (digital)
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	0% (digital)
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	Not applicable
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	Not applicable
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	Not applicable
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	Not applicable
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	0% (digital)
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	0% (digital)
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	0% (digital)
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	0% (digital)
910925865206	BGP307 LED54/740 II DM11 SR C10	0% (digital)
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	0% (digital)
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	0% (digital)
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	0% (digital)
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	0% (digital)
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	0% (digital)
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	0% (digital)
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	0% (digital)
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	0% (digital)
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	0% (digital)

Order Code	Full Product Name	Maximum dim level
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	0% (digital)
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	0% (digital)
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	0% (digital)
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	0% (digital)
910925865352	BGP307 LED35/740 II DM11 CLL C10	Not applicable
910925865374	BGP307 LED45/740 II DM11 CLL C10	Not applicable
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865405	BGP307 LED69/740 II DM11 C10	0% (digital)
910925865406	BGP307 LED84/740 II DM11 C10	0% (digital)
910925865407	BGP307 LED99/740 II DM11 C10	0% (digital)
910925865408	BGP307 LED109/740 II DM11 C10	0% (digital)
910925865409	BGP307 LED120/740 II DM11 C10	0% (digital)
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	0% (digital)

Order Code	Full Product Name	Maximum dim level
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	0% (digital)
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	0% (digital)
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	0% (digital)
910925865419	BGP307 LED25/740 II DM11 CLL C10	Not applicable
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	0% (digital)
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	0% (digital)
910925865690	BGP307 LED18/830 II DM11 SR C10	0% (digital)
910925865691	BGP307 LED54/830 II DM11 SRT C10	0% (digital)
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	0% (digital)
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	0% (digital)
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	0% (digital)
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	0% (digital)
910925865696	BGP307 LED18/740 II DM11 SR C10	0% (digital)
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	0% (digital)
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	0% (digital)
910925865699	BGP307 LED69/740 II DM11 SR C10	0% (digital)
910925865701	BGP307 LED84/740 II DM11 SR C10	0% (digital)
910925865702	BGP307 LED99/740 II DM11 SR C10	0% (digital)
910925865703	BGP307 LED109/740 II DM11 SR C10	0% (digital)
910925865704	BGP307 LED120/740 II DM11 SR C10	0% (digital)
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	0% (digital)
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	0% (digital)
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	0% (digital)
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	0% (digital)
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	0% (digital)
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	0% (digital)
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	0% (digital)
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	0% (digital)
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	0% (digital)
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	0% (digital)
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	0% (digital)
910925865716	BGP307 LED45/830 II DM11 CLL SR C10	0% (digital)
910925865717	BGP307 LED35/830 II DM11 CLL DDF1 SR C10	0% (digital)
910925865718	BGP307 LED45/830 II DM11 CLL DDF1 SR C10	0% (digital)
910925865719	BGP307 LED35/830 II DM11 CLL DDF2 SR C10	0% (digital)
910925865720	BGP307 LED45/830 II DM11 CLL DDF2 SR C10	0% (digital)
910925865721	BGP307 LED35/740 II DM11 CLL SR C10	0% (digital)
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	0% (digital)
910925865723	BGP307 LED35/740 II DM11 CLL DDF1 SR C10	0% (digital)
910925865724	BGP307 LED45/740 II DM11 CLL DDF1 SR C10	0% (digital)
910925865725	BGP307 LED35/740 II DM11 CLL DDF2 SR C10	0% (digital)
910925865726	BGP307 LED45/740 II DM11 CLL DDF2 SR C10	0% (digital)
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	Not applicable
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	Not applicable
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	Not applicable
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	Not applicable

Approval and Application

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925864560	BGP307 LED25/740 I DM 48/60S	IK08	Philips standard surge protection level
910925864561	BGP307 LED30/740 I DM 48/60S	IK08	Philips standard surge protection level
910925864562	BGP307 LED35/740 I DM 48/60S	IK08	Philips standard surge protection level
910925864563	BGP307 LED40/740 I DM 48/60S	IK08	Philips standard surge protection level
910925864564	BGP307 LED45/740 I DM 48/60S	IK08	Philips standard surge protection level
910925864565	BGP307 LED54/740 I DM 48/60S	IK08	Philips standard surge protection level
910925864566	BGP307 LED69/740 I DM 48/60S	IK08	Philips standard surge protection level
910925864567	BGP307 LED84/740 I DM 48/60S	IK08	Philips standard surge protection level
910925864568	BGP307 LED99/740 I DM 48/60S	IK08	Philips standard surge protection level
910925864569	BGP307 LED109/740 I DM 48/60S	IK08	Philips standard surge protection level
910925864572	BGP307 LED25/740 II DM 48/60S	IK08	Philips standard surge protection level
910925864573	BGP307 LED30/740 II DM 48/60S	IK08	Philips standard surge protection level
910925864574	BGP307 LED35/740 II DM 48/60S	IK08	Philips standard surge protection level
910925864575	BGP307 LED40/740 II DM 48/60S	IK08	Philips standard surge protection level
910925864576	BGP307 LED45/740 II DM 48/60S	IK08	Philips standard surge protection level
910925864577	BGP307 LED54/740 II DM 48/60S	IK08	Philips standard surge protection level
910925864578	BGP307 LED69/740 II DM 48/60S	IK08	Philips standard surge protection level
910925864579	BGP307 LED84/740 II DM 48/60S	IK08	Philips standard surge protection level
910925864580	BGP307 LED99/740 II DM 48/60S	IK08	Philips standard surge protection level
910925864581	BGP307 LED109/740 II DM 48/60S	IK08	Philips standard surge protection level
910925865125	BGP307 LED25/740 I DM DDF27 D18 48/60S	IK08	Philips standard surge protection level
910925865126	BGP307 LED69/740 I DM DDF27 D18 48/60S	IK08	Philips standard surge protection level
910925865127	BGP307 LED84/740 I DM DDF27 D18 48/60S	IK08	Philips standard surge protection level
910925865128	BGP307 LED99/740 I DM DDF27 D18 48/60S	IK08	Philips standard surge protection level

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925865375	BGP307 LED18/830 II DM11 C10	IK08	Philips standard surge protection level
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05Z1Z1-	IK08	Philips standard surge protection level
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05Z1Z1-	IK08	Philips standard surge protection level
910925865378	BGP307 LED54/740 II DM11 C10	IK08	Philips standard surge protection level
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	IK08	Philips standard surge protection level
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	IK08	Philips standard surge protection level
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	IK08	Philips standard surge protection level
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	IK08	Philips standard surge protection level
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	IK08	Philips standard surge protection level
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	IK08	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	IK08	Luminaire surge protection level until 6 kV

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
			differential mode and 6 kV common mode
910925865746	BGP307 LED12-4S/830 II DM10 MSP CLO-LS-8	IK08	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
910925865748	BGP307 LED25-4S/830 II DM10 MSP CLO-LS-8	IK08	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
910925868754	BGP307 LED25/740 II DM MSP CLO-LS-8 D18	IK08	Philips standard surge protection level
910925868755	BGP307 LED35/740 II DM MSP CLO-LS-8 D18	IK08	Philips standard surge protection level
910925868756	BGP307 LED45/740 II DM MSP CLO-LS-8 D18	IK08	Philips standard surge protection level
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	IK08	Philips standard surge protection level
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	IK08	Philips standard surge protection level
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	IK08	Philips standard surge protection level
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	IK08	Philips standard surge protection level
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	IK08	Philips standard surge protection level
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	IK08	Philips standard surge protection level
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	IK08	Philips standard surge protection level
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	IK08	Philips standard surge protection level
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	IK08	Philips standard surge protection level
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	IK08	Philips standard surge protection level
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	IK08	Philips standard surge protection level
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	IK08	Philips standard surge protection level
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	IK08	Philips standard surge protection level
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	IK08	Philips standard surge protection level
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	IK08	Philips standard surge protection level
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	IK08	Philips standard surge protection level
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	IK08	Philips standard surge protection level
910925865206	BGP307 LED54/740 II DM11 SR C10	IK08	Philips standard surge protection level
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	IK08	Philips standard surge protection level

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	IK08	Philips standard surge protection level
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	IK08	Philips standard surge protection level
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	IK08	Philips standard surge protection level
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	IK08	Philips standard surge protection level
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	IK08	Philips standard surge protection level
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	IK08	Philips standard surge protection level
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	IK08	Philips standard surge protection level
910925865352	BGP307 LED35/740 II DM11 CLL C10	IK08	Philips standard surge protection level

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925865374	BGP307 LED45/740 II DM11 CLL C10	IK08	Philips standard surge protection level
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865405	BGP307 LED69/740 II DM11 C10	IK08	Philips standard surge protection level
910925865406	BGP307 LED84/740 II DM11 C10	IK08	Philips standard surge protection level
910925865407	BGP307 LED99/740 II DM11 C10	IK08	Philips standard surge protection level
910925865408	BGP307 LED109/740 II DM11 C10	IK08	Philips standard surge protection level
910925865409	BGP307 LED120/740 II DM11 C10	IK08	Philips standard surge protection level
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	IK08	Philips standard surge protection level
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	IK08	Philips standard surge protection level
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	IK08	Philips standard surge protection level
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	IK08	Philips standard surge protection level
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	IK08	Philips standard surge protection level
910925865419	BGP307 LED25/740 II DM11 CLL C10	IK09	Luminaire surge protection level until 6 kV

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	IK08	Philips standard surge protection level
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	IK08	Philips standard surge protection level
910925865690	BGP307 LED18/830 II DM11 SR C10	IK08	Philips standard surge protection level
910925865691	BGP307 LED54/830 II DM11 SRT C10	IK08	Philips standard surge protection level
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	IK08	Philips standard surge protection level
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	IK08	Philips standard surge protection level
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	IK08	Philips standard surge protection level
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	IK08	Philips standard surge protection level
910925865696	BGP307 LED18/740 II DM11 SR C10	IK08	Philips standard surge protection level
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	IK08	Philips standard surge protection level
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	IK08	Philips standard surge protection level
910925865699	BGP307 LED69/740 II DM11 SR C10	IK08	Philips standard surge protection level
910925865701	BGP307 LED84/740 II DM11 SR C10	IK08	Philips standard surge protection level
910925865702	BGP307 LED99/740 II DM11 SR C10	IK08	Philips standard surge protection level
910925865703	BGP307 LED109/740 II DM11 SR C10	IK08	Philips standard surge protection level
910925865704	BGP307 LED120/740 II DM11 SR C10	IK08	Philips standard surge protection level
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	IK08	Philips standard surge protection level
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	IK08	Philips standard surge protection level
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	IK08	Philips standard surge protection level
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	IK08	Philips standard surge protection level
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	IK08	Philips standard surge protection level
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	IK08	Philips standard surge protection level
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	IK08	Philips standard surge protection level

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	IK08	Philips standard surge protection level
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	IK08	Philips standard surge protection level
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	IK08	Philips standard surge protection level
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	IK08	Philips standard surge protection level
910925865716	BGP307 LED45/830 II DM11 CLL SR C10	IK08	Philips standard surge protection level
910925865717	BGP307 LED35/830 II DM11 CLL DDF1 SR C10	IK08	Philips standard surge protection level
910925865718	BGP307 LED45/830 II DM11 CLL DDF1 SR C10	IK08	Philips standard surge protection level
910925865719	BGP307 LED35/830 II DM11 CLL DDF2 SR C10	IK08	Philips standard surge protection level
910925865720	BGP307 LED45/830 II DM11 CLL DDF2 SR C10	IK08	Philips standard surge protection level
910925865721	BGP307 LED35/740 II DM11 CLL SR C10	IK08	Philips standard surge protection level

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	IK08	Philips standard surge protection level
910925865723	BGP307 LED35/740 II DM11 CLL DDF1 SR C10	IK08	Philips standard surge protection level
910925865724	BGP307 LED45/740 II DM11 CLL DDF1 SR C10	IK08	Philips standard surge protection level
910925865725	BGP307 LED35/740 II DM11 CLL DDF2 SR C10	IK08	Philips standard surge protection level
910925865726	BGP307 LED45/740 II DM11 CLL DDF2 SR C10	IK08	Philips standard surge protection level
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	IK08	Philips standard surge protection level
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	IK08	Philips standard surge protection level
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	IK08	Philips standard surge protection level
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	IK08	Philips standard surge protection level

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925864560	BGP307 LED25/740 I DM 48/60S	No
910925864561	BGP307 LED30/740 I DM 48/60S	No
910925864562	BGP307 LED35/740 I DM 48/60S	No
910925864563	BGP307 LED40/740 I DM 48/60S	No
910925864564	BGP307 LED45/740 I DM 48/60S	No
910925864565	BGP307 LED54/740 I DM 48/60S	No
910925864566	BGP307 LED69/740 I DM 48/60S	No
910925864567	BGP307 LED84/740 I DM 48/60S	No
910925864568	BGP307 LED99/740 I DM 48/60S	No
910925864569	BGP307 LED109/740 I DM 48/60S	No
910925864572	BGP307 LED25/740 II DM 48/60S	No
910925864573	BGP307 LED30/740 II DM 48/60S	No
910925864574	BGP307 LED35/740 II DM 48/60S	No
910925864575	BGP307 LED40/740 II DM 48/60S	No
910925864576	BGP307 LED45/740 II DM 48/60S	No
910925864577	BGP307 LED54/740 II DM 48/60S	No
910925864578	BGP307 LED69/740 II DM 48/60S	No
910925864579	BGP307 LED84/740 II DM 48/60S	No
910925864580	BGP307 LED99/740 II DM 48/60S	No
910925864581	BGP307 LED109/740 II DM 48/60S	No
910925865125	BGP307 LED25/740 I DM DDF27 D18 48/60S	Yes
910925865126	BGP307 LED69/740 I DM DDF27 D18 48/60S	Yes
910925865127	BGP307 LED84/740 I DM DDF27 D18 48/60S	Yes
910925865128	BGP307 LED99/740 I DM DDF27 D18 48/60S	Yes
910925865375	BGP307 LED18/830 II DM11 C10	Yes

Order Code	Full Product Name	Dimmable
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05Z1Z1-	Yes
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05Z1Z1-	Yes
910925865378	BGP307 LED54/740 II DM11 C10	Yes
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	Yes
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	Yes
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	Yes
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	Yes
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	Yes
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	No
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Yes
910925865746	BGP307 LED12-4S/830 II DM10 MSP CLO-LS-8	Yes
910925865748	BGP307 LED25-4S/830 II DM10 MSP CLO-LS-8	Yes
910925868754	BGP307 LED25/740 II DM MSP CLO-LS-8 D18	Yes

Order Code	Full Product Name	Dimmable
910925868755	BGP307 LED35/740 II DM MSP CLO-LS-8 D18	Yes
910925868756	BGP307 LED45/740 II DM MSP CLO-LS-8 D18	Yes
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	No
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	No
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	No
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	No
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	No
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	No
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	No
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	No
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	No
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	No
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	No
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	No
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	No
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	No
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	No
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	No
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	No
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	No
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	No
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	No
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	No
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	No
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	No
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	No
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	Yes
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	Yes
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	Yes
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	Yes
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	Yes
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	Yes
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	No
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	No
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	No
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	No
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	Yes
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	Yes
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	Yes
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	Yes
910925865206	BGP307 LED54/740 II DM11 SR C10	Yes
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	Yes
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	Yes
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	Yes
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	Yes
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	Yes
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	Yes
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	Yes
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	Yes
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes

Order Code	Full Product Name	Dimmable
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	Yes
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	Yes
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	Yes
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	Yes
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Yes
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	Yes
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	Yes
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	Yes
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	Yes
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	Yes
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Yes
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Yes
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Yes
910925865352	BGP307 LED35/740 II DM11 CLL C10	No
910925865374	BGP307 LED45/740 II DM11 CLL C10	No
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865405	BGP307 LED69/740 II DM11 C10	Yes
910925865406	BGP307 LED84/740 II DM11 C10	Yes
910925865407	BGP307 LED99/740 II DM11 C10	Yes
910925865408	BGP307 LED109/740 II DM11 C10	Yes
910925865409	BGP307 LED120/740 II DM11 C10	Yes

Order Code	Full Product Name	Dimmable
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Yes
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Yes
910925865419	BGP307 LED25/740 II DM11 CLL C10	Yes
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Yes
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	Yes
910925865690	BGP307 LED18/830 II DM11 SR C10	Yes
910925865691	BGP307 LED54/830 II DM11 SRT C10	Yes
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	Yes
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	Yes
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	Yes
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	Yes
910925865696	BGP307 LED18/740 II DM11 SR C10	Yes
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	Yes
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	Yes
910925865699	BGP307 LED69/740 II DM11 SR C10	Yes
910925865701	BGP307 LED84/740 II DM11 SR C10	Yes
910925865702	BGP307 LED99/740 II DM11 SR C10	Yes
910925865703	BGP307 LED109/740 II DM11 SR C10	Yes
910925865704	BGP307 LED120/740 II DM11 SR C10	Yes

Order Code	Full Product Name	Dimmable
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	Yes
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	Yes
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	Yes
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	Yes
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	Yes
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	Yes
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	Yes
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	Yes
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	Yes
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	Yes
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	Yes
910925865716	BGP307 LED45/830 II DM11 CLL SR C10	Yes
910925865717	BGP307 LED35/830 II DM11 CLL DDF1 SR C10	Yes
910925865718	BGP307 LED45/830 II DM11 CLL DDF1 SR C10	Yes
910925865719	BGP307 LED35/830 II DM11 CLL DDF2 SR C10	Yes
910925865720	BGP307 LED45/830 II DM11 CLL DDF2 SR C10	Yes
910925865721	BGP307 LED35/740 II DM11 CLL SR C10	Yes
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	Yes
910925865723	BGP307 LED35/740 II DM11 CLL DDF1 SR C10	Yes
910925865724	BGP307 LED45/740 II DM11 CLL DDF1 SR C10	Yes
910925865725	BGP307 LED35/740 II DM11 CLL DDF2 SR C10	Yes
910925865726	BGP307 LED45/740 II DM11 CLL DDF2 SR C10	Yes
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	No
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	No
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	No
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	No

General Information (1/2)

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925864560	BGP307 LED25/740 I DM 48/60S	42° x 44°	-	740 neutral white	LED25
910925864561	BGP307 LED30/740 I DM 48/60S	42° x 44°	-	740 neutral white	LED30
910925864562	BGP307 LED35/740 I DM 48/60S	42° x 44°	-	740 neutral white	LED35
910925864563	BGP307 LED40/740 I DM 48/60S	42° x 44°	-	740 neutral white	LED40
910925864564	BGP307 LED45/740 I DM 48/60S	42° x 44°	-	740 neutral white	LED45
910925864565	BGP307 LED54/740 I DM 48/60S	42° x 44°	-	740 neutral white	LED54

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925864566	BGP307 LED69/740 I DM 48/60S	42° x 44°	-	740 neutral white	LED69
910925864567	BGP307 LED84/740 I DM 48/60S	42° x 44°	-	740 neutral white	LED84
910925864568	BGP307 LED99/740 I DM 48/60S	42° x 44°	-	740 neutral white	LED99
910925864569	BGP307 LED109/740 I DM 48/60S	42° x 44°	-	740 neutral white	LED109
910925864572	BGP307 LED25/740 II DM 48/60S	42° x 44°	-	740 neutral white	LED25
910925864573	BGP307 LED30/740 II DM 48/60S	42° x 44°	-	740 neutral white	LED30

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925864574	BGP307 LED35/740 II DM 48/60S	42° x 44°	-	740 neutral white	LED35
910925864575	BGP307 LED40/740 II DM 48/60S	42° x 44°	-	740 neutral white	LED40
910925864576	BGP307 LED45/740 II DM 48/60S	42° x 44°	-	740 neutral white	LED45
910925864577	BGP307 LED54/740 II DM 48/60S	42° x 44°	-	740 neutral white	LED54
910925864578	BGP307 LED69/740 II DM 48/60S	42° x 44°	-	740 neutral white	LED69
910925864579	BGP307 LED84/740 II DM 48/60S	42° x 44°	-	740 neutral white	LED84
910925864580	BGP307 LED99/740 II DM 48/60S	42° x 44°	-	740 neutral white	LED99
910925864581	BGP307 LED109/740 II DM 48/60S	42° x 44°	-	740 neutral white	LED109
910925865125	BGP307 LED25/740 I DM DDF27 D18 48/60S	42° x 44°	-	740 neutral white	LED25
910925865126	BGP307 LED69/740 I DM DDF27 D18 48/60S	42° x 44°	-	740 neutral white	LED69
910925865127	BGP307 LED84/740 I DM DDF27 D18 48/60S	42° x 44°	-	740 neutral white	LED84
910925865128	BGP307 LED99/740 I DM DDF27 D18 48/60S	42° x 44°	-	740 neutral white	LED99
910925865375	BGP307 LED18/830 II DM11 C10	160° - 42° x 54°	-	830 warm white	LED18
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	-	830 warm white	LED35
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	-	830 warm white	LED45
910925865378	BGP307 LED54/740 II DM11 C10	160° - 42° x 54°	-	740 neutral white	LED54
910925865379	BGP307 LED18-4S/830 II	160° - 42° x 54°	-	830 warm white	LED18

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925865380	DM11 CLO-DDF1 D18 BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	830 warm white	LED25
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	830 warm white	LED35
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	830 warm white	LED45
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	830 warm white	LED54
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	830 warm white	LED18
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	830 warm white	LED25
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	830 warm white	LED35
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	830 warm white	LED45
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	830 warm white	LED54
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	-	740 neutral white	LED18
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	-	740 neutral white	LED25
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	-	740 neutral white	LED35
910925865392	BGP307 LED45-4S/740 II	160° - 42° x 54°	-	740 neutral white	LED45

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
	DM11 CLL CLO S05Z				
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	-	740	LED54
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	740	LED18
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	740	LED25
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	-	740	LED54
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	160° - 42° x 54°	-	740	LED130
910925865746	BGP307 LED12-4S/830 II DM10 MSP CLO-LS-8	157° - 33° x 55°	Marine salt protected coating	830 warm white	LED12
910925865748	BGP307 LED25-4S/830 II DM10 MSP CLO-LS-8	157° - 33° x 55°	Marine salt protected coating	830 warm white	LED25
910925868754	BGP307 LED25/740 II DM MSP CLO-LS-8 D18	42° x 44°	-	740	LED25
910925868755	BGP307 LED35/740 II DM MSP CLO-LS-8 D18	42° x 44°	-	740	LED35
910925868756	BGP307 LED45/740 II DM MSP CLO-LS-8 D18	42° x 44°	-	740	LED45
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED18
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED25
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED30
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED35

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED40
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED45
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED54
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED69
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED84
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED99
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED109
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	154° - 31° x 54°	-	740	LED120
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740	LED18
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740	LED25
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740	LED30
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740	LED35
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740	LED40
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	154° - 31° x 54°	-	740	LED45
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740	LED54
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740	LED69

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740 neutral white	LED84
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740 neutral white	LED99
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740 neutral white	LED109
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	154° - 31° x 54°	-	740 neutral white	LED120
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	-	740 neutral white	LED18
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	-	740 neutral white	LED30
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	-	740 neutral white	LED35
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	-	740 neutral white	LED54
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	-	740 neutral white	LED69
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	154° - 31° x 54°	-	740 neutral white	LED120
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	160° - 42° x 54°	-	740 neutral white	LED18
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	160° - 42° x 54°	-	740 neutral white	LED35
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	160° - 42° x 54°	-	740 neutral white	LED69
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	160° - 42° x 54°	-	740 neutral white	LED120

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	160° - 42° x 54°	-	830 warm white	LED25
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	160° - 42° x 54°	-	830 warm white	LED25
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	160° - 42° x 54°	-	830 warm white	LED25
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	160° - 42° x 54°	-	740 neutral white	LED25
910925865206	BGP307 LED54/740 II DM11 SR C10	160° - 42° x 54°	-	740 neutral white	LED54
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	160° - 42° x 54°	-	740 neutral white	LED25
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	160° - 42° x 54°	-	740 neutral white	LED54
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	160° - 42° x 54°	-	740 neutral white	LED25
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	-	830 warm white	LED18
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	-	830 warm white	LED25
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	-	830 warm white	LED35
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	-	830 warm white	LED45
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	-	830 warm white	LED54
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	830 warm white	LED18
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	830 warm white	LED25
910925865217	BGP307 LED35-4S/830 II	160° - 42° x 54°	-	830 warm white	LED35

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
	DM11 CLO-DDF1 D18				
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54° -		830 warm white	LED45
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54° -		830 warm white	LED54
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54° -		830 warm white	LED18
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54° -		830 warm white	LED25
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54° -		830 warm white	LED35
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54° -		830 warm white	LED45
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54° -		830 warm white	LED54
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	160° - 42° x 54° -		740 neutral white	LED18
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	160° - 42° x 54° -		740 neutral white	LED25
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	160° - 42° x 54° -		740 neutral white	LED35
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	160° - 42° x 54° -		740 neutral white	LED45
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	160° - 42° x 54° -		740 neutral white	LED54
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54° -		740 neutral white	LED18

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54° -		740 neutral white	LED25
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54° -		740 neutral white	LED35
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54° -		740 neutral white	LED45
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54° -		740 neutral white	LED54
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54° -		740 neutral white	LED18
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54° -		740 neutral white	LED25
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54° -		740 neutral white	LED35
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54° -		740 neutral white	LED45
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54° -		740 neutral white	LED54
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	160° - 42° x 54° -		740 neutral white	LED69
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	160° - 42° x 54° -		740 neutral white	LED84
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	160° - 42° x 54° -		740 neutral white	LED99
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	160° - 42° x 54° -		740 neutral white	LED109

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	-	740	LED120
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	740	LED69
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	740	LED84
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	740	LED99
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	-	740	LED109
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	-	740	LED120
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740	LED69
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740	LED84
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740	LED99
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	160° - 42° x 54°	-	740	LED109
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	160° - 42° x 54°	-	740	LED120
910925865352	BGP307 LED35/740 II DM11 CLL C10	-	-	740	LED35
910925865374	BGP307 LED45/740 II DM11 CLL C10	-	-	740	LED45
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	740	LED35

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	740	LED45
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	740	LED54
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740	LED18
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740	LED25
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740	LED35
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740	LED45
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740	LED54
910925865405	BGP307 LED69/740 II DM11 C10	160° - 42° x 54°	-	740	LED69
910925865406	BGP307 LED84/740 II DM11 C10	160° - 42° x 54°	-	740	LED84
910925865407	BGP307 LED99/740 II DM11 C10	160° - 42° x 54°	-	740	LED99
910925865408	BGP307 LED109/740 II DM11 C10	160° - 42° x 54°	-	740	LED109
910925865409	BGP307 LED120/740 II DM11 C10	160° - 42° x 54°	-	740	LED120
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	740	LED69
910925865411	BGP307 LED84-4S/740 II	160° - 42° x 54°	-	740	LED84

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
	DM11 CLO-DDF1 D18				
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	-	740 neutral white	LED99
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	-	740 neutral white	LED109
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	-	740 neutral white	LED120
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740 neutral white	LED69
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740 neutral white	LED84
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	-	740 neutral white	LED99
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	160° - 42° x 54°	-	740 neutral white	LED109
910925865419	BGP307 LED25/740 II DM11 CLL C10	61° x 150°	-	740 neutral white	LED25
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	160° - 42° x 54°	-	740 neutral white	LED120
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	160° - 42° x 54°	-	740 neutral white	LED54
910925865690	BGP307 LED18/830 II DM11 SR C10	160° - 42° x 54°	-	830 warm white	LED18
910925865691	BGP307 LED54/830 II DM11 SRT C10	160° - 42° x 54°	-	830 warm white	LED54
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	160° - 42° x 54°	-	830 warm white	LED18
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	160° - 42° x 54°	-	830 warm white	LED54
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	160° - 42° x 54°	-	830 warm white	LED18

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	160° - 42° x 54°	-	830 warm white	LED54
910925865696	BGP307 LED18/740 II DM11 SR C10	160° - 42° x 54°	-	740 neutral white	LED18
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	160° - 42° x 54°	-	740 neutral white	LED18
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	160° - 42° x 54°	-	740 neutral white	LED18
910925865699	BGP307 LED69/740 II DM11 SR C10	160° - 42° x 54°	-	740 neutral white	LED69
910925865701	BGP307 LED84/740 II DM11 SR C10	160° - 42° x 54°	-	740 neutral white	LED84
910925865702	BGP307 LED99/740 II DM11 SR C10	160° - 42° x 54°	-	740 neutral white	LED99
910925865703	BGP307 LED109/740 II DM11 SR C10	160° - 42° x 54°	-	740 neutral white	LED109
910925865704	BGP307 LED120/740 II DM11 SR C10	160° - 42° x 54°	-	740 neutral white	LED120
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	160° - 42° x 54°	-	740 neutral white	LED69
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	160° - 42° x 54°	-	740 neutral white	LED84
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	160° - 42° x 54°	-	740 neutral white	LED99
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	160° - 42° x 54°	-	740 neutral white	LED109
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	160° - 42° x 54°	-	740 neutral white	LED120
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	160° - 42° x 54°	-	740 neutral white	LED69
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	160° - 42° x 54°	-	740 neutral white	LED84

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	160° - 42° x 54°	-	740 neutral white	LED99
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	160° - 42° x 54°	-	740 neutral white	LED109
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	160° - 42° x 54°	-	740 neutral white	LED120
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	160° - 42° x 54°	-	830 warm white	LED35
910925865716	BGP307 LED45/830 II DM11 CLL SR C10	160° - 42° x 54°	-	830 warm white	LED45
910925865717	BGP307 LED35/830 II DM11 CLL DDF1 SR C10	160° - 42° x 54°	-	830 warm white	LED35
910925865718	BGP307 LED45/830 II DM11 CLL DDF1 SR C10	160° - 42° x 54°	-	830 warm white	LED45
910925865719	BGP307 LED35/830 II DM11 CLL DDF2 SR C10	160° - 42° x 54°	-	830 warm white	LED35
910925865720	BGP307 LED45/830 II DM11 CLL DDF2 SR C10	160° - 42° x 54°	-	830 warm white	LED45
910925865721	BGP307 LED35/740 II DM11 CLL SR C10	160° - 42° x 54°	-	740 neutral white	LED35

Order Code	Full Product Name	Luminaire light		Light source color	Lamp family code
		beam spread	Coating		
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	160° - 42° x 54°	-	740 neutral white	LED45
910925865723	BGP307 LED35/740 II DM11 CLL DDF1 SR C10	160° - 42° x 54°	-	740 neutral white	LED35
910925865724	BGP307 LED45/740 II DM11 CLL DDF1 SR C10	160° - 42° x 54°	-	740 neutral white	LED45
910925865725	BGP307 LED35/740 II DM11 CLL DDF2 SR C10	160° - 42° x 54°	-	740 neutral white	LED35
910925865726	BGP307 LED45/740 II DM11 CLL DDF2 SR C10	160° - 42° x 54°	-	740 neutral white	LED45
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	-	-	740 neutral white	LED45
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	-	-	740 neutral white	LED69
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	152° - 25° x 66°	-	740 neutral white	LED69
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	152° - 25° x 66°	-	740 neutral white	LED84

General Information (2/2)

Order Code	Full Product Name	Lamp		Optical element	Service tag
		version	Optic type		
910925864560	BGP307 LED25/740 I DM 48/60S	-	Distribution medium	-	Yes
910925864561	BGP307 LED30/740 I DM 48/60S	-	Distribution medium	-	Yes
910925864562	BGP307 LED35/740 I DM 48/60S	-	Distribution medium	-	-
910925864563	BGP307 LED40/740 I DM 48/60S	-	Distribution medium	-	-
910925864564	BGP307 LED45/740 I DM 48/60S	-	Distribution medium	-	-
910925864565	BGP307 LED54/740 I DM 48/60S	-	Distribution medium	-	-
910925864566	BGP307 LED69/740 I DM 48/60S	-	Distribution medium	-	-

Order Code	Full Product Name	Lamp		Optical element	Service tag
		version	Optic type		
910925864567	BGP307 LED84/740 I DM 48/60S	-	Distribution medium	-	-
910925864568	BGP307 LED99/740 I DM 48/60S	-	Distribution medium	-	-
910925864569	BGP307 LED109/740 I DM 48/60S	-	Distribution medium	-	-
910925864572	BGP307 LED25/740 II DM 48/60S	-	Distribution medium	-	Yes
910925864573	BGP307 LED30/740 II DM 48/60S	-	Distribution medium	-	-
910925864574	BGP307 LED35/740 II DM 48/60S	-	Distribution medium	-	-
910925864575	BGP307 LED40/740 II DM 48/60S	-	Distribution medium	-	Yes

Order Code	Full Product Name	Lamp version	Optic type	Optical element	Service tag
910925864576	BGP307 LED45/740 II DM 48/60S	-	Distribution medium	-	-
910925864577	BGP307 LED54/740 II DM 48/60S	-	Distribution medium	-	-
910925864578	BGP307 LED69/740 II DM 48/60S	-	Distribution medium	-	-
910925864579	BGP307 LED84/740 II DM 48/60S	-	Distribution medium	-	-
910925864580	BGP307 LED99/740 II DM 48/60S	-	Distribution medium	-	-
910925864581	BGP307 LED109/740 II DM 48/60S	-	Distribution medium	Vertical diffuser element	-
910925865125	BGP307 LED25/740 I DM DDF27 D18 48/60S	-	Distribution medium	-	Yes
910925865126	BGP307 LED69/740 I DM DDF27 D18 48/60S	-	Distribution medium	-	-
910925865127	BGP307 LED84/740 I DM DDF27 D18 48/60S	-	Distribution medium	-	-
910925865128	BGP307 LED99/740 I DM DDF27 D18 48/60S	-	Distribution medium	-	-
910925865375	BGP307 LED18/830 II DM11 C10	-	Distribution medium 11	-	Yes
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05Z1Z1-	-	Distribution medium 11	-	-
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05Z1Z1-	-	Distribution medium 11	-	-
910925865378	BGP307 LED54/740 II DM11 C10	-	Distribution medium 11	-	-
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	Yes
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-

Order Code	Full Product Name	Lamp version	Optic type	Optical element	Service tag
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	Yes
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	4S	Distribution medium 11	-	-
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	-	Distribution medium 11	-	Yes
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	-	Distribution medium 11	-	Yes
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	-	Distribution medium 11	-	-
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	-	Distribution medium 11	-	-
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	-	Distribution medium 11	-	-
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	4S	Distribution medium 11	-	-
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	4S	Distribution medium 11	-	Yes
910925865746	BGP307 LED12-4S/830 II DM10 MSP CLO-LS-8	4S	Distribution medium 10	-	Yes
910925865748	BGP307 LED25-4S/830 II DM10 MSP CLO-LS-8	4S	Distribution medium 10	-	Yes
910925868754	BGP307 LED25/740 II DM MSP CLO-LS-8 D18	-	Distribution extra wide 10	-	Yes

Order Code	Full Product Name	Lamp version	Optic type	Optical element	Service tag
910925868755	BGP307 LED35/740 II DM MSP CLO-LS-8 D18	-	Distribution extra wide 10	-	Yes
910925868756	BGP307 LED45/740 II DM MSP CLO-LS-8 D18	-	Distribution extra wide 10	-	Yes
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	-	Distribution medium 50	Diffuser element	-
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	-	Distribution medium 50	-	-
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	-	Distribution medium 50	-	Yes
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	-	Distribution medium 50	-	Yes
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	-	Distribution medium 50	-	-

Order Code	Full Product Name	Lamp version	Optic type	Optical element	Service tag
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	-	Distribution medium 50	-	-
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	4S	Distribution medium 50	-	-
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	-	Distribution medium 50	-	-
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	-	Distribution medium 50	-	-
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	-	Distribution medium 50	-	-
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	-	Distribution medium 50	-	-
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	-	Distribution medium 50	-	-
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	-	Distribution medium 50	-	-
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	-	Distribution medium 50	-	-
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	-	Distribution medium 50	-	Yes
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	-	Distribution medium 50	-	-
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	-	Distribution medium 50	-	-
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	-	Distribution medium 50	-	-
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	-	Distribution medium 50	-	-
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	-	Distribution medium 50	-	-
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	-	Distribution medium 11	-	Yes
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	-	Distribution medium 11	-	-

Order Code	Full Product Name	Lamp version	Optic type	Optical element	Service tag
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	-	Distribution medium 11	-	-
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	-	Distribution medium 11	Prismatic diamond effect element	-
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	-	Distribution medium 11	-	-
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	-	Distribution medium 11	-	-
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	-	Distribution medium 11	-	Yes
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	-	Distribution medium 11	-	Yes
910925865206	BGP307 LED54/740 II DM11 SR C10	-	Distribution medium 11	-	-
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	-	Distribution medium 11	-	Yes
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	-	Distribution medium 11	-	-
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	-	Distribution medium 11	-	Yes
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	-	Distribution medium 11	-	Yes
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	Yes
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	Yes
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-

Order Code	Full Product Name	Lamp version	Optic type	Optical element	Service tag
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	Yes
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	-	Distribution medium 11	-	Yes
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	Yes
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-

Order Code	Full Product Name	Lamp version	Optic type	Optical element	Service tag
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	Yes
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	-	Distribution medium 11	-	-
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	-	Distribution medium 11	-	Yes
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	-	Distribution medium 11	-	-
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	-	Distribution medium 11	Diffuser element	-
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-

Order Code	Full Product Name	Lamp version	Optic type	Optical element	Service tag
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	-	Distribution medium 11	-	-
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	-	Distribution medium 11	-	Yes
910925865352	BGP307 LED35/740 II DM11 CLL C10	-	Distribution medium 11	-	Yes
910925865374	BGP307 LED45/740 II DM11 CLL C10	-	Distribution medium 11	-	Yes
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865405	BGP307 LED69/740 II DM11 C10	-	Distribution medium 11	-	-
910925865406	BGP307 LED84/740 II DM11 C10	-	Distribution medium 11	-	-
910925865407	BGP307 LED99/740 II DM11 C10	-	Distribution medium 11	-	-
910925865408	BGP307 LED109/740 II DM11 C10	-	Distribution medium 11	Diffuser element	-
910925865409	BGP307 LED120/740 II DM11 C10	-	Distribution medium 11	Diffuser element	-
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-

Order Code	Full Product Name	Lamp version	Optic type	Optical element	Service tag
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	-	Distribution medium 11	-	-
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	-	Distribution medium 11	-	-
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	-	Distribution medium 11	-	-
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	-	Distribution medium 11	-	-
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	-	Distribution medium 11	Prismatic circle effect element	-
910925865419	BGP307 LED25/740 II DM11 CLL C10	-	Distribution medium 11	-	Yes
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	-	Distribution medium 11	-	-
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	-	Distribution medium 11	-	-
910925865690	BGP307 LED18/830 II DM11 SR C10	-	Distribution medium 11	-	Yes
910925865691	BGP307 LED54/830 II DM11 SRT C10	-	Distribution medium 11	-	-
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	-	Distribution medium 11	-	Yes
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	-	Distribution medium 11	-	-
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	-	Distribution medium 11	-	-
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	-	Distribution medium 11	-	-
910925865696	BGP307 LED18/740 II DM11 SR C10	-	Distribution medium 11	-	Yes
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	-	Distribution medium 11	-	Yes
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	-	Distribution medium 11	-	Yes

Order Code	Full Product Name	Lamp version	Optic type	Optical element	Service tag
910925865699	BGP307 LED69/740 II DM11 SR C10	-	Distribution medium 11	-	-
910925865701	BGP307 LED84/740 II DM11 SR C10	-	Distribution medium 11	-	-
910925865702	BGP307 LED99/740 II DM11 SR C10	-	Distribution medium 11	-	-
910925865703	BGP307 LED109/740 II DM11 SR C10	-	Distribution medium 11	Diffuser element	-
910925865704	BGP307 LED120/740 II DM11 SR C10	-	Distribution medium 11	-	-
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	-	Distribution medium 11	-	-
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	-	Distribution medium 11	-	-
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	-	Distribution medium 11	-	-
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	-	Distribution medium 11	Vertical diffuser element	-
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	-	Distribution medium 11	-	-
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	-	Distribution medium 11	-	-
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	-	Distribution medium 11	-	-
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	-	Distribution medium 11	-	-
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	-	Distribution medium 11	-	-
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	-	Distribution medium 11	-	-
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	-	Distribution medium 11	-	-
910925865716	BGP307 LED45/830 II DM11 CLL SR C10	-	Distribution medium 11	-	-
910925865717	BGP307 LED35/830 II DM11 CLL DDF1 SR C10	-	Distribution medium 11	-	-
910925865718	BGP307 LED45/830 II DM11 CLL DDF1 SR C10	-	Distribution medium 11	-	-
910925865719	BGP307 LED35/830 II DM11 CLL DDF2 SR C10	-	Distribution medium 11	-	-
910925865720	BGP307 LED45/830 II DM11 CLL DDF2 SR C10	-	Distribution medium 11	-	-
910925865721	BGP307 LED35/740 II DM11 CLL SR C10	-	Distribution medium 11	-	-
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	-	Distribution medium 11	-	-

Order Code	Full Product Name	Lamp		Optical element	Service tag
		version	Optic type		
910925865723	BGP307 LED35/740 II DM11 CLL DDF1 SR C10	-	Distribution medium 11	-	-
910925865724	BGP307 LED45/740 II DM11 CLL DDF1 SR C10	-	Distribution medium 11	-	-
910925865725	BGP307 LED35/740 II DM11 CLL DDF2 SR C10	-	Distribution medium 11	-	-
910925865726	BGP307 LED45/740 II DM11 CLL DDF2 SR C10	-	Distribution medium 11	-	-

Order Code	Full Product Name	Lamp		Optical element	Service tag
		version	Optic type		
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	-	Distribution extra wide 10	-	Yes
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	-	Distribution extra wide 10	-	Yes
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	-	Distribution extra wide 10	-	Yes
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	-	Distribution extra wide 10	-	Yes

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color	Initial
			Rendering Index	luminous flux
910925864560	BGP307 LED25/740 I DM 48/60S	4000 K	70	2250 lm
910925864561	BGP307 LED30/740 I DM 48/60S	4000 K	70	2670 lm
910925864562	BGP307 LED35/740 I DM 48/60S	4000 K	70	3115 lm
910925864563	BGP307 LED40/740 I DM 48/60S	4000 K	70	3560 lm
910925864564	BGP307 LED45/740 I DM 48/60S	4000 K	70	4005 lm
910925864565	BGP307 LED54/740 I DM 48/60S	4000 K	70	4752 lm
910925864566	BGP307 LED69/740 I DM 48/60S	4000 K	70	6020 lm
910925864567	BGP307 LED84/740 I DM 48/60S	4000 K	70	7308 lm
910925864568	BGP307 LED99/740 I DM 48/60S	4000 K	70	8600 lm
910925864569	BGP307 LED109/740 I DM 48/60S	4000 K	70	9460 lm
910925864572	BGP307 LED25/740 II DM 48/60S	4000 K	70	2250 lm
910925864573	BGP307 LED30/740 II DM 48/60S	4000 K	70	2670 lm
910925864574	BGP307 LED35/740 II DM 48/60S	4000 K	70	3115 lm
910925864575	BGP307 LED40/740 II DM 48/60S	4000 K	70	3560 lm
910925864576	BGP307 LED45/740 II DM 48/60S	4000 K	70	4005 lm
910925864577	BGP307 LED54/740 II DM 48/60S	4000 K	70	4752 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color	Initial
			Rendering Index	luminous flux
910925864578	BGP307 LED69/740 II DM 48/60S	4000 K	70	6020 lm
910925864579	BGP307 LED84/740 II DM 48/60S	4000 K	70	7308 lm
910925864580	BGP307 LED99/740 II DM 48/60S	4000 K	70	8600 lm
910925864581	BGP307 LED109/740 II DM 48/60S	4000 K	70	9460 lm
910925865125	BGP307 LED25/740 I DM DDF27 D18 48/60S	4000 K	70	2250 lm
910925865126	BGP307 LED69/740 I DM DDF27 D18 48/60S	4000 K	70	6020 lm
910925865127	BGP307 LED84/740 I DM DDF27 D18 48/60S	4000 K	70	7308 lm
910925865128	BGP307 LED99/740 I DM DDF27 D18 48/60S	4000 K	70	8600 lm
910925865375	BGP307 LED18/830 II DM11 C10	3000 K	80	1522.5 lm
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05Z1Z1-	3000 K	80	2958 lm
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05Z1Z1-	3000 K	80	3741 lm
910925865378	BGP307 LED54/740 II DM11 C10	4000 K	70	4524 lm
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	1522.5 lm
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2088 lm
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2958 lm
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3741 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	4524 lm
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	1522.5 lm
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	2088 lm
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	2958 lm
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	3741 lm
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	4524 lm
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	4000 K	70	1522.5 lm
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	4000 K	70	2088 lm
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	4000 K	70	2958 lm
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	4000 K	70	3828 lm
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	4000 K	70	4524 lm
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	1522.5 lm
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2088 lm
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	4000 K	70	4524 lm
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	4000 K	70	10920 lm
910925865746	BGP307 LED12-4S/830 II DM10 MSP CLO-LS-8	3000 K	80	1000.5 lm
910925865748	BGP307 LED25-4S/830 II DM10 MSP CLO-LS-8	3000 K	80	2064 lm
910925868754	BGP307 LED25/740 II DM MSP CLO-LS-8 D18	4000 K	70	2371 lm
910925868755	BGP307 LED35/740 II DM MSP CLO-LS-8 D18	4000 K	70	3233 lm
910925868756	BGP307 LED45/740 II DM MSP CLO-LS-8 D18	4000 K	70	4118 lm
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	4000 K	70	1584 lm
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	4000 K	70	2175 lm
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	4000 K	70	2610 lm
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	4000 K	70	3080 lm
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	4000 K	70	3520 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	4000 K	70	3960 lm
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	4000 K	70	4698 lm
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	4000 K	70	6160 lm
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	4000 K	70	7308 lm
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	4000 K	70	8600 lm
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	4000 K	70	9460 lm
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	4000 K	70	10200 lm
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	4000 K	70	1584 lm
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	4000 K	70	2175 lm
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	4000 K	70	2610 lm
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	4000 K	70	3080 lm
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	4000 K	70	3520 lm
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	4000 K	70	3960 lm
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	4000 K	70	4698 lm
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	4000 K	70	6160 lm
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	4000 K	70	7308 lm
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	4000 K	70	8600 lm
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	4000 K	70	9460 lm
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	4000 K	70	10200 lm
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	4000 K	70	1584 lm
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	4000 K	70	2610 lm
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	4000 K	70	3080 lm
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	4000 K	70	4698 lm
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	4000 K	70	6160 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	4000 K	70	10200 lm
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	4000 K	70	1566 lm
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	4000 K	70	3045 lm
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	4000 K	70	6090 lm
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	4000 K	70	10200 lm
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	3000 K	80	2088 lm
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	3000 K	80	2088 lm
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	3000 K	80	2088 lm
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	4000 K	70	2088 lm
910925865206	BGP307 LED54/740 II DM11 SR C10	4000 K	70	4524 lm
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	4000 K	70	2088 lm
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	4000 K	70	4524 lm
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	4000 K	70	2088 lm
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	3000 K	80	1522.5 lm
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	3000 K	80	2088 lm
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	3000 K	80	2958 lm
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	3000 K	80	3741 lm
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	3000 K	80	4524 lm
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	1522.5 lm
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2088 lm
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2958 lm
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3741 lm
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	4524 lm
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	1522.5 lm
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	2088 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	2958 lm
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	3741 lm
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	4524 lm
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	4000 K	70	1522.5 lm
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	4000 K	70	2088 lm
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	4000 K	70	2958 lm
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	4000 K	70	3828 lm
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	4000 K	70	4524 lm
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	1522.5 lm
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2088 lm
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2958 lm
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3828 lm
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	4524 lm
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	1522.5 lm
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	2088 lm
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	2958 lm
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	3828 lm
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	4524 lm
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	4000 K	70	5916 lm
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	4000 K	70	7134 lm
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	4000 K	70	8256 lm
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	4000 K	70	9030 lm
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	4000 K	70	9775 lm
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	5916 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	7134 lm
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	8256 lm
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	9030 lm
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	9775 lm
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	5916 lm
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	7134 lm
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	8256 lm
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	4000 K	70	9030 lm
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	4000 K	70	9775 lm
910925865352	BGP307 LED35/740 II DM11 CLL C10	4000 K	70	3045 lm
910925865374	BGP307 LED45/740 II DM11 CLL C10	4000 K	70	3915 lm
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2958 lm
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3828 lm
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	4524 lm
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	1522.5 lm
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	2088 lm
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	2958 lm
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	3828 lm
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	4524 lm
910925865405	BGP307 LED69/740 II DM11 C10	4000 K	70	5916 lm
910925865406	BGP307 LED84/740 II DM11 C10	4000 K	70	7134 lm
910925865407	BGP307 LED99/740 II DM11 C10	4000 K	70	8256 lm
910925865408	BGP307 LED109/740 II DM11 C10	4000 K	70	9030 lm
910925865409	BGP307 LED120/740 II DM11 C10	4000 K	70	9775 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	5916 lm
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	7134 lm
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	8256 lm
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	9030 lm
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	9775 lm
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	5916 lm
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	7134 lm
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	8256 lm
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	4000 K	70	9030 lm
910925865419	BGP307 LED25/740 II DM11 CLL C10	3000 K	80	2175 lm
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	4000 K	70	9775 lm
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	4000 K	70	4524 lm
910925865690	BGP307 LED18/830 II DM11 SR C10	3000 K	80	1522.5 lm
910925865691	BGP307 LED54/830 II DM11 SRT C10	3000 K	80	4524 lm
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	3000 K	80	1522.5 lm
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	3000 K	80	4524 lm
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	3000 K	80	1522.5 lm
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	3000 K	80	4524 lm
910925865696	BGP307 LED18/740 II DM11 SR C10	4000 K	70	1522.5 lm
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	4000 K	70	1522.5 lm
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	4000 K	70	1522.5 lm
910925865699	BGP307 LED69/740 II DM11 SR C10	4000 K	70	5916 lm
910925865701	BGP307 LED84/740 II DM11 SR C10	4000 K	70	7134 lm
910925865702	BGP307 LED99/740 II DM11 SR C10	4000 K	70	8256 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865703	BGP307 LED109/740 II DM11 SR C10	4000 K	70	9030 lm
910925865704	BGP307 LED120/740 II DM11 SR C10	4000 K	70	9775 lm
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	4000 K	70	5916 lm
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	4000 K	70	7134 lm
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	4000 K	70	8256 lm
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	4000 K	70	9030 lm
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	4000 K	70	9775 lm
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	4000 K	70	5916 lm
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	4000 K	70	7134 lm
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	4000 K	70	8256 lm
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	4000 K	70	9030 lm
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	4000 K	70	9775 lm
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	3000 K	80	2958 lm
910925865716	BGP307 LED45/830 II DM11 CLL SR C10	3000 K	80	3741 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865717	BGP307 LED35/830 II DM11 CLL DDF1 SR C10	3000 K	80	2958 lm
910925865718	BGP307 LED45/830 II DM11 CLL DDF1 SR C10	3000 K	80	3741 lm
910925865719	BGP307 LED35/830 II DM11 CLL DDF2 SR C10	3000 K	80	2958 lm
910925865720	BGP307 LED45/830 II DM11 CLL DDF2 SR C10	3000 K	80	3741 lm
910925865721	BGP307 LED35/740 II DM11 CLL SR C10	4000 K	70	2958 lm
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	4000 K	70	3828 lm
910925865723	BGP307 LED35/740 II DM11 CLL DDF1 SR C10	4000 K	70	2958 lm
910925865724	BGP307 LED45/740 II DM11 CLL DDF1 SR C10	4000 K	70	3828 lm
910925865725	BGP307 LED35/740 II DM11 CLL DDF2 SR C10	4000 K	70	2958 lm
910925865726	BGP307 LED45/740 II DM11 CLL DDF2 SR C10	4000 K	70	3828 lm
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	4000 K	70	3780 lm
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	4000 K	70	5880 lm
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	4000 K	70	5880 lm
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	4000 K	70	6972 lm

Mechanical and Housing

Order Code	Full Product Name	Supply cable length	Color
910925864560	BGP307 LED25/740 I DM 48/60S	-	Gray
910925864561	BGP307 LED30/740 I DM 48/60S	-	Gray
910925864562	BGP307 LED35/740 I DM 48/60S	-	Gray
910925864563	BGP307 LED40/740 I DM 48/60S	-	Gray
910925864564	BGP307 LED45/740 I DM 48/60S	-	Gray
910925864565	BGP307 LED54/740 I DM 48/60S	-	Gray
910925864566	BGP307 LED69/740 I DM 48/60S	-	Gray
910925864567	BGP307 LED84/740 I DM 48/60S	-	Gray
910925864568	BGP307 LED99/740 I DM 48/60S	-	Gray
910925864569	BGP307 LED109/740 I DM 48/60S	-	Gray
910925864572	BGP307 LED25/740 II DM 48/60S	-	Gray
910925864573	BGP307 LED30/740 II DM 48/60S	-	Gray
910925864574	BGP307 LED35/740 II DM 48/60S	-	Gray
910925864575	BGP307 LED40/740 II DM 48/60S	-	Gray
910925864576	BGP307 LED45/740 II DM 48/60S	-	Gray
910925864577	BGP307 LED54/740 II DM 48/60S	-	Gray

Order Code	Full Product Name	Supply cable length	Color
910925864578	BGP307 LED69/740 II DM 48/60S	-	Gray
910925864579	BGP307 LED84/740 II DM 48/60S	-	Gray
910925864580	BGP307 LED99/740 II DM 48/60S	-	Gray
910925864581	BGP307 LED109/740 II DM 48/60S	-	Gray
910925865125	BGP307 LED25/740 I DM DDF27 D18 48/60S	-	Gray
910925865126	BGP307 LED69/740 I DM DDF27 D18 48/60S	-	Gray
910925865127	BGP307 LED84/740 I DM DDF27 D18 48/60S	-	Gray
910925865128	BGP307 LED99/740 I DM DDF27 D18 48/60S	-	Gray
910925865375	BGP307 LED18/830 II DM11 C10	-	Gray
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05Z1Z1-	-	Gray
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05Z1Z1-	-	Gray
910925865378	BGP307 LED54/740 II DM11 C10	-	Gray
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	-	Gray

Order Code	Full Product Name	Supply cable	
		length	Color
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	10 m	Gray
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05ZIZI-	-	Gray
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05ZIZI-	-	Gray
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05ZIZI-	-	Gray
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	-	Gray
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05ZIZI-	-	Gray
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	-	Aluminum
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	-	Aluminum
910925865746	BGP307 LED12-4S/830 II DM10 MSP CLO-LS-8	-	Aluminum
910925865748	BGP307 LED25-4S/830 II DM10 MSP CLO-LS-8	-	Aluminum
910925868754	BGP307 LED25/740 II DM MSP CLO-LS-8 D18	-	Gray
910925868755	BGP307 LED35/740 II DM MSP CLO-LS-8 D18	-	Gray
910925868756	BGP307 LED45/740 II DM MSP CLO-LS-8 D18	-	Gray
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	-	Gray
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	-	Gray
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	-	Gray
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	-	Gray
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	-	Gray
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	-	Gray
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	-	Gray
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	-	Gray
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	-	Gray
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	-	Gray
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	-	Gray
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	-	Gray
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	-	Gray
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	-	Gray
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	-	Gray
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	-	Gray
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	-	Gray

Order Code	Full Product Name	Supply cable	
		length	Color
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	-	Gray
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	-	Gray
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	-	Gray
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	-	Gray
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	-	Gray
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	-	Gray
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	-	Gray
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	-	Gray
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	-	Gray
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	-	Gray
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	-	Gray
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	-	Gray
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	-	Gray
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	-	Gray
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	-	Gray
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	-	Gray
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	-	Gray
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	-	Gray
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	-	Gray
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	-	Gray
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	-	Gray
910925865206	BGP307 LED54/740 II DM11 SR C10	-	Gray
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	-	Gray
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	-	Gray
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	-	Gray
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	-	Gray
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	-	Gray
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	-	Gray
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	-	Gray
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	-	Gray
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	-	Gray

Order Code	Full Product Name	Supply cable length	Color
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	-	Gray
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	-	Gray
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	-	Gray
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	-	Gray
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	-	Gray
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	-	Gray
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	-	Gray
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	-	Gray
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	-	Gray
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	-	Gray
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	-	Gray
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	-	Gray
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	-	Gray

Order Code	Full Product Name	Supply cable length	Color
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	-	Gray
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	-	Gray
910925865352	BGP307 LED35/740 II DM11 CLL C10	-	Gray
910925865374	BGP307 LED45/740 II DM11 CLL C10	-	Gray
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865405	BGP307 LED69/740 II DM11 C10	-	Gray
910925865406	BGP307 LED84/740 II DM11 C10	-	Gray
910925865407	BGP307 LED99/740 II DM11 C10	-	Gray
910925865408	BGP307 LED109/740 II DM11 C10	-	Gray
910925865409	BGP307 LED120/740 II DM11 C10	-	Gray
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	-	Gray
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	-	Gray
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	-	Gray
910925865419	BGP307 LED25/740 II DM11 CLL C10	-	Dark gray
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	-	Gray
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	-	Gray
910925865690	BGP307 LED18/830 II DM11 SR C10	-	Gray
910925865691	BGP307 LED54/830 II DM11 SRT C10	-	Gray

Order Code	Full Product Name	Supply cable	
		length	Color
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	-	Gray
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	-	Gray
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	-	Gray
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	-	Gray
910925865696	BGP307 LED18/740 II DM11 SR C10	-	Gray
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	-	Gray
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	-	Gray
910925865699	BGP307 LED69/740 II DM11 SR C10	-	Gray
910925865701	BGP307 LED84/740 II DM11 SR C10	-	Gray
910925865702	BGP307 LED99/740 II DM11 SR C10	-	Gray
910925865703	BGP307 LED109/740 II DM11 SR C10	-	Gray
910925865704	BGP307 LED120/740 II DM11 SR C10	-	Gray
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	-	Gray
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	-	Gray
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	-	Gray
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	-	Gray
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	-	Gray
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	-	Gray
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	-	Gray

Order Code	Full Product Name	Supply cable	
		length	Color
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	-	Gray
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	-	Gray
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	-	Gray
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	-	Gray
910925865716	BGP307 LED45/830 II DM11 CLL SR C10	-	Gray
910925865717	BGP307 LED35/830 II DM11 CLL DDF1 SR C10	-	Gray
910925865718	BGP307 LED45/830 II DM11 CLL DDF1 SR C10	-	Gray
910925865719	BGP307 LED35/830 II DM11 CLL DDF2 SR C10	-	Gray
910925865720	BGP307 LED45/830 II DM11 CLL DDF2 SR C10	-	Gray
910925865721	BGP307 LED35/740 II DM11 CLL SR C10	-	Gray
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	-	Gray
910925865723	BGP307 LED35/740 II DM11 CLL DDF1 SR C10	-	Gray
910925865724	BGP307 LED45/740 II DM11 CLL DDF1 SR C10	-	Gray
910925865725	BGP307 LED35/740 II DM11 CLL DDF2 SR C10	-	Gray
910925865726	BGP307 LED45/740 II DM11 CLL DDF2 SR C10	-	Gray
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	-	Gray
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	-	Gray
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	-	Gray
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	-	Gray

