



Coreline tempo Medium – For every project where light really matters

Coreline tempo medium

CoreLine tempo medium is a highly efficient range of floodlights designed for 1:1 retrofit replacement of conventional technology, while retaining the same electrical installation and poles. A limited range of options makes it easy to find the best lux-for-lux replacement. The easy-to-install CoreLine tempo medium offers lumen packages for many different application areas as well as a choice of high-performance asymmetrical and symmetrical optics. It includes a U-shaped universal mounting bracket and external quick 3-poles IP68 connector.

Benefits

- Fast payback: energy savings of 65%
- Low maintenance thanks to the long lifetime of the luminaire
- Simple to install and connect
- Robust, high-quality finish
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

Coreline tempo medium

Features

- Highly efficient: up to 130 lm/W
- Designed for 1:1 retrofit replacement of conventional technology: 150 W HID and up to 250 W HPI-T
- System flux: 8000, 12000 lm
- Long lifetime of 75Khrs L80 at Tq +25 °C
- High-performance asymmetrical and symmetrical optics
- U-shaped universal mounting bracket and external quick 3-pole IP68 connector
- High surge protection: 6 kV/8 kV
- Robust design IP66-IP68
- Compliance with: CE, ENEC, ROHS
- Options for projects : Dali control, CCT 3000K, special coating

Application

- Areas and recreational sports facilities
- Building facades
- Billboards

Specifications

Aiming possibilities from the horizontal	to °
Aiming possibilities from the vertical	to °
Ambient Temperature	-40 to +50 °C
Beam spread luminaire	69° x 25°, 9° - 41° x 102°
Main color of the Luminaire	Aluminum, gray
Connection	External connector (External connector)
Dimming	No
Driver	Power supply unit (Power supply unit)
Initial correlated color temperature	3000 K, 4000 K
Initial input power	106 W, 66 W, 72 W, 98 W
Initial LED luminaire efficacy	114, 116, 124, 126 lm/W

Initial luminous flux	12000 lm, 8000 lm
Input frequency	50 to 60 Hz
Input voltage	220 to 240 V
Inrush current (A)	53 A
Light source replaceable	No
Material	Bracket:
Material	Housing: aluminum
Material	Reflector: -
Optic	Optiflux asymmetrical axis angle 52°, symmetrical
Surge protection	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Type	BVP125
Warranty period	5 years

Versions



Coreline tempo medium - LED module 12,000 lm



Coreline tempo medium - LED module 8000 lm

Coreline tempo medium

Product details



Coreline_Tempo_Medium-
BVP125_Led120-1DPP.TIF



Coreline_Tempo_Medium-
BVP125_Led120-2DPP.TIF



Coreline_Tempo_Medium-
BVP125-1DPP.TIF



Coreline_Tempo_Medium-
BVP125-2DPP.TIF

Coreline tempo medium

Approval and Application

Mech. impact protection code	IK08
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Dimmable	No
----------	----

General Information

CE mark	CE mark
Optical cover/lens type	Flat glass
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Number of gear units	1 unit
Optical element	-
Product Family Code	BVP125

Initial Performance (IEC Compliant)

Init. Color Rendering Index	70
-----------------------------	----

Light Technical

Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Upward light output ratio	0

General Information (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
912300024001	BVP125 LED120-4S/740 OFA52	9° - 41° x 102°	740 neutral white	LED120-4S	-
912300024003	BVP125 LED120-4S/740 S	69° x 25°	740 neutral white	LED120-4S	-
912300057764	BVP125 LED120-4S/730 PSU OFA52 ALU C1KC3	9° - 41° x 102°	730 warm white	LED120	4S
912300057766	BVP125 LED120-4S/730 PSU S ALU C1KC3	69° x 25°	730 warm white	LED120	4S
912300024002	BVP125 LED80-4S/740 OFA52	9° - 41° x 102°	740 neutral white	LED80-4S	-
912300024004	BVP125 LED80-4S/740 S	69° x 25°	740 neutral white	LED80-4S	-
912300057765	BVP125 LED80-4S/730 PSU OFA52 ALU C1KC3	9° - 41° x 102°	730 warm white	LED80	4S
912300057767	BVP125 LED80-4S/730 PSU S ALU C1KC3	69° x 25°	730 warm white	LED80	4S

General Information (2/2)

Order Code	Full Product Name	Optic type	Service tag
912300024001	BVP125 LED120-4S/740 OFA52	Optiflux asymmetrical axis angle 52°	Yes
912300024003	BVP125 LED120-4S/740 S	Symmetrical	-
912300057764	BVP125 LED120-4S/730 PSU OFA52 ALU C1KC3	Optiflux asymmetrical axis angle 52°	-
912300057766	BVP125 LED120-4S/730 PSU S ALU C1KC3	Symmetrical	-

Order Code	Full Product Name	Optic type	Service tag
912300024002	BVP125 LED80-4S/740 OFA52	Optiflux asymmetrical axis angle 52°	-
912300024004	BVP125 LED80-4S/740 S	Symmetrical	-
912300057765	BVP125 LED80-4S/730 PSU OFA52 ALU C1KC3	Optiflux asymmetrical axis angle 52°	-
912300057767	BVP125 LED80-4S/730 PSU S ALU C1KC3	Symmetrical	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
912300024001	BVP125 LED120-4S/740 OFA52	4000 K	12000 lm
912300024003	BVP125 LED120-4S/740 S	4000 K	12000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
912300057764	BVP125 LED120-4S/730 PSU OFA52 ALU C1KC3	3000 K	12000 lm
912300057766	BVP125 LED120-4S/730 PSU S ALU C1KC3	3000 K	12000 lm

Coreline tempo medium

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
912300024002	BVP125 LED80-4S/740 OFA52	4000 K	8000 lm
912300024004	BVP125 LED80-4S/740 S	4000 K	8000 lm
912300057765	BVP125 LED80-4S/730 PSU OFA52 ALU C1KC3	3000 K	8000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
912300057767	BVP125 LED80-4S/730 PSU S ALU C1KC3	3000 K	8000 lm

Mechanical and Housing

Order Code	Full Product Name	Color
912300024001	BVP125 LED120-4S/740 OFA52	Gray
912300024003	BVP125 LED120-4S/740 S	Gray
912300057764	BVP125 LED120-4S/730 PSU OFA52 ALU C1KC3	Aluminum
912300057766	BVP125 LED120-4S/730 PSU S ALU C1KC3	Aluminum

Order Code	Full Product Name	Color
912300024002	BVP125 LED80-4S/740 OFA52	Gray
912300024004	BVP125 LED80-4S/740 S	Gray
912300057765	BVP125 LED80-4S/730 PSU OFA52 ALU C1KC3	Aluminum
912300057767	BVP125 LED80-4S/730 PSU S ALU C1KC3	Aluminum

