



Flexible and tunable white

FlexCove G3

Sustainable and flexible offering with excellent optical performance

Benefits

- Energy efficient
- Great diversity
- Dimming compatibility

Features


- System efficacy up to 105lm/W
- 3 lumen options, 4 CCTs
- Tunable white 1000~4000k

Application

- Hotel
- Retail
- Restaurant

FlexCove G3

Versions



FlexCove

FlexCove

Accessories



FlexCove

Ordercode 911401760352,
911401760362, 911401760382,
911401760392



FlexCove

Ordercode 911401760372,
911401760402



FlexCove

Ordercode 911401760412



FlexCove

Ordercode 911401760422



FlexCove

Ordercode 911401760452,
911401760462



FlexCove

Ordercode 911401760472,
911401760482, 911401760492

Application Conditions

Ambient temperature range -20 to +35 °C

Operating and Electrical

Input Voltage 24 DC V

General Information

Beam angle of light source 120 °
 CE mark -
 Protection class IEC Safety class III (III)
 Optical cover/lens type No
 Driver included No
 ENEC mark -
 Flammability mark NO
 Glow-wire test NO
 Light source replaceable No
 Number of gear units -
 Optic type Symmetrical

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-10%

Application Conditions

| Order Code | Full Product Name | Maximum dim level |
|--------------|-----------------------------|-------------------|
| 911401759392 | LS170S LED4 824 IP20 L5000 | Not applicable |
| 911401759402 | LS170S LED4 827 IP20 L5000 | Not applicable |
| 911401759412 | LS170S LED4 840 IP20 L5000 | Not applicable |
| 911401759422 | LS170S LED4 865 IP20 L5000 | Not applicable |
| 911401759432 | LS170S LED8 824 IP20 L5000 | Not applicable |
| 911401759442 | LS170S LED8 827 IP20 L5000 | Not applicable |
| 911401759452 | LS170S LED8 840 IP20 L5000 | Not applicable |
| 911401759462 | LS170S LED8 865 IP20 L5000 | Not applicable |
| 911401759472 | LS170S LED12 824 IP20 L5000 | Not applicable |
| 911401759482 | LS170S LED12 827 IP20 L5000 | Not applicable |
| 911401759492 | LS170S LED12 840 IP20 L5000 | Not applicable |
| 911401759502 | LS170S LED12 865 IP20 L5000 | Not applicable |
| 911401759512 | LS170S LED16 824 IP20 L5000 | Not applicable |
| 911401759522 | LS170S LED16 827 IP20 L5000 | Not applicable |
| 911401759532 | LS170S LED16 840 IP20 L5000 | Not applicable |
| 911401759542 | LS170S LED16 865 IP20 L5000 | Not applicable |
| 911401759712 | LS170S LED4 927 IP20 L5000 | Not applicable |
| 911401759722 | LS170S LED8 927 IP20 L5000 | Not applicable |
| 911401759732 | LS170S LED12 927 IP20 L5000 | Not applicable |
| 911401759742 | LS170S LED16 927 IP20 L5000 | Not applicable |
| 911401759552 | LS170S LED4 824 IP44 L5000 | Not applicable |
| 911401759562 | LS170S LED4 827 IP44 L5000 | Not applicable |
| 911401759572 | LS170S LED4 840 IP44 L5000 | Not applicable |
| 911401759582 | LS170S LED4 865 IP44 L5000 | Not applicable |
| 911401759592 | LS170S LED8 824 IP44 L5000 | Not applicable |
| 911401759602 | LS170S LED8 827 IP44 L5000 | Not applicable |
| 911401759612 | LS170S LED8 840 IP44 L5000 | Not applicable |
| 911401759622 | LS170S LED8 865 IP44 L5000 | Not applicable |
| 911401759632 | LS170S LED12 824 IP44 L5000 | Not applicable |
| 911401759642 | LS170S LED12 827 IP44 L5000 | Not applicable |
| 911401759652 | LS170S LED12 840 IP44 L5000 | Not applicable |
| 911401759662 | LS170S LED12 865 IP44 L5000 | Not applicable |
| 911401759672 | LS170S LED16 824 IP44 L5000 | Not applicable |
| 911401759682 | LS170S LED16 827 IP44 L5000 | Not applicable |
| 911401759692 | LS170S LED16 840 IP44 L5000 | Not applicable |
| 911401759702 | LS170S LED16 865 IP44 L5000 | Not applicable |
| 911401759752 | LS170S LED4 927 IP44 L5000 | Not applicable |
| 911401759762 | LS170S LED8 927 IP44 L5000 | Not applicable |
| 911401759772 | LS170S LED12 927 IP44 L5000 | Not applicable |
| 911401759782 | LS170S LED16 927 IP44 L5000 | Not applicable |
| 911401759792 | LS170S LED9 TNW IP44 L5000 | 5% (1 to 10 V) |
| 911401759802 | LS170S LED10 TNW IP44 L5000 | 5% (1 to 10 V) |

Approval and Application

| Order Code | Full Product Name | Mech. impact protection code | Ingress protection code | Order Code | Full Product Name | Mech. impact protection code | Ingress protection code |
|--------------|----------------------------|------------------------------|-------------------------|--------------|----------------------------|------------------------------|-------------------------|
| 911401759392 | LS170S LED4 824 IP20 L5000 | IK00 | IP20 | 911401759422 | LS170S LED4 865 IP20 L5000 | IK00 | IP20 |
| 911401759402 | LS170S LED4 827 IP20 L5000 | IK00 | IP20 | 911401759432 | LS170S LED8 824 IP20 L5000 | IK00 | IP20 |
| 911401759412 | LS170S LED4 840 IP20 L5000 | IK00 | IP20 | 911401759442 | LS170S LED8 827 IP20 L5000 | IK00 | IP20 |

FlexCove G3

| Order Code | Full Product Name | Mech. impact protection code | Ingress protection code |
|--------------|-----------------------------|------------------------------|-------------------------|
| 911401759452 | LS170S LED8 840 IP20 L5000 | IK00 | IP20 |
| 911401759462 | LS170S LED8 865 IP20 L5000 | IK00 | IP20 |
| 911401759472 | LS170S LED12 824 IP20 L5000 | IK00 | IP20 |
| 911401759482 | LS170S LED12 827 IP20 L5000 | IK00 | IP20 |
| 911401759492 | LS170S LED12 840 IP20 L5000 | IK00 | IP20 |
| 911401759502 | LS170S LED12 865 IP20 L5000 | IK00 | IP20 |
| 911401759512 | LS170S LED16 824 IP20 L5000 | IK00 | IP20 |
| 911401759522 | LS170S LED16 827 IP20 L5000 | IK00 | IP20 |
| 911401759532 | LS170S LED16 840 IP20 L5000 | IK00 | IP20 |
| 911401759542 | LS170S LED16 865 IP20 L5000 | IK00 | IP20 |
| 911401759712 | LS170S LED4 927 IP20 L5000 | IK00 | IP20 |
| 911401759722 | LS170S LED8 927 IP20 L5000 | IK00 | IP20 |
| 911401759732 | LS170S LED12 927 IP20 L5000 | IK00 | IP20 |
| 911401759742 | LS170S LED16 927 IP20 L5000 | IK00 | IP20 |
| 911401759552 | LS170S LED4 824 IP44 L5000 | IK03 | IP44 |
| 911401759562 | LS170S LED4 827 IP44 L5000 | IK03 | IP44 |
| 911401759572 | LS170S LED4 840 IP44 L5000 | IK03 | IP44 |
| 911401759582 | LS170S LED4 865 IP44 L5000 | IK03 | IP44 |

| Order Code | Full Product Name | Mech. impact protection code | Ingress protection code |
|--------------|-----------------------------|------------------------------|-------------------------|
| 911401759592 | LS170S LED8 824 IP44 L5000 | IK03 | IP44 |
| 911401759602 | LS170S LED8 827 IP44 L5000 | IK03 | IP44 |
| 911401759612 | LS170S LED8 840 IP44 L5000 | IK03 | IP44 |
| 911401759622 | LS170S LED8 865 IP44 L5000 | IK03 | IP44 |
| 911401759632 | LS170S LED12 824 IP44 L5000 | IK03 | IP44 |
| 911401759642 | LS170S LED12 827 IP44 L5000 | IK03 | IP44 |
| 911401759652 | LS170S LED12 840 IP44 L5000 | IK03 | IP44 |
| 911401759662 | LS170S LED12 865 IP44 L5000 | IK03 | IP44 |
| 911401759672 | LS170S LED16 824 IP44 L5000 | IK03 | IP44 |
| 911401759682 | LS170S LED16 827 IP44 L5000 | IK03 | IP44 |
| 911401759692 | LS170S LED16 840 IP44 L5000 | IK03 | IP44 |
| 911401759702 | LS170S LED16 865 IP44 L5000 | IK03 | IP44 |
| 911401759752 | LS170S LED4 927 IP44 L5000 | IK03 | IP44 |
| 911401759762 | LS170S LED8 927 IP44 L5000 | IK03 | IP44 |
| 911401759772 | LS170S LED12 927 IP44 L5000 | IK03 | IP44 |
| 911401759782 | LS170S LED16 927 IP44 L5000 | IK03 | IP44 |
| 911401759792 | LS170S LED9 TNW IP44 L5000 | IK03 | IP44 |
| 911401759802 | LS170S LED10 TNW IP44 L5000 | IK03 | IP44 |

Controls and Dimming

| Order Code | Full Product Name | Dimmable |
|--------------|-----------------------------|----------|
| 911401759392 | LS170S LED4 824 IP20 L5000 | No |
| 911401759402 | LS170S LED4 827 IP20 L5000 | No |
| 911401759412 | LS170S LED4 840 IP20 L5000 | No |
| 911401759422 | LS170S LED4 865 IP20 L5000 | No |
| 911401759432 | LS170S LED8 824 IP20 L5000 | No |
| 911401759442 | LS170S LED8 827 IP20 L5000 | No |
| 911401759452 | LS170S LED8 840 IP20 L5000 | No |
| 911401759462 | LS170S LED8 865 IP20 L5000 | No |
| 911401759472 | LS170S LED12 824 IP20 L5000 | No |
| 911401759482 | LS170S LED12 827 IP20 L5000 | No |
| 911401759492 | LS170S LED12 840 IP20 L5000 | No |
| 911401759502 | LS170S LED12 865 IP20 L5000 | No |
| 911401759512 | LS170S LED16 824 IP20 L5000 | No |
| 911401759522 | LS170S LED16 827 IP20 L5000 | No |
| 911401759532 | LS170S LED16 840 IP20 L5000 | No |
| 911401759542 | LS170S LED16 865 IP20 L5000 | No |
| 911401759712 | LS170S LED4 927 IP20 L5000 | No |
| 911401759722 | LS170S LED8 927 IP20 L5000 | No |
| 911401759732 | LS170S LED12 927 IP20 L5000 | No |
| 911401759742 | LS170S LED16 927 IP20 L5000 | No |
| 911401759552 | LS170S LED4 824 IP44 L5000 | No |

| Order Code | Full Product Name | Dimmable |
|--------------|-----------------------------|----------|
| 911401759562 | LS170S LED4 827 IP44 L5000 | No |
| 911401759572 | LS170S LED4 840 IP44 L5000 | No |
| 911401759582 | LS170S LED4 865 IP44 L5000 | No |
| 911401759592 | LS170S LED8 824 IP44 L5000 | No |
| 911401759602 | LS170S LED8 827 IP44 L5000 | No |
| 911401759612 | LS170S LED8 840 IP44 L5000 | No |
| 911401759622 | LS170S LED8 865 IP44 L5000 | No |
| 911401759632 | LS170S LED12 824 IP44 L5000 | No |
| 911401759642 | LS170S LED12 827 IP44 L5000 | No |
| 911401759652 | LS170S LED12 840 IP44 L5000 | No |
| 911401759662 | LS170S LED12 865 IP44 L5000 | No |
| 911401759672 | LS170S LED16 824 IP44 L5000 | No |
| 911401759682 | LS170S LED16 827 IP44 L5000 | No |
| 911401759692 | LS170S LED16 840 IP44 L5000 | No |
| 911401759702 | LS170S LED16 865 IP44 L5000 | No |
| 911401759752 | LS170S LED4 927 IP44 L5000 | No |
| 911401759762 | LS170S LED8 927 IP44 L5000 | No |
| 911401759772 | LS170S LED12 927 IP44 L5000 | No |
| 911401759782 | LS170S LED16 927 IP44 L5000 | No |
| 911401759792 | LS170S LED9 TNW IP44 L5000 | Yes |
| 911401759802 | LS170S LED10 TNW IP44 L5000 | Yes |

Initial Performance (IEC Compliant) (1/2)

FlexCove G3

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Init. Color Rendering Index | Initial LED luminaire efficacy |
|--------------|--------------------------------------|--------------------------|-------------------------------|-----------------------------|--------------------------------|
| 911401759392 | LS170S LED4 824 IP20 L5000 | 0.4899;0.4205; SDCM 3 | 2400 K | 80 | 95 lm/W |
| 911401759402 | LS170S LED4 827 IP20 L5000 | 0.463;0.42; SDCM 3 | 2700 K | 80 | 100 lm/W |
| 911401759412 | LS170S LED4 840 IP20 L5000 | 0.38;0.38; SDCM 3 | 4000 K | 80 | 110 lm/W |
| 911401759422 | LS170S LED4 865 IP20 L5000 | 0.3102;0.3329; SDCM 4 | 6500 K | 80 | 105 lm/W |
| 911401759432 | LS170S LED8 824 IP20 L5000 | 0.4899;0.4205; SDCM 3 | 2400 K | 80 | 90 lm/W |
| 911401759442 | LS170S LED8 827 IP20 L5000 | 0.463;0.42; SDCM 3 | 2700 K | 80 | 90 lm/W |
| 911401759452 | LS170S LED8 840 IP20 L5000 | 0.38;0.38; SDCM 3 | 4000 K | 80 | 105 lm/W |
| 911401759462 | LS170S LED8 865 IP20 L5000 | 0.3102;0.3329; SDCM 4 | 6500 K | 80 | 105 lm/W |
| 911401759472 | LS170S LED12 824 IP20 L5000 | 0.4899;0.4205; SDCM 3 | 2400 K | 80 | 85 lm/W |
| 911401759482 | LS170S LED12 827 IP20 L5000 | 0.463;0.42; SDCM 3 | 2700 K | 80 | 90 lm/W |
| 911401759492 | LS170S LED12 840 IP20 L5000 | 0.38;0.38; SDCM 3 | 4000 K | 80 | 100 lm/W |
| 911401759502 | LS170S LED12 865 IP20 L5000 | 0.3102;0.3329; SDCM 4 | 6500 K | 80 | 100 lm/W |
| 911401759512 | LS170S LED16 824 SDCM 3 | 0.4899;0.4205; SDCM 3 | 2400 K | 80 | 85 lm/W |

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Init. Color Rendering Index | Initial LED luminaire efficacy |
|--------------|--------------------------------------|---------------------------|-------------------------------|-----------------------------|--------------------------------|
| | IP20 L5000 | | | | |
| 911401759522 | LS170S LED16 827 IP20 L5000 | 0.463;0.42; SDCM 3 | 2700 K | 80 | 90 lm/W |
| 911401759532 | LS170S LED16 840 IP20 L5000 | 0.38;0.38; SDCM 3 | 4000 K | 80 | 100 lm/W |
| 911401759542 | LS170S LED16 865 IP20 L5000 | 0.3102;0.3329; SDCM 4 | 6500 K | 80 | 100 lm/W |
| 911401759712 | LS170S LED4 927 IP20 L5000 | 0.463;0.42; SDCM 3 | 2700 K | 90 | 85 lm/W |
| 911401759722 | LS170S LED8 927 IP20 L5000 | 0.463;0.42; SDCM 3 | 2700 K | 90 | 80 lm/W |
| 911401759732 | LS170S LED12 927 IP20 L5000 | 0.463;0.42; SDCM 3 | 2700 K | 90 | 80 lm/W |
| 911401759742 | LS170S LED16 927 IP20 L5000 | 0.463;0.42; SDCM 3 | 2700 K | 90 | 80 lm/W |
| 911401759552 | LS170S LED4 824 IP44 L5000 | 0.4916;0.4204; SDCM 3 | 2400 K | 80 | 95 lm/W |
| 911401759562 | LS170S LED4 827 IP44 L5000 | 0.4659; 0.421; SDCM 3 | 2700 K | 80 | 95 lm/W |
| 911401759572 | LS170S LED4 840 IP44 L5000 | 0.3825; 0.382; SDCM 3 | 4000 K | 80 | 105 lm/W |
| 911401759582 | LS170S LED4 865 IP44 L5000 | 0.3136; 0.3373; SDCM 4 | 6500 K | 80 | 105 lm/W |
| 911401759592 | LS170S LED8 824 IP44 L5000 | 0.4916;0.4204; SDCM 3 | 2400 K | 80 | 85 lm/W |

FlexCove G3

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Init. Color Rendering Index | Initial LED luminaire efficacy |
|--------------|-----------------------------|------------------------|-------------------------------|-----------------------------|--------------------------------|
| 911401759602 | LS170S LED8 827 IP44 L5000 | 0.4659; 0.421; SDCM 3 | 2700 K | 80 | 90 lm/W |
| 911401759612 | LS170S LED8 840 IP44 L5000 | 0.3825; 0.382; SDCM 3 | 4000 K | 80 | 100 lm/W |
| 911401759622 | LS170S LED8 865 IP44 L5000 | 0.3136; 0.3373; SDCM 4 | 6500 K | 80 | 100 lm/W |
| 911401759632 | LS170S LED12 824 IP44 L5000 | 0.4916; 0.4204; SDCM 3 | 2400 K | 80 | 80 lm/W |
| 911401759642 | LS170S LED12 827 IP44 L5000 | 0.4659; 0.421; SDCM 3 | 2700 K | 80 | 85 lm/W |
| 911401759652 | LS170S LED12 840 IP44 L5000 | 0.3825; 0.382; SDCM 3 | 4000 K | 80 | 95 lm/W |
| 911401759662 | LS170S LED12 865 IP44 L5000 | 0.3136; 0.3373; SDCM 4 | 6500 K | 80 | 95 lm/W |
| 911401759672 | LS170S LED16 824 IP44 L5000 | 0.4916; 0.4204; SDCM 3 | 2400 K | 80 | 80 lm/W |
| 911401759682 | LS170S LED16 827 IP44 L5000 | 0.4659; 0.421; SDCM 3 | 2700 K | 80 | 85 lm/W |

| Order Code | Full Product Name | Initial chromaticity | Init. Corr. Color Temperature | Init. Color Rendering Index | Initial LED luminaire efficacy |
|--------------|-----------------------------|------------------------|-------------------------------|-----------------------------|--------------------------------|
| | IP44 L5000 | | | | |
| 911401759692 | LS170S LED16 840 IP44 L5000 | 0.3825; 0.382; SDCM 3 | 4000 K | 80 | 95 lm/W |
| 911401759702 | LS170S LED16 865 IP44 L5000 | 0.3136; 0.3373; SDCM 4 | 6500 K | 80 | 95 lm/W |
| 911401759752 | LS170S LED4 927 IP44 L5000 | 0.4659; 0.421; SDCM 3 | 2700 K | 90 | 85 lm/W |
| 911401759762 | LS170S LED8 927 IP44 L5000 | 0.4659; 0.421; SDCM 3 | 2700 K | 90 | 75 lm/W |
| 911401759772 | LS170S LED12 927 IP44 L5000 | 0.4659; 0.421; SDCM 3 | 2700 K | 90 | 75 lm/W |
| 911401759782 | LS170S LED16 927 IP44 L5000 | 0.4659; 0.421; SDCM 3 | 2700 K | 90 | 75 lm/W |
| 911401759792 | LS170S LED9 TNW IP44 L5000 | - | - K | 80 | - |
| 911401759802 | LS170S LED10 TNW IP44 L5000 | - | - | 80 | - |

Initial Performance (IEC Compliant) (2/2)

| Order Code | Full Product Name | Initial luminous flux | Initial input power |
|--------------|-----------------------------|-----------------------|---------------------|
| 911401759392 | LS170S LED4 824 IP20 L5000 | 400 lm | 21 W |
| 911401759402 | LS170S LED4 827 IP20 L5000 | 400 lm | 19 W |
| 911401759412 | LS170S LED4 840 IP20 L5000 | 400 lm | 18 W |
| 911401759422 | LS170S LED4 865 IP20 L5000 | 400 lm | 18 W |
| 911401759432 | LS170S LED8 824 IP20 L5000 | 800 lm | 41 W |
| 911401759442 | LS170S LED8 827 IP20 L5000 | 800 lm | 39 W |
| 911401759452 | LS170S LED8 840 IP20 L5000 | 800 lm | 37 W |
| 911401759462 | LS170S LED8 865 IP20 L5000 | 800 lm | 37 W |
| 911401759472 | LS170S LED12 824 IP20 L5000 | 1200 lm | 61 W |
| 911401759482 | LS170S LED12 827 IP20 L5000 | 1200 lm | 57 W |
| 911401759492 | LS170S LED12 840 IP20 L5000 | 1200 lm | 53 W |

| Order Code | Full Product Name | Initial luminous flux | Initial input power |
|--------------|-----------------------------|-----------------------|---------------------|
| 911401759502 | LS170S LED12 865 IP20 L5000 | 1200 lm | 53 W |
| 911401759512 | LS170S LED16 824 IP20 L5000 | 1600 lm | 85 W |
| 911401759522 | LS170S LED16 827 IP20 L5000 | 1600 lm | 78 W |
| 911401759532 | LS170S LED16 840 IP20 L5000 | 1600 lm | 72 W |
| 911401759542 | LS170S LED16 865 IP20 L5000 | 1600 lm | 72 W |
| 911401759712 | LS170S LED4 927 IP20 L5000 | 400 lm | 21 W |
| 911401759722 | LS170S LED8 927 IP20 L5000 | 800 lm | 41 W |
| 911401759732 | LS170S LED12 927 IP20 L5000 | 1200 lm | 61 W |
| 911401759742 | LS170S LED16 927 IP20 L5000 | 1600 lm | 85 W |
| 911401759552 | LS170S LED4 824 IP44 L5000 | 400 lm | 21 W |
| 911401759562 | LS170S LED4 827 IP44 L5000 | 400 lm | 19 W |

FlexCove G3

| Order Code | Full Product Name | Initial luminous flux | Initial input power |
|--------------|-----------------------------|-----------------------|---------------------|
| 911401759572 | LS170S LED4 840 IP44 L5000 | 400 lm | 18 W |
| 911401759582 | LS170S LED4 865 IP44 L5000 | 400 lm | 18 W |
| 911401759592 | LS170S LED8 824 IP44 L5000 | 800 lm | 42 W |
| 911401759602 | LS170S LED8 827 IP44 L5000 | 800 lm | 41 W |
| 911401759612 | LS170S LED8 840 IP44 L5000 | 800 lm | 37 W |
| 911401759622 | LS170S LED8 865 IP44 L5000 | 800 lm | 37 W |
| 911401759632 | LS170S LED12 824 IP44 L5000 | 1200 lm | 65 W |
| 911401759642 | LS170S LED12 827 IP44 L5000 | 1200 lm | 59 W |
| 911401759652 | LS170S LED12 840 IP44 L5000 | 1200 lm | 55 W |
| 911401759662 | LS170S LED12 865 IP44 L5000 | 1200 lm | 55 W |

| Order Code | Full Product Name | Initial luminous flux | Initial input power |
|--------------|-----------------------------|-----------------------|---------------------|
| 911401759672 | LS170S LED16 824 IP44 L5000 | 1600 lm | 87 W |
| 911401759682 | LS170S LED16 827 IP44 L5000 | 1600 lm | 82 W |
| 911401759692 | LS170S LED16 840 IP44 L5000 | 1600 lm | 75 W |
| 911401759702 | LS170S LED16 865 IP44 L5000 | 1600 lm | 75 W |
| 911401759752 | LS170S LED4 927 IP44 L5000 | 400 lm | 21 W |
| 911401759762 | LS170S LED8 927 IP44 L5000 | 800 lm | 42 W |
| 911401759772 | LS170S LED12 927 IP44 L5000 | 1200 lm | 65 W |
| 911401759782 | LS170S LED16 927 IP44 L5000 | 1600 lm | 87 W |
| 911401759792 | LS170S LED9 TNW IP44 L5000 | 900 lm | 67 W |
| 911401759802 | LS170S LED10 TNW IP44 L5000 | 1000 lm | 51 W |

Mechanical and Housing

| Order Code | Full Product Name | Color |
|--------------|-----------------------------|-------|
| 911401759392 | LS170S LED4 824 IP20 L5000 | White |
| 911401759402 | LS170S LED4 827 IP20 L5000 | White |
| 911401759412 | LS170S LED4 840 IP20 L5000 | White |
| 911401759422 | LS170S LED4 865 IP20 L5000 | White |
| 911401759432 | LS170S LED8 824 IP20 L5000 | White |
| 911401759442 | LS170S LED8 827 IP20 L5000 | White |
| 911401759452 | LS170S LED8 840 IP20 L5000 | White |
| 911401759462 | LS170S LED8 865 IP20 L5000 | White |
| 911401759472 | LS170S LED12 824 IP20 L5000 | White |
| 911401759482 | LS170S LED12 827 IP20 L5000 | White |
| 911401759492 | LS170S LED12 840 IP20 L5000 | White |
| 911401759502 | LS170S LED12 865 IP20 L5000 | White |
| 911401759512 | LS170S LED16 824 IP20 L5000 | White |
| 911401759522 | LS170S LED16 827 IP20 L5000 | White |
| 911401759532 | LS170S LED16 840 IP20 L5000 | White |
| 911401759542 | LS170S LED16 865 IP20 L5000 | White |
| 911401759712 | LS170S LED4 927 IP20 L5000 | White |
| 911401759722 | LS170S LED8 927 IP20 L5000 | White |
| 911401759732 | LS170S LED12 927 IP20 L5000 | White |
| 911401759742 | LS170S LED16 927 IP20 L5000 | White |
| 911401759552 | LS170S LED4 824 IP44 L5000 | Clear |

| Order Code | Full Product Name | Color |
|--------------|-----------------------------|-------|
| 911401759562 | LS170S LED4 827 IP44 L5000 | Clear |
| 911401759572 | LS170S LED4 840 IP44 L5000 | Clear |
| 911401759582 | LS170S LED4 865 IP44 L5000 | Clear |
| 911401759592 | LS170S LED8 824 IP44 L5000 | Clear |
| 911401759602 | LS170S LED8 827 IP44 L5000 | Clear |
| 911401759612 | LS170S LED8 840 IP44 L5000 | Clear |
| 911401759622 | LS170S LED8 865 IP44 L5000 | Clear |
| 911401759632 | LS170S LED12 824 IP44 L5000 | Clear |
| 911401759642 | LS170S LED12 827 IP44 L5000 | Clear |
| 911401759652 | LS170S LED12 840 IP44 L5000 | Clear |
| 911401759662 | LS170S LED12 865 IP44 L5000 | Clear |
| 911401759672 | LS170S LED16 824 IP44 L5000 | Clear |
| 911401759682 | LS170S LED16 827 IP44 L5000 | Clear |
| 911401759692 | LS170S LED16 840 IP44 L5000 | Clear |
| 911401759702 | LS170S LED16 865 IP44 L5000 | Clear |
| 911401759752 | LS170S LED4 927 IP44 L5000 | Clear |
| 911401759762 | LS170S LED8 927 IP44 L5000 | Clear |
| 911401759772 | LS170S LED12 927 IP44 L5000 | Clear |
| 911401759782 | LS170S LED16 927 IP44 L5000 | Clear |
| 911401759792 | LS170S LED9 TNW IP44 L5000 | Clear |
| 911401759802 | LS170S LED10 TNW IP44 L5000 | Clear |

