



# Designed to be seen, looks good on or off

## Decorative LED candles and lusters

The new Deco collection (candles and lusters) transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience. With very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

### Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

### Features

- Perfect fit and high quality finishing
- High color rendering (CRI above 80) for vivid colors
- Eco-friendly: contains no mercury or other hazardous substances

### Application

- Perfect for decorative installations: domestic applications, hospitality (restaurants and hotels)

## Decorative LED candles and lusters

### Versions




LEDbulb E14 P45 Mirror Crown



LEDcandle E14 B35 Amber



LEDcandle E27 P45 Amber





LEDCandle E14 BA35 Amber



LEDCandle E14 P45 Amber

### Dimensional drawing






| Product                                    | D     | C      |
|--|-------|--------|
| Classic LEDCandle D 5-32W B35 E14 822 GOLD | 35 mm | 103 mm |

| Product                                     | D     | C      |
|---|-------|--------|
| Classic LEDCandle D 5-32W BA35 E14 822 GOLD | 35 mm | 129 mm |

## Decorative LED candles and lusters

### Dimensional drawing



| Product                                    | D     | C     |
|--|-------|-------|
| Classic LEDLuster D 5-32W P45 E27 822 GOLD | 45 mm | 80 mm |

| Product                                    | D     | C     |
|--|-------|-------|
| Classic LEDLuster D 5-32W P45 E14 822 GOLD | 45 mm | 85 mm |

| Product                                 | D     | C     |
|---|-------|-------|
| LEDClassic CM P45 35W WW E14 CL ND SRT4 | 45 mm | 82 mm |

#### Operating and Electrical

|                     |             |
|---------------------|-------------|
| Input Frequency     | 50 to 60 Hz |
| Voltage (Nom)       | 220-240 V   |
| Starting Time (Nom) | 0.5 s       |

#### General Information

|                        |         |
|------------------------|---------|
| Nominal Lifetime (Nom) | 15000 h |
| Switching Cycle        | 20000X  |

#### Light Technical

|                                       |      |
|---------------------------------------|------|
| Color Rendering Index (Nom)           | 80   |
| Llmf At End Of Nominal Lifetime (Nom) | 70 % |

### Approval and Application

## Decorative LED candles and lusters

| Order Code   | Full Product Name                             | Energy                     | Energy                    |
|--------------|---|----------------------------|---------------------------|
|              |   | Consumption kWh/<br>1000 h | Efficiency Label<br>(EEL) |
| 929001395101 | LEDClassic CM P45 35W WW<br>E14 CL ND SRT4    | 4 kWh                      | A++                       |
| 929001896302 | Classic LEDCandle D 5-32W<br>B35 E14 822 GOLD | 5 kWh                      | A+                        |
| 929001896402 | Classic LEDLuster D 5-32W<br>P45 E27 822 GOLD | 5 kWh                      | A+                        |

| Order Code   | Full Product Name                              | Energy                     | Energy                    |
|--------------|--|----------------------------|---------------------------|
|              |  | Consumption kWh/<br>1000 h | Efficiency Label<br>(EEL) |
| 929001896502 | Classic LEDCandle D 5-32W<br>BA35 E14 822 GOLD | 5 kWh                      | A+                        |
| 929001896602 | Classic LEDLuster D 5-32W<br>P45 E14 822 GOLD  | 5 kWh                      | A+                        |

### Controls and Dimming

| Order Code   | Full Product Name                          | Dimmable |
|--------------|--|----------|
| 929001395101 | LEDClassic CM P45 35W WW E14 CL ND SRT4    | No       |
| 929001896302 | Classic LEDCandle D 5-32W B35 E14 822 GOLD | Yes      |
| 929001896402 | Classic LEDLuster D 5-32W P45 E27 822 GOLD | Yes      |

| Order Code   | Full Product Name                           | Dimmable |
|--------------|---|----------|
| 929001896502 | Classic LEDCandle D 5-32W BA35 E14 822 GOLD | Yes      |
| 929001896602 | Classic LEDLuster D 5-32W P45 E14 822 GOLD  | Yes      |

### Operating and Electrical

| Order Code   | Full Product Name                             | Wattage    | Power (Rated) |
|--------------|---|------------|---------------|
|              |   | Equivalent | (Nom)         |
| 929001395101 | LEDClassic CM P45 35W WW E14<br>CL ND SRT4    | 35 W       | 4 W           |
| 929001896302 | Classic LEDCandle D 5-32W B35<br>E14 822 GOLD | 32 W       | 5 W           |
| 929001896402 | Classic LEDLuster D 5-32W P45 E27<br>822 GOLD | 32 W       | 5 W           |

| Order Code   | Full Product Name                              | Wattage    | Power (Rated) |
|--------------|--|------------|---------------|
|              |  | Equivalent | (Nom)         |
| 929001896502 | Classic LEDCandle D 5-32W BA35<br>E14 822 GOLD | 32 W       | 5 W           |
| 929001896602 | Classic LEDLuster D 5-32W P45 E14<br>822 GOLD  | 32 W       | 5 W           |

### General Information

| Order Code   | Full Product Name                          | Cap-Base |
|--------------|--|----------|
| 929001395101 | LEDClassic CM P45 35W WW E14 CL ND SRT4    | E14      |
| 929001896302 | Classic LEDCandle D 5-32W B35 E14 822 GOLD | E14      |
| 929001896402 | Classic LEDLuster D 5-32W P45 E27 822 GOLD | E27      |

| Order Code   | Full Product Name                           | Cap-Base |
|--------------|---|----------|
| 929001896502 | Classic LEDCandle D 5-32W BA35 E14 822 GOLD | E14      |
| 929001896602 | Classic LEDLuster D 5-32W P45 E14 822 GOLD  | E14      |

### Light Technical

| Order Code   | Full Product Name                             | Correlated Color |                      |                        |
|--------------|---|------------------|----------------------|------------------------|
|              |   | Color<br>Code    | Temperature<br>(Nom) | Luminous<br>Flux (Nom) |
| 929001395101 | LEDClassic CM P45 35W<br>WW E14 CL ND SRT4    | 827              | 2700 K               | 397 lm                 |
| 929001896302 | Classic LEDCandle D<br>5-32W B35 E14 822 GOLD | 822              | 2200 K               | 350 lm                 |
| 929001896402 | Classic LEDLuster D<br>5-32W P45 E27 822 GOLD | 822              | 2200 K               | 350 lm                 |

| Order Code   | Full Product Name                                 | Correlated Color |                      |                        |
|--------------|---|------------------|----------------------|------------------------|
|              |   | Color<br>Code    | Temperature<br>(Nom) | Luminous<br>Flux (Nom) |
| 929001896502 | Classic LEDCandle D<br>5-32W BA35 E14 822<br>GOLD | 822              | 2200 K               | 350 lm                 |
| 929001896602 | Classic LEDLuster D<br>5-32W P45 E14 822 GOLD     | 822              | 2200 K               | 350 lm                 |

### Mechanical and Housing

## Decorative LED candles and lusters

| Order Code   | Full Product Name                          | Bulb Finish | Bulb Shape |
|--------------|--|-------------|------------|
| 929001395101 | LEDClassic CM P45 35W WW E14 CL ND SRT4    | Clear       | P45        |
| 929001896302 | Classic LEDCandle D 5-32W B35 E14 822 GOLD | Amber       | B35        |
| 929001896402 | Classic LEDLuster D 5-32W P45 E27 822 GOLD | Amber       | P45        |

| Order Code   | Full Product Name                           | Bulb Finish | Bulb Shape |
|--------------|---|-------------|------------|
| 929001896502 | Classic LEDCandle D 5-32W BA35 E14 822 GOLD | Amber       | BA35       |
| 929001896602 | Classic LEDLuster D 5-32W P45 E14 822 GOLD  | Amber       | P45        |

### Temperature

| Order Code   | Full Product Name                           | T-Case Maximum (Nom) |
|--------------|---|----------------------|
| 929001395101 | LEDClassic CM P45 35W WW E14 CL ND SRT4     | 45 °C                |
| 929001896302 | Classic LEDCandle D 5-32W B35 E14 822 GOLD  | 50 °C                |
| 929001896402 | Classic LEDLuster D 5-32W P45 E27 822 GOLD  | 50 °C                |
| 929001896502 | Classic LEDCandle D 5-32W BA35 E14 822 GOLD | 50 °C                |
| 929001896602 | Classic LEDLuster D 5-32W P45 E14 822 GOLD  | 50 °C                |

