



Exquisite, stylish yet classic and versatile urban lighting

UNIUrban

UNIUrban is ideal for the urban lighting across the sidewalks, parks, gardens, residential areas, shopping center plazas. Its exquisite, stylish yet classic design is not only suitable for modern cities but also for historical architecture.

Benefits

- Exquisite, stylish yet classic design to beautify your space
- State-of-the-art LEDs and drivers ensure better lighting performance and reliability
- Comfort and safety for urban
- Future-oriented

Features

- 5 even more look-and-feels
- 3 options of wattage packages– 33W/ 65W / 100W
- 3000K/4000K CCT , 100+lm/w for energy-saving
- 3 options for installation - Side-entry, Post-top and Suspension
- 3 options for lighting distribution - Symmetrical / Asymmetrical / Omni
- IP65 / IK08 , professional design to ensure reliability
- 50K hrs. lifetime with 3 yrs. warranty
- Various mounting installation

Application

- Sidewalks
- Parks, gardens
- Residential areas
- Shopping center plazas

Versions



BDP461



BGP461



BSP461



BSS461



uniurban



uniurban



uniurban

Accessories



Chess

Ordercode 911401727812,
911401727842



Dome

Ordercode 911401727822,
911401727832

Approval and Application

Mech. impact protection code IK08

General Information

CE mark CE mark

Driver included Yes

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401727442	BDP461 LED33 WW 110-277V TS	No
911401727452	BDP461 LED33 NW 110-277V TS	No
911401727462	BDP461 LED65 WW 110-277V TS	No
911401727472	BDP461 LED65 NW 110-277V TS	No

Order Code	Full Product Name	Dimmable
911401727482	BDP461 LED100 WW 110-277V TS	No
911401727492	BDP461 LED100 NW 110-277V TS	No
911401727502	BGP461 LED40 WW 110-277V TS	No
911401727512	BGP461 LED40 NW 110-277V TS	No

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401727522	BGP461 LED40 WW 110-277V TA	No	911401727742	BSS461 LED40 WW 110-277V CLASSIC	No
911401727532	BGP461 LED40 NW 110-277V TA	No	911401727752	BSS461 LED40 NW 110-277V CLASSIC	No
911401727542	BGP461 LED78 WW 110-277V TS	No	911401727762	BSS461 LED78 WW 110-277V CLASSIC	No
911401727552	BGP461 LED78 NW 110-277V TS	No	911401727772	BSS461 LED78 NW 110-277V CLASSIC	No
911401727562	BGP461 LED78 WW 110-277V TA	No	911401727782	BSS461 LED120 WW 110-277V CLASSIC	No
911401727572	BGP461 LED78 NW 110-277V TA	No	911401727792	BSS461 LED120 NW 110-277V CLASSIC	No
911401727582	BGP461 LED120 WW 110-277V TS	No	911401756012	BDP461 LED100 NW 230V SR TS 7P	Yes
911401727592	BGP461 LED120 NW 110-277V TS	No	911401756042	BDP461 LED100 NW 230V PSD TS SR	Yes
911401727602	BGP461 LED120 WW 110-277V TA	No	911401756072	BDP461 LED100 NW 230V SR TS 7P II	Yes
911401727612	BGP461 LED120 NW 110-277V TA	No	911401756102	BDP461 LED100 NW 230V PSD TS SR II	Yes
911401727622	BSP461 LED40 WW 110-277V TS	No	911401767062	BDP461 LED100 NW 230V PSC TS 7P	Yes
911401727632	BSP461 LED40 NW 110-277V TS	No	911401756022	BSP461 LED120 NW 230V SR TA 7P	Yes
911401727642	BSP461 LED40 WW 110-277V TA	No	911401756032	BSS461 LED120 NW 230V SR CLASSIC 7P	Yes
911401727652	BSP461 LED40 NW 110-277V TA	No	911401756052	BSP461 LED120 NW 230V PSD TA SR	Yes
911401727662	BSP461 LED78 WW 110-277V TS	No	911401756062	BSS461 LED120 NW 230V PSD CLASSIC SR	Yes
911401727672	BSP461 LED78 NW 110-277V TS	No	911401756082	BSP461 LED120 NW 230V SR TA 7P II	Yes
911401727682	BSP461 LED78 WW 110-277V TA	No	911401756092	BSS461 LED120 NW 230V SR CLASSIC 7P II	Yes
911401727692	BSP461 LED78 NW 110-277V TA	No	911401756112	BSP461 LED120 NW 230V PSD TA SR II	Yes
911401727702	BSP461 LED120 WW 110-277V TS	No	911401756122	BSS461 LED120 NW 230V PSD CLASSIC SR II	Yes
911401727712	BSP461 LED120 NW 110-277V TS	No	911401759262	BGP461 LED78 NW 230V SR TS 7P Spg77	Yes
911401727722	BSP461 LED120 WW 110-277V TA	No	911401759272	BGP461 LED78 NW 230V SR TS 7P II Spg77	Yes
911401727732	BSP461 LED120 NW 110-277V TA	No	911401767072	BGP461 LED120 NW 230V PSC TA 7P Spg77	Yes

General Information

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark	Lamp family code	Light source replaceable
911401727442	BDP461 LED33 WW 110-277V TS	Warm white	Polycarbonate micro lens optic	-	-	No
911401727452	BDP461 LED33 NW 110-277V TS	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727462	BDP461 LED65 WW 110-277V TS	Warm white	Polycarbonate micro lens optic	-	-	No
911401727472	BDP461 LED65 NW 110-277V TS	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727482	BDP461 LED100 WW 110-277V TS	Warm white	Polycarbonate micro lens optic	-	-	No
911401727492	BDP461 LED100 NW 110-277V TS	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727502	BGP461 LED40 WW 110-277V TS	Warm white	Polycarbonate micro lens optic	-	-	No
911401727512	BGP461 LED40 NW 110-277V TS	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727522	BGP461 LED40 WW 110-277V TA	Warm white	Polycarbonate micro lens optic	-	-	No
911401727532	BGP461 LED40 NW 110-277V TA	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727542	BGP461 LED78 WW 110-277V TS	Warm white	Polycarbonate micro lens optic	-	-	No
911401727552	BGP461 LED78 NW 110-277V TS	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727562	BGP461 LED78 WW 110-277V TA	Warm white	Polycarbonate micro lens optic	-	-	No
911401727572	BGP461 LED78 NW 110-277V TA	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727582	BGP461 LED120 WW 110-277V TS	Tunable white	Polycarbonate micro lens optic	-	-	No
911401727592	BGP461 LED120 NW 110-277V TS	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727602	BGP461 LED120 WW 110-277V TA	Warm white	Polycarbonate micro lens optic	-	-	No
911401727612	BGP461 LED120 NW 110-277V TA	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727622	BSP461 LED40 WW 110-277V TS	Warm white	Polycarbonate micro lens optic	-	-	No
911401727632	BSP461 LED40 NW 110-277V TS	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727642	BSP461 LED40 WW 110-277V TA	Warm white	Polycarbonate micro lens optic	-	-	No
911401727652	BSP461 LED40 NW 110-277V TA	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727662	BSP461 LED78 WW 110-277V TS	Warm white	Polycarbonate micro lens optic	-	-	No
911401727672	BSP461 LED78 NW 110-277V TS	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727682	BSP461 LED78 WW 110-277V TA	Warm white	Polycarbonate micro lens optic	-	-	No
911401727692	BSP461 LED78 NW 110-277V TA	Neutral white	Polycarbonate micro lens optic	-	-	No

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark	Lamp family code	Light source replaceable
911401727702	BSP461 LED120 WW 110-277V TS	Warm white	Polycarbonate micro lens optic	-	-	No
911401727712	BSP461 LED120 NW 110-277V TS	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727722	BSP461 LED120 WW 110-277V TA	Warm white	Polycarbonate micro lens optic	-	-	No
911401727732	BSP461 LED120 NW 110-277V TA	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727742	BSS461 LED40 WW 110-277V CLASSIC	Warm white	Polycarbonate micro lens optic	-	-	No
911401727752	BSS461 LED40 NW 110-277V CLASSIC	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727762	BSS461 LED78 WW 110-277V CLASSIC	Warm white	Polycarbonate micro lens optic	-	-	No
911401727772	BSS461 LED78 NW 110-277V CLASSIC	Neutral white	Polycarbonate micro lens optic	-	-	No
911401727782	BSS461 LED120 WW 110-277V CLASSIC	Warm white	Polycarbonate micro lens optic	-	-	No
911401727792	BSS461 LED120 NW 110-277V CLASSIC	Neutral white	Polycarbonate micro lens optic	-	-	No
911401756012	BDP461 LED100 NW 230V SR TS 7P	740 neutral white	Acrylate micro-lens optic	-	-	-
911401756042	BDP461 LED100 NW 230V PSD TS SR	740 neutral white	Acrylate micro-lens optic	-	-	-
911401756072	BDP461 LED100 NW 230V SR TS 7P II	740 neutral white	Acrylate micro-lens optic	-	-	-
911401756102	BDP461 LED100 NW 230V PSD TS SR II	740 neutral white	Acrylate micro-lens optic	-	-	-
911401767062	BDP461 LED100 NW 230V PSC TS 7P	740 neutral white	Acrylate micro-lens optic	-	-	-
911401756022	BSP461 LED120 NW 230V SR TA 7P	740 neutral white	Acrylate micro-lens optic	-	-	-
911401756032	BSS461 LED120 NW 230V SR CLASSIC 7P	740 neutral white	-	-	-	-
911401756052	BSP461 LED120 NW 230V PSD TA SR	740 neutral white	Acrylate micro-lens optic	-	-	-
911401756062	BSS461 LED120 NW 230V PSD CLASSIC SR	740 neutral white	-	-	-	-
911401756082	BSP461 LED120 NW 230V SR TA 7P II	740 neutral white	Acrylate micro-lens optic	-	-	-
911401756092	BSS461 LED120 NW 230V SR CLASSIC 7P II	740 neutral white	-	-	-	-
911401756112	BSP461 LED120 NW 230V PSD TA SR II	740 neutral white	Acrylate micro-lens optic	-	-	-
911401756122	BSS461 LED120 NW 230V PSD CLASSIC SR II	740 neutral white	-	-	-	-
911401759262	BGP461 LED78 NW 230V SR TS 7P Spg77	740 neutral white	Acrylate micro-lens optic	-	-	-
911401759272	BGP461 LED78 NW 230V SR TS 7P II Spg77	740 neutral white	Acrylate micro-lens optic	-	-	-
911401767072	BGP461 LED120 NW 230V PSC TA 7P Spg77	740 neutral white	Acrylate micro-lens optic	-	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color		Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color	
			Rendering Index	Initial luminous flux				Rendering Index	Initial luminous flux
911401727442	BDP461 LED33 WW 110-277V TS	3000 K	≥70	3300 lm	911401727542	BGP461 LED78 WW 110-277V TS	3000 K	≥70	7800 lm
911401727452	BDP461 LED33 NW 110-277V TS	4000 K	≥70	3300 lm	911401727552	BGP461 LED78 NW 110-277V TS	4000 K	≥70	7800 lm
911401727462	BDP461 LED65 WW 110-277V TS	3000 K	≥70	6500 lm	911401727562	BGP461 LED78 WW 110-277V TA	3000 K	≥70	7800 lm
911401727472	BDP461 LED65 NW 110-277V TS	4000 K	≥70	6500 lm	911401727572	BGP461 LED78 NW 110-277V TA	4000 K	≥70	7800 lm
911401727482	BDP461 LED100 WW 110-277V TS	3000 K	≥70	10000 lm	911401727582	BGP461 LED120 WW 110-277V TS	3000 K	≥70	12000 lm
911401727492	BDP461 LED100 NW 110-277V TS	4000 K	≥70	10000 lm	911401727592	BGP461 LED120 NW 110-277V TS	4000 K	≥70	12000 lm
911401727502	BGP461 LED40 WW 110-277V TS	3000 K	≥70	4000 lm	911401727602	BGP461 LED120 WW 110-277V TA	3000 K	≥70	12000 lm
911401727512	BGP461 LED40 NW 110-277V TS	4000 K	≥70	4000 lm	911401727612	BGP461 LED120 NW 110-277V TA	4000 K	≥70	120000 lm
911401727522	BGP461 LED40 WW 110-277V TA	3000 K	≥70	4000 lm	911401727622	BSP461 LED40 WW 110-277V TS	3000 K	≥70	4000 lm
911401727532	BGP461 LED40 NW 110-277V TA	4000 K	≥70	4000 lm	911401727632	BSP461 LED40 NW 110-277V TS	4000 K	≥70	4000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color	
			Rendering Index	Initial luminous flux
911401727642	BSP461 LED40 WW 110-277V TA	3000 K	≥70	4000 lm
911401727652	BSP461 LED40 NW 110-277V TA	4000 K	≥70	4000 lm
911401727662	BSP461 LED78 WW 110-277V TS	3000 K	≥70	7800 lm
911401727672	BSP461 LED78 NW 110-277V TS	4000 K	≥70	7800 lm
911401727682	BSP461 LED78 WW 110-277V TA	3000 K	≥70	7800 lm
911401727692	BSP461 LED78 NW 110-277V TA	4000 K	≥70	7800 lm
911401727702	BSP461 LED120 WW 110-277V TS	3000 K	≥70	12000 lm
911401727712	BSP461 LED120 NW 110-277V TS	4000 K	≥70	12000 lm
911401727722	BSP461 LED120 WW 110-277V TA	3000 K	≥70	12000 lm
911401727732	BSP461 LED120 NW 110-277V TA	4000 K	≥70	12000 lm
911401727742	BSS461 LED40 WW 110-277V CLASSIC	3000 K	≥70	4000 lm
911401727752	BSS461 LED40 NW 110-277V CLASSIC	4000 K	≥70	4000 lm
911401727762	BSS461 LED78 WW 110-277V CLASSIC	3000 K	≥70	7800 lm
911401727772	BSS461 LED78 NW 110-277V CLASSIC	4000 K	≥70	7800 lm
911401727782	BSS461 LED120 WW 110-277V CLASSIC	3000 K	≥70	7800 lm
911401727792	BSS461 LED120 NW 110-277V CLASSIC	4000 K	≥70	12000 lm
911401756012	BDP461 LED100 NW 230V SR TS 7P	4000 K	>70	10000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color	
			Rendering Index	Initial luminous flux
911401756042	BDP461 LED100 NW 230V PSD TS SR	4000 K	>70	10000 lm
911401756072	BDP461 LED100 NW 230V SR TS 7P II	4000 K	>70	10000 lm
911401756102	BDP461 LED100 NW 230V PSD TS SR II	4000 K	>70	10000 lm
911401767062	BDP461 LED100 NW 230V PSC TS 7P	4000 K	>70	10000 lm
911401756022	BSP461 LED120 NW 230V SR TA 7P	4000 K	>70	12000 lm
911401756032	BSS461 LED120 NW 230V SR CLASSIC 7P	4000 K	>70	12000 lm
911401756052	BSP461 LED120 NW 230V PSD TA SR	4000 K	>70	12000 lm
911401756062	BSS461 LED120 NW 230V PSD CLASSIC SR	4000 K	>70	12000 lm
911401756082	BSP461 LED120 NW 230V SR TA 7P II	4000 K	>70	12000 lm
911401756092	BSS461 LED120 NW 230V SR CLASSIC 7P II	4000 K	>70	12000 lm
911401756112	BSP461 LED120 NW 230V PSD TA SR II	4000 K	>70	12000 lm
911401756122	BSS461 LED120 NW 230V PSD CLASSIC SR II	4000 K	>70	12000 lm
911401759262	BGP461 LED78 NW 230V SR TS 7P Spg77	4000 K	>70	7800 lm
911401759272	BGP461 LED78 NW 230V SR TS 7P II Spg77	4000 K	>70	7800 lm
911401767072	BGP461 LED120 NW 230V PSC TA 7P Spg77	4000 K	>70	12000 lm

Light Technical

Order Code	Full Product Name	Standard tilt angle posttop
911401727442	BDP461 LED33 WW 110-277V TS	-
911401727452	BDP461 LED33 NW 110-277V TS	-
911401727462	BDP461 LED65 WW 110-277V TS	-
911401727472	BDP461 LED65 NW 110-277V TS	-
911401727482	BDP461 LED100 WW 110-277V TS	-
911401727492	BDP461 LED100 NW 110-277V TS	-
911401727502	BGP461 LED40 WW 110-277V TS	15°
911401727512	BGP461 LED40 NW 110-277V TS	15°
911401727522	BGP461 LED40 WW 110-277V TA	15°
911401727532	BGP461 LED40 NW 110-277V TA	15°
911401727542	BGP461 LED78 WW 110-277V TS	15°

Order Code	Full Product Name	Standard tilt angle posttop
911401727552	BGP461 LED78 NW 110-277V TS	15°
911401727562	BGP461 LED78 WW 110-277V TA	15°
911401727572	BGP461 LED78 NW 110-277V TA	15°
911401727582	BGP461 LED120 WW 110-277V TS	15°
911401727592	BGP461 LED120 NW 110-277V TS	15°
911401727602	BGP461 LED120 WW 110-277V TA	15°
911401727612	BGP461 LED120 NW 110-277V TA	15°
911401727622	BSP461 LED40 WW 110-277V TS	-
911401727632	BSP461 LED40 NW 110-277V TS	-
911401727642	BSP461 LED40 WW 110-277V TA	-
911401727652	BSP461 LED40 NW 110-277V TA	-

Order Code	Full Product Name	Standard tilt angle posttop
911401727662	BSP461 LED78 WW 110-277V TS	-
911401727672	BSP461 LED78 NW 110-277V TS	-
911401727682	BSP461 LED78 WW 110-277V TA	-
911401727692	BSP461 LED78 NW 110-277V TA	-
911401727702	BSP461 LED120 WW 110-277V TS	-
911401727712	BSP461 LED120 NW 110-277V TS	-
911401727722	BSP461 LED120 WW 110-277V TA	-
911401727732	BSP461 LED120 NW 110-277V TA	-
911401727742	BSS461 LED40 WW 110-277V CLASSIC	-
911401727752	BSS461 LED40 NW 110-277V CLASSIC	-
911401727762	BSS461 LED78 WW 110-277V CLASSIC	-
911401727772	BSS461 LED78 NW 110-277V CLASSIC	-
911401727782	BSS461 LED120 WW 110-277V CLASSIC	-
911401727792	BSS461 LED120 NW 110-277V CLASSIC	-
911401756012	BDP461 LED100 NW 230V SR TS 7P	-

Order Code	Full Product Name	Standard tilt angle posttop
911401756042	BDP461 LED100 NW 230V PSD TS SR	-
911401756072	BDP461 LED100 NW 230V SR TS 7P II	-
911401756102	BDP461 LED100 NW 230V PSD TS SR II	-
911401767062	BDP461 LED100 NW 230V PSC TS 7P	-
911401756022	BSP461 LED120 NW 230V SR TA 7P	-
911401756032	BSS461 LED120 NW 230V SR CLASSIC 7P	-
911401756052	BSP461 LED120 NW 230V PSD TA SR	-
911401756062	BSS461 LED120 NW 230V PSD CLASSIC SR	-
911401756082	BSP461 LED120 NW 230V SR TA 7P II	-
911401756092	BSS461 LED120 NW 230V SR CLASSIC 7P II	-
911401756112	BSP461 LED120 NW 230V PSD TA SR II	-
911401756122	BSS461 LED120 NW 230V PSD CLASSIC SR II	-
911401759262	BGP461 LED78 NW 230V SR TS 7P Spg77	-
911401759272	BGP461 LED78 NW 230V SR TS 7P II Spg77	-
911401767072	BGP461 LED120 NW 230V PSC TA 7P Spg77	-

Mechanical and Housing

Order Code	Full Product Name	Color
911401727442	BDP461 LED33 WW 110-277V TS	Gray
911401727452	BDP461 LED33 NW 110-277V TS	Gray
911401727462	BDP461 LED65 WW 110-277V TS	Gray
911401727472	BDP461 LED65 NW 110-277V TS	Gray
911401727482	BDP461 LED100 WW 110-277V TS	Gray
911401727492	BDP461 LED100 NW 110-277V TS	Gray
911401727502	BGP461 LED40 WW 110-277V TS	Gray
911401727512	BGP461 LED40 NW 110-277V TS	Gray
911401727522	BGP461 LED40 WW 110-277V TA	Gray
911401727532	BGP461 LED40 NW 110-277V TA	Gray
911401727542	BGP461 LED78 WW 110-277V TS	Gray
911401727552	BGP461 LED78 NW 110-277V TS	Gray
911401727562	BGP461 LED78 WW 110-277V TA	Gray
911401727572	BGP461 LED78 NW 110-277V TA	Gray
911401727582	BGP461 LED120 WW 110-277V TS	Gray
911401727592	BGP461 LED120 NW 110-277V TS	Gray
911401727602	BGP461 LED120 WW 110-277V TA	Gray
911401727612	BGP461 LED120 NW 110-277V TA	Gray
911401727622	BSP461 LED40 WW 110-277V TS	Gray
911401727632	BSP461 LED40 NW 110-277V TS	Gray
911401727642	BSP461 LED40 WW 110-277V TA	Gray
911401727652	BSP461 LED40 NW 110-277V TA	Gray
911401727662	BSP461 LED78 WW 110-277V TS	Gray
911401727672	BSP461 LED78 NW 110-277V TS	Gray
911401727682	BSP461 LED78 WW 110-277V TA	Gray
911401727692	BSP461 LED78 NW 110-277V TA	Gray

Order Code	Full Product Name	Color
911401727702	BSP461 LED120 WW 110-277V TS	Gray
911401727712	BSP461 LED120 NW 110-277V TS	Gray
911401727722	BSP461 LED120 WW 110-277V TA	Gray
911401727732	BSP461 LED120 NW 110-277V TA	Gray
911401727742	BSS461 LED40 WW 110-277V CLASSIC	Gray
911401727752	BSS461 LED40 NW 110-277V CLASSIC	Gray
911401727762	BSS461 LED78 WW 110-277V CLASSIC	Gray
911401727772	BSS461 LED78 NW 110-277V CLASSIC	Gray
911401727782	BSS461 LED120 WW 110-277V CLASSIC	Gray
911401727792	BSS461 LED120 NW 110-277V CLASSIC	Gray
911401756012	BDP461 LED100 NW 230V SR TS 7P	Aluminum and gray
911401756042	BDP461 LED100 NW 230V PSD TS SR	Aluminum and gray
911401756072	BDP461 LED100 NW 230V SR TS 7P II	Aluminum and gray
911401756102	BDP461 LED100 NW 230V PSD TS SR II	Aluminum and gray
911401767062	BDP461 LED100 NW 230V PSC TS 7P	Aluminum and gray
911401756022	BSP461 LED120 NW 230V SR TA 7P	Aluminum and gray
911401756032	BSS461 LED120 NW 230V SR CLASSIC 7P	Aluminum and gray
911401756052	BSP461 LED120 NW 230V PSD TA SR	Aluminum and gray
911401756062	BSS461 LED120 NW 230V PSD CLASSIC SR	Aluminum and gray
911401756082	BSP461 LED120 NW 230V SR TA 7P II	Aluminum and gray
911401756092	BSS461 LED120 NW 230V SR CLASSIC 7P II	Aluminum and gray
911401756112	BSP461 LED120 NW 230V PSD TA SR II	Aluminum and gray
911401756122	BSS461 LED120 NW 230V PSD CLASSIC SR II	Aluminum and gray
911401759262	BGP461 LED78 NW 230V SR TS 7P Spg77	Aluminum and gray
911401759272	BGP461 LED78 NW 230V SR TS 7P II Spg77	Aluminum and gray
911401767072	BGP461 LED120 NW 230V PSC TA 7P Spg77	Aluminum and gray

