



# Luma gen2 – The standard in road lighting, redefined

## Luma gen2

Luma gen2 is the next generation of the Luma LED luminaire family, fully optimized to become your long-term lighting and innovation partner. While keeping the distinctive design characteristics of the first generation, Luma gen2 gives you the benefits of the latest technologies thanks to its future-proof System Ready architecture, use of optimized Ledgine LED and optical platform ensuring best in class lighting performance in a broad range of applications. It also offers improved serviceability. Installation has also become easier and faster, and thanks to the Service tag, you have access to all relevant documentations onsite. Also, the cable feed-through has been redesigned and access to the gear components is easy thanks to top down tool-less access. Luma gen2 also offers all connectivity and dimming options available today and thanks to being System Ready, it can also be paired with lighting management systems such as Interact City or existing and upcoming sensor innovations. The Luma gen2 has been developed to optimize and simplify spare part repair and maintenance work using a new plug & play GearFlex module containing all electrical components in an easy to handle and accessible box inside the housing. As a company conscious about the impact of light on the environment and biodiversity, we also equipped the Luma gen2 with dedicated light recipes that help with maintaining the optimal ecosystems for bats or preserve a dark night sky.

## Benefits

- Ease of maintenance and spare part repair enabled through the dedicated GearFlex module
- Best in class efficiency and light performance in a broad range of applications
- Future-ready thanks to the SR (System Ready) socket
- Luminaire is also equipped with dedicated light recipes that help with: 1) maintaining the optimal ecosystems for bats 2) preserve a dark night sky and reduce light pollution
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

## Features

- Dedicated GearFlex module enabling faster, safer and tool-less maintenance
- New cable feedthrough for easy installation
- Ready to be connected to the Interact City lighting management software
- Ready to be paired with third party lighting management systems and sensors
- Tilt now with 2,5 degrees precision
- Efficacy up to 155 lm/W
- Choice of 40+ different beams and option of different internal louvers
- Further optimization on performance flux level enabled by the Philips L-Tune
- Surge protection up to 10kV
- Wide range of lumen packages, ranging from 1,000 to 55,000 lm

## Application

- Motorways, inter-urban main roads, boulevards and avenues, roundabouts, pedestrian crossings
- Residential streets, side streets, squares, parks, cycle and pedestrian paths, playgrounds
- Parking areas, industrial areas, petrol stations, rail yards, airports, harbors, waterways

## Specifications

<b>Ambient Temperature</b>	-40 to +50 °C	<b>Initial input power</b>	154 W, 166 W, 174 W, 21.5 W, 24 W, 24.5 W, 25 W, 31.5 W, 37 W, 38 W, 40.5 W, 52 W, 6.1 W, 71 W, 74 W, 79 W, 83 W, 87 W, 91 W
<b>Main color of the Luminaire</b>	Gray	<b>Initial LED luminaire efficacy</b>	86, 108, 109, 111, 114, 115, 119, 120, 141, 142, 143, 144, 146, 147, 148, 150, 153, 154, 155 lm/W
<b>Dimming</b>	No, yes	<b>Initial luminous flux</b>	10350 lm, 10465 lm, 10800 lm, 10920 lm, 12740 lm, 13500 lm, 17850 lm, 18900 lm, 22500 lm, 26100 lm, 26700 lm, 3185 lm, 3220 lm, 3510 lm, 3558 lm, 3600 lm, 4482 lm, 4500 lm, 4550 lm, 5220 lm, 5278 lm, 5400 lm, 728 lm, 8600 lm, 9100 lm
<b>Driver</b>	Power supply unit regulating with constant light output (Power supply unit regulating with constant light output) Power supply unit with DALI and SystemReady interface (Power supply unit with DALI and SystemReady interface) Power supply unit with DALI and SystemReady interface and constant light output (integrated) (Power supply unit with DALI and SystemReady interface and constant light output (integrated)) Power supply unit with DynaDimmer (Power supply unit with DynaDimmer)	<b>Input frequency</b>	50 to 60 Hz
<b>Driver failure rate at 5000 h in %</b>	0.005 %	<b>Input voltage</b>	220 to 240, 220-240 V
<b>Initial correlated color temperature</b>	1000 K, 3000 K, 4000 K	<b>Inrush current (A)</b>	4, 11.5, 18, 21, 47, 58 A
		<b>Light source color</b>	510 ClearField, 740 neutral white, 830 warm white
		<b>Light source replaceable</b>	Yes
		<b>Material</b>	Bracket:
		<b>Material</b>	Gear box:
		<b>Material</b>	Housing: aluminum die cast

# Luma gen2

<b>Optic</b>	Distribution extra wide 10, distribution medium 10, distribution medium 11, distribution medium 12, distribution medium 31, distribution medium 32, distribution medium 50, distribution wide 50
<b>Optical cover</b>	Polymethyl methacrylate
<b>Surge protection</b>	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode, luminaire surge protection level until 6 kV differential mode and 8 kV common mode, surge protection level until 10 kV differential mode

<b>Tilt angle housing</b>	Standard tilt angle posttop: -, 0°Standard tilt angle side entry: -, 0°
<b>Type</b>	BGP701
	BGP702
	BGP703
	BGP704
	BGP705

## Versions

Luma gen2 Micro bottom view



Luma gen2 Micro with EasyAir module



Luma gen2 Mini bottom view



Luma gen2 Medium with EasyAir module



Luma gen2 Medium bottom view



BGP705 Luma gen2 Large GearFlex1



# Luma gen2

## Versions



LUMA GEN2 NANO - LED Module,  
system flux 800 lm - LED - 160° -  
42° x 54°



LUMA GEN2 MICRO - LED module  
5000 lm - LED - 70° x 37°



LUMA GEN2 MINI - LED module  
10000 lm - LED - 70° x 37°



LUMA GEN2 MEDIUM - LED  
module 21000 lm - LED - 70° x 37°



LUMA GEN2 MICRO - LED module  
6000 lm - LED - Power supply  
unit with DALI and SystemReady  
interface - Distribution medium 11  
- Glass - 70° x 37° - Internal (no  
external connection) - Post-top for  
diameter 60 to 76 mm



LUMA GEN2 MINI - LED module  
12000 lm - LED - Power supply  
unit with DALI and SystemReady  
interface - Distribution medium 50  
- Glass - 154° - 31° x 54° - Internal  
(no external connection) - Post-  
top for diameter 60 to 76 mm



LUMA GEN2 MEDIUM - LED  
module 14000 lm - LED - Power  
supply unit with DALI and  
SystemReady interface -  
Distribution medium 50 - Glass -  
154° - 31° x 54° - Internal (no  
external connection) - Post-top for  
diameter 60 to 76 mm



LUMA GEN2 NANO - LED module  
6000 lm - LED - 70° x 37°

## Product details

BGP705 Luma gen2 Large FG DPP



BGP705 Luma gen2 Large Open1 DPP



BGP701 Luma gen2 Nano FG DPP



BGP701 Luma gen2 Nano Open2 DPP



### General Information

Driver included	Yes
Light source replaceable	Yes

## Application Conditions

Order Code	Full Product Name	Maximum dim level
910925866534	BGP702 LED60-4S/740 DM11 GF SRT SRB 60/7	Not applicable
910925866535	BGP702 LED40-4S/740 DM10 GF SRT SRB 60/7	Not applicable
910925866536	BGP702 LW10 LED50-4S/830 DM11 GF CTGO	Not applicable
910925867784	BGP702 LED40-4S/740 II DM10 MSP CLO SRT	Not applicable
910925867785	BGP702 LED60-4S/740 II DM32 MSP CLO SRT	Not applicable
910925867786	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	Not applicable
910925867787	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	Not applicable
910925866537	BGP702 LED35-4S/740 II DM11 GF EZR SRB 6	Not applicable
910925866538	BGP703 LED120-4S/740 DM50 GF SRT SRB 60	Not applicable
910925866539	BGP703 LED100-4S/830 II DW50 GF SRT SRB	Not applicable
910925866540	BGP703 LED54-4S/610 DM11 GF SRT SRB 60/7	Not applicable
910925866541	BGP703 LED50-4S/740 II DM11 GF EZR SRB 6	Not applicable
910925867788	BGP703 LED60-4S/740 II DM31 MSP CLO SRT	Not applicable
910925867789	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	Not applicable
910925867790	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	Not applicable
910925867791	BGP703 LED120-4S/740 II DM32 MSP CLO SRT	Not applicable
910925866542	BGP704 LED140-4S/740 DM50 GF SRT SRB 60	Not applicable
910925866543	BGP704 LED210-4S/830 II DX10 GF D18 DDF3	30%
910925866544	BGP704 LW10 LED120-4S/830 DM11 GF CTGO	Not applicable
910925867794	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	Not applicable
910925867795	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	50%
910925866545	BGP704 LED140-4S/740 DM11 GF EZR SRB	Not applicable
910925867142	BGP705 LED150-4S/740 DM11 GF SRT SRB 60/	Not applicable

Order Code	Full Product Name	Maximum dim level
910925867143	BGP705 LED300-4S/740 II DM11 GF SRT SRB	Not applicable
910925868226	BGP705 LED300-4S/740 II DM32 MSP CLO SRT	Not applicable
910925867324	BGP701 LED8-4S/740 DM11 GF GR 42/60P	Not applicable
910925867325	BGP701 LED40-4S/740 DM10 GF SRT SRB 42/6	Not applicable
910925867326	BGP701 LW10 LED50-4S/830 DM11 GF CTGO-DG	Not applicable
910925867327	BGP701 LED35-4S/740 II DM11 GF EZR SRB 4	Not applicable
910925868225	BGP701 LED60-4S/740 II DM32 MSP CLO SRT	Not applicable
910925868227	BGP701 LED40-4S/740 II DM10 MSP CLO SRT	Not applicable
910925867833	BGP702 LED50-4S/830 DM11 DDF27 D18 SRG10	50%
910925867834	BGP703 LED100-4S/830 DM11 DDF27 D18 SRG1	50%
910925867835	BGP704 LED210-4S/830 DM11 DDF27 D18 SRG1	50%
910925868042	BGP702 LED60-4S/740 DM11 PGR SRT SRB 60	Not applicable
910925868043	BGP702 LED40-4S/740 DM10 PGR SRT SRB 60	Not applicable
910925868044	BGP702 LW10 LED50-4S/830 DM11 PGR CTGO	Not applicable
910925868045	BGP702 LED35-4S/740 II DM11 PGR EZR SRB	Not applicable
910925868046	BGP703 LED120-4S/740 DM50 PGR SRT SRB 60	Not applicable
910925868047	BGP703 LED100-4S/830 II DW50 PGR SRT SRB	Not applicable
910925868048	BGP703 LED54-4S/610 DM11 PGR SRT SRB 60	Not applicable
910925868049	BGP703 LED50-4S/740 II DM11 PGR EZR SRB	Not applicable
910925868050	BGP704 LED140-4S/740 DM50 PGR SRT SRB 60	Not applicable
910925868051	BGP704 LED210-4S/830 II DX10 PGR DDF3 D1	30%
910925868052	BGP704 LW10 LED120-4S/830 DM11 CTGO-DG	Not applicable
910925868053	BGP704 LED140-4S/740 DM11 PGR EZR SRB 60	Not applicable

Order Code	Full Product Name	Maximum dim level
910925868136	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	Not applicable

Order Code	Full Product Name	Maximum dim level
910925868137	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	Not applicable

Approval and Application

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925866534	BGP702 LED60-4S/740 DM11 GF SRT SRB 60/7	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866535	BGP702 LED40-4S/740 DM10 GF SRT SRB 60/7	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866536	BGP702 LW10 LED50-4S/830 DM11 GF CTGO	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867784	BGP702 LED40-4S/740 II DM10 MSP CLO SRT	IK09	Surge protection level until 10 kV differential mode
910925867785	BGP702 LED60-4S/740 II DM32 MSP CLO SRT	IK09	Surge protection level until 10 kV differential mode
910925867786	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867787	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866537	BGP702 LED35-4S/740 II DM11 GF EZR SRB 6	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866538	BGP703 LED120-4S/740 DM50 GF SRT SRB 60	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866539	BGP703 LED100-4S/830 II DW50 GF SRT SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866540	BGP703 LED54-4S/610 DM11 GF SRT SRB 60/7	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866541	BGP703 LED50-4S/740 II DM11 GF EZR SRB 6	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867788	BGP703 LED60-4S/740 II DM31 MSP CLO SRT	IK09	Surge protection level until 10 kV differential mode
910925867789	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867790	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867791	BGP703 LED120-4S/740 II DM32 MSP CLO SRT	IK09	Surge protection level until 10 kV differential mode

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925866542	BGP704 LED140-4S/740 DM50 GF SRT SRB 60	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866543	BGP704 LED210-4S/830 II DX10 GF D18 DDF3	IK10	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866544	BGP704 LW10 LED120-4S/830 DM11 GF CTGO	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867794	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867795	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	IK10	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866545	BGP704 LED140-4S/740 DM11 GF EZR SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867142	BGP705 LED150-4S/740 DM11 GF SRT SRB 60/	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867143	BGP705 LED300-4S/740 II DM11 GF SRT SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868226	BGP705 LED300-4S/740 II DM32 MSP CLO SRT	-	Surge protection level until 10 kV differential mode
910925867324	BGP701 LED8-4S/740 DM11 FG GR 42/60P	IK10	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867325	BGP701 LED40-4S/740 DM10 GF SRT SRB 42/6	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867326	BGP701 LW10 LED50-4S/830 DM11 GF CTGO-DG	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867327	BGP701 LED35-4S/740 II DM11 GF EZR SRB 4	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868225	BGP701 LED60-4S/740 II DM32 MSP CLO SRT	-	Surge protection level until 10 kV differential mode
910925868227	BGP701 LED40-4S/740 II DM10 MSP CLO SRT	-	Surge protection level until 10 kV differential mode

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925867833	BGP702 LED50-4S/830 DM11 DDF27 D18 SRG10	IK10	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925867834	BGP703 LED100-4S/830 DM11 DDF27 D18 SRG1	IK10	Surge protection level until 10 kV differential mode
910925867835	BGP704 LED210-4S/830 DM11 DDF27 D18 SRG1	IK10	Surge protection level until 10 kV differential mode
910925868042	BGP702 LED60-4S/740 DM11 PGR SRT SRB 60	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868043	BGP702 LED40-4S/740 DM10 PGR SRT SRB 60	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868044	BGP702 LW10 LED50-4S/830 DM11 PGR CTGO	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868045	BGP702 LED35-4S/740 II DM11 PGR EZR SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868046	BGP703 LED120-4S/740 DM50 PGR SRT SRB 60	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868047	BGP703 LED100-4S/830 II DW50 PGR SRT SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Mech. impact protection code	Surge Protection (Common/Differential)
910925868048	BGP703 LED54-4S/610 DM11 PGR SRT SRB 60	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868049	BGP703 LED50-4S/740 II DM11 PGR EZR SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868050	BGP704 LED140-4S/740 DM50 PGR SRT SRB 60	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868051	BGP704 LED210-4S/830 II DX10 PGR DDF3 D1	IK10	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868052	BGP704 LW10 LED120-4S/830 DM11 CTGO-DG	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868053	BGP704 LED140-4S/740 DM11 PGR EZR SRB 60	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868136	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868137	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	IK09	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

**Controls and Dimming**

Order Code	Full Product Name	Dimmable
910925866534	BGP702 LED60-4S/740 DM11 GF SRT SRB 60/7	No
910925866535	BGP702 LED40-4S/740 DM10 GF SRT SRB 60/7	No
910925866536	BGP702 LW10 LED50-4S/830 DM11 GF CTGO	Yes
910925867784	BGP702 LED40-4S/740 II DM10 MSP CLO SRT	No
910925867785	BGP702 LED60-4S/740 II DM32 MSP CLO SRT	No
910925867786	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	No
910925867787	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	No
910925866537	BGP702 LED35-4S/740 II DM11 GF EZR SRB 6	No
910925866538	BGP703 LED120-4S/740 DM50 GF SRT SRB 60	No
910925866539	BGP703 LED100-4S/830 II DW50 GF SRT SRB	No
910925866540	BGP703 LED54-4S/610 DM11 GF SRT SRB 60/7	No
910925866541	BGP703 LED50-4S/740 II DM11 GF EZR SRB 6	No
910925867788	BGP703 LED60-4S/740 II DM31 MSP CLO SRT	No
910925867789	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	No
910925867790	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	No
910925867791	BGP703 LED120-4S/740 II DM32 MSP CLO SRT	No
910925866542	BGP704 LED140-4S/740 DM50 GF SRT SRB 60	No
910925866543	BGP704 LED210-4S/830 II DX10 GF D18 DDF3	Yes

Order Code	Full Product Name	Dimmable
910925866544	BGP704 LW10 LED120-4S/830 DM11 GF CTGO	Yes
910925867794	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	No
910925867795	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	No
910925866545	BGP704 LED140-4S/740 DM11 GF EZR SRB	No
910925867142	BGP705 LED150-4S/740 DM11 GF SRT SRB 60/	No
910925867143	BGP705 LED300-4S/740 II DM11 GF SRT SRB	No
910925868226	BGP705 LED300-4S/740 II DM32 MSP CLO SRT	Yes
910925867324	BGP701 LED8-4S/740 DM11 FG GR 42/60P	No
910925867325	BGP701 LED40-4S/740 DM10 GF SRT SRB 42/6	No
910925867326	BGP701 LW10 LED50-4S/830 DM11 GF CTGO-DG	Yes
910925867327	BGP701 LED35-4S/740 II DM11 GF EZR SRB 4	No
910925868225	BGP701 LED60-4S/740 II DM32 MSP CLO SRT	Yes
910925868227	BGP701 LED40-4S/740 II DM10 MSP CLO SRT	Yes
910925867833	BGP702 LED50-4S/830 DM11 DDF27 D18 SRG10	Yes
910925867834	BGP703 LED100-4S/830 DM11 DDF27 D18 SRG1	Yes
910925867835	BGP704 LED210-4S/830 DM11 DDF27 D18 SRG1	Yes
910925868042	BGP702 LED60-4S/740 DM11 PGR SRT SRB 60	No
910925868043	BGP702 LED40-4S/740 DM10 PGR SRT SRB 60	No

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910925868044	BGP702 LW10 LED50-4S/830 DM11 PGR CTGO	Yes	910925868050	BGP704 LED140-4S/740 DM50 PGR SRT SRB 60	No
910925868045	BGP702 LED35-4S/740 II DM11 PGR EZR SRB	Yes	910925868051	BGP704 LED210-4S/830 II DX10 PGR DDF3 D1	Yes
910925868046	BGP703 LED120-4S/740 DM50 PGR SRT SRB 60	No	910925868052	BGP704 LW10 LED120-4S/830 DM11 CTGO-DG	Yes
910925868047	BGP703 LED100-4S/830 II DW50 PGR SRT SRB	No	910925868053	BGP704 LED140-4S/740 DM11 PGR EZR SRB 60	Yes
910925868048	BGP703 LED54-4S/610 DM11 PGR SRT SRB 60	No	910925868136	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	No
910925868049	BGP703 LED50-4S/740 II DM11 PGR EZR SRB	Yes	910925868137	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	No

General Information (1/2)

Order Code	Full Product Name	Luminaire light beam spread	CE mark	Light source color	Optical		Flammability mark	Lamp family code	Number of gear units
					cover/lens type				
910925866534	BGP702 LED60-4S/740 DM11 GF SRT SRB 60/7	70° x 37°	CE mark	740 neutral white	Glass	-	LED60	1 unit	
910925866535	BGP702 LED40-4S/740 DM10 GF SRT SRB 60/7	73° x 44°	CE mark	740 neutral white	Glass	-	LED40	1 unit	
910925866536	BGP702 LW10 LED50-4S/830 DM11 GF CTGO	70° x 37°	CE mark	830 warm white	Glass	-	LED50	1 unit	
910925867784	BGP702 LED40-4S/740 II DM10 MSP CLO SRT	73° x 44°	CE mark	740 neutral white	Glass	-	LED40	1 unit	
910925867785	BGP702 LED60-4S/740 II DM32 MSP CLO SRT	65° x 39°	CE mark	740 neutral white	Glass	-	LED60	1 unit	
910925867786	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	70° x 37°	CE mark	740 neutral white	Glass	-	LED60	1 unit	
910925867787	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	70° x 37°	CE mark	740 neutral white	Glass	-	LED60	1 unit	
910925866537	BGP702 LED35-4S/740 II DM11 GF EZR SRB 6	70° x 37°	CE mark	740 neutral white	Glass	-	LED35	1 unit	
910925866538	BGP703 LED120-4S/740 DM50 GF SRT SRB 60	154° - 31° x 54°	CE mark	740 neutral white	Glass	-	LED120	1 unit	
910925866539	BGP703 LED100-4S/830 II DW50 GF SRT SRB	150° - 43° x 67°	CE mark	830 warm white	Glass	-	LED100	1 unit	
910925866540	BGP703 LED54-4S/610 DM11 GF SRT SRB 60/7	70° x 37°	CE mark	510 ClearField	Glass	-	LED54	1 unit	
910925866541	BGP703 LED50-4S/740 II DM11 GF EZR SRB 6	70° x 37°	CE mark	740 neutral white	Glass	-	LED50	1 unit	
910925867788	BGP703 LED60-4S/740 II DM31 MSP CLO SRT	65° x 23°	CE mark	740 neutral white	Glass	-	LED60	1 unit	
910925867789	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	70° x 37°	CE mark	740 neutral white	Glass	-	LED120	1 unit	
910925867790	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	70° x 37°	CE mark	740 neutral white	Glass	-	LED120	1 unit	
910925867791	BGP703 LED120-4S/740 II DM32 MSP CLO SRT	65° x 39°	CE mark	740 neutral white	Glass	-	LED120	1 unit	
910925866542	BGP704 LED140-4S/740 DM50 GF SRT SRB 60	154° - 31° x 54°	CE mark	740 neutral white	Glass	-	LED140	1 unit	
910925866543	BGP704 LED210-4S/830 II DX10 GF D18 DDF3	150° - 43° x 67°	CE mark	830 warm white	Glass	-	LED210	1 unit	
910925866544	BGP704 LW10 LED120-4S/830 DM11 GF CTGO	70° x 37°	CE mark	830 warm white	Glass	-	LED120	1 unit	
910925867794	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	70° x 37°	CE mark	740 neutral white	Glass	-	LED260	1 unit	
910925867795	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	70° x 37°	CE mark	740 neutral white	Glass	-	LED260	1 unit	
910925866545	BGP704 LED140-4S/740 DM11 GF EZR SRB	70° x 37°	CE mark	740 neutral white	Glass	-	LED140	1 unit	
910925867142	BGP705 LED150-4S/740 DM11 GF SRT SRB 60/	70° x 37°	CE mark	740 neutral white	Glass	-	LED150	1 unit	



Order Code	Full Product Name	Luminaire light beam			Optical cover/lens type	Flammability mark	Lamp family code	Number of gear units
		spread	CE mark	Light source color				
910925867143	BGP705 LED300-4S/740 II DM11 GF SRT SRB	70° x 37°	CE mark	740 neutral white	Glass	-	LED300	3 units
910925868226	BGP705 LED300-4S/740 II DM32 MSP CLO SRT	-	-	740 neutral white	-	-	LED300	3 units
910925867324	BGP701 LED8-4S/740 DM11 FG GR 42/60P	70° x 37°	CE mark	740 neutral white	Glass	-	LED8	1 unit
910925867325	BGP701 LED40-4S/740 DM10 GF SRT SRB 42/6	73° x 44°	CE mark	740 neutral white	Glass	-	LED40	1 unit
910925867326	BGP701 LW10 LED50-4S/830 DM11 GF CTGO-DG	70° x 37°	CE mark	830 warm white	Glass	-	LED50	1 unit
910925867327	BGP701 LED35-4S/740 II DM11 GF EZR SRB 4	70° x 37°	CE mark	740 neutral white	Glass	-	LED35	1 unit
910925868225	BGP701 LED60-4S/740 II DM32 MSP CLO SRT	-	-	740 neutral white	-	-	LED60	1 unit
910925868227	BGP701 LED40-4S/740 II DM10 MSP CLO SRT	-	-	740 neutral white	-	-	LED40	1 unit
910925867833	BGP702 LED50-4S/830 DM11 DDF27 D18 SRG10	70° x 37°	CE mark	830 warm white	Glass	-	LED50	1 unit
910925867834	BGP703 LED100-4S/830 DM11 DDF27 D18 SRG1	70° x 37°	CE mark	830 warm white	Glass	-	LED100	1 unit
910925867835	BGP704 LED210-4S/830 DM11 DDF27 D18 SRG1	70° x 37°	CE mark	830 warm white	Glass	-	LED210	1 unit
910925868042	BGP702 LED60-4S/740 DM11 PGR SRT SRB 60	70° x 37°	CE mark	740 neutral white	Glass	-	LED60	1 unit
910925868043	BGP702 LED40-4S/740 DM10 PGR SRT SRB 60	73° x 44°	CE mark	740 neutral white	Glass	-	LED40	1 unit
910925868044	BGP702 LW10 LED50-4S/830 DM11 PGR CTGO	70° x 37°	CE mark	830 warm white	Glass	-	LED50	1 unit
910925868045	BGP702 LED35-4S/740 II DM11 PGR EZR SRB	70° x 37°	CE mark	740 neutral white	Glass	-	LED35	1 unit
910925868046	BGP703 LED120-4S/740 DM50 PGR SRT SRB 60	154° - 31° x 54°	CE mark	740 neutral white	Glass	-	LED120	1 unit
910925868047	BGP703 LED100-4S/830 II DW50 PGR SRT SRB	150° - 43° x 67°	CE mark	830 warm white	Glass	-	LED100	1 unit
910925868048	BGP703 LED54-4S/610 DM11 PGR SRT SRB 60	70° x 37°	CE mark	510 ClearField	Glass	-	LED54	1 unit
910925868049	BGP703 LED50-4S/740 II DM11 PGR EZR SRB	70° x 37°	CE mark	740 neutral white	Glass	-	LED50	1 unit
910925868050	BGP704 LED140-4S/740 DM50 PGR SRT SRB 60	154° - 31° x 54°	CE mark	740 neutral white	Glass	-	LED140	1 unit
910925868051	BGP704 LED210-4S/830 II DX10 PGR DDF3 D1	150° - 43° x 67°	CE mark	830 warm white	Glass	-	LED210	1 unit
910925868052	BGP704 LW10 LED120-4S/830 DM11 CTGO-DG	70° x 37°	CE mark	830 warm white	Glass	-	LED120	1 unit
910925868053	BGP704 LED140-4S/740 DM11 PGR EZR SRB 60	70° x 37°	CE mark	740 neutral white	Glass	-	LED140	1 unit
910925868136	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	70° x 37°	CE mark	740 neutral white	Glass	-	LED60	1 unit
910925868137	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	70° x 37°	CE mark	740 neutral white	Glass	-	LED60	1 unit

General Information (2/2)

Order Code	Full Product Name	Optic type	Product Family Code	Service tag
910925866534	BGP702 LED60-4S/740 DM11 GF SRT SRB 60/7	Distribution medium 11	BGP702	Yes
910925866535	BGP702 LED40-4S/740 DM10 GF SRT SRB 60/7	Distribution medium 10	BGP702	Yes
910925866536	BGP702 LW10 LED50-4S/830 DM11 GF CTGO	Distribution medium 11	BGP702	Yes
910925867784	BGP702 LED40-4S/740 II DM10 MSP CLO SRT	Distribution medium 10	BGP702	Yes
910925867785	BGP702 LED60-4S/740 II DM32 MSP CLO SRT	Distribution medium 32	BGP702	Yes
910925867786	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	Distribution medium 11	BGP702	Yes
910925867787	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	Distribution medium 11	BGP702	Yes
910925866537	BGP702 LED35-4S/740 II DM11 GF EZR SRB 6	Distribution medium 12	BGP702	Yes
910925866538	BGP703 LED120-4S/740 DM50 GF SRT SRB 60	Distribution medium 50	BGP703	Yes
910925866539	BGP703 LED100-4S/830 II DW50 GF SRT SRB	Distribution wide 50	BGP703	Yes
910925866540	BGP703 LED54-4S/610 DM11 GF SRT SRB 60/7	Distribution medium 11	BGP703	Yes
910925866541	BGP703 LED50-4S/740 II DM11 GF EZR SRB 6	Distribution medium 11	BGP703	Yes
910925867788	BGP703 LED60-4S/740 II DM31 MSP CLO SRT	Distribution medium 31	BGP703	Yes
910925867789	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	Distribution medium 11	BGP703	Yes
910925867790	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	Distribution medium 11	BGP703	Yes
910925867791	BGP703 LED120-4S/740 II DM32 MSP CLO SRT	Distribution medium 32	BGP703	Yes
910925866542	BGP704 LED140-4S/740 DM50 GF SRT SRB 60	Distribution medium 50	BGP704	Yes
910925866543	BGP704 LED210-4S/830 II DX10 GF D18 DDF3	Distribution extra wide 10	BGP704	Yes
910925866544	BGP704 LW10 LED120-4S/830 DM11 GF CTGO	Distribution medium 11	BGP704	Yes
910925867794	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	Distribution medium 31	BGP704	Yes
910925867795	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	Distribution medium 11	BGP704	Yes
910925866545	BGP704 LED140-4S/740 DM11 GF EZR SRB	Distribution medium 11	BGP704	Yes
910925867142	BGP705 LED150-4S/740 DM11 GF SRT SRB 60/	Distribution medium 11	BGP705	Yes
910925867143	BGP705 LED300-4S/740 II DM11 GF SRT SRB	Distribution medium 11	BGP705	Yes
910925868226	BGP705 LED300-4S/740 II DM32 MSP CLO SRT	-	BGP705	-

Order Code	Full Product Name	Optic type	Product Family Code	Service tag
910925867324	BGP701 LED8-4S/740 DM11 FG GR 42/60P	Distribution medium 11	BGP701	Yes
910925867325	BGP701 LED40-4S/740 DM10 GF SRT SRB 42/6	Distribution medium 10	BGP701	Yes
910925867326	BGP701 LW10 LED50-4S/830 DM11 GF CTGO-DG	Distribution medium 11	BGP701	Yes
910925867327	BGP701 LED35-4S/740 II DM11 GF EZR SRB 4	Distribution medium 11	BGP701	Yes
910925868225	BGP701 LED60-4S/740 II DM32 MSP CLO SRT	-	BGP701	-
910925868227	BGP701 LED40-4S/740 II DM10 MSP CLO SRT	-	BGP701	-
910925867833	BGP702 LED50-4S/830 DM11 DDF27 D18 SRG10	Distribution medium 11	BGP702	Yes
910925867834	BGP703 LED100-4S/830 DM11 DDF27 D18 SRG1	Distribution medium 32	BGP703	Yes
910925867835	BGP704 LED210-4S/830 DM11 DDF27 D18 SRG1	Distribution medium 31	BGP704	Yes
910925868042	BGP702 LED60-4S/740 DM11 PGR SRT SRB 60	Distribution medium 11	BGP702	Yes
910925868043	BGP702 LED40-4S/740 DM10 PGR SRT SRB 60	Distribution medium 10	BGP702	Yes
910925868044	BGP702 LW10 LED50-4S/830 DM11 PGR CTGO	Distribution medium 11	BGP702	Yes
910925868045	BGP702 LED35-4S/740 II DM11 PGR EZR SRB	Distribution medium 12	BGP702	Yes
910925868046	BGP703 LED120-4S/740 DM50 PGR SRT SRB 60	Distribution medium 50	BGP703	Yes
910925868047	BGP703 LED100-4S/830 II DW50 PGR SRT SRB	Distribution wide 50	BGP703	Yes
910925868048	BGP703 LED54-4S/610 DM11 PGR SRT SRB 60	Distribution medium 11	BGP703	Yes
910925868049	BGP703 LED50-4S/740 II DM11 PGR EZR SRB	Distribution medium 11	BGP703	Yes
910925868050	BGP704 LED140-4S/740 DM50 PGR SRT SRB 60	Distribution medium 50	BGP704	Yes
910925868051	BGP704 LED210-4S/830 II DX10 PGR DDF3 D1	Distribution extra wide 10	BGP704	Yes
910925868052	BGP704 LW10 LED120-4S/830 DM11 CTGO-DG	Distribution medium 11	BGP704	Yes
910925868053	BGP704 LED140-4S/740 DM11 PGR EZR SRB 60	Distribution medium 11	BGP704	Yes
910925868136	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	Distribution medium 11	BGP701	Yes
910925868137	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	Distribution medium 11	BGP701	Yes

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866534	BGP702 LED60-4S/740 DM11 GF SRT SRB 60/7	4000 K	>70	5400 lm
910925866535	BGP702 LED40-4S/740 DM10 GF SRT SRB 60/7	4000 K	>70	3600 lm
910925866536	BGP702 LW10 LED50-4S/830 DM11 GF CTGO	3000 K	>80	4500 lm
910925867784	BGP702 LED40-4S/740 II DM10 MSP CLO SRT	4000 K	>70	3510 lm
910925867785	BGP702 LED60-4S/740 II DM32 MSP CLO SRT	4000 K	>70	5278 lm
910925867786	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	4000 K	>70	5220 lm
910925867787	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	4000 K	>70	5220 lm
910925866537	BGP702 LED35-4S/740 II DM11 GF EZR SRB 6	4000 K	>70	3220 lm
910925866538	BGP703 LED120-4S/740 DM50 GF SRT SRB 60	4000 K	>70	10800 lm
910925866539	BGP703 LED100-4S/830 II DW50 GF SRT SRB	3000 K	>80	8600 lm
910925866540	BGP703 LED54-4S/610 DM11 GF SRT SRB 60/7	1000 K	>60	4482 lm
910925866541	BGP703 LED50-4S/740 II DM11 GF EZR SRB 6	4000 K	>70	4550 lm
910925867788	BGP703 LED60-4S/740 II DM31 MSP CLO SRT	4000 K	>70	5278 lm
910925867789	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	4000 K	>70	10350 lm
910925867790	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	4000 K	>70	10350 lm
910925867791	BGP703 LED120-4S/740 II DM32 MSP CLO SRT	4000 K	>70	10465 lm
910925866542	BGP704 LED140-4S/740 DM50 GF SRT SRB 60	4000 K	>70	12740 lm
910925866543	BGP704 LED210-4S/830 II DX10 GF D18 DDF3	3000 K	>80	17850 lm
910925866544	BGP704 LW10 LED120-4S/830 DM11 GF CTGO	3000 K	>80	10920 lm
910925867794	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	4000 K	>70	22500 lm
910925867795	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	4000 K	>70	22500 lm
910925866545	BGP704 LED140-4S/740 DM11 GF EZR SRB	4000 K	>70	12740 lm
910925867142	BGP705 LED150-4S/740 DM11 GF SRT SRB 60/	4000 K	>70	13500 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925867143	BGP705 LED300-4S/740 II DM11 GF SRT SRB	4000 K	>70	26700 lm
910925868226	BGP705 LED300-4S/740 II DM32 MSP CLO SRT	4000 K	70	26100 lm
910925867324	BGP701 LED8-4S/740 DM11 FG GR 42/60P	4000 K	>70	728 lm
910925867325	BGP701 LED40-4S/740 DM10 GF SRT SRB 42/6	4000 K	>70	3600 lm
910925867326	BGP701 LW10 LED50-4S/830 DM11 GF CTGO-DG	3000 K	>80	4500 lm
910925867327	BGP701 LED35-4S/740 II DM11 GF EZR SRB 4	4000 K	>70	3185 lm
910925868225	BGP701 LED60-4S/740 II DM32 MSP CLO SRT	4000 K	70	5278 lm
910925868227	BGP701 LED40-4S/740 II DM10 MSP CLO SRT	4000 K	70	3558 lm
910925867833	BGP702 LED50-4S/830 DM11 DDF27 D18 SRG10	3000 K	>80	4500 lm
910925867834	BGP703 LED100-4S/830 DM11 DDF27 D18 SRG1	3000 K	>80	9100 lm
910925867835	BGP704 LED210-4S/830 DM11 DDF27 D18 SRG1	3000 K	>80	18900 lm
910925868042	BGP702 LED60-4S/740 DM11 PGR SRT SRB 60	4000 K	>70	5400 lm
910925868043	BGP702 LED40-4S/740 DM10 PGR SRT SRB 60	4000 K	>70	3600 lm
910925868044	BGP702 LW10 LED50-4S/830 DM11 PGR CTGO	3000 K	>80	4500 lm
910925868045	BGP702 LED35-4S/740 II DM11 PGR EZR SRB	4000 K	>70	3220 lm
910925868046	BGP703 LED120-4S/740 DM50 PGR SRT SRB 60	4000 K	>70	10800 lm
910925868047	BGP703 LED100-4S/830 II DW50 PGR SRT SRB	3000 K	>80	8600 lm
910925868048	BGP703 LED54-4S/610 DM11 PGR SRT SRB 60	1000 K	>60	4482 lm
910925868049	BGP703 LED50-4S/740 II DM11 PGR EZR SRB	4000 K	>70	4550 lm
910925868050	BGP704 LED140-4S/740 DM50 PGR SRT SRB 60	4000 K	>70	12740 lm
910925868051	BGP704 LED210-4S/830 II DX10 PGR DDF3 D1	3000 K	>80	17850 lm
910925868052	BGP704 LW10 LED120-4S/830 DM11 CTGO-DG	3000 K	>80	10920 lm
910925868053	BGP704 LED140-4S/740 DM11 PGR EZR SRB 60	4000 K	>70	12740 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925868136	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	4000 K	>70	5220 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925868137	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	4000 K	>70	5220 lm

Light Technical

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
910925866534	BGP702 LED60-4S/740 DM11 GF SRT SRB 60/7	-	0°	0
910925866535	BGP702 LED40-4S/740 DM10 GF SRT SRB 60/7	-	0°	0
910925866536	BGP702 LW10 LED50-4S/830 DM11 GF CTGO	-	0°	0
910925867784	BGP702 LED40-4S/740 II DM10 MSP CLO SRT	-	0°	0
910925867785	BGP702 LED60-4S/740 II DM32 MSP CLO SRT	-	0°	0
910925867786	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	0°	-	0
910925867787	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	0°	-	0
910925866537	BGP702 LED35-4S/740 II DM11 GF EZR SRB 6	-	0°	0
910925866538	BGP703 LED120-4S/740 DM50 GF SRT SRB 60	-	0°	0
910925866539	BGP703 LED100-4S/830 II DW50 GF SRT SRB	-	0°	0
910925866540	BGP703 LED54-4S/610 DM11 GF SRT SRB 60/7	-	0°	0
910925866541	BGP703 LED50-4S/740 II DM11 GF EZR SRB 6	-	0°	0
910925867788	BGP703 LED60-4S/740 II DM31 MSP CLO SRT	-	0°	0
910925867789	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	-	0°	0
910925867790	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	0°	-	0
910925867791	BGP703 LED120-4S/740 II DM32 MSP CLO SRT	-	0°	0
910925866542	BGP704 LED140-4S/740 DM50 GF SRT SRB 60	-	0°	0
910925866543	BGP704 LED210-4S/830 II DX10 GF D18 DDF3	-	0°	0
910925866544	BGP704 LW10 LED120-4S/830 DM11 GF CTGO	-	0°	0
910925867794	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	0°	-	0

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
910925867795	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	0°	-	0
910925866545	BGP704 LED140-4S/740 DM11 GF EZR SRB	-	0°	0
910925867142	BGP705 LED150-4S/740 DM11 GF SRT SRB 60/	-	0°	0
910925867143	BGP705 LED300-4S/740 II DM11 GF SRT SRB	-	0°	0
910925868226	BGP705 LED300-4S/740 II DM32 MSP CLO SRT	-	-	-
910925867324	BGP701 LED8-4S/740 DM11 FG GR 42/60P	-	0°	0
910925867325	BGP701 LED40-4S/740 DM10 GF SRT SRB 42/6	-	0°	0
910925867326	BGP701 LW10 LED50-4S/830 DM11 GF CTGO-DG	-	0°	0
910925867327	BGP701 LED35-4S/740 II DM11 GF EZR SRB 4	-	0°	0
910925868225	BGP701 LED60-4S/740 II DM32 MSP CLO SRT	-	-	-
910925868227	BGP701 LED40-4S/740 II DM10 MSP CLO SRT	-	-	-
910925867833	BGP702 LED50-4S/830 DM11 DDF27 D18 SRG10	0°	-	0
910925867834	BGP703 LED100-4S/830 DM11 DDF27 D18 SRG1	0°	-	0
910925867835	BGP704 LED210-4S/830 DM11 DDF27 D18 SRG1	0°	-	0
910925868042	BGP702 LED60-4S/740 DM11 PGR SRT SRB 60	-	0°	0
910925868043	BGP702 LED40-4S/740 DM10 PGR SRT SRB 60	-	0°	0
910925868044	BGP702 LW10 LED50-4S/830 DM11 PGR CTGO	-	0°	0
910925868045	BGP702 LED35-4S/740 II DM11 PGR EZR SRB	-	0°	0
910925868046	BGP703 LED120-4S/740 DM50 PGR SRT SRB 60	-	0°	0
910925868047	BGP703 LED100-4S/830 II DW50 PGR SRT SRB	-	0°	0

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
910925868048	BGP703 LED54-4S/610 DM11 PGR SRT SRB 60	-	0°	0
910925868049	BGP703 LED50-4S/740 II DM11 PGR EZR SRB	-	0°	0
910925868050	BGP704 LED140-4S/740 DM50 PGR SRT SRB 60	-	0°	0
910925868051	BGP704 LED210-4S/830 II DX10 PGR DDF3 D1	-	0°	0

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
910925868052	BGP704 LW10 LED120-4S/830 DM11 CTGO-DG	-	0°	0
910925868053	BGP704 LED140-4S/740 DM11 PGR EZR SRB 60	-	0°	0
910925868136	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	0°	-	0
910925868137	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	0°	-	0

**Mechanical and Housing**

Order Code	Full Product Name	Color
910925866534	BGP702 LED60-4S/740 DM11 GF SRT SRB 60/7	Gray
910925866535	BGP702 LED40-4S/740 DM10 GF SRT SRB 60/7	Gray
910925866536	BGP702 LW10 LED50-4S/830 DM11 GF CTGO	Gray
910925867784	BGP702 LED40-4S/740 II DM10 MSP CLO SRT	Gray
910925867785	BGP702 LED60-4S/740 II DM32 MSP CLO SRT	Gray
910925867786	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	Gray
910925867787	BGP702 LED60-4S/740 II DM11 CLO SRT SRB	Gray
910925866537	BGP702 LED35-4S/740 II DM11 GF EZR SRB 6	Gray
910925866538	BGP703 LED120-4S/740 DM50 GF SRT SRB 60	Gray
910925866539	BGP703 LED100-4S/830 II DW50 GF SRT SRB	Gray
910925866540	BGP703 LED54-4S/610 DM11 GF SRT SRB 60/7	Gray
910925866541	BGP703 LED50-4S/740 II DM11 GF EZR SRB 6	Gray
910925867788	BGP703 LED60-4S/740 II DM31 MSP CLO SRT	Gray
910925867789	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	Gray
910925867790	BGP703 LED120-4S/740 II DM11 CLO SRT SRB	Gray
910925867791	BGP703 LED120-4S/740 II DM32 MSP CLO SRT	Gray
910925866542	BGP704 LED140-4S/740 DM50 GF SRT SRB 60	Gray
910925866543	BGP704 LED210-4S/830 II DX10 GF D18 DDF3	Gray
910925866544	BGP704 LW10 LED120-4S/830 DM11 GF CTGO	Gray
910925867794	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	Gray
910925867795	BGP704 LED260-4S/740 DM11 CLO SRT SRB 48	Gray
910925866545	BGP704 LED140-4S/740 DM11 GF EZR SRB	Gray
910925867142	BGP705 LED150-4S/740 DM11 GF SRT SRB 60/	Gray
910925867143	BGP705 LED300-4S/740 II DM11 GF SRT SRB	Gray

Order Code	Full Product Name	Color
910925868226	BGP705 LED300-4S/740 II DM32 MSP CLO SRT	-
910925867324	BGP701 LED8-4S/740 DM11 FG GR 42/60P	Gray
910925867325	BGP701 LED40-4S/740 DM10 GF SRT SRB 42/6	Gray
910925867326	BGP701 LW10 LED50-4S/830 DM11 GF CTGO-DG	Gray
910925867327	BGP701 LED35-4S/740 II DM11 GF EZR SRB 4	Gray
910925868225	BGP701 LED60-4S/740 II DM32 MSP CLO SRT	-
910925868227	BGP701 LED40-4S/740 II DM10 MSP CLO SRT	-
910925867833	BGP702 LED50-4S/830 DM11 DDF27 D18 SRG10	Gray
910925867834	BGP703 LED100-4S/830 DM11 DDF27 D18 SRG1	Gray
910925867835	BGP704 LED210-4S/830 DM11 DDF27 D18 SRG1	Gray
910925868042	BGP702 LED60-4S/740 DM11 PGR SRT SRB 60	Gray
910925868043	BGP702 LED40-4S/740 DM10 PGR SRT SRB 60	Gray
910925868044	BGP702 LW10 LED50-4S/830 DM11 PGR CTGO	Gray
910925868045	BGP702 LED35-4S/740 II DM11 PGR EZR SRB	Gray
910925868046	BGP703 LED120-4S/740 DM50 PGR SRT SRB 60	Gray
910925868047	BGP703 LED100-4S/830 II DW50 PGR SRT SRB	Gray
910925868048	BGP703 LED54-4S/610 DM11 PGR SRT SRB 60	Gray
910925868049	BGP703 LED50-4S/740 II DM11 PGR EZR SRB	Gray
910925868050	BGP704 LED140-4S/740 DM50 PGR SRT SRB 60	Gray
910925868051	BGP704 LED210-4S/830 II DX10 PGR DDF3 D1	Gray
910925868052	BGP704 LW10 LED120-4S/830 DM11 CTGO-DG	Gray
910925868053	BGP704 LED140-4S/740 DM11 PGR EZR SRB 60	Gray
910925868136	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	Gray
910925868137	BGP701 LED60-4S/740 II DM11 CLO SRT SRB	Gray

