



The easy way to ledify your road lighting – UniStreet gen2

UniStreet gen2

Designed for large-scale ledification projects, the UniStreet gen2 is the ideal 1:1 luminaire replacement for municipalities. Thanks to its high efficiency and low initial cost, the UniStreet gen2 luminaire enables a fast payback and significant savings in terms of energy consumption within a short period of time. The ease of installation and maintenance is enabled by the Philips Service tag and the Philips SR (System Ready) socket makes it future-ready and you can pair this luminaire with lighting control and software applications such as Interact City. Available with a number of different optics and lumen packages that can even be tuned further to fit exact project requirements, UniStreet gen2 is a true point-to-point replacement solution for conventional light sources. The compact luminaire, using high-quality materials is also easy to dismantle and recycle at the end of its lifetime.

Benefits

- 1 to 1 replacement for conventional luminaires
- Offers high efficiency and energy savings
- Made of high-quality materials for longer lifetime and minimized maintenance

Features

- Good application coverage thanks to wide range of optics, tunable flux and tillable spigot
- Easy luminaire identification due to the Philips Service tag
- Future-ready thanks to the SR (System Ready) socket
- Luminaire is also equipped with dedicated light recipes that help with: 1) maintaining an optimal ecosystems for bats or 2) preserving a dark night sky and reduce light pollution
- Increased shock resistance with optional IK09 glass cover

UniStreet gen2

Application

- Roads and streets
- Residential streets

Versions



UniStreet gen2 Micro



UniStreet gen2 Mini



UniStreet gen2 Medium



UniStreet gen2 Large

Product details



UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2

Bottom view for spigot regulation and screw



UniStreet_LumiStreet_gen2



UniStreet gen2

Product details

UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2

UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2

UniStreet gen2 spigot regulation



UniStreet_LumiStreet_gen2

UniStreet_LumiStreet_gen2



Product details



UniStreet_LumiStreet_gen2

Approval and Application

Mech. impact protection code IK08

General Information

CE mark CE mark

Optical cover/lens type Flat glass

Driver included Yes

Flammability mark For mounting on normally flammable surfaces

Light source replaceable Yes

Service tag Yes

Light Technical

Standard tilt angle side entry 0°

Standard tilt angle posttop 0°

Upward light output ratio 0

Mechanical and Housing

Color Gray

Application Conditions

Order Code	Full Product Name	Maximum dim level
910925865663	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	0% (digital)
910925865665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	0% (digital)
910925865666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	0% (digital)
910925865667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	0% (digital)
910925865669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	0% (digital)
910925865674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	0% (digital)
910925865675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	0% (digital)
910925865687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	0% (digital)
910925865688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	0% (digital)
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	0% (digital)
910925866446	BGP391 LED50-4S/740 I DM11 SRT SRB SRG10	0% (digital)
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	0% (digital)
910925866648	BGP391 LED8-4S/740 II DM11 D948/60S	0% (digital)
910925866649	BGP391 LED20-4S/740 II DM11 D9 48/60S	0% (digital)
910925866650	BGP391 LED40-4S/740 II DM11 D9 48/60S	0% (digital)
910925866651	BGP391 LED50-4S/740 II DM11 D9 48/60S	0% (digital)
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	0% (digital)
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	0% (digital)
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	0% (digital)
910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	0% (digital)
910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	0% (digital)
910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	0% (digital)
910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	0% (digital)
910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	0% (digital)
910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	0% (digital)
910925866709	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	0% (digital)
910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	0% (digital)
910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	0% (digital)
910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	0% (digital)
910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	0% (digital)
910925866736	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	0% (digital)
910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	0% (digital)
910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	0% (digital)
910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	0% (digital)
910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	0% (digital)
910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	0% (digital)
910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	0% (digital)

Order Code	Full Product Name	Maximum dim level
910925866768	BGP281 LED45-4S/740 I DN10 48/60S	0% (digital)
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	0% (digital)
910925866784	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	0% (digital)
910925866785	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	0% (digital)
910925866815	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	0% (digital)
910925866916	BGP291 LED22-4S/740 II DM10 MSP CLO SRTH	0% (digital)
910925867829	BGP281 LED50-4S/830 I DM11 DDF27 D18 SRG	Programmable
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	Programmable
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	Programmable
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	Programmable
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	Programmable
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	Programmable
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	Programmable
910925865664	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	0% (digital)
910925865676	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	0% (digital)
910925865678	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	0% (digital)
910925866439	BGP282 LED120-4S/740 I DM11 48/60S	0% (digital)
910925866609	BGP282 LED59-4S/740 II DM50 D9 48/60S	0% (digital)
910925866653	BGP392 LED34-4S/740 II DM11 D9 48/60S	0% (digital)
910925866654	BGP392 LED60-4S/740 II DM11 D9 48/60S	0% (digital)
910925866655	BGP392 LED80-4S/740 II DM11 D9 48/60S	0% (digital)
910925866656	BGP392 LED100-4S/740 II DM11 D9 48/60S	0% (digital)
910925866677	BGP282 LED60-4S/740 I DM50 D948/60S	0% (digital)
910925866678	BGP282 LED120-4S/740 I DM50 D9 48/60S	0% (digital)
910925866691	BGP282 LED70-4S/740 I DM11 D948/60S	0% (digital)
910925866692	BGP282 LED80-4S/740 I DM11 D948/60S	0% (digital)
910925866693	BGP282 LED90-4S/740 I DM11 D948/60S	0% (digital)
910925866701	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	0% (digital)
910925866706	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	0% (digital)
910925866710	BGP282 LED70-4S/740 I DM50 D948/60S	0% (digital)
910925866741	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	0% (digital)
910925866752	BGP282 LED80-4S/740 I DM11 D948/60S	0% (digital)
910925866754	BGP282 LED70-4S/740 I DN10 48/60S	0% (digital)
910925866764	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	0% (digital)
910925866770	BGP282 LED120-4S/740 I DM11 D9 48/60S	0% (digital)
910925866790	BGP282 LED30-4S/740 I DW10 48/60S	0% (digital)
910925866794	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	0% (digital)
910925866803	BGP282 LED70-4S/740 I DM50 D948/60S	0% (digital)
910925866806	BGP282 LED100-4S/740 I DM50 48/60S	0% (digital)
910925866811	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	0% (digital)
910925866812	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	0% (digital)
910925866816	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	0% (digital)
910925867830	BGP282 LED69-4S/830 I DM11 DDF27 D18 SRG	Programmable
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	Programmable
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	Programmable
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	Programmable

Order Code	Full Product Name	Maximum dim level
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	Programmable
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	Programmable
910925865682	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	0% (digital)
910925866440	BGP283 LED240-4S/740 I DM11 48/60S	0% (digital)
910925866448	BGP393 LED240-4S/740 I DM11 SRT SRB SRG1	0% (digital)
910925866452	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	0% (digital)
910925866659	BGP393 LED100-4S/740 II DM11 D9 48/60S	0% (digital)
910925866661	BGP393 LED180-4S/740 II DM11 D9 48/60S	0% (digital)
910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	0% (digital)
910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	0% (digital)
910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	0% (digital)
910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	0% (digital)
910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	0% (digital)
910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	0% (digital)
910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	0% (digital)
910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	0% (digital)
910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	0% (digital)
910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	0% (digital)
910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	0% (digital)
910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	0% (digital)
910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	0% (digital)
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	0% (digital)
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	0% (digital)
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	0% (digital)
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	0% (digital)
910925867831	BGP283 LED190-4S/830 I DM11 DDF27 D18 SR	Programmable
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	Programmable
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	Programmable
910925866669	BGP284 LED180-4S/740 II DM11 D9 48/60S P	0% (digital)
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	0% (digital)
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	0% (digital)
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	0% (digital)
910925867832	BGP284 LED320-4S/830 I DM11 DDF27 D18 SR	Programmable
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	Programmable
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	Programmable
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	Programmable
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	Programmable
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	Programmable
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	Programmable

Approval and Application

Order Code	Full Product Name	Surge Protection (Common/Differential)	Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865663	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925865666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925865667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)	Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925865688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866709	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866446	BGP391 LED50-4S/740 I DM11 SRT SRB SRG10	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866648	BGP391 LED8-4S/740 II DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866649	BGP391 LED20-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866736	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866650	BGP391 LED40-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866651	BGP391 LED50-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866768	BGP281 LED45-4S/740 I DN10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)	Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866609	BGP282 LED59-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866784	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866653	BGP392 LED34-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866785	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866654	BGP392 LED60-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866815	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866655	BGP392 LED80-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866916	BGP291 LED22-4S/740 II DM10 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866656	BGP392 LED100-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867829	BGP281 LED50-4S/830 I DM11 DDF27 D18 SRG	Surge protection level until 10 kV	910925866677	BGP282 LED60-4S/740 I DM50 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866678	BGP282 LED120-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866691	BGP282 LED70-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866692	BGP282 LED80-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866693	BGP282 LED90-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866701	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866706	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866710	BGP282 LED70-4S/740 I DM50 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866741	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866752	BGP282 LED80-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866754	BGP282 LED70-4S/740 I DN10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865664	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866764	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925865676	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode			
910925865678	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode			
910925866439	BGP282 LED120-4S/740 I DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode			

Order Code	Full Product Name	Surge Protection (Common/Differential)	Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866770	BGP282 LED120-4S/740 I DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866448	BGP393 LED240-4S/740 I DM11 SRT SRB SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866790	BGP282 LED30-4S/740 I DW10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866452	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866794	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866659	BGP393 LED100-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866803	BGP282 LED70-4S/740 I DM50 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866661	BGP393 LED180-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866806	BGP282 LED100-4S/740 I DM50 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866811	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866812	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866816	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867830	BGP282 LED69-4S/830 I DM11 DDF27 D18 SRG	Surge protection level until 10 kV	910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level	910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865682	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode			
910925866440	BGP283 LED240-4S/740 I DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode			

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867831	BGP283 LED190-4S/830 I DM11 DDF27 D18 SR	Surge protection level until 10 kV
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925866669	BGP284 LED180-4S/740 II DM11 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867832	BGP284 LED320-4S/830 I DM11 DDF27 D18 SR	Surge protection level until 10 kV
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	Philips standard surge protection level
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	Philips standard surge protection level
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	Philips standard surge protection level
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925865663	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Yes
910925865665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	Yes
910925865666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	Yes
910925865667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	No
910925865669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	Yes
910925865674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Yes
910925865675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	Yes
910925865687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	Yes
910925865688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	Yes
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	No
910925866446	BGP391 LED50-4S/740 I DM11 SRT SRB SRG10	No
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	No
910925866648	BGP391 LED8-4S/740 II DM11 D948/60S	Yes
910925866649	BGP391 LED20-4S/740 II DM11 D9 48/60S	Yes
910925866650	BGP391 LED40-4S/740 II DM11 D9 48/60S	Yes
910925866651	BGP391 LED50-4S/740 II DM11 D9 48/60S	Yes
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	Yes
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	Yes
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	Yes
910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	Yes
910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	Yes
910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	Yes
910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	Yes

Order Code	Full Product Name	Dimmable
910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	Yes
910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	Yes
910925866709	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	Yes
910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	No
910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Yes
910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Yes
910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	Yes
910925866736	BGP281 LED60-4S/740 I DM11 DDF2 D18 48/6	Yes
910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	Yes
910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	Yes
910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	Yes
910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	Yes
910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	Yes
910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	Yes
910925866768	BGP281 LED45-4S/740 I DN10 48/60S	No
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	Yes
910925866784	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	Yes
910925866785	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	Yes
910925866815	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	Yes
910925866916	BGP291 LED22-4S/740 II DM10 MSP CLO SRTH	No
910925867829	BGP281 LED50-4S/830 I DM11 DDF27 D18 SRG	Yes
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	Yes

Order Code	Full Product Name	Dimmable
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	Yes
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	No
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	No
910925865664	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	Yes
910925865676	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	Yes
910925865678	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	Yes
910925866439	BGP282 LED120-4S/740 I DM11 48/60S	No
910925866609	BGP282 LED59-4S/740 II DM50 D9 48/60S	Yes
910925866653	BGP392 LED34-4S/740 II DM11 D9 48/60S	Yes
910925866654	BGP392 LED60-4S/740 II DM11 D9 48/60S	Yes
910925866655	BGP392 LED80-4S/740 II DM11 D9 48/60S	Yes
910925866656	BGP392 LED100-4S/740 II DM11 D9 48/60S	Yes
910925866677	BGP282 LED60-4S/740 I DM50 D948/60S	Yes
910925866678	BGP282 LED120-4S/740 I DM50 D9 48/60S	Yes
910925866691	BGP282 LED70-4S/740 I DM11 D948/60S	Yes
910925866692	BGP282 LED80-4S/740 I DM11 D948/60S	Yes
910925866693	BGP282 LED90-4S/740 I DM11 D948/60S	Yes
910925866701	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	Yes
910925866706	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	Yes
910925866710	BGP282 LED70-4S/740 I DM50 D948/60S	Yes
910925866741	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	Yes
910925866752	BGP282 LED80-4S/740 I DM11 D948/60S	Yes
910925866754	BGP282 LED70-4S/740 I DN10 48/60S	No
910925866764	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	Yes
910925866770	BGP282 LED120-4S/740 I DM11 D9 48/60S	Yes
910925866790	BGP282 LED30-4S/740 I DW10 48/60S	No
910925866794	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	No
910925866803	BGP282 LED70-4S/740 I DM50 D948/60S	Yes
910925866806	BGP282 LED100-4S/740 I DM50 48/60S	No
910925866811	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	Yes
910925866812	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	Yes
910925866816	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	Yes
910925867830	BGP282 LED69-4S/830 I DM11 DDF27 D18 SRG	Yes
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes

Order Code	Full Product Name	Dimmable
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	No
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	No
910925865682	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	Yes
910925866440	BGP283 LED240-4S/740 I DM11 48/60S	No
910925866448	BGP393 LED240-4S/740 I DM11 SRT SRB SRG1	No
910925866452	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	No
910925866659	BGP393 LED100-4S/740 II DM11 D9 48/60S	Yes
910925866661	BGP393 LED180-4S/740 II DM11 D9 48/60S	Yes
910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	Yes
910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	Yes
910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	Yes
910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	Yes
910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	Yes
910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	Yes
910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	Yes
910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	Yes
910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	Yes
910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	Yes
910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	Yes
910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	Yes
910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	No
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	Yes
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	Yes
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	Yes
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	Yes
910925867831	BGP283 LED190-4S/830 I DM11 DDF27 D18 SR	Yes
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	Yes
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes
910925866669	BGP284 LED180-4S/740 II DM11 D9 48/60S P	Yes
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	Yes
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	Yes
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	Yes
910925867832	BGP284 LED320-4S/830 I DM11 DDF27 D18 SR	Yes
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	No
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	Yes
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	Yes
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	Yes
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	Yes
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	Yes

General Information (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925865663	BGP281 LED25-4S/740 I	68° x 158°	740 neutral white	LED25	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
	DN10 DDF2 D18 SRG1				

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925865665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED40	1 unit
910925865666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED50	1 unit
910925865667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	68° x 158°	740 neutral white	LED25	1 unit
910925865669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED60	1 unit
910925865674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	LED25	1 unit
910925865675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	53° x 71°	740 neutral white	LED45	1 unit
910925865687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	160° - 42° x 54°	740 neutral white	LED35	1 unit
910925865688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	68° x 158°	740 neutral white	LED40	1 unit
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	LED50	1 unit
910925866446	BGP391 LED50-4S/740 I DM11 SRT SRB SRG10	160° - 42° x 54°	740 neutral white	LED50	1 unit
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	160° - 42° x 54°	740 neutral white	LED50	1 unit
910925866648	BGP391 LED8-4S/740 II DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED8	1 unit
910925866649	BGP391 LED20-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED20	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866650	BGP391 LED40-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED40	1 unit
910925866651	BGP391 LED50-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED50	1 unit
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	LED16	1 unit
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	LED20	1 unit
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	LED25	1 unit
910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	LED54	1 unit
910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED20	1 unit
910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED30	1 unit
910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED40	1 unit
910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED60	1 unit
910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	68° x 158°	830 warm white	LED40	1 unit
910925866709	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	160° - 42° x 54°	740 neutral white	LED40	1 unit
910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	68° x 158°	740 neutral white	LED20	1 unit
910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	68° x 158°	830 warm white	LED45	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	68° x 158°	830 warm white	LED45	1 unit
910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	157° - 33° x 55°	830 warm white	LED30	1 unit
910925866736	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	160° - 42° x 54°	740 neutral white	LED60	1 unit
910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	LED54	1 unit
910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED20	1 unit
910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	LED35	1 unit
910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	68° x 158°	830 warm white	LED50	1 unit
910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	160° - 42° x 54°	830 warm white	LED40	1 unit
910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	160° - 42° x 54°	740 neutral white	LED20	1 unit
910925866768	BGP281 LED45-4S/740 I DN10 48/60S	68° x 158°	740 neutral white	LED45	1 unit
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	157° - 33° x 55°	740 neutral white	LED45	1 unit
910925866784	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	160° - 42° x 54°	740 neutral white	LED60	1 unit
910925866785	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	LED40	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866815	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	160° - 42° x 54°	740 neutral white	LED16	1 unit
910925866916	BGP291 LED22-4S/740 II DM10 MSP CLO SRTH	157° - 33° x 55°	740 neutral white	LED22	1 unit
910925867829	BGP281 LED50-4S/830 I DM11 DDF27 D18 SRG	160° - 42° x 54°	830 warm white	LED50	1 unit
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED20	1 unit
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED20	1 unit
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED25	1 unit
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED25	1 unit
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED35	1 unit
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED35	1 unit
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED45	1 unit
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED45	1 unit
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	154° - 31° x 54°	730 warm white	LED51	1 unit
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	154° - 31° x 54°	730 warm white	LED51	1 unit
910925865664	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	157° - 33° x 55°	740 neutral white	LED100	1 unit
910925865676	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	157° - 33° x 55°	740 neutral white	LED120	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925865678	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED70	1 unit
910925866439	BGP282 LED120-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	LED120	1 unit
910925866609	BGP282 LED59-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED59	1 unit
910925866653	BGP392 LED34-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED34	1 unit
910925866654	BGP392 LED60-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED60	1 unit
910925866655	BGP392 LED80-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED80	1 unit
910925866656	BGP392 LED100-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED100	1 unit
910925866677	BGP282 LED60-4S/740 I DM50 D948/60S	154° - 31° x 54°	740 neutral white	LED60	1 unit
910925866678	BGP282 LED120-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED120	1 unit
910925866691	BGP282 LED70-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED70	1 unit
910925866692	BGP282 LED80-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED80	1 unit
910925866693	BGP282 LED90-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED90	1 unit
910925866701	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED80	1 unit
910925866706	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED60	1 unit
910925866710	BGP282 LED70-4S/740 I DM50 D948/60S	154° - 31° x 54°	740 neutral white	LED70	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866741	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	LED54	1 unit
910925866752	BGP282 LED80-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED80	1 unit
910925866754	BGP282 LED70-4S/740 I DN10 48/60S	68° x 158°	740 neutral white	LED70	1 unit
910925866764	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	68° x 158°	830 warm white	LED69	1 unit
910925866770	BGP282 LED120-4S/740 I DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED120	1 unit
910925866790	BGP282 LED30-4S/740 I DW10 48/60S	61° x 150°	740 neutral white	LED30	1 unit
910925866794	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	160° - 42° x 54°	830 warm white	LED70	1 unit
910925866803	BGP282 LED70-4S/740 I DM50 D948/60S	154° - 31° x 54°	740 neutral white	LED70	1 unit
910925866806	BGP282 LED100-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED100	1 unit
910925866811	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	61° x 150°	740 neutral white	LED64	1 unit
910925866812	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	160° - 42° x 54°	830 warm white	LED74	1 unit
910925866816	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	160° - 42° x 54°	740 neutral white	LED100	1 unit
910925867830	BGP282 LED69-4S/830 I DM11 DDF27 D18 SRG	160° - 42° x 54°	830 warm white	LED69	1 unit
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED35	1 unit
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED35	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED45	1 unit
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED45	1 unit
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED54	1 unit
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED64	1 unit
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	154° - 31° x 54°	730 warm white	LED100	1 unit
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	154° - 31° x 54°	730 warm white	LED100	1 unit
910925866682	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	157° - 33° x 55°	740 neutral white	LED149	1 unit
910925866440	BGP283 LED240-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	LED240	1 unit
910925866448	BGP393 LED240-4S/740 I DM11 SRT SRB SRG1	160° - 42° x 54°	740 neutral white	LED240	1 unit
910925866452	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	160° - 42° x 54°	740 neutral white	LED240	1 unit
910925866659	BGP393 LED100-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED100	1 unit
910925866661	BGP393 LED180-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED180	1 unit
910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED70	1 unit
910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED80	1 unit
910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED90	1 unit
910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED100	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED120	1 unit
910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED139	1 unit
910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED149	1 unit
910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED160	1 unit
910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED149	1 unit
910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED149	1 unit
910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED139	1 unit
910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	53° x 71°	740 neutral white	LED139	1 unit
910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	150° - 43° x 67°	740 neutral white	LED200	1 unit
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED100	1 unit
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	68° x 158°	830 warm white	LED100	1 unit
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED120	1 unit
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED120	1 unit
910925867831	BGP283 LED190-4S/830 I DM11 DDF27 D18 SR	160° - 42° x 54°	830 warm white	LED190	1 unit
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED60	1 unit
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED80	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED100	1 unit
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED120	1 unit
910925866669	BGP284 LED180-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	LED180	2 units
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	LED240	2 units
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	LED280	2 units
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	LED340	2 units
910925867832	BGP284 LED320-4S/830 I DM11 DDF27 D18 SR	160° - 42° x 54°	830 warm white	LED320	2 units

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED150	2 units
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED300	2 units
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED400	2 units
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED150	2 units
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED300	2 units
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED400	2 units

General Information (2/2)

Order Code	Full Product Name	Optic type	Product Family Code
910925866663	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP281
910925866665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP281
910925866666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP281
910925866667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	Distribution narrow 10	BGP281
910925866669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP281
910925866674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP281
910925866675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	Distribution medium 12	BGP281
910925866687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	Distribution medium 11	BGP281
910925866688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	Distribution narrow 10	BGP281
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	Distribution medium 11	BGP281
910925866446	BGP391 LED50-4S/740 I DM11 SRT SRB SRG10	Distribution medium 11	BGP391

Order Code	Full Product Name	Optic type	Product Family Code
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	Distribution medium 11	BGP281
910925866648	BGP391 LED8-4S/740 II DM11 D948/60S	Distribution medium 11	BGP391
910925866649	BGP391 LED20-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP391
910925866650	BGP391 LED40-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP391
910925866651	BGP391 LED50-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP391
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	Distribution medium 10	BGP281
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	Distribution medium 10	BGP281
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	Distribution medium 10	BGP281
910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	Distribution medium 10	BGP281
910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	Distribution medium 11	BGP281
910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	Distribution medium 11	BGP281

Order Code	Full Product Name	Optic type	Product Family Code
910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	Distribution medium 11	BGP281
910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	Distribution medium 11	BGP281
910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	Distribution narrow 10	BGP281
910925866709	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	Distribution medium 11	BGP281
910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	Distribution narrow 10	BGP281
910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Distribution narrow 10	BGP281
910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Distribution narrow 10	BGP281
910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	Distribution medium 10	BGP281
910925866736	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	Distribution medium 11	BGP281
910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP281
910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP281
910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP281
910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	Distribution narrow 10	BGP281
910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	Distribution medium 11	BGP281
910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	Distribution medium 11	BGP281
910925866768	BGP281 LED45-4S/740 I DN10 48/60S	Distribution narrow 10	BGP281
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	Distribution medium 10	BGP281
910925866784	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	Distribution medium 11	BGP281
910925866785	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP281
910925866815	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	Distribution medium 11	BGP281
910925866916	BGP291 LED22-4S/740 II DM10 MSP CLO SRTH	Distribution medium 10	BGP291
910925867829	BGP281 LED50-4S/830 I DM11 DDF27 D18 SRG	Distribution medium 11	BGP281
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291

Order Code	Full Product Name	Optic type	Product Family Code
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	Distribution medium 50	BGP291
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	Distribution medium 50	BGP291
910925865664	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	Distribution medium 10	BGP282
910925865676	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	Distribution medium 10	BGP282
910925865678	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP282
910925866439	BGP282 LED120-4S/740 I DM11 48/60S	Distribution medium 11	BGP282
910925866609	BGP282 LED59-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP282
910925866653	BGP392 LED34-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP392
910925866654	BGP392 LED60-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP392
910925866655	BGP392 LED80-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP392
910925866656	BGP392 LED100-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP392
910925866677	BGP282 LED60-4S/740 I DM50 D948/60S	Distribution medium 50	BGP282
910925866678	BGP282 LED120-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP282
910925866691	BGP282 LED70-4S/740 I DM11 D948/60S	Distribution medium 11	BGP282
910925866692	BGP282 LED80-4S/740 I DM11 D948/60S	Distribution medium 11	BGP282
910925866693	BGP282 LED90-4S/740 I DM11 D948/60S	Distribution medium 11	BGP282
910925866701	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP282
910925866706	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP282
910925866710	BGP282 LED70-4S/740 I DM50 D948/60S	Distribution medium 50	BGP282
910925866741	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP282

Order Code	Full Product Name	Optic type	Product Family Code
910925866752	BGP282 LED80-4S/740 I DM11 D948/60S	Distribution medium 11	BGP282
910925866754	BGP282 LED70-4S/740 I DN10 48/60S	Distribution narrow 10	BGP282
910925866764	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	Distribution narrow 10	BGP282
910925866770	BGP282 LED120-4S/740 I DM11 D9 48/60S	Distribution medium 11	BGP282
910925866790	BGP282 LED30-4S/740 I DW10 48/60S	Distribution wide 10	BGP282
910925866794	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	Distribution medium 11	BGP282
910925866803	BGP282 LED70-4S/740 I DM50 D948/60S	Distribution medium 50	BGP282
910925866806	BGP282 LED100-4S/740 I DM50 48/60S	Distribution medium 50	BGP282
910925866811	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	Distribution wide 10	BGP282
910925866812	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	Distribution medium 11	BGP282
910925866816	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	Distribution medium 11	BGP282
910925867830	BGP282 LED69-4S/830 I DM11 DDF27 D18 SRG	Distribution medium 11	BGP282
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	Distribution medium 50	BGP292
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	Distribution medium 50	BGP292
910925865682	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	Distribution medium 10	BGP283
910925866440	BGP283 LED240-4S/740 I DM11 48/60S	Distribution medium 11	BGP283
910925866448	BGP393 LED240-4S/740 I DM11 SRT SRB SRG1	Distribution medium 11	BGP393
910925866452	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	Distribution medium 11	BGP283
910925866659	BGP393 LED100-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP393

Order Code	Full Product Name	Optic type	Product Family Code
910925866661	BGP393 LED180-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP393
910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	Distribution medium 11	BGP283
910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP283
910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP283
910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	Distribution medium 12	BGP283
910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	Distribution extra wide 10	BGP283
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP283
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	Distribution narrow 10	BGP283
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP283
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925867831	BGP283 LED190-4S/830 I DM11 DDF27 D18 SR	Distribution medium 11	BGP283
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP293
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP293
91092586809	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11	BGP293
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11	BGP293
910925866669	BGP284 LED180-4S/740 II DM11 D9 48/60S P	Distribution medium 11	BGP284
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	Distribution medium 11	BGP284

Order Code	Full Product Name	Optic type	Product Family Code
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	Distribution medium 11	BGP284
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	Distribution medium 11	BGP284
910925867832	BGP284 LED320-4S/830 I DM11 DDF27 D18 SR	Distribution medium 11	BGP284
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	Distribution medium 11	BGP294
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	Distribution medium 11	BGP294

Order Code	Full Product Name	Optic type	Product Family Code
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	Distribution medium 11	BGP294
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11	BGP294
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11	BGP294
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11	BGP294

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865663	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	2250 lm
910925865665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	3432 lm
910925865666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	4312 lm
910925865667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	4000 K	70	2250 lm
910925865669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	5104 lm
910925865674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	2250 lm
910925865675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	4000 K	70	4005 lm
910925865687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	4000 K	70	3115 lm
910925865688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	4000 K	70	3600 lm
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	4000 K	70	4450 lm
910925866446	BGP391 LED50-4S/740 I DM11 SRT SRB SRG10	4000 K	70	4450 lm
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	4000 K	70	4450 lm
910925866648	BGP391 LED8-4S/740 II DM11 D948/60S	4000 K	70	712 lm
910925866649	BGP391 LED20-4S/740 II DM11 D9 48/60S	4000 K	70	1780 lm
910925866650	BGP391 LED40-4S/740 II DM11 D9 48/60S	4000 K	70	3560 lm
910925866651	BGP391 LED50-4S/740 II DM11 D9 48/60S	4000 K	70	4450 lm
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	4000 K	70	1424 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	4000 K	70	1780 lm
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	4000 K	70	2225 lm
910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	4000 K	70	4752 lm
910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	4000 K	70	1780 lm
910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	4000 K	70	2670 lm
910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	4000 K	70	3560 lm
910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	4000 K	70	5280 lm
910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	3000 K	80	3560 lm
910925866709	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	4000 K	70	3471 lm
910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	4000 K	70	1800 lm
910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	3000 K	80	3960 lm
910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	3000 K	80	3960 lm
910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	3000 K	80	2670 lm
910925866736	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	4000 K	70	5280 lm
910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	4806 lm
910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	1735.5 lm
910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	3150 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	3000 K	80	4400 lm
910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	3000 K	80	3560 lm
910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	4000 K	70	1735.5 lm
910925866768	BGP281 LED45-4S/740 I DN10 48/60S	4000 K	70	4005 lm
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	4000 K	70	3960 lm
910925866784	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	4000 K	70	5162 lm
910925866785	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	3600 lm
910925866815	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	4000 K	70	1424 lm
910925866916	BGP291 LED22-4S/740 II DM10 MSP CLO SRTH	4000 K	70	1869 lm
910925867829	BGP281 LED50-4S/830 I DM11 DDF27 D18 SRG	3000 K	80	4400 lm
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	1735.5 lm
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	1735.5 lm
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2136 lm
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2225 lm
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3026 lm
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3026 lm
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3916 lm
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3827 lm
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	3000 K	70	4524 lm
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	3000 K	70	4524 lm
910925865664	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	4000 K	70	8526 lm
910925865676	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	4000 K	70	9890 lm
910925865678	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	5984 lm
910925866439	BGP282 LED120-4S/740 I DM11 48/60S	4000 K	70	10440 lm
910925866609	BGP282 LED59-4S/740 II DM50 D9 48/60S	4000 K	70	5160 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866653	BGP392 LED34-4S/740 II DM11 D9 48/60S	4000 K	70	3026 lm
910925866654	BGP392 LED60-4S/740 II DM11 D9 48/60S	4000 K	70	5280 lm
910925866655	BGP392 LED80-4S/740 II DM11 D9 48/60S	4000 K	70	7040 lm
910925866656	BGP392 LED100-4S/740 II DM11 D9 48/60S	4000 K	70	8800 lm
910925866677	BGP282 LED60-4S/740 I DM50 D948/60S	4000 K	70	5160 lm
910925866678	BGP282 LED120-4S/740 I DM50 D9 48/60S	4000 K	70	10200 lm
910925866691	BGP282 LED70-4S/740 I DM11 D948/60S	4000 K	70	6230 lm
910925866692	BGP282 LED80-4S/740 I DM11 D948/60S	4000 K	70	7040 lm
910925866693	BGP282 LED90-4S/740 I DM11 D948/60S	4000 K	70	7920 lm
910925866701	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	6612 lm
910925866706	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	5104 lm
910925866710	BGP282 LED70-4S/740 I DM50 D948/60S	4000 K	70	6090 lm
910925866741	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	4806 lm
910925866752	BGP282 LED80-4S/740 I DM11 D948/60S	4000 K	70	7040 lm
910925866754	BGP282 LED70-4S/740 I DN10 48/60S	4000 K	70	6230 lm
910925866764	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	3000 K	80	6160 lm
910925866770	BGP282 LED120-4S/740 I DM11 D9 48/60S	4000 K	70	10440 lm
910925866790	BGP282 LED30-4S/740 I DW10 48/60S	4000 K	70	2670 lm
910925866794	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	3000 K	80	6160 lm
910925866803	BGP282 LED70-4S/740 I DM50 D948/60S	4000 K	70	6090 lm
910925866806	BGP282 LED100-4S/740 I DM50 48/60S	4000 K	70	8600 lm
910925866811	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	4000 K	70	5632 lm
910925866812	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	3000 K	80	6438 lm
910925866816	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	4000 K	70	8800 lm
910925867830	BGP282 LED69-4S/830 I DM11 DDF27 D18 SRG	3000 K	80	6160 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3026 lm
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3026 lm
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3916 lm
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3827 lm
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	4628 lm
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	5456 lm
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	3000 K	70	8600 lm
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	3000 K	70	8600 lm
910925866682	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	4000 K	70	12615 lm
910925866440	BGP283 LED240-4S/740 I DM11 48/60S	4000 K	70	20640 lm
910925866448	BGP393 LED240-4S/740 I DM11 SRT SRB SRG1	4000 K	70	20640 lm
910925866452	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	4000 K	70	20640 lm
910925866659	BGP393 LED100-4S/740 II DM11 D9 48/60S	4000 K	70	8900 lm
910925866661	BGP393 LED180-4S/740 II DM11 D9 48/60S	4000 K	70	15660 lm
910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	4000 K	70	6160 lm
910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	4000 K	70	7040 lm
910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	4000 K	70	7830 lm
910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	4000 K	70	8700 lm
910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	4000 K	70	10440 lm
910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	4000 K	70	12040 lm
910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	4000 K	70	12900 lm
910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	4000 K	70	14080 lm
910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	4000 K	70	12900 lm
910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	4000 K	70	12900 lm
910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	4000 K	70	12040 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	4000 K	70	12320 lm
910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	4000 K	70	16800 lm
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	4000 K	70	8700 lm
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	3000 K	80	8900 lm
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	4000 K	70	10440 lm
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	4000 K	70	10440 lm
910925867831	BGP283 LED190-4S/830 I DM11 DDF27 D18 SR	3000 K	80	16340 lm
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	5162 lm
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	6942 lm
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	8722 lm
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	10235 lm
910925866669	BGP284 LED180-4S/740 II DM11 D9 48/60S P	4000 K	70	16020 lm
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	4000 K	70	21120 lm
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	4000 K	70	24360 lm
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	4000 K	70	29240 lm
910925867832	BGP284 LED320-4S/830 I DM11 DDF27 D18 SR	3000 K	80	26880 lm
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	4000 K	70	13350 lm
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	4000 K	70	25230 lm
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	4000 K	70	32300 lm
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	13350 lm
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	25230 lm
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	32300 lm

