

The professional LED HID replacement lamp, instant retrofit, instant savings.

LED Wallpack Retrofits

Philips LED HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Benefits

- Energy savings up to >70%
- Longer lifetime and less maintenance cost
- Adjustable light direction enable to use in a variety of applications

Features

- Standard E26/EX39 base to replace metal halide lamps and E39 options
- Available in 3000K, 4000K and 5000K CCTs
- 360o Rotatable lamp cap
- Available in ranges between 70W and 175W replacements options and upto 9,000 lumens
- 3-year limited warranty

Application

- Design for horizontal application
- Wall packs, Shoeboxes, Post-Top fixtures
- Parking lots, public areas and office outdoor fixtures

LED Wallpack Retrofits


Versions



Single Contact Medium Screw Wall
Pack Clear





Exclusionary Mogul Screw Wall
Pack Clear



Exclusionary Mogul Screw Wall
Pack Clear

Dimensional drawing




Product	D	C
60WP/LED/840/ND EX39 G2 BB 6/1	92 mm	270 mm
60WP/LED/850/ND EX39 G2 BB 6/1	92 mm	270 mm

Product	D	C
20WP/LED/840/ND E26 G2 BB 6/1	92 mm	135 mm
20WP/LED/830/ND E26 G2 BB 6/1	92 mm	135 mm
20WP/LED/850/ND E26 G2 BB 6/1	92 mm	135 mm

LED Wallpack Retrofits

Dimensional drawing



Product	D	C
40WP/LED/850/ND EX39 G2 BB 6/1	92 mm	215 mm
40WP/LED/840/ND EX39 G2 BB 6/1	92 mm	215 mm

Approval and Application	
Energy Efficiency Label (EEL)	A++
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Frequency	50 to 60 Hz
Voltage (Nom)	100-277 V
Starting Time (Nom)	1 s
General Information	
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Light Technical	
Color Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	Wall Pack

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002397904	20WP/LED/830/ND E26 G2 BB 6/1	20 kWh
929002398004	20WP/LED/840/ND E26 G2 BB 6/1	20 kWh
929002398104	20WP/LED/850/ND E26 G2 BB 6/1	20 kWh
929002398204	40WP/LED/840/ND EX39 G2 BB 6/1	40 kWh
929002398304	40WP/LED/850/ND EX39 G2 BB 6/1	40 kWh
929002398404	60WP/LED/840/ND EX39 G2 BB 6/1	60 kWh
929002398504	60WP/LED/850/ND EX39 G2 BB 6/1	60 kWh

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
929002397904	20WP/LED/830/ND E26 G2 BB 6/1	20 W
929002398004	20WP/LED/840/ND E26 G2 BB 6/1	20 W
929002398104	20WP/LED/850/ND E26 G2 BB 6/1	20 W
929002398204	40WP/LED/840/ND EX39 G2 BB 6/1	40 W

Order Code	Full Product Name	Power (Rated) (Nom)
929002398304	40WP/LED/850/ND EX39 G2 BB 6/1	40 W
929002398404	60WP/LED/840/ND EX39 G2 BB 6/1	60 W
929002398504	60WP/LED/850/ND EX39 G2 BB 6/1	60 W

General Information

Order Code	Full Product Name	Cap-Base
929002397904	20WP/LED/830/ND E26 G2 BB 6/1	E26
929002398004	20WP/LED/840/ND E26 G2 BB 6/1	E26
929002398104	20WP/LED/850/ND E26 G2 BB 6/1	E26
929002398204	40WP/LED/840/ND EX39 G2 BB 6/1	EX39

Order Code	Full Product Name	Cap-Base
929002398304	40WP/LED/850/ND EX39 G2 BB 6/1	EX39
929002398404	60WP/LED/840/ND EX39 G2 BB 6/1	EX39
929002398504	60WP/LED/850/ND EX39 G2 BB 6/1	EX39

LED Wallpack Retrofits

Light Technical

Order Code	Full Product Name	Color Code	Correlated Color	
			Temperature (Nom)	Luminous Flux (Nom)
929002397904	20WP/LED/830/ND E26 G2 BB 6/1	830	3000 K	2800 lm
929002398004	20WP/LED/840/ND E26 G2 BB 6/1	840	4000 K	2900 lm
929002398104	20WP/LED/850/ND E26 G2 BB 6/1	850	5000 K	3000 lm
929002398204	40WP/LED/840/ND EX39 G2 BB 6/1	840	4000 K	5800 lm

Order Code	Full Product Name	Color Code	Correlated Color	
			Temperature (Nom)	Luminous Flux (Nom)
929002398304	40WP/LED/850/ND EX39 G2 BB 6/1	850	5000 K	6000 lm
929002398404	60WP/LED/840/ND EX39 G2 BB 6/1	840	4000 K	8700 lm
929002398504	60WP/LED/850/ND EX39 G2 BB 6/1	850	5000 K	9000 lm

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002397904	20WP/LED/830/ND E26 G2 BB 6/1	60 °C
929002398004	20WP/LED/840/ND E26 G2 BB 6/1	60 °C
929002398104	20WP/LED/850/ND E26 G2 BB 6/1	60 °C
929002398204	40WP/LED/840/ND EX39 G2 BB 6/1	65 °C
929002398304	40WP/LED/850/ND EX39 G2 BB 6/1	65 °C
929002398404	60WP/LED/840/ND EX39 G2 BB 6/1	65 °C
929002398504	60WP/LED/850/ND EX39 G2 BB 6/1	65 °C

