



# OptiVision MVP507

## MVP507 MHN-LA2000W/956 400V WB SI

OPTIVISION - MASTER MHN-LA - 2000 W - Wide beam

OptiVision is an asymmetric downlighting luminaire that combines compact dimensions with very high efficiency. Available with narrow, medium and wide beams for flexibility in application, it provides excellent control of spill light and limitation of glare and upward leakage of light. OptiVision can accommodate metal-halide lamps for good colour rendering or high-pressure sodium lamps for economical operation. Excellent spill-light control, limitation of glare and upward leakage of light is secured by asymmetric optics that achieve peak intensity at 60° and a sharp cut-off of light at 80°. The MHN-LA/FC lamps guarantee pleasant and natural colour rendering and comfortable atmosphere.

### Product data

| General Information         |  | Product family code                 |   |
|-----------------------------|--|-------------------------------------|---|
| Number of light sources     | 1 [ 1 pc]  |                                     | MVP507 [ OPTIVISION]                          |
| Lamp family code            | MHN-LA [ MASTER MHN-LA]  | Operating and Electrical            |   |
| Lamp power                  | 2000 W   | Lamp supply voltage                 | 400 V [ 400]                                  |
| Light source colour         | 956 daylight   | Input Voltage                       | 400 V   |
| Kombipack                   | Lamp(s) included   | Ignitor                             | SI [ Series]                                  |
| Protection class IEC        | Safety class I   | Mechanical and Housing              |   |
| CE mark                     | CE mark  | Colour                              | Aluminium                                     |
| ENEC mark                   | -  | Dimensions (height x width x depth) | NaN x NaN x NaN mm (NaN x NaN x NaN in)       |
| Ball impact resistance mark | Ball Impact Resistance mark  | Approval and Application            |   |
| Mechanical accessories      | No [ -]  | Ingress protection code             | IP65 [ Dust penetration-protected, jet-proof] |
| Optic type outdoor          | Wide beam  | Mech. impact protection code        | IK08 [ 5 J vandal-protected]                  |
| Serviceability class        | Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts |                                     |   |

# OptiVision MVP507


## Product Data

|                               |                                   |
|-------------------------------|-----------------------------------|
| Full product code             | 871155915207300                   |
| Order product name            | MVP507 MHN-LA2000W/956 400V WB SI |
| EAN/UPC – product             | 8711559152073                     |
| Order code                    | 15207300                          |
| Local code                    | MVP5072KW956WB                    |
| Numerator – quantity per pack | 1                                 |


SAP numerator – packs per outer box 1

Material no. (12 NC) 910400188812

SAP net weight (piece) 17.200 kg



## Dimensional drawing



OptiVision MVP507

