



# Metronomis LED Fluid

## BDS670 LED20-4S/740 I MDM D9 STD 60

Metronomis LED - LED Module 2000 lm - LED - 740 neutral white - Power supply unit with DALI interface - 220 to 240 V - 50 to 60 Hz - Safety class I - Metronomis distribution medium - Polycarbonate bowl/cover - Grey - Surge protection level up to 10 kV - - - Spigot for diameter 60 mm

Metronomis LED is the first post-top range in the world to offer a palette of environmental lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow creates an environmental pattern on the ground or on the bowl to create additional ambience. Four new iconic designs – with a visual and modular link to Metronomis I – are reduced to the essential elements. During the day, the discreet, transparent design blends into its context, be it contemporary or classical, while its night-time appearance is both functional and decorative. The flexible, modular Metronomis LED comes with a range of columns and a wide variety of optics and effects, enabling architects and lighting designers to create a unified, consistent lighting design that still reflects the differences in urban culture and history.

### Product data

General Information			
Lamp family code	LED20 [ LED Module 2000 lm]	Control interface	DALI
Light source colour	740 neutral white	Connection	Screw connector
Light source replaceable	Yes	Cable	-
Number of gear units	1 unit	Protection class IEC	Safety class I
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]	Flammability mark	NO [ -]
Driver included	Yes	CE mark	CE mark
Optical cover/lens type	PC [ Polycarbonate bowl/cover]	ENEC mark	ENEC mark
Luminaire light beam spread	48° x 66°	Warranty period	5 years
		Optic type outdoor	Metronomis distribution medium

# Metronomis LED Fluid

Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	No
Number of products on MCB (16 A type B)	26
EU RoHS compliant	Yes
LED engine type	LED
Serviceability class	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Product family code	BDS670 [ Metronomis LED]

## Light Technical

Upward light output ratio	4.92
Standard tilt angle post-top	-
Standard tilt angle side entry	-

## Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.225 ms
Power factor (min.)	0.92

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Housing material	Aluminium
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Mounting device	60 [ Spigot for diameter 60 mm]
Optical cover/lens shape	-
Optical cover/lens finish	-
Overall height	990 mm
Overall diameter	560 mm
Effective projected area	0.4396 m <sup>2</sup>
Colour	Grey

Dimensions (height x width x depth)	990 x NaN x NaN mm (39 x NaN x NaN in)
-------------------------------------	--

## Approval and Application

Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Surge protection (common/differential)	Surge protection level up to 10 kV

## Initial Performance (IEC Compliant)

Initial luminous flux	1700 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	131 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	≥70
Initial chromaticity	(0.3818, 0.3796) SDCM <5
Initial input power	13 W
Power consumption tolerance	+/-11%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L98

## Application Conditions

Ambient temperature range	-40 to +50 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Programmable


## Product Data

Full product code	871951419964400
Order product name	BDS670 LED20-4S/740 I MDM D9 STD 60
EAN/UPC – product	8719514199644
Order code	19964400
Numerator – quantity per pack	1
SAP numerator – packs per outer box	1
Material no. (12 NC)	910925868169
SAP net weight (piece)	16.610 kg




# Metronomis LED Fluid

## Dimensional drawing




Metronomis LED BDS650-670

## Photometric data



OFPL1\_BDS670T251xLED20-4S740MDM



OFPC1\_BDS670T251xLED20-4S740MDM

