



# GreenPerform Waterproof G3

## WT198C LED40S/840 PSU L1200 CL

Power supply unit - - - - 114°

GreenPerform Waterproof G3 provides excellent optics with reliable performance, easy installation and maintenance

### Product data

General Information	
Beam angle of light source	120°
Lamp colour code	840 neutral white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSU [ Power supply unit]
Driver included	Yes
Optic type	No [-]
Optical cover/lens type	No [-]
Luminaire light beam spread	114°
Control interface	-
Connection	No [-]
Cable	-
Protection class IEC	Safety class I (I)
Glow-wire test	850/30 [ Temperature 850 °C, duration 30 s]
Flammability mark	NO [-]
CE mark	CE mark
ENEC mark	-
Constant light output	No
Number of products on MCB (16 A type B)	24

EU RoHS compliant	No
LED engine type	LED

### Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 or 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	5.16 A
Inrush time	47 ms
Power factor (min.)	0.9

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate

## GreenPerform Waterproof G3

Fixation material	Stainless steel
Optical cover/lens finish	Opal
Overall length	1215 mm
Overall width	80 mm
Overall height	85 mm
Overall diameter	80 mm
Colour	Grey

### Approval and Application

Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [ 5 J vandal-protected]

### Initial Performance (IEC Compliant)

Initial luminous flux	4000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	140 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	>80
Initial chromaticity	(0.38,0.38)
Initial input power	28.6 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)


Median useful life L70B50	50000 h
Median useful life L80B50	42000 h
Median useful life L90B50	20000 h

### Application Conditions


Ambient temperature range	-25 to +40 °C
Maximum dimming level	Not applicable

### Product Data

Full product code	871016335894999
Order product name	WT198C LED40S/840 PSU L1200 CL
EAN/UPC – product	8710163358949
Order code	911401552261
Local code	WT194084P12
Numerator – quantity per pack	1
SAP numerator – packs per outer box	9
Material no. (12 NC)	911401552261
SAP net weight (piece)	1.400 kg



## Dimensional drawing



WT188C/WL020C

