



LineBase

EGP472 220/30W 4/7 210W

LineBase - Aluminum

LineBase is breakthrough lighting for the city tunnel, underpass. It's a really and amazingly linear lighting yet easy to install, and it's the ideal solution to replace fluorescent lighting. The customized lumen output of LineBase enables lighting designers to have freedom on lighting layout. Its continuous installation is to create a seamless, brighter, comfortable visual effect with less flicker. Its plug-and-play electrical connection and remote waterproof drivers save total cost of owner. The products pass kinds of safety and durability test to prove a long lifespan on its operation.

Warnings and Safety

- Strongly recommended to use surge protection device in electricity cabinet to wire luminaires

Product data

General Information	
Protection class IEC	Safety class I
CE mark	CE mark
Material	Aluminum
Accessory color	Aluminum

Operating and Electrical	
Input Voltage	220 to 240 V
Input Frequency	50 or 60 Hz

Mechanical and Housing	
Overall length	230 mm
Overall width	69 mm

Overall height	45 mm
----------------	-------

Approval and Application	
Ingress protection code	IP67 [Dust penetration-protected, watertight]

Product Data	
Full product code	911401682005
Order product name	EGP472 220/30W 4/7 210W
Order code	911401682005
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	911401682005
Net Weight (Piece)	0.160 kg

