



# Greenperform Batten

## BN208X LED60/NW L1500 ACW2 OS ACF EN

LED Module, system flux 6000 lm - - - Power supply unit with DALI interface - Wide beam - Opal - 110°

GreenPerform Batten BN208C Dali is a high quality LED batten that delivers significant energy savings of up to 50% comparing to conventional T8 battens. BN208X incorporates the reliable structure, long lifetime LED lighting, and the global standard ZigBee control system, to achieve an easy-to-use networked solution. In the mean time, it helps to further increase energy saving maximum to 80% with daylight harvest and occupancy sensor.

### Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress and as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

### Product data

General Information			
Lamp family code	LED60S [ LED Module, system flux 6000 lm]	Control interface	DALI
Lamp colour code	Neutral white	Connection	SI [ Screw connection block]
Light source replaceable	No	Protection class IEC	Safety class I (I)
Number of gear units	1 unit	Glow-wire test	650/30 [ Temperature 650 °C, duration 30 s]
Gear	-	Flammability mark	NO [-]
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]	CE mark	CE mark
Driver included	Yes	ENEC mark	-
Optic type	WB [ Wide beam]	UL mark	No
Optical cover/lens type	O [ Opal]	Constant light output	Yes
Luminaire light beam spread	110°	Spare parts available	No
		Number of products on MCB (16 A type B)	24

# Greenperform Batten

LED engine type	LED
<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Power factor (min.)	0.9
Power factor (nom.)	0.9
<b>Controls and Dimming</b>	
Dimmable	Yes
<b>Mechanical and Housing</b>	
Housing material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polymethyl methacrylate
Gear tray material	Steel
Optical cover/lens finish	Opal
Colour	White
<b>Approval and Application</b>	
Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK03 [ 0.3 J]
<b>Initial Performance (IEC Compliant)</b>	
Initial luminous flux	6000 lm
Luminous flux tolerance	+/-7.5%

Initial LED luminaire efficacy	118 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	80
Initial chromaticity	-
Initial input power	51 W
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Median useful life L70B50	50000 h
---------------------------	---------

## Application Conditions

Ambient temperature range	0 to +40 °C
Maximum dimming level	1% (depends on dimmer, ELV)

## Product Data

Full product code	911401831999
Order product name	BN208X LED60/NW L1500 ACW2 OS ACF EN
Order code	911401831999
Local code	BN208X53WNWAC
Numerator – quantity per pack	1
SAP numerator – packs per outer box	1
Material no. (12 NC)	911401831999
SAP net weight (piece)	2.300 kg



## Dimensional drawing

—

Greenperform Batten BN208C/BN208X

## Greenperform Batten

