



# ClearFlood Large

## BVP651 LED600-4S/740 DX60 ALU PSU

ClearFlood large - LED module 60000 lm - LED - Power supply unit - Distribution extra-wide 60 - Grey

ClearFlood Large is designed to meet the requirements of a wide range of floodlighting applications. It also includes all the necessary control features and interfaces to make it future-proof and even more efficient. ClearFlood Large lets you choose the exact number of lumens you need for your application. Incorporating extremely high-efficiency optics and state-of-the-art LEDs, it is a highly competitive solution offering an outstanding lux/euro ratio and energy savings of up to 40% (without the use of additional controls). The wide choice of optics ensures maximum application coverage. ClearFlood Large is easy to install – you simply plug it in and select the best option for your needs. Perfect for replacing conventional technology and enabling intelligent lighting control while retaining the same electrical installation and poles.

### Product data

General information		Flammability mark	F [ For mounting on normally flammable surfaces]
Lamp family code	LED600 [ LED module 60000 lm]	CE mark	CE mark
Light source colour	740 neutral white	ENEC mark	ENEC mark
Light source replaceable	Yes	Warranty period	5 years
Number of gear units	2 units	Optic type outdoor	Distribution extra-wide 60
Driver/power unit/transformer	PSU [ Power supply unit]	Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme
Driver included	Yes		
Optical cover/lens type	FG [ Flat glass]		
Luminaire light beam spread	8° - 26° x 82°		
Connection	Connection unit 5-pole		
Cable	-		
Protection class IEC	Safety class I		

# ClearFlood Large

	ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	No
Number of products on MCB (16 A type B)	3
EU RoHS compliant	Yes
LED engine type	LED
Serviceability class	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Product family code	BVP651 [ ClearFlood large]

## Light Technical

Upward light output ratio	0
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°

## Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Inrush current	13 A
Inrush time	1.32 ms
Power factor (min.)	0.97

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Housing material	Aluminium die-cast
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Steel
Mounting device	MBA [ Mounting bracket adjustable]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	817 mm
Overall width	597 mm
Overall height	80 mm
Effective projected area	0.41 m <sup>2</sup>

Colour	Grey
Dimensions (height x width x depth)	80 x 597 x 817 mm (3.1 x 23.5 x 32.2 in)

## Approval and Application

Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [ 5 J vandal-protected]
Surge protection (common/differential)	Luminaire surge protection level up to 4 kV differential mode and 4 kV common mode

## Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	52800 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	139 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	70
Initial chromaticity	(0.380, 0.390) SDCM <5
Initial input power	380 W
Power consumption tolerance	+/-11%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L96

## Application Conditions

Ambient temperature range	-40 to +50 °C
Performance ambient temperature Tq	25 °C

## Product Data

Full product code	871869912905700
Order product name	BVP651 LED600-4S/740 DX60 ALU PSU
EAN/UPC – product	8718699129057
Order code	12905700
Numerator – quantity per pack	1
SAP numerator – packs per outer box	1
Material no. (12 NC)	912300023964
Net Weight (Piece)	24.000 kg



# ClearFlood Large

## Dimensional drawing

← 532 →

ClearFlood BVP650/651

