



Coreline Bollard

BCP155 LED100/WW PSU 220-240V A 7043

LED Module 1000 lm - Warm white - Power supply unit - 220-240 V - Asymmetrical

Coreline Bollard is a professional bollard that will guide people at night time and will integrate very well in most urban landscape thanks to its discreet design.

Product data

General Information		
Number of light sources	1 [1 pc]	
Lamp family code	LED10 [LED Module 1000 lm]	
Light source colour	Warm white	
Light source replaceable	No	
Number of gear units	1 unit	
Driver/power unit/transformer	PSU [Power supply unit]	
Driver included	Yes	
Optical cover/lens type	O [Opal]	
Luminaire light beam spread	135°	
Connection	External connector	
Cable	Cable 0.5 m with cable connector	
Protection class IEC	Safety class I	
Flammability mark	NO [-]	
CE mark	CE mark	
ENEC mark	-	
Warranty period	3 years	
Optic type outdoor	Asymmetrical	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires – January 2018": statistically there	is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	No	
Number of products on MCB (16 A type B)	1	
EU RoHS compliant	Yes	
LED engine type	LED	
Light Technical		
Upward light output ratio	50	
Standard tilt angle post-top	-	
Standard tilt angle side entry	-	
Operating and Electrical		
Input Voltage	220-240 V	
Input frequency	50 or 60 Hz	

Coreline Bollard

Inrush current	13.4 A
Inrush time	21.86 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Extruded aluminium
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Mounting device	Baseplate
Optical cover/lens shape	Cylinder/cylindrical
Optical cover/lens finish	Opal
Overall height	1000 mm
Overall diameter	100 mm
Effective projected area	0.1 m ²
Colour	Dark Grey
Dimensions (height x width x depth)	1000 x NaN x NaN mm (39.4 x NaN x NaN in)

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge protection (common/differential)	6/8 kV

Initial Performance (IEC Compliant)

Initial luminous flux	1000 lm
Luminous flux tolerance	+/-10%

Initial LED luminaire efficacy	80 lm/W
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	>80
Initial chromaticity	(0.434, 0.403) SDCM<5
Initial input power	13 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L70

Application Conditions


Ambient temperature range	-40 to +50 °C
Performance ambient temperature Tq	25 °C

Product Data

Full product code	871869938375600
Order product name	BCP155 LED100/WW PSU 220-240V A 7043
EAN/UPC – product	8718699383756
Order code	38375600
Local code	BCP155WWUA7043
Numerator – quantity per pack	1
SAP numerator – packs per outer box	1
Material no. (12 NC)	912401483109
SAP net weight (piece)	5.700 kg



Dimensional drawing



CoreLine Bollard BCP155

