



# GreenSpace

## DN472B LED20S/830 PSU-E C PCC WH

200mm + anti-glare ring - LED Module, system flux 2000 lm - 830 warm white - Power supply unit DC compatible, external - High-gloss mirror - - - Feed-through connector 3-pole - Dust accumulation-protected, splash-proof - White RAL 9003

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable color performance and high color rendering. The product's long lifetime makes it a true 'fit and forget' solution.

### Product data

General Information		Control interface	
Number of light sources	1 pc	Control interface	-
Lamp family code	LED20S [ LED Module, system flux 2000 lm]	Connection	Feed-through connector 3-pole
Beam angle of light source	- °	Cable	-
Light source color	830 warm white	Protection class IEC	Safety class II
Cap-Base	- [ -]	Glow-wire test	Temperature 750 °C, duration 5 s
Light source replaceable	No	Flammability mark	-
Number of gear units	1 unit	CE mark	CE mark
Gear	-	ENEC mark	ENEC mark
Driver/power unit/transformer	Power supply unit DC compatible, external	Warranty period	5 years
Driver included	Yes	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example
Optic type	High-gloss mirror		
Luminaire light beam spread	120°		
Emergency lighting	-		

	B10. Therefore, the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB of 16 A type B	36
EU RoHS compliant	Yes
Service tag	Yes
Product family code	DN471B [ 200mm + anti-glare ring]
Unified glare rating CEN	22

#### Light Technical

Optical cover/lens type accessory	-
-----------------------------------	---

#### Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Control signal voltage	-
Initial CLO power consumption	- W W
Average CLO power consumption	- W W
Inrush current	15.8 A
Inrush time	0.224 ms
Power Factor (Min)	0.9

#### Controls and Dimming

Dimmable	No
----------	----

#### Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Clear
Overall height	94 mm
Overall diameter	216 mm
Color	White RAL 9003
Dimensions (Height x Width x Depth)	94 x NaN x NaN mm (3.7 x NaN x NaN in)

#### Approval and Application

Ingress protection code	IP54 [ Dust accumulation-protected, splash-proof]
-------------------------	---

Mech. impact protection code	IK06 [ 1 J]
------------------------------	-------------

#### Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	2025 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	120 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	>80
Initial chromaticity	(0.44, 0.40) SDCM <5
Initial input power	16.8 W
Power consumption tolerance	+/-10%

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

#### Application Conditions


Ambient temperature range	-15 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Yes

#### Product Data

Full product code	871869938470800
Order product name	DN472B LED20S/830 PSU-E C PCC WH
EAN/UPC - Product	8718699384708
Order code	912500100070
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912500100070
Net Weight (Piece)	1.000 kg




Dimensional drawing




GreenSpace gen2 DN460B-DN473B

Photometric data



IFGU1\_DN472BPSU-E1xLED205830CPCC



OFPC1\_DN472BPSU-E1xLED205830CPCC

