



OccuSwitch

LRM1070/00 SENSr MOV DET ST

Movement detector with a built-in switch -up to 6 A - - controls max 25 m² area - Basic


Movement detector with a built-in switch -up to 6 A - controls max 25 m² area - Basic

Product data

Product Data	
Full product code	871155973138499
Order product name	LRM1070/00 SENSr MOV DET ST
EAN/UPC - Product	8711559731384
Order code	913700327803
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	42
Material Nr. (12NC)	913700327803
Net Weight (Piece)	0.200 kg

Dimensional drawing



LRM1070/00 SENSr MOV DET ST