



# OccuSwitch

## LRM1080/00 SENSR MOV DET ST IR

Movement detector with a built-in switch -up to 6 A - - controls max 25 m<sup>2</sup> area - Advanced


Movement detector with a built-in switch -up to 6 A - controls max 25 m<sup>2</sup> area - Advanced

### Product data

Product Data	
Full product code	871155973140799
Order product name	LRM1080/00 SENSR MOV DET ST IR
EAN/UPC - Product	8711559731407
Order code	913700327903
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	42
Material Nr. (12NC)	913700327903
Net Weight (Piece)	0.200 kg

### Dimensional drawing



LRM1080/00 SENSR MOV DET ST IR